

Service unit combinations FRC-K, D series










FESTO



Service unit combinations FRC-K, D series, metal design

FESTO

Product range overview D series service units, metal design

Type		Size	Pneumatic connection										Pressure regulation range [bar]			Grade of filtration			
																[µm]			
			M5	M7	G1/8	G1/4	G3/8	G1/2	G3/4	G1	QS4	QS6	0.5 ...	0.5 ...	2.5 ...	0.01	1	5	40
		Micro	■	■	■	–	–	–	–	–	■	■	■	–	–	–	–	■	–
		Mini	–	–	■	■	■	–	–	–	–	–	■	■	–	–	–	■	■
		Midi	–	–	–	■	■	■	■	–	–	–	■	■	–	–	–	■	■
		Maxi	–	–	–	–	–	■	■	■	–	–	■	■	–	–	–	■	■
Service unit combinations																			
		Micro	–																
		Mini	–	–	■	■	–	–	–	–	–	–	–	■	■	–	–	–	■
		Midi	–	–	–	■	■	■	–	–	–	–	–	■	■	–	–	–	■
		Maxi	–	–	–	–	–	■	■	–	–	–	–	■	■	–	–	–	■
		Micro	–																
		Mini	–	–	■	■	–	–	–	–	–	–	–	■	■	–	–	–	■
		Midi	–	–	–	■	■	■	–	–	–	–	–	■	■	–	–	–	■
		Maxi	–	–	–	–	–	■	■	–	–	–	–	■	■	–	–	–	■
Individual devices																			
		Micro	■	■	■	–	–	–	–	–	■	■	■	–	–	–	–	■	–
		Mini	–	–	■	■	■	–	–	–	–	–	■	■	–	–	–	■	■
		Midi	–	–	–	■	■	■	■	–	–	–	■	■	–	–	–	■	■
		Maxi	–	–	–	–	–	■	■	■	–	–	■	■	–	–	–	■	■
		Micro	■	■	■	–	–	–	–	–	■	■	–	–	–	–	–	■	–
		Mini	–	–	■	■	■	–	–	–	–	–	–	–	–	–	–	■	■
		Midi	–	–	–	■	■	■	■	–	–	–	–	–	–	–	–	■	■
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–	–	–	–	■	■
		Micro	–																
		Mini	–	–	■	■	■	–	–	–	–	–	–	–	–	■	■	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–	–	■	■	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–	–	■	■	–	–
		Micro	–																
		Mini	–	–	■	■	■	–	–	–	–	–	–	–	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–	–	–	–	–	–
		Micro	–																
		Mini	–	–	■	■	■	–	–	–	–	–	–	–	■	■	–	–	
		Midi	–	–	–	■	■	■	■	–	–	–	–	–	■	■	–	–	
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–	■	■	–	–	
		Micro	■	■	■	–	–	–	–	–	■	■	■	–	–	–	–	–	–
		Mini	–	–	■	■	■	–	–	–	–	–	■	■	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	■	■	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	■	■	–	–	–	–	–

Service unit combinations FRC-K, D series, metal design

FESTO








Product range overview D series service units, metal design

Type	Size	Bowl guard		Condensate drain			Pressure indication		Actuator lock		Supply voltage			Options			→ Page/ Internet
		Metal bowl guard	Plastic bowl	Manual rotary	Semi-automatic	Fully automatic	With pressure gauge	Without pressure gauge	Rotary knob with detent	Rotary knob with integrated lock	24 V DC	110 V AC	230 V AC	Directly actuated pressure regulator with integrated return flow function	Pilot actuated pressure regulator with integrated return flow function	Differential pressure indicator	
Service units																	
FRC/FRCS	Micro	–	■	■	■	–	■	■	■	–	–	–	–	–	–	–	frc
	Mini	■	–	■	–	■	■	■	■	■	–	–	–	–	–	–	
	Midi	■	–	■	–	■	■	■	■	■	–	–	–	–	–	–	
	Maxi	■	–	■	–	■	■	■	■	■	–	–	–	■	■	–	
Service unit combinations																	
FRC-K	Micro	–															6
	Mini	■	–	■	–	■	■	–	■	–	–	–	–	–	–	–	
	Midi	■	–	■	–	■	■	–	■	–	–	–	–	–	–	–	
	Maxi	■	–	■	–	■	■	–	■	–	–	–	–	■	■	–	
LFR-K LFRS-K	Micro	–															lfr
	Mini	■	–	■	–	■	■	–	■	■	■	–	–	–	–	–	
	Midi	■	–	■	–	■	■	–	■	■	■	–	–	–	–	–	
	Maxi	■	–	■	–	■	■	–	■	■	■	–	–	■	■	–	
Individual devices																	
Filter regulators LFR/LFRS	Micro	–	■	■	■	–	■	■	■	–	–	–	–	–	–	–	lfr
	Mini	■	–	■	–	■	■	■	■	■	–	–	–	–	–	–	
	Midi	■	–	■	–	■	■	■	■	■	–	–	–	–	–	–	
	Maxi	■	–	■	–	■	■	■	■	■	–	–	–	■	■	–	
Filters LF	Micro	–	■	■	■	–	–	–	–	–	–	–	–	–	–	–	lf
	Mini	■	–	■	–	■	–	–	–	–	–	–	–	–	–	–	
	Midi	■	–	■	–	■	–	–	–	–	–	–	–	–	–	–	
	Maxi	■	–	■	–	■	–	–	–	–	–	–	–	–	–	–	
Fine and micro filters LFMA/LFMB	Micro	–															lfma, lfmb
	Mini	■	–	■	–	■	–	–	–	–	–	–	–	–	–	■	
	Midi	■	–	■	–	■	–	–	–	–	–	–	–	–	–	■	
	Maxi	■	–	■	–	■	–	–	–	–	–	–	–	–	–	■	
Active carbon filters LFX	Micro	–															lfx
	Mini	■	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
	Midi	■	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
	Maxi	■	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
Filter combinations LFMBA	Micro	–															lfmba
	Mini	■	–	■	–	■	–	–	–	–	–	–	–	–	–	■	
	Midi	■	–	■	–	■	–	–	–	–	–	–	–	–	–	■	
	Maxi	■	–	■	–	■	–	–	–	–	–	–	–	–	–	■	
Pressure regulators LR/LRS	Micro	–	–	–	–	–	■	■	■	–	–	–	–	–	–	–	lr
	Mini	–	–	–	–	–	■	■	■	■	–	–	–	■	–	–	
	Midi	–	–	–	–	–	■	■	■	■	–	–	–	■	–	–	
	Maxi	–	–	–	–	–	■	■	■	■	–	–	–	■	■	–	

Service unit combinations FRC-K, D series, metal design

FESTO

Product range overview D series service units, metal design

Type		Size	Pneumatic connection										Pressure regulation range [bar]	
			M5	M7	G1/8	G1/4	G3/8	G1/2	G3/4	G1	QS4	QS6	0.5 ... 7	0.5 ... 12
Individual devices														
Pressure regulators LRB/LRBS		Micro	–											
		Mini	–	–	–	■	–	–	–	–	–	–	■	■
		Midi	–	–	–	–	■	–	–	–	–	–	■	■
		Maxi	–											
Pressure regulator combinations LRB-K		Micro	–											
		Mini	–	–	–	■	■	–	–	–	–	–	■	■
		Midi	–	–	–	–	■	■	–	–	–	–	■	■
		Maxi	–											
Lubricators LOE		Micro	■	■	■	–	–	–	–	–	■	■	–	–
		Mini	–	–	■	■	■	–	–	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–
On-off valves HE		Micro	–											
		Mini	–	–	■	■	■	–	–	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–
On-off valves, electrical HEE		Micro	–											
		Mini	–	–	■	■	■	–	–	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–
On-off valves, pneumatic HEP		Micro	–											
		Mini	–	–	■	■	■	–	–	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–
Soft-start valves HEL		Micro	–											
		Mini	–	–	■	■	■	–	–	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–
Membrane air dryers LDM1		Micro	–											
		Mini	–											
		Midi	–											
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–
Branching modules FRM		Micro	–											
		Mini	–	–	■	■	■	–	–	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–
Distributor block FRZ		Micro	–	–	–	–	–	–	–	–	–	–	–	–
		Mini	–	–	–	–	–	–	–	–	–	–	–	–
		Midi	–	–	–	–	–	–	–	–	–	–	–	–
		Maxi	–	–	–	–	–	–	–	–	–	–	–	–

Service unit combinations FRC-K, D series, metal design






Product range overview D series service units, metal design

Type	Size	Bowl guard		Pressure indication		Actuator lock		Supply voltage			Options		→ Page/ Internet
		Metal bowl guard	Plastic bowl	With pressure gauge	Without pressure gauge	Rotary knob with detent	Rotary knob with integrated lock	24 V DC	110 V AC	230 V AC	Non-return function	Pressure switch	
Individual devices													
Pressure regulators LRB/LRBS	Micro	-											lrb
	Mini	-	-	-	■	■	■	-	-	-	-	-	
	Midi	-	-	-	■	■	■	-	-	-	-	-	
	Maxi	-	-										
Pressure regulator combinations LRB-K	Micro	-											lrb
	Mini	-	-	-	■	■	-	-	-	-	-	-	
	Midi	-	-	-	■	■	-	-	-	-	-	-	
	Maxi	-	-										
Lubricators LOE	Micro	-	■	-	■	-	-	-	-	-	-	-	loe
	Mini	■	-	-	■	-	-	-	-	-	-	-	
	Midi	■	-	-	■	-	-	-	-	-	-	-	
	Maxi	■	-	-	■	-	-	-	-	-	-	-	
On-off valves HE	Micro	-											he
	Mini	-	-	-	■	■	-	-	-	-	-	-	
	Midi	-	-	-	■	■	-	-	-	-	-	-	
	Maxi	-	-	-	■	■	-	-	-	-	-	-	
On-off valves, electrical HEE	Micro	-											hee
	Mini	-	-	-	■	-	-	■	■	■	-	-	
	Midi	-	-	-	■	-	-	■	■	■	-	-	
	Maxi	-	-	-	■	-	-	■	■	■	-	-	
On-off valves, pneumatic HEP	Micro	-											hep
	Mini	-	-	-	■	-	-	-	-	-	-	-	
	Midi	-	-	-	■	-	-	-	-	-	-	-	
	Maxi	-	-	-	■	-	-	-	-	-	-	-	
Soft-start valves HEL	Micro	-											hel
	Mini	-	-	-	■	-	-	-	-	-	-	-	
	Midi	-	-	-	■	-	-	-	-	-	-	-	
	Maxi	-	-	-	■	-	-	-	-	-	-	-	
Membrane air dryers LDM1	Micro	-											ldm1
	Mini	-											
	Midi	-											
	Maxi	■	-	-	■	-	-	-	-	-	-	-	
Branching modules FRM	Micro	-											frm
	Mini	-	-	-	■	-	-	-	-	-	■	■	
	Midi	-	-	-	■	-	-	-	-	-	■	■	
	Maxi	-	-	-	■	-	-	-	-	-	■	■	
Distributor block FRZ	Micro	-	-	-	■	-	-	-	-	-	-	-	frz
	Mini	-	-	-	■	-	-	-	-	-	-	-	
	Midi	-	-	-	■	-	-	-	-	-	-	-	
	Maxi	-	-	-	■	-	-	-	-	-	-	-	

Service unit combinations FRC-K, D series, metal design

FESTO


Product range overview

FRC Rotary knob with detent	 KA	 KB	 KC	 KE	 KF
Individual devices					
On-off valve, manual	–	–	■	–	■
Filter regulator with pressure gauge	■	■	■	■	■
Branching module	■	–	–	–	–
Branching module with pressure switch	–	■	■	–	■
Lubricator	■	■	■	■	■
On-off valve with solenoid coil 24 V DC	–	–	–	■	■
Soft-start valve	–	–	–	■	■
Mounting bracket	■	■	■	■	■
→ Page/Internet	9	12	15	18	21

Service unit combinations FRC-K, D series, metal design

Peripherals overview

FESTO



Note

The choice of accessories depends on the selected service unit combination. The example shows the service unit combination FRC-KF.

Range of accessories

→ Peripherals pages of the individual devices

Mounting attachments and accessories		→ Page/ Internet
1	Regulator lock LRVS	lrvs-d
2	Padlock LRVS	lrvs-d
3	Plug socket MSSD-C	24
4	Angled plug socket PEV-...-WD-LED	24
5	Plug socket with cable KMEB-1	24
6	Plug socket MSSD-EB	24

Service unit combinations FRC-K, D series, metal design

FESTO

Type codes


		FRC	–	1/2	–	D	–	DI	–	MAXI	–	KA	–	A
Basic function														
FRC	Service unit combination													
Pneumatic connection														
1/8	Thread G1/8													
1/4	Thread G1/4													
3/8	Thread G3/8													
1/2	Thread G1/2													
3/4	Thread G3/4													
Series														
D	Series													
Function (Maxi size only)														
DI	Directly actuated pressure regulator with integrated return flow function													
Size														
MINI	Grid dimension for individual device 40 mm (without connecting plates)													
MIDI	Grid dimension for individual device 55 mm (without connecting plates)													
MAXI	Grid dimension for individual device 66 mm (without connecting plates)													
Options for service unit combinations														
KA	Filter regulator, branching module and lubricator													
KB	Filter regulator, branching module with pressure switch and lubricator													
KC	On-off valve, filter regulator, branching module with pressure switch and lubricator													
KE	Filter regulator, lubricator, on-off valve with solenoid coil 24 V DC, soft-start valve													
KF	On-off valve, filter regulator, lubricator, on-off valve with solenoid coil 24 V DC, soft-start valve, branching module with pressure switch													
Condensate drain														
	Turned manually													
A	Fully automatic													

Service unit combinations FRC-KA, D series, metal design

FESTO

Technical data combination FRC-KA

Function



Flow rate
650 ... 8200 l/min

Temperature range
-10 ... +60 °C

 Input pressure
1 ... 16 bar

- Filter regulator LFR
 - grade of filtration 40 µm
 - metal bowl guard
 - condensate drain, turned manually or fully automatic
 - rotary knob with detent
 - pressure gauge
- Branching module FRM
- Lubricator LOE
 - metal bowl guard
- Mounting accessories



- For lubricated and unlubricated compressed air
- Two connections for unlubricated compressed air supply
- One connection for lubricated compressed air supply

General technical data							
Size	Mini		Midi			Maxi	
Pneumatic connection	G1/8	G1/4	G1/4	G3/8	G1/2	G1/2	G3/4
Operating medium	Compressed air						
Type of mounting	Via accessories						
	In-line installation						
Assembly position	Vertical ±5°						
Grade of filtration [µm]	40						
Max. hysteresis [bar]	0.25	0.2	0.25	0.35	0.3	0.1	0.2
Pressure regulation range [bar]	0.5 ... 12						
Pressure indication	Via pressure gauge						
Max. condensate volume [cm³]	22		43			80 ¹⁾	
Input pressure [bar]							
Condensate drain	turned manually	1 ... 16					
	fully automatic	2 ... 12					

1) The max. condensate volume for the FRC...-DI-MAXI-KA is 43 cm³.
Note: This product conforms to ISO 1179-1 and to ISO 228-1

Service unit combinations FRC-KA, D series, metal design

FESTO

Technical data combination FRC-KA

Standard nominal flow rate ¹⁾ qnN [l/min]					
Connection	G1/8	G1/4	G3/8	G1/2	G3/4
Mini					
FRC-...-D-...	650	980	–	–	–
Midi					
FRC-...-D-...	–	1400	2100	2500	–
Maxi					
FRC-...-D-...	–	–	–	7500	8200
Maxi – Directly actuated pressure regulator with integrated return flow function					
FRC-...-D-DI-...	–	–	–	5200	5800

1) Measured at p1 = 10 bar, p2 = 6 bar and Δp = 1 bar.

Ambient conditions		
Size	Mini	Midi
Ambient temperature [°C]	–10 ... +60	
Temperature of medium [°C]	–10 ... +60	
Corrosion resistance class CRC ¹⁾	2	

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Weight [g]				
Size	Mini	Midi	Maxi	
			D	D-DI
FRC	1000	2400	3500	3700

Note

Materials → Technical data of the individual devices

Standard flow rate qn as a function of the output pressure p2

FRC-1/2-D-DI-MAXI-KA(-A)



Primary pressure p1 = 10 bar

Service unit combinations FRC-KA, D series, metal design


FESTO

Technical data combination FRC-KA

Dimensions

Download CAD Data → www.festo.com/us/cad

FRC-...-KA



3 Installation dimensions

→ Flow direction

Type	B5	B6	D1	H1	H2	H3	L1	L2	L3	L4	L5	L8	L9	L10	T1	T2
Mini																
FRC-...-D-MINI-KA (-A)	144	132	4.3	43	17.5	17.5	193	124	60	68	100	15	19	3	39	95
Midi																
FRC-...-D-MIDI-KA (-A)	195	180	5.3	70	24.5	35.5	250	152	80	99	120	15	19	3	47	114
Maxi																
FRC-...-D-MAXI-KA (-A)	228	212	5.3	70	24.5	35.5	252	171	90	82	150	15	19	3	53	126
FRC-...-D-DI-MAXI-KA (-A)							275			105						

Ordering data

Size	Connection	Condensate drain turned manually		Condensate drain fully automatic	
		Part No.	Type	Part No.	Type
Mini	G1/8	185791	FRC-1/8-D-MINI-KA	185792	FRC-1/8-D-MINI-KA-A
	G1/4	185793	FRC-1/4-D-MINI-KA	185794	FRC-1/4-D-MINI-KA-A
Midi	G1/4	185795	FRC-1/4-D-MIDI-KA	185796	FRC-1/4-D-MIDI-KA-A
	G3/8	185797	FRC-3/8-D-MIDI-KA	185798	FRC-3/8-D-MIDI-KA-A
	G1/2	185799	FRC-1/2-D-MIDI-KA	185800	FRC-1/2-D-MIDI-KA-A
Maxi	G1/2	186053	FRC-1/2-D-MAXI-KA	186054	FRC-1/2-D-MAXI-KA-A
	G3/4	185801	FRC-3/4-D-MAXI-KA	185802	FRC-3/4-D-MAXI-KA-A
Directly actuated pressure regulator with integrated return flow function					
Maxi	G1/2	192468	FRC-1/2-D-DI-MAXI-KA	192478	FRC-1/2-D-DI-MAXI-KA-A
	G3/4	192473	FRC-3/4-D-DI-MAXI-KA	192483	FRC-3/4-D-DI-MAXI-KA-A


Note: This product conforms to ISO 1179-1 and to ISO 228-1

Service unit combinations FRC-KB, D series, metal design

FESTO

Technical data combination FRC-KB

Function




Flow rate
650 ... 8200 l/min

Temperature range
-10 ... +60 °C

 Input pressure
1 ... 16 bar

- Filter regulator LFR
 - grade of filtration 40 µm
 - metal bowl guard
 - condensate drain, turned manually or fully automatic
 - rotary knob with detent
 - pressure gauge
- Branching module FRM
 - Pressure switch without display
- Lubricator LOE
 - metal bowl guard
- Mounting accessories



- Electrical pressure monitoring with adjustable switching pressure
- For lubricated and unlubricated compressed air
- One connection for unlubricated compressed air supply
- One connection for lubricated compressed air supply

General technical data							
Size	Mini		Midi			Maxi	
Pneumatic connection	G1/8	G1/4	G1/4	G3/8	G1/2	G1/2	G3/4
Operating medium	Compressed air						
Type of mounting	Via accessories						
	In-line installation						
Assembly position	Vertical ±5°						
Grade of filtration [µm]	40						
Max. hysteresis [bar]	0.25	0.2	0.25	0.35	0.35	0.1	0.2
Pressure regulation range [bar]	0.5 ... 12						
Pressure indication	Via pressure gauge						
Max. condensate volume [cm ³]	22		43			80 ¹⁾	
Input pressure [bar]							
Condensate drain	turned manually	1 ... 16					
	fully automatic	2 ... 12					

1) The max. condensate volume for the FRC...-DI-MAXI-KB is 43 cm³.
Note: This product conforms to ISO 1179-1 and to ISO 228-1

Service unit combinations FRC-KB, D series, metal design

FESTO

Technical data combination FRC-KB

Standard nominal flow rate ¹⁾ qnN [l/min]					
Connection	G ¹ / ₈	G ¹ / ₄	G ³ / ₈	G ¹ / ₂	G ³ / ₄
Mini					
FRC-...-D-...	650	980	–	–	–
Midi					
FRC-...-D-...	–	1400	2100	2500	–
Maxi					
FRC-...-D-...	–	–	–	7500	8200
Maxi – Directly actuated pressure regulator with integrated return flow function					
FRC-...-D-DI-...	–	–	–	5000	6000

1) Measured at p₁ = 10 bar, p₂ = 6 bar and Δp = 1 bar.

Ambient conditions		Mini	Midi	Maxi
Size				
Ambient temperature	[°C]	–10 ... +60		
Temperature of medium	[°C]	–10 ... +60		
Corrosion resistance class	CRC ¹⁾	2		

1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Weight [g]				
Size	Mini	Midi	Maxi	
			D	D-DI
FRC	1200	2600	3500	3700

Note

Materials → Technical data of the individual devices

Standard flow rate qn as a function of the output pressure p₂

FRC-1/2-D-DI-MAXI-KB(-A)




Primary pressure p₁ = 10 bar

Service unit combinations FRC-KB, D series, metal design

FESTO

Technical data combination FRC-KB



Type	B5	B6	D1	H1	H2	H3	L1	L2	L3	L4	L5	L9	L10	T1	T2	T3	T5
Mini																	
FRC-...-D-MINI-KB (-A)	144	132	4.3	43	17.5	17.5	193	124	60	68	100	19	3	39	95	97	15
Midi																	
FRC-...-D-MIDI-KB (-A)	195	180	5.3	70	24.5	35.5	250	152	80	99	120	19	3	47	114	105	15
Maxi																	
FRC-...-D-MAXI-KB (-A)	228	212	5.3	70	24.5	35.5	252	171	90	82	150	19	3	53	126	111	15
FRC-...-D-DI-MAXI-KB (-A)							275			105							

Ordering data					
Size	Connection	Condensate drain turned manually		Condensate drain fully automatic	
		Part No.	Type	Part No.	Type
Mini	G1/8	185803	FRC-1/8-D-MINI-KB	185804	FRC-1/8-D-MINI-KB-A
	G1/4	185805	FRC-1/4-D-MINI-KB	185806	FRC-1/4-D-MINI-KB-A
Midi	G1/4	185807	FRC-1/4-D-MIDI-KB	185808	FRC-1/4-D-MIDI-KB-A
	G3/8	185809	FRC-3/8-D-MIDI-KB	185810	FRC-3/8-D-MIDI-KB-A
	G1/2	185811	FRC-1/2-D-MIDI-KB	185812	FRC-1/2-D-MIDI-KB-A
Maxi	G1/2	186055	FRC-1/2-D-MAXI-KB	186056	FRC-1/2-D-MAXI-KB-A
	G3/4	185813	FRC-3/4-D-MAXI-KB	185814	FRC-3/4-D-MAXI-KB-A
Directly actuated pressure regulator with integrated return flow function					
Maxi	G1/2	192469	FRC-1/2-D-DI-MAXI-KB	192479	FRC-1/2-D-DI-MAXI-KB-A
	G3/4	192474	FRC-3/4-D-DI-MAXI-KB	192484	FRC-3/4-D-DI-MAXI-KB-A


Note: This product conforms to ISO 1179-1 and to ISO 228-1

Service unit combinations FRC-KC, D series, metal design

FESTO

Technical data combination FRC-KC

Function




Flow rate
640 ... 7800 l/min

Temperature range
-10 ... +60 °C

 Input pressure
1 ... 16 bar

- On-off valve HE
 - manually actuated
- Filter regulator LFR
 - grade of filtration 40 µm
 - metal bowl guard
 - condensate drain, turned manually or fully automatic
 - rotary knob with detent
 - pressure gauge
- Branching module FRM
 - pressure switch without display
- Lubricator LOE
 - metal bowl guard
- Mounting accessories



- To ensure safe venting of the system, an additional quick exhaust valve is necessary at the output of the service unit combination
- Electrical pressure monitoring with adjustable switching pressure
- The system is vented when supply air is closed
- For lubricated and unlubricated compressed air
- One connection for unlubricated compressed air supply
- One connection for lubricated compressed air supply

General technical data							
Size	Mini		Midi			Maxi	
Pneumatic connection	G1/8	G1/4	G1/4	G3/8	G1/2	G1/2	G3/4
Operating medium	Compressed air						
Type of mounting	Via accessories						
	In-line installation						
Assembly position	Vertical ±5°						
Grade of filtration [µm]	40						
Max. hysteresis [bar]	0.2	0.2	0.4	0.3	0.3	0.15	0.15
Pressure regulation range [bar]	0.5 ... 12						
Pressure indication	Via pressure gauge						
Max. condensate volume [cm³]	22		43			80 ¹⁾	
Input pressure [bar]							
Condensate drain	turned manually	1 ... 16					
	fully automatic	1.5 ... 12					

1) The max. condensate volume for the FRC...-DI-MAXI-KC is 43 cm³.

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Service unit combinations FRC-KC, D series, metal design

FESTO

Technical data combination FRC-KC

Standard nominal flow rate ¹⁾ qnN [l/min]					
Connection	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{1}{2}$	G $\frac{3}{4}$
Mini					
FRC-...-D-...	640	870	–	–	–
Midi					
FRC-...-D-...	–	1320	1870	2400	–
Maxi					
FRC-...-D-...	–	–	–	6600	7800
Maxi – Directly actuated pressure regulator with integrated return flow function					
FRC-...-D-DI-...	–	–	–	4800	5400

1) Measured at p₁ = 10 bar, p₂ = 6 bar and Δp = 1 bar.

Ambient conditions		
Size	Mini	Midi
Ambient temperature [°C]	–10 ... +60	
Temperature of medium [°C]	–10 ... +60	
Corrosion resistance class CRC ¹⁾	2	

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Weight [g]				
Size	Mini	Midi	Maxi	
			D	D-DI
FRC	1400	3000	4600	4800

Note

Materials → Technical data of the individual devices

Standard flow rate qn as a function of the output pressure p₂

FRC-1/2-D-DI-MAXI-KC(-A)



Primary pressure p₁ = 10 bar

Service unit combinations FRC-KC, D series, metal design


FESTO

Technical data combination FRC-KC

Dimensions

Download CAD Data → www.festo.com/us/cad

FRC-...-KC



3 Installation dimensions

→ Flow direction

Type	B7	B8	D1	H1	H2	H3	L1	L2	L3	L4	L5	L9	L10	T1	T2	T3	T5
Mini																	
FRC-...-D-MINI-KC (-A)	184	172	4.3	43	17.5	17.5	193	124	60	68	100	19	3	39	95	97	15
Midi																	
FRC-...-D-MIDI-KC (-A)	250	235	5.3	70	24.5	35.5	250	152	80	99	120	19	3	47	114	105	15
Maxi																	
FRC-...-D-MAXI-KC (-A)	294	278	5.3	70	24.5	35.5	252	171	90	82	150	19	3	53	126	111	15
FRC-...-D-DI-MAXI-KC (-A)							275			105							

Ordering data

Size	Connection	Condensate drain turned manually		Condensate drain fully automatic	
		Part No.	Type	Part No.	Type
Mini	G1/8	185815	FRC-1/8-D-MINI-KC	185816	FRC-1/8-D-MINI-KC-A
	G1/4	185817	FRC-1/4-D-MINI-KC	185818	FRC-1/4-D-MINI-KC-A
Midi	G1/4	185819	FRC-1/4-D-MIDI-KC	185820	FRC-1/4-D-MIDI-KC-A
	G3/8	185821	FRC-3/8-D-MIDI-KC	185822	FRC-3/8-D-MIDI-KC-A
	G1/2	185823	FRC-1/2-D-MIDI-KC	185824	FRC-1/2-D-MIDI-KC-A
Maxi	G1/2	186057	FRC-1/2-D-MAXI-KC	186058	FRC-1/2-D-MAXI-KC-A
	G3/4	185825	FRC-3/4-D-MAXI-KC	185826	FRC-3/4-D-MAXI-KC-A
Directly actuated pressure regulator with integrated return flow function					
Maxi	G1/2	192470	FRC-1/2-D-DI-MAXI-KC	192480	FRC-1/2-D-DI-MAXI-KC-A
	G3/4	192475	FRC-3/4-D-DI-MAXI-KC	192485	FRC-3/4-D-DI-MAXI-KC-A


Note: This product conforms to ISO 1179-1 and to ISO 228-1

Service unit combinations FRC-KE, D series, metal design

FESTO

Technical data combination FRC-KE

Function



Flow rate

550 ... 6000 l/min


Temperature range

-10 ... +60 °C



Input pressure
3 ... 16 bar

- Filter regulator LFR
 - grade of filtration 40 µm
 - metal bowl guard
 - condensate drain, turned manually or fully automatic
 - rotary knob with detent
 - pressure gauge
- Lubricator LOE
 - metal bowl guard
- On-off valve HEE
 - solenoid actuated
 - 24 V DC
- Soft-start valve HEL
 - pneumatically actuated
- Mounting accessories



- Gradual pressure build-up prevents sudden, unpredictable movements
- When supply pressure is closed, quick venting ensures rapid pressure reduction
- For lubricated compressed air

General technical data							
Size	Mini		Midi			Maxi	
Pneumatic connection	G1/8	G1/4	G1/4	G3/8	G1/2	G1/2	G3/4
Operating medium	Compressed air						
Type of mounting	Via accessories						
	In-line installation						
Assembly position	Vertical ±5°						
Grade of filtration [µm]	40						
Max. hysteresis [bar]	0.15	0.18	0.25	0.35	0.4	0.3	0.3
Pressure regulation range [bar]	2.5 ... 12						
Pressure indication	Via pressure gauge						
Max. condensate volume [cm³]	22		43			80 ¹⁾	
Input pressure [bar]							
Condensate drain	turned manually	3 ... 16					
	fully automatic	3 ... 12					

1) The max. condensate volume for the FRC-...-DI-MAXI-KE is 43 cm³.

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Service unit combinations FRC-KE, D series, metal design

FESTO

Technical data combination FRC-KE

Standard nominal flow rate ¹⁾ qnN [l/min]					
Connection	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{1}{2}$	G $\frac{3}{4}$
Mini					
FRC-...-D-...	550	650	–	–	–
Midi					
FRC-...-D-...	–	1100	1420	1590	–
Maxi					
FRC-...-D-...	–	–	–	3500	3800
Maxi – Directly actuated pressure regulator with integrated return flow function					
FRC-...-D-DI-...	–	–	–	5000	6000

1) Measured at p₁ = 10 bar, p₂ = 6 bar and Δp = 1 bar.

Ambient conditions			
Size	Mini	Midi	Maxi
Ambient temperature [°C]	–10 ... +60		
Temperature of medium [°C]	–10 ... +60		
Corrosion resistance class CRC ¹⁾	2		

1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Weight [g]				
Size	Mini	Midi	Maxi	
			D	D-DI
FRC	1200	2800	4200	4400

Note

Materials → Technical data of the individual devices

Standard flow rate qn as a function of the output pressure p₂

FRC-1/2-D-DI-MAXI-KE(-A)




Primary pressure p₁ = 10 bar

Service unit combinations FRC-KE, D series, metal design

FESTO

Technical data combination FRC-KE



Type	B7	B8	D1	H1	H2	H3	L1	L2	L3	L4	L5	L9	L10	T1	T2	T4	T5
Mini																	
FRC-...-D-MINI-KE (-A)	184	172	4.3	43	17.5	17.5	193	124	60	68	100	19	3	39	95	78	15
Midi																	
FRC-...-D-MIDI-KE (-A)	250	235	5.3	70	24.5	35.5	250	152	80	99	120	19	3	47	114	86	15
Maxi																	
FRC-...-D-MAXI-KE (-A)	294	278	5.3	70	24.5	35.5	252	171	90	82	150	19	3	53	126	92	15
FRC-...-D-DI-MAXI-KE (-A)							275			105							

Ordering data						
Size	Connection	Condensate drain turned manually		Condensate drain fully automatic		
		Part No.	Type	Part No.	Type	
Mini	G1/8	185827	FRC-1/8-D-MINI-KE	185828	FRC-1/8-D-MINI-KE-A	
	G1/4	185829	FRC-1/4-D-MINI-KE	185830	FRC-1/4-D-MINI-KE-A	
Midi	G1/4	185831	FRC-1/4-D-MIDI-KE	185832	FRC-1/4-D-MIDI-KE-A	
	G3/8	185833	FRC-3/8-D-MIDI-KE	185834	FRC-3/8-D-MIDI-KE-A	
	G1/2	185835	FRC-1/2-D-MIDI-KE	185836	FRC-1/2-D-MIDI-KE-A	
Maxi	G1/2	186059	FRC-1/2-D-MAXI-KE	186060	FRC-1/2-D-MAXI-KE-A	
	G3/4	185837	FRC-3/4-D-MAXI-KE	185838	FRC-3/4-D-MAXI-KE-A	
Directly actuated pressure regulator with integrated return flow function						
Maxi	G1/2	192471	FRC-1/2-D-DI-MAXI-KE	192481	FRC-1/2-D-DI-MAXI-KE-A	
	G3/4	192476	FRC-3/4-D-DI-MAXI-KE	192486	FRC-3/4-D-DI-MAXI-KE-A	


Note: This product conforms to ISO 1179-1 and to ISO 228-1

Service unit combinations FRC-KF, D series, metal design

FESTO

Technical data combination FRC-KF

Function




Flow rate
530 ... 6000 l/min

Temperature range
-10 ... +60 °C

 Input pressure
3 ... 16 bar

- On-off valve HE
 - manually actuated
- Filter regulator LFR
 - grade of filtration 40 µm
 - metal bowl guard
 - condensate drain, turned manually or fully automatic
 - rotary knob with detent
 - pressure gauge
- Lubricator LOE
 - metal bowl guard
- On-off valve HEE
 - solenoid actuated
 - 24 V DC
- Soft-start valve HEL
 - pneumatically actuated
- Branching module FRM
 - pressure switch without display
- Mounting accessories



- Gradual pressure build-up prevents sudden, unpredictable movements
- To ensure safe venting of the system, an additional quick exhaust valve is necessary at the output of the service unit combination
- For lubricated compressed air
- Two branch connections are available
- Supply pressure can be opened and closed

General technical data								
Size		Mini		Midi		Maxi		
Pneumatic connection		G1/8	G1/4	G1/4	G3/8	G1/2	G1/2	G3/4
Operating medium		Compressed air						
Type of mounting		Via accessories						
		In-line installation						
Assembly position		Vertical ±5°						
Grade of filtration	[µm]	40						
Max. hysteresis	[bar]	0.2	0.3	0.4	0.3	0.35	0.25	0.3
Pressure regulation range	[bar]	2.5 ... 12						
Pressure indication		Via pressure gauge						
Max. condensate volume	[cm ³]	22		43		80 ¹⁾		
Input pressure		[bar]						
Condensate drain	turned manually	3 ... 16						
	fully automatic	3 ... 12						

1) The max. condensate volume for the FRC...-DI-MAXI-KF is 43 cm³.

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Service unit combinations FRC-KF, D series, metal design

FESTO

Technical data combination FRC-KF

Standard nominal flow rate ¹⁾ qnN [l/min]					
Connection	G1/8	G1/4	G3/8	G1/2	G3/4
Mini					
FRC-...-D-...	530	620	–	–	–
Midi					
FRC-...-D-...	–	1060	1150	1220	–
Maxi					
FRC-...-D-...	–	–	–	3400	3700
Maxi – Directly actuated pressure regulator with integrated return flow function					
FRC-...-D-DI-...	–	–	–	5000	6000

1) Measured at p1 = 10 bar, p2 = 6 bar and Δp = 1 bar.

Ambient conditions		
Size	Mini	Midi
Ambient temperature [°C]	–10 ... +60	
Temperature of medium [°C]	–10 ... +60	
Corrosion resistance class CRC ¹⁾	2	

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Weight [g]				
Size	Mini	Midi	Maxi	
			D	D-DI
FRC	1800	4000	6300	6500

Note

Materials → Technical data of the individual devices

Standard flow rate qn as a function of the output pressure p2

FRC-1/2-D-DI-MAXI-KF(-A)



Primary pressure p1 = 10 bar

Service unit combinations FRC-KF, D series, metal design


FESTO

Technical data combination FRC-KF

Dimensions

Download CAD Data → www.festo.com/us/cad

FRC-...-KF



3 Installation dimensions

→ Flow direction

Type	B9	B10	D1	H1	H2	H3	L1	L2	L3	L4	L5	L9	L10	T1	T2	T3	T4	T5
Mini																		
FRC-...-D-MINI-KF (-A)	264	252	4.3	43	17.5	17.5	193	124	60	68	100	19	3	39	95	97	78	15
Midi																		
FRC-...-D-MIDI-KF (-A)	360	344	5.3	70	24.5	35.5	250	152	80	99	120	19	3	47	114	105	86	15
Maxi																		
FRC-...-D-MAXI-KF (-A)	426	410	5.3	70	24.5	35.5	252	171	90	82	150	19	3	53	126	111	92	15
FRC-...-D-DI-MAXI-KF (-A)							275											

Ordering data

Size	Connection	Condensate drain turned manually		Condensate drain fully automatic	
		Part No.	Type	Part No.	Type
Mini	G $\frac{1}{8}$	185839	FRC- $\frac{1}{8}$ -D-MINI-KF	185840	FRC- $\frac{1}{8}$ -D-MINI-KF-A
	G $\frac{1}{4}$	185841	FRC- $\frac{1}{4}$ -D-MINI-KF	185842	FRC- $\frac{1}{4}$ -D-MINI-KF-A
Midi	G $\frac{1}{4}$	185843	FRC- $\frac{1}{4}$ -D-MIDI-KF	185844	FRC- $\frac{1}{4}$ -D-MIDI-KF-A
	G $\frac{3}{8}$	185845	FRC- $\frac{3}{8}$ -D-MIDI-KF	185846	FRC- $\frac{3}{8}$ -D-MIDI-KF-A
	G $\frac{1}{2}$	185847	FRC- $\frac{1}{2}$ -D-MIDI-KF	185848	FRC- $\frac{1}{2}$ -D-MIDI-KF-A
Maxi	G $\frac{1}{2}$	186061	FRC- $\frac{1}{2}$ -D-MAXI-KF	186062	FRC- $\frac{1}{2}$ -D-MAXI-KF-A
	G $\frac{3}{4}$	185849	FRC- $\frac{3}{4}$ -D-MAXI-KF	185850	FRC- $\frac{3}{4}$ -D-MAXI-KF-A
Directly actuated pressure regulator with integrated return flow function					
Maxi	G $\frac{1}{2}$	192472	FRC- $\frac{1}{2}$ -D-DI-MAXI-KF	192482	FRC- $\frac{1}{2}$ -D-DI-MAXI-KF-A
	G $\frac{3}{4}$	192477	FRC- $\frac{3}{4}$ -D-DI-MAXI-KF	192487	FRC- $\frac{3}{4}$ -D-DI-MAXI-KF-A

Note: This product conforms to ISO 1179-1 and to ISO 228-1


Service unit combinations FRC-K, D series

Accessories

FESTO

Ordering data – Angled socket PEV					Technical data → Internet: pev-1/4	
	Description	Operating voltage range	Electrical connection	Switching status display	Part No.	Type
	for PEV-1/4-...-OD	15 ... 30 V DC	4-pin	Yellow LED	164274	PEV-1/4-WD-LED-24
		≤ 230 V AC	4-pin	Yellow LED	164275	PEV-1/4-WD-LED-230
		≤ 180 V DC				

Ordering data – Plug socket MSSD					Technical data → Internet: mssd	
	Description	Operating voltage range	Electrical connection	Type of mounting cable connection	Part No.	Type
	for PEV-1/4-...-OD	≤ 250 V AC/DC	3-pin	Clamping screws	171157	MSSD-C-4P
	for on-off valve HEE	≤ 250 V AC/DC	3-pin	Clamping screws	151687	MSSD-EB
			4-pin	Insulation displacement technology	192745	MSSD-EB-S-M14

Ordering data – Plug socket with cable KMEB						Technical data → Internet: kmeb	
	Description	Operating voltage range	Electrical connection	Switching status display	Cable length [m]	Part No.	Type
	for on-off valve HEE	24 V DC	3-pin	LED	2.5	151688	KMEB-1-24-2,5-LED
					5	151689	KMEB-1-24-5-LED
					10	193457	KMEB-1-24-10-LED
		230 V AC	3-pin	–	2.5	151690	KMEB-1-230AC-2,5
					5	151691	KMEB-1-230AC-5

Ordering data – Illuminating seal MEB-LD				Technical data → Internet: meb	
	Description	Operating voltage range		Part No.	Type
	for plug socket with cable KMEB and plug socket MSSD-EB	12 ... 24 V DC		151717	MEB-LD-12-24DC
		230 V DC/AC ±10%		151718	MEB-LD-230AC

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com