

Feed separators HPV

FESTO



Feed separators HPV


Key features at a glance

FESTO

Separation of workpieces in the supply process


Previously

- Required at least 2 drives, 2 valves and 4 proximity sensors
- Extensive programming required




Today

- One unit (1 drive, 1 valve and 2 proximity sensors)
- More cost-effective
- Reliable
- No programming required



High functionality

- 1 Corrosion-resistant thanks to stainless steel plungers
- 2 Optimum, accurate combination options with centring sleeves
- 3 Supply ports optionally at top or rear
- 4 Supports proximity sensors that can be integrated in the housing (SME/SMT-8)




Note


An integrated mechanical locking mechanism between the two plungers ensures that one piston cannot retract until the other has advanced. Both plungers are briefly extended upon changeover and the part to be separated is surrounded.

Function principle


Plunger A is retracted. The locking mechanism locks plunger B.




Plunger A advances.




Plunger B cannot retract from the locking mechanism until plunger A is fully advanced.



Plunger B advances.



Plunger A cannot retract from the locking mechanism until plunger B is fully advanced.




Feed separators HPV

Peripherals overview and type codes

FESTO

Peripherals overview



Accessories		
	Brief description	→ Page/Internet
1	Centring sleeve, connecting sleeve	For centring when mounting
2	Proximity sensor	For position sensing, sensor is integrated in sensor slot
3	QS push-in fitting	For connecting compressed air tubing with standard external diameter
		quick star

Type codes

		HPV	–	14	–	20	–	A
Type								
Double-acting								
HPV	Feed separator							
Size [mm]								
Stroke [mm]								
Position sensing								
A	Via proximity sensor							

Feed separators HPV


Technical data

FESTO

Function



- Ø - Size
10 ... 22
- I - Stroke length
20 ... 60 mm



General technical data			
Size	10	14	22
Pneumatic connection	M5/M3	M5/M5	
Mode of operation	Double-acting		
Operating medium	Compressed air, filtered, lubricated or unlubricated		
Design	Twin piston		
	Piston rod		
	Locking mechanism		
	Non-rotating		
Protection against torsion/guide	Square plungers		
Max. interchangeability [mm]	0.3		
Cushioning	None		
Position sensing	Via proximity sensor		
Type of mounting	Via through-holes		
	Via female thread		
Mounting position	Any		

Operating and environmental conditions		
Operating pressure [bar]	3 ... 8	
Ambient temperature [°C]	+5 ... +60	
Protection class	IP40	
Corrosion resistance class CRC ¹⁾	2	

- 1) Corrosion resistance class 2 to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Forces [N]			
Size	10	14	22
Theoretical force at 6 bar Advancing	45	90	225
Theoretical force at 6 bar Retracting	35	75	180

Retracting and advancing times [ms] without add-on plunger separators at 6 bar (unrestricted)					
Size	10	14		22	
Stroke	10	20	40	30	60
Retracting time	20	22	43	95	192
Advancing time	18	21	42	83	162
Cycle time	45	42	83	189	380

Feed separators HPV

Technical data

FESTO

Weights [g]					
Size	10	14		22	
Stroke	10	20	40	30	60
Product weight	135	290	460	950	1,500


Max. permissible weight [g] of add-on plunger separators for unrestricted operation					
Size	10	14		22	
Add-on plunger separators ¹⁾	56	150		395	

1) If the max. permissible weights of the add-on plunger fingers are exceeded, the retracting and advancing times must be adapted in accordance with the table below using one-way flow control valves. Failure to do so may result in components of the feed separator being damaged.

Retracting and advancing times [s] with add-on plunger separators as a function of the weight force [N] of the fingers						
Size		10	14		22	
Stroke		10	20	40	30	60
Weight force	1 N	0.03	–	–	–	–
	2 N	0.04	0.03	0.05	–	–
	3 N	0.05	0.04	0.08	–	–
	4 N	0.06	0.05	0.11	0.24	0.48
	5 N	–	0.07	0.13	0.3	0.6
	6 N	–	–	–	0.36	0.72
	7 N	–	–	–	0.42	0.84
	8 N	–	–	–	0.48	0.96

Materials

Sectional view



Feed separator		
1	Body	Wrought aluminium alloy (with CompCoat)
2	End cover	High-alloy steel
3	Plunger	High-alloy steel
4	Locking mechanism	Case-hardened steel
5	Piston rod	High-alloy steel
–	Seals	Nitrile rubber
Note on materials		Copper, PTFE and silicone-free
		Conforms to RoHS

Note

The plunger slideways in the housing are determined by the appropriate fit selected and cannot be adjusted. The necessary basic lubrication is


performed during assembly. We recommend that the feed separator be re-lubricated after 2 million cycles.

Feed separators HPV

Technical data


FESTO

Permissible characteristic static load values at the plungers



Size	10	14	22
Force F [N]	75	100	180
Torque Mx [Nm]	3	5	9
Torque My [Nm]	3	5	9
Torque Mr [Nm]	3	5	9


Plunger backlash



Size	10	14	22
Stroke	10	20	30
Sx [mm]	0.05	0.05	0.05
Sz [mm]	0.03	0.03	0.03
αx [°]	0.12	0.12	0.07
αy [°]	0.2	0.2	0.11
αz [°]	0.262	0.175	0.12

Minimum clearances

To prevent malfunctioning of the proximity sensors, the feed separators must comply with the minimum clearances specified in the table.




Size	10	14	22
For SME-8-... [mm]	60	59	73
For SMT-8-...-B [mm]	60	54	69

Feed separators HPV

Technical data

FESTO

Projection of proximity sensors




Size		10	14	22
For SME-8-...	[mm]	14		
For SMT-8-...	[mm]	22		

Mounting options


Only the mounting surface on the underside (opposite the supply ports) may be used.

From above via through-holes




Size	10	14	22
Screw	M3	M4	M6
Permitted tightening torque [Nm]	1.2	2.9	9.9

From below via female threads



Size	10	14	22
Screw	M4	M5	M8
Permitted tightening torque [Nm]	2.9	5.9	24

Surface finish and positional accuracy of bearing surface




Feed separators HPV

Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad



Type	B1	B2	B3	B4	B5	D1	D2	D3	D4	D5	D6	EE	EE1	H1
			±0.02	±0.05		Ø		H8/h7 Ø	H13 Ø	H13 Ø	H13 Ø			
HPV-10-10-A	47	6	7	20	7	5.3	M4	7	6	–	3.2	M5	M3	78
HPV-14-20-A	60	12	10	30	10	5.3	M5	7	7.4	–	4.2	M5	M5	119
HPV-14-40-A	60	12	10	30	10	5.3	M5	7	7.4	–	4.2	M5	M5	189
HPV-22-30-A	78	13	14	38	11	8.4	M8	12	10.4	6.2	6.2	M5	M5	175
HPV-22-60-A	78	13	14	38	11	8.4	M8	12	10.4	6.2	6.2	M5	M5	280

Type	H2	H3	H4	H5 ¹⁾	H6	H7	H8	H9	L1	L2	T1	T2	T3	T5
			±0.1		±0.2	±0.1	±0.5				+0.1		min.	–0.3
HPV-10-10-A	53	24.5	16	30	7	4	10	7.5	18	9	1.6	3.1	4	1.4
HPV-14-20-A	79	36	20	30	10	5	20	36	19	7	1.6	4.6	5	1.4
HPV-14-40-A	129	56	20	60	10	5	40	56	19	7	1.6	4.6	5	1.4
HPV-22-30-A	115	48	40	60	14	8	30	48	32	16	2.6	6.1	5	2.4
HPV-22-60-A	190	78	40	120	14	8	60	78	32	16	2.6	6.1	5	2.4

1) Tolerance for centring hole ±0.02
Tolerance for threaded and through-hole ±0.1

Ordering data

Size	Stroke [mm]	Part No.	Type
10	10	550 908	HPV-10-10-A
14	20	529 351	HPV-14-20-A
	40	529 352	HPV-14-40-A
22	30	529 353	HPV-22-30-A
	60	529 354	HPV-22-60-A

Feed separators HPV

Accessories

FESTO

Ordering data			Technical data → Internet: zbh	
	For size	Part No.	Type	PU ¹⁾
Centring sleeve ZBH				
	10, 14	186 717	ZBH-7	10
	22	189 653	ZBH-12	10

1) Packaging unit quantity

Ordering data – Proximity sensors for T-slot, magneto-resistive					Technical data → Internet: smt	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot lengthwise, flush with the cylinder profile	PNP	Cable, 3-wire	2.5	175 436	SMT-8-PS-K-LED-24-B
			Plug M8x1, 3-pin	0.3	175 484	SMT-8-PS-S-LED-24-B

Ordering data – Proximity sensors for T-slot, magnetic reed					Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot lengthwise, flush with the cylinder profile	Via contact	Cable, 3-wire	2.5	150 855	SME-8-K-LED-24
			Plug M8x1, 3-pin	0.3	150 857	SME-8-S-LED-24

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Straight socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 363	NEBU-M12G5-K-2.5-LE3
			5	541 364	NEBU-M12G5-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3
	Angled socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 367	NEBU-M12W5-K-2.5-LE3
			5	541 370	NEBU-M12W5-K-5-LE3

Ordering data – Slot covers			
	Mounting	Length [m]	Part No. Type
	Inserted from above	2 x 0.5	151 680 ABP-5-S

Ordering data – One-way flow control valves				Technical data → Internet: grla-m5-qs	
	Connection		Material	Part No.	Type
	Thread	For tubing outer Ø			
	M5	3	Metal design	193 137	GRLA-M5-QS-3-D
		4		193 138	GRLA-M5-QS-4-D
		6		193 139	GRLA-M5-QS-6-D

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788
Phone: 1.631.435.0800; Fax: 1.631.435.8026;
Email: info@festo-usa.com www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4
Phone: 1.905.624.9000; Fax: 1.905.624.9001;
Email: festo.canada@ca.festo.com www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México
Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;
Email: festo.mexico@mx.festo.com www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com