


Angrenaj|cutie de viteze|reductor|transmisie
EMGA-60-P-G5-EAS-60

Numar piesa: 2297687

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiunea flansei reductorului	60 mm
Dimensiune flansa motor	60 mm
Joc de rasucire	0.17 grd
Tipul de reductor	Reductor planetar
Raportul de transmisie	5:1
Turatie de lucru max.	13000 1/min
Temperatura de functionare unitate actionare	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de iesire continuu	40 Nm
Momentul de inertie al reductorului	0.078 kgcm ²
Cuplu de iesire max.	64 Nm
Randament max.	98 %
Rigiditate la torsiune	2.3 Nm/arcmin
Greutate produs	900 g
Interfata de iesire la unitatea de actionare	60H
Interfata reductor unitate de actionare	60P
Nota privind materialele	Conform RoHS