


Plastic tubing, standard O.D., NPT

FESTO



Plastic tubing, standard O.D., NPT

Product range overview

FESTO

Version	Type	Outside diameter [inch]	Colour									Operating medium	
			Silver	Blue	Black	Yellow	Green	Red	Brown	White	Natural	Compressed air	Vacuum
	PEN Polyethylene	$\frac{5}{32}$, $\frac{3}{16}$, $\frac{1}{4}$, $\frac{5}{16}$, $\frac{3}{8}$, $\frac{1}{2}$, $\frac{5}{8}$	■	■	■	■	■	■	■	■	■	■	■
	PLN Polyethylene	$\frac{5}{32}$, $\frac{3}{16}$, $\frac{1}{4}$, $\frac{5}{16}$, $\frac{3}{8}$, $\frac{1}{2}$, $\frac{5}{8}$	■	■	■	■	■	■	■	■	■	■	■
	PUN-H Polyurethane	$\frac{1}{8}$, $\frac{5}{32}$, $\frac{3}{16}$, $\frac{1}{4}$, $\frac{5}{16}$, $\frac{3}{8}$, $\frac{1}{2}$, $\frac{5}{8}$	■	■	■	■	■	■	■	■	■	■	■

Plastic tubing, standard O.D., NPT

Product range overview

FESTO

Type	Approved for use in the food industry to 2002/72/EC	FDA approved for use in the food industry	Halogen-free	Contact with electric cables	PWIS-free to FN 942 010	Suitable for use with energy chains	Resistance				Flexibility	Shore hardness	→ Page/ Internet
							Chemicals	Microbes	UV radiation	Hydrolysis			
PEN	-	-	■	■	■	■	++	++	++ ¹⁾	+++	++	D 52	6
PLN	■	-	■	■	■	-	++	++	++ ¹⁾	+++	+	-	8
PUN-H	■	■	■	■	■	■	+	++	++ ¹⁾	++	+++	D 52	10

+++ Highly suitable
++ Suitable

+ Limited suitability (upon request)
- Unsuitable

1) Applies to black colour


Plastic tubing, standard O.D., NPT

Technical data


FESTO

Method of measurement

Bending radius relevant for flow rate R_d



The tubing is bent in the direction of its curvature until a flattening corresponding to 5% of the tubing O.D. occurs.
 R_d is then calculated mathematically.
The flow rate is not reduced until R_d is reached.




Cross section flattened by bending the tubing.

d = Non-deformed tubing O.D.

$d1$ = Deformed tubing O.D.

Minimum bending radius R_{min}



The tubing fixed to the base plate is bent until the deformation results in a kink. The measured value is the minimum bending radius R_{min} . This R_{min} results in significant reductions in flow rate.

Plastic tubing, standard O.D., NPT

Type codes

PEN		—		—		—	BL	—	150	—	CB
Material											
PEN	Polyethylene										
PLN	Polyethylene										
PUN	Polyurethane										
Approval											
H	Hydrolysis-resistant										
Outside diameter [inch]											
Colour											
SW	Black										
BL	Blue										
GN	Green										
RT	Red										
WS	White										
GE	Yellow										
BR	Brown										
SI	Silver										
NT	Natural										
Packaging unit [feet]											
Packaging											
CB	Cardboard box										
HA	Reel										

Plastic tubing PEN, standard O.D., NPT

Technical data

Plastic tubing PEN

Compressed air tubing made of polyethylene is distinguished by great resistance to chemicals and hydrolysis. It is resistant to most cleaning agents and lubricants.

-  - Ambient temperature
-22 ... +140 °F


-  - Temperature-dependent operating pressure
-14.4 ... +145 psi

Material:
PE

Note on materials:
Free of copper and PTFE
RoHS-compliant



Operating pressure p as a function of temperature t



Possible fittings



Push-in fitting QS-U,
Quick Star
→ Internet: qs*-u



Push-in fitting QB-U,
Quick Basic
→ Internet: qb*-u

Dimensions and ordering data

Outside diameter [inch]	Min. bending radius [ft]	Bending radius relevant for flow rate [ft]	Weight [oz/ft]	Colour	Part No.	Type	PU ¹⁾ [ft]
5/32	0.032	0.065	0.067	Black	569881	PEN-5/32-SW-150-CB	150
				Blue	569889	PEN-5/32-BL-150-CB	150
3/16	0.039	0.075	0.100	Black	569882	PEN-3/16-SW-150-CB	150
				Blue	569890	PEN-3/16-BL-150-CB	150
1/4	0.041	0.085	0.186	Black	569883	PEN-1/4-SW-150-CB	150
				Blue	569891	PEN-1/4-BL-150-CB	150
5/16	0.073	0.114	0.250	Black	569884	PEN-5/16-SW-150-CB	150
				Blue	569892	PEN-5/16-BL-150-CB	150
3/8	0.088	0.131	0.376	Black	569885	PEN-3/8-SW-150-CB	150
				Blue	569893	PEN-3/8-BL-150-CB	150
1/2	0.108	0.196	0.848	Black	569886	PEN-1/2-SW-150-CB	150
				Blue	569894	PEN-1/2-BL-150-CB	150
5/8	0.196	0.410	1.158	Black	569887	PEN-5/8-SW-150-CB	150
				Blue	569895	PEN-5/8-BL-150-CB	150

1) Packaging unit

Plastic tubing PEN, standard O.D., NPT

Ordering data – Modular product

Ordering table (minimum order quantity 10,000 ft, rounding-off value 50 ft)										
Size	5/32	3/16	1/4	5/16	3/8	1/2	5/8	Condi- tions	Code	Enter code
[M] Module No.	567448									
Function	Polyethylene tubing, standard O.D., economical								PEN	PEN
Tubing O.D. [inch]	5/32	–	–	–	–	–	–		-5/32	
	–	3/16	–	–	–	–	–		-3/16	
	–	–	1/4	–	–	–	–		-1/4	
	–	–	–	5/16	–	–	–		-5/16	
	–	–	–	–	3/8	–	–		-3/8	
	–	–	–	–	–	1/2	–		-1/2	
	–	–	–	–	–	–	5/8		-5/8	
Colour	Silver								-SI	
	Blue								-BL	
	Black								-SW	
	Yellow								-GE	
	Green								-GN	
	Red								-RT	
	Brown								-BR	
	White								-WS	
	Natural								-NT	
[O] Inscription text (on request)	Standard									
	Customer-specific tubing inscription							[1]	-TXT	
[M] Packaging unit [ft]	150								-150	
	500								-500	
	1,000					–	–		-1000	
	1,500				–	–	–		-1500	
Packaging	Cardboard box							[2]	-CB	
	Reel							[3]	-HA	

[1] TXT

Only on request

[3] HA

Not with packaging unit 150

[2] CB

Only with packaging unit 150

Transfer order code

567448 **PEN** – – – – –

Plastic tubing PLN, standard O.D., NPT

Technical data

Plastic tubing PLN

Compressed air tubing made of polyethylene is distinguished by great resistance to chemicals and hydrolysis. It is resistant to most cleaning agents and lubricants.

-  - Ambient temperature
-22 ... +176 °F


-  - Temperature-dependent operating pressure
-14.4 ... +203 psi

Material:
PE

Note on materials:
Free of copper and PTFE
RoHS-compliant



Operating pressure p as a function of temperature t



Possible fittings



Push-in fitting QS-U,
Quick Star
→ Internet: qs*-u



Push-in fitting QB-U,
Quick Basic
→ Internet: qb*-u

Dimensions and ordering data

Outside diameter [inch]	Min. bending radius [ft]	Bending radius relevant for flow rate [ft]	Weight [oz/ft]	Colour	Part No.	Type	PU ¹⁾ [ft]
5/32	0.039	0.082	0.065	Natural	569897	PLN-5/32-NT-150-CB	150
				Black	569905	PLN-5/32-SW-150-CB	150
				Blue	569913	PLN-5/32-BL-150-CB	150
3/16	0.036	0.095	0.107	Natural	569898	PLN-3/16-NT-150-CB	150
				Black	569906	PLN-3/16-SW-150-CB	150
				Blue	569914	PLN-3/16-BL-150-CB	150
1/4	0.039	0.105	0.180	Natural	569899	PLN-1/4-NT-150-CB	150
				Black	569907	PLN-1/4-SW-150-CB	150
				Blue	569915	PLN-1/4-BL-150-CB	150
5/16	0.082	0.164	0.231	Natural	569900	PLN-5/16-NT-150-CB	150
				Black	569908	PLN-5/16-SW-150-CB	150
				Blue	569916	PLN-5/16-BL-150-CB	150
3/8	0.115	0.187	0.403	Natural	569901	PLN-3/8-NT-150-CB	150
				Black	569909	PLN-3/8-SW-150-CB	150
				Blue	569917	PLN-3/8-BL-150-CB	150
1/2	0.138	0.213	0.580	Natural	569902	PLN-1/2-NT-150-CB	150
				Black	569910	PLN-1/2-SW-150-CB	150
				Blue	569918	PLN-1/2-BL-150-CB	150
5/8	0.197	0.311	0.881	Natural	569903	PLN-5/8-NT-150-CB	150
				Black	569911	PLN-5/8-SW-150-CB	150
				Blue	569919	PLN-5/8-BL-150-CB	150

1) Packaging unit

Plastic tubing PLN, standard O.D., NPT

Ordering data – Modular product

Ordering table (minimum order quantity 10,000 ft, rounding-off value 50 ft)										
Size	5/32	3/16	1/4	5/16	3/8	1/2	5/8	Condi- tions	Code	Enter code
[M] Module No.	567449									
Function	Polyethylene tubing, standard O.D., resistant to cleaning agents (approved for use in the food industry)								PLN	PLN
Tubing O.D. [inch]	5/32	–	–	–	–	–	–		-5/32	
	–	3/16	–	–	–	–	–		-3/16	
	–	–	1/4	–	–	–	–		-1/4	
	–	–	–	5/16	–	–	–		-5/16	
	–	–	–	–	3/8	–	–		-3/8	
	–	–	–	–	–	1/2	–		-1/2	
	–	–	–	–	–	–	5/8		-5/8	
Colour	Silver								-SI	
	Blue								-BL	
	Black								-SW	
	Yellow								-GE	
	Green								-GN	
	Red								-RT	
	Brown								-BR	
	White								-WS	
	Natural								-NT	
[O] Inscription text (on request)	Standard									
	Customer-specific tubing inscription							[1]	-TXT	
[M] Packaging unit [ft]	150								-150	
	500								-500	
	1,000					–	–		-1000	
	1,500			–	–	–	–		-1500	
Packaging	Cardboard box							[2]	-CB	
	Reel							[3]	-HA	

[1] TXT

Only on request

[3] HA

Not with packaging unit 150

[2] CB

Only with packaging unit 150

Transfer order code

567449 PLN – – – –

Plastic tubing PUN-H, standard O.D., hydrolysis-resistant, NPT

FESTO

Technical data

Plastic tubing PUN-H


Approved for use in the food industry.

-  - Ambient temperature
-31 ... +145 °F


-  - Temperature-dependent
operating pressure
-14.4 ... +145 psi

Material:
TPE-U (PU)

Note on materials:
Free of copper and PTFE
RoHS-compliant



Operating pressure p as a function of temperature t



Possible fittings



Push-in fitting QS-U,
Quick Star
→ Internet: qs*-u



Push-in fitting QB-U,
Quick Basic
→ Internet: qb*-u

Dimensions and ordering data

Outside diameter [inch]	Min. bending radius [ft]	Bending radius relevant for flow rate [ft]	Weight [oz/ft]	Colour	Part No.	Type	PU ¹⁾ [ft]
1/8	0.020	0.039	0.060	Silver	567937	PUN-H-1/8-SI-150-CB	150
				Blue	567945	PUN-H-1/8-BL-150-CB	150
				Black	567953	PUN-H-1/8-SW-150-CB	150
				Natural	567961	PUN-H-1/8-NT-150-CB	150
				Yellow	567969	PUN-H-1/8-GE-150-CB	150
				Green	567977	PUN-H-1/8-GN-150-CB	150
				Red	567985	PUN-H-1/8-RT-150-CB	150
				Brown	567993	PUN-H-1/8-BR-150-CB	150
				White	568001	PUN-H-1/8-WE-150-CB	150
5/32	0.020	0.052	0.090	Silver	567938	PUN-H-5/32-SI-150-CB	150
				Silver	568009	PUN-H-5/32-SI-500-HA	500
				Blue	567946	PUN-H-5/32-BL-150-CB	150
				Blue	568013	PUN-H-5/32-BL-500-HA	500
				Black	567954	PUN-H-5/32-SW-150-CB	150
				Black	568017	PUN-H-5/32-SW-500-HA	500
				Natural	567962	PUN-H-5/32-NT-150-CB	150
				Yellow	567970	PUN-H-5/32-GE-150-CB	150
				Green	567978	PUN-H-5/32-GN-150-CB	150
				Red	567986	PUN-H-5/32-RT-150-CB	150
				Brown	567994	PUN-H-5/32-BR-150-CB	150
				White	568002	PUN-H-5/32-WE-150-CB	150

1) Packaging unit

Plastic tubing PUN-H, standard O.D., hydrolysis-resistant, NPT

Technical data

Dimensions and ordering data							
Outside diameter	Min. bending radius	Bending radius relevant for flow rate	Weight	Colour	Part No.	Type	PU ¹⁾
[inch]	[ft]	[ft]	[oz/ft]				[ft]
3/16	0.025	0.069	0.130	Silver	567939	PUN-H-3/16-SI-150-CB	150
				Blue	567947	PUN-H-3/16-BL-150-CB	150
				Black	567955	PUN-H-3/16-SW-150-CB	150
				Natural	567963	PUN-H-3/16-NT-150-CB	150
				Yellow	567971	PUN-H-3/16-GE-150-CB	150
				Green	567979	PUN-H-3/16-GN-150-CB	150
				Red	567987	PUN-H-3/16-RT-150-CB	150
				Brown	567995	PUN-H-3/16-BR-150-CB	150
				White	568003	PUN-H-3/16-WE-150-CB	150
1/4	0.032	0.085	0.230	Silver	567940	PUN-H-1/4-SI-150-CB	150
				Silver	568010	PUN-H-1/4-SI-500-HA	500
				Blue	567948	PUN-H-1/4-BL-150-CB	150
				Blue	568014	PUN-H-1/4-BL-500-HA	500
				Blue	568021	PUN-H-1/4-BL-1000-HA	1000
				Black	567956	PUN-H-1/4-SW-150-CB	150
				Black	568018	PUN-H-1/4-SW-500-HA	500
				Black	568023	PUN-H-1/4-SW-1000-HA	1000
				Natural	567964	PUN-H-1/4-NT-150-CB	150
				Yellow	567972	PUN-H-1/4-GE-150-CB	150
				Green	567980	PUN-H-1/4-GN-150-CB	150
				Red	567988	PUN-H-1/4-RT-150-CB	150
				Brown	567996	PUN-H-1/4-BR-150-CB	150
				White	568804	PUN-H-1/4-WE-150-CB	150
5/16	0.065	0.121	0.310	Silver	567941	PUN-H-5/16-SI-150-CB	150
				Silver	568011	PUN-H-5/16-SI-500-HA	500
				Blue	567949	PUN-H-5/16-BL-150-CB	150
				Blue	568015	PUN-H-5/16-BL-500-HA	500
				Blue	568022	PUN-H-5/16-BL-1000-HA	1000
				Black	567957	PUN-H-5/16-SW-150-CB	150
				Black	568019	PUN-H-5/16-SW-500-HA	500
				Black	568024	PUN-H-5/16-SW-1000-HA	1000
				Natural	567965	PUN-H-5/16-NT-150-CB	150
				Yellow	567973	PUN-H-5/16-GE-150-CB	150
				Green	567981	PUN-H-5/16-GN-150-CB	150
				Red	567989	PUN-H-5/16-RT-150-CB	150
				Brown	567997	PUN-H-5/16-BR-150-CB	150
				White	568005	PUN-H-5/16-WE-150-CB	150

1) Packaging unit

Plastic tubing PUN-H, standard O.D., hydrolysis-resistant, NPT

FESTO

Technical data

Dimensions and ordering data							
Outside diameter	Min. bending radius	Bending radius relevant for flow rate	Weight	Colour	Part No.	Type	PU ¹⁾
[inch]	[ft]	[ft]	[oz./ft]				[ft]
3/8	0.081	0.171	0.480	Silver	567942	PUN-H-3/8-SI-150-CB	150
				Silver	568012	PUN-H-3/8-SI-500-HA	500
				Blue	567950	PUN-H-3/8-BL-150-CB	150
				Blue	568016	PUN-H-3/8-BL-500-HA	500
				Black	567958	PUN-H-3/8-SW-150-CB	150
				Black	568020	PUN-H-3/8-SW-500-HA	500
				Natural	567966	PUN-H-3/8-NT-150-CB	150
				Yellow	567974	PUN-H-3/8-GE-150-CB	150
				Green	567982	PUN-H-3/8-GN-150-CB	150
				Red	567990	PUN-H-3/8-RT-150-CB	150
				Brown	567998	PUN-H-3/8-BR-150-CB	150
				White	568006	PUN-H-3/8-WE-150-CB	150
1/2	0.075	0.204	0.880	Silver	567943	PUN-H-1/2-SI-150-CB	150
				Blue	567951	PUN-H-1/2-BL-150-CB	150
				Black	567959	PUN-H-1/2-SW-150-CB	150
				Natural	567967	PUN-H-1/2-NT-150-CB	150
				Yellow	567975	PUN-H-1/2-GE-150-CB	150
				Green	567983	PUN-H-1/2-GN-150-CB	150
				Red	567991	PUN-H-1/2-RT-150-CB	150
				Brown	567999	PUN-H-1/2-BR-150-CB	150
				White	568007	PUN-H-1/2-WE-150-CB	150
5/8	0.125	0.288	1.380	Silver	567944	PUN-H-5/8-SI-150-CB	150
				Blue	567952	PUN-H-5/8-BL-150-CB	150
				Black	567960	PUN-H-5/8-SW-150-CB	150
				Natural	567968	PUN-H-5/8-NT-150-CB	150
				Yellow	567976	PUN-H-5/8-GE-150-CB	150
				Green	567984	PUN-H-5/8-GN-150-CB	150
				Red	567992	PUN-H-5/8-RT-150-CB	150
				Brown	568000	PUN-H-5/8-BR-150-CB	150
				White	568008	PUN-H-5/8-WE-150-CB	150

1) Packaging unit

Plastic tubing PUN, standard O.D., NPT

Ordering data – Modular product

Ordering table (minimum order quantity 10,000 ft, rounding-off value 50 ft)											
Size	1/8	5/32	3/16	1/4	5/16	3/8	1/2	5/8	Condi- tions	Code	Enter code
[M] Module No.	567446										
Function	Polyurethane tubing, standard O.D.									PUN	PUN
Alternative material characteristic	Hydrolysis-resistant									-H	
[M] Tubing O.D. [inch]	1/8	–	–	–	–	–	–	–		-1/8	
	–	5/32	–	–	–	–	–	–		-5/32	
	–	–	3/16	–	–	–	–	–		-3/16	
	–	–	–	1/4	–	–	–	–		-1/4	
	–	–	–	–	5/16	–	–	–		-5/16	
	–	–	–	–	–	3/8	–	–		-3/8	
	–	–	–	–	–	–	1/2	–		-1/2	
	–	–	–	–	–	–	–	5/8		-5/8	
	Colour										
	Silver									-SI	
	Blue									-BL	
	Black									-SW	
	Yellow									-GE	
	Green									-GN	
	Red									-RT	
	Brown									-BR	
	White									-WS	
	Natural								[4]	-NT	
[O] Inscription text (on request)	Standard										
	Customer-specific tubing inscription								[1]	-TXT	
[M] Packaging unit [ft]	150									-150	
	500									-500	
	1,000						–	–		-1000	
	1,500					–	–	–		-1500	
	Packaging										
	Cardboard box								[2]	-CB	
	Reel								[3]	-HA	

[1] TXT Only on request
[2] CB Only with packaging unit 150

[3] HA Not with packaging unit 150
[4] NT Only with alternative material characteristic H

Transfer order code

567446 **PUN** – – – – –

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com