

**Cuplaj**  
**EAMD-33-22-19-10X12**  
Numar piesa: 5030024

**FESTO**



**Fisa de date**

| Caracteristica               | Valoare               |
|------------------------------|-----------------------|
| Diametrul de montare 1       | 19 mm                 |
| Diametru de montare 2        | 10 mm                 |
| Dimensiune                   | 33                    |
| Lungime nominala             | 22 mm                 |
| Pozitie de instalare         | orice                 |
| Turatie max.                 | 8000 1/min            |
| Conformitatea LABS           | VDMA24364-B2-L        |
| Temperatura de depozitare    | -25 °C...60 °C        |
| Umiditate relativa           | 0 - 95 %              |
| Temperatura ambianta         | -25 °C...60 °C        |
| Momentul de inertie al masei | 4.6 kgmm <sup>2</sup> |
| Cuplu transmisibil           | 9 Nm                  |
| Greutate produs              | 46.1 g                |
| Nota privind materialele     | Conform RoHS          |