

Filtru
MS12N-LF
Numar piesa: 535026

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	12
Seria	MS
Pozitie de instalare	vertical +/- 5°
Purjare a condensului	complet automat complet automat, controlat electric palpare manuala rotire manuala
Structura constructiva	Filtru sinterizat cu separator centrifugal
Eficienta de separare a condensatului	75 %
Presiune de lucru	0.8 bar...20 bar
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [-:9:-] Aer comprimat conform ISO 8573-1:2010 [7:9:-] Gaze inerte
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura de depozitare	-10 °C...60 °C
Temperatura medie	-10 °C...60 °C
Temperatura ambianta	-10 °C...60 °C
Tipul de montare	Instalarea liniei cu accesorii optional:
Conector pneumatic 1	intern
Conexiune pneumatica 2	intern
Material carcasa	Aluminiu turnat sub presiune Aliaj de aluminiu forjat