


Axa ghidare EGC-185- -FA

Numar piesa: 558868

FESTO



Fisa de date

Caracteristica	Valoare
Cursa de lucru	50 mm...8500 mm
Dimensiune	185
Pozitie de instalare	orice
Ghidaj	Ghidaj cu bile de recirculare
Structura constructiva	Ghidaj
Acceleratie max.	50 m/s ²
Viteza max.	5 m/s
Clasa de rezistenta la coroziune KBK	0 - nu este afectat de coroziune
Conformitatea LABS	VDMA24364 zona III
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Momente de gradul 2 ale suprafetei Ix	23400000 mm ⁴
Momentele de gradul 2 ale suprafetei Iy	27400000 mm ⁴
Forta max. Fy	15200 N
Forta max. Fz	15200 N
Rezistenta max. de deplasare fara sarcina	15 N
Moment max. Mx	529 Nm
Max. Moment My	1157 Nm...1820 Nm
Moment max. Mz	1157 Nm...1820 Nm
Forta max. Fy axa totala	15200 N
Forta max. Fz axa totala	15200 N
Moment max. Mx axa totala	529 Nm
Moment max. axa mea totala	1157 Nm...1820 Nm
Moment max. Mz axa totala	1157 Nm...1820 Nm
Momentul de inertie torsional It	14100000 mm ⁴
Conexiune pneumatica, unitate de blocare	M5
Material profil	Aliaj de aluminiu forjat anodizat
Nota privind materialele	Conform RoHS
Materialul profilului de acoperire	ABS
Material capac	Aliaj de aluminiu forjat anodizat

Caracteristica	Valoare
Material ghidare sanie	Otel
Material sina de ghidaj	Otel
Material sanie	Aliaj de aluminiu forjat anodizat