

Solenoid valves VZWM-L

FESTO



Solenoid valves VZWM-L

Key features and type codes

FESTO

Brief description

- Indirectly controlled diaphragm valve
- Connection, valve
G $\frac{1}{4}$... G2
- Flow rate
1,400 ... 31,000 l/min
- Available in brass or special steel casting
- Varied range of coils


VZWM – L – M22C – G14 – F4 –	
Type	
VZWM	Solenoid valve, process directional control valve
Design	
L	In-line valve
Valve function	
M22C	2/2-way valve, normally closed
Connection, valve	
G14	G $\frac{1}{4}$
G38	G $\frac{3}{8}$
G12	G $\frac{1}{2}$
G34	G $\frac{3}{4}$
G1	G1
G114	G1 $\frac{1}{4}$
G112	G1 $\frac{1}{2}$
G2	G2
Electrical connection	
F4	For solenoid armature tube, system 8
F5	For solenoid armature tube, system 13
Housing material	
R1	Special steel casting
	Brass

Solenoid valves VZWM-L

FESTO

Technical data

Function



Flow rate

1,400 ... 31,000 l/min

Voltage

24 V DC
110/230 V AC



General technical data									
Connection, valve		G1/4	G3/8	G1/2	G3/4	G1	G1 1/4	G1 1/2	G2
Nominal size DN		[mm]	13.5	13.5	13.5	27.5	27.5	40	50
Valve function		2/2, single solenoid							
Constructional design		Diaphragm valve							
Sealing principle		Soft							
Actuation type		Electrical							
Reset method		Pneumatic spring							
Control type		Piloted							
Direction of flow		Non-reversible							
Exhaust function		No flow control							
Manual override		None							
Type of mounting		In-line installation							
Mounting position		Preferably vertical							
Standard nominal flow rate		[l/min]	1,400	2,100	2,400	10,000	11,700	24,000	31,000
Flow rate Kv		[m³/h]	1.6	2	2.4	8.5	10.7	21.3	39
C value		[l/sbar]	6	8.8	9.8	39	41	75	110
b value			0.3	0.35	0.37	0.5	0.57	0.6	0.67
Differential pressure		[bar]	0.5	0.5	0.5	0.5	0.7	0.7	0.7
Product weight	Brass housing	[g]	500	480	450	1,270	1,200	2,850	3,800
	Special steel casting housing	[g]	400	400	330	1,200	1,100	2,650	3,660
Materials	Housing	Brass or special steel casting							
	Diaphragm	Nitrile rubber							
	Plunger tube	High-alloy steel							
Note on materials		Contains paint wetting impairment substances							
Max. tightening torque	Connecting thread	[Nm]	35	60	105	200	350	450	620
	Cover screw	[Nm]	20	20	20	30	30	30	30
	Coil mounting	[Nm]	2	2	2	2	2	2	2

Operating and environmental conditions										
Connection, valve			G¼	G¾	G½	G¾	G1	G1¼	G1½	G2
Operating medium			Filtered compressed air, lubricated, grade of filtration 50 µm, neutral gases, water, neutral fluids							
Operating pressure, valve	Gases	[bar]	0.5 ... 10					0.7 ... 10		
	Fluids	[bar]	0.5 ... 6					0.7 ... 6		
Ambient temperature		[°C]	-10 ... +60							
Temperature of medium	Gases	[°C]	-10 ... +60							
	Fluids	[°C]	5 ... 50							
Max. viscosity		[mm²/s]	22							
Corrosion resistance class CRC ¹⁾	Brass		1							
	Special steel casting		3							

1) Corrosion resistance class 1 to Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Corrosion resistance class 3 to Festo standard 940 070

Components with heavy corrosion exposure. Externally visible components in direct contact with normal industrial atmosphere or media such as solvents and cleaning agents, where the surface requirement is predominantly functional.

Solenoid valves VZWM-L

Technical data

FESTO

Valve response times										
Connection, valve			G1/4	G3/8	G1/2	G3/4	G1	G1 1/4	G1 1/2	G2
Gases										
Response time	off	[ms]	10	10	10	12	12	20	20	21
	on	[ms]	8	8	8	15	15	26	26	62
Fluids										
Response time	off	[ms]	200	210	220	930	930	1,900	2,000	2,800
	on	[ms]	100	110	110	400	400	1,400	1,400	2,100
Response time, variant R1	off	[ms]	210	190	200	950	950	1,900	2,000	2,800
	on	[ms]	80	110	110	420	300	1,400	1,400	2,100

Electrical data										
			G1/4	G3/8	G1/2	G3/4	G1	G1¼	G1½	G2
Electrical connection			Solenoid armature tube, system 8 (order separately)						Solenoid armature tube, system 13 (order separately)	
Operating voltage	DC voltage	[V DC]	24							
	AC voltage	[V AC]	110/230 (50 ... 60 Hz)							
Coil characteristics	DC voltage	[W]	6.8						7.6	
	AC voltage	[VA]	Pull: 14.5 Hold: 10.5						14	
Protection class to EN 60529			IP65 (with plug socket)							

Weights [g]										
Brass housing					Special steel casting housing					
VZWM-...-G14-F4	500				VZWM-...-G14-F5-R1	400				
VZWM-...-G38-F4	480				VZWM-...-G38-F5-R1	400				
VZWM-...-G12-F4	450				VZWM-...-G12-F5-R1	360				
VZWM-...-G34-F4	1,270				VZWM-...-G34-F5-R1	1,200				
VZWM-...-G1-F4	1,200				VZWM-...-G1-F5-R1	1,100				
VZWM-...-G114-F5	2,850				VZWM-...-G114-F5-R1	2,650				
VZWM-...-G112-F5	2,570				VZWM-...-G112-F5-R1	2,400				
VZWM-...-G2-F5	3,800				VZWM-...-G2-F5-R1	3,660				

Solenoid valves VZWM-L


Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad

2/2-way valve



Type	B ±1.5	D	D1	H ±2	H1 ±1.5	H2 ±1	L ±2	L1 ±1.5	L2	F	t1 ±1.5	∅
VZWM-...-G14-F4	48	G1/4	M4	85.5	15	49	67	25	21	F4	4	27
VZWM-...-G38-F4	48	G3/8	M4	85.5	15	49	67	25	21	F4	4	27
VZWM-...-G12-F4	48	G1/2	M4	85	15	49	67	25	21	F4	4	27
VZWM-...-G34-F4	70	G3/4	M6	107	24.2	70.5	96	40	28	F4	6	41
VZWM-...-G1-F4	70	G1	M6	107	24.2	70.5	96	40	28	F4	6	41
VZWM-...-G114-F5	96	G1 1/4	M6	143.5	32.5	88	140	59.5	40.25	F5	6	58
VZWM-...-G112-F5	96	G1 1/2	M6	143.5	32.5	88	140	59.5	40.25	F5	6	58
VZWM-...-G2-F5	112	G2	M6	159	38.5	103.5	168	59.5	54.25	F5	6	70
VZWM-...-G14-F5-R1	44	G1/4	M4	106	15.6	51	67	25	21	F5	4	27
VZWM-...-G38-F5-R1	44	G3/8	M4	106	15.6	51	67	25	21	F5	4	27
VZWM-...-G12-F5-R1	44	G1/2	M4	106	15.6	51	67	25	21	F5	4	27
VZWM-...-G34-F5-R1	70	G3/4	M6	126	24.2	70	96	40	28	F5	6	41
VZWM-...-G1-F5-R1	70	G1	M6	126	24.2	70	96	40	28	F5	6	41
VZWM-...-G114-F5-R1	96	G1 1/4	M6	145	34	89.5	140	59.5	40.25	F5	6	58
VZWM-...-G112-F5-R1	96	G1 1/2	M6	145	34	89.5	140	59.5	40.25	F5	6	58
VZWM-...-G2-F5-R1	112	G2	M6	159	38.5	104	168	59.5	54.25	F5	6	70

Ordering data

Connection, valve	Brass housing		Special steel casting housing	
	Part No.	Type	Part No.	Type
G1/4	546 146	VZWM-L-M22C-G14-F4	546162	VZWM-L-M22C-G14-F5-R1
G3/8	546 147	VZWM-L-M22C-G38-F4	546163	VZWM-L-M22C-G38-F5-R1
G1/2	546 148	VZWM-L-M22C-G12-F4	546164	VZWM-L-M22C-G12-F5-R1
G3/4	546 149	VZWM-L-M22C-G34-F4	546165	VZWM-L-M22C-G34-F5-R1
G1	546 150	VZWM-L-M22C-G1-F4	546166	VZWM-L-M22C-G1-F5-R1
G1 1/4	546 151	VZWM-L-M22C-G114-F5	546167	VZWM-L-M22C-G114-F5-R1
G1 1/2	546 152	VZWM-L-M22C-G112-F5	546168	VZWM-L-M22C-G112-F5-R1
G2	546 153	VZWM-L-M22C-G2-F5	546169	VZWM-L-M22C-G2-F5-R1

Solenoid valves VZWM-L


Accessories

FESTO



Mounting bracket HRM

Material:

Galvanised steel



Dimensions and ordering data											Part No.	Type
B	B1	B2	D Ø	D1 Ø	H	H1	L	L1	Weight [g]			
25	12.5	2	6	5	37	10	40	25	39		9 769	HRM-1
35	17.5	3	7	7	66	16	55	40	130		9 770	HRM-2
47	23.5	3	9	7	87	23	75	59.5	246		9 771	HRM-3

Ordering data – Solenoid coils				Technical data → Internet: md, mh	
	Voltage	Part No.	Type		
MD					
	24 V DC	549 903	MD-2-24VDC-PA		
	110 V AC, 50 ... 60 Hz	549 904	MD-2-110VAC-PA		
	230 V AC, 50 ... 60 Hz	549 905	MD-2-230VAC-PA		
MH					
	24 V DC	549 906	MH-2-24VDC-PA		
	110 V AC, 50 ... 60 Hz	549 907	MH-2-110VAC-PA		
	230 V AC, 50 ... 60 Hz	549 908	MH-2-230VAC-PA		

Ordering data – Plug socket				Technical data → Internet: mssd	
		Part No.	Type		
	3-pin, square design MSF	550 067	MSSD-N		

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com