

Operator units CDPX

FESTO



Operator units CDPX

Key features

FESTO

Properties

Festo CDPX panels are high-performance processors combined with wide-screen technology. They provide more functions at a higher resolution for the interfaces between man and machine.

Functionality

- | | | | |
|---|--|---|---|
| <ul style="list-style-type: none"> • Advanced graphics and animations • Symbol gallery • Advanced functions with script language | <ul style="list-style-type: none"> • Remote access, remote control • FTP and HTTP servers • Templates | <ul style="list-style-type: none"> • Pop-up • Incorporation of standard documents | <ul style="list-style-type: none"> • Differential download • Open for web and multimedia applications |
|---|--|---|---|

The Front End Displays with touchscreen CDPX

The CDPX panels visualise data and, at the same time, operate as servers by allowing access for external clients both on-site and around the world; networking made simple thanks to the Ethernet interface with integrated

switch. They are distinguished by a high-resolution graphic display and simple, intuitive project planning and programming in Designer Studio. Ideally matched to Festo controllers (CoDeSys V2.3 and V3) and Modbus


TCP networks, they display data and parameters in graphic format simply, flexibly and with great diversity. Thanks to modern touch technology, the projected dialogue with machines and systems is extremely easy. With

the CoDeSys V3 controller provided by Festo which can be optionally integrated, CDPX panels can be expanded into a space-saving controller concept.

Operator units CDPX

Key features

The Front End Displays in the Festo controller range



Functions

- | | | | |
|---|---|--|---|
| <ul style="list-style-type: none"> • Data display in numerical, textual and graphic form • Data acquisition | <ul style="list-style-type: none"> • Trend display • Recipe handling • Alarm management • Multilingualism | <ul style="list-style-type: none"> • Editor for Java script language • Security management • Audit trail • Scheduler functionality | <ul style="list-style-type: none"> • Extendable memory area on SD card • Web browser • IP camera image display |
|---|---|--|---|

Operator units CDPX

Product range overview, type codes

FESTO

Type	Display resolution	Number of colours	Display size	Interfaces	→ Page/ Internet
Touchscreen					
CDPX-X-A-W-4	WQVGA, 480x272 pixels	64 k	4.3"	USB, Ethernet ¹⁾ , RS485, USB, SD card	5
CDPX-X-A-W-7	WVGA, 800x480 pixels		7"		
CDPX-X-A-S-10	SVGA, 800x600 pixels		10.4"		
CDPX-X-A-W-13	WXGA, 1280x800 pixels		13.3"		

1) Ethernet switch 2x RJ45 10/100 MBd


Type codes

		CDPX-X-A	–		–	
Function						
CDPX-X-A	Operator unit					
Display size, equipment						
S	Standard display, touchscreen					
10	10.4", 64 k colours					
W	Wide-screen display, touchscreen					
4	4.3", 64 k colours					
7	7", 64 k colours					
13	13.3", 64 k colours					

Operator units CDPX

Technical data

-  - Voltage
18 ... 30 V DC
-  - Temperature range
0 ... +50 °C



General technical data				
	CDPX-X-A-W-4	CDPX-X-A-W-7	CDPX-X-A-S-10	CDPX-X-A-W-13
Display	Colour TFT			
Display properties	Touchscreen			
Display size	4.3"	7"	10.4"	13.3"
Display resolution	WQVGA, 480x272 pixels	WVGA, 800x480 pixels	SVGA, 800x600 pixels	WXGA, 1280x800 pixels
Number of colours	64 k			
Number of system LEDs	1			
Recipe memory [KB]	32			
Event lists	2,048			
Alerts	2,000			
Type of mounting	Front panel mounting			
Installation depth [mm]	56	47	56	56
Height [mm]	109	147	232	267
Length [mm]	149	187	287	336
Max. front panel thickness [mm]	4			
Note on materials	RoHS-compliant			

Electrical data				
	CDPX-X-A-W-4	CDPX-X-A-W-7	CDPX-X-A-S-10	CDPX-X-A-W-13
Nominal operating voltage DC [V]	24			
Operating voltage range DC [V]	18 ... +30			
Current consumption at nominal operating voltage [A]	0.4	0.7	1	1.2
Programming software	Designer Studio			
PLC interface	Modbus RTU			
	RS485			
USB interface	Yes			
Ethernet interface	RJ45 10/100 MBd			
Backup battery	Rechargeable lithium battery			
Real-time clock	Yes			
Real-time clock deviation	130 s/month			
Protection class	IP65 at the front following installation into control panel, IP20 at the back			

Operator units CDPX

Technical data



FESTO

Operating and environmental conditions		
Ambient temperature	[°C]	0 ... +50
Storage temperature	[°C]	−20 ... +70
Relative air humidity	[%]	5 - 85
		Non-condensing
CE marking (see declaration of conformity)		To EU EMC Directive ¹⁾
Certification		C-Tick
		cULus listed (OL)

- 1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com → Support → User documentation.
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Weight [g]					
	CDPX-X-A-W-4	CDPX-X-A-W-7	CDPX-X-A-S-10	CDPX-X-A-W-13	
Product weight	[g]	1,000	1,000	2,100	2,800

Dimensions Download CAD data → www.festo.com



Type	B1	B2	H1	H2	L1	L2
CDPX-X-A-W-4	149	136	109	996	56	4.5
CDPX-X-A-W-7	187	176	147	136	47	4


Operator units CDPX

Technical data


Dimensions

Download CAD data → www.festo.com

CDPX-X-A-S-10



CDPX-X-A-W-13



Type	B1	B2	H1	H2	L1	L2
CDPX-X-A-S-10	287	276	232	221	56	4
CDPX-X-A-W-13	336	326	267	256	56	4

Ordering data

Display resolution	Display size	Number of colours	Part No.	Type
WQVGA, 480x272 pixels	4.3"	64 k	574410	CDPX-X-A-W-4
WVGA, 800x480 pixels	7"		574411	CDPX-X-A-W-7
SVGA, 800x600 pixels	10.4"		574412	CDPX-X-A-S-10
WXGA, 1280x800 pixels	13.3"		574413	CDPX-X-A-W-13