

Amortizor de soc DYSD-Q11-12-12-Y1F-S-Y14

Numar piesa: 8161527

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	12
Cursa	12 mm
Amortizare	autoreglare
Pozitie de instalare	orice
Detectarea pozitiei	fara
Viteza max. de impact	1 m/s
Timp de resetare la temperatura camerei	0.2 s
Mod de functionare	cu apasare cu simpla actiune
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	0 °C...60 °C
Lungime de amortizare	12 mm
Forta max. de ridicare	1000 N
Consumul max. de energie pe cursa	8 J
Consum max. de energie pe ora	36000 J
Energie reziduala max.	0.05 J
Forta de restabilire	28 N
Forta minima de insertie	100 N
Greutate produs	95 g
Tipul de montare	cu piulita de blocare
Nota privind materialele	Conform RoHS
Material garnituri	NBR
Material carcasa	Otel galvanizat
Material tija de piston	otel aliaj inalt
Material piulita	Otel, galvanizat