


Heavy-duty three-point grippers HGDT

FESTO



Heavy-duty three-point grippers HGDT

Key features

FESTO

At a glance

The force generated by the linear motion is translated into the gripper jaw movement via a force-guided triple wedge mechanism. This also guarantees synchronous movement of the gripper jaw. The virtually backlash-free slideway is realised using ground-in gripper jaws.

A wide range of uses:

- Double-acting gripper
- Compression springs for supplementing or retaining gripper forces, or for use as a single-acting gripper with only one compressed air connection
- Suitable for external and internal gripping

Sealing air connection:

Compressed air flows past the gripper jaw when sealing air (max. 0.5 bar) is connected.

This prevents particles and soluble oil, etc. from entering the gripper jaw guides.

There are two variants available:

Standard – HGDT-...

Stroke per gripper jaw:

3 ... 10 mm

Total gripping force:

207 ... 1,728 N


High force – HGDT-...-F

Stroke per gripper jaw:

1.5 ... 5 mm

Total gripping force:

411 ... 3,372 N




- 1 Gripper jaw
- 2 Triple wedge mechanism
- 3 Slot for proximity sensor
- 4 Piston with magnet

Note

Design software for gripper selection
[→ www.festo.com](http://www.festo.com)


Wide range of supply ports

Direct from the front




- 1 Supply ports
- 2 O-rings

Via adapter plate from underneath




Mounting options

Direct mounting from above



- 3 Mounting screws
- 4 Centring pins or centring disc


Via adapter plate from underneath



Note


These grippers are not suitable or are of limited suitability for the following application examples:

Not suitable for:




- Welding splashes

Of limited suitability for:



- Machining with sealing air possible
- Aggressive media only possible after consultation with Festo




Heavy-duty three-point grippers HGDT


Peripherals overview and type codes

FESTO

Peripherals overview



System product for handling and assembly technology



Accessories			
Type	Brief description		→ Page/Internet
1 Gripper jaw blank BUB-HGDT	Blank specially matched to the gripper jaws for custom production of gripper fingers		17
2 Centring sleeve ZBH	For centring gripper jaw blanks/gripper fingers on the gripper jaws		18
3 Push-in fitting QS	For connecting compressed air tubing with standard O.D.		quick star
4 Blanking plug B	For sealing supply ports when using ports at the front		18
5 Proximity sensor SMT-10	For sensing the piston position, 3 slots available		18
6 Central mounting SLZZ	For centring the gripper during mounting		18
7 Dowel pin	For centring the gripper during mounting		–
8 Adapter kit HMSV, HAPG	Drive/gripper connections		15

Type codes


HGDT		–	25	–	A	–	F	–	G1
Type									
HGDT	Three-point gripper								
Size									
Position sensing									
A	Via proximity sensor								
Force variant									
F	High force								
Gripping force backup									
G1	Opening								
G2	Closing								

Heavy-duty three-point grippers HGDT

FESTO

Technical data

Function
Double-acting
HGDT-...-A



- - Size
25 ... 63
- - Stroke
1.5 ... 10 mm

Single-acting or
with gripping force retention ...
... opening HGDT-...-G1



... closing HGDT-...-G2



General technical data							
Size			25	35	40	50	63
Constructional design			Wedge-shaped actuator				
			Force-guided motion sequence				
Mode of operation			Double-acting				
Gripper function			3-point				
Number of gripper jaws			3				
Stroke per gripper jaw	HGDT-...-A	[mm]	3	4	6	8	10
	HGDT-...-A-F	[mm]	1.5	2	3	4	5
Pneumatic connection			M5	M5	M5	G1/8	G1/8
Pneumatic connection for sealing air			M5				
Repetition accuracy ¹⁾		[mm]	≤0.03				
Max. operating frequency		[Hz]	≤4				
Position sensing			Via proximity sensor				
Type of mounting			Via through-hole, locating pin or centring disc				
			Via female thread, locating pin or centring disc				
Mounting position			Any				

1) Concentric to the central shaft

Operating and environmental conditions		
Min. operating pressure	HGDT-... [bar]	3
	HGDT-...-G... [bar]	4
Max. operating pressure	[bar]	8
Sealing air operating pressure	[bar]	0 ... 0.5
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)	
Ambient temperature ¹⁾ [°C]	+5 ... +60	
Corrosion resistance class CRC ²⁾	2	

1) Note operating range of proximity sensors

2) Corrosion resistance class 2 as per Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Heavy-duty three-point grippers HGDT


FESTO

Technical data

Weight [g]					
Size	25	35	40	50	63
HGDT-...	185	307	712	1,104	1,873
HGDT-...-G1	203	337	840	1,592	2,469
HGDT-...-G2	203	385	837	1,440	2,543


Materials

Sectional view



Three-point gripper		
1	Gripper jaw	Hardened steel
2	Housing	Aluminium, coated with CompCote
3	Piston	Anodised aluminium
4	Spring	Spring steel
–	Seals	Nitrile rubber
–	Note on materials	Free of copper, PTFE and silicone
		RoHS-compliant

Characteristic load values at the gripper jaws




The indicated permissible forces and torques apply to a single gripper jaw. They include the lever arm, additional applied loads due to the workpiece or external gripper fingers and acceleration forces occurring during movement.

The zero coordinate line (gripper finger point of rotation) must be taken into consideration for the calculation of torques.

Size		25	35	40	50	63
Max. permissible force F_z	[N]	350	400	800	1,500	2,500
Max. permissible torque M_x	[Nm]	7	15	30	50	80
Max. permissible torque M_y	[Nm]	10	10	20	30	50
Max. permissible torque M_z	[Nm]	5	10	25	40	60

Moment of inertia [kgcm²]



Mass moment of inertia of the three-point gripper in relation to the central axis, without external gripper fingers, without load.

Size	25	35	40	50	63
HGDT-...	0.48	1.17	4.37	11.05	28.77
HGDT-...-G1	0.5	1.37	5.59	15.33	42.44
HGDT-...-G2	0.5	1.37	5.23	13.92	39.50

Heavy-duty three-point grippers HGDT



Technical data

FESTO

Opening and closing times [ms] at 6 bar

Without external gripper fingers

With external gripper fingers




The indicated opening and closing times [ms] have been measured at room temperature at an operating pressure of 6 bar with horizontally mounted gripper without additional

gripper fingers. The grippers must be throttled for greater applied loads. Opening and closing times must then be adjusted accordingly.

Size			25	35	40	50	63
Without external gripper fingers							
Standard	HGDT-...-A	opening	28	40	62	85	152
		closing	25	45	59	75	142
	HGDT-...-A-G1	opening	27	32	58	32	48
		closing	33	56	160	146	246
	HGDT-...-A-G2	opening	33	46	111	61	159
		closing	25	35	87	70	107
High force	HGDT-...-A-F	opening	20	43	48	96	163
		closing	30	39	49	83	162
	HGDT-...-A-F-G1	opening	25	29	63	31	70
		closing	61	67	190	170	299
	HGDT-...-A-F-G2	opening	38	53	117	88	169
		closing	33	36	104	65	128
With external gripper fingers per gripper finger (as a function of weight force)							
HGDT-...	0.2 N	80	–	–	–	–	
	0.3 N	100	130	–	–	–	
	0.7 N	150	200	115	–	–	
	1 N	180	240	140	–	–	
	1.5 N	220	290	170	–	–	
	2 N	–	335	200	190	–	
	2.5 N	–	–	220	210	190	
	3 N	–	–	–	230	200	
	4 N	–	–	–	270	230	
5 N	–	–	–	–	260		

Gripping force [N] at 6 bar



Size			25	35	40	50	63
Gripping force per gripper jaw							
Standard	HGDT-...-A	opening	82	164	229	347	576
		closing	69	152	206	307	551
High force	HGDT-...-A-F	opening	180	294	367	740	1,124
		closing	148	274	330	625	864
Total gripping force							
Standard	HGDT-...-A	opening	246	492	687	1,041	1,728
		closing	207	456	618	921	1,653
High force	HGDT-...-A-F	opening	540	882	1,101	2,220	3,372
		closing	444	822	990	1,875	2,592
Total gripping force with spring support (gripping force retention)							
Standard	HGDT-...-A	opening	286	555	814	1,159	2,186
		closing	228	547	712	1,052	2,172
High force	HGDT-...-A-F	opening	708	1,254	1,629	2,800	4,456
		closing	612	1,194	1,518	2,655	4,338

Heavy-duty three-point grippers HGDT


FESTO

Technical data

Standard – HGDT-...


Gripping force F_{Grip} per gripper jaw as a function of operating pressure and lever arm x

The gripping forces as a function of operating pressure and lever arm can be determined from the following graphs.




External gripping (closing)


HGDT-25-A




HGDT-35-A




HGDT-40-A



HGDT-50-A



HGDT-63-A



— 3 bar
 - - - 6 bar
 - · - 8 bar

Heavy-duty three-point grippers HGDT


Technical data

FESTO

Standard – HGDT-...


Gripping force F_{Grip} per gripper jaw as a function of operating pressure and lever arm x

The gripping forces as a function of operating pressure and lever arm can be determined from the following graphs.




Internal gripping (opening)


HGDT-25-A




HGDT-35-A




HGDT-40-A



HGDT-50-A



HGDT-63-A



— 3 bar
 - - - 6 bar
 - · - 8 bar

Heavy-duty three-point grippers HGDT


FESTO

Technical data

High force – HGDT-...-F


Gripping force F_{Grip} per gripper jaw as a function of operating pressure and lever arm x

The gripping forces as a function of operating pressure and lever arm can be determined from the following graphs.




External gripping (closing)


HGDT-25-A-F




HGDT-35-A-F




HGDT-40-A-F



HGDT-50-A-F



HGDT-63-A



— 3 bar
 - - - 6 bar
 - · - 8 bar

Heavy-duty three-point grippers HGDT


Technical data

FESTO

High force – HGDT-...-F


Gripping force F_{Grip} per gripper jaw as a function of operating pressure and lever arm x

The gripping forces as a function of operating pressure and lever arm can be determined from the following graphs.




Internal gripping (opening)


HGDT-25-A-F




HGDT-35-A-F




HGDT-40-A-F



HGDT-50-A-F



HGDT-63-A-F



— 3 bar
 - - - 6 bar
 - · - 8 bar

Heavy-duty three-point grippers HGDT


Technical data

FESTO


Spring force F_S as a function of size, gripper jaw stroke l and gripper length x , per gripper finger

Gripping force retention for HGDT-...-G...

The spring forces F_S as a function of the gripper jaw stroke can be determined from the following graph.




Standard – HGDT-...



——— HGDT-25-A-G... - - - - - HGDT-50-A-G...
 - - - - - HGDT-35-A-G... - HGDT-63-A-G...
 ——— HGDT-40-A-G...

High force – HGDT-...-F-...



——— HGDT-25-A-F-G... - - - - - HGDT-50-A-F-G...
 - - - - - HGDT-35-A-F-G... - HGDT-63-A-F-G...
 ——— HGDT-40-A-F-G...

The lever arm x [mm] must be taken into consideration when determining the actual spring force $F_{S\text{total}}$.

The formulae for calculating the spring force are provided in the table below.

Size	$F_{S\text{total}}$, per gripper finger	
	Standard – HGDT-...	High force – HGDT-...-F
25	$-0.3 \cdot x + 0.85 \cdot F_S$	$-2.24 \cdot x + 0.64 \cdot F_S$
35	$-0.5 \cdot x + 0.75 \cdot F_S$	$-0.97 \cdot x + 0.7 \cdot F_S$
40	$-0.5 \cdot x + 0.8 \cdot F_S$	$-1.45 \cdot x + 0.66 \cdot F_S$
50	$-0.6 \cdot x + 0.7 \cdot F_S$	$-0.97 \cdot x + 0.51 \cdot F_S$
63	$-0.6 \cdot x + 0.75 \cdot F_S$	$-2.35 \cdot x + 0.72 \cdot F_S$

Determining the actual gripping forces F_{Gr} for HGDT-...-A-G1 and HGDT-...-A-G2 as a function of the application, per gripper finger

The three-point grippers with integrated spring type HGDT-...-G1 (opening gripping force retention) and HGDT-...-G2 (closing gripping force retention) can be used as:

- single-acting grippers

- grippers with supplementary gripping force and
- grippers with gripping force retention depending on the requirements.

In order to calculate the available gripping forces F_{Gr} (per gripper finger), the gripping force (F_{Grip}) and spring

force ($F_{S\text{total}}$) must be combined accordingly.

Application forces per gripper finger

Single-acting	Supplementary gripping force	Gripping force retention
- Gripping with spring force: $F_{Gr} = F_{S\text{total}}$ - Gripping with pressure force: $F_{Gr} = F_{Grip} - F_{S\text{total}}$	Gripping with pressure and spring force: $F_{Gr} = F_{Grip} + F_{S\text{total}}$	Gripping with spring force: $F_{Gr} = F_{S\text{total}}$


Heavy-duty three-point grippers HGDT

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



Size	B1	B2		B3	B4	B5	B6	B7	D1	D2
		with HGDT-...	with HGDT-...F							
[mm]	±0.5	±0.5	±0.5			±0.02	±0.02	-0.05 -0.1	∅ ±0.1	∅ ±0.1
HGDT-25-A	22	25	23.5	9.5	19	6	3	6	48	38
HGDT-25-A-G...										
HGDT-35-A	27	31	29	11	22	8	4	6.5	58	44
HGDT-35-A-G...										
HGDT-40-A	35	41	38	14	28	12	5	10	74	56
HGDT-40-A-G...										
HGDT-50-A	43.5	51.5	47.5	17.5	35	15	6	12	93	70
HGDT-50-A-G...										
HGDT-63-A	54	64	59	22.5	45	18	10	14	116	90
HGDT-63-A-G...										

Heavy-duty three-point grippers HGDT

FESTO

Technical data

Size [mm]	D3 Ø H8	D4 Ø H8/h7	D5 Ø	D6 Ø	D7 Ø	D8 Ø H13	D9 Ø H13	D10 Ø H8	D11	D12 Ø	D13 Ø H8/h7	EE	EE1
HGDT-25-A	3	5	3.2	M3	M4	5.9	3.3	14	M2	–	–	M5	M3
HGDT-25-A-G...													
HGDT-35-A	3	5	3.2	M3	M4	5.9	3.3	25	M3	3.2	5	M5	M3
HGDT-35-A-G...													
HGDT-40-A	4	7	5.3	M4	M6	9.4	5.1	25	M3	3.2	5	M5	M5
HGDT-40-A-G...													
HGDT-50-A	5	9	6.4	M6	M8	10.2	6.4	25	M5	5.3	7	G ¹ / ₈	M5
HGDT-50-A-G...													
HGDT-63-A	5	9	6.4	M6	M8	10.4	6.4	25	M5	5.3	7	G ¹ / ₈	M5
HGDT-63-A-G...													

Size [mm]	EE2	H1 ±0.05	H2 ±0.05	H3	H4	H5 ±0.1	H6 ±0.1	H7 –0.3	H8	H9 –0.02	H10 –0.2	H11 –0.3	L1 ±0.5
HGDT-25-A	M5	41.5	40.5	32.5	29.3	9	13.5	1.1	2.25±0.1	8.5	3.5	–	6
HGDT-25-A-G...													
HGDT-35-A	M5	46	45	37	33.5	9	18.5	1.1	3±0.02	12	3.5	1.1	7
HGDT-35-A-G...													
HGDT-40-A	M5	55	54	44	38.4	9	25	1.4	4.5±0.02	16	3.5	1.1	9
HGDT-40-A-G...													
HGDT-50-A	M5	64.5	63.5	50.5	45	12	32	1.9	5.5±0.02	19	3.5	1.4	9
HGDT-50-A-G...													
HGDT-63-A	M5	69	68	50	44.5	12	42	1.9	5.5±0.02	22	3.5	1.4	12
HGDT-63-A-G...													

Size [mm]	L2 ±0.1	L3 ±0.1	L4 ±0.02	L5	L6	T1 min.	T2 +0.1	T3 min.	T4 +0.2	T5 min.	T6 +0.1	T7 +0.1	T8 min.
HGDT-25-A	12	12	38	16.45	6±0.1	3.5	1.3	5	3.2	8	2	–	3
HGDT-25-A-G...													
HGDT-35-A	12	15	45	19.05	6±0.02	5	1.3	5.5	3.2	8	2	1.3	6
HGDT-35-A-G...													
HGDT-40-A	12	18	56	24.25	6±0.02	6	1.6	6.5	5.1	10	2	1.3	6
HGDT-40-A-G...													
HGDT-50-A	24	18	70	30.31	13±0.02	8	2.1	10.5	6.1	12	2	1.6	9
HGDT-50-A-G...													
HGDT-63-A	24	24	90	38.97	13±0.02	8	2.1	10.5	6.1	12	2	1.6	9
HGDT-63-A-G...													

Heavy-duty three-point grippers HGDT



Technical data

Ordering data						
Size [mm]	Double-acting without compression spring Part No. Type		Single-acting or with gripping force retention			
			opening Part No. Type		closing Part No. Type	
Standard						
25	540859	HGDT-25-A	540860	HGDT-25-A-G1	540861	HGDT-25-A-G2
35	540862	HGDT-35-A	540863	HGDT-35-A-G1	540864	HGDT-35-A-G2
40	540865	HGDT-40-A	540866	HGDT-40-A-G1	540867	HGDT-40-A-G2
50	540868	HGDT-50-A	540869	HGDT-50-A-G1	540870	HGDT-50-A-G2
63	540871	HGDT-63-A	540872	HGDT-63-A-G1	540873	HGDT-63-A-G2
High force						
25	560177	HGDT-25-A-F	560178	HGDT-25-A-F-G1	560179	HGDT-25-A-F-G2
35	560180	HGDT-35-A-F	560181	HGDT-35-A-F-G1	560182	HGDT-35-A-F-G2
40	560183	HGDT-40-A-F	560184	HGDT-40-A-F-G1	560185	HGDT-40-A-F-G2
50	560186	HGDT-50-A-F	560187	HGDT-50-A-F-G1	560188	HGDT-50-A-F-G2
63	560189	HGDT-63-A-F	560190	HGDT-63-A-F-G1	560191	HGDT-63-A-F-G2

Heavy-duty three-point grippers HGDT

Accessories

FESTO





Adapter kit
HAPG, HMSV

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant



Note

The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit				Download CAD data → www.festo.com	
Combination	Drive	Gripper	Adapter kit		
	Size	Size	CRC ¹⁾	Part No.	Type
DGSL/HGDT	DGSL	HGDT	HAPG		
	16	25	2	542439	HAPG-SD2-32
	16	35		542436	HAPG-94
				548805	ZBV-9-7
	20, 25	35		542436	HAPG-94
	20, 25	40		542437	HAPG-95
	25	50		542443	HAPG-SD2-36
			548806	ZBV-12-9	
SLT/HGDT	SLT	HGDT	HAPG		
	16	25	2	542433	HAPG-97
	20	25		542439	HAPG-SD2-32
	16	35		542435	HAPG-99
	20, 25	35		542436	HAPG-94
	20, 25	40		542437	HAPG-95
	25	50		542443	HAPG-SD2-36
HMP/HGDT	HMP	HGDT	HAPG		
	16	35	2	542434	HAPG-98
	16, 20, 25	40		542437	HAPG-95
	20, 25, 32	50		542443	HAPG-SD2-36
	25, 32	63		542438	HAPG-96
DRQD/HGDT	DRQD	HGDT	HAPG		
	16 ²⁾	25	2	542439	HAPG-SD2-32
	20 ²⁾ , 25 ³⁾	25		542440	HAPG-SD2-33
	20 ²⁾ , 25 ³⁾ , 32 ³⁾	35		542441	HAPG-SD2-34
	25 ³⁾ , 35 ³⁾	40		542442	HAPG-SD2-35
	32 ³⁾	50		542443	HAPG-SD2-36

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 2) Possible in combination with DRQD-...-E422 (flanged shaft with energy through-feed).
- 3) Possible in combination with DRQD-...-E444 (flanged shaft with energy through-feed).

Heavy-duty three-point grippers HGDT

Accessories

FESTO





Adapter kit
HAPG, HMSV

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant



Note

The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit				Download CAD data → www.festo.com	
Combination	Drive	Gripper	Adapter kit		
	Size	Size	CRC ¹⁾	Part No.	Type
EGSL/HGDT	EGSL	HGDT	HAPG		
	35	25	2	542433	HAPG-97
	45, 55	25		542439	HAPG-SD2-32
	45, 55, 75	35		542436	HAPG-94
	75	40		542437	HAPG-95
	75	50		542443	HAPG-SD2-36
EGSA/HGDT	EGSA	HGDT	HAPG, HMSV		
	50	25	2	542439	HAPG-SD2-32
				560017	HMSV-61
	50	35		542436	HAPG-94
				560017	HMSV-61
				548805	ZBV-9-7
	60	35		542436	HAPG-94
				560018	HMSV-62
				548806	ZBV-12-9
	60	40		542437	HAPG-95
				560018	HMSV-62
				548806	ZBV-12-9
ERMB/HGDT	ERMB	HGDT	HAPG		
	20, 25	25	2	542440	HAPG-SD2-33
	20, 25, 32	35		542441	HAPG-SD2-34
	25, 32	40		542442	HAPG-SD2-35
	32	50		542443	HAPG-SD2-36
EHMB/HGDT	EHMB	HGDT	HAPG		
	20	35	2	542441	HAPG-SD2-34
	20	40		542442	HAPG-SD2-35
	20	50		542443	HAPG-SD2-36

1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Heavy-duty three-point grippers HGDT

Accessories

FESTO


Gripper jaw blank BUB-HGDT

(scope of delivery: 3 pieces)

Material:

Wrought aluminium alloy

Free of copper, PTFE and silicone



Dimensions and ordering data							
For size	B1	B2	D1	D2	D3	H1	L1
[mm]	±0.05	+0.22	∅ H13	∅ H8	∅ +0.22	±0.05	±0.05
25	11	5.9	3.2	5	–	20	21.6
35	11	–	3.2	5	5.9	35	26.5
40	16	–	4.3	7	7.4	50	34
50	20	–	6.3	9	10.4	65	42
63	24	–	6.3	9	10.4	80	52

For size	L2 ±0.02 ¹⁾ ±0.1 ²⁾	L3 ±0.01 ¹⁾ ±0.1 ¹⁾	T1 +0.1	T2	Weight per blank [g]	Part No.	Type
[mm]							
25	12.6	6	1.3	14	10	541101	BUB-HGDT-25
35	14.5	8	1.3	29	22	541102	BUB-HGDT-35
40	17	12	1.6	45	59	541103	BUB-HGDT-40
50	21	15	2.1	58	112	541104	BUB-HGDT-50
63	24	18	2.1	73	222	541105	BUB-HGDT-63

1) For centring

2) For through-hole

Heavy-duty three-point grippers HGDT

Accessories

FESTO

Ordering data						
	For size [mm]	Remarks	Weight [g]	Part No.	Type	PU ¹⁾
Centring sleeve ZBH Technical data → Internet: zbh						
	25, 35	For centring gripper jaw blanks/gripper fingers on the gripper jaws	1	189652	ZBH-5	10
	40		1	186717	ZBH-7	
	50, 63		1	150927	ZBH-9	
	35, 40	For lateral centring of gripper fingers on the gripper jaws	1	189652	ZBH-5	
	50, 63		1	186717	ZBH-7	
Central mounting SLZZ Technical data → Internet: slzz						
	25	For centring the gripper during mounting	21	150900	SLZZ-16/10	–
	35, 40, 50, 63		40	150901	SLZZ-25/16	
Blanking plug B Technical data → Internet: blanking plug						
	25 ... 63	For sealing the supply ports	0.6	30979	B-M3-S9	10
			1	174308	B-M5-B	
			5	3568	B-1/8	

1) Packaging unit

Ordering data – Proximity sensors for C-slot, in-line connecting cable						Technical data → Internet: smt	
	Assembly	Electrical connection		Cable length [m]	Part No.	Type	
		Cable	Plug M8				
N/O contact, magneto-resistive							
	Insertable in the slot from above	–	3-pin	0.3	551375	SMT-10M-PS-24V-E-0,3-L-M8D	
		3-wire	–	2.5	551373	SMT-10M-PS-24V-E-2,5-L-OE	

Ordering data – Proximity sensors for C-slot, lateral connecting cable						Technical data → Internet: smt	
	Assembly	Electrical connection		Cable length [m]	Part No.	Type	
		Cable	Plug M8				
	N/O contact, magneto-resistive						
	Insertable in the slot from above	3-wire	–	2.5	551374	SMT-10M-PS-24V-E-2,5-Q-OE	
		–	3-pin	0.3	551376	SMT-10M-PS-24V-E-0,3-Q-M8D	

Ordering data – Connecting cables					Technical data → Internet: nebu
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541333	NEBU-M8G3-K-2.5-LE3
			5	541334	NEBU-M8G3-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541338	NEBU-M8W3-K-2.5-LE3
			5	541341	NEBU-M8W3-K-5-LE3