

Pressure gauges

FESTO



Pressure gauges

Product range overview

FESTO


Type		Pneumatic connection	Nominal size							Display unit			Red/ green range	→ Page/ Internet
			15	23	26	27	40	50	63	bar	MPa	psi		
Pressure gauge MA-...-EN		R $\frac{1}{8}$, R $\frac{1}{4}$, G $\frac{1}{4}$	-	-	-	-	■	■	■	■	-	■	-	3
Pressure gauge with red/green range MA-...-RG		R $\frac{1}{8}$, R $\frac{1}{4}$	-	-	-	-	■	■	■	■	■	■	■	6
Pressure gauge MA		M5, R $\frac{1}{8}$, G $\frac{1}{8}$, G $\frac{1}{4}$	■	■	-	■	■	■	■	■	■	■	-	9
Precision pressure gauge MAP		R $\frac{1}{8}$	-	-	-	-	■	-	-	■	-	■	-	13
Pressure gauge MA-...-QS		QS-4, QS-6, QS-8	■	-	-	-	-	-	-	■	-	-	-	14
Flanged pressure gauge FMA-...-EN		G $\frac{1}{4}$	-	-	-	-	■	■	■	■	-	■	-	15
Flanged pressure gauge FMA		G $\frac{1}{4}$	-	-	-	-	-	-	■	■	-	■	-	17
Precision flanged pressure gauge FMAP		G $\frac{1}{4}$	-	-	-	-	-	-	■	■	-	■	-	18
Pressure gauge PAGN		For QSP10	-	-	■	-	■	-	-	■	■	■	-	20

Pressure gauges MA-EN

Technical data

FESTO

Function



— — Temperature range
–20 ... +60 °C



Technical data					
Nominal size	40			50	63
Pneumatic connection	R $\frac{1}{8}$	R $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{1}{4}$
Operating medium	Inert gases				
	Neutral liquids				
Note on operating/pilot medium	No oxygen				
	No acetylene				
Design	Bourdon tube pressure gauge				
Conforms to	EN 837-1				
Type of mounting	Inline installation				
Connection position	Centred, rear side				
Ambient temperature [°C]	–20 ... +60				
Temperature of medium [°C]	–20 ... +60 ¹⁾				
Measurement accuracy class	2.5				
Continuous load factor	0.75				
Intermittent load factor	0.66				
Protection class	IP43				
For MS series service units	MS4	MS4/MS6/MS9/MS12		–	–
Weight [g]	60	70	70	70	80

1) With a media temperature below 0 °C, the operating medium should be dry.

Materials					
Nominal size	40			50	63
Pneumatic connection	R $\frac{1}{8}$	R $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{1}{4}$
Housing	Acrylic butadiene styrene (colour: black)				
Inspection window	Polystyrene				
Threaded plug	Brass				
Materials in contact with the medium	Brass				
Note on materials	RoHS-compliant				

Display range						
Nominal size	40			50	63	
Pneumatic connection	R $\frac{1}{8}$	R $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{1}{4}$	
[bar]	[psi]					
0 ... 1	0 ... 14.5	–	–	–	–	■
0 ... 2.5	0 ... 36	–	–	–	■	■
0 ... 6	0 ... 87	–	■	■	–	–
0 ... 10	0 ... 145	■	■	■	■	■
0 ... 16	0 ... 232	–	■	■	■	■
0 ... 25	0 ... 360	■	■	■	–	–

Pressure gauges MA-EN


Technical data

FESTO

Dimensions


Download CAD data → www.festo.com

MA-40, R $\frac{1}{8}$




- 1 PTFE seal with
MA-40-25- $\frac{1}{8}$ -EN

MA-40, R $\frac{1}{4}$




- 1 PTFE seal

MA-40, G $\frac{1}{4}$



- 1 With pre-assembled PTFE
sealing ring

MA-50/63, G $\frac{1}{4}$



Type	D1 Ø	L1	L2
MA-50	49	47.5	26.5
MA-63	61.5	48.5	27.5

- 2 - Type MA-40-25-G $\frac{1}{4}$ -EN discontinued
Available up until 2012

Pressure gauges MA-EN

Technical data

FESTO

Ordering data					
Nominal size	Pneumatic connection	Operating pressure	Display range		Part No. Type
			[bar]	[psi]	
40	R $\frac{1}{8}$	0 ... 10 bar	0 ... 10	0 ... 145	162835 MA-40-10-R $\frac{1}{8}$ -EN
		0 ... 25 bar	0 ... 25	0 ... 360	526167 MA-40-25-R $\frac{1}{8}$ -EN
	R $\frac{1}{4}$	0 ... 6 bar	0 ... 6	0 ... 87	187078 MA-40-6-R $\frac{1}{4}$ -EN
		0 ... 10 bar	0 ... 10	0 ... 145	187079 MA-40-10-R $\frac{1}{4}$ -EN
		0 ... 16 bar	0 ... 16	0 ... 232	187080 MA-40-16-R $\frac{1}{4}$ -EN
		0 ... 25 bar	0 ... 25	0 ... 360	187081 MA-40-25-R $\frac{1}{4}$ -EN
	G $\frac{1}{4}$	0 ... 6 bar	0 ... 6	0 ... 87	183899 MA-40-6-G $\frac{1}{4}$ -EN
		0 ... 10 bar	0 ... 10	0 ... 145	183900 MA-40-10-G $\frac{1}{4}$ -EN
		0 ... 16 bar	0 ... 16	0 ... 232	183901 MA-40-16-G $\frac{1}{4}$ -EN
		0 ... 25 bar	0 ... 25	0 ... 360	183902 MA-40-25-G $\frac{1}{4}$ -EN
50	G $\frac{1}{4}$	0 ... 2.5 bar	0 ... 2.5	0 ... 36	162837 MA-50-2,5-G $\frac{1}{4}$ -EN
		0 ... 10 bar	0 ... 10	0 ... 145	162838 MA-50-10-G $\frac{1}{4}$ -EN
		0 ... 16 bar	0 ... 16	0 ... 232	162839 MA-50-16-G $\frac{1}{4}$ -EN
63	G $\frac{1}{4}$	0 ... 1 bar	0 ... 1	0 ... 14.5	162844 MA-63-1-G $\frac{1}{4}$ -EN
		0 ... 2.5 bar	0 ... 2.5	0 ... 36	162845 MA-63-2,5-G $\frac{1}{4}$ -EN
		0 ... 10 bar	0 ... 10	0 ... 145	162840 MA-63-10-G $\frac{1}{4}$ -EN
		0 ... 16 bar	0 ... 16	0 ... 232	162841 MA-63-16-G $\frac{1}{4}$ -EN

Pressure gauges MA-RG, with red/green range

FESTO

Technical data

Function



-  - Temperature range
-20 ... +60 °C



The adjustable red/green range provides additional safety when monitoring compressed air.

With the two red segments above the pressure gauge scale along with the printed green segment it is possible to

individually limit the desired pressure range. This coloured demarcation enables you to recognise immediately

whether or not the pressure is in the permitted tolerance range.

Technical data			
Nominal size	40	50	63
Pneumatic connection	R $\frac{1}{8}$	R $\frac{1}{4}$	R $\frac{1}{4}$
Operating medium	Inert gases		
	Neutral liquids		
Note on operating/pilot medium	No oxygen		
	No acetylene		
Design	Bourdon tube pressure gauge		
Conforms to	EN 837-1		
Type of mounting	Inline installation		
Connection position	Centred, rear side		
Ambient temperature [°C]	-20 ... +60		
Temperature of medium [°C]	-20 ... +60 ¹⁾		
Measurement accuracy class	2.5		
Continuous load factor	0.75		
Intermittent load factor	0.66		
Protection class	IP43		
For MS series service units	MS4	MS4/MS6/MS9/MS12	–
Weight [g]	60	75	90

1) With a media temperature below 0 °C, the operating medium should be dry.

Materials	
Housing	Acrylic butadiene styrene (colour: black)
Inspection window	Polymethyl methacrylate
Threaded plug/ materials in contact with the medium	Brass
Note on materials	RoHS-compliant

Pressure gauges MA-RG, with red/green range

FESTO


Technical data

Display range			
Nominal size	40	50	63
Pneumatic connection	R $\frac{1}{8}$	R $\frac{1}{4}$	R $\frac{1}{4}$
[bar]			
0 ... 2.5	■	■	■
0 ... 10	■	■	■
0 ... 16	■	■	■
[MPa]			
0 ... 0.25	–	■	■
0 ... 1	■	■	■
0 ... 1.6	■	■	■
[psi]			
0 ... 36	–	■	■
0 ... 145	■	■	■
0 ... 232	■	■	■

Dimensions

Download CAD data → www.festo.com

MA-...-E-RG



Type	D1 Ø ±0.5	D2	L1 ±1	L2 ±0.5	L3
MA-40-...-E-RG	39	R $\frac{1}{8}$	46	28	10
MA-50-...-E-RG	49	R $\frac{1}{4}$	49	28	13
MA-63-...-E-RG	61.5	R $\frac{1}{4}$	50.5	29.5	13

Pressure gauges MA-RG, with red/green range

FESTO

Technical data

Ordering data					
Nominal size	Pneumatic connection	Operating pressure	Display range	Part No.	Type
Display unit [bar]					
40	R1/8	0 ... 2.5 bar	0 ... 2.5	546963	MA-40-2,5-R1/8-E-RG
		0 ... 10 bar	0 ... 10	525725	MA-40-10-R1/8-E-RG
		0 ... 16 bar	0 ... 16	525726	MA-40-16-R1/8-E-RG
50	R1/4	0 ... 2.5 bar	0 ... 2.5	525727	MA-50-2,5-R1/4-E-RG
		0 ... 10 bar	0 ... 10	525728	MA-50-10-R1/4-E-RG
		0 ... 16 bar	0 ... 16	525729	MA-50-16-R1/4-E-RG
63	R1/4	0 ... 2.5 bar	0 ... 2.5	525730	MA-63-2,5-R1/4-E-RG
		0 ... 10 bar	0 ... 10	525731	MA-63-10-R1/4-E-RG
		0 ... 16 bar	0 ... 16	525732	MA-63-16-R1/4-E-RG
Display unit [MPa]					
40	R1/8	0 ... 1 MPa	0 ... 1	526778	MA-40-1,0-R1/8-MPA-E-RG
		0 ... 1.6 MPa	0 ... 1.6	526779	MA-40-1,6-R1/8-MPA-E-RG
50	R1/4	0 ... 0.25 MPa	0 ... 0.25	526780	MA-50-0,25-R1/4-MPA-E-RG
		0 ... 1 MPa	0 ... 1	526781	MA-50-1,0-R1/4-MPA-E-RG
		0 ... 1.6 MPa	0 ... 1.6	526782	MA-50-1,6-R1/4-MPA-E-RG
63	R1/4	0 ... 0.25 MPa	0 ... 0.25	526783	MA-63-0,25-R1/4-MPA-E-RG
		0 ... 1 MPa	0 ... 1	526784	MA-63-1,0-R1/4-MPA-E-RG
		0 ... 1.6 MPa	0 ... 1.6	526785	MA-63-1,6-R1/4-MPA-E-RG
Display unit [psi]					
40	R1/8	0 ... 145 psi	0 ... 145	526786	MA-40-145-R1/8-PSI-E-RG
		0 ... 232 psi	0 ... 232	526787	MA-40-232-R1/8-PSI-E-RG
50	R1/4	0 ... 36 psi	0 ... 36	526788	MA-50-36-R1/4-PSI-E-RG
		0 ... 145 psi	0 ... 145	526789	MA-50-145-R1/4-PSI-E-RG
		0 ... 232 psi	0 ... 232	526790	MA-50-232-R1/4-PSI-E-RG
63	R1/4	0 ... 36 psi	0 ... 36	526791	MA-63-36-R1/4-PSI-E-RG
		0 ... 145 psi	0 ... 145	526792	MA-63-145-R1/4-PSI-E-RG
		0 ... 232 psi	0 ... 232	526793	MA-63-232-R1/4-PSI-E-RG

Pressure gauges MA


Technical data

FESTO

Function



— — Temperature range
–20 ... +60 °C



Technical data									
Nominal size	15	23	27			40		50	63
Pneumatic connection	M5	R1/8	M5	R1/8	G1/8	G1/4	G1/4	G1/4	
Operating medium	Inert gases								Gaseous media
	Neutral liquids								Fluid media
Note on operating/pilot medium	No oxygen								
	No acetylene								
Design	Bourdon tube pressure gauge without measuring mechanism	Bourdon tube pressure gauge							Capsule pressure gauge
Conforms to	EN 837-1								EN 837-3
Type of mounting	Inline installation								
Connection position	Centred, rear side								
Ambient temperature [°C]	-20 ... +60		0 ... +60		-20 ... +60			-20 ... +60	
Temperature of medium [°C]	-20 ... +60 ¹⁾		0 ... +60		-20 ... +60 ¹⁾			-20 ... +80 ¹⁾	
Measurement accuracy class	5		4		2.5			1.6	
Continuous load factor	0.75		0.75					0.75	
Intermittent load factor	0.66	0.6	0.66					0.9	
Protection class	IP53	IP44	IP43					IP43	
For D series service units	–	–	MICRO	–	MINI	–	MIDI/MAXI	–	
Weight [g]	10	27	11	8	60	70	70	180	

1) With a media temperature below 0 °C, the operating medium should be dry.

Materials								
Nominal size	15	23	27		40		50	63
Pneumatic connection	M5	R1/8	M5	R1/8	G1/8	G1/4	G1/4	G1/4
Housing	Steel (colour: black)	Brass (colour: black)	Polyamide (colour: black)		Acrylic butadiene styrene (colour: black)			Steel
Inspection window	Polycarbonate		Polystyrene		Polystyrene			Polymethyl methacrylate
Threaded plug/ materials in contact with the medium	Brass		Brass	Reinforced polyamide	Brass			Brass
Note on materials	RoHS-compliant							

Pressure gauges MA

Technical data


FESTO

Display range									
Nominal size		15	23	27		40		50	63
Pneumatic connection		M5	R $\frac{1}{8}$	M5	R $\frac{1}{8}$	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{1}{4}$
[bar]	[psi]								
0 ... 0.25	0 ... 3.6	–	–	–	–	–	–	–	■
0 ... 6	0 ... 87	–	■	–	–	–	–	–	–
0 ... 10	0 ... 145	–	■	–	–	■	–	■	–
0 ... 16	0 ... 232	–	■	–	■	■	–	■	–
0 ... 25	0 ... 360	–	–	–	■	–	–	–	–
[bar]									
0 ... 10		■	–	■	–	–	–	–	–
[MPa]									
0 ... 0.6		–	–	–	–	–	■	–	–
0 ... 1		–	–	■	–	■	■	■	–
0 ... 1.6		–	–	–	–	■	■	■	–
0 ... 2.5		–	–	–	–	–	■	–	–
[psi]									
0 ... 145		■	–	–	–	–	–	–	–
0 ... 160		–	–	■	–	–	–	–	–

Dimensions

Download CAD data → www.festo.com

MA-15



Type	D1 Ø	D2	L1	L2	≡
MA-15	15	M5	16.5	3	14

Pressure gauges MA


Technical data

FESTO


Dimensions

Download CAD data → www.festo.com

MA-23




MA-27, M5




1 With pre-assembled polyamide sealing ring

MA-27, R1/8




MA-40, G1/8




1 With pre-assembled aluminium sealing ring with MA-40-...-G1/8-MPA

MA-40, G1/4




MA-50



1 With pre-assembled aluminium sealing ring with MA-50-...-G1/4-MPA

MA-63



Pressure gauges MA

Technical data

FESTO

Ordering data						
Nominal size	Pneumatic connection	Operating pressure	Display range		Part No.	Type
			[bar]	[psi]		
23	R1/8	0 ... 6 bar	0 ... 6	0 ... 87	183896	MA-23-6-R1/8
		0 ... 10 bar	0 ... 10	0 ... 145	183897	MA-23-10-R1/8
		0 ... 16 bar	0 ... 16	0 ... 232	183898	MA-23-16-R1/8
27	R1/8	0 ... 16 bar	0 ... 16	0 ... 232	541733	MA-27-16-R1/8
		0 ... 25 bar	0 ... 25	0 ... 360	541734	MA-27-25-R1/8
40	G1/8	0 ... 10 bar	0 ... 10	0 ... 145	359874	MA-40-10-1/8
		0 ... 16 bar	0 ... 16	0 ... 232	345395	MA-40-16-1/8
50	G1/4	0 ... 10 bar	0 ... 10	0 ... 145	359873	MA-50-10-1/4
		0 ... 16 bar	0 ... 16	0 ... 232	356759	MA-50-16-1/4
63	G1/4	0 ... 0.25 bar	0 ... 0.25	0 ... 3.6	7169	MA-63-0,25


Ordering data					
Nominal size	Pneumatic connection	Operating pressure	Display range	Part No.	Type
Display unit [bar]					
15	M5	0 ... 10 bar	0 ... 10	132340	MA-15-10-M5
27	M5	0 ... 10 bar	0 ... 10	526323	MA-27-10-M5
Display unit [MPa]					
27	M5	0 ... 1 MPa	0 ... 1	526324	MA-27-1,0-M5-MPA
40	G1/8	0 ... 1 MPa	0 ... 1	192732	MA-40-1-G1/8-MPA
		0 ... 1.6 MPa	0 ... 1.6	192733	MA-40-1,6-G1/8-MPA
	G1/4	0 ... 0.6 MPa	0 ... 0.6	184285	MA-40-0,6-G1/4-MPA
		0 ... 1 MPa	0 ... 1	184286	MA-40-1,0-G1/4-MPA
		0 ... 1.6 MPa	0 ... 1.6	184287	MA-40-1,6-G1/4-MPA
		0 ... 2.5 MPa	0 ... 2.5	184288	MA-40-2,5-G1/4-MPA
50	G1/4	0 ... 1 MPa	0 ... 1	192734	MA-50-1-G1/4-MPA
		0 ... 1.6 MPa	0 ... 1.6	192735	MA-50-1,6-G1/4-MPA
Display unit [psi]					
15	M5	0 ... 145 psi	0 ... 145	132341	MA-15-145-M5-PSI
27	M5	0 ... 160 psi	0 ... 160	527405	MA-27-160-M5-PSI

Precision pressure gauges MAP

FESTO

Technical data

Function



-  - Temperature range
-20 ... +60 °C



Technical data	
Nominal size	40
Pneumatic connection	R1/8
Operating medium	Inert gases Neutral liquids
Note on operating/pilot medium	No oxygen No acetylene
Design	Bourdon tube pressure gauge
Conforms to	EN 837-1
Type of mounting	Inline installation
Connection position	Centred, rear side
Ambient temperature [°C]	-20 ... +60
Temperature of medium [°C]	-20 ... +60 ¹⁾
Measurement accuracy class	1.6
Continuous load factor	0.75
Intermittent load factor	0.66
Protection class	IP43
Weight [g]	60

1) With a media temperature below 0 °C, the operating medium should be dry.

Materials	
Housing	Acrylic butadiene styrene (colour: black)
Inspection window	Polystyrene
Threaded plug/ materials in contact with the medium	Brass
Note on materials	RoHS-compliant

Dimensions	Download CAD data → www.festo.com

Ordering data					
Nominal size	Pneumatic connection	Operating pressure	Display range		Part No. Type
			[bar]	[psi]	
40	R1/8	0 ... 1 bar	0 ... 1	0 ... 15	161126 MAP-40-1-1/8-EN
		0 ... 4 bar	0 ... 4	0 ... 58	162842 MAP-40-4-1/8-EN
		0 ... 6 bar	0 ... 6	0 ... 87	161127 MAP-40-6-1/8-EN
		0 ... 16 bar	0 ... 16	0 ... 232	161128 MAP-40-16-1/8-EN

Pressure gauges MA-QS

Technical data

FESTO

Function




—  — Temperature range
–20 ... +60 °C



Technical data			
Nominal size	15		
Pneumatic connection	QS-4	QS-6	QS-8
Operating medium	Inert gases		
	Neutral liquids		
Note on operating/pilot medium	No oxygen		
	No acetylene		
Design	Bourdon tube pressure gauge without measuring mechanism		
Conforms to	EN 837-1		
Type of mounting	Inline installation		
Connection position	Centred, rear side		
Ambient temperature [°C]	–20 ... +60		
Temperature of medium [°C]	–20 ... +60		
Measurement accuracy class	5		
Continuous load factor	0.75		
Intermittent load factor	0.66		
Protection class	IP53		
Weight [g]	10		

Materials	
Housing	Steel (colour: black)
Inspection window	Polycarbonate
Threaded plug/ materials in contact with the medium	Brass
Note on materials	RoHS-compliant

Dimensions Download CAD data → www.festo.com



Dimensions and ordering data							
Nominal size	Pneumatic connection D	L	L1	L2	Operating pressure	Display range [bar]	Part No. Type
15	QS-4	36	23	15	0 ... 10 bar	0 ... 10	153383 MA-15-10-QS-4
	QS-6	38	25	17	0 ... 10 bar	0 ... 10	153384 MA-15-10-QS-6
	QS-8	34	21	18.5	0 ... 10 bar	0 ... 10	153385 MA-15-10-QS-8

Flanged pressure gauges FMA-EN

FESTO

Technical data

Function




 - Temperature range
 -20 ... +60 °C



Technical data			
Nominal size	40	50	63
Pneumatic connection	G $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{1}{4}$
Operating medium	Inert gases Neutral fluids		
Note on operating/pilot medium	No oxygen No acetylene		
Design	Bourdon tube pressure gauge		
Conforms to	EN 837-1		
Type of mounting	Front panel mounting		
Connection position	Centred, rear side		
Ambient temperature [°C]	-20 ... +60		
Temperature of medium [°C]	-20 ... +60 ¹⁾		
Measurement accuracy class	2.5		
Continuous load factor	0.75		
Intermittent load factor	0.66		
Protection class	IP43		
Weight [g]	80	100	120

1) With a media temperature below 0 °C, the operating medium should be dry.

Materials	
Housing	Acrylic butadiene styrene (colour: black)
Inspection window	Styrene acrylonitrile copolymer
Mounting ring	Steel
Threaded plug/ materials in contact with the medium	Brass
Note on materials	RoHS-compliant

Display range			
Nominal size	40	50	63
Pneumatic connection	G $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{1}{4}$
[bar]	[psi]		
0 ... 2.5	0 ... 36	—	■
0 ... 10	0 ... 145	■	■
0 ... 16	0 ... 232	■	■


Flanged pressure gauges FMA-EN

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



Type	B1	B2	D1 Ø	D2 Ø	L1	L2	L3
FMA-40	48	56	40	45	4.5	26.5	43
FMA-50	57	66	49.5	54	4.5	26.8	43.3
FMA-63	70	79	63	68	4.8	29.5	42.5

Ordering data


Nominal size	Pneumatic connection	Operating pressure	Display range		Part No.	Type
			[bar]	[psi]		
40	G1/4	0 ... 10 bar	0 ... 10	0 ... 145	159596	FMA-40-10-1/4-EN
		0 ... 16 bar	0 ... 16	0 ... 232	159597	FMA-40-16-1/4-EN
50	G1/4	0 ... 2.5 bar	0 ... 2.5	0 ... 36	159598	FMA-50-2,5-1/4-EN
		0 ... 10 bar	0 ... 10	0 ... 145	159599	FMA-50-10-1/4-EN
		0 ... 16 bar	0 ... 16	0 ... 232	159600	FMA-50-16-1/4-EN
63	G1/4	0 ... 2.5 bar	0 ... 2.5	0 ... 36	159601	FMA-63-2,5-1/4-EN
		0 ... 10 bar	0 ... 10	0 ... 145	159602	FMA-63-10-1/4-EN
		0 ... 16 bar	0 ... 16	0 ... 232	159603	FMA-63-16-1/4-EN

Flanged pressure gauges FMA

Technical data

FESTO

Function



— — Temperature range
–20 ... +60 °C




Technical data	
Nominal size	63
Pneumatic connection	G1/4
Operating medium	Gaseous media
	Fluid media
Note on operating/pilot medium	No oxygen
	No acetylene
Design	Capsule pressure gauge
Conforms to	EN 837-3
Type of mounting	Front panel mounting
Connection position	Centred, rear side
Ambient temperature [°C]	–20 ... +60
Temperature of medium [°C]	–20 ... +80
Measurement accuracy class	1.6
Continuous load factor	0.75
Intermittent load factor	0.9
Protection class	IP43
Weight [g]	120

Materials	
Housing	Steel
Inspection window	Polymethyl methacrylate
Mounting ring/screws	Steel
Threaded plug	Brass

Dimensions

Download CAD data → www.festo.com



Ordering data					
Nominal size	Pneumatic connection	Operating pressure	Display range		Part No. Type
			[bar]	[psi]	
63	G1/4	0 ... 0.25 bar	0 ... 0.25	0 ... 3.6	225783 FMA-63-0,25-C

Precision flanged pressure gauges FMAP

FESTO

Technical data

Function



— — Temperature range
–20 ... +60 °C



Technical data		
Nominal size	63	
Pneumatic connection	G1/4	
Operating medium	Inert gases	
	Neutral liquids	
Note on operating/pilot medium	No oxygen	
	No acetylene	
Design	Bourdon tube pressure gauge	
Conforms to	EN 837-1	
Type of mounting	Front panel mounting	
Connection position	Centred, rear side	
Ambient temperature [°C]	–20 ... +60	
Temperature of medium [°C]	–20 ... +60 ¹⁾	
Measurement accuracy class	1.0	
Continuous load factor	0.75	
Intermittent load factor	0.66	
Protection class	IP43	
Weight [g]	120	

1) With a media temperature below 0 °C, the operating medium should be dry.

Materials	
Housing	Acrylic butadiene styrene (colour: black)
Inspection window	Styrene acrylonitrile copolymer
Mounting ring	Steel
Threaded plug/ materials in contact with the medium	Brass
Note on materials	RoHS-compliant

Dimensions	Download CAD data → www.festo.com

Precision flanged pressure gauges FMAP

FESTO

Technical data

Ordering data					
Nominal size	Pneumatic connection	Operating pressure	Display range		Part No. Type
			[bar]	[psi]	
63	G $\frac{1}{4}$	0 ... 1 bar	0 ... 1	0 ... 15	161129 FMAP-63-1-$\frac{1}{4}$-EN
		0 ... 4 bar	0 ... 4	0 ... 58	162843 FMAP-63-4-$\frac{1}{4}$-EN
		0 ... 6 bar	0 ... 6	0 ... 87	161130 FMAP-63-6-$\frac{1}{4}$-EN
		0 ... 16 bar	0 ... 16	0 ... 232	161131 FMAP-63-16-$\frac{1}{4}$-EN

Pressure gauges PAGN

Technical data

FESTO

Function



— — Temperature range
–20 ... +60 °C



Technical data		
Nominal size	26	40
Pneumatic connection	For QSP10	For QSP10
Operating medium	Inert gases	
	Neutral liquids	
Note on operating/pilot medium	No oxygen	
	No acetylene	
Design	Bourdon tube pressure gauge	
Conforms to	EN 837-1	
Type of mounting	Inline installation	
Connection position	Centred, rear side	
Ambient temperature [°C]	–20 ... +60	
Temperature of medium [°C]	–20 ... +60 ¹⁾	
Measurement accuracy class	4.0	2.5
Continuous load factor	0.75	
Intermittent load factor	0.66	
Protection class	IP43	
	NEMA 4	
Weight [g]	15	50

1) With a media temperature below 0 °C, the operating medium should be dry.

Materials		
Housing	Polyamide (colour: black)	Acrylic butadiene styrene (colour: black)
Inspection window	Polystyrene	
Threaded plug/ materials in contact with the medium	Brass	
Note on materials	RoHS-compliant	

Dimensions		Download CAD data → www.festo.com
PAGN-26	PAGN-40	
1 Sealing ring		

Pressure gauges PAGN

FESTO

Technical data

Ordering data						
Nominal size	Pneumatic connection	Operating pressure	Display range		Part No.	Type
			Outer scale	Inner scale		
Outer scale in bar, inner scale in psi						
26	For QSP10	0 ... 10 bar	0 ... 10 bar	0 ... 145 psi	543488	PAGN-26-10-P10
		0 ... 16 bar	0 ... 16 bar	0 ... 232 psi	543487	PAGN-26-16-P10
40	For QSP10	0 ... 10 bar	0 ... 10 bar	0 ... 145 psi	548009	PAGN-40-10-P10
		0 ... 16 bar	0 ... 16 bar	0 ... 232 psi	548010	PAGN-40-16-P10
Outer scale in psi, inner scale in bar						
26	For QSP10	0 ... 145 psi	0 ... 145 psi	0 ... 10 bar	563732	PAGN-26-145P-P10
		0 ... 232 psi	0 ... 232 psi	0 ... 16 bar	563731	PAGN-26-232P-P10
40	For QSP10	0 ... 145 psi	0 ... 145 psi	0 ... 10 bar	563734	PAGN-40-145P-P10
		0 ... 232 psi	0 ... 232 psi	0 ... 16 bar	563733	PAGN-40-232P-P10
Outer scale in MPa						
26	For QSP10	0 ... 1 MPa	0 ... 1 MPa	–	563736	PAGN-26-1M-P10
		0 ... 1.6 MPa	0 ... 1.6 MPa	–	563735	PAGN-26-1.6M-P10
40	For QSP10	0 ... 1 MPa	0 ... 1 MPa	–	563738	PAGN-40-1M-P10
		0 ... 1.6 MPa	0 ... 1.6 MPa	–	563737	PAGN-40-1.6M-P10