

On-off/soft-start valves MS-EM/EE/DL/DE/SV, MS series





FESTO



On-off/soft-start valves MS-EM/EE/DL/DE/SV, MS series

Product range overview – MS series service units

FESTO

Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]						Grade of filtration [μm]			
				0.05	0.05	0.1	0.3	0.1	0.5	0.01	1	5	40
Code		AG...		D2	D4	D5	D6	D7	D8	A	B	C	E
Service units													
MSB-FRC		4	G $\frac{1}{8}$, G $\frac{1}{4}$	G $\frac{1}{8}$, G $\frac{1}{4}$, G $\frac{3}{8}$	–	–	–	■	■	–	–	–	■
		6	G $\frac{1}{4}$, G $\frac{3}{8}$, G $\frac{1}{2}$	G $\frac{1}{4}$, G $\frac{3}{8}$, G $\frac{1}{2}$, G $\frac{3}{4}$	–	–	–	■	■	–	–	–	■
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–
Service unit combinations (further variants can be ordered using the configurator → Internet: msb4, msb6 or msb9)													
MSB		4	G $\frac{1}{4}$	G $\frac{1}{8}$, G $\frac{1}{4}$, G $\frac{3}{8}$	–	–	–	■	■	–	–	–	■
		6	G $\frac{1}{2}$	G $\frac{1}{4}$, G $\frac{3}{8}$, G $\frac{1}{2}$, G $\frac{3}{4}$	–	–	–	■	■	–	–	–	■
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–
Individual devices													
Filter regulators		4	G $\frac{1}{8}$, G $\frac{1}{4}$	G $\frac{1}{8}$, G $\frac{1}{4}$, G $\frac{3}{8}$	–	–	■	■	■	–	–	–	■
MS-LFR		6	G $\frac{1}{4}$, G $\frac{3}{8}$, G $\frac{1}{2}$	G $\frac{1}{4}$, G $\frac{3}{8}$, G $\frac{1}{2}$, G $\frac{3}{4}$	–	–	■	■	■	■	–	–	■
		9	G $\frac{3}{4}$, G1	G $\frac{1}{2}$, G $\frac{3}{4}$, G1, G $\frac{1}{4}$, G $\frac{1}{2}$	–	–	■	■	■	■	–	–	■
		12	–	G1, G $\frac{1}{4}$, G $\frac{1}{2}$, G2	–	–	–	■	■	■	–	–	■
Filters		4	G $\frac{1}{8}$, G $\frac{1}{4}$	G $\frac{1}{8}$, G $\frac{1}{4}$, G $\frac{3}{8}$	–	–	–	–	–	–	–	–	■
MS-LF		6	G $\frac{1}{4}$, G $\frac{3}{8}$, G $\frac{1}{2}$	G $\frac{1}{4}$, G $\frac{3}{8}$, G $\frac{1}{2}$, G $\frac{3}{4}$	–	–	–	–	–	–	–	–	■
		9	G $\frac{3}{4}$, G1	G $\frac{1}{2}$, G $\frac{3}{4}$, G1, G $\frac{1}{4}$, G $\frac{1}{2}$	–	–	–	–	–	–	–	–	■
		12	–	G1, G $\frac{1}{4}$, G $\frac{1}{2}$, G2	–	–	–	–	–	–	–	–	■
Fine and micro filters		4	G $\frac{1}{8}$, G $\frac{1}{4}$	G $\frac{1}{8}$, G $\frac{1}{4}$, G $\frac{3}{8}$	–	–	–	–	–	■	■	–	–
MS-LFM		6	G $\frac{1}{4}$, G $\frac{3}{8}$, G $\frac{1}{2}$	G $\frac{1}{4}$, G $\frac{3}{8}$, G $\frac{1}{2}$, G $\frac{3}{4}$	–	–	–	–	–	■	■	–	–
		9	G $\frac{3}{4}$, G1	G $\frac{1}{2}$, G $\frac{3}{4}$, G1, G $\frac{1}{4}$, G $\frac{1}{2}$	–	–	–	–	–	■	■	–	–
		12	–	G1, G $\frac{1}{4}$, G $\frac{1}{2}$, G2	–	–	–	–	–	■	■	–	–
Activated carbon filters		4	G $\frac{1}{8}$, G $\frac{1}{4}$	G $\frac{1}{8}$, G $\frac{1}{4}$, G $\frac{3}{8}$	–	–	–	–	–	–	–	–	–
MS-LFX		6	G $\frac{1}{4}$, G $\frac{3}{8}$, G $\frac{1}{2}$	G $\frac{1}{4}$, G $\frac{3}{8}$, G $\frac{1}{2}$, G $\frac{3}{4}$	–	–	–	–	–	–	–	–	–
		9	G $\frac{3}{4}$, G1	G $\frac{1}{2}$, G $\frac{3}{4}$, G1, G $\frac{1}{4}$, G $\frac{1}{2}$	–	–	–	–	–	–	–	–	–
		12	–	G1, G $\frac{1}{4}$, G $\frac{1}{2}$, G2	–	–	–	–	–	–	–	–	–
Water separators		4	–	–	–	–	–	–	–	–	–	–	–
MS-LWS		6	G $\frac{1}{4}$, G $\frac{3}{8}$, G $\frac{1}{2}$	G $\frac{1}{4}$, G $\frac{3}{8}$, G $\frac{1}{2}$, G $\frac{3}{4}$	–	–	–	–	–	–	–	–	–
		9	G $\frac{3}{4}$, G1	G $\frac{1}{2}$, G $\frac{3}{4}$, G1, G $\frac{1}{4}$, G $\frac{1}{2}$	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–

On-off/soft-start valves MS-EM/EE/DL/DE/SV, MS series

FESTO

Product range overview – MS series service units

Type	Size	Bowl guard		Condensate drains				Pressure indicator				Security		Options		➔ Page/ Internet		
		Plastic bowl with plastic bowl guard	Metal bowl	Manual rotary	Semi-automatic	Fully automatic	External, fully automatic, electrical	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G $\frac{1}{8}$	Adapter plate for EN pressure gauge G $\frac{1}{4}$	Pressure sensor	Rotary knob with detent, lockable via accessories	Rotary knob with integrated lock	Silencer	Flow direction from right to left		
Code		R	U	M	H	V	E...	VS	AG	A8	A4	AD...	AS	E11	S	Z		
Service units																		
MSB-FRC	4	■	–	■	–	■	–	–	■	–	–	–	■	–	–	■	msb4	
	6	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	msb6	
	9	–															–	
	12	–															–	
Service unit combinations																		
MSB	4	■	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	msb4
	6	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	msb6	
	9	–															–	
	12	–															–	
Individual devices																		
Filter regulators MS-LFR	4	■	■	■	■	■	■	–	■	■	■	■	■	■	■	–	■	ms4-lfr
	6	■	■	■	■	■	■	■	■	■	■	■	■	■	■	–	■	ms6-lfr
	9	–	■	■	■	■	■	■	■	■	■	–	■	■	■	–	■	ms9-lfr
	12	–	■	■	■	–	■	■	■	■	■	–	■	■	■	–	■	ms12-lfr
Filters MS-LF	4	■	■	■	■	■	■	■	–	–	–	–	–	–	–	–	■	ms4-lf
	6	■	■	■	■	■	■	■	■	■	–	–	–	–	–	–	■	ms6-lf
	9	–	■	■	■	■	■	■	■	■	–	–	–	–	–	–	■	ms9-lf
	12	–	■	■	■	–	■	■	■	–	–	–	–	–	–	–	■	ms12-lf
Fine and micro filters MS-LFM	4	■	■	■	■	■	■	■	–	–	–	–	–	–	–	–	■	ms4-lfm
	6	■	■	■	■	■	■	■	■	–	–	–	–	–	–	–	■	ms6-lfm
	9	–	■	■	■	■	■	■	■	–	–	–	–	–	–	–	■	ms9-lfm
	12	–	■	■	■	–	■	■	■	–	–	–	–	–	–	–	■	ms12-lfm
Activated carbon filters MS-LFX	4	■	■	■	–	–	–	–	–	–	–	–	–	–	–	–	■	ms4-lfx
	6	■	■	■	–	–	–	–	–	–	–	–	–	–	–	–	■	ms6-lfx
	9	–	■	–	–	–	–	–	–	–	–	–	–	–	–	–	■	ms9-lfx
	12	–	■	–	–	–	–	–	–	–	–	–	–	–	–	–	■	ms12-lfx
Water separators MS-LWS	4	–															–	
	6	–	■	–	–	–	■	■	–	–	–	–	–	–	–	–	■	ms6-lws
	9	–	■	–	–	–	■	■	–	–	–	–	–	–	–	–	■	ms9-lws
	12	–															–	

On-off/soft-start valves MS-EM/EE/DL/DE/SV, MS series

Product range overview – MS series service units

FESTO

Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]						Supply voltage			
				0.05	0.05	0.1	0.3	0.1	0.5	24 VDC, connection pattern to EN 175301	24 VDC, connection pattern M12 to DE5MA	110 VAC, connection pattern to EN 175301	V24
Code		AG...		D2	D4	D5	D6	D7	D8	V24	V24P	V110	V230
Individual devices													
Pressure regulators MS-LR		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	■	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	■	■	■	■	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	■	■	■	–	–	–
Pressure regulators MS-LRB		4	G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	–
		6	G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	■	–	–	–
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–
Precision pressure regulators MS-LRP		4	–	–	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	■	–	■	–	–	–
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–
Precision pressure regulators MS-LRPB		4	–	–	–	–	–	–	–	–	–	–	–
		6	G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	■	–	■	–	–	–
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–
Electrical pressure regulators MS-LRE		4	–	–	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	■	–	–	–
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–
Lubricators MS-LOE		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	–	–	–
Electrical on-off valves MS-EM(1)		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	–	–	–
Electrical on-off valves MS-EE		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	■	–	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	■	–	■
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	■	–	■
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	■	–	■
Electrical soft-start valves MS-DL		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	–	–	–
Electrical soft-start valves MS-DE		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	■	–	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	■	–	■
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	■	–	■
Soft start and exhaust valves MS-SV		4	–	–	–	–	–	–	–	–	–	–	–
		6	G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	■	–	–
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–

On-off/soft-start valves MS-EM/EE/DL/DE/SV, MS series

FESTO


Product range overview – MS series service units

Type	Size	Bowl guard		Pressure indicator					Security		Options		➔ Page/ Internet
		Plastic bowl with plastic bowl guard	Metal bowl	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G _{1/8}	Adapter plate for EN pressure gauge G _{1/4}	Pressure sensor	Rotary knob with detent, lockable via accessories	Rotary knob with integrated lock	Silencer	Flow direction from right to left	
		Code	R	U	VS	AG	A8	A4	AD...	AS	E11	S	Z
Individual devices													
Pressure regulators	4	–	–	■	■	■	■	■	■	■	–	■	ms4-lr
	6	–	–	■	■	–	■	■	■	■	–	■	ms6-lr
	9	–	–	■	■	–	■	■	■	■	–	■	ms9-lr
	12	–	–	■	■	–	■	–	■	■	–	■	ms12-lr
Pressure regulators	4	–	–	■	■	■	■	■	■	■	–	■	ms4-lrb
	6	–	–	■	■	–	■	■	■	■	–	■	ms6-lrb
	9	–									–		
	12	–									–		
Precision pressure regulators	4	–											
	6	–	–	■	–	■	■	■	■	■	–	■	ms6-lrp
	9	–											
	12	–											
Precision pressure regulators	4	–											
	6	–	–	■	–	■	■	■	■	■	–	■	ms6-lrbp
	9	–											
	12	–											
Electrical pressure regulators	4	–											
	6	–	–	■	■	–	■	–	–	–	–	■	ms6-lre
	9	–											
	12	–											
Lubricators	4	■	■	–	–	–	–	–	–	–	–	■	ms4-loe
	6	■	■	–	–	–	–	–	–	–	–	■	ms6-loe
	9	–	■	–	–	–	–	–	–	–	–	■	ms9-loe
	12	–	■	–	–	–	–	–	–	–	–	■	ms12-loe
Electrical on-off valves	4	–	–	■	■	■	■	■	■	–	■	■	8
	6	–	–	■	■	–	■	■	–	–	■	■	8
	9	–	–	■	■	–	■	–	–	–	■	■	64
	12	–	–	■	■	–	■	–	–	–	■	■	82
Electrical on-off valves	4	–	–	■	■	■	■	■	–	–	■	■	18
	6	–	–	■	■	–	■	■	–	–	■	■	18
	9	–	–	■	■	–	■	–	–	–	■	■	72
	12	–	–	■	■	–	■	–	–	–	■	■	88
Electrical soft-start valves	4	–	–	■	■	■	■	■	–	–	–	–	30
	6	–	–	■	■	–	■	■	–	–	–	–	30
	9	–											
	12	–	–	■	■	–	■	–	–	–	–	■	94
Electrical soft-start valves	4	–	–	■	■	■	■	■	–	–	–	–	38
	6	–	–	■	■	–	■	■	–	–	–	–	38
	9	–											
	12	–	–	■	■	–	■	–	–	–	–	■	100
Soft start and exhaust valves	4	–											
	6	–	–	■	■	–	■	■	–	–	■	■	50
	9	–											
	12	–											

On-off/soft-start valves MS-EM/EE/DL/DE/SV, MS series

Product range overview – MS series service units

FESTO

Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]				Supply voltage			
				0.1	0.3	0.1	0.5	24 V DC, connection pattern to EN 175301	24 V DC, connection pattern M12 to DE5INA	110 V AC, connection pattern to EN 175301	230 V AC, connection pattern to EN 175301
Code	AG...	D5	D6	D7	D8	V24	V24P	V110	V230		
Individual devices											
Membrane air dryers MS-LDM1		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–
		9	–								
		12	–								
Branching modules MS-FRM		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	–
Distributor blocks MS-FRM-FRZ		4	G1/4	–	–	–	–	–	–	–	–
		6	G1/2	–	–	–	–	–	–	–	–
		9	–								
		12	–								
Flow sensors SFAM		4	–								
		6	G1/2	G1/2	–	–	–	–	–	–	–
		9	–	G1, G11/2	–	–	–	–	–	–	–
		12	–								

On-off/soft-start valves MS-EM/EE/DL/DE/SV, MS series

FESTO

Product range overview – MS series service units


Type	Size	Bowl guard		Pressure indicator				Switch output		Options		➔ Page/ Internet
		Plastic bowl with plastic bowl guard	Metal bowl	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G1/8	Adapter plate for EN pressure gauge G1/4	Pressure sensor	2x PNP or NPN, 1 analogue output 4 ... 20 mA	2x PNP or NPN, 1 analogue output 0 ... 10 V	Silencer	Flow direction from right to left
Code		R	U	VS	AG	A8	A4	AD...	2SA	2SV	S	Z/R
Individual devices												
Membrane air dryers	4	–	■	–	–	–	–	–	–	–	–	■ ms4-ldm1
	6	–	■	–	–	–	–	–	–	–	–	■ ms6-ldm1
	9	–										–
	12	–										–
MS-LDM1	4	–	–	■	■	■	■	■	–	–	–	■ ms4-ldm1
	6	–	–	■	■	–	■	■	–	–	–	■ ms6-ldm1
	9	–										–
	12	–										–
Branching modules	4	–	–	■	■	■	■	■	–	–	–	■ ms4-frm
	6	–	–	■	■	–	■	■	–	–	–	■ ms6-frm
	9	–	–	■	■	–	■	■	–	–	–	■ ms9-frm
	12	–	–	■	–	–	–	–	–	–	–	■ ms12-frm
MS-FRM	4	–	–	–	–	–	–	–	–	–	–	■ ms4-frm
	6	–	–	–	–	–	–	–	–	–	–	■ ms6-frm
	9	–										–
	12	–										–
Distributor blocks	4	–	–	–	–	–	–	–	–	–	–	■ ms4-frm
	6	–	–	–	–	–	–	–	–	–	–	■ ms6-frm
	9	–										–
	12	–										–
MS-FRM-FRZ	4	–	–	–	–	–	–	–	–	–	–	–
	6	–	–	–	–	–	–	–	–	–	–	–
	9	–										–
	12	–										–
Flow sensors SFAM	4	–										–
	6	–	–	–	–	–	–	–	■	■	–	■ sfam-62
	9	–	–	–	–	–	–	–	■	■	–	■ sfam-90
	12	–										–

On-off valves MS4/MS6-EM1, MS series

Peripherals overview

FESTO

On-off valve MS4/MS6-EM1



- - Note

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter plate for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80

Mounting attachments and accessories

	Individual device		Combination		→ Page/Internet
	Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1] Cover cap MS4-6-END	■	-	■	-	ms4-end, ms6-end
[2] Connecting plate MS4/6-AG...	-	■	-	■	ms4-ag, ms6-ag
[3] Module connector MS4/6-MV	-	■	■	■	ms4-mv, ms6-mv
[4] Mounting bracket MS4/6-WB	■	■	-	-	ms4-wb, ms6-wb
[5] Mounting bracket MS4-WBM	■	■	-	-	ms4-wbm
[6] Silencer U	■	■	■	■	107
[7] MS pressure gauge AG/RG	■	■	■	■	16
[8] Adapter plate for EN pressure gauge 1/8/1/4 A8/A4	■	■	■	■	16
[9] Pressure gauge MA	■	■	■	■	107
[10] Pressure sensor without display AD1 ... AD10	■	■	■	■	16
[11] Connecting cable NEBU-M8...-LE3	■	■	■	■	107
[12] Pressure sensor with display AD1 ... AD4	■	■	■	■	16
[13] Connecting cable NEBU-M8...-LE3/NEBU-M12...-LE4	■	■	■	■	107
[14] Padlock LRVS-D	■	■	■	■	107
- Mounting bracket MS4/6-WP/WPB/WPE/WPM	-	■	■	■	ms4-wp, ms6-wp

On-off valves MS4/MS6-EM1, MS series

FESTO

Type codes

MS	6	-	EM1	-	1/2	-	S
Series							
MS	Standard service unit						
Size							
4	Grid dimension 40 mm						
6	Grid dimension 62 mm						
Service function							
EM1	Manually operated on-off valve						
Pneumatic connection							
MS4							
1/8	Female thread G1/8						
1/4	Female thread G1/4						
MS6							
1/4	Female thread G1/4						
3/8	Female thread G3/8						
1/2	Female thread G1/2						
Silencer							
	Without silencer						
S	Silencer						

Additional variants can be ordered using the modular system ➔ 16


- Connecting plates
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Type of mounting
- Flow direction

On-off valves MS4/MS6-EM1, MS series

Technical data

FESTO

Function



- - Flow rate
1,200 ... 8,700 l/min
- - Temperature range
-10 ... +60 °C
- - Operating pressure
0 ... 18 bar



- Manually operated on-off valve for pressurising and venting pneumatic installations
- The valve is activated by turning the rotary knob
- At connection 3 there is the facility to attach a silencer and/or to duct the exhaust air
- When the valve is closed, the rotary knob can be secured with a padlock
- Optional pressure gauge
- Optional pressure sensor

General technical data					
Size	MS4		MS6		
Pneumatic connection 1, 2	G1/8	G1/4	G1/4	G3/8	G1/2
Pneumatic connection 3	G1/4		G1/2		
Design	Rotary slide valve				
Type of mounting	Via accessories In-line installation				
Assembly position	Any				
Pressure indicator	Via pressure sensor for displaying output pressure via LCD display and electrical output Via pressure sensor for displaying output pressure via operational status indicator and electrical output Via pressure gauge for displaying output pressure Via pressure gauge with red/green scale for displaying output pressure G1/4 prepared G1/8 prepared				
Valve function	3/2-way valve, double solenoid				
Exhaust function	No flow control				
Switching position display	Knob actuator direction = flow direction				
Pilot control mode	Direct				
Direction of flow	Non-reversible				
C value [l/(s*bar)]	4.6	9.0	10.7	21.2	30.8
b value	0.51	0.39	0.56	0.49	0.57

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Standard nominal flow rate qnN ¹⁾ [l/min]					
Size	MS4		MS6		
Pneumatic connection	G1/8	G1/4	G1/4	G3/8	G1/2
In main flow direction 1 → 2	1,200	2,200	3,000	5,500	8,700
In relief direction 2 → 3	1,900	1,700	6,800	6,600	6,200

1) Measured at p1 = 6 bar and p2 = 5 bar, Δp = 1 bar

On-off valves MS4/MS6-EM1, MS series

FESTO

Technical data

Operating and environmental conditions

Variant	Standard		Pressure sensor AD...	
Size	MS4	MS6	MS4	MS6
Operating pressure [bar]	0 ... 14	0 ... 18	0 ... 10	0 ... 10
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]			
Note on operating/pilot medium	Inert gases			
Ambient temperature [°C]	-10 ... +60	-10 ... +60	0 ... +50	0 ... +50
Temperature of medium [°C]	-10 ... +60	-10 ... +60	0 ... +50	0 ... +50
Corrosion resistance	CRC ¹⁾	2		

1) Corrosion resistance class 2 according to Festo standard 940 070


Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [g]

Size	MS4	MS6
On-off valve	190	580
On-off valve with silencer S	210	655

Materials

Sectional view



On-off valve

[1] Body	Die-cast aluminium
[2] Rotary valve	PA reinforced
[3] Lock slide	PA reinforced
- Seals	NBR, TPE-U(PU)
Note on materials	RoHS-compliant Free of copper and PTFE (not with variants AG or AD...)

On-off valves MS4/MS6-EM1, MS series


Technical data

FESTO

Dimensions – Basic version

With female thread, with cover plate

Download CAD data ➔ www.festo.com



Type	B1	B2	B3	B4	B5	B6	D1	D5	L1	L2	L3	L7
MS4-EM1-1/8	40	21	54	30	9	20	G1/8	G1/4	104	31.5	59	20.6
MS4-EM1-1/4							G1/4					
MS6-EM1-1/4	62	31	76	45	10	24	G3/8	G1/2	150.9	45.5	84.5	28.2
MS6-EM1-3/8							G1/2					
MS6-EM1-1/2												

Note: This product conforms to ISO 1179-1 and to ISO 228-1

On-off valves MS4/MS6-EM1, MS series

FESTO


Technical data

Dimensions – Pressure gauge/pressure gauge alternatives

Integrated MS pressure gauge with standard scale AG or red-green scale RG, display unit [bar]

Download CAD data → www.festo.com

Adapter plate A8/A4 for EN pressure gauge 1/8/1/4, without pressure gauge



Type	B2	B3	D1	D4
MS4-EM1-1/8...-AG	21	65	G1/8	-
MS4-EM1-1/4...-AG			G1/4	
MS4-EM1-1/8...-RG	21	66.5	G1/8	-
MS4-EM1-1/4...-RG			G1/4	
MS4-EM1-1/8...-A8	21	58.5	G1/8	G1/8
MS4-EM1-1/4...-A8			G1/4	
MS4-EM1-1/8...-A4	21	58.5	G1/8	G1/4
MS4-EM1-1/4...-A4			G1/4	
MS6-EM1-1/4...-AG	31	85	G1/4	-
MS6-EM1-3/8...-AG			G3/8	
MS6-EM1-1/2...-AG			G1/2	
MS6-EM1-1/4...-RG	31	86.5	G1/4	-
MS6-EM1-3/8...-RG			G3/8	
MS6-EM1-1/2...-RG			G1/2	
MS6-EM1-1/4...-A4	31	78.5	G1/4	G1/4
MS6-EM1-3/8...-A4			G3/8	
MS6-EM1-1/2...-A4			G1/2	

Note: This product conforms to ISO 1179-1 and to ISO 228-1


On-off valves MS4/MS6-EM1, MS series

Technical data

FESTO

Dimensions – Pressure gauge/pressure gauge alternatives

Pressure sensor with LCD display AD1 ... AD4



Variant AD1:
SDE1-D10-G2-MS-L-P1-M8 with
3-pin plug M8x1, 1 switching output PNP

Variant AD2:
SDE1-D10-G2-MS-L-N1-M8 with
3-pin plug M8x1, 1 switching output NPN


Download CAD data → www.festo.com
Technical data → Internet: sde1

Variant AD3:
SDE1-D10-G2-MS-L-PI-M12 with
4-pin plug M12x1, 1 switching output PNP and 4 ... 20 mA analogue

Variant AD4:
SDE1-D10-G2-MS-L-NI-M12 with
4-pin plug M12x1, 1 switching output NPN and 4 ... 20 mA analogue

Pressure sensor with operational status indicator AD7 ... AD10

Technical data → Internet: sde5



Variant AD7:
SDE5-D10-O-...-P-M8 with 3-pin
plug M8x1, threshold value
comparator, 1 switching output PNP,
N/O contact

Variant AD8:
SDE5-D10-C-...-P-M8 with 3-pin
plug M8x1, threshold value
comparator, 1 switching output PNP,
N/C contact

Variant AD9:
SDE5-D10-O3-...-P-M8 with 3-pin
plug M8x1, window comparator,
1 switching output PNP, N/O contact

Variant AD10:
SDE5-D10-C3-...-P-M8 with 3-pin
plug M8x1, window comparator,
1 switching output PNP, N/C contact

Type	B2	B3	D1	D6	L5	L6
MS4-EM1-1/8-...-AD1/AD2	21	82.6	G1/8	M8x1	35.1	46.7
MS4-EM1-1/4-...-AD1/AD2			G1/4			
MS4-EM1-1/8-...-AD3/AD4	21	82.6	G1/8	M12x1	35.1	55.8
MS4-EM1-1/4-...-AD3/AD4			G1/4			
MS4-EM1-1/8-...-AD7/AD8/AD9/AD10	21	59.1	G1/8	M8x1	–	–
MS4-EM1-1/4-...-AD7/AD8/AD9/AD10			G1/4			
MS6-EM1-1/4-...-AD1/AD2	31	103	G1/4	M8x1	35.1	46.7
MS6-EM1-3/8-...-AD1/AD2			G3/8			
MS6-EM1-1/2-...-AD1/AD2			G1/2			
MS6-EM1-1/4-...-AD3/AD4	31	103	G1/4	M12x1	35.1	55.8
MS6-EM1-3/8-...-AD3/AD4			G3/8			
MS6-EM1-1/2-...-AD3/AD4			G1/2			
MS6-EM1-1/4-...-AD7/AD8/AD9/AD10	31	79	G1/4	M8x1	–	–
MS6-EM1-3/8-...-AD7/AD8/AD9/AD10			G3/8			
MS6-EM1-1/2-...-AD7/AD8/AD9/AD10			G1/2			

Note: This product conforms to ISO 1179-1 and to ISO 228-1


On-off valves MS4/MS6-EM1, MS series

FESTO

Technical data

Dimensions – Silencer

Download CAD data ➔ www.festo.com



Type	D2	L4
MS4-EM1-...-S	19.5	47
MS6-EM1-...-S	28	106

Ordering data

Size	Connection	Standard		With silencer	
		Part No.	Type	Part No.	Type
MS4	G ¹ / ₈	541262	MS4-EM1-1/8 ¹⁾	541263	MS4-EM1-1/8-S ¹⁾
	G ¹ / ₄	541258	MS4-EM1-1/4 ¹⁾	541259	MS4-EM1-1/4-S ¹⁾
MS6	G ¹ / ₄	541271	MS6-EM1-1/4 ¹⁾	541272	MS6-EM1-1/4-S ¹⁾
	G ³ / ₈	541275	MS6-EM1-3/8 ¹⁾	541276	MS6-EM1-3/8-S ¹⁾
	G ¹ / ₂	541267	MS6-EM1-1/2 ¹⁾	541268	MS6-EM1-1/2-S ¹⁾

1) Free of copper and PTFE

On-off valves MS4/MS6-EM1, MS series

Ordering data – Modular products

FESTO

M Mandatory data →				
Module No.	Series	Size	Function	Pneumatic connection
541266	MS	4	EM1	1/8, 1/4, 3/8, 1/2, AGA, AGB, AGC, AGD, AGE
541279		6		
Order example				
541266	MS	4	- EM1	- 1/4

Ordering table						
Grid dimension [mm]	40	62	Condi-	Code	Enter	code
M Module No.	541266	541279				
Series	Standard			MS		MS
Size	4	6		...		
Function	On-off valve, manual			-EM1		-EM1
Pneumatic connection	Female thread G1/8	-		-1/8		
	Female thread G1/4	Female thread G1/4		-1/4		
	-	Female thread G3/8		-3/8		
	-	Female thread G1/2		-1/2		
	Connecting plate G1/8	-		-AGA		
	Connecting plate G1/4	Connecting plate G1/4		-AGB		
	Connecting plate G3/8	Connecting plate G3/8		-AGC		
	-	Connecting plate G1/2		-AGD		
	-	Connecting plate G3/4		-AGE		

Transfer order code		MS		- EM1	-	
---------------------	--	----	--	-------	---	--

On-off valves MS4/MS6-EM1, MS series

FESTO

Ordering data – Modular products

→ [0] Options				
Silencer	Pressure gauge/pressure gauge alternatives	Alternative pressure gauge scale	Type of mounting	Flow direction
S	AG, A8, A4, RG, AD1 ... AD4, AD7 ... AD10	PSI, MPA	WP, WPM, WB, WBM	Z
- S	- AG	- PSI	- WB	- Z

Ordering table		Grid dimension [mm]	40	62	Condi-tions	Code	Enter code
[0]	Silencer	Silencer				-S	
	Pressure gauge/pressure gauge alternatives	MS pressure gauge, bar (with adapter plate)	MS pressure gauge, bar			-AG	
		Adapter plate for EN pressure gauge 1/8, without pressure gauge	–			-A8	
		Adapter plate for EN pressure gauge 1/4, without pressure gauge				-A4	
		Integrated pressure gauge, red-green scale				-RG	
		Pressure sensor with LCD display, plug M8, 1 switching output PNP, 3-pin	[1]			-AD1	
		Pressure sensor with LCD display, plug M8, 1 switching output NPN, 3-pin	[1]			-AD2	
		Pressure sensor with LCD display, plug M12, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA	[1]			-AD3	
		Pressure sensor with LCD display, plug M12, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA	[1]			-AD4	
		Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/O contact	[1]			-AD7	
		Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/C contact	[1]			-AD8	
		Pressure sensor with operational status indicator, plug M8, window comparator, PNP, N/O contact	[1]			-AD9	
		Pressure sensor with operational status indicator, plug M8, window comparator, PNP, N/C contact	[1]			-AD10	
	Alternative pressure gauge scale	psi	[2]			-PSI	
		MPa	[2]			-MPA	
	Type of mounting	Mounting bracket	[3]			-WP	
		Mounting bracket	[3]			-WPM	
		Mounting bracket				-WB	
		Mounting bracket	–			-WBM	
	Flow direction	Flow direction from right to left				-Z	

[1] AD1 ... AD4, AD7 ... AD10

Measuring range max. 10 bar

[2] PSI, MPa Only with pressure gauge AG or RG

[3] WP, WPM Only with connecting plate AGA, AGB, AGC, AGD or AGE

Transfer order code

- [] - [] - [] - [] - []


 New
Variant 10V24P

On-off valves MS4/MS6-EE, MS series

Peripherals overview

FESTO

On-off valve MS4/MS6-EE




 Note

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter plate for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80

Supply voltage
V24/10V24/V110/V230

Supply voltage
10V24P



On-off valves MS4/MS6-EE, MS series

Peripherals overview

Mounting attachments and accessories	Individual device		Combination		➔ Page/Internet
	Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1] Cover cap MS4/6-END	■	-	■	-	ms4-end, ms6-end
[2] Mounting plate MS4/6-AEND	■ ¹⁾	-	■ ¹⁾	-	ms4-aend, ms6-aend
[3] Connecting plate MS4/6-AG...	-	■ ¹⁾	-	■ ¹⁾	ms4-ag, ms6-ag
[4] Mounting bracket MS4/6-WB	■	■	-	-	ms4-wb, ms6-wb
[5] Mounting bracket MS4-WBM	■	■	-	-	ms4-wbm
[6] Module connector MS4/6-MV	-	■	■	■	ms4-mv, ms6-mv
[7] Mounting bracket MS4/6-WP	■	■	■	■	ms4-wp, ms6-wp
Mounting bracket (not illustrated) MS4/6-WPB/WPE/WPM	■	■	■	■	ms4-wp, ms6-wp
[8] Silencer U	■	■	■	■	107
[9] MS pressure gauge AG/RG	■	■	■	■	28
[10] Adapter plate for EN pressure gauge 1/8/1/4 A8/A4	■	■	■	■	28
[11] Pressure gauge MA	■	■	■	■	107
[12] Pressure sensor without display AD7 ... AD10	■	■	■	■	28
[13] Connecting cable NEBU-M8...-LE3	■	■	■	■	107
[14] Pressure sensor with display AD1 ... AD4	■	■	■	■	28
[15] Connecting cable NEBU-M8...-LE3/NEBU-M12...-LE4	■	■	■	■	107
[16] Illuminating seal MEB-LD	■	■	■	■	106
[17] Plug socket with cable KMEB	■	■	■	■	106
[18] Plug socket MSSD-EB	■	■	■	■	106
[19] Locking clip CPV18-HV	■	■	■	■	106
[20] Connecting cable NEBU-M12G5	■	■	■	■	107
[21] Connecting cable NEBU-M12W5	■	■	■	■	107

1) Module connector MS4/6-MV [6] or mounting bracket MS4/6-WP/WPB/WPE/WPM [7] is required for mounting.

On-off valves MS4/MS6-EE, MS series

Type codes

MS	6	-	EE	-	½	-	V110	-										
Series																		
MS	Standard service unit																	
Size																		
4	Grid dimension 40 mm																	
6	Grid dimension 62 mm																	
Service function																		
EE	Solenoid actuated on-off valve																	
Pneumatic connection																		
MS4																		
1/8	Female thread G1/8																	
1/4	Female thread G1/4																	
MS6																		
1/4	Female thread G1/4																	
3/8	Female thread G3/8																	
1/2	Female thread G1/2																	
Supply voltage																		
10V24	Supply voltage 24 V DC																	
V110	Supply voltage 110 V AC																	
V230	Supply voltage 230 V AC																	
Silencer																		
	Without silencer																	
S	Silencer																	


Additional variants can be ordered using the modular system → 28

- Connecting plates
- Supply voltage
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Type of mounting
- EU Certification
- Flow direction

On-off valves MS4/MS6-EE, MS series

Technical data

Function



-  - Flow rate
1,000 ... 7,000 l/min
-  - Temperature range
-10 ... +60 °C
-  - Operating pressure
4 ... 18 bar



- Solenoid actuated on-off valve for pressurising and venting pneumatic installations
- Three voltage ranges can be selected
- Non-detenting and detenting manual override (variant 10V24: only non-detenting)
- Optional pressure sensor
- With solenoid coil without plug socket
- Ducted exhaust possible via a threaded connection with silencer
- Solenoid actuator can be repositioned by 180°
- Optional device variant EX2 for use in potentially explosive areas in zones 2 and 22

General technical data

Size	MS4		MS6		
Pneumatic connection 1, 2	G ¹ / ₈	G ¹ / ₄	G ¹ / ₄	G ³ / ₈	G ¹ / ₂
Pneumatic connection 3	G ¹ / ₄		G ¹ / ₂		
Design	Piston spool valve				
Type of mounting	Via accessories In-line installation				
Assembly position	Any				
Pressure indicator	Via pressure sensor for displaying output pressure via LCD display and electrical output Via pressure sensor for displaying output pressure via operational status indicator and electrical output Via pressure gauge for displaying output pressure Via pressure gauge with red/green scale for displaying output pressure G ¹ / ₄ prepared G ¹ / ₈ prepared				
Valve function	3/2-way valve, single solenoid, closed				
Exhaust function	Without flow control				
Type of reset	Mechanical spring				
Switching position display	Via accessories				
Pilot control mode	Direct				
Pilot air supply	Internal				
Direction of flow	Non-reversible				
C value	[l/(s*bar)]	4.5	9.5	11.0	22.0
b value		0.5	0.44	0.5	0.4

 Note: This product conforms to ISO 1179-1 and to ISO 228-1

Electrical data

Coil characteristics	V24	24 V DC: 1.5 W; perm. voltage fluctuations -25%/+10%
	10V24	24 V DC: 2.5 W; perm. voltage fluctuations ±10%
	10V24P	24 V DC: 1.8 W; perm. voltage fluctuations -15%/+10%
	V110	110 V AC: 50/60 Hz; pick-up power 3.0 W; holding power 2.4 W; perm. voltage fluctuations ±10%
	V230	230 V AC: 50/60 Hz; pick-up power 3.0 W; holding power 2.4 W; perm. voltage fluctuations -14%/+10%
Electrical connection	V24, 10V24, V110, V230	Plug, square design to EN 175301-803, type C
	10V24P	M12x1 to IEC 61076-2-101
Protection class for solenoid coil	IP65	
Duty cycle	[%]	100

**New
Variant 10V24P**

On-off valves MS4/MS6-EE, MS series

Technical data

FESTO

Standard nominal flow rate q_{nN}^1 [l/min]					
Size	MS4		MS6		
Pneumatic connection	G1/8	G1/4	G1/4	G3/8	G1/2
In main flow direction 1 → 2	1,000	2,000	2,600	5,500	7,000
In relief direction 2 → 3	1,600	1,600	7,000	6,200	5,500

1) Measured at $p_1 = 6$ bar and $p_2 = 5$ bar, $\Delta p = 1$ bar

Operating and environmental conditions						
Variant	Coil parameter V24, V110, V230		Coil parameter 10V24, 10V24P		Pressure sensor AD...	
Size	MS4	MS6	MS4	MS6	MS4	MS6
Operating pressure [bar]	4 ... 14 (4 ... 10 with silencer S)	4 ... 18 (4 ... 10 with silencer S)	4 ... 10	4 ... 10	4 ... 10	4 ... 10
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]					
	Inert gases					
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)					
Ambient temperature [°C]	-10 ... +60	-10 ... +60	-10 ... +50	-10 ... +50	0 ... +50	0 ... +50
Temperature of medium [°C]	-10 ... +60	-10 ... +60	-10 ... +50	-10 ... +50	0 ... +50	0 ... +50
Corrosion resistance	CRC ¹⁾	2				

1) Corrosion resistance class 2 according to Festo standard 940 070


Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

ATEX	
Variant	EX2
ATEX category gas	II 3G
Ex-ignition protection type gas	Ex nA II T4 X
ATEX category dust	II 3D
Ex-ignition protection type dust	Ex tD A22 IP65 T105°C X
ATEX ambient temperature	-10 °C ≤ Ta ≤ +60 °C
ATEX certification	For zones 2 and 22
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

Weights [g]		
Size	MS4	MS6
On-off valve	273	740
On-off valve with silencer S	289	816

Materials

Sectional view



On-off valve	
1 Body	Die-cast aluminium
2 Piston spool	NBR/aluminium
3 Springs	High-alloy stainless steel
4 End cap	PA
5 Top plate	PA
6 Socket end connection	PA
– Seals	NBR
Note on materials	
RoHS-compliant	
Free of copper and PTFE (not with variants AG, 10V24, 10V24P or AD...)	

On-off valves MS4/MS6-EE, MS series



Technical data

FESTO

Dimensions – Basic version

With female thread, with cover plate

Download CAD data → www.festo.com



Type	B1	B2		B3		B4	B5	D1	D5
		V24/V110/ V230	10V24/ 10V24P	V24/V110/ V230	10V24/ 10V24P				
MS4-EE-1/8	40	42.2	34.9	75.2	67.9	21	54	G ¹ / ₈	G ¹ / ₄
MS4-EE-1/4								G ¹ / ₄	
MS6-EE-1/4	62	52	44.7	97	89.7	31	76	G ¹ / ₄	G ¹ / ₂
MS6-EE-3/8								G ³ / ₈	
MS6-EE-1/2								G ¹ / ₂	

Type	L1			L2	L3	L7	L8	L9
	V24/V110/ V230	10V24	10V24P					
MS4-EE-1/8	142.8	140.4	145.2	58.9	100	8.6	36.7	26.1
MS4-EE-1/4								
MS6-EE-1/4	185.6	183.2	188	84	143	8.6	36.7	26.1
MS6-EE-3/8								
MS6-EE-1/2								

 Note: This product conforms to ISO 1179-1 and to ISO 228-1

On-off valves MS4/MS6-EE, MS series

Technical data


FESTO

Dimensions – Pressure gauge/pressure gauge alternatives

Integrated MS pressure gauge with standard scale AG or red-green scale RG,
display unit [bar]

Download CAD data → www.festo.com

Adapter plate A8/A4 for EN pressure gauge 1/8/1/4, without pressure gauge



Type	B2 V24/V110/V230	B2 10V24/10V24P	B3 V24/V110/V230	B3 10V24/10V24P	D1	D4
MS4-EE-1/8...-AG	42.2	34.9	86.2	78.9	G1/8	–
MS4-EE-1/4...-AG					G1/4	
MS4-EE-1/8...-RG	42.2	34.9	87.7	80.4	G1/8	–
MS4-EE-1/4...-RG					G1/4	
MS4-EE-1/8...-A8	42.2	34.9	79.7	72.4	G1/8	
MS4-EE-1/4...-A8					G1/4	G1/8
MS4-EE-1/8...-A4	42.2	34.9	79.7	72.4	G1/8	
MS4-EE-1/4...-A4					G1/4	G1/4
MS6-EE-1/4...-AG					G1/4	
MS6-EE-3/8...-AG	52	44.7	106	98.7	G3/8	–
MS6-EE-1/2...-AG					G1/2	
MS6-EE-1/4...-RG					G1/4	
MS6-EE-3/8...-RG	52	44.7	107.5	100.2	G3/8	–
MS6-EE-1/2...-RG					G1/2	
MS6-EE-1/4...-A4					G1/4	
MS6-EE-3/8...-A4	52	44.7	99.6	92.3	G3/8	G1/4
MS6-EE-1/2...-A4					G1/2	

 Note: This product conforms to ISO 1179-1 and to ISO 228-1


On-off valves MS4/MS6-EE, MS series

Technical data

FESTO

Dimensions – Pressure gauge/pressure gauge alternatives

Pressure sensor with LCD display AD1 ... AD4



Download CAD data → www.festo.com

Technical data → Internet: sde1

Variant AD1:
SDE1-D10-G2-MS-L-P1-M8 with
3-pin plug M8x1, 1 switching output PNP

Variant AD2:
SDE1-D10-G2-MS-L-N1-M8 with
3-pin plug M8x1, 1 switching output NPN

Variant AD3:
SDE1-D10-G2-MS-L-PI-M12 with
4-pin plug M12x1, 1 switching output PNP and 4 ... 20 mA analogue

Variant AD4:
SDE1-D10-G2-MS-L-NI-M12 with
4-pin plug M12x1, 1 switching output NPN and 4 ... 20 mA analogue

Type	B2		B3		B4	B5	D1	D6	L5	L6
	V24/ V110/ V230	10V24/ 10V24P	V24/ V110/ V230	10V24/ 10V24P						
MS4-EE-1/8-...-AD1/AD2	42.2	34.9	103.8	96.5	21	82.6	G1/8 G1/4	M8x1	35.1	46.7
MS4-EE-1/4-...-AD1/AD2										
MS4-EE-1/8-...-AD3/AD4	42.2	34.9	103.8	96.5	21	82.6	G1/8 G1/4	M12x1	35.1	55.8
MS4-EE-1/4-...-AD3/AD4										
MS6-EE-1/4-...-AD1/AD2	52	44.7	124	116.7	31	103	G1/4 G3/8 G1/2	M8x1	35.1	46.7
MS6-EE-3/8-...-AD1/AD2										
MS6-EE-1/2-...-AD1/AD2										
MS6-EE-1/4-...-AD3/AD4	52	44.7	124	116.7	31	103	G1/4 G3/8 G1/2	M12x1	35.1	55.8
MS6-EE-3/8-...-AD3/AD4										
MS6-EE-1/2-...-AD3/AD4										

Note: This product conforms to ISO 1179-1 and to ISO 228-1

**New
Variant 10V24P**


On-off valves MS4/MS6-EE, MS series

Technical data

FESTO

Dimensions – Pressure gauge/pressure gauge alternatives

Pressure sensor with operational status indicator AD7 ... AD10



→ Flow direction

Download CAD data → www.festo.com

Technical data → Internet: sde5

Variant AD7:
SDE5-D10-O-...-P-M8 with 3-pin
plug M8x1, threshold value
comparator, 1 switching output PNP,
N/O contact

Variant AD8:
SDE5-D10-C-...-P-M8 with 3-pin
plug M8x1, threshold value
comparator, 1 switching output PNP,
N/C contact

Variant AD9:
SDE5-D10-O3-...-P-M8 with 3-pin
plug M8x1, window comparator,
1 switching output PNP, N/O contact

Variant AD10:
SDE5-D10-C3-...-P-M8 with 3-pin
plug M8x1, window comparator,
1 switching output PNP, N/C contact

Type	B2		B3		B4	B5	D1	D6
	V24/ V110/ V230	10V24/ 10V24P	V24/ V110/ V230	10V24/ 10V24P				
MS4-EE-1/8-...-AD7/AD8/AD9/AD10	42.2	34.9	80.3	73	21	59.1	G ¹ / ₈	M8x1
MS4-EE-1/4-...-AD7/AD8/AD9/AD10							G ¹ / ₄	
MS6-EE-1/4-...-AD7/AD8/AD9/AD10	52	44.7	100.2	92.9	31	79	G ¹ / ₄	M8x1
MS6-EE-3/8-...-AD7/AD8/AD9/AD10							G ³ / ₈	
MS6-EE-1/2-...-AD7/AD8/AD9/AD10							G ¹ / ₂	

Note: This product conforms to ISO 1179-1 and to ISO 228-1


On-off valves MS4/MS6-EE, MS series

Technical data

FESTO

Dimensions – Silencer

Download CAD data → www.festo.com



Type	D2	L4
MS4-EE-...-S	19.5	48.5
MS6-EE-...-S	28	106

Ordering data

Size	Connection	Without silencer		With silencer	
		Part No.	Type	Part No.	Type
Supply voltage 24 V DC					
MS4	G ¹ / ₈	542580	MS4-EE-1/8-10V24	542600	MS4-EE-1/8-10V24-S
	G ¹ / ₄	542578	MS4-EE-1/4-10V24	542598	MS4-EE-1/4-10V24-S
MS6	G ¹ / ₄	542584	MS6-EE-1/4-10V24	542604	MS6-EE-1/4-10V24-S
	G ³ / ₈	542586	MS6-EE-3/8-10V24	542606	MS6-EE-3/8-10V24-S
	G ¹ / ₂	542582	MS6-EE-1/2-10V24	542602	MS6-EE-1/2-10V24-S
Supply voltage 110 V AC					
MS4	G ¹ / ₈	529541	MS4-EE-1/8-V110 ¹⁾	538725	MS4-EE-1/8-V110-S ¹⁾
	G ¹ / ₄	529535	MS4-EE-1/4-V110 ¹⁾	538719	MS4-EE-1/4-V110-S ¹⁾
MS6	G ¹ / ₄	529829	MS6-EE-1/4-V110 ¹⁾	538737	MS6-EE-1/4-V110-S ¹⁾
	G ³ / ₈	529835	MS6-EE-3/8-V110 ¹⁾	538743	MS6-EE-3/8-V110-S ¹⁾
	G ¹ / ₂	529823	MS6-EE-1/2-V110 ¹⁾	538731	MS6-EE-1/2-V110-S ¹⁾
Supply voltage 230 V AC					
MS4	G ¹ / ₈	529543	MS4-EE-1/8-V230 ¹⁾	538727	MS4-EE-1/8-V230-S ¹⁾
	G ¹ / ₄	529537	MS4-EE-1/4-V230 ¹⁾	538721	MS4-EE-1/4-V230-S ¹⁾
MS6	G ¹ / ₄	529831	MS6-EE-1/4-V230 ¹⁾	538739	MS6-EE-1/4-V230-S ¹⁾
	G ³ / ₈	529837	MS6-EE-3/8-V230 ¹⁾	538745	MS6-EE-3/8-V230-S ¹⁾
	G ¹ / ₂	529825	MS6-EE-1/2-V230 ¹⁾	538733	MS6-EE-1/2-V230-S ¹⁾

1) Free of copper and PTFE

 New
Variant 10V24P

FESTO

On-off valves MS4/MS6-EE, MS series

Ordering data – Modular products

M Mandatory data →					
Module No.	Series	Size	Function	Pneumatic connection	Supply voltage
527709	MS	4	EE	1/8, 1/4, 3/8, 1/2, AGA, AGB, AGC, AGD, AGE	V24, 10V24, 10V24P, V110, V230
527682		6			
Order example	527709	MS	4 - EE - AGB - V24		-

Ordering table						
Grid dimension [mm]	40	62	Conditions	Code	Enter code	
M Module No.	527709	527682				
Series	Standard			MS		MS
Size	4	6		...		
Function	On-off valve, electrical			-EE		-EE
Pneumatic connection	Female thread G1/8	-	[5]	-1/8		
	Female thread G1/4	Female thread G1/4	[5]	-1/4		
	-	Female thread G3/8	[5]	-3/8		
	-	Female thread G1/2	[5]	-1/2		
	Connecting plate G1/8	-		-AGA		
	Connecting plate G1/4	Connecting plate G1/4		-AGB		
	Connecting plate G3/8	Connecting plate G3/8		-AGC		
	-	Connecting plate G1/2		-AGD		
	-	Connecting plate G3/4		-AGE		
Supply voltage	24 V DC (pin allocation to EN 175301)			-V24		
	4 ... 14 bar	4 ... 18 bar				
	24 V DC (pin allocation to EN 175301)		[1][5]	-10V24		
	4 ... 10 bar	4 ... 10 bar				
	24 V DC, M12 to IEC 61076-2-101		[1][5]	-10V24P		
	4 ... 10 bar	4 ... 10 bar				
	110 V AC (pin allocation to EN 175301)		[5]	-V110		
	4 ... 14 bar	4 ... 18 bar				
	230 V AC (pin allocation to EN 175301)		[5]	-V230		
	4 ... 14 bar	4 ... 18 bar				

10V24, 10V24P

Max. operating pressure 10 bar

Transfer order code

	MS		EE		-	
--	----	--	----	--	---	--

On-off valves MS4/MS6-EE, MS series

Ordering data – Modular products

FESTO

→ Options

Silencer	Pressure gauge/ pressure gauge alternatives	Alternative pressure gauge scale	Type of mounting	EU certification	Flow direction
S	AG, A8, A4, RG, AD1, AD2, AD3, AD4, AD7, AD8, AD9, AD10	PSI, MPA	WP, WPM, WB, WBM	EX2	Z
- S -	- AG -	- PSI -	- WP -	-	- Z -

Ordering table

Grid dimension [mm]	40	62	Conditions	Code	Enter code
<input type="checkbox"/> Silencer	Silencer			-S	
Pressure gauge/pressure gauge alternatives	MS pressure gauge (with adapter plate)	MS pressure gauge		-AG	
	Adapter plate for EN pressure gauge 1/8, without pressure gauge	-		-A8	
	Adapter plate for EN pressure gauge 1/4, without pressure gauge			-A4	
	Integrated pressure gauge, red-green scale			-RG	
	Pressure sensor with LCD display, plug M8, 1 switching output PNP, 3-pin	[2] [5]		-AD1	
	Pressure sensor with LCD display, plug M8, 1 switching output NPN, 3-pin	[2] [5]		-AD2	
	Pressure sensor with LCD display, plug M12, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA	[2] [5]		-AD3	
	Pressure sensor with LCD display, plug M12, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA	[2] [5]		-AD4	
	Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/O contact	[2] [5]		-AD7	
	Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/C contact	[2] [5]		-AD8	
	Pressure sensor with operational status indicator, plug M8, window comparator, PNP, N/O contact	[2] [5]		-AD9	
	Pressure sensor with operational status indicator, plug M8, window comparator, PNP, N/C contact	[2] [5]		-AD10	
Alternative pressure gauge scale	psi	[3]		-PSI	
	MPa	[3]		-MPA	
Type of mounting	Mounting bracket	[4]		-WP	
	Mounting bracket	[4] [5]		-WPM	
	Mounting bracket			-WB	
	Mounting bracket	-		-WBM	
EU certification	II 3GD to EU Directive 94/9/EG			-EX2	
Flow direction	Flow direction from right to left			-Z	

AD1 ... AD4, AD7 ... AD10

Measuring range max. 10 bar

PSI, MPa Only in combination with pressure gauge AG or RG

WP, WPM Only with connecting plate AGA, AGB, AGC, AGD or AGE

1/8, 1/4, 3/8, 1/2, 10V24, 10V24P, V110, V230, AD1 ... AD4, AD7 ... AD10, WPM

Not with EU EX2 certification

Transfer order code


- - - - - -

Soft-start valves MS4/MS6-DL, MS series

Peripherals overview

FESTO

Soft-start valve MS4/MS6-DL



- - Note

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter plate for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80

Mounting attachments and accessories

	Individual device		Combination		→ Page/Internet
	Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1] Cover cap MS4/6-END	■	-	■	-	ms4-end, ms6-end
[2] Connecting plate MS4/6-AG...	-	■	-	■	ms4-ag, ms6-ag
[3] Module connector MS4/6-MV	-	■	■	■	ms4-mv, ms6-mv
[4] Mounting bracket MS4/6-WB	■	■	-	-	ms4-wb, ms6-wb
[5] Mounting bracket MS4-WBM	■	■	-	-	ms4-wbm
[6] MS pressure gauge AG/RG	■	■	■	■	36
[7] Adapter plate for EN pressure gauge 1/8/1/4 A8/A4	■	■	■	■	36
[8] Pressure gauge MA	■	■	■	■	107
[9] Pressure sensor without display AD7 ... AD10	■	■	■	■	36
[10] Connecting cable NEBU-M8...-LE3	■	■	■	■	107
[11] Pressure sensor with display AD1 ... AD4	■	■	■	■	36
[12] Connecting cable NEBU-M8...-LE3/NEBU-M12...-LE4	■	■	■	■	107
- Mounting bracket MS4/6-WP/WPB/WPE/WPM	-	■	■	■	ms4-wp, ms6-wp

Soft-start valves MS4/MS6-DL, MS series

FESTO

Type codes

MS	6	-	DL	-	1/2					
Series										
MS	Standard service unit									
Size										
4	Grid dimension 40 mm									
6	Grid dimension 62 mm									
Service function										
DL	Pneumatically actuated soft-start valve									
Pneumatic connection										
MS4										
1/8	Female thread G1/8									
1/4	Female thread G1/4									
MS6										
1/4	Female thread G1/4									
3/8	Female thread G3/8									
1/2	Female thread G1/2									

Additional variants can be ordered using the modular system ➔ 36


- Connecting plates
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Type of mounting
- Flow direction

Soft-start valves MS4/MS6-DL, MS series

Technical data

FESTO

Function



- - Flow rate
1,000 ... 6,450 l/min
- - Temperature range
-10 ... +60 °C
- - Operating pressure
4 ... 18 bar



The duration of the pressure build-up is adjusted using the restrictor attached to the valve cap.

The output pressure p2 rises slowly in accordance with the restrictor setting. The main seat opens when the switch-through pressure is reached.

- Pneumatically actuated soft-start valve for slowly pressurising and venting pneumatic installations (for use with on-off valves EM1 and EE)
- The drives advance slowly and reliably into the initial position

- Sudden and erratic movements are avoided
- Pressure switching approx. 50% of operating pressure
- Adjustable switching time delay
- Optional pressure sensor

General technical data					
Size	MS4		MS6		
Pneumatic connection 1, 2	G1/8	G1/4	G1/4	G3/8	G1/2
Design	Piston poppet valve				
Type of mounting	Via accessories In-line installation				
Assembly position	Any				
Pressure indicator	Via pressure sensor for displaying output pressure via LCD display and electrical output Via pressure sensor for displaying output pressure via operational status indicator and electrical output Via pressure gauge for displaying output pressure Via pressure gauge with red/green scale for displaying output pressure G1/4 prepared G1/8 prepared				
Valve function	2/2-way valve				
Exhaust function	Flow control				
Type of reset	Mechanical spring				
Pilot control mode	Direct				
Pilot air supply	External				
Direction of flow	Non-reversible				
C value [l/(s*bar)]	4.6	9.6	11.22	21.05	28.97
b value	0.5	0.45	0.54	0.48	0.39

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Standard nominal flow rate qnN ¹⁾ [l/min]					
Size	MS4		MS6		
Pneumatic connection	G1/8	G1/4	G1/4	G3/8	G1/2
In main flow direction 1 → 2	1,000	2,000	2,800	5,050	6,450
In relief direction 2 → 1	1,000	2,000	2,800	5,050	6,400

1) Measured at p1 = 6 bar and p2 = 5 bar, Δp = 1 bar

Soft-start valves MS4/MS6-DL, MS series

FESTO

Technical data

Operating and environmental conditions				
Variant	Standard		Pressure sensor AD...	
Size	MS4	MS6	MS4	MS6
Operating pressure [bar]	4 ... 14	4 ... 18	4 ... 10	4 ... 10
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]			
	Inert gases			
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)			
Ambient temperature [°C]	-10 ... +60	-10 ... +60	0 ... +50	0 ... +50
Temperature of medium [°C]	-10 ... +60	-10 ... +60	0 ... +50	0 ... +50
Corrosion resistance	CRC ¹⁾	2		


1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [g]				
Size	MS4	MS6		
Soft-start valve	213	650		

Materials


Sectional view




Soft-start valve	
[1] Body	Die-cast aluminium
[2] Base	PET
[3] End cap	PA
[4] Top plate	PA
[5] Seat	Aluminium
[6] Springs	Spring steel
- Seals	NBR
Note on materials	RoHS-compliant Free of copper and PTFE (not with variants AG or AD...)

Switching point – Pressure p as a function of time t

MS4



MS6



- Note

The tolerance specification +20%/-10% of the switching point refers to the operating pressure p_1 .

Example: at an operating pressure of 4 bar a switching point of 1.6 bar to 2.8 bar is permitted.

- Note

The tolerance specification +20%/-20% of the switching point refers to the operating pressure p_1 .

Example: at an operating pressure of 4 bar a switching point of 1.2 bar to 2.8 bar is permitted.

Soft-start valves MS4/MS6-DL, MS series

Technical data

FESTO

Dimensions – Basic version

With female thread, with cover plate




Type	B1	B2	B3	D1	L1	L2
MS4-DL-1/8	40	21	54	G1/8	82.7	31
MS4-DL-1/4				G1/4		
MS6-DL-1/4	62	31	76	G1/4	116	45
MS6-DL-3/8				G3/8		
MS6-DL-1/2				G1/2		

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Dimensions – Pressure gauge/pressure gauge alternatives

Integrated MS pressure gauge with standard scale AG or red-green scale RG, display unit [bar]

Download CAD data → www.festo.com



Type	B2	B3	D1	D4
MS4-DL-1/8....AG	21	65	G1/8	–
MS4-DL-1/4....AG			G1/4	
MS4-DL-1/8....RG	21	66.5	G1/8	–
MS4-DL-1/4....RG			G1/4	
MS4-DL-1/8....A8	21	58.5	G1/8	G1/8
MS4-DL-1/4....A8			G1/4	
MS4-DL-1/8....A4	21	58.5	G1/8	G1/4
MS4-DL-1/4....A4			G1/4	
MS6-DL-1/4....AG	31	85	G1/4	–
MS6-DL-3/8....AG			G3/8	
MS6-DL-1/2....AG			G1/2	
MS6-DL-1/4....RG	31	86.5	G1/4	–
MS6-DL-3/8....RG			G3/8	
MS6-DL-1/2....RG			G1/2	
MS6-DL-1/4....A4	31	78.5	G1/4	G1/4
MS6-DL-3/8....A4			G3/8	
MS6-DL-1/2....A4			G1/2	

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Internet: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/)

Subject to change – 2012/05


Soft-start valves MS4/MS6-DL, MS series

FESTO

Technical data

Dimensions – Pressure gauge/pressure gauge alternatives

Pressure sensor with LCD display AD1 ... AD4



Variant AD1:
SDE1-D10-G2-MS-L-P1-M8 with
3-pin plug M8x1, 1 switching output PNP

Variant AD2:
SDE1-D10-G2-MS-L-N1-M8 with
3-pin plug M8x1, 1 switching output NPN

Download CAD data → www.festo.com

Technical data → Internet: sde1

Variant AD3:
SDE1-D10-G2-MS-L-PI-M12 with
4-pin plug M12x1, 1 switching output PNP and 4 ... 20 mA analogue

Variant AD4:
SDE1-D10-G2-MS-L-NI-M12 with
4-pin plug M12x1, 1 switching output NPN and 4 ... 20 mA analogue

Pressure sensor with operational status indicator AD7 ... AD10

Variant AD7:
SDE5-D10-O-...-P-M8 with 3-pin
plug M8x1, threshold value
comparator, 1 switching output PNP,
N/O contact

Variant AD8:
SDE5-D10-C-...-P-M8 with 3-pin
plug M8x1, threshold value
comparator, 1 switching output PNP,
N/C contact

Variant AD9:
SDE5-D10-O3-...-P-M8 with 3-pin
plug M8x1, window comparator,
1 switching output PNP, N/O contact

Variant AD10:
SDE5-D10-C3-...-P-M8 with 3-pin
plug M8x1, window comparator,
1 switching output PNP, N/C contact

Type	B2	B3	D1	D6	L5	L6
MS4-DL-1/8-...-AD1/AD2	21	82.6	G ¹ / ₈	M8x1	35.1	46.7
MS4-DL-1/4-...-AD1/AD2			G ¹ / ₄			
MS4-DL-1/8-...-AD3/AD4	21	82.6	G ¹ / ₈	M12x1	35.1	55.8
MS4-DL-1/4-...-AD3/AD4			G ¹ / ₄			
MS4-DL-1/8-...-AD7/AD8/AD9/AD10	21	59.1	G ¹ / ₈	M8x1	-	-
MS4-DL-1/4-...-AD7/AD8/AD9/AD10			G ¹ / ₄			
MS6-DL-1/4-...-AD1/AD2	31	103	G ¹ / ₄	M8x1	35.1	46.7
MS6-DL-3/8-...-AD1/AD2			G ³ / ₈			
MS6-DL-1/2-...-AD1/AD2			G ¹ / ₂			
MS6-DL-1/4-...-AD3/AD4	31	103	G ¹ / ₄	M12x1	35.1	55.8
MS6-DL-3/8-...-AD3/AD4			G ³ / ₈			
MS6-DL-1/2-...-AD3/AD4			G ¹ / ₂			
MS6-DL-1/4-...-AD7/AD8/AD9/AD10	31	79	G ¹ / ₄	M8x1	-	-
MS6-DL-3/8-...-AD7/AD8/AD9/AD10			G ³ / ₈			
MS6-DL-1/2-...-AD7/AD8/AD9/AD10			G ¹ / ₂			

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data

Size	Connection	Part No.	Type
MS4	G ¹ / ₈	529533	MS4-DL-1/8 ¹⁾
	G ¹ / ₄	529531	MS4-DL-1/4 ¹⁾
MS6	G ¹ / ₄	529819	MS6-DL-1/4 ¹⁾
	G ³ / ₈	529821	MS6-DL-3/8 ¹⁾
	G ¹ / ₂	529817	MS6-DL-1/2 ¹⁾

1) Free of copper and PTFE

Soft-start valves MS4/MS6-DL, MS series

Ordering data – Modular products

FESTO

M Mandatory data →				
Module No.	Series	Size	Function	Pneumatic connection
527711	MS	4	DL	1/8, 1/4, 3/8, 1/2, AGA, AGB, AGC, AGD, AGE
527684		6		
Order example				
527711	MS	4	- DL	- AGA

Ordering table						
Grid dimension [mm]	40	62	Condi-	Code	Enter	code
M Module No.	527711	527684				
Series	Standard			MS		
Size	4	6		...		
Function	Soft-start valve, pneumatic			-DL		
Pneumatic connection	Female thread G1/8	–		-1/8		
	Female thread G1/4	Female thread G1/4		-1/4		
	–	Female thread G3/8		-3/8		
	–	Female thread G1/2		-1/2		
	Connecting plate G1/8	–		-AGA		
	Connecting plate G1/4	Connecting plate G1/4		-AGB		
	Connecting plate G3/8	Connecting plate G3/8		-AGC		
	–	Connecting plate G1/2		-AGD		
	–	Connecting plate G3/4		-AGE		

Transfer order code				
	MS		- DL	–

Soft-start valves MS4/MS6-DL, MS series

FESTO

Ordering data – Modular products

→ Options

Pressure gauge/pressure gauge alternatives	Alternative pressure gauge scale	Type of mounting	Flow direction
AG, A8, A4, RG, AD1 ... AD4, AD7 ... AD10	PSI, MPA	WP, WPM, WB, WBM	Z
- AG	- PSI	- WB	- Z

Ordering table

Grid dimension [mm]	40	62	Condi-tions	Code	Enter code
<input type="checkbox"/> Pressure gauge/pressure gauge alternatives	MS pressure gauge, bar (with adapter plate)	MS pressure gauge, bar		-AG	
	Adapter plate for EN pressure gauge 1/8, without pressure gauge	-		-A8	
	Adapter plate for EN pressure gauge 1/4, without pressure gauge			-A4	
	Integrated pressure gauge, red-green scale			-RG	
	Pressure sensor with LCD display, plug M8, 1 switching output PNP, 3-pin	[1]		-AD1	
	Pressure sensor with LCD display, plug M8, 1 switching output NPN, 3-pin	[1]		-AD2	
	Pressure sensor with LCD display, plug M12, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA	[1]		-AD3	
	Pressure sensor with LCD display, plug M12, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA	[1]		-AD4	
	Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/O contact	[1]		-AD7	
	Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/C contact	[1]		-AD8	
	Pressure sensor with operational status indicator, plug M8, window comparator, PNP, N/O contact	[1]		-AD9	
	Pressure sensor with operational status indicator, plug M8, window comparator, PNP, N/C contact	[1]		-AD10	
Alternative pressure gauge scale	psi	[2]		-PSI	
	MPa	[2]		-MPA	
Type of mounting	Mounting bracket	[3]		-WP	
	Mounting bracket	[3]		-WPM	
	Mounting bracket			-WB	
	Mounting bracket	-		-WBM	
Flow direction	Flow direction from right to left			-Z	

AD1 ... AD4, AD7 ... AD10

Measuring range max. 10 bar

PSI, MPa Only with pressure gauge AG or RG

WP, WPM Only with connecting plate AGA, AGB, AGC, AGD or AGE

Transfer order code


- - - -

Soft-start valves MS4/MS6-DE, MS series

Peripherals overview

FESTO

Soft-start valve MS4/MS6-DE




 Note

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter plate for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80

Supply voltage
V24/10V24/V110/V230

Supply voltage
10V24P



Soft-start valves MS4/MS6-DE, MS series

Peripherals overview

Mounting attachments and accessories	Individual device		Combination		➔ Page/Internet
	Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1] Cover cap MS4/6-END	■	-	■	-	ms4-end, ms6-end
[2] Mounting plate MS4/6-AEND	■ ¹⁾	-	■ ¹⁾	-	ms4-aend, ms6-aend
[3] Connecting plate MS4/6-AG...	-	■ ¹⁾	-	■ ¹⁾	ms4-ag, ms6-ag
[4] Mounting bracket MS4/6-WB	■	■	-	-	ms4-wb, ms6-wb
[5] Mounting bracket MS4-WBM	■	■	-	-	ms4-wbm
[6] Module connector MS4/6-MV	-	■	■	■	ms4-mv, ms6-mv
[7] Mounting bracket MS4/6-WP	■	■	■	■	ms4-wp, ms6-wp
Mounting bracket (not illustrated) MS4/6-WPB/WPE/WPM	■	■	■	■	ms4-wp, ms6-wp
[8] MS pressure gauge AG/RG	■	■	■	■	48
[9] Adapter plate for EN pressure gauge 1/8/1/4 A8/A4	■	■	■	■	48
[10] Pressure gauge MA	■	■	■	■	107
[11] Pressure sensor without display AD7 ... AD10	■	■	■	■	48
[12] Connecting cable NEBU-M8...-LE3	■	■	■	■	107
[13] Pressure sensor with display AD1 ... AD4	■	■	■	■	48
[14] Connecting cable NEBU-M8...-LE3/NEBU-M12...-LE4	■	■	■	■	107
[15] Illuminating seal MEB-LD	■	■	■	■	106
[16] Plug socket with cable KMEB	■	■	■	■	106
[17] Plug socket MSSD-EB	■	■	■	■	106
[18] Locking clip CPV18-HV	■	■	■	■	106
[19] Connecting cable NEBU-M12G5	■	■	■	■	107
[20] Connecting cable NEBU-M12W5	■	■	■	■	107

1) Module connector MS4/6-MV [6] or mounting bracket MS4/6-WP/WPB/WPE/WPM [7] is required for mounting.

 **New
Variant 10V24P**

Soft-start valves MS4/MS6-DE, MS series

Type codes

FESTO

MS	6	-	DE	-	1/2	-	V110							
Series														
MS	Standard service unit													
Size														
4	Grid dimension 40 mm													
6	Grid dimension 62 mm													
Service function														
DE	Solenoid actuated soft-start valve													
Pneumatic connection														
MS4														
1/8	Female thread G1/8													
1/4	Female thread G1/4													
MS6														
1/4	Female thread G1/4													
3/8	Female thread G3/8													
1/2	Female thread G1/2													
Supply voltage														
10V24	Supply voltage 24 V DC													
V110	Supply voltage 110 V AC													
V230	Supply voltage 230 V AC													


Additional variants can be ordered using the modular system → 48

- Connecting plates
- Supply voltage
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Type of mounting
- EU Certification
- Flow direction

Soft-start valves MS4/MS6-DE, MS series

Technical data

Function



-  - Flow rate
1,000 ... 6,450 l/min
-  - Temperature range
-10 ... +60 °C
-  - Operating pressure
4 ... 18 bar



The duration of the pressure build-up is adjusted using the restrictor attached to the valve cap. The output pressure p_2 rises slowly in accordance with the restrictor setting. Only the air flow from the restrictor is available when the solenoid valve is not actuated. The main seat is only opened by energising the solenoid valve.

When the solenoid valve is switched off, the main seat is closed and only the air flow from the flow control valve is available. The solenoid valve should remain switched on in order to vent a system as this increases the flow rate from 2 and 1 and reduces the exhaust time.

- Solenoid actuated soft-start valve for slowly pressurising and venting pneumatic installations
- The drives advance slowly and reliably into the initial position
- Sudden and erratic movements are avoided
- With solenoid coil without plug socket
- Switch-through pressure can be precisely controlled using a solenoid valve
- Adjustable switching time delay
- Three voltage ranges can be selected
- Non-detenting and detenting manual override (variant 10V24: only non-detenting)
- Solenoid actuator can be repositioned by 180°
- Optional pressure sensor
- Optional device variant EX2 for use in potentially explosive areas in zones 2 and 22

General technical data

Size	MS4	MS6			
Pneumatic connection 1, 2	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{1}{2}$
Design	Piston poppet valve				
Type of mounting	Via accessories				
	In-line installation				
Assembly position	Any				
Pressure indicator	Via pressure sensor for displaying output pressure via LCD display and electrical output Via pressure sensor for displaying output pressure via operational status indicator and electrical output Via pressure gauge for displaying output pressure Via pressure gauge with red/green scale for displaying output pressure G $\frac{1}{4}$ prepared G $\frac{1}{8}$ prepared				
Valve function	2/2-way valve				
Exhaust function	Flow control				
Type of reset	Mechanical spring				
Switching position display	Via accessories				
Pilot control mode	Piloted				
Pilot air supply	External				
Direction of flow	Non-reversible				
C value [l/(s*bar)]	4.6	9.6	11.22	21.05	28.97
b value	0.5	0.45	0.54	0.48	0.39

 Note: This product conforms to ISO 1179-1 and to ISO 228-1

 **New**
Variant 10V24P

Soft-start valves MS4/MS6-DE, MS series

Technical data

FESTO

Electrical data		
Coil characteristics	V24	24 V DC: 1.5 W; perm. voltage fluctuations -25%/+10%
	10V24	24 V DC: 2.5 W; perm. voltage fluctuations ±10%
	10V24P	24 V DC: 1.8 W; perm. voltage fluctuations -15%/+10%
	V110	110 V AC: 50/60 Hz; pick-up power 3.0 W; holding power 2.4 W; perm. voltage fluctuations ±10%
	V230	230 V AC: 50/60 Hz; pick-up power 3.0 W; holding power 2.4 W; perm. voltage fluctuations -14%/+10%
Electrical connection	V24, 10V24, V110, V230	Plug, square design to EN 175301-803, type C
	10V24P	M12x1 to IEC 61076-2-101
Protection class solenoid coil	IP65	
Duty cycle [%]	100	

Standard nominal flow rate q_{nN}^1 [l/min]					
Size	MS4	MS6	MS4	MS6	MS4
Pneumatic connection	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{1}{2}$
In main flow direction 1 → 2	1,000	2,000	2,700	5,050	6,450
In relief direction 2 → 1 ²⁾	1,000	2,000	2,600	5,050	6,400

1) Measured at p₁ = 6 bar and p₂ = 5 bar, Δp = 1 bar

2) For energised solenoid valve.

Operating and environmental conditions						
Variant	Coil parameter V24, V110, V230		Coil parameter 10V24, 10V24P		Pressure sensor AD...	
Size	MS4	MS6	MS4	MS6	MS4	MS6
Operating pressure [bar]	4 ... 14	4 ... 18	4 ... 10	4 ... 10	4 ... 10	4 ... 10
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]					
	Inert gases					
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)					
Ambient temperature [°C]	-10 ... +60	-10 ... +60	-10 ... +50	-10 ... +50	0 ... +50	0 ... +50
Temperature of medium [°C]	-10 ... +60	-10 ... +60	-10 ... +50	-10 ... +50	0 ... +50	0 ... +50
Corrosion resistance	CRC ¹⁾	2				

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

ATEX	
Variant	EX2
ATEX category gas	II 3G
Ex-ignition protection type gas	Ex nA II T4 X
ATEX category dust	II 3D
Ex-ignition protection type dust	Ex tD A22 IP65 T105°C X
ATEX ambient temperature	-10 °C ≤ Ta ≤ +60 °C
ATEX certification	For zones 2 and 22
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

Soft-start valves MS4/MS6-DE, MS series

Technical data


FESTO

Weights [g]

Size	MS4	MS6
Soft-start valve	263	680

Materials

Sectional view



Soft-start valve

[1] Body	Die-cast aluminium
[2] Base	PET
[3] Valve stem	Aluminium
[4] End cap	PA
[5] Top plate	PA
[6] Seat	Aluminium
[7] Springs	Spring steel
- Seals	NBR
Note on materials	RoHS-compliant Free of copper and PTFE (not with variants AG, 10V24, 10V24P or AD...)

**New
Variant 10V24P**

Soft-start valves MS4/MS6-DE, MS series



Technical data

FESTO

Dimensions – Basic version

With female thread, with cover plate

Download CAD data → www.festo.com



Type	B1	B2		B3		B4	B5	D1
		V24/ V110/ V230	10V24/ 10V24P	V24/ V110/ V230	10V24/ 10V24P			
MS4-DE-1/8	40	42.2	34.9	75.2	67.9	21	54	G ¹ / ₈
MS4-DE-1/4								G ¹ / ₄
MS6-DE-1/4	62	52	44.7	97	89.7	31	76	G ¹ / ₄
MS6-DE-3/8								G ³ / ₈
MS6-DE-1/2								G ¹ / ₂

Type	L1			L2	L7	L8	L9
	V24/ V110/ V230	10V24	10V24P				
MS4-DE-1/8	115.4	112.9	117.8	31.5	8.6	36.7	26.1
MS4-DE-1/4							
MS6-DE-1/4	147	144.9	149.8	45.5	8.6	36.7	26.1
MS6-DE-3/8							
MS6-DE-1/2							

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Soft-start valves MS4/MS6-DE, MS series

Technical data


FESTO

Dimensions – Pressure gauge/pressure gauge alternatives

Integrated MS pressure gauge with standard scale AG or red-green scale RG, display unit [bar]

Download CAD data → www.festo.com

Adapter plate A8/A4 for EN pressure gauge 1/8/1/4, without pressure gauge



Type	B2		B3		D1	D4
	V24/V110/V230	10V24/10V24P	V24/V110/V230	10V24/10V24P		
MS4-DE-1/8-...-AG	42.2	34.9	86.2	78.9	G ¹ / ₈	–
MS4-DE-1/4-...-AG					G ¹ / ₄	
MS4-DE-1/8-...-RG	42.2	34.9	87.7	80.4	G ¹ / ₈	–
MS4-DE-1/4-...-RG					G ¹ / ₄	
MS4-DE-1/8-...-A8	42.2	34.9	79.7	72.4	G ¹ / ₈	G ¹ / ₈
MS4-DE-1/4-...-A8					G ¹ / ₄	
MS4-DE-1/8-...-A4	42.2	34.9	79.7	72.4	G ¹ / ₈	G ¹ / ₄
MS4-DE-1/4-...-A4					G ¹ / ₄	
MS6-DE-1/4-...-AG	52	44.7	106	98.7	G ¹ / ₄	–
MS6-DE-3/8-...-AG					G ³ / ₈	
MS6-DE-1/2-...-AG					G ¹ / ₂	
MS6-DE-1/4-...-RG	52	44.7	107.5	100.2	G ¹ / ₄	–
MS6-DE-3/8-...-RG					G ³ / ₈	
MS6-DE-1/2-...-RG					G ¹ / ₂	
MS6-DE-1/4-...-A4	52	44.7	99.6	92.3	G ¹ / ₄	G ¹ / ₄
MS6-DE-3/8-...-A4					G ³ / ₈	
MS6-DE-1/2-...-A4					G ¹ / ₂	

 Note: This product conforms to ISO 1179-1 and to ISO 228-1


Soft-start valves MS4/MS6-DE, MS series

Technical data

FESTO

Dimensions – Pressure gauge/pressure gauge alternatives

Pressure sensor with LCD display AD1 ... AD4



Download CAD data → www.festo.com

Technical data → Internet: sde1

Variant AD1:
SDE1-D10-G2-MS-L-P1-M8 with
3-pin plug M8x1, 1 switching output PNP

Variant AD2:
SDE1-D10-G2-MS-L-N1-M8 with
3-pin plug M8x1, 1 switching output NPN

Variant AD3:
SDE1-D10-G2-MS-L-PI-M12 with
4-pin plug M12x1, 1 switching output PNP and 4 ... 20 mA analogue

Variant AD4:
SDE1-D10-G2-MS-L-NI-M12 with
4-pin plug M12x1, 1 switching output NPN and 4 ... 20 mA analogue

Type	B2		B3		B4	B5	D1	D6	L5	L6
	V24/ V110/ V230	10V24/ 10V24P	V24/ V110/ V230	10V24/ 10V24P						
MS4-DE-1/8-...-AD1/AD2	42.2	34.9	103.8	96.5	21	82.6	G1/8	M8x1	35.1	46.7
MS4-DE-1/4-...-AD1/AD2							G1/4			
MS4-DE-1/8-...-AD3/AD4	42.2	34.9	103.8	96.5	21	82.6	G1/8	M12x1	35.1	55.8
MS4-DE-1/4-...-AD3/AD4							G1/4			
MS6-DE-1/4-...-AD1/AD2	52	44.7	124	116.7	31	103	G1/4	M8x1	35.1	46.7
MS6-DE-3/8-...-AD1/AD2							G3/8			
MS6-DE-1/2-...-AD1/AD2							G1/2			
MS6-DE-1/4-...-AD3/AD4	52	44.7	124	116.7	31	103	G1/4	M12x1	35.1	55.8
MS6-DE-3/8-...-AD3/AD4							G3/8			
MS6-DE-1/2-...-AD3/AD4							G1/2			

 Note: This product conforms to ISO 1179-1 and to ISO 228-1


Soft-start valves MS4/MS6-DE, MS series

Technical data

FESTO

Dimensions – Pressure gauge/pressure gauge alternatives

Pressure sensor with operational status indicator AD7 ... AD10



Download CAD data → www.festo.com

Technical data → Internet: sde5

Variant AD7:
SDE5-D10-0...-P-M8 with 3-pin
plug M8x1, threshold value
comparator, 1 switching output PNP,
N/O contact

Variant AD8:
SDE5-D10-C...-P-M8 with 3-pin
plug M8x1, threshold value
comparator, 1 switching output PNP,
N/C contact

Variant AD9:
SDE5-D10-03...-P-M8 with 3-pin
plug M8x1, window comparator,
1 switching output PNP, N/O contact

Variant AD10:
SDE5-D10-C3...-P-M8 with 3-pin
plug M8x1, window comparator,
1 switching output PNP, N/C contact

Type	B2		B3		B4	B5	D1	D6
	V24/ V110/ V230	10V24/ 10V24P	V24/ V110/ V230	10V24/ 10V24P				
MS4-DE-1/8...-AD7/AD8/AD9/AD10	42.2	34.9	80.3	73	21	59.1	G1/8	M8x1
MS4-DE-1/4...-AD7/AD8/AD9/AD10							G1/4	
MS6-DE-1/4...-AD7/AD8/AD9/AD10	52	44.7	100.2	92.9	31	79	G1/4	M8x1
MS6-DE-3/8...-AD7/AD8/AD9/AD10							G3/8	
MS6-DE-1/2...-AD7/AD8/AD9/AD10							G1/2	

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data		
Size	Connection	Supply voltage 24 V DC
		Part No. Type
MS4	G1/8	542560 MS4-DE-1/8-10V24
	G1/4	542558 MS4-DE-1/4-10V24
MS6	G1/4	542564 MS6-DE-1/4-10V24
	G3/8	542566 MS6-DE-3/8-10V24
	G1/2	542562 MS6-DE-1/2-10V24
Supply voltage 110 V AC		
		Part No. Type
		529525 MS4-DE-1/8-V110 ¹⁾
		529519 MS4-DE-1/4-V110 ¹⁾
		529805 MS6-DE-1/4-V110 ¹⁾
		529811 MS6-DE-3/8-V110 ¹⁾
		529799 MS6-DE-1/2-V110 ¹⁾
Supply voltage 230 V AC		
		Part No. Type
		529527 MS4-DE-1/8-V230 ¹⁾
		529521 MS4-DE-1/4-V230 ¹⁾
		529807 MS6-DE-1/4-V230 ¹⁾
		529813 MS6-DE-3/8-V230 ¹⁾
		529801 MS6-DE-1/2-V230 ¹⁾

1) Free of copper and PTFE

 New
Variant 10V24P

Soft-start valves MS4/MS6-DE, MS series

Ordering data – Modular products

FESTO

M Mandatory data					
Module No.	Series	Size	Function	Pneumatic connection	Supply voltage
527713	MS	4	DE	1/8, 1/4, 3/8, 1/2, AGA, AGB, AGC, AGD, AGE	V24, 10V24, 10V24P, V110, V230
527686		6			
Order example	527713	MS	4	- DE	- AGA - V110 -

Ordering table					
Grid dimension	[mm]	40	62	Conditions	Code
M Module No.	527713	527686			
Series	Standard			MS	MS
Size	4	6		...	
Function	Soft-start valve, electrical			-DE	-DE
Pneumatic connection	Female thread G1/8	–	5	-1/8	
	Female thread G1/4	Female thread G1/4	5	-1/4	
	–	Female thread G3/8	5	-3/8	
	–	Female thread G1/2	5	-1/2	
	Connecting plate G1/8	–		-AGA	
	Connecting plate G1/4	Connecting plate G1/4		-AGB	
	Connecting plate G3/8	Connecting plate G3/8		-AGC	
	–	Connecting plate G1/2		-AGD	
	–	Connecting plate G3/4		-AGE	
Supply voltage	24 V DC (pin allocation to EN 175301)				-V24
	4 ... 14 bar	4 ... 18 bar			
	24 V DC (pin allocation to EN 175301)		1 5	-10V24	
	4 ... 10 bar	4 ... 10 bar			
	24 V DC, M12 to IEC 61076-2-101		1 5	-10V24P	
	4 ... 10 bar	4 ... 10 bar			
	110 V AC (pin allocation to EN 175301)		5	-V110	
	4 ... 14 bar	4 ... 18 bar			
	230 V AC (pin allocation to EN 175301)		5	-V230	
	4 ... 14 bar	4 ... 18 bar			

1 10V24, 10V24P

Max. operating pressure 10 bar

Transfer order code

MS	4	- DE	- AGA	- V110
-----------	----------	-------------	--------------	---------------

Soft-start valves MS4/MS6-DE, MS series

FESTO

Ordering data – Modular products

→ Options

Pressure gauge/pressure gauge alternatives	Alternative pressure gauge scale	Type of mounting	EU certification	Flow direction
AG, A8, A4, RG, AD1, AD2, AD3, AD4, AD7, AD8, AD9, AD10	PSI, MPA	WP, WPM, WB, WBM	EX2	Z
- AG	- PSI	- WP	-	- Z

Ordering table

Grid dimension [mm]	40	62	Conditions	Code	Enter code
<input type="checkbox"/> Pressure gauge/pressure gauge alternatives	MS pressure gauge (with adapter plate) Adapter plate for EN pressure gauge 1/8, without pressure gauge Adapter plate for EN pressure gauge 1/4, without pressure gauge Integrated pressure gauge, red-green scale Pressure sensor with LCD display, plug M8, 1 switching output PNP, 3-pin Pressure sensor with LCD display, plug M8, 1 switching output NPN, 3-pin Pressure sensor with LCD display, plug M12, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA Pressure sensor with LCD display, plug M12, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/O contact Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/C contact Pressure sensor with operational status indicator, plug M8, window comparator, PNP, N/O contact Pressure sensor with operational status indicator, plug M8, window comparator, PNP, N/C contact	MS pressure gauge –		-AG -A8 -A4 -RG [2][5] -AD1 [2][5] -AD2 [2][5] -AD3 [2][5] -AD4 [2][5] -AD7 [2][5] -AD8 [2][5] -AD9 [2][5] -AD10	
Alternative pressure gauge scale	psi MPa			[3] -PSI [3] -MPA	
Type of mounting	Mounting bracket Mounting bracket Mounting bracket Mounting bracket			[4] -WP [4][5] -WPM -WB -WBM	
EU certification	II 3GD to EU Directive 94/9/EG			-EX2	
Flow direction	Flow direction from right to left			-Z	

AD1 ... AD4, AD7 ... AD10

Measuring range max. 10 bar

PSI, MPA Only with pressure gauge AG or RG

WP, WPM Only with connecting plate AGA, AGB, AGC, AGD or AGE

1/8, 1/4, 3/8, 1/2, 10V24, 10V24P, V110, V230, AD1 ... AD4, AD7 ... AD10, WPM

Not with EU EX2 certification

Transfer order code


- - - - -

Soft start and exhaust valves MS6-SV, MS series

Peripherals overview

FESTO

Soft start and exhaust valves MS6-SV



 Note

Other accessories:

- Module connector for combination with sizes MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter plate for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80

Soft start and exhaust valves MS6-SV, MS series

Peripherals overview

Mounting attachments and accessories	Individual device		Combination		➔ Page/Internet
	Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1] Cover cap MS6-END	-	-	■	-	ms6-end
[2] Mounting plate MS6-AEND	■ ¹⁾	-	■ ²⁾	-	ms6-aend
[3] Connecting plate MS6-AG...	-	■ ¹⁾	-	■ ²⁾	ms6-ag
[4] Module connector MS6-MV	-	-	■	■	ms6-mv
[5] Mounting bracket MS6-WPB	■	■	■	■	ms6-wpb
[6] Mounting bracket MS6-WPE	■	■	■	■	ms6-wpe
[7] MS pressure gauge AG	■	■	■	■	60
[8] Adapter plate for EN pressure gauge 1/4 A4	■	■	■	■	60
[9] Pressure gauge MA	■	■	■	■	107
[10] Pressure sensor with display AD1 ... AD4	■	■	■	■	60
[11] Connecting cable NEBU-M8...-LE3/NEBU-M12...-LE4	■	■	■	■	107
[12] Multi-pin plug socket NECA	■	■	■	■	62
[13] Silencer UOS-1	■	■	■	■	63

1) Mounting bracket MS6-WPB/WPE is required for mounting.

2) Module connector MS6-MV or mounting bracket MS6-WPB/WPE is required for mounting.

Soft-start and exhaust valves MS6-SV, MS series

Type codes

FESTO

MS	6	SV	1/2	E	10V24	SO	AG
Series							
MS	Standard service unit						
Size							
6	Grid dimension 62 mm						
Service function							
SV	Soft-start and exhaust valve						
Pneumatic connection							
1/2	Female thread G1/2						
Performance level							
E	Category 4 to EN ISO 13849-1, 2-channel with self-monitoring						
Supply voltage							
10V24	Supply voltage 24 V DC						
Silencer							
	Without silencer						
SO	Silencer, open						
Pressure gauge/pressure gauge alternatives							
AG	MS pressure gauge						
AD1	Pressure sensor with LCD display, M8 plug, PNP, 3-pin						


Additional variants can be ordered using the modular system → 60

- Connecting plates
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Multi-pin plug socket
- Type of mounting
- UL certification
- Flow direction

Soft-start and exhaust valves MS6-SV, MS series

Technical data

Function



- - Flow rate
4,300 l/min
- - Temperature range
-10 ... +50 °C
- - Operating pressure
3.5 ... 10 bar
- - www.festo.com



The electropneumatic soft-start and exhaust valve is used to reduce pressure quickly and reliably and to build up pressure gradually in industrial pneumatic systems and terminals. The device is a self-testing, redundant mechatronic system conforming to the

requirements of EN ISO 13849-1. The safety-related pneumatic protection objective of safe venting is also guaranteed in the event of faults inside the valve (e.g. due to wear, contamination, electronic faults). Thanks to the 2-channel design and its monitoring,

the device fulfils controller category 3 and 4 requirements. This enables a performance level of max. "e" to be attained.

Via the electrical connection (multi-pin plug socket NECA Sub-D, 9-pin), the device receives the secure enable

signals (EN1/EN2) from commercially available electronic or electromechanical protective switchgear, which monitor the protective equipment of the machine (e.g. emergency stop, light curtain, electrical door switch of the protective enclosure etc.).

Note

The device must only be used in conjunction with an NECA approved multi-pin plug socket. This can be ordered via the modular product system (MP... → 60) or as an accessory (NECA → 62).

Note

To avoid back pressures, it is recommended that the device be operated together with the silencer UOS-1. The silencer can be ordered via the modular product system (SO → 60) or as an accessory (UOS-1 → 63).

Note

Only devices that do not impair the pneumatic protective measure – safe venting – may be placed downstream of the MS6-SV. The MS6-SV is not permitted for use as a press safety valve.

- Performance level "e"/category 4 to EN ISO 13849-1
- Conforms to IEC 61508
- A switching time delay adjusted via a flow control valve for gradual pressure build-up
- Optional pressure sensor

Safety-related characteristics

Conforms to	EN ISO 13849-1
Safety function	Venting Protection against manipulation, prevention of unexpected start-up
Performance Level (PL)	Venting: category 4, PL e Protection against manipulation, prevention of unexpected start-up: category 4, PL e
Safety Integrity Level (SIL)	Venting: SIL 3 Protection against manipulation, prevention of unexpected start-up: SIL 3
Reliable component	Yes
Note on forced checking procedure	Switching frequency min. 1/month
Certificate issuing authority	BGIA 0904020
CE marking (see declaration of conformity)	To EC Machinery Directive To EU EMC Directive
Shock resistance	Shock test with severity level 2 according to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

Note on forced checking procedure: Switching frequency min. 1/month

The mechanical system is not tested in the controlled (i.e. pressurised)

state. If the process-related switching frequency (safe venting) is less than

once a month, the machine operator must carry out a forced switch-off.

Soft-start and exhaust valves MS6-SV, MS series

Technical data

FESTO

General technical data	
Pneumatic connection 1, 2	G1/2
Pneumatic connection 3	G1
Type of actuation	Electrical
Design	Piston seat
Type of mounting	Via accessories In-line installation
Mounting position	Any
Pressure display	Via pressure sensor for displaying output pressure via LCD display and electrical output Via pressure gauge for displaying output pressure G1/4 prepared
Position sensing principle	Solenoid piston principle
Valve function	3/2-way valve, single solenoid, closed Soft-start function
Freedom from overlap	No
Exhaust function	Without flow control
Manual override	None
Reset method	Mechanical spring
Switching position display	LED and floating contact
Type of control	Piloted
Pilot air supply	Internal
Sealing principle	Soft
C value	[l/(s*bar)] 19.3
b value	0.21

 Note: This product conforms to ISO 1179-1 and to ISO 228-1

Standard nominal flow rate $q_{nN}^1)$ [l/min]	
In main flow direction 1 → 2	4,300
In relief direction 2 → 3	9,000 ²⁾

1) Measured at $p_1 = 6$ bar and $p_2 = 5$ bar, $\Delta p = 1$ bar

2) Measured with respect to atmosphere with silencer UOS-1

Electrical data	
Electrical connection	Sub-D, 9-pin
Nominal operating voltage [V DC]	24
Perm. voltage fluctuations [%]	±10
Duty cycle [%]	100
Max. switching frequency [Hz]	1
Response time off [ms]	40
Response time on [ms]	130
Degree of protection	IP65 with multi-pin plug socket NECA

Soft-start and exhaust valves MS6-SV, MS series

Technical data

Operating and environmental conditions		
Variant	Standard	Pressure sensor AD...
Operating pressure [bar]	3.5 ... 10	3.5 ... 10
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)	
Ambient temperature [°C]	-10 ... +50	0 ... +50
Temperature of medium [°C]	-10 ... +50	0 ... +50
Storage temperature [°C]	-10 ... +50	0 ... +50
Corrosion resistance class CRC ¹⁾	2	
Noise level [dB (A)]	75 (with silencer UOS-1)	
CE mark (see declaration of conformity)	To EU EMC Directive To EU Machinery Directive	
Fire protection classification to UL 94	V0-V2	
Certification	c UL us - Recognized (OL) C-Tick	

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.







Weights [g]	
Soft-start and exhaust valve	2,000
Soft-start and exhaust valve with silencer UOS-1	2,200

Materials	
Housing	Die-cast aluminium
Piston spool	High-alloy stainless steel
Seals	NBR
Note on materials	RoHS-compliant

Soft-start and exhaust valves MS6-SV, MS series

Technical data

FESTO


Multi-pin plug socket		Enable signals (EN1/EN2)	Example of connection
Description			
NECA-...-MP1	<ul style="list-style-type: none"> • Static enable signals (EN1 = 24 V, EN2 = 24 V). 		
NECA-...-MP3	<ul style="list-style-type: none"> • Static enable signals (EN1 = 0 V, EN2 = 24 V). • Static cross circuit monitoring possible. A cross circuit in lines EN1 and EN2 does not lead to inadvertent start-up of the valve. 		

Soft-start and exhaust valves MS6-SV, MS series

Technical data

Switching point

Pressure p as a function of time t




Note

The tolerance specification +20%/-10% of the switching point refers to the operating pressure p_1 . Example: at an operating pressure of 4 bar a switching point of 1.6 bar to 2.8 bar is permitted.

Dimensions – Basic version

With female thread 1/2, with cover plate

Download CAD data → www.festo.com

- [1] Regulating screw for flow control valve
- [2] Silencer UOS-1
- [3] Multi-pin plug socket NECA
- [4] Dimension without cable

→ Flow direction

• Note: This product conforms to ISO 1179-1 and to ISO 228-1


Soft-start and exhaust valves MS6-SV, MS series

Technical data

FESTO


Dimensions – Pressure gauge/pressure gauge alternatives

Integrated MS pressure gauge AG, display unit [bar]



Download CAD data → www.festo.com


Adapter plate A4 for EN pressure gauge 1/4, without pressure gauge



Note: This product conforms to ISO 1179-1 and to ISO 228-1

Dimensions – Pressure gauge/pressure gauge alternatives

Pressure sensor with LCD display AD1 ... AD4



Download CAD data → www.festo.com

Technical data → Internet: [sde1](#)

AD1 variants:

SDE1-D10-G2-MS-L-P1-M8
with 3-pin plug M8x1,
1 switching output PNP

AD2 variants:

SDE1-D10-G2-MS-L-N1-M8
with 3-pin plug M8x1,
1 switching output NPN

AD3 variants:

SDE1-D10-G2-MS-L-PI-M12
with 4-pin plug M12x1,
1 switching output PNP
and 4 ... 20 mA analogue

AD4 variants:

SDE1-D10-G2-MS-L-NI-M12
with 4-pin plug M12x1,
1 switching output NPN
and 4 ... 20 mA analogue

Type	D1	L1
MS6-SV-...-AD1/AD2	M8x1	46.7
MS6-SV-...-AD3/AD4	M12x1	55.8

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Soft-start and exhaust valves MS6-SV, MS series

Technical data

Ordering data		Without silencer		With silencer	
Size	Connection	Part No.	Type	Part No.	Type
MS pressure gauge, display unit [bar]					
MS6	G1/2	548715	MS6-SV-1/2-E-10V24-AG	548717	MS6-SV-1/2-E-10V24-SO-AG
Pressure sensor with LCD display, M8 plug, PNP, 3-pin					
MS6	G1/2	562580	MS6-SV-1/2-E-10V24-AD1	-	-

Soft-start and exhaust valves MS6-SV, MS series

Ordering data – Modular products

FESTO

M Mandatory data →						
Module No.	Series	Size	Function	Pneumatic connection	Performance level	Supply voltage
548713	MS	6	SV	1/2, AGB, AGC, AGD, AGE	E	10V24
Order example	548713	MS	6	SV	AGB	E
						- 10V24 -

Ordering table		Conditions	Code	Enter code
Grid dimension	[mm]	62		
M Module No.	548713			
Series	Standard		MS	MS
Size	6		6	6
Function	Soft-start and exhaust valve		-SV	-SV
Pneumatic connection	Female thread G1/2		-1/2	
	Connecting plate G1/4		-AGB	
	Connecting plate G3/8		-AGC	
	Connecting plate G1/2		-AGD	
	Connecting plate G3/4		-AGE	
Performance level	Category 4 to EN ISO 13849-1, 2-channel with self-monitoring		-E	-E
Supply voltage	24 V DC (connection pattern to EN 175301), 10 bar		-10V24	-10V24

Transfer order code

548713 MS 6 SV E 10V24

Soft-start and exhaust valves MS6-SV, MS series

Ordering data – Modular products

→ Options

Silencer	Pressure gauge/ pressure gauge alternatives	Alternative pres- sure gauge scale	Multi-pin plug socket	Mounting type	UL certification	Flow direction
SO	AG, A4, AD1, AD2, AD3, AD4	PSI, MPA	MP1, MP3	WPB	UL1	Z
- SO -	- AG -	-	- MP1 -	- WPB -	-	-

Ordering table

Grid dimension [mm]	62	Conditions	Code	Enter code
<input type="checkbox"/> Silencer	Open silencer		-SO	
Pressure gauge/pressure gauge alternatives	MS pressure gauge		-AG	
	Adapter plate for EN pressure gauge 1/4, without pressure gauge		-A4	
	Pressure sensor with LCD display, plug M8, 1 switching output PNP, 3-pin		-AD1	
	Pressure sensor with LCD display, plug M8, 1 switching output NPN, 3-pin		-AD2	
	Pressure sensor with LCD display, plug M12, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA		-AD3	
	Pressure sensor with LCD display, plug M12, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA		-AD4	
Alternative pressure gauge scale	psi	[1]	-PSI	
	MPa	[1]	-MPA	
Multi-pin plug socket	Sub-D, 9-pin, screw terminal, without cable, enable signals static (EN1 = 24 V, EN2 = 24 V)		-MP1	
	Sub-D, 9-pin, screw terminal, without cable, enable signals static (EN1 = 0 V, EN2 = 24 V), short-circuit detection possible		-MP3	
Mounting type	Wall mounting plate, large clearance		-WPB	
UL certification	cULus, ordinary location for Canada and USA		-UL1	
Flow direction	Flow direction from right to left		-Z	

PSI, MPa Not with pressure gauge/pressure gauge alternatives A4, AD1, AD2, AD3, AD4

Transfer order code

- - - - - - -

Soft start and exhaust valves MS6-SV, MS series

Accessories

Multi-pin plug socket NECA

(order code: MP1/MP3)

- For soft start and exhaust valve
MS6-SV


Material:

Housing: Reinforced polyamide

Screws: Steel

Union nut: Brass

Seals: Nitrile rubber



Technical data

Type of mounting	Via through-holes
Electrical connection	Sub-D, 9-pin, screw terminal 9-pin
Operating voltage range [V DC]	21.6 ... 26.4
Nominal operating voltage [V DC]	24
Current-carrying capacity [A]	1.0
Connection cross section [mm ²]	0.34 ... 1.0 without wire end sleeves
	[mm ²] 0.34 ... 0.5 with wire end sleeves
Permissible cable diameter [mm]	5 ... 10
Protection class to IEC 60529	IP65

Operating and environmental conditions

Relative air humidity	95%, non-condensing
Ambient temperature [°C]	0 ... +50
Storage temperature [°C]	-20 ... +70
Corrosion resistance class CRC ¹⁾	2

1) Corrosion resistance class 2 to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Ordering data

Size	Connection	Weight [g]	Part No.	Type
MS6	Without cable, enable signals static (EN1 = 24 V, EN2 = 24 V)	60	548719	NECA-S1G9-P9-MP1
	Without cable, enable signals static (EN1 = 0 V, EN2 = 24 V), short-circuit detection possible	60	552703	NECA-S1G9-P9-MP3

Soft start and exhaust valves MS6-SV, MS series

Accessories


Silencer UOS-1

(order code: SO)

- For soft start and exhaust valve
MS6-SV

Materials:

Housing: Polyacetate
Sleeve: Wrought aluminium alloy
Silencer insert: Polyethylene
Free of copper and PTFE



Technical data

Pneumatic connection	G1
Design	Silencer, open
Type of mounting	Via male thread
Assembly position	Any
Type of seal on threaded collar	No seal

Operating and environmental conditions

Operating pressure [bar]	0 ... 10
Operating medium	Compressed air
Ambient temperature [°C]	-10 ... +50
Corrosion resistance class CRC ¹⁾	2

1) Corrosion resistance class 2 to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Ordering data

Size	Weight [g]	Part No.	Type
MS6	200	552252	UOS-1

On-off valves MS9-EM, MS series

Peripherals overview

FESTO



- - Note

Additional accessories:


- Module connector for combinations with size MS6, MS9 or size MS12

➔ Internet: rmv, armv

Mounting attachments and accessories	Individual component		Combination	➔ Page/Internet
	Without connecting thread	With connecting thread 3/4 or 1		
[1] Connecting plate MS9-AG...	■	-	■	ms9-ag
[2] Module connector MS9-MV	■	-	■	ms9-mv
[3] Mounting bracket MS9-WP	■	■	■	ms9-wp
[4] Mounting bracket MS9-WPB	■	■	■	ms9-wp
[5] Mounting bracket MS9-WPM	■	-	■	ms9-wp
[6] Silencer U	■	■	■	107
[7] Cover plate VS	■	■	■	70
[8] MS pressure gauge AG/RG	■	■	■	70
[9] Adapter plate for EN pressure gauge 1/4 A4	■	■	■	70
[10] Pressure gauge MA	■	■	■	107
[11] Padlock LRVS-D	■	■	■	107

On-off valves MS9-EM, MS series

Type codes




Additional variants can be ordered using the modular system → 70

- Pneumatic connection
- Silencer
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Valve function
- Type of mounting
- Flow direction

On-off valves MS9-EM, MS series


Technical data

2/2-way valve, double solenoid



-  - Flow rate
8,000 ... 18,000 l/min
-  - Temperature range
-10 ... +60 °C
-  - Operating pressure
0 ... 20 bar

3/2-way valve, double solenoid



- Manually operated on-off valve for pressurising and venting pneumatic installations
- Ducted exhaust possible via a threaded connection with silencer
- The switching position is immediately recognisable
- Actuator secured by locking the rotary knob
- Commercially available padlock can be used for security
- Optional pressure gauge

General technical data							
Pneumatic connection 1, 2	G3/4 (Female thread)	G1 (Female thread)	G1/2 ... G1½ (With connecting plate AG...)	– (Module without connecting thread, without connecting plate G)			
Pneumatic connection 3	G1						
Design	Piston spool valve						
Type of mounting	Via accessories In-line installation						
Mounting position	Any						
Regulator lock	Rotary knob with detent						
Pressure display	Via pressure gauge for displaying output pressure Via pressure gauge with red/green scale for displaying output pressure G1/4 prepared						
Valve function	2/2-way valve, double solenoid 3/2-way valve, double solenoid						
Exhaust air function	No flow control						
Reset method	Forced						
Type of control	Direct						
Sealing principle	Soft						

 Note: This product conforms to ISO 1179-1 and to ISO 228-1

On-off valves MS9-EM, MS series

Technical data

Flow rate characteristic values							
Pneumatic connection	Female thread		Connecting plate				
	G3/4	G1	AGD	AGE	AGF	AGG	AGH
Standard nominal flow rate q_{nN}^1 [l/min]							
In main flow direction 1 → 2	14,500	18,000	8,000	14,000	18,000	18,000	18,000
In relief direction 2 → 3	14,900	14,100	16,500	14,400	13,800	13,200	13,200
C value [l/s*min]							
In main flow direction 1 → 2	59.59	76.90	32.75	57.50	75.65	75.51	75.17
In relief direction 2 → 3	55.11	53.54	56.22	54.07	52.73	51.06	51.36
b value							
In main flow direction 1 → 2	0.41	0.37	0.45	0.39	0.38	0.39	0.38
In relief direction 2 → 3	0.50	0.48	0.60	0.49	0.47	0.45	0.44

1) Measured at $p_1 = 6$ bar and $p_2 = 5$ bar, $\Delta p = 1$ bar

Operating and environmental conditions

Operating pressure [bar]	0 ... 20
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)
Ambient temperature [°C]	-10 ... +60
Temperature of medium [°C]	-10 ... +60
Corrosion resistance class CRC ¹⁾	2
Noise level [dB (A)]	93 ²⁾ with silencer
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)
ATEX	Specified types → www.festo.com

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


2) Venting at 10 bar at a distance of 1 m.

Weight [g]

On-off valve	2,200
On-off valve with silencer S	2,400

Materials

Sectional view



On-off valve

[1] Housing	Die-cast aluminium
[2] Piston spool	POM
- Seals	NBR
Note on materials	RoHS-compliant

On-off valves MS9-EM, MS series


Technical data

FESTO

Dimensions – Basic version

Module without connecting thread, without connecting plate G, with cover plate VS

Download CAD data → www.festo.com




Type	B1	B2	B3	D5	L1	L2	L3		L6
							2/2-way valve	3/2-way valve	
MS9-EM-G	90	45	109	G1	242	159	30	23	189

Dimensions – Connecting thread/connecting plate

With female thread 3/4 or 1

Download CAD data → www.festo.com

With connecting plate AG...



Type	B4	B5	B6	B7	B8	D1	D6	D7	L4	T1	=C
MS9-EM-3/4	90	104	91.5	–	–	G3/4	11	6.5	66	6	–
MS9-EM-1						G1					
MS9-EM-AGD	–	–	–	112	132	G1/2	–	–	–	–	30
MS9-EM-AGE	–	–	–	112	132	G3/4	–	–	–	–	36
MS9-EM-AGF	–	–	–	112	142	G1	–	–	–	–	41
MS9-EM-AGG	–	–	–	112	162	G1 1/4	–	–	–	–	50
MS9-EM-AGH	–	–	–	112	176	G1 1/2	–	–	–	–	55

On-off valves MS9-EM, MS series


Technical data

Dimensions – Pressure gauge/pressure gauge alternatives

Integrated MS pressure gauge with standard scale AG or red/green scale RG

Download CAD data → www.festo.com

Adapter plate A4 for EN pressure gauge 1/4, without pressure gauge



Type	B2	B3	B9	D2
MS9-EM-...-AG/RG	45	109	–	–
MS9-EM-...-A4	–	–	110	G1/4

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data

3/2-way valve, with silencer

Size	Connection	Part No.	Type
MS9	–	562952	MS9-EM-G-S-VS

On-off valves MS9-EM, MS series

Ordering data – Modular products

M Mandatory data →			
Module No.	Series	Size	Function
562178	MS	9	EM
Ordering example			
562178	MS	9	- EM
			- G

Ordering table		Cond-	Code	Enter
Grid dimension	[mm]	tions		code
562178	90			
Module No.	562178			
Series	Standard		MS	
Size	9		9	
Function	Manual on-off valve		-EM	
Pneumatic connection	Female thread G $\frac{3}{4}$		- $\frac{3}{4}$	
	Female thread G1		-1	
	Connecting plate G $\frac{1}{2}$		-AGD	
	Connecting plate G $\frac{3}{4}$		-AGE	
	Connecting plate G1		-AGF	
	Connecting plate G $1\frac{1}{4}$		-AGG	
	Connecting plate G $1\frac{1}{2}$		-AGH	
	Module without connecting thread, without connecting plate		-G	

Transfer order code

562178 - MS - 9 - EM -

On-off valves MS9-EM, MS series

Ordering data – Modular products

→ Options	M Mandatory data	Options
Silencer	Pressure gauge/ pressure gauge alter- natives	Alternative pressure gauge scale
S	AG, VS, A4, RG	PSI, MPA, BAR
- S	- AG	- BAR

Ordering table						
Grid dimension	[mm]	90		Condi- tions	Code	Enter code
<input type="checkbox"/> Silencer	Silencer				-S	
<input type="checkbox"/> Pressure gauge/pressure gauge alternatives	MS pressure gauge Cover plate Adapter plate for EN pressure gauge 1/4, without pressure gauge Integrated pressure gauge, red/green scale				-AG -VS -A4 [1] -RG	
<input type="checkbox"/> Alternative pressure gauge scale	Psi MPa Bar				[2] -PSI [2] -MPA [2] -BAR	
<input type="checkbox"/> Valve function	Standard (3/2-way valve) 2/2-way valve				- [3] -2	
<input type="checkbox"/> Type of mounting	Mounting bracket Mounting bracket Mounting bracket for large wall gap				[4] -WP [4] -WPM [4] -WPB	
<input type="checkbox"/> Flow direction	Flow direction from right to left				-Z	

- [1] RG** Not with alternative pressure gauge scale PSI
 PSI scale serves only as an auxiliary scale
[2] PSI, MPA, BAR Not with pressure gauge/pressure gauge alternatives VS, A4

- [3] 2** Not with silencer S
[4] WP, WPM, WPB Not with module G


Transfer order code

- - - - - -

On-off valves MS9-EE, MS series

Peripherals overview

FESTO



- - Note


Additional accessories:

- Module connector for combinations with size MS6, MS9 or size MS12

➔ Internet: rmv, armv

Supply voltage
V24/V110/V230

Supply voltage
V24P



On-off valves MS9-EE, MS series


Peripherals overview

Mounting attachments and accessories	Individual component		Combination	➔ Page/Internet
	Without connecting thread	With connecting thread ¾ or 1		
[1] Connecting plate MS9-AG...	■	-	■	ms9-ag
[2] Module connector MS9-MV	■	-	■	ms9-mv
[3] Mounting bracket MS9-WP	■	■	■	ms9-wp
[4] Mounting bracket MS9-WPB	■	■	■	ms9-wp
[5] Mounting bracket MS9-WPM	■	-	■	ms9-wp
[6] Silencer U	■	■	■	107
[7] Cover plate VS	■	■	■	80
[8] MS pressure gauge AG/RG	■	■	■	80
[9] Adapter plate for EN pressure gauge ¼ A4	■	■	■	80
[10] Pressure gauge MA	■	■	■	107
[11] Illuminating seal MC-LD	■	■	■	106
[12] Plug socket with cable KMC	■	■	■	106
[13] Plug socket MSSD-C	■	■	■	106
[14] Connecting cable NEBU-M12G5	■	■	■	107
[15] Connecting cable NEBU-M12W5	■	■	■	107
[16] Sensor socket SIE-GD	■	■	■	107
[17] Angled plug socket SIE-WD	■	■	■	107

On-off valves MS9-EE, MS series

Type codes

FESTO




Additional variants can be ordered using the modular system → 80

- Pneumatic connection
- Supply voltage
- Silencer
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Valve function
- Type of mounting
- Flow direction

On-off valves MS9-EE, MS series

Technical data

2/2-way valve, single solenoid, closed




- - Flow rate
8,000 ... 18,000 l/min

- - Temperature range
-10 ... +60 °C

- - Operating pressure
3.5 ... 16 bar

3/2-way valve, single solenoid, closed



- Solenoid actuated on-off valve for pressurising and venting pneumatic installations
- Ducted exhaust possible via a threaded connection with silencer

- With solenoid coil without plug socket
- 3 voltage ranges can be selected
- Non-detenting or detenting manual override

- Optional pressure gauge

General technical data

Pneumatic connection 1, 2	G3/4 (Female thread)	G1 (Female thread)	G1/2 ... G1½ (With connecting plate AG...)	– (Module without connecting thread, without connecting plate G)
Pneumatic connection 3	G1			
Design	Piston spool valve			
Type of mounting	Via accessories			
	In-line installation			
Mounting position	Any			
Pressure display	Via pressure gauge for displaying output pressure			
	Via pressure gauge with red/green scale for displaying output pressure			
	G1/4 prepared			
Valve function	2/2-way valve, single solenoid, closed			
	3/2-way valve, single solenoid, closed			
Exhaust air function	No flow control			
Reset method	Mechanical spring			
Type of control	Piloted			
Pilot air supply	Internal			
Sealing principle	Soft			

- Note: This product conforms to ISO 1179-1 and to ISO 228-1

Electrical data

Coil characteristics	V24/V24P	24 V DC: 4.5 W; perm. voltage fluctuations ±10%
	V110	110 V AC: 50 Hz; pick-up power 11.5 W; holding power 8.9 W; perm. voltage fluctuations ±10%
		110 V AC: 60 Hz; pick-up power 9.5 W; holding power 6.2 W; perm. voltage fluctuations ±10%
	V230	230 V AC: 50 Hz; pick-up power 11.5 W; holding power 9.1 W; perm. voltage fluctuations ±10%
		230 V AC: 60 Hz; pick-up power 9.5 W; holding power 6.4 W; perm. voltage fluctuations ±10%
Electrical connection	V24/V110/V230	Plug socket, square design to EN 175301-803, type A
	V24P	Plug M12, 4-pin to DESINA
Protection class for solenoid coil		IP65
Duty cycle [%]		100

On-off valves MS9-EE, MS series

Technical data

Flow rate characteristic values								
Pneumatic connection	Female thread		Connecting plate					None G
	G3/4	G1	AGD	AGE	AGF	AGG	AGH	
Standard nominal flow rate $q_{nN}^1)$ [l/min]								
In main flow direction 1 → 2	14,500	18,000	8,000	14,000	18,000	18,000	18,000	18,000
In relief direction 2 → 3	14,900	14,100	16,500	14,400	13,800	13,200	13,200	14,100
C value [l/s*min]								
In main flow direction 1 → 2	59.59	76.90	32.75	57.50	75.65	75.51	75.17	-
In relief direction 2 → 3	55.11	53.54	56.22	54.07	52.73	51.06	51.36	-
b value								
In main flow direction 1 → 2	0.41	0.37	0.45	0.39	0.38	0.39	0.38	-
In relief direction 2 → 3	0.50	0.48	0.60	0.49	0.47	0.45	0.44	-


1) Measured at $p_1 = 6$ bar and $p_2 = 5$ bar, $\Delta p = 1$ bar

Operating and environmental conditions	
Operating pressure [bar]	3.5 ... 16
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)
Ambient temperature [°C]	-10 ... +60
Temperature of medium [°C]	-10 ... +60
Corrosion resistance class CRC ¹⁾	2
Noise level [dB (A)]	93 ²⁾ with silencer
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)
ATEX	Specified types → www.festo.com

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 2) Venting at 10 bar at a distance of 1 m.

Weight [g]	
On-off valve	2,100
On-off valve with silencer S	2,300

Materials
Sectional view



On-off valve	
[1] Housing	Die-cast aluminium
[2] Piston spool	POM
- Seals	NBR
Note on materials	RoHS-compliant


On-off valves MS9-EE, MS series

Technical data

Dimensions – Basic version

Module without connecting thread, without connecting plate G, with cover plate VS

Download CAD data → www.festo.com



Type	B1	B2	B3	D2	D5	L1	L2	L3		L4	L5	L6
								2/2-way valve	3/2-way valve			
MS9-EE-G-V24/V110/V230	90	45	109	–	G1	161	83	30	23	36	12	189
MS9-EE-G-V24P				M12x1						39	10	


On-off valves MS9-EE, MS series

Technical data


FESTO

Dimensions – Connecting thread/connecting plate

With female thread $\frac{3}{4}$ or 1



With connecting plate AG...



[1] Mounting screw M6xmin.90 to DIN 912 (not included in the scope of delivery) for wall mounting without mounting bracket

→ Flow direction

Type	B4	B5	B6	B7	B8	D1	D6	D7	L6	T1	=C
MS9-EE-3/4	90	104	91.5	–	–	G3/4	11	6.5	66	6	–
MS9-EE-1						G1					
MS9-EE-AGD	–	–	–	112	132	G1/2	–	–	–	–	30
MS9-EE-AGE					132	G3/4					36
MS9-EE-AGF					142	G1					41
MS9-EE-AGG					162	G1 1/4					50
MS9-EE-AGH					176	G1 1/2					55

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

On-off valves MS9-EE, MS series


Technical data

Dimensions – Pressure gauge/pressure gauge alternatives

Integrated MS pressure gauge with standard scale AG or red/green scale RG

Download CAD data → www.festo.com

Adapter plate A4 for EN pressure gauge 1/4, without pressure gauge



Type	B2	B3	B9	D3
MS9-EE-...-AG/RG	45	109	–	–
MS9-EE-...-A4	–	–	110	G ¹ / ₄

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data

3/2-way valve, with silencer, supply voltage 24 V DC

Size	Connection	Part No.	Type
MS9	–	562940	MS9-EE-G-V24-S-VS

On-off valves MS9-EE, MS series

Ordering data – Modular products

M Mandatory data →					
Module No.	Series	Size	Function	Pneumatic connection	Supply voltage
562177	MS	9	EE	3/4, 1, AGD, AGE, AGF, AGG, AGH, G	V24, V24P, V110, V230
Ordering example	562177	MS	9	- EE	- 1 - V24

Ordering table		Cond- itions	Code	Enter code
Grid dimension	[mm]	90		
M Module No.	562177			
Series	Standard		MS	
Size	9		9	
Function	Electrical on-off valve		-EE	
Pneumatic connection	Female thread G3/4		-3/4	
	Female thread G1		-1	
	Connecting plate G1/2		-AGD	
	Connecting plate G3/4		-AGE	
	Connecting plate G1		-AGF	
	Connecting plate G1 1/4		-AGG	
	Connecting plate G1 1/2		-AGH	
	Module without connecting thread, without connecting plate		-G	
Supply voltage	24 V DC (pin allocation to EN 175301), 16 bar		V24	
	24 V DC plug (connection pattern M12 to DESINA), 16 bar		V24P	
	110 V AC (pin allocation to EN 175301), 16 bar		V110	
	230 V AC (pin allocation to EN 175301), 16 bar		V230	

Transfer order code

562177 **MS** **9** **- EE** **-** **-**

On-off valves MS9-EE, MS series

Ordering data – Modular products

→ Options	M Mandatory data	Options
Silencer	Pressure gauge/ pressure gauge alternatives	Alternative pressure gauge scale
S	AG, VS, A4, RG	PSI, MPA, BAR
- S	- AG	- BAR

Ordering table						
Grid dimension	[mm]	90		Condi-	Code	Enter
Conditions				tions	Code	code
<input type="checkbox"/> Silencer	Silencer				-S	
<input type="checkbox"/> Pressure gauge/pressure gauge alternatives	MS pressure gauge				-AG	
	Cover plate				-VS	
	Adapter plate for EN pressure gauge 1/4, without pressure gauge				-A4	
	Integrated pressure gauge, red/green scale		[1]		-RG	
<input type="checkbox"/> Alternative pressure gauge scale	Psi		[2]		-PSI	
	MPa		[2]		-MPA	
	Bar		[2]		-BAR	
<input type="checkbox"/> Valve function	Standard (3/2-way valve)				-	
	2/2-way valve		[3]		-2	
<input type="checkbox"/> Type of mounting	Mounting bracket		[4]		-WP	
	Mounting bracket		[4]		-WPM	
	Mounting bracket for large wall gap		[4]		-WPB	
<input type="checkbox"/> Flow direction	Flow direction from right to left				-Z	

- [1] RG** Not with alternative pressure gauge scale PSI
 PSI scale serves only as an auxiliary scale
[2] PSI, MPA, BAR Not with pressure gauge/pressure gauge alternatives VS, A4

- [3] 2** Not with silencer S
[4] WP, WPM, WPB Not with module G

Transfer order code


- - - - -

On-off valves MS12-EM, MS series

Peripherals overview

FESTO

On-off valves MS12-EM



- - Note

Additional accessories:

- Module connector for combination with size MS9 → Internet: armv

Mounting attachments and accessories

	→ Page/Internet
[1] Connecting plate MS12-AG...	ms12-ag
[2] Mounting bracket MS12-WP	ms12-wp
[3] Module connector MS12-MV	ms12-mv
[4] Silencer U	107
[5] MS pressure gauge AG	87
[6] Adapter for EN pressure gauge 1/4 A4	87
[7] Pressure gauge MA	107
[8] Padlock LRVS-D	107

On-off valves MS12-EM, MS series

FESTO

Type codes

MS	12	-	EM	-	G
Series					
MS	Standard service unit				
Size					
12	Grid dimension 124 mm				
Service function					
EM	On-off valve, manually operated				
Pneumatic connection					
G	Module without connecting thread, without connecting plate Connecting plates → Accessories				


Further variants can be ordered using the modular system → 87

- Pneumatic connection
- Silencer
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Type of mounting
- Flow direction

On-off valves MS12-EM, MS series

Technical data

Function



- - Flow rate
25,000 ... 32,000 l/min
- - Temperature range
-10 ... +60 °C
- - Operating pressure
0 ... 20 bar



- Manually operated on-off valve for pressurising and venting pneumatic installations
- Ducted exhaust possible via a threaded connection with silencer
- The switching position is immediately recognisable
- Actuator secured by locking the rotary knob
- Commercially available padlock can be used for security

General technical data		
Pneumatic connection 1, 2	G1 ... G2 (With connecting plate AG...)	– (Module without connecting thread, without connecting plate G)
Pneumatic connection 3	G1	
Design	Piston spool valve	
Type of mounting	Via accessories In-line installation	
Assembly position	Any	
Valve function	3/2-way valve, double solenoid	
Exhaust function	Without flow control	
Switching position display	Knob actuator direction = flow direction	
Type of actuation	Direct	
Direction of flow	Non-reversible	

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Standard nominal flow rate q_{N1}^1) [l/min]	
In main flow direction 1 → 2	25,000 ... 32,000
In relief direction 2 → 3	13,000

1) Measured at $p_1 = 6$ bar and $\Delta p = 1$ bar

Operating and environmental conditions	
Operating pressure	[bar] 0 ... 20
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [-:-:-]
Ambient temperature	[°C] -10 ... +60
Temperature of medium	[°C] -10 ... +60
Corrosion resistance	CRC ¹⁾ 2

1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

On-off valves MS12-EM, MS series

FESTO


Technical data

Weights [g]

On-off valve	3,900
On-off valve with silencer S	4,000

Materials

Sectional view




On-off valve

[1] Body	Die-cast aluminium
[2] Cap, top	Aluminium
[3] Cap, bottom	Aluminium
[4] Valve spool	Stainless steel, POM, NBR
- Springs	Steel
- Covers/cover plates	PA
- Seals	NBR
- Connecting plate, module connector, mounting bracket	Die-cast aluminium
Note on materials	Free of copper and PTFE (not with variant AG)

Dimensions – Basic version

Module without connecting thread, without connecting plate G, with cover plate

Download CAD data → www.festo.com



Type	B1	B2	B3	B4	L1	L2	L3	D5
MS12-EM-G	124	122	61	148	255	148	228	G1


On-off valves MS12-EM, MS series

Technical data

FESTO

Dimensions – Silencer

Download CAD data → www.festo.com




Type	D2 ∅	L4
MS12-EM-....S	47.8	165.5

Dimensions – Pressure gauge/pressure gauge alternatives

Integrated MS pressure gauge AG, display unit [bar]

Download CAD data → www.festo.com

Adapter A4 for EN pressure gauge 1/4, without pressure gauge



Type	B3	B4	D4
MS12-EM-....AG	61	148	–
MS12-EM-....A4	61	148	G1/4

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data

Size	Connection	Part No.	Type
MS12	–	541495	MS12-EM-G1)

1) Free of copper and PTFE

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

On-off valves MS12-EM, MS series

FESTO

Ordering data – Modular products

M Mandatory data					O Options				
Module No.	Series	Size	Function	Pneumatic connection	Silencer	Pressure gauge/pressure gauge alternatives	Alternative pressure gauge scale	Type of mounting	Flow direction
535031	MS	12	EM	AGF, AGG, AGH, AGI, G	S	AG, A4	PSI, MPA	WP	Z
Order example					-	-	-	-	-
535031	MS	12	- EM	- G	- S	- AG	- PSI	-	- Z

Ordering table		Grid dimension [mm]	124	Conditions	Code	Enter code
M	Module No.	535031				
	Series	Standard			MS	MS
	Size	12			12	12
	Function	On-off valve, manual			-EM	-EM
	Pneumatic connection	Connecting plate G1 Connecting plate G1½ Connecting plate G1½ Connecting plate G2 Module without connecting thread, without connecting plate			-AGF -AGG -AGH -AGI -G	
O	Silencer	Silencer			-S	
	Pressure gauge/pressure gauge alternatives	MS pressure gauge, bar Adapter plate for EN pressure gauge ¼, without pressure gauge			-AG -A4	
	Alternative pressure gauge scale	psi MPa	[1]	[1]	-PSI -MPA	
	Type of mounting	Mounting bracket	[2]		-WP	
	Flow direction	Flow direction from right to left			-Z	

[1] PSI, MPA Only with pressure gauge AG.

[2] WP Only with connecting plate AGF, AGG, AGH or AGI.

Transfer order code


535031 MS 12 - EM - [] - [] - [] - [] - [] - [] - [] - []

On-off valves MS12-EE, MS series

Peripherals overview

FESTO

On-off valves MS12-EE



- - Note

Additional accessories:

- Module connector for combination with size MS9 → Internet: armv

Mounting attachments and accessories

→ Page/Internet

[1] Connecting plate MS12-AG...	ms12-ag
[2] Mounting bracket MS12-WP	ms12-wp
[3] Module connector MS12-MV	ms12-mv
[4] Silencer U	107
[5] MS pressure gauge AG	93
[6] Adapter for EN pressure gauge 1/4 A4	93
[7] Pressure gauge MA	107
[8] Illuminating seal MC-LD	106
[9] Plug socket with cable KMC	106
[10] Plug socket MSSD-C	106
[11] Connecting cable NEBU-M12...-LE4	107
[12] Manual override AHB-MD/MF/MV	106

On-off valves MS12-EE, MS series

FESTO

Type codes

MS	12	-	EE	-	G	-	V24
Series							
MS	Standard service unit						
Size							
12	Grid dimension 124 mm						
Service function							
EE	On-off valve, solenoid actuated						
Pneumatic connection							
G	Module without connecting thread, without connecting plate Connecting plates → Accessories						
Supply voltage							
V24	Supply voltage 24 V DC						

Further variants can be ordered using the modular system → 93


- Pneumatic connection
- Supply voltage
- Silencer
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Type of mounting
- Flow direction

On-off valves MS12-EE, MS series

Technical data

FESTO

Function



- 1 - Flow rate
25,000 ... 32,000 l/min
- 2 - Temperature range
-10 ... +50 °C
- 3 - Operating pressure
3 ... 16 bar



- Solenoid actuated on-off valve for pressurising and venting pneumatic installations
- With solenoid coil without plug socket
- Three voltage ranges can be selected
- Ducted exhaust possible via a threaded connection with silencer
- Non-detenting and detenting manual override

General technical data

Pneumatic connection 1, 2	G1 ... G2 (With connecting plate AG...)	– (Module without connecting thread, without connecting plate G)
Pneumatic connection 3	G1	
Design	Piston spool valve	
Type of mounting	Via accessories In-line installation	
Assembly position	Any	
Valve function	3/2-way valve, single solenoid, closed	
Exhaust function	Without flow control	
Type of reset	Mechanical spring	
Switching position display	Via accessories LED (with variant V24P)	
Type of actuation	Direct	
Pilot air supply	Internal	
Direction of flow	Non-reversible	

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Electrical data

Coil characteristics	V24/V24P	24 V DC: 4.5 W; perm. voltage fluctuations ±10%
	V110	110 V AC: 50 Hz; pick-up power 11.5 W; holding power 8.9 W; perm. voltage fluctuations ±10%
	V230	110 V AC: 60 Hz; pick-up power 9.5 W; holding power 6.2 W; perm. voltage fluctuations ±10%
Electrical connection	V24/V110/V230	230 V AC: 50 Hz; pick-up power 11.5 W; holding power 9.1 W; perm. voltage fluctuations ±10%
	V24P	230 V AC: 60 Hz; pick-up power 9.5 W; holding power 6.4 W; perm. voltage fluctuations ±10%
Protection class for solenoid coil	IP65	
Duty cycle	[%]	100

Standard nominal flow rate q_{nN}^1 [l/min]

In main flow direction 1 → 2	25,000 ... 32,000
In relief direction 2 → 3	8,900

1) Measured at $p_1 = 6$ bar and $\Delta p = 1$ bar

On-off valves MS12-EE, MS series

FESTO

Technical data

Operating and environmental conditions

Operating pressure [bar]	3 ... 16
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [-:-:-]
Ambient temperature [°C]	-10 ... +50
Temperature of medium [°C]	-10 ... +50
Corrosion resistance CRC ¹⁾	2

1) Corrosion resistance class 2 according to Festo standard 940 070


Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [g]

On-off valve	3,800
On-off valve with silencer S	3,900

Materials

Sectional view




On-off valve

[1] Body	Die-cast aluminium
[2] Cap, top	Aluminium
[3] Cap, bottom	Aluminium
[4] Valve spool	Stainless steel, POM, NBR
[5] Springs	Steel
- Covers/cover plates	PA
- Seals	NBR
- Connecting plate, module connector, mounting bracket	Die-cast aluminium
Note on materials	Free of copper and PTFE (not with variant AG)

Dimensions – Basic version

Module without connecting thread, without connecting plate G, with cover plate

Download CAD data → www.festo.com



Type	B1	B2	B3	B4	L1	L2	L3	L4	L5	D5
MS12-EE-G-V24/V110/V230	124	122	61	148	237	130	162	35.7	12.3	G1
MS12-EE-G-V24P								36	10	


On-off valves MS12-EE, MS series

Technical data

FESTO

Dimensions – Silencer

Download CAD data → www.festo.com




Type	D2 ∅	L4
MS12-EE-...-S	47.8	165.5

Dimensions – Pressure gauge/pressure gauge alternatives

Integrated MS pressure gauge AG, display unit [bar]

Download CAD data → www.festo.com

Adapter A4 for EN pressure gauge 1/4, without pressure gauge



Type	B3	B4	D4
MS12-EE-...-AG	61	148	–
MS12-EE-...-A4	61	148	G1/4

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data

Size	Connection	Supply voltage 24 V DC
Part No.	Type	
MS12	–	541496 MS12-EE-G-V24¹⁾

1) Free of copper and PTFE

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

On-off valves MS12-EE, MS series

FESTO

Ordering data – Modular products

M Mandatory data					O Options					
Module No.	Series	Size	Function	Pneumatic connection	Supply voltage	Silencer	Pressure gauge/pressure gauge alternatives	Alternative pressure gauge scale	Type of mounting	Flow direction
535032	MS	12	EE	AGF, AGG, AGH, AGI, G	V24, V24P, V110, V230	S	AG, A4	PSI, MPA	WP	Z
Order example	535032	MS	12	- EE	- AGI	- V110	- S	- AG	- MPA	- WP

Ordering table		Grid dimension [mm]	124	Conditions	Code	Enter code
M	Module No.	535032				
	Series	Standard			MS	MS
	Size	12			12	12
	Function	On-off valve, electrical			-EE	-EE
	Pneumatic connection	Connecting plate G1 Connecting plate G1½ Connecting plate G1½ Connecting plate G2 Module without connecting thread, without connecting plate			-AGF -AGG -AGH -AGI G	
	Supply voltage	24 V DC (connection pattern to EN 175301), 16 bar 24 V DC plug (connection pattern M12 to DESINA), 16 bar 110 V AC (connection pattern to EN 175301), 16 bar 230 V AC (connection pattern to EN 175301), 16 bar			-V24 -V24P -V110 -V230	
O	Silencer	Silencer			-S	
	Pressure gauge/pressure gauge alternatives	MS pressure gauge, bar Adapter plate for EN pressure gauge ¼, without pressure gauge			-AG -A4	
	Alternative pressure gauge scale	psi MPa		[1]	-PSI [1] -MPA	
	Type of mounting	Mounting bracket		[2]	-WP	
	Flow direction	Flow direction from right to left			-Z	

[1] PSI, MPa Only with pressure gauge AG.

[2] WP Only with connecting plate AGF, AGG, AGH or AGI.


Transfer order code

535032 MS 12 - EE - [] - [] - [] - [] - [] - [] - [] - []

Soft-start valves MS12-DL, MS series

Peripherals overview

Soft-start valves MS12-DL



Mounting attachments and accessories

	➔ Page/Internet
[1] Connecting plate MS12-AG...	ms12-ag
[2] Mounting bracket MS12-WP	ms12-wp
[3] Module connector MS12-MV	ms12-mv
[4] MS pressure gauge AG	99
[5] Adapter for EN pressure gauge 1/4 A4	99
[6] Pressure gauge MA	107

Soft-start valves MS12-DL, MS series

FESTO

Type codes

MS	12	-	DL	-	G
Series					
MS	Standard service unit				
Size					
12	Grid dimension 124 mm				
Service function					
DL	Soft-start valve, pneumatically actuated				
Pneumatic connection					
G	Module without connecting thread, without connecting plate Connecting plates → Accessories				

Further variants can be ordered using the modular system → 99


- Pneumatic connection
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Type of mounting
- Flow direction

Soft-start valves MS12-DL, MS series

Technical data

FESTO

Function



- - Flow rate
25,000 ... 42,000 l/min
- - Temperature range
-10 ... +60 °C
- - Operating pressure
2 ... 20 bar



The duration of the pressure build-up is adjusted using the restrictor attached to the valve cap.

The output pressure p₂ rises slowly in accordance with the restrictor setting. The main seat opens when the switch-through pressure is reached.

- Pneumatically actuated soft-start valve for slowly pressurising and venting pneumatic installations (for use with on-off valves EM and EE)
- The drives advance slowly and reliably into the initial position

- Sudden and erratic movements are avoided
- Pressure switching approx. 50% of operating pressure
- Adjustable switching time delay

General technical data

Pneumatic connection 1, 2	G1 ... G2 (With connecting plate AG...)	– (Module without connecting thread, without connecting plate G)
Design	Piston poppet valve	
Type of mounting	Via accessories In-line installation	
Assembly position	Any	
Valve function	2/2-way valve	
Exhaust function	Flow control	
Type of reset	Mechanical spring	
Type of actuation	Direct	
Pilot air supply	Internal	
Direction of flow	Non-reversible	

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Standard nominal flow rate q_N¹⁾ [l/min]

In main flow direction 1 → 2	25,000 ... 42,000
In relief direction 2 → 1	25,000 ... 42,000

1) Measured at p₁ = 6 bar and p₂ = 5 bar, Δp = 1 bar

Soft-start valves MS12-DL, MS series

FESTO

Technical data

Operating and environmental conditions

Operating pressure [bar]	2 ... 20
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:-:-]
Ambient temperature [°C]	-10 ... +60
Temperature of medium [°C]	-10 ... +60
Corrosion resistance CRC ¹⁾	2

1) Corrosion resistance class 2 according to Festo standard 940 070


Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [g]

Soft-start valve	3,600
------------------	-------

Materials


Sectional view



Soft-start valve

[1] Body	Die-cast aluminium
[2] Cap, top	Aluminium
[3] Cap, bottom	Aluminium
[4] Valve stem	Aluminium, NBR
[5] Springs	Steel
- Covers/cover plates	PA
- Seals	NBR
- Connecting plate, module connector, mounting bracket	Die-cast aluminium
Note on materials	Free of copper and PTFE (not with variant AG)

Switching point – Pressure p as a function of time t



Note

The tolerance specification
+25%/-20% of the switching point
refers to the operating pressure p1.

Example: at an operating pressure of
4 bar a switching point of 1.2 bar to
3.0 bar is permitted.

Soft-start valves MS12-DL, MS series


Technical data

FESTO

Dimensions – Basic version

Module without connecting thread, without connecting plate G, with cover plate

Download CAD data → www.festo.com




Type	B1	B2	B3	B4	L1	L2	L3
MS12-DL-G	124	122	61	148	178	82	162

Dimensions – Pressure gauge/pressure gauge alternatives

Integrated MS pressure gauge AG, display unit [bar]

Download CAD data → www.festo.com

Adapter A4 for EN pressure gauge 1/4, without pressure gauge



Type	B3	B4	D4
MS12-DL-...-AG	61	148	–
MS12-DL-...-A4	61	148	G1/4

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data

Size	Connection	Part No.	Type
MS12	–	541497	MS12-DL-G ¹⁾

1) Free of copper and PTFE

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Soft-start valves MS12-DL, MS series

FESTO

Ordering data – Modular products

M Mandatory data				O Options				
Module No.	Series	Size	Function	Pneumatic connection	Pressure gauge/pressure gauge alternatives	Alternative pressure gauge scale	Type of mounting	Flow direction
535033	MS	12	DL	AGF, AGG, AGH, AGI, G	AG, A4	PSI, MPA	WP	Z
Order example	535033	MS	12	- DL - AGI - AG - MPA - WP - Z				

Ordering table		Grid dimension [mm]	124	Conditions	Code	Enter code
M	Module No.	535033				
	Series	Standard			MS	MS
	Size	12			12	12
	Function	Soft-start valve, pneumatic			-DL	-DL
	Pneumatic connection	Connecting plate G1 Connecting plate G1½ Connecting plate G1½ Connecting plate G2 Module without connecting thread, without connecting plate			-AGF -AGG -AGH -AGI -G	
O	Pressure gauge/pressure gauge alternatives	MS pressure gauge, bar Adapter plate for EN pressure gauge ¼, without pressure gauge			-AG -A4	
	Alternative pressure gauge scale	psi MPa		[1]	-PSI -MPA	
	Type of mounting	Mounting bracket		[2]	-WP	
	Flow direction	Flow direction from right to left			-Z	

[1] PSI, MPa Only with pressure gauge AG.

[2] WP Only with connecting plate AGF, AGG, AGH or AGI.


Transfer order code

535033 MS 12 - DL - [] - [] - [] - [] - [] - []

Soft-start valves MS12-DE, MS series

Peripherals overview

Soft-start valves MS12-DE



- - Note

Additional accessories:

- Module connector for combination with size MS9 → Internet: armv

Mounting attachments and accessories

→ Page/Internet

[1] Connecting plate MS12-AG...	ms12-ag
[2] Mounting bracket MS12-WP	ms12-wp
[3] Module connector MS12-MV	ms12-mv
[4] MS pressure gauge AG	105
[5] Adapter for EN pressure gauge 1/4 A4	105
[6] Pressure gauge MA	107
[7] Illuminating seal MC-LD	106
[8] Plug socket with cable KMC	106
[9] Plug socket MSSD-C	106
[10] Connecting cable NEBU-M12...-LE4	107

Soft-start valves MS12-DE, MS series

FESTO

Type codes

MS	12	-	DE	-	G	-	V24
Series							
MS	Standard service unit						
Size							
12	Grid dimension 124 mm						
Service function							
DE	Soft-start valve, solenoid actuated						
Pneumatic connection							
G	Module without connecting thread, without connecting plate Connecting plates → Accessories						
Supply voltage							
V24	Supply voltage 24 V DC						

Further variants can be ordered using the modular system → 105


- Pneumatic connection
- Supply voltage
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Type of mounting
- Flow direction

Soft-start valves MS12-DE, MS series

Technical data

FESTO

Function



- - Flow rate
25,000 ... 42,000 l/min
- - Temperature range
-10 ... +50 °C
- - Operating pressure
3 ... 16 bar



The duration of the pressure build-up is adjusted using the restrictor attached to the valve cap. The output pressure p_2 rises slowly in accordance with the restrictor setting. Only the air flow from the restrictor is available when the solenoid valve is not actuated. The main seat is only opened by energising the solenoid valve.

When the solenoid valve is switched off, the main seat is closed and only the air flow from the flow control valve is available. The solenoid valve should remain switched on in order to vent a system as this increases the flow rate from 2 and 1 and reduces the exhaust time.

- Solenoid actuated soft-start valve for slowly pressurising and venting pneumatic installations
- The drives advance slowly and reliably into the initial position
- Sudden and erratic movements are avoided

- With solenoid coil without plug socket
- Switch-through pressure can be exactly controlled using a solenoid valve
- Adjustable switching time delay
- Three voltage ranges can be selected
- Non-detenting and detenting manual override

General technical data

Pneumatic connection 1, 2	G1 ... G2 (With connecting plate AG...)	– (Module without connecting thread, without connecting plate G)
Design	Piston poppet valve	
Type of mounting	Via accessories	
	In-line installation	
Assembly position	Any	
Valve function	2/2-way valve	
Exhaust function	Flow control	
Type of reset	Mechanical spring	
Switching position display	Via accessories	
	LED (with variant V24P)	
Type of actuation	Piloted	
Pilot air supply	Internal	
Direction of flow	Non-reversible	

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Electrical data

Coil characteristics	V24	24 V DC
	V24P	24 V DC
	V110	110 V AC
	V230	230 V AC
Electrical connection	V24/V110/V230	Plug, square design to EN 175301-803, type A
	V24P	Plug M12, 4-pin to DESINA
Protection class for solenoid coil		IP65
Duty cycle	[%]	100

Soft-start valves MS12-DE, MS series

FESTO

Technical data

Standard nominal flow rate $q_{nN}^1)$ [l/min]

In main flow direction 1 → 2	25,000 ... 42,000
In relief direction 2 → 1 ²⁾	25,000 ... 42,000

1) Measured at $p_1 = 6$ bar and $p_2 = 5$ bar, $\Delta p = 1$ bar

2) For energised solenoid valve

Operating and environmental conditions

Operating pressure [bar]	3 ... 16
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [-:-:-]
Ambient temperature [°C]	-10 ... +50
Temperature of medium [°C]	-10 ... +50
Corrosion resistance CRC ¹⁾	2

1) Corrosion resistance class 2 according to Festo standard 940 070


Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [g]

Soft-start valve	3,800
------------------	-------

Materials

Sectional view



Soft-start valve

[1] Body	Die-cast aluminium
[2] Cap, top	Aluminium
[3] Cap, bottom	Aluminium
[4] Valve stem	Aluminium, NBR
[5] Springs	Steel
- Covers/cover plates	PA
- Seals	NBR
- Connecting plate, module connector, mounting bracket	Die-cast aluminium
Note on materials	Free of copper and PTFE (not with variant AG)


Soft-start valves MS12-DE, MS series

Technical data

FESTO

Dimensions – Basic version


Module without connecting thread, without connecting plate G, with cover plate



Type	B1	B2	B3	B4	L1	L2	L3	L4	L5
MS12-DE-G-V24/V110/V230	124	122	61	148	226	130	162	35.7	12.3
MS12-DE-G-V24P								36	10

Dimensions – Pressure gauge/pressure gauge alternatives

Integrated MS pressure gauge AG, display unit [bar]



Type	B3	B4	D4
MS12-DE....AG	61	148	–
MS12-DE....A4	61	148	G1/4

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data

Size	Connection	Supply voltage 24 V DC
		Part No. Type
MS12	–	541498 MS12-DE-G-V24 ¹⁾

1) Free of copper and PTFE

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Soft-start valves MS12-DE, MS series

FESTO

Ordering data – Modular products

M Mandatory data					O Options				
Module No.	Series	Size	Function	Pneumatic connection	Supply voltage	Pressure gauge/pressure gauge alternatives	Alternative pressure gauge scale	Type of mounting	Flow direction
535034	MS	12	DE	AGF, AGG, AGH, AGI, G	V24, V24P, V110, V230	AG, A4	PSI, MPA	WP	Z
Order example					535034	MS	12	-DE	-AGH
					-V230	-A4		-WP	-Z

Ordering table

Grid dimension [mm]	124	Conditions	Code	Enter code
M Module No.	535034			
Series	Standard		MS	MS
Size	12		12	12
Function	Soft-start valve, electrical		-DE	-DE
Pneumatic connection	Connecting plate G1 Connecting plate G1½ Connecting plate G1½ Connecting plate G2 Module without connecting thread, without connecting plate		-AGF -AGG -AGH -AGI -G	
Supply voltage	24 V DC (connection pattern to EN 175301), 16 bar 24 V DC plug (connection pattern M12 to DESINA), 16 bar 110 V AC (connection pattern to EN 175301), 16 bar 230 V AC (connection pattern to EN 175301), 16 bar		-V24 -V24P -V110 -V230	
O Pressure gauge/pressure gauge alternatives	MS pressure gauge, bar Adapter plate for EN pressure gauge ¼, without pressure gauge		-AG -A4	
Alternative pressure gauge scale	psi MPa	[1]	-PSI -MPA	
Type of mounting	Mounting bracket	[2]	-WP	
Flow direction	Flow direction from right to left		-Z	

[1] **PSI, MPA** Only with pressure gauge AG.

[2] **WP**

Only with connecting plate AGF, AGG, AGH or AGI.

Transfer order code


535034 **MS** **12** **-DE** - - - - - - -

On-off/soft-start valves MS-EM/EE/DL/DE/SV, MS series

Accessories

FESTO

Ordering data – Plug socket MSSD					Technical data → Internet: mssd	
	Description	Electrical connection	Type of mounting cable connection	Part No.	Type	
	for MS4/6-EE/DE	–	3-pin	Clamping screws	151687	MSSD-EB
			4-pin	Insulation displacement technology	192745	MSSD-EB-S-M14
	For use in the explosion protection area	3-pin	Clamping screws	539712	MSSD-EB-M12	
	for MS9-EE, for MS12-EE/DE	–	3-pin	Clamping screws	34583	MSSD-C
			4-pin	Insulation displacement technology	192748	MSSD-C-S-M16

Ordering data – Plug socket with cable KMEB/KMC						Technical data → Internet: kmeb, kmc	
	Description	Operating voltage range	Electrical connection	Switching status display	Cable length [m]	Part No.	Type
	for MS4/6-EE/DE	24 V DC	2-pin	LED	2.5	547268	KMEB-3-24-2,5-LED
					5	547269	KMEB-3-24-5-LED
					2.5	547270	KMEB-3-24-2,5
					5	547271	KMEB-3-24-5
			3-pin	LED	2.5	151688	KMEB-1-24-2,5-LED
					5	151689	KMEB-1-24-5-LED
		230 V AC	3-pin	–	10	193457	KMEB-1-24-10-LED
					2.5	151690	KMEB-1-230AC-2,5
	for MS9-EE, for MS12-EE/DE	24 V DC	3-pin	LED	5	151691	KMEB-1-230AC-5
					2.5	30931	KMC-1-24DC-2,5-LED
					5	30933	KMC-1-24DC-5-LED
					10	193459	KMC-1-24-10-LED
					2.5	30932	KMC-1-230AC-2,5
					5	30934	KMC-1-230AC-5

Ordering data – Illuminating seal MEB-LD/MC-LD				Technical data → Internet: meb, mc	
	Description	Operating voltage range	Part No.	Type	
	for plug socket with cable KMEB and plug socket MSSD-EB	12 ... 24 V DC	151717	MEB-LD-12-24DC	
		230 V DC/AC ±10%	151718	MEB-LD-230AC	
	for plug socket with cable KMC and plug socket MSSD-C	12 ... 24 V DC	19145	MC-LD-12-24DC	
		230 V DC/AC ±10%	19146	MC-LD-230AC	

Ordering data – Locking clip CPV18-HV				Technical data → Internet: cpv18-hv	
	Description	Part No.	Type	PU ¹⁾	
	for MS4/6-EE/DE....V24	530056	CPV18-HV	10	

1) Packaging unit quantity

Ordering data – Manual override AHB-MD/MF/MV				Technical data → Internet: ahb	
	Description	Part No.	Type		
	for MS12-EE	157651	AHB-MD/MF/MV		

On-off/soft-start valves MS-EM/EE/DL/DE/SV, MS series

FESTO

Accessories

Ordering data – Connecting cable NEBU-M8					Technical data → Internet: nebu	
	Electrical connection	Number of wires	Cable length [m]	Part No.	Type	
	M8x1, straight socket	3	2.5	541333	NEBU-M8G3-K-2.5-LE3	
			5	541334	NEBU-M8G3-K-5-LE3	
	M8x1, angled socket	3	2.5	541338	NEBU-M8W3-K-2.5-LE3	
			5	541341	NEBU-M8W3-K-5-LE3	


Ordering data – Connecting cable NEBU-M12					Technical data → Internet: nebu	
	Electrical connection	Number of wires	Cable length [m]	Part No.	Type	
	M12x1, straight socket	4	2.5	550326	NEBU-M12G5-K-2.5-LE4	
			5	541328	NEBU-M12G5-K-5-LE4	
	M12x1, angled socket	4	2.5	550325	NEBU-M12W5-K-2.5-LE4	
			5	541329	NEBU-M12W5-K-5-LE4	

Ordering data – Sensor socket SIE-GD					Technical data → Internet: sie-gd	
	Electrical connection				Part No.	Type
	M12x1, 4-pin				18494	SIE-GD

Ordering data – Angled plug socket SIE-WD					Technical data → Internet: sie-wd	
	Electrical connection				Part No.	Type
	M12x1, 4-pin				12956	SIE-WD-TR

Ordering data – Silencer U					Technical data → Internet: u	
	Description	Pneumatic connection			Part No.	Type
	for MS4-EM1/EE	G1/4			6842	U-1/4-B
	for MS6-EM1/EE	G1/2			6844	U-1/2-B
	for MS9/12-EM/EE	G1			151990	U-1-B

Ordering data – Pressure gauge MA					Technical data → Internet: ma	
	Nominal size	Pneumatic connection	Indicating range		Part No.	Type
	Pressure gauge MA, EN 837-1					
	40	R1/4	0 ... 16	0 ... 232	187080	MA-40-16-R1/4-EN
			0 ... 25	0 ... 360	187081	MA-40-25-R1/4-EN
	40	G1/4	0 ... 16	0 ... 232	183901	MA-40-16-G1/4-EN
			0 ... 25	0 ... 360	183902	MA-40-25-G1/4-EN
Pressure gauge MA, EN 837-1, with red-green range					Technical data → Internet: ma	
	40	R1/8	0 ... 16	-	525726	MA-40-16-R1/8-E-RG
	50	R1/4	0 ... 16	-	525729	MA-50-16-R1/4-E-RG

Ordering data – Padlock LRV5-D						
	Weight [g]				Part No.	Type
	120				193786	LRVS-D