



Solenoid coils MSF/MSN1

Product range overview



Design	Type	For valve series										→ Page
		MFH	MOFH	JMFH	JMFDH	MFXMH	NVF3	MUFH	MN1H	JMN1H	JMN1DH	
F solenoid coil												
	MSF	■	■	■	■	■	■	■	—	—	—	2 / 7.1-3
F solenoid coil for explosive atmospheres (with ATEX certification)												
	MSF...-EX	■	■	■	■	■	■	■	—	—	—	2 / 7.1-5
N1 solenoid coil												
	MSN1 ¹⁾	—	—	—	—	—	—	—	■	■	■	2 / 7.1-8

1) Free of copper, PTFE and silicone



Note

ATEX certification is only effective in combination with other ATEX-certified components.

→ www.festo.com/en/ex

Solenoid coils MSF/MSN1

Selection aid

FESTO

Solenoid valves and corresponding solenoid coils													
Valve family	Valve type	Solenoid coil											
		D	E	EB	F	N1	N2	V	Y	Z	ZB	ZC	
ISO 15 407-1	MN2H, JMN2H, JMN2DH	-	-	-	-	-	■	-	-	-	-	-	-
ISO 5599-1	MN1H, JMN1H, JMN1DH	-	-	-	-	■	-	-	-	-	-	-	-
	MFH, JMFH, JMFDH	-	-	-	■	-	-	-	-	-	-	-	-
	MDH, JMDH	■	-	-	-	-	-	-	-	-	-	-	-
	MEBH, JMEBH, JMEBDH	-	-	■	-	-	-	-	-	-	-	-	-
Namur	NVF3, MFXMH	-	-	-	■	-	-	-	-	-	-	-	-
	MN1H	-	-	-	-	■	-	-	-	-	-	-	-
Compact Performance	CPE10-M1BH, CPE14-M1BH	-	-	-	-	-	-	-	-	-	-	-	■
	CPE18, CPE24	-	-	■	-	-	-	-	-	-	-	-	-
Tiger 2000	MFH, JMFH	-	-	-	■	-	-	-	-	-	-	-	-
	MVH, JMVH	-	-	-	-	-	-	■	-	-	-	-	-
Tiger Classic	MFH, MOFH, JMFH, JMFDH	-	-	-	■	-	-	-	-	-	-	-	-
Midi Pneumatic	MEBH, MOEBH, JMEBH	-	-	■	-	-	-	-	-	-	-	-	-
	MEH, MOEH, JMEH	-	■	-	-	-	-	-	-	-	-	-	-
Directly actuated solenoid valves	MZBH, MOZBH	-	-	-	-	-	-	-	-	-	■	-	-
	MEBH, MOEBH	-	-	■	-	-	-	-	-	-	-	-	-
	MVH, MOVH	-	-	-	-	-	-	■	-	-	-	-	-
	MDH, MODH	■	-	-	-	-	-	-	-	-	-	-	-
Fast-switching valves	MH2, MH3	-	-	-	-	-	-	-	-	-	-	-	■
Micro/Mini Pneumatic	MZH, MOZH, JMZH	-	-	-	-	-	-	-	-	■	-	-	-
	MYH, MOYH, JMYH	-	-	-	-	-	-	-	■	-	-	-	-
M5 Compact	MUFH	-	-	-	■	-	-	-	-	-	-	-	-

Type codes

		MSFG	—	24DC	—	OD
Type						
MSFG	F solenoid coil, for D.C. voltage					
MSFW	F solenoid coil, for A.C. voltage					
MSN1G	N1 solenoid coil, for D.C. voltage					
MSN1W	N1 solenoid coil, for A.C. voltage					
Operating voltage						
12DC	12 V DC					
24DC	24 V DC					
24AC/12DC	12 V DC/24 V AC					
24DC/42AC	24 V DC/42 V AC					
42DC	42 V DC					
24AC	24 V AC					
48AC	48 V AC					
110AC	110 V AC					
230AC	230 V AC					
240AC	240 V AC					
Scope of delivery						
OD	Without plug socket					

		MSFG	—	24DC	—	K5	—	M	—	EX
Type										
MSFG	F solenoid coil, for D.C. voltage									
MSPW	F solenoid coil, for A.C. voltage									
Operating voltage										
24	24 V DC									
24DC	24 V DC									
24AC	24 V AC									
24-50/60	24 V AC, 50/60 Hz									
110AC	110 V AC									
110-50/60	110 V AC, 50/60 Hz									
230AC	230 V AC									
230-50/60	230 V AC, 50/60 Hz									
Cable length										
	1 m									
K5	5 m									
KX	Upon request									
ATEX symbol										
	II 3 GD EEx nA II T1 30°C X									
M	II 2 GD EExm II T5									
Explosion protection										
EX	Explosion-proof to EN 50 028									


Solenoid coils MSF

Technical data

FESTO

-  - Voltage
12 ... 48 V DC
24 ... 240 V AC
-  - Temperature range
-5 ... +40 °C

- In compliance with VDE regulation 0580, insulation class F
- Can be replaced without interrupting the pneumatic circuit
- Low power consumption and temperature rise



General technical data		
	D.C. voltage	A.C. voltage
Min. pick-up time	[ms]	10
Type of mounting	Via knurled nut	
Mounting position	Any (can be rotated 360° on the armature tube)	
Product weight	[g]	65
Materials	Steel, copper, duroplastic	

Electrical data			
		D.C. voltage	A.C. voltage
Electrical connection		Plug vanes for plug sockets MSSD-F, KMF	
Operating voltage	D.C. voltage	[V DC]	12, 24, 42, 48
	A.C. voltage	[V AC]	24, 42, 48, 110, 230, 240
Perm. voltage fluctuation		[%]	±10
Coil characteristics	D.C. voltage 12 V	[W]	4.1
	24, 42, 48 V	[W]	4.5
	A.C. voltage	[VA]	Pull: 7.5 Hold: 6
Duty cycle		[%]	100
Power factor cosφ			0.7
Protection class to EN 60 529		IP65 with plug socket	
CE symbol			73/23/EEC (low voltage)

Operating and environmental conditions		
Ambient temperature	[°C]	-5 ... +40
Temperature of medium	[°C]	-10 ... +60


Solenoid coils MSF

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com/en/engineering



1 Retaining nut
(min. tightening
torque 100 Ncm,
max. 150 Ncm)

2 Solenoid coil
(can be rotated 360° on the
armature tube)
3 Plug vanes for plug sockets
MSSD-F, KMF




Note

Can only be operated on aluminium
valves with the following valve body
dimensions:
≥ 26 x 16 x 14 mm

Ordering data

	Description	Operating voltage		Part No.	Type
		V DC	V AC (50 ... 60 Hz)		
	Solenoid coil, without plug socket, with spring washer and knurled nut	12	–	34 410	MSFG-12DC-OD
		24	42	34 411	MSFG-24DC/42AC-OD
		42	–	34 413	MSFG-42DC-OD
		–	24	34 415	MSFW-24AC-OD
		–	48	34 418	MSFW-48AC-OD
		–	110	34 420	MSFW-110AC-OD
		–	230	34 422	MSFW-230AC-OD
		–	240	34 424	MSFW-240AC-OD

Ordering data – Accessories

	Description	Cable length [m]	Switching status display with LED	Part No.	Type
Plug socket					Technical data➔ 2 / 7.2-10
	–	–	–	34 431	MSSD-F
Plug socket with insulation displacement technology					Technical data➔ 2 / 7.2-10
	–	–	–	192 746	MSSD-F-S-M16
Plug socket with cable					Technical data➔ 2 / 7.3-24
	24 V DC	2.5	■	30 935	KMF-1-24DC-2,5-LED
		5	■	30 937	KMF-1-24DC-5-LED
		10	■	193 458	KMF-1-24DC-10-LED
	Up to 240 V	2.5	–	30 936	KMF-1-230AC-2,5
		5	–	30 938	KMF-1-230AC-5
Illuminating seal					Technical data➔ 2 / 7.4-1
	12 ... 24 V DC	–	■	19 143	MF-LD-12-24DC
	230 V DC/V AC	–	■	19 144	MF-LD-230AC
Inscription label					Technical data➔ 2 / 7.7-0
	Scope of delivery: 35 pieces in each frame	–	–	33 362	KMC/F/V-BZ-35X

Solenoid coils MSF...-EX



Technical data

FESTO

-  - Voltage
24 V DC
24 ... 240 V AC

-  - Temperature range
-5 ... +40 °C

- In compliance with ATEX directive
- In compliance with VDE regulation 0580, insulation class F
- With cable or plug
- Can be replaced without interrupting the pneumatic circuit
- Manifold mounting permissible (minimum clearance from coil to coil 5 mm)



General technical data			
		D.C. voltage	A.C. voltage
Min. pick-up time	[ms]	12	
Type of mounting		Via knurled nut	
Mounting position		Any (can be rotated 360° on the armature tube)	
Product weight	Cable version	[g]	175
	Plug version	[g]	65
Materials	Cable version		170
	Plug version		55
Materials		Steel, copper, aluminium, epoxy resin	
		Steel, copper, duroplastic	

Operating and environmental conditions			
ATEX ambient temperature	[°C]	-5 ... +40	
Ambient temperature	[°C]	-5 ... +40	
Temperature of medium	[°C]	-5 ... +40	

Electrical data – cable version			
		D.C. voltage	A.C. voltage
ATEX symbol		II 2 GD EEx m II T5	
Electrical connection		Moulded-in cable 3x0.75 mm², 1 m or 5 m long (other lengths upon request)	
Operating voltage	D.C. voltage	[V DC]	24
	A.C. voltage	[V AC]	–
Perm. voltage fluctuation			24, 110, 120, 220, 230, 240
		[%]	±10
Coil characteristics	D.C. voltage	24 V [W]	4.5
	A.C. voltage	24 V [VA]	–
			50 Hz, pull: 4.6 60 Hz, pull: 3.77
		110 V [VA]	–
			50 Hz, pull: 4.84 60 Hz, pull: 4.32
		230 V [VA]	–
			50 Hz, pull: 6.2 60 Hz, pull: 5.6
Duty cycle	[%]	100	
Min. pick-up time	[ms]	12	
Power factor cosφ		–	0.7
Protection class to EN 60 529		IP65	
CE symbol		94/9/EC (ATEX)	94/9/EC (ATEX) 73/23/EEC (low voltage)


Solenoid coils MSF...EX

Technical data

FESTO

Dimensions – cable version

Download CAD data → www.festo.com/en/engineering



- 1 Solenoid coil
(can be rotated 360° on the armature tube)
- 2 Protective earth connection
- 3 Heat resistant rubber tubing,
Ø 6,1 ... 7,9 mm
- 4 Retaining nut
(min. tightening torque 100 Ncm,
max. 150 Ncm)
- 5 Cable length

- - Note


Can only be operated on aluminium valves with the following valve body dimensions:
≥ 25 x 25 x 17 mm

Electrical data – plug version

				D.C. voltage	A.C. voltage
ATEX symbol				II 3 GD EEx nA II T130°C X	
Electrical connection				Plug vanes for plug sockets MSSD-F, KMF	
Operating voltage	D.C. voltage	[V DC]	24	–	
	A.C. voltage	[V AC]	–	24, 110, 120, 220, 230, 240	
Perm. voltage fluctuation			[%]	±10	
Coil characteristics	D.C. voltage	24 V	[W]	4.5	–
	A.C. voltage	24 V	[VA]	–	Pull: 7 Hold: 6
		110 V	[VA]	–	Pull: 7 Hold: 6
		230 V	[VA]	–	Pull: 7 Hold: 6
Duty cycle			[%]	100	
Min. pick-up time			[ms]	12	
Power factor cosφ				–	0.7
Protection class to EN 60 529				IP65 with plug socket	
CE symbol				94/9/EC (ATEX)	94/9/EC (ATEX) 73/23/EEC (lower voltage)

Dimensions – plug version

Download CAD data → www.festo.com/en/engineering



- 1 Retaining nut
(min. tightening torque 100 Ncm,
max. 150 Ncm)

- 2 Solenoid coil
(can be rotated 360° on the armature tube)
- 3 Plug vanes for plug sockets
MSSD-F, KMF



- - Note

Can only be operated on aluminium valves with the following valve body dimensions:
≥ 26 x 16 x 14 mm

Solenoid coils MSF...EX

Technical data

FESTO

Ordering data						
	Description	Operating voltage		Cable length [m]	Part No.	Type
		V DC	V AC			
ATEX symbol: II 2 GD EEx m II T5						
	Solenoid coil with cable, explosion-proof, moulded-in cable, with spring washer and knurled nut	24	–	1	535 619	MSFG-24DC-M-EX
		–	–	5	535 621	MSFG-24DC-K5-M-EX
		–	24	1	535 623	MSPW-24AC-M-EX
		–	110	1	535 622	MSPW-110AC-M-EX
		–		5	535 624	MSPW-110AC-K5-M-EX
		–	230	1	535 620	MSPW-230AC-M-EX
		–		5	535 625	MSPW-230AC-K5-M-EX
		24	–	Upon request	538 215	MSFG-24DC-KX-M-EX
		–	24		538 216	MSPW-24AC-KX-M-EX
		–	110		538 218	MSPW-110AC-KX-M-EX
		–	230		538 217	MSPW-230AC-KX-M-EX
ATEX symbol: II 3 GD EEx nA II T130°C X						
	Solenoid coil with plug vanes, explosion-proof, without plug socket, with spring washer and knurled nut	24	–	–	536 931	MSFG-24-EX
		–	24	–	536 932	MSPW-24-50/60-EX
		–	110	–	536 933	MSPW-110-50/60-EX
		–	230	–	536 934	MSPW-230-50/60-EX

Ordering data – Accessories					
	Description	Cable length [m]	Switching status display with LED	Part No.	Type
Plug socket					
Technical data → 2 / 7.2-10					
	–	–	–	34 431	MSSD-F

Solenoid coils MSN1

Technical data

FESTO

 Voltage
 24 V DC
 24 ... 230 V AC

 Temperature range
 -10 ... +50 °C

- In compliance with VDE regulation 0580, insulation class F
- Can be replaced without interrupting the pneumatic circuit
- Connection pattern to DIN EN 175 301-803, type A
- Free of copper, PTFE and silicone



General technical data		
Min. pick-up time	[ms]	10
Type of mounting		Via mounting clip
Mounting position		Any (can be rotated 360° on the armature tube)
Product weight	[g]	80
Materials		Steel, copper, thermoplastic
Note on materials		Free of copper, PTFE and silicone

Electrical data						
			D.C. voltage	D.C. voltage/ A.C. voltage	A.C. voltage	
Operating voltage	D.C. voltage	[V DC]	24	12	–	–
	A.C. voltage	[V AC]	–	24 (50 ... 60 Hz)	110 (50 ... 60 Hz), 120 (60 Hz)	230 (50 ... 60 Hz)
Perm. voltage fluctuation		[%]	–15 ... +10	50 Hz: ±10 60 Hz: -10 ... +20		±10
Coil characteristics	D.C. voltage	[W]	2.5	5	–	–
	A.C. voltage, 50 Hz	[VA]	–	Pull: 7.5 Hold: 5.0	Pull: 7.5 Hold: 5.0	Pull: 7.5 Hold: 5.0
	A.C. voltage, 60 Hz	[VA]	–	Pull: 5.0 Hold: 3.7	Pull: 5.0 Hold: 3.7	Pull: 5.0 Hold: 3.7
Duty cycle		[%]	100			
Power factor cosφ			–	–	0.7	
Electrical connection			Plug vanes with connection pattern to DIN EN 175 301-803, type A			
Protection class to EN 60 529			IP65 with plug socket			
CE symbol			–	–	73/23/EEC (low voltage)	

Ambient conditions		
Ambient temperature	[°C]	–10 ... +50
Temperature of medium	[°C]	–10 ... +50


Solenoid coils MSN1

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com/en/engineering





- 1 Solenoid coil
(can be rotated 360° on the
armature tube)
- 2 Securing clip

- 3 Plug vanes with connection
pattern to
DIN EN 175 301-803,
type A

Ordering data

	Description	Operating voltage		Part No.	Type
		V DC	V AC		
	Solenoid coil, without plug socket, with mounting clip, connection pattern to DIN EN 175 301-803, type A	24	–	123 060	MSN1G-24DC-OD
		12	24	170 152	MSN1W-24AC/12DC-OD
		–	110/120	123 061	MSN1W-110AC-OD
		–	230	123 062	MSN1W-230AC-OD

Ordering data – Accessories

Description		Cable length [m]	Switching status display with LED	Part No.	Type
Plug socket				Technical data ➔ 2 / 7.2-10	
	–	–	–	34 583	MSSD-C
Plug socket with insulation displacement technology				Technical data ➔ 2 / 7.2-10	
	–	–	–	192 748	MSSD-C-S-M16
Plug socket with cable				Technical data ➔ 2 / 7.3-24	
	24 V DC	2.5	■	30 931	KMC-1-24DC-2,5-LED
		5	■	30 933	KMC-1-24DC-5-LED
		10	■	193 459	KMC-1-24DC-10-LED
	Up to 240 V	2.5	–	30 932	KMC-1-230AC-2,5
		5	–	30 934	KMC-1-230AC-5
Illuminating seal				Technical data ➔ 2 / 7.4-1	
	12 ... 24 V DC	–	■	19 145	MC-LD-12-24DC
	230 V DC/V AC	–	■	19 146	MC-LD-230AC
Inscription label				Technical data ➔ 2 / 7.7-0	
	Scope of delivery: 35 pieces in each frame	–	–	33 362	KMC/F/V-BZ-35X