

Proportional media valves VZQA



Proportional media valves VZQA

Key features and overview

Function

The proportional media valve is a 2/2-way valve for controlling material flows. It is open in normal position. The shut-off element is a tubular pinch element made from


elastomer. When the valve is pressurised, the tubular pinch element closes and the material flow is tightly shut off. The valve opens when pressurisation stops

due to the internal stress of the pinch element or the pressure of the medium. The valve can be used to shut off liquid and dusty media, solids (granulates) as well as

mixtures of substances. The free passage when the valve is opened ensures minimum flow resistance and prevents the valve becoming blocked or clogged.

General

 G $\frac{1}{2}$


 Standard nominal flow rate
12,800 l/min


Application


- The valve can be used to shut off media as well as mixtures of substances

Design

- Easy-to-clean, cylindrical housing
- Normally open
- Pinch element made from elastomer

 Note
Pilot air connection 12: G $\frac{1}{8}$. Max. permissible thread length: 5 mm.

| Version | Type | Process valve connection | Nominal size (DN) | Process valve nominal pressure (PN) | → Page/Internet |
|--|------|--------------------------|-------------------|-------------------------------------|-----------------|
|  | VZQA | G $\frac{1}{2}$ | 15 | 10 | 4 |

 Note

The proportional media valve must only be used in systems where a damaged or leaking cartridge cannot pose a hazard to people or property. The media circuit must be sized for the set pilot pressure. The designer and operator of the system are responsible for the suitability of the product in combination with the respective system as well as for the resistance of the cartridge material to the medium used. Appropriate tests are generally required to assess the suitability. The risk of a leaking cartridge together with the associated consequences must be taken into consideration when planning the system.

Proportional media valves VZQA


Type codes


| | | | | | | | | | | | | | | | | | |
|----------------------------------|--|------|---|---|---|------|---|----|---|---|---|---|----|----|---|---|---|
| | | VZQA | - | C | - | M22U | - | 15 | - | G | G | - | V4 | V4 | N | - | 4 |
| Type | | | | | | | | | | | | | | | | | |
| VZQA | Proportional media valve, pneumatically actuated | | | | | | | | | | | | | | | | |
| Product version | | | | | | | | | | | | | | | | | |
| C | Easy-to-clean design | | | | | | | | | | | | | | | | |
| Valve function | | | | | | | | | | | | | | | | | |
| M22U | 2/2-way valve, normally open | | | | | | | | | | | | | | | | |
| Nominal size (DN) | | | | | | | | | | | | | | | | | |
| 15 | DN 15 | | | | | | | | | | | | | | | | |
| Connection type 1 | | | | | | | | | | | | | | | | | |
| G | G thread, female | | | | | | | | | | | | | | | | |
| Connection type 2 | | | | | | | | | | | | | | | | | |
| G | G thread, female | | | | | | | | | | | | | | | | |
| Housing material | | | | | | | | | | | | | | | | | |
| V4 | Stainless steel | | | | | | | | | | | | | | | | |
| Housing cover material | | | | | | | | | | | | | | | | | |
| V4 | Stainless steel | | | | | | | | | | | | | | | | |
| Shut-off element material | | | | | | | | | | | | | | | | | |
| N | NBR | | | | | | | | | | | | | | | | |
| E | EPDM | | | | | | | | | | | | | | | | |
| Pressure range of media | | | | | | | | | | | | | | | | | |
| 4 | 0 ... 4 bar | | | | | | | | | | | | | | | | |

Proportional media valves VZQA


Technical data

Function



 Standard nominal flow rate
12,800 l/min



 Connecting thread
G $\frac{1}{2}$

| General technical data | | |
|--------------------------|-------------------------------------|-------------|
| VZQA-... | ...-V4V4N-4 | ...-V4V4E-4 |
| Process valve connection | G $\frac{1}{2}$ | |
| Pilot air connection 1/2 | G $\frac{1}{8}$ | |
| Nominal size (DN) | 15 | |
| Valve function | 2/2-way, single solenoid, open | |
| Design | Pinch valve, pneumatically actuated | |
| Type of mounting | In-line installation | |
| Actuation type | Pneumatic | |
| Type of control | External | |
| Reset method | Rebound resilience | |
| Mounting position | Any | |
| Sealing principle | Soft | |
| Direction of flow | Reversible | |
| Max. viscosity | [mm ² /s] | 4,000 |
| Product weight | [g] | 440 |

| Operating and environmental conditions | | |
|--|---|--|
| VZQA-... | ...-V4V4N-4 | ...-V4V4E-4 |
| Process valve connection | G $\frac{1}{2}$ | |
| Switching time on | [ms] | 250 |
| Switching time off | [ms] | 250 |
| Standard nominal flow rate | [l/min] | 12,800 |
| Medium pressure | [bar] | 0 ... 4 |
| Process valve nominal pressure (PN) | 10 | |
| Overload pressure | [bar] | 7.8 |
| Pilot pressure | [bar] | 1 ... 6.5 |
| Differential pressure | [bar] | 2.5 |
| Medium | Compressed air to ISO 8573-1:2010 [-:-:-] | Compressed air to ISO 8573-1:2010 [-:-:1], water |
| Pilot medium | Compressed air to ISO 8573-1:2010 [7:4:4] | Compressed air to ISO 8573-1:2010 [7:4:1] |
| Ambient temperature | [°C] | -5 ... 60 |
| Temperature of medium | [°C] | -5 ... 60 |
| b value | 0.85 | |
| C value | [l/sbar] | 33.44 |
| Corrosion resistance class CRC ¹⁾ | 4 | |

1) Corrosion resistance class 4 according to Festo standard 940 070
Components subject to particularly high corrosion stress. Parts used with aggressive media, e.g. in the food or chemical industry. These applications should be supported with special tests with the media if required.

| Materials | | | |
|-----------|------------------------|----------------------------|-----------------|
| VZQA-... | ...-V4V4N-4 | ...-V4V4E-4 | Material number |
| 1 | Housing, housing cover | High-alloy stainless steel | 1.4435 |
| 2 | Seals | FPM | - |
| 3 | Shut-off element | NBR | EPDM |
| - | Note on materials | RoHS-compliant | - |


Proportional media valves VZQA

Technical data

FESTO


Dimensions

Download CAD data → www.festo.com



| | D1 | D2 | D3 | D4 | L1 | T1 | $\ominus 1$ | $\ominus 2$ |
|---------------------------|------|------|----|----|----|----|-------------|-------------|
| VZQA-C-M22U-15-GG-V4V4N-4 | G1/2 | G1/8 | 15 | 38 | 95 | 14 | 36 | 36 |
| VZQA-C-M22U-15-GG-V4V4E-4 | | | | | | | | |

Ordering data

| | Process valve connection | Part No. | Type |
|---|--------------------------|----------|---------------------------|
|  | G1/2 | 1387297 | VZQA-C-M22U-15-GG-V4V4N-4 |
| | | 1387298 | VZQA-C-M22U-15-GG-V4V4E-4 |

Note

The hermetic separation between the media circuit and pilot circuit is no longer guaranteed if wear causes the pinch element to leak. The flow medium can then get into the pilot circuit, from where it can escape.

Any potential hazard (e.g. due to aggressive or hot media) must be ruled out. The compressed air supply to the control valve must be protected against the ingress of the

flow medium using a suitable non-return valve or a suitable protection against return flow must be integrated in the pilot line in the immediate vicinity of the media valve.

Pilot medium can get into the media circuit if the pinch element fails. The media circuit must therefore be sized for the set pilot pressure. Any potential hazard must be ruled out.