


Compact cylinders ADNGF, standard port pattern

FESTO




Compact cylinders ADNGF, standard port pattern

Key features and type codes


FESTO

At a glance

With guide rod and yoke plate
ADNGF-...



With guide rod, yoke plate and through piston rod
ADNGF-...-S2



Cushioning types

	Cushioning P	Cushioning PPS
Mode of operation	The drive is equipped with polymer flexible end-position cushioning	The drive is equipped with self-adjusting, pneumatic end-position cushioning
Application	- Small loads - Low speeds - Small cushioning capacity	- Larger loads - Higher speeds - Larger cushioning capacity
Advantages	- No adjustment required - Time-saving	- No adjustment required - Up to four times greater cushioning capacity than ADNGF-...-P - Time-saving - Noise reduction


Type codes

		ADNGF	–	50	–	25	–	P	–	A	–	S6
Type												
Double-acting												
ADNGF	Compact cylinder											
Piston Ø [mm]												
Stroke [mm]												
Cushioning												
P	Flexible cushioning rings/pads at both ends											
PPS	Pneumatic cushioning, self-adjusting at both ends											
Position sensing												
A	Via proximity sensor											
Variant												
S2	Through piston rod											
S6	Heat-resistant seals up to max. 120 °C											
TL	Captive rating plate											

Compact cylinders ADNGF, standard port pattern

Peripherals overview

FESTO




Mounting attachments and accessories		
	Brief description	→ Page/Internet
1	Flange mounting FNC	For end caps
2	Swivel flange SNCL	For end caps
3	Swivel flange SNCB	For end caps
4	Multi-position kit DPNA	For connecting two cylinders with identical piston diameters to form a multi-position cylinder
5	Trunnion flange ZNCF/CRZNG	For end caps
6	Trunnion support LNZG	For trunnion flange ZNCF/CRZNG
7	Swivel flange SNCS	For end caps
8	Clevis foot LBG	For swivel flange SNCS
9	Proximity sensor SME/SMT-8	Can be integrated in the cylinder profile barrel
10	Proximity sensor SME/SMT-8M	Can be integrated in the cylinder profile barrel
11	Slot cover ABP-5-S	For protecting the sensor cable and keeping dirt out of the sensor slots
12	Proximity sensor SMPO-8E	Pneumatic output signal
13	Mounting kit SMB-8E	For proximity sensor SMPO-8E
14	One-way flow control valve GRLA/GRLZ	For regulating speed
15	Push-in fitting QS	For connecting compressed air tubing with standard O.D.
		quick star

Compact cylinders ADNGF, standard port pattern

FESTO

Technical data

Function



-N- Diameter
12 ... 100 mm

-T- Stroke length
1 ... 400 mm

Variants



S2



S6



General technical data											
Piston Ø	12	16	20	25	32	40	50	63	80	100	
Pneumatic connection	M5	M5	M5	M5	G¼	G¼	G¼	G¼	G¼	G¼	
Design	Piston										
	Piston rod										
	Cylinder barrel										
Mode of operation	Double-acting										
Cushioning											
P	Flexible cushioning rings/pads at both ends										
PPS	–				Pneumatic cushioning, self-adjusting at both ends					–	
Cushioning length											
PPS	[mm]				–	4	5	6	7	7.5	–
Position sensing	Via proximity sensor										
Type of mounting	Via through-hole										
	Via female thread										
	Via accessories										
Mounting position	Any										

Operating and environmental conditions										
Piston Ø	12	16	20	25	32	40	50	63	80	100
Operating medium	Filtered compressed air, lubricated or unlubricated									
Operating pressure [bar]										
–	1.5 ... 10			1 ... 10						
PPS	–				1.5 ... 10		1 ... 10			–
S2	1.5 ... 10				1 ... 10					
Ambient temperature ¹⁾ [°C]										
–	–20 ... +80									
S6	0 ... +120									
Corrosion resistance class CRC ²⁾	2									

1) Note operating range of proximity sensors

2) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weight [g]										
Piston Ø	12	16	20	25	32	40	50	63	80	100
Product weight with 0 mm stroke	90	93	161	191	327	430	687	915	1,678	2,673
Additional weight per 10 mm stroke	14	16	26	28	38	45	64	72	97	116
Moving load with 0 mm stroke	22	29	60	85	122	164	287	373	778	1,089
Additional load per 10 mm stroke	4	6	11	11	17	17	29	29	43	43

Compact cylinders ADNGF, standard port pattern

FESTO

Technical data

Forces [N] and impact energy [J]										
Piston Ø	12	16	20	25	32	40	50	63	80	100
Theoretical force at 6 bar, advancing										
–	68	121	188	295	483	754	1,178	1,870	3,016	4,712
S2	51	90	141	247	415	686	1,057	1,750	2,827	4,524
Theoretical force at 6 bar, retracting										
–	51	90	141	247	415	686	1,057	1,750	2,827	4,524
S2	51	90	141	247	415	686	1,057	1,750	2,827	4,524
Max. impact energy in the end positions										
–	0.07	0.15	0.2	0.3	0.4	0.7	1.0	1.3	1.8	2.5
S6	0.035	0.075	0.1	0.15	0.2	0.35	0.5	0.65	0.9	1.25


Note

In combination with PPS cushioning, the maximum impact energy is still obtained.

Max. energy conversion capacity [J]


Piston Ø	32	40	50	63	80
For PPS cushioning	1	1.7	2.8	4.8	8

Max. lateral force F_q as a function of projection x



—	Ø 12/16	- - - - -	Ø 40
- - - - -	Ø 20/25	- - - - -	Ø 50/63
- - - - -	Ø 32	- - - - -	Ø 80/100


Torque M as a function of stroke length l



—	Ø 12/16	- - - - -	Ø 50
- - - - -	Ø 20	- - - - -	Ø 63
- - - - -	Ø 25	- - - - -	Ø 80
- - - - -	Ø 32	- - - - -	Ø 100
- - - - -	Ø 40		

Materials

Sectional view



Compact cylinder	Basic version	S6
1 Bearing and end cap	Anodised aluminium	
2 Cylinder barrel	Anodised aluminium	
3 Piston rod	High-alloy steel	
4 Flange screws	Ø 12 ... 16	High-alloy steel
	Ø 20 ... 63	Galvanised steel
	Ø 80 ... 100	Standard screws, galvanised steel
– Seals	Polyurethane	Fluoro elastomer

Compact cylinders ADNGF, standard port pattern

FESTO

Technical data

Dimensions – Basic version


Download CAD Data → www.festo.com/us/cad

Ø 12 ... 63


Ø 32 ... 63

Ø 12 ... 25

Ø 12



Ø 80 ... 100



Ø	BG	D1 Ø	D4 Ø	D5 Ø	D6	D7 Ø	E	EE	FB Ø	G	J2	J3
[mm]	min.	H9		F9		H9			H8			
12	17	9	12	6	M3	–	27.5 +0.3	M5	3	10.5	2	–
16			14				29 +0.3			11	2.6	
20	19.5		17	M4	35.5 +0.3		4		12			
25			22	9	M5	14	39.5 +0.3	G1/8	5	15	6	
32	26		28			17	47 +0.3				8	
40			33		54.5 +0.3	11.5						
50	27	12	42	12	M6				22		75.5 +0.3	6
63			50			75.5 +0.3						
80	17		65	15	M8	24	95.5 +0.6		8	16.5		
100	21.5	80	M10		113.5 +0.6		10		21.5			

Ø [mm]	LA +0.2	ME	MM Ø h8	PL +0.2	RT	SF h13	T1	T2 +0.1	TG ±0.2	WH		ZA ±0.3	ZB	
										+1.3	PPS +1.4		+1.2	PPS +1.3
12	3.5	6	6	6	M4	5	–	2.1	16	4.2	–	35	39.2	–
16			8			7			18	4.7			39.7	
20		5	8		10	M5			9	5		22	5.5	
25	26			39			44.5							
32	10		12	8.2	M6	10	6	32.5	6	6.5	44	50	50.6	
40								38	6.1	6.6	45	51.1	51.7	
50	12		16		M8	13	7.5	46.5	7.7	8.2		52.7	53.2	
63								56.5	7.5	8	49	56.5	57	
80	2.6		14		20	M10	17	10.5	72	8.9	9.4	54	62.9	63.4
100		89		9					–	67	76	–		

Compact cylinders ADNGF, standard port pattern


Technical data

FESTO

Dimensions – Variant

Download CAD Data → www.festo.com/us/cad

S2 – Through piston rod



+ = plus stroke length
++ = plus 2x stroke length

Ø [mm]	AF min.	KF	T4	WH		ZM	
				+1.3	PPS +1.4		PPS
12	8	M3	1.5	4.2	–	44.5 ^{+0.5}	–
16	10	M4		4.7		45.7 ^{+0.5}	
20	14	M6	2.6	5.5	–	49.5 ^{+0.5}	–
25						51.5 ^{+0.5}	
32	16	M8	3.3	6	6.5	57.5 ^{+0.5}	58.6 ^{+0.6}
40				6.1	6.6	58.6 ^{+0.6}	59.7 ^{+0.7}
50	20	M10	4.7	8.2	8.2	62.0 ^{+0.6}	63.1 ^{+0.7}
63				8.1	8	65.4 ^{+0.6}	66.5 ^{+0.7}
80		M12	6.1	8.9	9.4	73.2 ^{+0.6}	74.3 ^{+0.7}
100				9	–	86.4 ^{+0.6}	–

Compact cylinders ADNGF, standard port pattern

Technical data

FESTO

Ordering data					
Type	Piston Ø [mm]	Stroke [mm] [mm]	P – Flexible cushioning rings/pads at both ends		PPS – Pneumatic cushioning, self-adjusting at both ends
			Part No.	Type	Part No. Type
	12	5	554205	ADNGF-12-5-P-A	–
		10	554206	ADNGF-12-10-P-A	
		15	554207	ADNGF-12-15-P-A	
		20	554208	ADNGF-12-20-P-A	
		25	554209	ADNGF-12-25-P-A	
		30	554210	ADNGF-12-30-P-A	
		40	554211	ADNGF-12-40-P-A	
	16	5	554212	ADNGF-16-5-P-A	–
		10	554213	ADNGF-16-10-P-A	
		15	554214	ADNGF-16-15-P-A	
		20	554215	ADNGF-16-20-P-A	
		25	554216	ADNGF-16-25-P-A	
		30	554217	ADNGF-16-30-P-A	
		40	554218	ADNGF-16-40-P-A	
		50	554219	ADNGF-16-50-P-A	
	20	5	554220	ADNGF-20-5-P-A	–
		10	554221	ADNGF-20-10-P-A	
		15	554222	ADNGF-20-15-P-A	
		20	554223	ADNGF-20-20-P-A	
		25	554224	ADNGF-20-25-P-A	
		30	554225	ADNGF-20-30-P-A	
		40	554226	ADNGF-20-40-P-A	
		50	554227	ADNGF-20-50-P-A	
		60	554228	ADNGF-20-60-P-A	
	25	5	554229	ADNGF-25-5-P-A	–
		10	554230	ADNGF-25-10-P-A	
		15	554231	ADNGF-25-15-P-A	
		20	554232	ADNGF-25-20-P-A	
		25	554233	ADNGF-25-25-P-A	
		30	554234	ADNGF-25-30-P-A	
		40	554235	ADNGF-25-40-P-A	
		50	554236	ADNGF-25-50-P-A	
		60	554237	ADNGF-25-60-P-A	
	32	5	554238	ADNGF-32-5-P-A	–
		10	554239	ADNGF-32-10-P-A	
		15	554240	ADNGF-32-15-P-A	
		20	554241	ADNGF-32-20-P-A	
		25	554242	ADNGF-32-25-P-A	
		30	554243	ADNGF-32-30-P-A	
		40	554244	ADNGF-32-40-P-A	
		50	554245	ADNGF-32-50-P-A	
		60	554246	ADNGF-32-60-P-A	
		80	554247	ADNGF-32-80-P-A	
					574022 ADNGF-32-10-PPS-A
					574023 ADNGF-32-15-PPS-A
					574024 ADNGF-32-20-PPS-A
					574025 ADNGF-32-25-PPS-A
					574026 ADNGF-32-30-PPS-A
					574027 ADNGF-32-40-PPS-A
					574028 ADNGF-32-50-PPS-A
					574029 ADNGF-32-60-PPS-A
					574030 ADNGF-32-80-PPS-A

Compact cylinders ADNGF, standard port pattern

Technical data

Ordering data					
Type	Piston Ø [mm]	Stroke [mm]	P – Flexible cushioning rings/pads at both ends		PPS – Pneumatic cushioning, self-adjusting at both ends
			Part No.	Type	Part No. Type
	40	5	554248	ADNGF-40-5-P-A	–
		10	554249	ADNGF-40-10-P-A	574031 ADNGF-40-10-PPS-A
		15	554250	ADNGF-40-15-P-A	574032 ADNGF-40-15-PPS-A
		20	554251	ADNGF-40-20-P-A	574033 ADNGF-40-20-PPS-A
		25	554252	ADNGF-40-25-P-A	574034 ADNGF-40-25-PPS-A
		30	554253	ADNGF-40-30-P-A	574035 ADNGF-40-30-PPS-A
		40	554254	ADNGF-40-40-P-A	574036 ADNGF-40-40-PPS-A
		50	554255	ADNGF-40-50-P-A	574037 ADNGF-40-50-PPS-A
		60	554256	ADNGF-40-60-P-A	574038 ADNGF-40-60-PPS-A
		80	554257	ADNGF-40-80-P-A	574039 ADNGF-40-80-PPS-A
	50	5	554258	ADNGF-50-5-P-A	–
		10	554259	ADNGF-50-10-P-A	574040 ADNGF-50-10-PPS-A
		15	554260	ADNGF-50-15-P-A	574041 ADNGF-50-15-PPS-A
		20	554261	ADNGF-50-20-P-A	574042 ADNGF-50-20-PPS-A
		25	554262	ADNGF-50-25-P-A	574043 ADNGF-50-25-PPS-A
		30	554263	ADNGF-50-30-P-A	574044 ADNGF-50-30-PPS-A
		40	554264	ADNGF-50-40-P-A	574045 ADNGF-50-40-PPS-A
		50	554265	ADNGF-50-50-P-A	574046 ADNGF-50-50-PPS-A
		60	554266	ADNGF-50-60-P-A	574047 ADNGF-50-60-PPS-A
		80	554267	ADNGF-50-80-P-A	574048 ADNGF-50-80-PPS-A
	63	10	554268	ADNGF-63-10-P-A	574049 ADNGF-63-10-PPS-A
		15	554269	ADNGF-63-15-P-A	574050 ADNGF-63-15-PPS-A
		20	554270	ADNGF-63-20-P-A	574051 ADNGF-63-20-PPS-A
		25	554271	ADNGF-63-25-P-A	574052 ADNGF-63-25-PPS-A
		30	554272	ADNGF-63-30-P-A	574053 ADNGF-63-30-PPS-A
		40	554273	ADNGF-63-40-P-A	574054 ADNGF-63-40-PPS-A
		50	554274	ADNGF-63-50-P-A	574055 ADNGF-63-50-PPS-A
		60	554275	ADNGF-63-60-P-A	574056 ADNGF-63-60-PPS-A
		80	554276	ADNGF-63-80-P-A	574057 ADNGF-63-80-PPS-A
	80	10	554277	ADNGF-80-10-P-A	574058 ADNGF-80-10-PPS-A
		15	554278	ADNGF-80-15-P-A	574059 ADNGF-80-15-PPS-A
		20	554279	ADNGF-80-20-P-A	574060 ADNGF-80-20-PPS-A
		25	554280	ADNGF-80-25-P-A	574061 ADNGF-80-25-PPS-A
		30	554281	ADNGF-80-30-P-A	574062 ADNGF-80-30-PPS-A
		40	554282	ADNGF-80-40-P-A	574063 ADNGF-80-40-PPS-A
		50	554283	ADNGF-80-50-P-A	574064 ADNGF-80-50-PPS-A
		60	554284	ADNGF-80-60-P-A	574065 ADNGF-80-60-PPS-A
		80	554285	ADNGF-80-80-P-A	574066 ADNGF-80-80-PPS-A
	100	10	554286	ADNGF-100-10-P-A	–
		15	554287	ADNGF-100-15-P-A	
		20	554288	ADNGF-100-20-P-A	
		25	554289	ADNGF-100-25-P-A	
		30	554290	ADNGF-100-30-P-A	
		40	554291	ADNGF-100-40-P-A	
		50	554292	ADNGF-100-50-P-A	
		60	554293	ADNGF-100-60-P-A	
		80	554294	ADNGF-100-80-P-A	

Compact cylinders ADNGF, standard port pattern

Ordering data – Modular products

FESTO

M Mandatory data						O Options		
Module No.	Function	Size	Stroke	Cushioning	Position sensing	Piston rod type	Temperature resistance	Captive rating plate
537 123	ADNGF	12	1 ... 400	P	A	S2		
537 124		16						
537 125		20						
537 126		25						
537 127		32						
537 128		40						
537 129		50						
537 130		63						
537 131		80						
537 132	100							
Ordering example								
537 128	ADNGF	- 40	- 250	- P	- A	- S2	- S6	- TL

Ordering table																
Size		12	16	20	25	32	40	50	63	80	100	Conditions	Code	Enter code		
M	Module No.	537 123	537 124	537 125	537 126	537 127	537 128	537 129	537 130	537 131	537 132					
	Function	Compact cylinder, double-acting, standard hole pattern											ADNGF		ADNGF	
	Size [mm]	12	16	20	25	32	40	50	63	80	100		-...			
	Stroke [mm]	1 ... 200			3 ... 200			5 ... 300			5 ... 400					-...
	Cushioning	Flexible cushioning rings/pads at both ends											-P			
						Pneumatic cushioning, self-adjusting at both ends					-	1	-PPS			
	Position sensing	Via proximity sensor											-A	-A		
O	Piston rod type	Through piston rod											-S2			
	Temperature resistance	Heat-resistant seals up to max. 120 °C										2	-S6			
	Captive rating plate	Laser etched rating plate											-TL			

[1] PPS Not with temperature resistance S6

[2] S6 Max. stroke: 250 mm

Transfer order code

	ADNGF	-		-		-	A	-		-		-	
--	-------	---	--	---	--	---	---	---	--	---	--	---	--

Compact cylinders ADNGF, standard port pattern

Accessories


FESTO

Flange mounting FNC

Material:

Galvanised steel

Free of copper, PTFE and silicone



Dimensions and ordering data											
For Ø	E	FB Ø	MF	R	TF	UF	ZF	CRC ¹⁾	Weight	Part No.	Type
[mm]						±1			[g]		
12	28	5.5	8	–	40	50	47.2	1	79	537 245	FNC-12
16	29				43	55	47.9	1	88	537 246	FNC-16
20	36	6.6			55	70	50.7	1	141	537 247	FNC-20
25	40				60	76	52.7	1	165	537 248	FNC-25
32	45	7	10	32	64	80	60.2	1	221	174 376	FNC-32
40	54	9		36	72	90	61.2	1	291	174 377	FNC-40
50	65		12	45	90	110	65.2	1	536	174 378	FNC-50
63	75			50	100	120	69.2	1	679	174 379	FNC-63
80	93	12	16	63	126	150	79	1	1,495	174 380	FNC-80
100	110	14		75	150	175	92	1	2,041	174 381	FNC-100

1) CRC1: Corrosion resistance class to Festo standard 940070

Components with light corrosion exposure. Protection for transport and storage. Components without significant decorative function or surface, e.g. installed out of sight internally or behind covers.

Compact cylinders ADNGF, standard port pattern

FESTO

Accessories


Swivel flange SNCL

Material:

SNCL: Die-cast aluminium

SNCL-...-R3: Die-cast aluminium with protective coating

Free of copper, PTFE and silicone



Dimensions and ordering data						
For Ø	CD	EW	FL	L	MR	XC
[mm]	Ø H9		±0.2			
12	6	12 _{h12}	16	10	6	56
16						
20	8	16 _{h12}	20	14	8	63
25						65
32	10	26 _{-0.2/-0.6}	22	13	10	72
40	12	28 _{-0.2/-0.6}	25	16	12	76
50		32 _{-0.2/-0.6}	27			80
63	16	40 _{-0.2/-0.6}	32	21	16	89
80		50 _{-0.2/-0.6}	36	22		99
100	20	60 _{-0.2/-0.6}	41	27	20	117

For Ø	Basic version				R3 – High corrosion protection			
	CRC ¹⁾	Weight [g]	Part No.	Type	CRC ¹⁾	Weight [g]	Part No.	Type
[mm]								
12	2	20	537 790	SNCL-12	3	20	537 794	SNCL-12-R3
16	2	25	537 791	SNCL-16	3	25	537 795	SNCL-16-R3
20	2	40	537 792	SNCL-20	3	40	537 796	SNCL-20-R3
25	2	45	537 793	SNCL-25	3	45	537 797	SNCL-25-R3
32	2	85	174 404	SNCL-32	–	–	–	–
40	2	115	174 405	SNCL-40	–	–	–	–
50	2	180	174 406	SNCL-50	–	–	–	–
63	2	270	174 407	SNCL-63	–	–	–	–
80	2	480	174 408	SNCL-80	–	–	–	–
100	2	700	174 409	SNCL-100	–	–	–	–

1) Corrosion resistance class 2 to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Corrosion resistance class 3 to Festo standard 940 070

Components requiring higher corrosion resistance. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface



Compact cylinders ADNGF, standard port pattern

FESTO

Accessories

Swivel flange SNCS

Material:
Die-cast aluminium



Dimensions and ordering data											
For Ø	CN	EP	EX	FL	LT	MS	XC	CRC ¹⁾	Weight	Part No.	Type
[mm]	Ø H7	±0.2		±0.2					[g]		
32	10	10.5	14	22	13	15	66	2	85	174 397	SNCS-32
40	12	12	16	25	16	17	70	2	125	174 398	SNCS-40
50	16	15	21	27	16	20	72	2	210	174 399	SNCS-50
63	16	15	21	32	21	22	81	2	280	174 400	SNCS-63
80	20	18	25	36	22	27	90	2	540	174 401	SNCS-80
100	20	18	25	41	27	29	108	2	700	174 402	SNCS-100


1) Corrosion resistance class 2 to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

Clevis foot LBG

The clevis foot is secured against rotation with a dowel pin.

Material:
Nodular graphite cast iron
Free of copper, PTFE and silicone



Dimensions and ordering data																		
For Ø	CL	CM	EK Ø	FL	GL	HB Ø	L2	LE	MR	RF	RG	S1 Ø	UK	UX	CRC ¹⁾	Weight	Part No.	Type
[mm]	±0.2															[g]		
32	28	14.1	10	32	16±0.25	6.8	35	24	12	42	20±0.3	4.8	56	36	2	220	31 761	LBG-32
40	30	16.1	12	36	20±0.3	6.8	39	26	14	44	26±0.3	5.8	58	41.5	2	300	31 762	LBG-40
50	40	21.1	16	45	25±0.3	9.2	50	33	15	56	31±0.4	5.8	70	47	2	540	31 763	LBG-50
63	40	21.1	16	50	25±0.3	9	50	38	17	56	31±0.4	7.8	70	45	2	580	31 764	LBG-63
80	50	25.1	20	63	30	11	60	49	18	70	36	7.8	89	55	2	1050	31 765	LBG-80
100	50	25.1	20	71	41	11	60	56	22	70	46	9.8	89	65	2	1375	31 766	LBG-100

1) Corrosion resistance class 2 to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

Compact cylinders ADNGF, standard port pattern

Accessories

FESTO


Multi-position kit DPNA

Material:

Flange: Aluminium

Screws: Galvanised steel

Free of copper, PTFE and silicone



Note

The maximum overall stroke length may not be exceeded when combining cylinders and multi-position kits.

Dimensions and ordering data						
For Ø	L2	B1	Max. overall stroke length	CRC ¹⁾	Part No.	Type
[mm]			[mm]			
12	35	13	600	2	537 263	DPNA-12
16			600	2	537 264	DPNA-16
20			600	2	537 265	DPNA-20
25	39		600	2	537 266	DPNA-25
32	44		800	2	537 267	DPNA-32
40	45	15	800	2	537 268	DPNA-40
50			800	2	537 269	DPNA-50
63	49		800	2	537 270	DPNA-63
80	54	17	1000	2	537 271	DPNA-80
100	67	19.5	1000	2	537 272	DPNA-100

1) Corrosion resistance class 2 to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents


Compact cylinders ADNGF, standard port pattern

FESTO

Accessories

Swivel flange SNCB/SNCB-...-R3

Material:
SNCB: Die-cast aluminium
SNCB-...-R3: Die-cast aluminium with
protective coating, high corrosion
protection
Free of copper, PTFE and silicone



Dimensions and ordering data							
For Ø	CB	EK	FL	L	MR	UB	XC
[mm]	H14	Ø e8	±0.2			h14	
32	26	10	22	13	8.5	45	72
40	28	12	25	16	12	52	76
50	32	12	27	16	12	60	80
63	40	16	32	21	16	70	89
80	50	16	36	22	16	90	99
100	60	20	41	27	20	110	117

For Ø [mm]	Basic version				R3 – High corrosion protection			
	CRC ¹⁾	Weight [g]	Part No.	Type	CRC ¹⁾	Weight [g]	Part No.	Type
32	2	100	174 390	SNCB-32	3	100	176 944	SNCB-32-R3
40	2	150	174 391	SNCB-40	3	150	176 945	SNCB-40-R3
50	2	225	174 392	SNCB-50	3	225	176 946	SNCB-50-R3
63	2	365	174 393	SNCB-63	3	365	176 947	SNCB-63-R3
80	2	610	174 394	SNCB-80	3	610	176 948	SNCB-80-R3
100	2	925	174 395	SNCB-100	3	925	176 949	SNCB-100-R3

- 1) Corrosion resistance class 2 to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- Corrosion resistance class 3 to Festo standard 940 070
Components requiring higher corrosion resistance. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface

Compact cylinders ADNGF, standard port pattern

FESTO

Accessories


Trunnion flange ZNCF/CRZNG

Material:

ZNCF: Special steel casting

CRZNG: Electrolytically polished special steel casting

Free of copper, PTFE and silicone



Dimensions and ordering data									
For Ø	C2	C3	TD Ø e9	TK	TL	TM	US	XH	XL
[mm]									
32	71	86	12	16	12	50	45	2	52
40	87	105	16	20	16	63	54	4	55
50	99	117	16	24	16	75	64	4	57
63	116	136	20	24	20	90	75	4	61
80	136	156	20	28	20	110	93	5	81
100	164	189	25	38	25	132	110	10	86

For Ø [mm]	Basic version				R3 – High corrosion protection			
	CRC ¹⁾	Weight [g]	Part No.	Type	CRC ¹⁾	Weight [g]	Part No.	Type
32	2	130	174 411	ZNCF-32	4	150	161 852	CRZNG-32
40	2	240	174 412	ZNCF-40	4	260	161 853	CRZNG-40
50	2	390	174 413	ZNCF-50	4	430	161 854	CRZNG-50
63	2	600	174 414	ZNCF-63	4	640	161 855	CRZNG-63
80	2	1150	174 415	ZNCF-80	4	1300	161 856	CRZNG-80
100	2	2030	174 416	ZNCF-100	4	2400	161 857	CRZNG-100

1) Corrosion resistance class 2 to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Corrosion resistance class 4 to Festo standard 940 070

Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required

Compact cylinders ADNGF, standard port pattern

FESTO

Accessories


Trunnion support LN2G

Material:

Trunnion support: Anodised aluminium

Plain bearing: Plastic

Free of copper, PTFE and silicone



Dimensions and ordering data															
For Ø	CR Ø	DA Ø	FK Ø	FN	FS	H1	HB Ø	KE	NH	TH	UL	CRC ¹⁾	Weight	Part No.	Type
[mm]	D11	H13	±0.1				H13			±0.2			[g]		
32	12	11	15	30	10.5	15	6.6	6.8	18	32	46	2	90	32 959	LNZG-32
40, 50	16	15	18	36	12	18	9	9	21	36	55	2	140	32 960	LNZG-40/50
63, 80	20	18	20	40	13	20	11	11	23	42	65	2	190	32 961	LNZG-63/80
100	25	20	25	50	16	24.5	14	13	28.5	50	75	2	320	32 962	LNZG-100/125

1) Corrosion resistance class 2 to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

Compact cylinders ADNGF, standard port pattern

Accessories

FESTO

Ordering data – One-way flow control valves				Technical data → Internet: grl	
	Connection		Material	Part No.	Type
	For Ø	For tubing O.D.			
For exhaust air					
	12, 16, 20, 25	3	Metal design	193 137	GRLA-M5-QS-3-D
		4		193 138	GRLA-M5-QS-4-D
		6		193 139	GRLA-M5-QS-6-D
	32, 40, 50, 63, 80, 100	3		193 142	GRLA-1/8-QS-3-D
		4		193 143	GRLA-1/8-QS-4-D
		6		193 144	GRLA-1/8-QS-6-D
		8		193 145	GRLA-1/8-QS-8-D
For supply air					
	12, 16, 20, 25	3	Metal design	193 153	GRLZ-M5-QS-3-D
		4		193 154	GRLZ-M5-QS-4-D
		6		193 155	GRLZ-M5-QS-6-D
	32, 40, 50, 63, 80, 100	3		193 156	GRLZ-1/8-QS-3-D
		4		193 157	GRLZ-1/8-QS-4-D
		6		193 158	GRLZ-1/8-QS-6-D
		8		193 159	GRLZ-1/8-QS-8-D

Compact cylinders ADNGF, standard port pattern

Accessories

FESTO

Ordering data – Proximity sensors for T-slot, magneto-resistive					Technical data → Internet: smt	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with cylinder profile	PNP	Cable, 3-wire	2.5	543 867	SMT-8M-PS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 866	SMT-8M-PS-24V-K-0,3-M8D
			Plug M12x1, 3-pin	0.3	543 869	SMT-8M-PS-24V-K-0,3-M12
		NPN	Cable, 3-wire	2.5	543 870	SMT-8M-NS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 871	SMT-8M-NS-24V-K-0,3-M8D
	Insertable in the slot lengthwise, flush with the cylinder profile	PNP	Cable, 3-wire	2.5	175 436	SMT-8-PS-K-LED-24-B
			Plug M8x1, 3-pin	0.3	175 484	SMT-8-PS-S-LED-24-B
N/C contact						
	Insertable in the slot from above, flush with cylinder profile	PNP	Cable, 3-wire	7.5	543 873	SMT-8M-PO-24V-K7,5-OE

Ordering data – Proximity sensors for T-slot, magnetic reed					Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with cylinder profile	Contacting	Cable, 3-wire	2.5	543 862	SME-8M-DS-24V-K-2,5-OE
				5.0	543 863	SME-8M-DS-24V-K-5,0-OE
			Cable, 3-wire	2.5	543 872	SME-8M-ZS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 861	SME-8M-DS-24V-K-0,3-M8D
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	2.5	150 855	SME-8-K-LED-24
			Plug M8x1, 3-pin	0.3	150 857	SME-8-S-LED-24
N/C contact						
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	7.5	160 251	SME-8-O-K-LED-24

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Straight socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 363	NEBU-M12G5-K-2.5-LE3
			5	541 364	NEBU-M12G5-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3
	Angled socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 367	NEBU-M12W5-K-2.5-LE3
			5	541 370	NEBU-M12W5-K-5-LE3

Compact cylinders ADNGF, standard port pattern

Accessories

FESTO

Ordering data – Rectangular proximity sensors, pneumatic			Technical data ➔ Internet: smpo	
	Pneumatic connection	Part No.	Type	
3/2-way valve, normally closed				
	Female thread M5	178 563	SMPO-8E	

Ordering data – Mounting kit for proximity sensors SMPO-8E			Technical data → Internet: smb	
	Assembly	Part No.	Type	
	Clamped in T-slot	178 230	SMB-8E	

Ordering data – Slot cover for T-slot				
	Assembly	Length	Part No.	Type
	Insertable from above	2x 0.5 m	151 680	ABP-5-S

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com