

Parallel grippers HGP

FESTO




- 1 - Type discontinued
Available up until 2011

Parallel grippers HGP

Key features

FESTO




At a glance

- Double-acting piston drive
- Self-centring
- Variable gripping action:
 - External/internal gripping
- Versatility thanks to externally adaptable gripper fingers
- Wide range of options for mounting on drive units
- High gripping force and compact size
- Max. repetition accuracy
- Gripping force retention
- Internal fixed flow control
- With protective dust cap for use in dusty environments (protection class IP54)
- Sensor technology:
 - Adaptable proximity sensors on the small grippers
 - Integral proximity sensors for medium and large grippers

Note
Sizing software
Gripper selection
→ www.festo.com

Mounting options for external gripper fingers (customer-specific)

- 1 Parallel gripper
- 2 External gripper fingers
- 3 Mounting screws
- 4 Centring pins






With protective dust cap

The sizes 16 and 25 can be adapted for use in dusty environments. They fulfil the requirements for protection class IP54.

The technical data corresponds to the data for parallel gripper HGP without protective dust cap.



Note
Grippers should always be used with exhaust air flow control. They are not suitable for the following, or for similar applications:




Parallel grippers HGP


Peripherals overview and type codes

Peripherals overview


HGP-06



HGP-10 ... 35



System product for handling and assembly technology



Accessories			
Type	Brief description		→ Page/Internet
1 Position sensor SMH-S1	Adaptable and integratable sensor technology, for sensing the piston position		13
2 Evaluation unit SMH-AE1	For position sensor SMH-S1		13
3 Proximity sensor SME/SMT-8	For sensing the piston position		14
4 Bondable sensor rail HGP-SL	Allows the use of proximity sensors SME/SMT-10		13
5 Proximity sensor SME/SMT-10	For sensing the piston position		15
6 –	Drive/gripper connections		adapter kit

Type codes

		HGP	–	16	–	A	–	B	–	G1	–	SSK
Type												
HGP	Parallel gripper											
Size												
Position sensing												
A	For proximity sensing											
Generation												
B	B series											
Gripping force retention												
G1	Opening											
G2	Closing											
Protective dust cap												
SSK	Protective dust cap											

- 1 - Type discontinued
Available up until 2011


Parallel grippers HGP

Technical data

Function

Double-acting

HGP-06-A, HGP-...-A-B



Variants

- With gripping force retention...
... opening HGP-...-G1
... closing HGP-...-G2
- With protective dust cap




www.festo.com

Wearing parts kits

→ 12

- Ø - Size
6 ... 35 mm

- I - Stroke
4 ... 25 mm



General technical data							
Size	6	10	16	20	25	35	
Design	Wedge-shaped	Lever mechanism					
Mode of operation	Double-acting						
Gripper function	Parallel						
Number of gripper jaws	2						
Max. weight force per external gripper finger ¹⁾	[N]	0.1	0.2	0.4	0.6	0.8	1.2
Stroke per gripper jaw	[mm]	2	3	5	6.5	7.5	12.5
Pneumatic connection	M3			M5		G1/8	
Repetition accuracy ²⁾	[mm]	≤ 0.04					
Max. interchangeability	[mm]	0.2					
Max. operating frequency	[Hz]	4					
Position sensing	For proximity sensing						
Type of mounting	With female thread and centring sleeve						
	–	Via through-holes and centring sleeve					

1) Valid for unthrottled operation

2) End position drift under constant conditions of use with 100 consecutive strokes in the direction of movement of the gripper jaws

- ¶ - Note: This product conforms to ISO 1179-1 and to ISO 228-1

Operating and environmental conditions								
Size			6	10	16	20	25	35
Min. operating pressure	HGP-...-A/-B	[bar]	2					
	HGP-...-G...	[bar]	5					
Max. operating pressure		[bar]	8					
Operating medium			Filtered compressed air, lubricated or unlubricated					
Ambient temperature		[°C]	+5 ... +60					
Corrosion resistance class CRC ¹⁾			2	1				

1) Corrosion resistance class 1 according to Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

Weights [g]						
Size	6	10	16	20	25	35
HGP-...-A	18	75	194	396	725	1 369
HGP-...-G1	-	76	197	402	737	1 387
HGP-...-G2	-	76	197	402	737	1 387
With protective dust cap						
HGP-...-SSK	-	-	197	-	737	-


Parallel grippers HGP

Technical data

FESTO


Materials

Sectional view




Parallel gripper	6	10	16	20	25	35
1 Body	Nickel-plated aluminium	Hard anodised aluminium				
2 Gripper jaw	Nickel-plated steel	High-alloy steel				
3 Cover cap	Polyamide					
– Protective dust cap SSK	–		Thermoplastic vulcanizate	–	Thermoplastic vulcanizate	–
– Note on materials	Copper, PTFE and silicone-free					
	Conforms to RoHS					

Gripping force [N] at 6 bar



Size	6	10	16	20	25	35
Gripping force per gripper jaw						
Opening	10	22	70	120	185	375
Closing	10	17	80	115	170	350
Total gripping force						
Opening	20	44	140	240	370	750
Closing	20	34	160	230	340	700

Characteristic load values per gripper jaw



The indicated permissible forces and torques apply to a single gripper jaw. The indicated values include the lever arm, additional applied loads caused

by the workpiece or external gripper fingers, as well as forces which occur during movement.

The zero co-ordinate line (gripper jaw guide) must be taken into consideration for the calculation of torques.

Size		6	10	16	20	25	35
Max. permissible force F_Z	[N]	14	25	90	150	240	380
Max. permissible torque M_X	[Nm]	0.1	0.5	3.3	6	11	25
Max. permissible torque M_Y	[Nm]	0.1	0.5	3.3	6	11	25
Max. permissible torque M_Z	[Nm]	0.1	0.5	3.3	6	11	25


- 1 - Type discontinued
Available up until 2011

Parallel grippers HGP

Technical data

FESTO

Mass moment of inertia [kgm²x10⁻⁴]





Mass moment of inertia [kgm²x10⁻⁴]
 for parallel grippers in relation to the
 central axis, without external gripper
 fingers, without load.

Size	6	10	16	20	25	35
HGP-...-A	0.01	0.08	0.47	1.49	3.83	12.70
HGP-...-G1	–	0.08	0.47	1.52	3.92	12.83
HGP-...-G2	–	0.08	0.47	1.49	3.84	12.73

Opening and closing times [ms] at 6 bar

without external gripper fingers

with external gripper fingers



The indicated opening and closing
 times [ms] have been measured at
 room temperature and 6 bar operating
 pressure without external gripper
 fingers.

The grippers must be throttled for
 greater applied loads. Opening and
 closing times must then be adjusted
 accordingly.


Size		6	10	16	20	25	35
Without external gripper fingers							
HGP-...-A	Opening	5	22	44	32	47	77
	Closing	5	31	60	44	50	77
HGP-...-G1	Opening	–	17	39	30	39	71
	Closing	–	29	62	48	60	82
HGP-...-G2	Opening	–	33	66	39	62	90
	Closing	–	29	44	42	49	72
With external gripper fingers (as a function of weight force)							
HGP	0.06 N	5	–	–	–	–	–
	0.08 N	10	–	–	–	–	–
	0.10 N	20	–	–	–	–	–
	0.20 N	50	–	–	–	–	–
	0.50 N	–	100	–	–	–	–
	1.00 N	–	200	100	–	–	–
	1.25 N	–	–	–	100	–	–
	1.50 N	–	300	200	–	100	–
	1.75 N	–	–	–	200	–	–
	2.00 N	–	–	300	–	200	100
	2.50 N	–	–	–	300	–	–
	3.00 N	–	–	–	–	300	200
	4.00 N	–	–	–	–	–	300

Parallel grippers HGP

Technical data

Gripping force F_{Grip} per gripper jaw as a function of operating pressure and lever arm x

External and internal gripping (closing and opening)




Gripping forces can be determined with the following diagrams for the various sizes in relation to operating

pressure and lever arm (distance from the zero co-ordinate line shown


opposite to the pressure point at which the fingers grip the workpiece).

HGP-06-A¹⁾




1) Due to the design, the opening and closing gripping forces for HGP-06-A are identical


HGP-10-A-B




HGP-16-A-B




HGP-20-A-B



HGP-25-A-B



HGP-35-A-B




— Closing
 - - - Opening

Parallel grippers HGP



Technical data

FESTO


Spring force F_{Spring} as a function of the gripper size and overall stroke length l



Gripper retention force, opening:
the spring forces F_{Spring} of the parallel gripper HGP-...-G1 can be determined from the following graphs.



Gripper retention force, closing:
the spring forces F_{Spring} of the parallel gripper HGP-...-G2 can be determined from the following graphs.



Determination of actual gripping forces for parallel grippers HGP-...-G1 and HGP-...-G2 depending upon the application

The parallel grippers with integrated spring can be used as:

- single-acting grippers
- grippers with supplementary gripping force and
- grippers with gripping force retention

In order to calculate available gripping forces F_{Gr} (per gripper jaw), the gripping force F_{Grip} and spring

force (F_{Spring}) must be combined accordingly.

Application

The resulting gripping force F_{Gr} , conditional on the application, depends on the gripping action (external/internal gripping) and the gripper design (with/without spring return). The spring force is supplemented in accordance with the design and gripping action.

Single-acting

- Gripping with spring force:
 $F_{\text{Gr}} = F_{\text{Spring}}$
- Gripping with pressure force:
 $F_{\text{Gr}} = F_{\text{Grip}} - F_{\text{Spring}}$

Supplementary gripping force

- Gripping with pressure and spring force:
 $F_{\text{Gr}} = F_{\text{Grip}} + F_{\text{Spring}}$

Gripping force retention

- Gripping with spring force:
 $F_{\text{Gr}} = F_{\text{Spring}}$


		Pressurised (in gripping action)	Unpressurised
HGP	Opening	$F_{\text{Gr}} = F_{\text{Grip}}$	$F_{\text{Gr}} = 0$
	Closing	$F_{\text{Gr}} = F_{\text{Grip}}$	$F_{\text{Gr}} = 0$
HGP-...-G1	Opening	$F_{\text{Gr}} = F_{\text{Grip}} + F_{\text{Spring}}$	$F_{\text{Gr}} = F_{\text{Spring}}$
	Closing	$F_{\text{Gr}} = F_{\text{Grip}} - F_{\text{Spring}}$	$F_{\text{Gr}} = 0$
HGP-...-G2	Opening	$F_{\text{Gr}} = F_{\text{Grip}} - F_{\text{Spring}}$	$F_{\text{Gr}} = 0$
	Closing	$F_{\text{Gr}} = F_{\text{Grip}} + F_{\text{Spring}}$	$F_{\text{Gr}} = F_{\text{Spring}}$

Parallel grippers HGP

Technical data

Gripping force F_{Grip} per gripper jaw at 6 bar as a function of lever arm x and eccentricity y

External and internal gripping (closing and opening)



Gripping forces can be determined with the following diagrams for the various sizes at 6 bar in relation to

eccentric application of force (distance from the zero co-ordinate line shown opposite to the pressure point at

which the fingers grip the workpiece) and the maximum permissible off-centre point at which force is applied.

Calculation example

Given:

HGP-16-A-B

Lever arm $x = 20$ mm

Eccentricity $y = 22$ mm

To be found:


Gripping force at 6 bar

Procedure:


- Determine the intersection xy between lever arm x and eccentricity y in the graph for HGP-16-A-B
- Draw an arc (with centre at origin) through intersection xy
- Determine the intersection between the arc and the X axis
- Read the gripping force

Result:


Gripping force = approx. 66 N




HGP-06-A




HGP-10-A-B




HGP-16-A-B




HGP-20-A



HGP-25-A-B



HGP-35-A-B



- 1 Closing
2 Opening

- 1 - Type discontinued
Available up until 2011



Parallel grippers HGP

Technical data

FESTO


Dimensions

Download CAD data → www.festo.com



- | | |
|---|---|
| <p>1 Sensor slot for proximity sensor SME/SMT-8 (not with HGP-06-A). Proximity sensors SME/SMT-10 can also be used in combination with the sensor strip HGP-SL-... (can be glued into place).</p> | <p>2 Compressed air connection, opening</p> <p>3 Compressed air connection, closing</p> <p>4 Closed</p> <p>5 Open</p> <p>6 Centring sleeves ZBH (2 included in scope of delivery)</p> |
|---|---|

With protective dust cap HGP-...-SSK



Parallel grippers HGP

Technical data

FESTO

Type	B1	B2 ¹⁾	B3	B4	B5	B6	B7	D1 Ø	D2	D3 Ø H8/h7	D5	D6 Ø H8	EE	H1	H2	H3	H4 ²⁾
		±0.1	±0.5	±0.5	±0.5	-0.03	±0.5										±0.1
HGP-06-A	18	11	6	10	21	5.5	-	3.2	M3	5	M2	1.5	M3	45.5	9.9	10.2	7.5
HGP-10-A-B	32	16	15.8	21.8	35.8	7	-	3.2	M3	5	M3	2	M3	66	15	16	7.5
HGP-16-A-B	47	25	17.8	27.8	53.8	13	-	5.3	M4	7	M4	3	M3	80	20	21.9	7.5
HGP-20-A-B	55.6	25	17.4	30.4	65.4	17.5	-	5.3	M4	7	M4	4	M5	101	24.9	26.1	7.5
HGP-25-A-B	68.2	29	21	36	80	22	-	6.4	M6	9	M5	4	G ¹ / ₈	121	30	32.2	17.5
HGP-35-A-B	88	33	31	56	110	27	-	8.4	M8	12	M6	5	G ¹ / ₈	142	31.9	44.8	17.5
With protective dust cap																	
HGP-16-A-B-SSK	47	25	16.4	26.4	46.4	10	67	5.3	M4	7	M4	3	M3	83	20.5	21.9	7.5
HGP-25-A-B-SSK	68.2	29	21	36	66	15	101	6.4	M6	9	M5	4	G ¹ / ₈	126.8	31.5	32.2	17.5

Type	H5	H6	H7	H8	H9	H10	H11	L1	L2	L3	L6	L7	T1	T3	T4	T5
						±0.2				-0.03			+0.1	+1	+0.5	-0.3
HGP-06-A	7	4	5.8	2.9	5	33	-	10	1.5	5	1.8	-	1.2	-	3.5	1.2
HGP-10-A-B	7	4	8	4	7.5	51	-	15.5	4.2	7	1.5	-	1.2	6	3.5	1.2
HGP-16-A-B	7	4	11	5.5	10	62.5	-	22	5.7	10	-	-	1.6	7.5	3.5	1.4
HGP-20-A-B	10.5	11.5	14	7	12.5	81	-	30	9	12	-	-	1.6	8	6	1.4
HGP-25-A-B	16.5	8.3	16	8	15	88.5	-	37	10.5	15	-	-	2.1	15	6.5	1.9
HGP-35-A-B	16.5	8.5	17	8.5	16	108.5	-	45	10.5	20	-	-	2.6	16	6.5	2.4
With protective dust cap																
HGP-16-A-B-SSK	7	4	11	5.5	10	65.5	38.1	22	5.7	10	-	30	1.6	7.5	3.5	1.4
HGP-25-A-B-SSK	16.5	8.3	16	8	15	94.3	58.8	37	10.5	15	-	47	2.1	15	6.5	1.9

1) Tolerance for centring hole: ±0.02

2) Tolerance for centring hole: -0.05

- 1 - Note: This product conforms to ISO 1179-1 and to ISO 228-1

Note

Due to the distance H5 between the two air connections on types HGP-06/-10/-16 which measures 7 mm, only the following tube fittings can be used

- QSM-M3-3
- QSML-M3-3
- QSMLL-M3-3
- CN-M3-PK-3
- LCN-M3-PK-3

→ Internet: fitting

- 1 - Type discontinued
Available up until 2011

Parallel grippers HGP

Technical data

FESTO

Ordering data						
Size	Double-acting		Gripper retention force G1		Gripper retention force G2	
	Without compression spring		Opening		Closing	
[mm]	Part No.	Type	Part No.	Type	Part No.	Type
6	174 815	HGP-06-A	–		–	
10	197 542	HGP-10-A-B	197 543	HGP-10-A-B-G1	197 544	HGP-10-A-B-G2
16	197 545	HGP-16-A-B	197 546	HGP-16-A-B-G1	197 547	HGP-16-A-B-G2
20	525 889	HGP-20-A-B	525 890	HGP-20-A-B-G1	525 891	HGP-20-A-B-G2
25	197 548	HGP-25-A-B	197 549	HGP-25-A-B-G1	197 550	HGP-25-A-B-G2
35	197 551	HGP-35-A-B	197 552	HGP-35-A-B-G1	197 553	HGP-35-A-B-G2
With protective dust cap						
16	539 636	HGP-16-A-B-SSK	–		–	
25	539 635	HGP-25-A-B-SSK	–		–	

Ordering data – Wearing parts kits		
Size [mm]	Part No.	Type
6	378 516	HGP-06-A
10	397 376	HGP-10
16	397 377	HGP-16
20	397 378	HGP-20
25	397 397	HGP-25
32	397 380	HGP-35

Parallel grippers HGP


Accessories

Sensor rail HGP-SL


can be glued into place

Material:

Wrought aluminium alloy




Dimensions and ordering data					
For size [mm]	L1	Weight [g]	Part No.	Type	
10	35	1.4	535 582	HGP-SL-10-10	
16	38	1.5	535 583	HGP-SL-10-16	
20	50	2.0	535 584	HGP-SL-10-20	
25	58	2.3	535 585	HGP-SL-10-25	
35	65	2.6	535 586	HGP-SL-10-35	

Ordering data						
Type	For size	Weight [g]	Part No.	Type	PU ¹⁾	
Position sensor SMH-S1			Technical data → Internet: smh-s1			
	6	20	175 710	SMH-S1-HGP06	1	
Evaluation unit SMH-AE1			Technical data → Internet: smh-ae			
	6	170	175 708	SMH-AE1-PS3-M12	1	
			175 709	SMH-AE1-NS3-M12		
Centring sleeve ZBH			Technical data → Internet: zbh			
	6, 10	1	189 652	ZBH-5	10	
	16, 20		186 717	ZBH-7		
	25		150 927	ZBH-9		
	35		189 653	ZBH-12		

1) Packaging unit quantity

Installation instructions for position sensor SMH-S1

In order to ensure the correct functioning of the position sensor the outlet cables and the compressed air tubing must be mounted in the same direction.






- 2 - Type discontinued
Available up until 2011

Parallel grippers HGP

Accessories

FESTO

Ordering data – Proximity sensors for T-slot, magneto-resistive					Technical data → Internet: smt	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with cylinder profile	PNP	Cable, 3-wire	2.5	543 867	SMT-8M-PS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 866	SMT-8M-PS-24V-K-0,3-M8D
			Plug M12x1, 3-pin	0.3	543 869	SMT-8M-PS-24V-K-0,3-M12
	Insertable in the slot lengthwise, flush with the cylinder profile	PNP	Cable, 3-wire	2.5	543 870	SMT-8M-NS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 871	SMT-8M-NS-24V-K-0,3-M8D
			Plug M8x1, 3-pin	0.3	175 436	SMT-8-PS-K-LED-24-B
					175 484	SMT-8-PS-S-LED-24-B
N/C contact						
	Insertable in the slot from above, flush with cylinder profile	PNP	Cable, 3-wire	7.5	543 873	SMT-8M-PO-24V-K7,5-OE

Ordering data – Proximity sensors for T-slot, magnetic reed					Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with cylinder profile	Contacting	Cable, 3-wire	2.5	543 862	SME-8M-DS-24V-K-2,5-OE
				5.0	543 863	SME-8M-DS-24V-K-5,0-OE
			Cable, 3-wire	2.5	543 872	SME-8M-ZS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 861	SME-8M-DS-24V-K-0,3-M8D
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	2.5	150 855	SME-8-K-LED-24
			Plug M8x1, 3-pin	0.3	150 857	SME-8-S-LED-24
N/C contact						
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	7.5	160 251	SME-8-O-K-LED-24

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Straight socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 363	NEBU-M12G5-K-2.5-LE3
			5	541 364	NEBU-M12G5-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3
	Angled socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 367	NEBU-M12W5-K-2.5-LE3
			5	541 370	NEBU-M12W5-K-5-LE3

Parallel grippers HGP

Accessories

FESTO

Ordering data – Proximity sensors for C-slot, magneto-resistive					Technical data → Internet: smt	
	Type of mounting	Switch output	Electrical connection, connection direction	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above	PNP	Cable, 3-wire, in-line	2.5	551 373	SMT-10M-PS-24V-E-2,5-L-OE
			Plug M8x1, 3-pin, in-line	0.3	551 375	SMT-10M-PS-24V-E-0,3-L-M8D
			Plug M8x1, 3-pin, lateral	0.3	551 376	SMT-10M-PS-24V-E-0,3-Q-M8D

Ordering data – Proximity sensors for C-slot, magnetic reed					Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection, connection direction	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above	Contacting	Plug M8x1, 3-pin, in-line	0.3	551 367	SME-10M-DS-24V-E-0,3-L-M8D
			Cable, 3-wire, in-line	2.5	551 365	SME-10M-DS-24V-E-2,5-L-OE
			Cable, 2-wire, in-line	2.5	551 369	SME-10M-ZS-24V-E-2,5-L-OE
	Insertable in the slot lengthwise	Contacting	Plug M8x1, 3-pin, in-line	0.3	173 212	SME-10-SL-LED-24
			Cable, 3-wire, in-line	2.5	173 210	SME-10-KL-LED-24

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3