

Parallel grippers HGPC

FESTO



Parallel grippers HGPC

Key features

FESTO

At a glance

General

The compact and low-cost parallel gripper consists of a two-part symmetrical housing. The piston moves traverse to the half-shell casing in an optimum housing design that

guarantees reliable operation, long service life and convenient sensing. The gripper jaws move along the half shells in backlash-free, preloaded ball bearing guides.


- Double-acting gripper
- Compression spring for supplementary or retaining gripping forces
- Internal fixed flow control, does away with the need for external flow control in 80% of applications
- High force with minimal volume

- Suitable for external and internal gripping
- Wide range of options for attaching drive units
- Repetition accuracy of 0.05 mm
- Slot for proximity sensor SME/SMT-10

Note


Sizing software
Gripper selection
→ www.festo.com

Details




- 1 Gripper jaw with ball bearing guide
- 2 Housing based on half-shell principle
- 3 Slot for proximity sensor, for sensing the piston position
- 4 Mounting option
- 5 Supply port

Mounting option from underneath




from above




Note


Parallel grippers are not designed for the following applications:



- Machining
- Aggressive media



- Grinding dust




- Welding spatter

Parallel grippers HGPC


Peripherals overview and type codes

FESTO

Peripherals overview



System product for handling and assembly technology



Accessories			
Type	Brief description		→ Page/Internet
1 One-way flow control valve GRLA	For speed regulation		gria
2 Push-in fitting QS	For connecting compressed air tubing with standard external diameters		quick star
3 Proximity sensor SME/SMT-10	For sensing the piston position		12
4 Centring sleeve ZBH	For centring when attaching to a drive		12
5 –	Drive/gripper connections		adapter kit

Type codes


		HGPC	–	12	–	A	–	G2
Type								
HGPC	Parallel gripper							
Size								
Position sensing								
A	For proximity sensing							
Gripping force retention								
G2	Closing							

Parallel grippers HGPC

Technical data

FESTO

Function
Double-acting
HGPC-...-A



Single-acting or
with gripping force retention
closing HGPC-...-G2



 Size
12, 16, 20 mm
 Stroke
6 ... 14 mm



General technical data			
Size	12	16	20
Constructional design	Wedge-shaped drive Guided motion sequence		
Mode of operation	Double-acting		
Gripper function	Parallel		
Number of gripper jaws	2		
Max. weight force per external gripper finger ¹⁾ [N]	0.2	0.5	0.8
Stroke per gripper jaw [mm]	3	5	7
Pneumatic connection	M5		
Repetition accuracy ²⁾ [mm]	≤ 0.05		
Max. interchangeability [mm]	≤ 0.2		
Max. gripper jaw backlash ³⁾ [mm]	0		
Max. gripper jaw angular backlash ⁴⁾ [°]	0		
Max. operating frequency [Hz]	4		
Rotational symmetry [mm]	< Ø 0.2		
Position sensing	For proximity sensing		
Type of mounting	With female thread and centring sleeve		
Mounting position	Any		

- 1) Valid for unthrottled operation
 2) End-position drift under constant conditions of use with 100 consecutive strokes in the direction of movement of the gripper jaws
 3) Perpendicular to the direction of motion of the gripper jaws
 4) Pretensioned, backlash-free ball bearing guide

Operating and environmental conditions			
Min. operating pressure	HGPC-...-A	[bar]	2
	HGPC-...-G2	[bar]	4
Max. operating pressure		[bar]	8
Operating medium			Filtered compressed air, lubricated or unlubricated
Ambient temperature ¹⁾		[°C]	+5 ... +60
Corrosion resistance class CRC ²⁾			2

- 1) Note operating range of proximity sensors
 2) Corrosion resistance class 2 according to Festo standard 940 070
 Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

Weights [g]			
Size	12	16	20
HGPC-...-A	152	241	473
HGPC-...-G2	154	244	477


Parallel grippers HGPC

Technical data

FESTO


Materials

Sectional view




Parallel gripper		
1	Gripper jaw	High-alloy steel
2	Housing	Die-cast zinc
3	Piston	Polyamide
-	Seals	Polyurethane, nitrile rubber
-	Note on materials	Copper, PTFE and silicone-free
		Conforms to RoHS

Gripping force [N] at 6 bar



Size	12	16	20
Gripping force per gripper jaw			
Opening	22	41.5	63
Closing	22	41.5	63
Total gripping force			
Opening	44	83	126
Closing	44	83	126

Static characteristic load values at the gripper jaws



Indicated permissible forces and torques apply to a single gripper jaw. The indicated values include the lever arm, additional applied loads caused by the workpiece or external gripper

fingers, as well as forces which occur during movement.

The zero coordinate line (gripper finger guide) must be taken into consideration for the calculation of torques.


Size		12	16	20
Max. permissible force F_z	[N]	40	80	120
Max. permissible torque M_x	[Nm]	1	2,5	5
Max. permissible torque M_y	[Nm]	1	2,5	5
Max. permissible torque M_z	[Nm]	1	2,5	5

Parallel grippers HGPC

Technical data

FESTO

Mass moment of inertia [$\text{kgm}^2 \times 10^{-4}$]





Mass moment of inertia [$\text{kgm}^2 \times 10^{-4}$]
of the parallel gripper in relation to
the central axis with no load.

Size	12	16	20
HGPC-...-A	0.272	0.679	2.095
HGPC-...-G2	0.274	0.683	2.105

Opening and closing times [ms] at 6 bar

without external gripper fingers

with external gripper fingers



The indicated opening and closing
times [ms] have been measured at
room temperature and at 6 bar
operating pressure with horizontally
mounted gripper without additional

gripper fingers. The grippers must be
throttled for greater applied loads.
Opening and closing times must then
be adjusted correspondingly.


Size		12	16	20
without external gripper fingers				
HGPC-...-A	Opening	30	60	90
	Closing	30	60	90
HGPC-...-G2	Opening	30	70	105
	Closing	30	50	75
with external gripper fingers as a function of weight force				
HGPC-...	0.4 N	40	–	–
	0.5 N	60	–	–
	0.6 N	80	–	–
	0.7 N	–	80	–
	1.0 N	–	100	–
	1.2 N	–	–	100

Parallel grippers HGPC


Technical data

Gripping force F_{Grip} per gripper jaw as a function of operating pressure and lever arm x


Gripping forces as a function of the operating pressure and the lever arm can be determined for the size using the following graph.




HGPC-12-A



HGPC-16-A



HGPC-20-A



Parallel grippers HGPC



Technical data

FESTO

Spring force F_S as a function of the gripper size and the overall stroke l

Gripping force retention for HGPC-...-G2

Spring forces F_S as a function of the gripper size and the overall stroke l for various gripper types (HGPC-...-G2) can be determined using the following graphs.



The lever arm x must be taken into consideration when determining the actual spring force $F_{S\text{total}}$. The formulae for calculating the spring force are provided in the table opposite.

Size	$F_{S\text{total}} =$
12	$-0.02 \cdot x + 0.5 \cdot F_S$
16	$-0.05 \cdot x + 0.5 \cdot F_S$
20	$-0.05 \cdot x + 0.5 \cdot F_S$

Determination of the actual gripping forces F_{Gr} for HGPC-...-G2 depending on the application

Parallel grippers with integrated spring type HGPC-...-G2 (closing gripping force retention) can be used as:

- single-acting grippers

- grippers with supplementary gripping force
- grippers with gripping force retention

In order to calculate available gripping forces F_{Gr} (per gripper jaw), the gripping force (F_{Grip}) and spring

force ($F_{S\text{total}}$) must be combined accordingly.


Application		
Single-acting	Supplementary gripping force	Gripping force retention
- Gripping with spring force: $F_{Gr} = F_{S\text{total}}$ - Gripping with pressure force: $F_{Gr} = F_{Grip} - F_{S\text{total}}$	Gripping with pressure and spring force: $F_{Gr} = F_{Grip} + F_{S\text{total}}$	Gripping with spring force: $F_{Gr} = F_{S\text{total}}$

Parallel grippers HGPC

Technical data

FESTO

Gripping force F_{Grip} per gripper jaw at 6 bar as a function of lever arm x and eccentricity y



Gripping forces at 6 bar dependent upon eccentric application of force and the maximum permissible off-centre point of force application can be determined for the size using the following graph.

Calculation example

Given:

Lever arm $x = 20$ mm

Eccentricity $y = 22$ mm

To be found:


Gripping force at 6 bar

Procedure:


- Determine the intersection xy between lever arm x and eccentricity y in the graph for HGPC-12-A...
- Draw an arc (with centre at origin) through intersection xy .
- Determine the intersection between the arc and the X axis.
- Read the gripping force.

Result:


Gripping force $F = \text{approx. } 20.5$ N




HGPC-12-A



HGPC-16-A



HGPC-20-A




Parallel grippers HGPC

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



- 1 Sensor slot for proximity sensor
- 2 Supply port, opening
- 3 Supply port, closing
- 4 Gripper jaw closed
- 5 Gripper jaw open
- 6 Centring sleeves ZBH
(2 included in scope of delivery)

Size	B1	B2	B3	B4	D1	D2	D3	D4	D5	D6
[mm]				±0.1			±0.1	Ø F10/h7	Ø	
12	38	33	22.4	6	12	2.5 ^{+0.04/+0.01}	3.3	7	5.3	M4
16	46	39	28	7	12	3 ^{H8}	4.3	7	5.3	M5
20	57	50	35	8	12	4 ^{H8}	5.3	9	6.4	M6

Size	EE	H1	H2	H3	H4	H5	H6	H7	H8	H9	H10
[mm]		±0.5							-0.2		
12	M5	48.2	33.6	21.7	20.2	6.9	5 ^{+0.05/-0.1}	9 ^{+0.05/-0.1}	25	1.2	9.2
16	M5	55.2	38.2	25.2	23.7	8.2	6±0.1	10.5±0.4	28.5	1.5	10.7
20	M5	68.7	48.2	32.5	30.5	10.2	7.5±0.1	13±0.4	34.5	1.5	13.7


Size	L1	L2	L3	L4 ¹⁾	L5	L6	T1	T2	T3	T4	T5
[mm]	±0.5	±0.5					min.		±0.1	+0.4 -0.3	+0.1 -0.3
12	45	39	10 ^{-0.02/-0.06}	33	42	10	4.5	2.2	1.7	3.1	1.3
16	62	52	12 ^{-0.05}	40	51	12	4.5	2.7	1.8	3.8	1.2
20	76	63	14 ^{-0.05}	50	65	16	4.5	3.2	2.3	5.2	1.7

1) Tolerance for centring hole ±0.03
Tolerance for thread ±0.1


Parallel grippers HGPC

Technical data

FESTO



Minimum distance l between gripper and ferritic object			
	12	16	20
Distance	[mm]	10	

Ordering data					
	Size	Double-acting Without compression spring		Single-acting or with gripping force retention Closing	
	[mm]	Part No.	Type	Part No.	Type
	12	539 267	HGPC-12-A	539 268	HGPC-12-A-G2
	16	539 269	HGPC-16-A	539 270	HGPC-16-A-G2
	20	539 271	HGPC-20-A	539 272	HGPC-20-A-G2

Parallel grippers HGPC

Accessories

FESTO

Ordering data – Centring sleeves				Technical data → Internet: zbh	
	For size [mm]	Weight [g]	Part No.	Type	PU ¹⁾
	12, 16	1	186 717	ZBH-7	10
	20	1	150 927	ZBH-9	10

1) Packaging unit quantity

Ordering data – Proximity sensors for rounded slot, longitudinal connecting cable						
	Assembly	Electrical connection		Cable length [m]	Part No.	Type
		Cable	M8 plug			
	NO contact, magneto-resistive				Technical data ➔ Internet: smt	
	Insertable from end	3-wire	–	2.5	173 218	SMT-10-PS-KL-LED-24
		–	3-pin	0.3	173 220	SMT-10-PS-SL-LED-24
	NO contact, magnetic reed				Technical data ➔ Internet: sme	
	Insertable from end	3-wire	–	2.5	173 210	SME-10-KL-LED-24
–		3-pin	0.3	173 212	SME-10-SL-LED-24	

Ordering data – Proximity sensors for rounded slot, lateral connecting cable						
	Assembly	Electrical connection		Cable length [m]	Part No.	Type
		Cable	M8 plug			
	NO contact, magneto-resistive				Technical data ➔ Internet: smt	
	Insertable from end	3-wire	–	2.5	173 219	SMT-10-PS-KQ-LED-24
		–	3-pin	0.3	173 221	SMT-10-PS-SQ-LED-24
	NO contact, magnetic reed				Technical data ➔ Internet: sme	
	Insertable from end	3-wire	–	2.5	173 211	SME-10-KQ-LED-24
		–	3-pin	0.3	173 213	SME-10-SQ-LED-24

Ordering data – Connecting cables					Technical data → Internet: nebu
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com