

Angle grippers HGWM, micro


FESTO



Angle grippers HGWM, micro

Key features

FESTO




At a glance


- Compact, handy design
- With open or closed gripper jaws
- Versatility thanks to externally adaptable gripper fingers
- Wide range of options for attaching drive units
- With stroke compensation after installation
- Mounting options:
 - Clamping spigot
 - Male thread




-  - Note
Sizing software
Gripper selection
→ www.festo.com

Mounting options for external gripper fingers (customer-specific)

- 1 Angle gripper
- 2 External gripper fingers
- 3 Mounting screws



-  - Note
Grippers are not suitable for the following, or for similar applications:




Angle grippers HGWM, micro

Key features


FESTO

Mounting options


With through-holes




With through-holes, screws and retaining nuts




With set screw
Direct air supply




Integrated air supply



With male thread and lock nut



System product for handling and assembly technology



	→ Page/Internet
Drives	drive
Grippers	gripper
Adapters	adapter kit
Basic mounting components	basic component
Installation components	installation component
Axes	axes
Motors	motor

Angle grippers HGWM, micro

Type codes

HGWM		–	12	–	EO	–	G8
Type							
HGWM	Angle gripper						
Size							
Gripper jaw position							
EO	Open						
EZ	Closed						
Mounting options							
G6	With stroke compensation						
G7	With male thread						
G8	With clamping spigot						

Angle grippers HGWM, micro

Technical data

FESTO

Function


Single-acting
with open gripper jaws
HGWM-...-EO-G...



with closed gripper jaws
HGWM-...-EZ-G...



Size
8 ... 12 mm



General technical data					
Size				8	12
Constructional design				Wedge-shaped drive	
Mode of operation				Single-acting	
Gripper function				Angle	
Number of gripper jaws				2	
Opening angle (±2°)	Gripper jaws open	Open	[°]	20	18.5
		Closed	[°]	4	3.5
	Gripper jaws closed	Open	[°]	14	14
		Closed	[°]	4	4
Spring resetting torque ¹⁾	Gripper jaws open		[Ncm]	0.5	1.3
	Gripper jaws closed		[Ncm]	0.55	1.5
Pneumatic connection				M3	
Repetition accuracy ^{2) 3)}			[mm]	< 0.02	
Max. operating frequency			[Hz]	4	
Position sensing				Without	
Type of mounting	HGWM-...-E...-G6			With internally threaded cap screws	
	HGWM-...-E...-G7			With lock nut	
	HGWM-...-E...-G8			Clamped	

- 1) Spring resetting force between the gripper jaws
- 2) End position drift under constant conditions of use with 100 consecutive strokes in the direction of movement of the gripper jaws
- 3) The indicated values are only valid when gripping with compressed air, not with spring force

Operating and environmental conditions		
Min. operating pressure	[bar]	2
Max. operating pressure	[bar]	8
Operating medium	Filtered compressed air, lubricated or unlubricated (grade of filtration 40µm)	
Ambient temperature	[°C]	+5 ... +60
Corrosion resistance class CRC ¹⁾	2	

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

Weights [g]		
Size	8	12
With stroke compensation	23	75
With male thread	14	52
With clamping spigot	13	45


Angle grippers HGWM, micro

Technical data

FESTO

Materials


Sectional view



Angle gripper


1	Body	Stainless steel
2	Gripper jaw	Stainless steel
3	Cover cap	Polyacetate
–	Note on materials	Copper, PTFE and silicone-free Conforms to RoHS

Total gripping torque [Ncm] at 6 bar



Size	8		12	
	HGPM-...EO-...	HGPM-...EZ-...	HGPM-...EO-...	HGPM-...EZ-...
Total gripping torque				
Opening	–	24	–	76
Closing	22	–	64	–

Characteristic load values at the gripper jaws



The indicated permissible forces and torques apply to a single gripper jaw. Static forces and torques relate to additional applied loads caused by

the workpiece or external gripper fingers, as well as forces which occur during handling. The zero co-ordinate

line (gripper jaws point of rotation) must be taken into consideration for the calculation of torques.


Size		8	12
Max. permissible force F_z	[N]	7	20
Max. permissible torque M_x	[Ncm]	20	40
Max. permissible torque M_y	[Ncm]	20	40
Max. permissible torque M_z	[Ncm]	20	40

Angle grippers HGWM, micro

Technical data

FESTO


Applied load [N] and mass moment of inertia [$\text{kgm}^2 \times 10^{-4}$] per external gripper finger



Size	8	12
Applied load $F_{z1}^{1)}$	< 0.04	< 0.1
Mass moment of inertia $J_x^{1)}$	< 0.025	< 0.056

1) Valid for unthrottled operation

Mass moment of inertia [$\text{kgm}^2 \times 10^{-4}$]




Mass moment of inertia [$\text{kgm}^2 \times 10^{-4}$]
for angle grippers in relation to the
central axis without external gripper
fingers.

Size	8	12
With stroke compensation	0.00705	0.0421
With male thread	0.00315	0.0267
With clamping spigot	0.00252	0.02154

Opening and closing times [ms] at 6 bar

Without external gripper fingers



The indicated opening and closing
times [ms] have been measured at
room temperature and 6 bar operat-
ing pressure with vertically mounted

gripper and without external gripper
fingers. Load is increased if external
gripper fingers are attached. This
means that kinetic energy is also

increased, as this is determined by
gripper finger mass moment of inertia
and angular velocity.

Size		8	12
HGPM-...EO-...	Opening	2.7	3.7
	Closing	1.2	1.8
HGPM-...EZ-...	Opening	1	1.7
	Closing	2.5	2.8


Angle grippers HGWM, micro

Technical data

FESTO

Gripper jaw backlash

Without external gripper fingers




With angle grippers, backlash occurs between the gripper jaws and the guide element due to the plain-bearing guide. The backlash values listed

in the table have been calculated based upon the traditional accumulative tolerance method and usually do not occur with mounted grippers.

Size	8	12
Gripper jaw backlash s_z [mm]	< 0.03	
Gripper jaw angular backlash α_x, α_y [°]	< 0.5	

Spring displacement forces [N]



Theoretical actuating force due to stroke compensation for design variant with stroke compensation.

Size	8	12
Spring displacement forces F_1	4	10
Spring displacement forces F_2	6	23

Angle grippers HGWM, micro

Technical data

FESTO

Application example



Angle grippers HGWM, micro


Technical data

FESTO


Dimensions

Download CAD data → www.festo.com/en/engineering


With stroke compensation – HGWM-...-E...-G6



With male thread – HGWM-...-E...-G7



With clamping spigot – HGWM-...-E...-G8



Angle grippers HGWM, micro

Technical data

FESTO

Type	B1 ±0.1	B2 ±0.25	B3	B4 ±0.3	B5	D1	D2 Ø +0.1	D3 Ø +0.1	D4 Ø	D5 Ø	D6
HGWM-08-EO-G6	24	15	5.5	11.8	5 ±0.02	M3	3.4	12	8 -0.02/-0.05	15 ±0.5	M2
HGWM-08-EZ-G6											
HGWM-12-EO-G6	35	24	8.5	18.2	7.5 -0.05	M3	4.5	18	11 -0.02/-0.05	22 ±0.5	M3
HGWM-12-EZ-G6											
HGWM-08-EO-G7	-	-	5.5	11.8	5 ±0.02	M3	-	12	M10x1	-	M2
HGWM-08-EZ-G7											
HGWM-12-EO-G7	-	-	8.5	18.2	7.5 -0.05	M3	-	18	M15x1.5	-	M3
HGWM-12-EZ-G7											
HGWM-08-EO-G8	-	-	5.5	11.8	5 ±0.02	M3	-	12	6.6 -0.03	10 h8	M2
HGWM-08-EZ-G8											
HGWM-12-EO-G8	-	-	8.5	18.2	7.5 -0.05	M3	-	18	10.6 -0.03	15 h8	M3
HGWM-12-EZ-G8											

Type	D7 Ø +0.1	D8 +0.1	H1 +0.25	H2	H3	H4	H5 +0.1	H6	H7	H8	H9 +0.1
HGWM-08-EO-G6	-	-	54	47 ±0.3	5 ±0.2	22-0.3	16	0 ... 5 +0.6/-0.3	2	4.3	10
HGWM-08-EZ-G6											
HGWM-12-EO-G6	-	-	77.5	67 ±0.3	7.5	29-0.3	24	0 ... 8 +0.6/-0.3	3	6.5	15
HGWM-12-EZ-G6											
HGWM-08-EO-G7	-	-	37	32 +0.3/-0.2	5 ±0.2	12	16	11	2	4.3	10
HGWM-08-EZ-G7											
HGWM-12-EO-G7	-	-	55.5	48 +0.3/-0.2	7.5	18	24	16	3	6.5	15
HGWM-12-EZ-G7											
HGWM-08-EO-G8	8	10	37	32 +0.3/-0.2	5 ±0.2	12	16	1.4 -0.1	2	4.3	10
HGWM-08-EZ-G8											
HGWM-12-EO-G8	12	15	55.5	48 +0.3/-0.2	7.5	18	24	1.4 -0.1	3	6.5	15
HGWM-12-EZ-G8											

Type	H10	H11 ±0.3	L1	L2 -0.02	T1 -0.2	T2 ¹⁾	W1 ±2°	W2 ±2°	W3 ±2°	≤G1
HGWM-08-EO-G6	32.4 ±0.6	9.5	14.2 -0.2	4	3	3.4 ±0.2	20°	4°	-	5.7
HGWM-08-EZ-G6						-	14°			
HGWM-12-EO-G6	47 ±0.6	12.5	20.2 -0.2	6	4	5.9	18.5°	3.5°	-	7.5
HGWM-12-EZ-G6						-	14°			
HGWM-08-EO-G7	-	-	-	4	-	3.4 ±0.2	20°	4°	-	12
HGWM-08-EZ-G7						-	14°			
HGWM-12-EO-G7	-	-	-	6	-	5.9	18.5°	3.5°	-	19
HGWM-12-EZ-G7						-	14°			
HGWM-08-EO-G8	5	-	4.5 -0.05	4	-	3.4 ±0.2	20°	4°	8°	-
HGWM-08-EZ-G8						-	14°			
HGWM-12-EO-G8	7	-	6.5 -0.05	6	-	5.9	18.5°	3.5°	8°	-
HGWM-12-EZ-G8						-	14°			


1) Do not exceed max. thread screw-in depth

Angle grippers HGWM, micro

Technical data and accessories

FESTO

Ordering data						
Single-acting	Size [mm]	Mounting options				
		With stroke compensation		With male thread		With clamping spigot
		Part No.	Type	Part No.	Type	Part No. Type
Gripper jaws open	8	185 693	HGWM-08-EO-G6	185 694	HGWM-08-EO-G7	185 695 HGWM-08-EO-G8
	12	185 699	HGWM-12-EO-G6	185 700	HGWM-12-EO-G7	185 701 HGWM-12-EO-G8
Gripper jaws closed	8	185 696	HGWM-08-EZ-G6	185 697	HGWM-08-EZ-G7	185 698 HGWM-08-EZ-G8
	12	185 702	HGWM-12-EZ-G6	185 703	HGWM-12-EZ-G7	185 704 HGWM-12-EZ-G8

Accessories	
For angle grippers with clamping flange	
Adapter kits A08 and A12	
	<p>In combination with semi-rotary drives DRQD-6 to 12</p> <p>→ Internet: drqd</p> <p>Adapter kits for drive/gripper combinations</p> <p>→ Internet: adapter kit</p>

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components

Complete custom engineered solutions



Custom Control Cabinets

Comprehensive engineering support and on-site services



Complete Systems

Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical

Electromechanical actuators, motors, controllers & drives



Pneumatics

Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices

PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

United States

Customer Resource Center

502 Earth City Expy., Suite 125
Earth City, MO 63045

For ordering assistance, or to find
your nearest Festo Distributor,

Call: 1.800.99.FESTO

Fax: 1.800.96.FESTO

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO

Fax: 1.800.96.FESTO

Email: product.support@us.festo.com

Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788
www.festo.com/us

Sales Offices

Appleton

N. 922 Tower View Drive, Suite N
Greenville, WI 54942

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057

Detroit - Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326

New York

395 Moreland Road
Hauppauge, NY 11788

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550

Design and Manufacturing Operations



East: 395 Moreland Road, Hauppauge, NY 11788



Central: 1441 East Business Center Drive, Mt. Prospect, IL 60056



West: 4935 Southfront Road, Suite F, Livermore, CA 94550

Mexico

Headquarters

Festo Pneumatic, S.A.
Av. Ceylán 3, Col. Tequesquahuac
54020 Tlalnepantla, Edo. de México
Call: 011 52 [55] 53 21 66 00
Fax: 011 52 [55] 53 21 66 65
Email: festo.mexico@mx.festo.com
www.festo.com/mx



Canada

Headquarters

Festo Inc.
5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Call: 1.905.624.9000
Fax: 1.905.624.9001
Email: info.ca@ca.festo.com
www.festo.com/ca



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan
Latvia Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com