

Solenoid valves VZWF, force pilot operated, NPT

FESTO



Solenoid valves VZWF, force pilot operated, NPT

Key features and overview

FESTO

Function

Normally closed solenoid valve with diaphragm and forced lifting. When the solenoid is energised, the differential pressure from the secondary side of the diaphragm is reduced via the servo hole. The effective differential pressure lifts

the diaphragm away from the valve seat. If there is no differential pressure, the diaphragm is lifted directly by the solenoid. The valve opens and closes without a differential pressure between the inlet and outlet.

General

- N- Connecting thread
NPT1/4 ... NPT2
-  - Flow rate Kv
1.8 ... 28 m³/h

Application


- Suitable for closed applications such as cooling or filling systems
- Vacuum
- Liquid gas
- Bottling systems

Design

- Diaphragm valves
- Forced lifting of the valve diaphragm
- 2/2-way valve, normally closed

Advantages

- Choice of sealing materials for different fields of applications
- Medium pressure 0 bar or higher

Version	Type	Process valve connection	Nominal size (DN)	Process valve nominal pressure (PN)	→ Page/Internet
	VZWF-...	NPT1/4	13.5	40	4
		NPT3/8	13.5		
		NPT1/2	13.5		
		NPT3/4	27.5		
		NPT1	27.5		
	VZWF-...	NPT114	40	40	8
		NPT112	40		
		NPT2	50		

Solenoid valves VZWF, force pilot operated, NPT

Type codes


		VZWF	-	B	-	L	-	M22C	-	G14	-	135	-	V	-	2AP4	-	10	-	R1
Type																				
VZWF	Solenoid valve, force pilot operated																			
Product version																				
	Standard																			
B	Optimised function																			
Type of directional control valve																				
L	In-line valve																			
Valve function																				
M22C	2/2-way valve, normally closed																			
Process valve connection																				
N14	NPT 1/4																			
N38	NPT 3/8																			
N12	NPT 1/2																			
N34	NPT 3/4																			
N1	NPT 1																			
N114	NPT1 1/4																			
N112	NPT1 1/2																			
N2	NPT 2																			
Nominal size (DN)																				
135	13.5 mm																			
275	27.5 mm																			
400	40 mm																			
500	50 mm																			
Sealing material																				
	Standard (NBR)																			
E	EPDM																			
V	FPM																			
Nominal operating voltage																				
1	24 V DC																			
2A	110 V AC/50-60 Hz																			
3A	230 V AC/50-60 Hz																			
Electrical connection																				
P4	Plug socket, 3-pin																			
Operating pressure																				
6	Max. 6 bar																			
10	Max. 10 bar																			
Corrosion protection																				
	Standard (brass)																			
R1	Stainless steel																			

Solenoid valves VZWF, force pilot operated, NPT

FESTO

Technical data

Function



 Flow rate Kv
1.8 ... 11 m³/h

-N- Connecting thread
NPT¹/₄ ... NPT1



General technical data					
Process valve connection	NPT ¹ / ₄	NPT ³ / ₈	NPT ¹ / ₂	NPT ³ / ₄	NPT1
Nominal size (DN)	13.5	13.5	13.5	27.5	27.5
Valve function	2/2-way, single solenoid, closed				
Design	Diaphragm valve, force pilot operated				
Type of mounting	In-line installation				
Actuation type	Electric				
Manual override	None				
Mounting position	Solenoid vertical				
Sealing principle	Soft				
Direction of flow	Non-reversible				
Max. viscosity [mm ² /s]	22				
Protection class	IP 65				
Product weight [g]	1,000			1,500	

Operating and environmental conditions					
Process valve connection	NPT ¹ / ₄	NPT ³ / ₈	NPT ¹ / ₂	NPT ³ / ₄	NPT1
Switching time on [ms]	130			275	
Switching time off [ms]	180			290	
Standard nominal flow rate [l/min]	1,920	2,350	2,660	8,020	11,750
Flow rate [m³/h]	1.8	2.2	2.5	7.5	11
Operating pressure [bar]	0 ... 10			0 ... 6	
Process valve nominal pressure (PN)	40				
Differential pressure [bar]	0				
Operating medium with NBR seal (standard)	Dried, filtered compressed air, neutral gases, vacuum, cold water				
Operating medium with EPDM seal	Filtered, unlubricated compressed air, neutral gases, unlubricated vacuum air, water				
Operating medium with FPM seal	Filtered compressed air 50 µm, neutral gases, vacuum, neutral liquids, water, mineral oil				
Ambient temperature [°C]	−10 ... +35 °C				
Temperature of medium [°C]	−10 ... +80 °C				
Leak rate to EN 12266-1	A				
Corrosion resistance class					
CRC ¹⁾ Brass	1				
CRC ²⁾ Stainless steel	3				

- 1) Corrosion resistance class 1 according to Festo standard 940 070
Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.
- 2) Corrosion resistance class 3 according to Festo standard 940 070
Components subject to high corrosion stress. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface.

Solenoid valves VZWF, force pilot operated, NPT

Technical data

Materials		
Solenoid valves		Material number
1 Housing	Brass casting	CW617N
	Stainless steel casting	1.4581
2 Screws	High-alloy stainless steel	1.4301
3 Seals	NBR, FPM, EPDM	–
– Note on materials	Contains PWIS (paint-wetting impairment substances), RoHS-compliant	

Electrical data						
			VZWF- ... 1	VZWF- ... 2A	VZWF- ... 3A	
Electrical connection			Plug to EN 175301-803 type A, square design			
CE mark as per EU Pressure Equipment Directive			–	Yes	Yes	
Coil characteristics for solenoid coil type VACS-H1P	Direct current DC	[V]	24	–	–	
	Alternating current AC	[V]	–	110	230	
		[W]	11	–	–	
	Switching power	[VA]	–	19	18	
	Holding power	[VA]	–	16	15	
		[Hz]	–	50, 60	50, 60	
Coil characteristics for solenoid coil type VACS-G2P	Direct current DC	[V]	24	–	–	
	Alternating current AC	[V]	–	110	230	
		[W]	30	–	–	
	Switching power	[VA]	–	30	30	
	Holding power	[VA]	–	30	30	
		[Hz]	–	50, 60	50, 60	
Permissible voltage fluctuations		[%]	±10			


Solenoid valves VZWF, force pilot operated, NPT

Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad



	B1	B2	D1	D2	H1	H2	H3	H4	L1	L2	L3	L4	L5	T1	T2	≙
VZWF-B-L-M22C-N14-135-...	48	30	NPT $\frac{1}{4}$	M4	101	85.6	42	7	92	67	58	25	21	12	4	27
VZWF-B-L-M22C-N14-135-...-R1	44	30	NPT $\frac{1}{4}$	M4	101	85.6	42	7	94	67	58	25	21	12	4	27
VZWF-B-L-M22C-N38-135-...	48	30	NPT $\frac{3}{8}$	M4	101	85.6	42	7	92	67	58	25	21	12	4	27
VZWF-B-L-M22C-N38-135-...-R1	44	30	NPT $\frac{3}{8}$	M4	101	85.6	42	7	94	67	58	25	21	12	4	27
VZWF-B-L-M22C-N12-135-...	48	30	NPT $\frac{1}{2}$	M4	101	85.6	42	7	92	67	58	25	21	12	4	27
VZWF-B-L-M22C-N12-135-...-R1	44	30	NPT $\frac{1}{2}$	M4	101	85.6	42	7	94	67	58	25	21	12	4	27
VZWF-B-L-M22C-N34-275-...	70	30	NPT $\frac{3}{4}$	M6	120	95.4	42	7	106	96	58	40	28	16	6	41
VZWF-B-L-M22C-N1-275-...	70	30	NPT1	M6	120	95.4	42	7	106	96	58	40	28	16	6	41




New

FESTO

Solenoid valves VZWF, force pilot operated, NPT

Technical data


Ordering data – Solenoid valve VZWF					
	Process valve connection	Brass housing		Stainless steel casting housing	
		Part No.	Type	Part No.	Type
	NPT $\frac{1}{4}$	1492174	VZWF-B-L-M22C-N14-135-E-1P4-10	1492166	VZWF-B-L-M22C-N14-135-1P4-10-R1
		1492158	VZWF-B-L-M22C-N14-135-1P4-10	1492182	VZWF-B-L-M22C-N14-135-E-1P4-10-R1
		1492254	VZWF-B-L-M22C-N14-135-2AP4-10	1492390	VZWF-B-L-M22C-N14-135-V-3AP4-10-R1
		1492350	VZWF-B-L-M22C-N14-135-3AP4-10	1492198	VZWF-B-L-M22C-N14-135-V-1P4-10-R1
		1492270	VZWF-B-L-M22C-N14-135-E-2AP4-10	1492262	VZWF-B-L-M22C-N14-135-2AP4-10-R1
		1492286	VZWF-B-L-M22C-N14-135-V-2AP4-10	1492278	VZWF-B-L-M22C-N14-135-E-2AP4-10-R1
		1492366	VZWF-B-L-M22C-N14-135-E-3AP4-10	1492294	VZWF-B-L-M22C-N14-135-V-2AP4-10-R1
		1492190	VZWF-B-L-M22C-N14-135-V-1P4-10	1492358	VZWF-B-L-M22C-N14-135-3AP4-10-R1
		1492382	VZWF-B-L-M22C-N14-135-V-3AP4-10	1492374	VZWF-B-L-M22C-N14-135-E-3AP4-10-R1
	NPT $\frac{3}{8}$	1492175	VZWF-B-L-M22C-N38-135-E-1P4-10	1492167	VZWF-B-L-M22C-N38-135-1P4-10-R1
		1492159	VZWF-B-L-M22C-N38-135-1P4-10	1492183	VZWF-B-L-M22C-N38-135-E-1P4-10-R1
		1492255	VZWF-B-L-M22C-N38-135-2AP4-10	1492391	VZWF-B-L-M22C-N38-135-V-3AP4-10-R1
		1492351	VZWF-B-L-M22C-N38-135-3AP4-10	1492199	VZWF-B-L-M22C-N38-135-V-1P4-10-R1
		1492191	VZWF-B-L-M22C-N38-135-V-1P4-10	1492263	VZWF-B-L-M22C-N38-135-2AP4-10-R1
		1492271	VZWF-B-L-M22C-N38-135-E-2AP4-10	1492279	VZWF-B-L-M22C-N38-135-E-2AP4-10-R1
		1492287	VZWF-B-L-M22C-N38-135-V-2AP4-10	1492295	VZWF-B-L-M22C-N38-135-V-2AP4-10-R1
		1492367	VZWF-B-L-M22C-N38-135-E-3AP4-10	1492359	VZWF-B-L-M22C-N38-135-3AP4-10-R1
		1492383	VZWF-B-L-M22C-N38-135-V-3AP4-10	1492375	VZWF-B-L-M22C-N38-135-E-3AP4-10-R1
	NPT $\frac{1}{2}$	1492176	VZWF-B-L-M22C-N12-135-E-1P4-10	1492168	VZWF-B-L-M22C-N12-135-1P4-10-R1
		1492256	VZWF-B-L-M22C-N12-135-2AP4-10	1492184	VZWF-B-L-M22C-N12-135-E-1P4-10-R1
		1492352	VZWF-B-L-M22C-N12-135-3AP4-10	1492392	VZWF-B-L-M22C-N12-135-V-3AP4-10-R1
		1492192	VZWF-B-L-M22C-N12-135-V-1P4-10	1492200	VZWF-B-L-M22C-N12-135-V-1P4-10-R1
		1492272	VZWF-B-L-M22C-N12-135-E-2AP4-10	1492264	VZWF-B-L-M22C-N12-135-2AP4-10-R1
		1492288	VZWF-B-L-M22C-N12-135-V-2AP4-10	1492280	VZWF-B-L-M22C-N12-135-E-2AP4-10-R1
		1492368	VZWF-B-L-M22C-N12-135-E-3AP4-10	1492296	VZWF-B-L-M22C-N12-135-V-2AP4-10-R1
		1492384	VZWF-B-L-M22C-N12-135-V-3AP4-10	1492360	VZWF-B-L-M22C-N12-135-3AP4-10-R1
		1492160	VZWF-B-L-M22C-N12-135-V-1P4-10	1492376	VZWF-B-L-M22C-N12-135-E-3AP4-10-R1
	NPT $\frac{3}{4}$	1492385	VZWF-B-L-M22C-N34-275-V-3AP4-6	1492169	VZWF-B-L-M22C-N34-275-1P4-6-R1
		1492161	VZWF-B-L-M22C-N34-275-1P4-6	1492185	VZWF-B-L-M22C-N34-275-E-1P4-6-R1
		1492257	VZWF-B-L-M22C-N34-275-2AP4-6	1492393	VZWF-B-L-M22C-N34-275-V-3AP4-6-R1
		1492353	VZWF-B-L-M22C-N34-275-3AP4-6	1492201	VZWF-B-L-M22C-N34-275-V-1P4-6-R1
		1492177	VZWF-B-L-M22C-N34-275-E-1P4-6	1492265	VZWF-B-L-M22C-N34-275-2AP4-6-R1
		1492193	VZWF-B-L-M22C-N34-275-V-1P4-6	1492281	VZWF-B-L-M22C-N34-275-E-2AP4-6-R1
		1492273	VZWF-B-L-M22C-N34-275-E-2AP4-6	1492297	VZWF-B-L-M22C-N34-275-V-2AP4-6-R1
		1492289	VZWF-B-L-M22C-N34-275-V-2AP4-6	1492361	VZWF-B-L-M22C-N34-275-3AP4-6-R1
		1492369	VZWF-B-L-M22C-N34-275-E-3AP4-6	1492377	VZWF-B-L-M22C-N34-275-E-3AP4-6-R1
	NPT1	1492162	VZWF-B-L-M22C-N1-275-1P4-6	1492170	VZWF-B-L-M22C-N1-275-1P4-6-R1
		1492258	VZWF-B-L-M22C-N1-275-2AP4-6	1492186	VZWF-B-L-M22C-N1-275-E-1P4-6-R1
		1492354	VZWF-B-L-M22C-N1-275-3AP4-6	1492394	VZWF-B-L-M22C-N1-275-V-3AP4-6-R1
		1492178	VZWF-B-L-M22C-N1-275-E-1P4-6	1492202	VZWF-B-L-M22C-N1-275-V-1P4-6-R1
		1492274	VZWF-B-L-M22C-N1-275-E-2AP4-6	1492266	VZWF-B-L-M22C-N1-275-2AP4-6-R1
		1492370	VZWF-B-L-M22C-N1-275-E-3AP4-6	1492282	VZWF-B-L-M22C-N1-275-E-2AP4-6-R1
		1492194	VZWF-B-L-M22C-N1-275-V-1P4-6	1492298	VZWF-B-L-M22C-N1-275-V-2AP4-6-R1
		1492290	VZWF-B-L-M22C-N1-275-V-2AP4-6	1492362	VZWF-B-L-M22C-N1-275-3AP4-6-R1
		1492386	VZWF-B-L-M22C-N1-275-V-3AP4-6	1492378	VZWF-B-L-M22C-N1-275-E-3AP4-6-R1

Solenoid valves VZWF, force pilot operated, NPT

FESTO

Technical data

Function



 Flow rate Kv
20 ... 28 m³/h

-N- Connecting thread
NPT1¼ ... NPT2



General technical data			
Process valve connection	NPT1¼	NPT1½	NPT2
Nominal size (DN)	40	40	50
Valve function	2/2-way, single solenoid, closed		
Design	Diaphragm valve, force pilot operated		
Type of mounting	In-line installation		
Actuation type	Electric		
Manual override	None		
Mounting position	Solenoid vertical		
Sealing principle	Soft		
Direction of flow	Non-reversible		
Max. viscosity [mm ² /s]	22		
Protection class	IP 65		
Product weight [g]	4,500		6,500

Operating and environmental conditions			
Process valve connection	NPT1¼	NPT1½	NPT2
Switching time on [ms]	620		1,220
Switching time off [ms]	1,140		2,140
Standard nominal flow rate [l/min]	21,370	23,500	29,900
Flow rate [m ³ /h]	20	22.5	28
Operating pressure [bar]	0 ... 10		0 ... 6
Process valve nominal pressure (PN)	40		
Differential pressure [bar]	0		
Operating medium with NBR seal (standard)	Dried, filtered compressed air, neutral gases, vacuum, cold water		
Operating medium with EPDM seal	Filtered, unlubricated compressed air, neutral gases, unlubricated vacuum air, water		
Operating medium with FPM seal	Filtered compressed air 50 µm, neutral gases, vacuum, neutral liquids, water, mineral oil		
Ambient temperature [°C]	-10 ... +35 °C		
Temperature of medium [°C]	-10 ... +80 °C		
Leak rate to EN 12266-1	A		
Corrosion resistance class			
CRC ¹⁾ Brass	1		
CRC ²⁾ Stainless steel	3		

- 1) Corrosion resistance class 1 according to Festo standard 940 070
Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.
- 2) Corrosion resistance class 3 according to Festo standard 940 070
Components subject to high corrosion stress. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface.

Solenoid valves VZWF, force pilot operated, NPT

Technical data

Materials		
Solenoid valves		Material number
1 Housing	Brass casting	CW617N
	Stainless steel casting	1.4581
2 Screws	High-alloy stainless steel	1.4301
3 Seals	NBR, FPM, EPDM	–
– Note on materials	Contains PWIS (paint-wetting impairment substances), RoHS-compliant	

Electrical data						
			VZWF- ... 1	VZWF- ... 2A	VZWF- ... 3A	
Electrical connection			Plug to EN 175301-803 type A, square design			
CE mark as per EU Pressure Equipment Directive			–	Yes	Yes	
Coil characteristics for solenoid coil type VACS-H1P	Direct current DC	[V]	24	–	–	
	Alternating current AC	[V]	–	110	230	
		[W]	11	–	–	
	Switching power	[VA]	–	19	18	
	Holding power	[VA]	–	16	15	
		[Hz]	–	50, 60	50, 60	
Coil characteristics for solenoid coil type VACS-G2P	Direct current DC	[V]	24	–	–	
	Alternating current AC	[V]	–	110	230	
		[W]	30	–	–	
	Switching power	[VA]	–	30	30	
	Holding power	[VA]	–	30	30	
		[Hz]	–	50, 60	50, 60	
Permissible voltage fluctuations		[%]	±10			


Solenoid valves VZWF, force pilot operated, NPT

Technical data

FESTO

Dimensions


Download CAD data → www.festo.com/en/engineering



	B1	B2	D1	H1	H2	H3	H4	L1	L2	L3	T1	≙
VZWF-L-M22C-N114-400-...	96	63	NPT1¼	205	172.2	59	17	148	140	76	22	58
VZWF-L-M22C-N112-400-...	96	63	NPT1½	205	172.2	59	17	148	140	76	22	58
VZWF-L-M22C-N2-500-...	112	63	NPT2	218	178.6	59	17	159	168	76	25	70

Solenoid valves VZWF, force pilot operated, NPT

Technical data

Ordering data – Solenoid valve VZWF					
	Process valve connection	Brass housing		Stainless steel casting housing	
		Part No.	Type	Part No.	Type
	NPT114	1492387	VZWF-L-M22C-N114-400-V-3AP4-10	1492171	VZWF-L-M22C-N114-400-1P4-10-R1
		1492163	VZWF-L-M22C-N114-400-1P4-10	1492187	VZWF-L-M22C-N114-400-E-1P4-10-R1
		1492259	VZWF-L-M22C-N114-400-2AP4-10	1492395	VZWF-L-M22C-N114-400-V-3AP4-10-R1
		1492355	VZWF-L-M22C-N114-400-3AP4-10	1492203	VZWF-L-M22C-N114-400-V-1P4-10-R1
		1492179	VZWF-L-M22C-N114-400-E-1P4-10	1492267	VZWF-L-M22C-N114-400-2AP4-10-R1
		1492195	VZWF-L-M22C-N114-400-V-1P4-10	1492283	VZWF-L-M22C-N114-400-E-2AP4-10-R1
		1492275	VZWF-L-M22C-N114-400-E-2AP4-10	1492299	VZWF-L-M22C-N114-400-V-2AP4-10-R1
		1492291	VZWF-L-M22C-N114-400-V-2AP4-10	1492363	VZWF-L-M22C-N114-400-3AP4-10-R1
		1492371	VZWF-L-M22C-N114-400-E-3AP4-10	1492379	VZWF-L-M22C-N114-400-E-3AP4-10-R1
	NPT112	1492388	VZWF-L-M22C-N112-400-V-3AP4-10	1492172	VZWF-L-M22C-N112-400-1P4-10-R1
		1492164	VZWF-L-M22C-N112-400-1P4-10	1492188	VZWF-L-M22C-N112-400-E-1P4-10-R1
		1492260	VZWF-L-M22C-N112-400-2AP4-10	1492396	VZWF-L-M22C-N112-400-V-3AP4-10-R1
		1492356	VZWF-L-M22C-N112-400-3AP4-10	1492204	VZWF-L-M22C-N112-400-V-1P4-10-R1
		1492180	VZWF-L-M22C-N112-400-E-1P4-10	1492268	VZWF-L-M22C-N112-400-2AP4-10-R1
		1492196	VZWF-L-M22C-N112-400-V-1P4-10	1492284	VZWF-L-M22C-N112-400-E-2AP4-10-R1
		1492276	VZWF-L-M22C-N112-400-E-2AP4-10	1492300	VZWF-L-M22C-N112-400-V-2AP4-10-R1
		1492292	VZWF-L-M22C-N112-400-V-2AP4-10	1492364	VZWF-L-M22C-N112-400-3AP4-10-R1
		1492372	VZWF-L-M22C-N112-400-E-3AP4-10	1492380	VZWF-L-M22C-N112-400-E-3AP4-10-R1
	NPT2	1492165	VZWF-L-M22C-N2-500-1P4-6	1492173	VZWF-L-M22C-N2-500-1P4-6-R1
		1492261	VZWF-L-M22C-N2-500-2AP4-6	1492189	VZWF-L-M22C-N2-500-E-1P4-6-R1
		1492357	VZWF-L-M22C-N2-500-3AP4-6	1492397	VZWF-L-M22C-N2-500-V-3AP4-6-R1
		1492181	VZWF-L-M22C-N2-500-E-1P4-6	1492205	VZWF-L-M22C-N2-500-V-1P4-6-R1
		1492277	VZWF-L-M22C-N2-500-E-2AP4-6	1492269	VZWF-L-M22C-N2-500-2AP4-6-R1
		1492373	VZWF-L-M22C-N2-500-E-3AP4-6	1492365	VZWF-L-M22C-N2-500-3AP4-6-R1
		1492197	VZWF-L-M22C-N2-500-V-1P4-6	1492301	VZWF-L-M22C-N2-500-V-2AP4-6-R1
		1492293	VZWF-L-M22C-N2-500-V-2AP4-6	1492285	VZWF-L-M22C-N2-500-E-2AP4-6-R1
		1492389	VZWF-L-M22C-N2-500-V-3AP4-6	1492381	VZWF-L-M22C-N2-500-E-3AP4-6-R1

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com