

Solenoid valves VZWM-L, NPT

FESTO



Solenoid valves VZWM-L, NPT

FESTO

Key features and type codes

General

- Indirectly actuated diaphragm valve
- Process valve connection
N14 ... N2
- Flow rate
1,400 ... 31,000 l/min
- Available in brass or stainless steel casting
- Wide range of coils


		VZWM	–	L	–	M22C	–	N14	–	F4	–	
Type												
VZWM	Solenoid valve, process directional control valve											
Design												
L	In-line valve											
Valve function												
M22C	2/2-way valve, normally closed											
Process valve connection												
N14	NPT1/4											
N38	NPT3/8											
N12	NPT1/2											
N34	NPT3/4											
N1	NPT1											
N114	NPT1 1/4											
N112	NPT1 1/2											
N2	NPT2											
Electrical connection												
F4	MD-2-With armature tube for solenoid coil MD-2- ... -PA (system 8)											
F5	MH-2-With armature tube for solenoid coil MH-2- ... -PA (system 13)											
Housing material												
R1	Stainless steel casting											
	Brass											

Solenoid valves VZWM-L, NPT

FESTO

Technical data

Function



-  - Flow rate
1,400 ... 31,000 l/min

-  - Voltage
24 V DC
110, 230 V AC



General technical data											
Process valve connection			NPT1/4	NPT3/8	NPT1/2	NPT3/4	NPT1	NPT1 1/4	NPT1 1/2	NPT2	
Nominal size (DN)			[mm]	13.5	13.5	13.5	27.5	27.5	40	40	50
Valve function			2/2-way, single solenoid								
Design			Diaphragm valve								
Sealing principle			Soft								
Actuation type			Electric								
Reset method			Pneumatic spring								
Type of control			Piloted								
Direction of flow			Non-reversible								
Exhaust function			No flow control								
Manual override			None								
Type of mounting			In-line installation								
Mounting position			Preferably vertical								
Standard nominal flow rate			[l/min]	1,400	2,100	2,400	10,000	11,700	24,000	26,400	31,000
Flow rate Kv			[m³/h]	1.6	2	2.4	8.5	10.7	21.3	27.4	39
c value			[l/sbar]	6	8.8	9.8	39	41	75	82	110
b value				0.3	0.35	0.37	0.5	0.5	0.6	0.67	0.68
Pressure differential			[bar]	0.5	0.5	0.5	0.5	0.5	0.7	0.7	0.7
Materials	Housing		Brass or stainless steel casting								
	Diaphragm		Nitrile rubber								
	Armature tube		High-alloy steel								
Note on materials			Contains PWIS (paint-wetting impairment substances)								
Max. tightening torque	Connecting thread		[Nm]	35	60	105	200	350	450	540	620
	Cover screw		[Nm]	20	20	20	30	30	30	30	30
	Coil mounting		[Nm]	2	2	2	2	2	2	2	2

Operating and environmental conditions										
Process valve connection			NPT1/4	NPT3/8	NPT1/2	NPT3/4	NPT1	NPT1 1/4	NPT1 1/2	NPT2
Operating medium			Filtered, lubricated compressed air, grade of filtration 50 µm, neutral gases, water, neutral liquids							
Process valve operating pressure	Gases	[bar]	0.5 ... 10					0.7 ... 10		
	Liquids	[bar]	0.5 ... 6					0.7 ... 6		
Ambient temperature ¹⁾		[°C]	-10 ... +60							
Temperature of medium	Gases	[°C]	-10 ... +60							
	Liquids	[°C]	5 ... 50							
Max. viscosity		[mm ² /s]	22							
Corrosion resistance class CRC ²⁾	Brass		1							
	Stainless steel casting		3							

1) Note ambient temperature of solenoid coils

2) Corrosion resistance class 1 according to Festo standard 940 070

Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Corrosion resistance class 3 according to Festo standard 940 070

Components subject to high corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as solvents and cleaning agents.

Solenoid valves VZWM-L, NPT

Technical data

FESTO

Valve switching times										
Process valve connection			NPT1/4	NPT3/8	NPT1/2	NPT3/4	NPT1	NPT1 1/4	NPT1 1/2	NPT2
Gases										
Switching time	Off	[ms]	10	10	10	12	12	20	20	21
	On	[ms]	8	8	8	15	15	26	26	62
Liquids										
Switching time	Off	[ms]	200	210	220	930	930	1,900	2,000	2,800
	On	[ms]	100	110	110	400	400	1,400	1,400	2,100
Switching time of variant R1	Off	[ms]	210	190	200	950	950	1,900	2,000	2,800
	On	[ms]	80	110	110	420	300	1,400	1,400	2,100

Electrical data										
			NPT1/4	NPT3/8	NPT1/2	NPT3/4	NPT1	NPT1 1/4	NPT1 1/2	NPT2
Electrical connection			F4, with armature tube for solenoid coil MD-2- ... -PA (system 8), must be ordered separately					MH-2-F5, with armature tube for solenoid coil MH-2- ... -PA (system 13), must be ordered separately		
Operating voltage	DC voltage	[V DC]	24							
	AC voltage	[V AC]	110/230 (50 ... 60 Hz)							
Coil characteristics	DC voltage	[W]	6.8					7.9		
	AC voltage	[VA]	Pull: 14.5 Hold: 10.5					14		
Protection class to EN 60529			IP65 (with plug socket)							

Weight [g]										
Brass housing					Stainless steel casting housing					
VZWM-L-M22C-N14-F4	500				VZWM-L-M22C-N14-F5-R1	400				
VZWM-L-M22C-N38-F4	450				VZWM-L-M22C-N38-F5-R1	400				
VZWM-L-M22C-N12-F4	415				VZWM-L-M22C-N12-F5-R1	400				
VZWM-L-M22C-N34-F4	1,220				VZWM-L-M22C-N34-F5-R1	1,200				
VZWM-L-M22C-N1-F4	1,200				VZWM-L-M22C-N1-F5-R1	1,100				
VZWM-L-M22C-N114-F5	2,700				VZWM-L-M22C-N114-F5-R1	2,600				
VZWM-L-M22C-N112-F5	2,510				VZWM-L-M22C-N112-F5-R1	2,500				
VZWM-L-M22C-N2-F5	4,000				VZWM-L-M22C-N2-F5-R1	3,700				

Solenoid valves VZWM-L, NPT


Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad

2/2-way valve



Type	B ±1.5	D	D1	H ±2	H1 ±1.5	H2 ±1	L ±2	L1 ±1.5	L2	F	t1 ±1.5	⌀
VZWM-L-M22C-N14-F4	48	NPT1/4	M4	85.5	15	49	67	25	21	F5	4	27
VZWM-L-M22C-N38-F4	48	NPT3/8	M4	85.5	15	49	67	25	21	F5	4	27
VZWM-L-M22C-N12-F4	48	NPT1/2	M4	85	15	49	67	25	21	F5	4	27
VZWM-L-M22C-N34-F4	70	NPT3/4	M6	107	24.2	70.5	96	40	28	F5	6	41
VZWM-L-M22C-N1-F4	70	NPT1	M6	107	24.2	70.5	96	40	28	F5	6	41
VZWM-L-M22C-N114-F5	96	NPT1 1/4	M6	143.5	32.5	87	140	59.5	40.25	F5	6	58
VZWM-L-M22C-N112-F5	96	NPT1 1/2	M6	143.5	32.5	87	140	59.5	40.25	F5	6	58
VZWM-L-M22C-N2-F5	112	NPT2	M6	159	38.5	103.5	168	59.5	54.25	F5	6	70
VZWM-L-M22C-N14-F5-R1	44	NPT1/4	M4	106	15.6	51	67	25	21	F4	4	27
VZWM-L-M22C-N38-F5-R1	44	NPT3/8	M4	106	15.6	51	67	25	21	F4	4	27
VZWM-L-M22C-N12-F5-R1	44	NPT1/2	M4	106	15.6	51	67	25	21	F4	4	27
VZWM-L-M22C-N34-F5-R1	70	NPT3/4	M6	126	24.2	70	96	40	28	F4	6	41
VZWM-L-M22C-N1-F5-R1	70	NPT1	M6	126	24.2	70	96	40	28	F4	6	41
VZWM-L-M22C-N114-F5-R1	96	NPT1 1/4	M6	145	34	89.5	140	59.5	40.25	F5	6	58
VZWM-L-M22C-N112-F5-R1	96	NPT1 1/2	M6	145	34	89.5	140	59.5	40.25	F5	6	58
VZWM-L-M22C-N2-F5-R1	112	NPT2	M6	159	38.5	104	168	59.5	40.25	F5	6	70

Ordering data

Process valve connection	Brass housing		Stainless steel casting housing	
	Part No.	Type	Part No.	Type
NPT1/4	546 154	VZWM-L-M22C-N14-F4	546 170	VZWM-L-M22C-N14-F5-R1
NPT3/8	546 155	VZWM-L-M22C-N38-F4	546 171	VZWM-L-M22C-N38-F5-R1
NPT1/2	546 156	VZWM-L-M22C-N12-F4	546 172	VZWM-L-M22C-N12-F5-R1
NPT3/4	546 157	VZWM-L-M22C-N34-F4	546 173	VZWM-L-M22C-N34-F5-R1
NPT1	546 158	VZWM-L-M22C-N1-F4	546 174	VZWM-L-M22C-N1-F5-R1
NPT1 1/4	546 159	VZWM-L-M22C-N114-F5	546 175	VZWM-L-M22C-N114-F5-R1
NPT1/2	546 160	VZWM-L-M22C-N112-F5	546 176	VZWM-L-M22C-N112-F5-R1
NPT2	546 161	VZWM-L-M22C-N2-F5	546 177	VZWM-L-M22C-N2-F5-R1

Solenoid valves VZWM-L


Accessories

FESTO


Mounting bracket HRM

Material:

Galvanised steel



Dimensions and ordering data											
B	B1	B2	D Ø	D1 Ø	H	H1	L	L1	Weight [g]	Part No.	Type
25	12.5	2	6	5	37	10	40	25	39	9 769	HRM-1
35	17.5	3	7	7	66	16	55	40	130	9 770	HRM-2
47	23.5	3	9	7	87	23	75	59.5	246	9 771	HRM-3

Ordering data – Solenoid coils				Technical data ➔ Internet: solenoid coil	
	Voltage	Part No.	Type		
Solenoid coil for VZWM- ... -F4- ... (system 8) ¹⁾					
	24 V DC	549 903	MD-2-24VDC-PA		
	110 V AC, 50 ... 60 Hz	549 904	MD-2-110VAC-PA		
	230 V AC, 50 ... 60 Hz	549 905	MD-2-230VAC-PA		
Solenoid coil for VZWM- ... -F5- ... (system 13) ¹⁾					
	24 V DC	549 906	MH-2-24VDC-PA		
	110 V AC, 50 ... 60 Hz	549 907	MH-2-110VAC-PA		
	230 V AC, 50 ... 60 Hz	549 908	MH-2-230VAC-PA		

1) Ambient temperature –20 ... 50 °C

Ordering data – Plug socket			Technical data → Internet: mssd-n	
		Part No.	Type	
	3-pin, square design MSF	550 067	MSSD-N	

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788
Phone: 1.631.435.0800; Fax: 1.631.435.8026;
Email: info@festo-usa.com www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4
Phone: 1.905.624.9000; Fax: 1.905.624.9001;
Email: festo.canada@ca.festo.com www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México
Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;
Email: festo.mexico@mx.festo.com www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com