

Pressure and vacuum switches PEV/VPEV, PE converters PE/PEN/VPE

FESTO

Product overview



- Mechanical pressure and vacuum switches with adjustable switching point
- PE converter
- Designs with adjustable hysteresis
- Designs with switching status display
- Variant with scale for pressure adjustment
- Wide range of mounting options

Detailed product information

→ www.festo.com/catalog/pev

Product overview							
Method of measurement	Operating pressure [bar]	Type	Pneumatic connection	Type of mounting	Max. switching output voltage		➔ Page/ Internet
					[V DC]	[V AC]	
Pressure switches							
Pneumatic/electrical pressure transducer	1 ... 12	PEV-1/4-B-M12	G1/4	With through-holes	48	48	2
		PEV-1/4-B			125	250	
		PEV-1/4-SC-OD			125	250	
	0 ... 8	PEV-W	M5	Via DIN H-rail	10 ... 30	–	4
	1 ... 10	PEV-1/4-A	G1/4	Screw-in	250	250	6
Vacuum switches							
Pneumatic/electrical pressure transducer	–1 ... 1.6	VPEV-1/8-M12	G1/8	Via through-hole	48	48	2
		VPEV-1/8			125	250	
	–1 ... 0	VPEV-W	M5	Via DIN H-rail	10 ... 30	–	4
PE converter							
Pneumatic/electrical differential pressure switch	–1 ... +8	PEN-M5	M5	On mounting frame 2N	10 ... 30	–	7
Pneumatic/electrical pressure transducer	0 ... 8	PE-1/8-2N	G1/8	On mounting frame 2N	12 ... 250	12 ... 250	
	–0.95 ... 0	VPE-1/8-2N	G1/8	On mounting frame 2N	12 ... 250	12 ... 250	

Pressure and vacuum switches PEV/VPEV, with through-holes

FESTO

Type codes, technical data

Type codes

		PEV	-	1/4	-	B	-		-		-	
Type												
PEV	Pressure switch											
VPEV	Vacuum switch											
Pneumatic connection												
1/8	G1/8											
1/4	G1/4											
Generation												
B	B series											
Electrical connection												
-	Plug, square design to EN 43 650, type A											
M12	Plug, M12x1, 4-pin, round design											
Setting options												
SC	Scale for pressure adjustment											
Plug socket												
-	Included in scope of delivery											
OD	Not included in scope of delivery											

Technical data					
Type		PEV-1/4-B-M12	PEV-1/4-B(-OD) PEV-1/4-SC-OD	VPEV-1/8-M12	VPEV-1/8
Design					
Pneumatic connection		G1/4		G1/8	
Electrical data					
Max. switching output voltage	[V DC]	48	125	48	125
	[V AC]	48	250	48	250
Switching element function		Changeover switch			
Max. output current	[mA]	5,000		–	
Protection against short circuit		No			
Protection against polarity reversal		Yes			
Protection class		IP65			
Operating and environmental conditions					
Operating medium		Filtered compressed air, lubricated or unlubricated Water Mineral oil		Filtered compressed air, lubricated or unlubricated Vacuum, lubricated or unlubricated	
Operating pressure	[bar]	1 ... 12		–1 ... +1.6	
Ambient temperature	[°C]	–20 ... +80			
CE mark (see declaration of conformity)		In accordance with EU Low Voltage Directive			
Certification		CCC			
		c UL us - Recognized (OL)	–	c UL us - Recognized (OL)	–
Materials					
Housing		Wrought aluminium alloy			
Note on materials		RoHS-compliant		RoHS-compliant	


Pressure and vacuum switches PEV/VPEV, with through-holes

FESTO

Technical data, peripherals overview

Ordering data						
Description	Electrical connection	Adjustable hysteresis	Visual scale for pressure adjustment	Plug socket in scope of delivery	Part No.	Type
Pressure switches						
	Plug, square design to DIN 43650, type A	■	–	■	10773	PEV-1/4-B
		■	–	–	175250	PEV-1/4-B-OD
		–	■	–	161760	PEV-1/4-SC-OD
	Plug M12x1, 4-pin	■	–	–	192488	PEV-1/4-B-M12
Vacuum switches						
	Plug, square design to DIN 43650, type A	■	–	■	150261	VPEV-1/8
	Plug M12x1, 4-pin	■	–	–	192489	VPEV-1/8-M12

Peripherals overview



Accessories	
1	Pressure switch PEV-1/4-B..., vacuum switch VPEV-1/8
2	Pressure switch PEV-1/4-B-OD...
3	Pressure switch PEV-1/4-SC-OD... with scale for pressure adjustment
4	Pressure switch PEV-1/4-B-M12, vacuum switch VPEV-1/8-M12
5	Plug socket PEV-1/4-WD-LED... with switching status display Plug socket MSSD-C-4P without switching status display
6	Connecting cable NEBU-M12G5-... with straight socket
7	Connecting cable NEBU-M12W5-... with angled socket
8	Push-in fitting QS...
9	Mounting plate APL-2N-PEV
10	Mounting frame NRRQ-2N

Ordering data – Plug sockets

	Description	Part No.	Type
	With switching status display	164274	PEV-1/4-WD-LED-24
		164275	PEV-1/4-WD-LED-230
	Without switching status display	171157	MSSD-C-4P

Ordering data – Connecting cables

Technical data → Internet: nebu

	Number of wires	Cable length [m]	Part No.	Type
M12x1, straight socket				
	4	5	541328	NEBU-M12G5-K-5-LE4
M12x1, angled socket				
	4	5	541329	NEBU-M12W5-K-5-LE4

Ordering data – Push-in fittings

Technical data → Internet: quick star

	Part No.	Type
	186097	QS-G1/4-6
	186099	QS-G1/4-8

Ordering data – Mounting attachments

	Part No.	Type
	9349	APL-2N-PEV
	9365	NRRQ-2N
	11571	NRW-9/1,5-B

Pressure and vacuum switches PEV-W/VPEV-W, DIN H-rail mounting

FESTO

Type codes, technical data



Type codes

		PEV-W	–	KL	–	LED	–	GH
Type								
PEV-W	Pressure switch							
VPEV-W	Vacuum switch							
Electrical connection								
KL	Screw terminal, 4-pin							
S	Plug, M8x1, 4-pin							
Switching status display								
LED	Yellow LED							
Type of mounting								
GH	Via DIN H-rail or via through-holes							

Technical data

Type	PEV-W	VPEV-W	
Design			
Pneumatic connection	M5	M5	
Electrical data			
Operating voltage range	[V DC]	10 ... 30	10 ... 30
	[V AC]	–	–
Switching element function	Changeover switch		
Max. output current	[mA]	2,500	2,500
Protection against short circuit	No		
Protection against polarity reversal	Yes		
Protection class	IP65		
Operating and environmental conditions			
Operating medium	Filtered compressed air, lubricated or unlubricated		Filtered compressed air, lubricated or unlubricated Vacuum, lubricated or unlubricated
Operating pressure	[bar]	0 ... 8	0 ... –1
Ambient temperature	[°C]	–20 ... +80	
CE mark (see declaration of conformity)	In accordance with EU EMC directive		
Materials			
Housing	Wrought aluminium alloy		
Note on materials	RoHS-compliant		

Ordering data


Description	Electrical connection	Plug socket in scope of delivery	Part No.	Type
Pressure switches				
	Screw terminal, 4-pin	–	152618	PEV-W-KL-LED-GH
	Plug, M8x1, 4-pin	–	152616	PEV-W-S-LED-GH
Vacuum switches				
	Screw terminal, 4-pin	–	152619	VPEV-W-KL-LED-GH
	Plug, M8x1, 4-pin	–	152617	VPEV-W-S-LED-GH

Pressure and vacuum switches PEV-W/VPEV-W, DIN H-rail mounting

Peripherals overview

FESTO

Peripherals overview



Accessories

1	Pressure switch PEV-W-S-... with plug M8x1 Vacuum switch VPEV-W-S-... with plug M8x1
2	Pressure switch PEV-W-KL-... with screw terminals Vacuum switch VPEV-W-KL-... with screw terminals
3	Connecting cable NEBU-M8G4-... with straight socket
4	Connecting cable NEBU-M8W4-... with angled socket
5	Push-in fitting QSM-M5
6	Mounting latch PENV-BGH
7	Mounting rail to DIN EN 60715
8	Mounting rail to DIN EN 50035

Ordering data – Connecting cables

Technical data → Internet: nebu

	Number of wires	Cable length [m]	Part No.	Type
M8x1, straight socket				
	4	2.5	541342	NEBU-M8G4-K-2.5-LE4
	5		541343	NEBU-M8G4-K-5-LE4
M8x1, angled socket				
	4	2.5	541344	NEBU-M8W4-K-2.5-LE4
	5		541345	NEBU-M8W4-K-5-LE4

Ordering data – Push-in fittings

Technical data → Internet: quick star

	For tubing O.D. [mm]	Part No.	Type
	3	153302	QSM-M5-3
	4	153304	QSM-M5-4
	6	153306	QSM-M5-6

Ordering data – Accessories

	Part No.	Type
	164597	PENV-BGH

Pressure switches PEV, screw-in

Type codes, technical data

FESTO

Type codes

		PEV	-	1/4	-	A	-	SW27	-	
Type										
PEV	Pressure switch									
Pneumatic connection										
1/4	G1/4									
Generation										
A	A series									
Width across flats										
SW27	27 mm									
Electrical connection										
-	For plug socket PEV-1/4-A-WD									
B-OD	For plug socket PEV-1/4-WD-LED-...									

Technical data

Type	PEV-1/4-A-SW27		PEV-1/4-A-SW27-B-OD
Design			
Pneumatic connection	G1/4		
Electrical data			
Operating voltage range	[V DC]	12 ... 250	
Max. switching output voltage	[V DC]	250	
	[V AC]	250	
Switching element function	Changeover switch		
Max. output current	[mA]	4,000	
Protection against short circuit	No		
Protection against polarity reversal	No		
Protection class	IP65		
Operating and environmental conditions			
Operating medium	Filtered compressed air, lubricated or unlubricated		
Operating pressure	[bar]	1 ... 10	
Ambient temperature	[°C]	-30 ... +100	-20 ... +100
CE mark (see declaration of conformity)	In accordance with EU Low Voltage Directive		
Materials			
Housing	Galvanised steel		

Ordering data

		Electrical connection	Plug socket in scope of delivery	Part No.	Type
		Plug, 4-pin	-	159259	PEV-1/4-A-SW27
		Plug, 4-pin	-	175252	PEV-1/4-A-SW27-B-OD

Ordering data – Plug sockets

		Description	Operating voltage range		Part No.	Type
			[V DC]	[V AC]		
		For pressure switch PEV-1/4-A-SW27	≤180	≤230	161209	PEV-1/4-A-WD
		For pressure switch PEV-1/4-A-SW27-B-OD	15 ... 30	-	164274	PEV-1/4-WD-LED-24
			≤180	≤230	164275	PEV-1/4-WD-LED-230

PE converter PE/PEN/VPE

Type codes, technical data

FESTO

Type codes

		PE	–	1/8	–	2N	–	SW
Type								
PE	PE converter							
PEN	PE converter							
VPE	PE converter for vacuum							
Pneumatic connection								
1/8	G1/8							
M5	Female thread M5							
Type of mounting								
2N	On mounting frame 2N							
Width across flats								
SW	Splash proof design							




Technical data

Type		PE-1/8-2N	PE-1/8-2N-SW	PEN-M5	VPE-1/8-2N	VPE-1/8-2N-SW
Design						
Pneumatic connection		G1/8		M5	G1/8	
Electrical data						
Operating voltage range	[V DC]	12 ... 250		12 ... 30	12 ... 250	
	[V AC]	12 ... 250		–	12 ... 250	
Switch output		–		PNP	–	
Switching element function		Changeover switch		N/O contact	Changeover switch	
Max. output current	[mA]	4,000				
Minimum load current	[mA]	100		–	100	
Protection against short circuit		No		Yes	No	
Protection against polarity reversal		No				
Protection class		IP00, IP20 with protective cap	IP67	IP67	IP00, IP20 with protective cap	IP67
Operating and environmental conditions						
Operating medium		Filtered compressed air, lubricated or unlubricated, grade of filtration 40 µm				
		–				Vacuum
Operating pressure	[bar]	0 ... 8		–1 ... +8	–0.95 ... 0	
Ambient temperature	[°C]	0 ... 60		–20 ... +60	0 ... 60	
CE mark (see declaration of conformity)		In accordance with EU Low Voltage Directive		In accordance with EU EMC directive	In accordance with EU Low Voltage Directive	
Certification		CCC		–	CCC	
Materials						
Housing		Die-cast aluminium, polyamide		Die-cast zinc	Die-cast aluminium, polyamide	

PE converters PE/PEN/VPE

Technical data

FESTO

Ordering data				
	Operating pressure [bar]	Electrical connection	Part No.	Type
	0 ... 8	Screw terminal	7860	PE-1/8-2N
		3 wires	7862	PE-1/8-2N-SW
	-1 ... +8	Cable, 3-wire	8625	PEN-M5
	-0.95 ... 0	Screw terminal	12594	VPE-1/8-2N
		3 wires	12595	VPE-1/8-2N-SW

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788
Phone: 1.631.435.0800; Fax: 1.631.435.8026;
Email: info@festo-usa.com www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4
Phone: 1.905.624.9000; Fax: 1.905.624.9001;
Email: festo.canada@ca.festo.com www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México
Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;
Email: festo.mexico@mx.festo.com www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com