

Membrane air dryers MS-LDM1, MS series



FESTO



Membrane air dryers MS-LDM1, MS series

Product range overview – MS series service units

FESTO

Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]						Grade of filtration [μm]			
				0.05	0.05	0.1	0.3	0.1	0.5	0.01
Code		AG...		D2	D4	D5	D6	D7	D8	A	B	C	E
Service units													
MSB-FRC		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	■	■	–	–	–	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	■	■	–	–	–	■
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–
Service unit combinations (further variants can be ordered using the configurator → Internet: msb4, msb6 or msb9)													
MSB		4	G1/4	G1/8, G1/4, G3/8	–	–	–	■	■	–	–	–	■
		6	G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	■	■	–	–	–	■
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–
Individual devices													
Filter regulators MS-LFR		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	–	–	–	■
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	■	■	■	–	–	–	■
		12	–	G1, G11/4, G11/2, G2	–	–	–	■	■	–	–	–	■
Filters MS-LF		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	■
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	–	–	■
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	–	–	■
Fine and micro filters MS-LFM		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	■	■	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	■	■	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	■	■	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	■	■	–
Activated carbon filters MS-LFX		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	–	–	–
Water separators MS-LWS		4	–	–	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	–	–	–

Membrane air dryers MS-LDM1, MS series

FESTO

Product range overview – MS series service units

Type	Size	Bowl guard		Condensate drains				Pressure indicator				Security		Options		➔ Page/ Internet		
		Plastic bowl with plastic bowl guard	Metal bowl	Manual rotary	Semi-automatic	Fully automatic	External, fully automatic, electrical	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G1/8	Adapter plate for EN pressure gauge G1/4	Pressure sensor	Rotary knob with detent, lockable via accessories	Rotary knob with integrated lock	Silencer	Flow direction from right to left		
Code		R	U	M	H	V	E...	VS	AG	A8	A4	AD...	AS	E11	S	Z		
Service units																		
MSB-FRC	4	■	–	■	–	■	–	–	■	–	–	–	■	–	–	■	msb4	
	6	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	msb6	
	9	–															–	
	12	–															–	
Service unit combinations																		
MSB	4	■	■	■	■	–	■	–	–	■	–	–	■	–	–	■	msb4	
	6	■	■	■	■	–	■	–	–	■	–	–	■	–	–	■	msb6	
	9	–															–	
	12	–															–	
Individual devices																		
Filter regulators MS-LFR	4	■	■	■	■	■	■	–	■	■	■	■	■	■	■	–	■	ms4-lfr
	6	■	■	■	■	■	■	■	■	–	■	■	■	■	■	–	■	ms6-lfr
	9	–	■	■	■	■	■	■	■	–	■	■	■	■	■	–	■	ms9-lfr
	12	–	■	■	■	–	■	■	■	–	■	–	■	■	■	–	■	ms12-lfr
Filters MS-LF	4	■	■	■	■	■	■	■	–	–	–	–	–	–	–	–	■	ms4-lf
	6	■	■	■	■	■	■	■	■	–	–	–	–	–	–	–	■	ms6-lf
	9	–	■	■	■	■	■	■	■	–	–	–	–	–	–	–	■	ms9-lf
	12	–	■	■	■	–	■	■	■	–	–	–	–	–	–	–	■	ms12-lf
Fine and micro filters MS-LFM	4	■	■	■	■	■	■	–	–	–	–	–	–	–	–	–	■	ms4-lfm
	6	■	■	■	■	■	■	■	■	–	–	–	–	–	–	–	■	ms6-lfm
	9	–	■	■	■	■	■	■	■	–	–	–	–	–	–	–	■	ms9-lfm
	12	–	■	■	■	–	■	■	■	–	–	–	–	–	–	–	■	ms12-lfm
Activated carbon filters MS-LFX	4	■	■	■	–	–	–	–	–	–	–	–	–	–	–	–	■	ms4-lfx
	6	■	■	■	–	–	–	–	–	–	–	–	–	–	–	–	■	ms6-lfx
	9	–	■	–	–	–	–	–	–	–	–	–	–	–	–	–	■	ms9-lfx
	12	–	■	–	–	–	–	–	–	–	–	–	–	–	–	–	■	ms12-lfx
Water separators MS-LWS	4	–															–	
	6	–	■	–	–	■	■	–	–	–	–	–	–	–	–	–	■	ms6-lws
	9	–	■	–	–	■	■	–	–	–	–	–	–	–	–	–	■	ms9-lws
	12	–	■	–	–	–	■	■	–	–	–	–	–	–	–	–	■	ms12-lws

Membrane air dryers MS-LDM1, MS series

Product range overview – MS series service units

FESTO

Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]						Supply voltage			
				0.05	0.05	0.1	0.3	0.1	0.5	24 VDC, connection pattern to EN 175301	24 VDC, connection M12 to IEC 61076-2-101	110 VAC, connection pattern to EN 175301	230 VAC, connection pattern to EN 175301
Code		AG...		D2	D4	D5	D6	D7	D8	V24	V24P	V110	V230
Individual devices													
Pressure regulators MS-LR		4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	■	■	■	-	-	-	-
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	■	■	■	■	-	-	-
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	-	-	■	■	■	■	-	-	-
		12	-	G1, G11/4, G11/2, G2	-	-	-	■	■	■	-	-	-
Pressure regulators MS-LRB		4	G1/4	G1/8, G1/4, G3/8	-	-	■	■	■	-	-	-	-
		6	G1/2	G1/4, G3/8, G1/2, G3/4	-	-	■	■	■	■	-	-	-
		9	-										
		12	-										
Precision pressure regulators MS-LRP		4	-										
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	-	■	-	-	-	-
		9	-										
		12	-										
Precision pressure regulators MS-LRPB		4	-										
		6	G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	-	■	-	-	-	-
		9	-										
		12	-										
Electrical pressure regulators MS-LRE		4	-										
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	■	■	■	■	-	-	-
		9	-										
		12	-										
Lubricators MS-LOE		4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	-	-	-	-	-	-
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	-	-	-	-
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	-	-	-	-	-	-	-	-	-
		12	-	G1, G11/4, G11/2, G2	-	-	-	-	-	-	-	-	-
On-off valves, manually actuated MS-EM(1)		4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	-	-	-	-	-	-
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	-	-	-	-
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	-	-	-	-	-	-	-	-	-
		12	-	G1, G11/4, G11/2, G2	-	-	-	-	-	-	-	-	-
On-off valves, electrically actuated MS-EE		4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	-	-	■	-	■	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	■	-	■	■
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	-	-	-	-	-	■	■	■	■
		12	-	G1, G11/4, G11/2, G2	-	-	-	-	-	■	■	■	■
Soft-start valves, pneumatically actuated MS-DL		4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	-	-	-	-	-	-
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	-	-	-	-
		9	-										
		12	-	G1, G11/4, G11/2, G2	-	-	-	-	-	-	-	-	-
Soft-start valves, electrically actuated MS-DE		4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	-	-	■	-	■	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	■	-	■	■
		9	-										
		12	-	G1, G11/4, G11/2, G2	-	-	-	-	-	■	■	■	■

Membrane air dryers MS-LDM1, MS series

FESTO

Product range overview – MS series service units

Type	Size	Bowl guard		Pressure indicator					Security		Options		➔ Page/ Internet	
		Plastic bowl with plastic bowl guard	Metal bowl	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G1/8	Adapter plate for EN pressure gauge G1/4	Pressure sensor	Rotary knob with detent, lockable via accessories	Rotary knob with integrated lock	Silencer	Flow direction from right to left		
		Code	Code	R	U	VS	AG	A8	A4	AD...	AS	E11	S	Z
Individual devices														
Pressure regulators MS-LR	4	–	–	■	■	■	■	■	■	■	–	■	ms4-lr	
	6	–	–	■	■	–	■	■	■	■	–	■	ms6-lr	
	9	–	–	■	■	–	■	■	■	■	–	■	ms9-lr	
	12	–	–	■	■	–	■	–	■	■	–	■	ms12-lr	
Pressure regulators MS-LRB	4	–	–	■	■	■	■	■	■	■	–	■	ms4-lrb	
	6	–	–	■	■	–	■	■	■	■	–	■	ms6-lrb	
	9	–	–	–	–	–	–	–	–	–	–	–	–	
	12	–	–	–	–	–	–	–	–	–	–	–	–	
Precision pressure regulators MS-LRP	4	–	–	–	–	–	–	–	–	–	–	–	–	
	6	–	–	■	–	■	■	■	■	■	–	■	ms6-lrp	
	9	–	–	–	–	–	–	–	–	–	–	–	–	
	12	–	–	–	–	–	–	–	–	–	–	–	–	
Precision pressure regulators MS-LRPB	4	–	–	–	–	–	–	–	–	–	–	–	–	
	6	–	–	■	–	■	■	■	■	■	–	■	ms6-lrbp	
	9	–	–	–	–	–	–	–	–	–	–	–	–	
	12	–	–	–	–	–	–	–	–	–	–	–	–	
Electrical pressure regulators MS-LRE	4	–	–	–	–	–	–	–	–	–	–	–	–	
	6	–	–	■	■	–	■	■	■	–	–	■	ms6-lre	
	9	–	–	–	–	–	–	–	–	–	–	–	–	
	12	–	–	–	–	–	–	–	–	–	–	–	–	
MS-LOE	4	■	■	–	–	–	–	–	–	–	–	–	■	ms4-loe
	6	■	■	–	–	–	–	–	–	–	–	–	■	ms6-loe
	9	–	■	–	–	–	–	–	–	–	–	–	■	ms9-loe
	12	–	■	–	–	–	–	–	–	–	–	–	■	ms12-loe
On-off valves, manually actuated MS-EM(1)	4	–	–	■	■	■	■	■	■	–	–	■	■	ms4-em1
	6	–	–	■	■	–	■	■	■	–	–	■	■	ms6-em1
	9	–	–	■	■	–	■	■	–	–	–	■	■	ms9-em
	12	–	–	■	■	–	■	■	–	–	–	■	■	ms12-em
On-off valves, electrically actuated MS-EE	4	–	–	■	■	■	■	■	■	–	–	■	■	ms4-ee
	6	–	–	■	■	–	■	■	■	–	–	■	■	ms6-ee
	9	–	–	■	■	–	■	■	–	–	–	■	■	ms9-ee
	12	–	–	■	■	–	■	■	–	–	–	■	■	ms12-ee
Soft-start valves, pneumatically actuated MS-DL	4	–	–	■	■	■	■	■	■	–	–	–	■	ms4-dl
	6	–	–	■	■	–	■	■	■	–	–	–	■	ms6-dl
	9	–	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	■	■	–	■	■	–	–	–	–	■	ms12-dl
Soft-start valves, electrically actuated MS-DE	4	–	–	■	■	■	■	■	■	–	–	–	■	ms4-de
	6	–	–	■	■	–	■	■	■	–	–	–	■	ms6-de
	9	–	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	■	■	–	■	■	–	–	–	–	■	ms12-de

Membrane air dryers MS-LDM1, MS series

Product range overview – MS series service units

FESTO

Type	Size	Pneumatic connection in housing	Connecting plate	Performance Level		Supply voltage			
				Category 1, 1-channel	Category 4, 2-channel with self-monitoring	24 VDC, connection pattern to EN 175301	24 VDC, connection M12 to IEC 61076-2-101 / to EN 60947-5-2	110 VAC, connection pattern to EN 175301	230 VAC, connection pattern to EN 175301
Code		AG...		C	E	V24	V24P	V110	V230
Individual devices									
Soft start and exhaust valves MS-SV-C		4	–						
		6	G1/2	G1/4, G3/8, G1/2, G3/4	■	–	■	■	■
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	■	–	■	■	■
		12	–						
Soft start and exhaust valves MS-SV-E		4	–						
		6	G1/2	G1/4, G3/8, G1/2, G3/4	–	■	■	–	–
		9	–						
		12	–						
Membrane air dryers MS-LDM1		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–
		9	–						
		12	–						
Branching modules MS-FRM		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–
Distributor blocks MS-FRM-FRZ		4	G1/4	–	–	–	–	–	–
		6	G1/2	–	–	–	–	–	–
		9	–						
		12	–						
Flow sensors SFAM		4	–						
		6	G1/2	G1/2	–	–	–	–	–
		9	–	G1, G11/2	–	–	–	–	–
		12	–						

Membrane air dryers MS-LDM1, MS series

FESTO

Product range overview – MS series service units


Type	Size	Bowl guard		Pressure indicator				Switch output		Options		➔ Page/ Internet
		Plastic bowl with plastic bowl guard	Metal bowl	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G1/8	Adapter plate for EN pressure gauge G1/4	Pressure sensor	2x PNP or NPN, 1 analogue output 4 ... 20 mA	2x PNP or NPN, 1 analogue output 0 ... 10 V	Silencer	Flow direction from right to left
Code		R	U	VS	AG	A8	A4	AD...	2SA	2SV	S	Z/R
Individual devices												
Soft start and exhaust valves MS-SV-C	4	–										–
	6	–	–	■	■	–	■	■	–	–	■	■
	9	–	–	■	■	–	■	■	–	–	■	■
	12	–										–
Soft start and exhaust valves MS-SV-E	4	–										–
	6	–	–	■	■	–	■	■	–	–	■	■
	9	–										–
	12	–										–
Membrane air dryers MS-LDM1	4	–	■	–	–	–	–	–	–	–	–	■ 8
	6	–	■	–	–	–	–	–	–	–	–	■ 8
	9	–										–
	12	–										–
Branching modules MS-FRM	4	–	–	■	■	■	■	■	–	–	–	■ ms4-frm
	6	–	–	■	■	–	■	■	–	–	–	■ ms6-frm
	9	–	–	■	■	–	■	■	–	–	–	■ ms9-frm
	12	–	–	■	–	–	–	–	–	–	–	ms12-frm
Distributor blocks MS-FRM-FRZ	4	–	–	–	–	–	–	–	–	–	–	■ ms4-frm
	6	–	–	–	–	–	–	–	–	–	–	■ ms6-frm
	9	–										–
	12	–										–
Flow sensors SFAM	4	–										–
	6	–	–	–	–	–	–	–	■	■	–	■ sfam-62
	9	–	–	–	–	–	–	–	■	■	–	■ sfam-90
	12	–										–

Membrane air dryers MS4/MS6-LDM1, MS series

Peripherals overview

FESTO

Membrane air dryers MS4/MS6-LDM1



 Note

Additional accessories:

- Module connector for combination with sizes MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter plate for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80

Mounting attachments and accessories

	Individual unit		Combination		➔ Page/Internet
	without connecting plate	with connecting plate	without connecting plate	with connecting plate	
[1] Cover cap MS4/6-END	■	-	■	-	ms4-end, ms6-end
[2] Connecting plate MS4/6-AG...	-	■	-	■	ms4-ag, ms6-ag
[3] Mounting bracket MS4/6-WB	■	■	-	-	ms4-wb, ms6-wb
[5] Module connector MS4/6-MV	-	■	■	■	ms4-mv, ms6-mv
- Mounting bracket MS4-WBM	■	■	-	-	ms4-wbm
- Mounting bracket MS4/6-WP/WPB/WPE/WPM	-	■	■	■	ms4-wp, ms6-wp

Membrane air dryers MS4/MS6-LDM1, MS series

Type codes

MS	6	-	LDM1	-	1/2	-	P20
Series							
MS	Standard service unit						
Size							
4	Grid dimension 40 mm						
6	Grid dimension 62 mm						
Service function							
LDM1	Membrane air dryer						
Pneumatic connection							
MS4							
1/8	Female thread G1/8						
1/4	Female thread G1/4						
MS6							
1/4	Female thread G1/4						
3/8	Female thread G3/8						
1/2	Female thread G1/2						
Flow cartridge							
P10	Cartridge P10						
P20	Cartridge P20						
P40	Cartridge P40						

Further variants can be ordered using the modular system → 15


- Connecting plates
- Flow cartridge
- Ducted purging air
- Type of mounting
- UL certification
- Flow direction

**New
Variant UL1**

Membrane air dryers MS4/MS6-LDM1, MS series

Technical data

Function



- - Flow rate
50 ... 400 l/min
- - Temperature range
+2 ... +50 °C
- - Operating pressure
3 ... 12.5 bar

Pressure dew point reduction:
20 K



- Optimum final dryer with excellent operational reliability
- Suitable for use as an individual unit or for integration in existing service unit combinations
- Flow rate-dependent dew point reduction
- Wear-free function requiring no external energy
- The composition of the compressed air remains almost unchanged due to the drying process
- 15% purge air flow rate
- Optional purge ring for ducting of purging air

- Typical areas of application:
- Drying, cleaning of precision parts
 - Measuring technology
 - Rinsing of precision glass scales
 - Painting systems
 - Paper and packaging machines

- - Note
Prefiltration of the compressed air using a micro filter MS-LFM-A, grade of filtration 0.01 µm (residual particles < 0.1 µm, residual oil content < 0.1 mg/m³) is vital for flawless functioning of the unit.

General technical data

Size	MS4	MS6
Pneumatic connection 1, 2	G1/8	G1/4
Design	Membrane dryer with internal air consumption	
Type of mounting	Via accessories In-line installation	
Assembly position	Vertical ±5°	
Air purity class at the output	Compressed air in accordance with ISO 8573-1:2010 [1:3:2]	

- - Note: This product conforms to ISO 1179-1 and to ISO 228-1

Standard flow rate q_{n1}^1 [l/min]

Size	MS4		MS6		
	Cartridge P05	Cartridge P10	Cartridge P20	Cartridge P30	Cartridge P40
Input q_{n1} In	59	118	235	353	471
Output q_{n1} Out	50	100	200	300	400
Purge air q_{n1} Purge	8.8	17.6	35.3	52.9	70.6

1) Measured at $p_1 = 6.9$ bar, $\vartheta_{pd\text{ In}} = 25^\circ\text{C}$, $\vartheta_{pd\text{ Out}} = 5^\circ\text{C} \pm 1.5^\circ\text{C}$ ($\vartheta_{pA\text{ Out}} = -21.5^\circ\text{C} \pm 1.2^\circ\text{C}$), $\vartheta_{amb} = 25^\circ\text{C}$

Membrane air dryers MS4/MS6-LDM1, MS series

Technical data

Operating and environmental conditions

Operating pressure [bar]	3 ... 12.5 (3 ... 10) ¹⁾
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [1:4:2]
Note on operating/pilot medium	Operation with lubricated medium not possible
Pressure dew point reduction [K]	20
Ambient temperature [°C]	+2 ... +50
Temperature of medium [°C]	+2 ... +50
Storage temperature [°C]	-20 ... +60
Corrosion resistance class CRC ²⁾	2
UL certification	cULus recognized (OL)

1) Value in brackets applies to MS4/MS6-LDM1 with UL certification.

2) Corrosion resistance class 2 according to Festo standard 940 070


Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [g]

Size	MS4		MS6		
	Cartridge P05	Cartridge P10	Cartridge P20	Cartridge P30	Cartridge P40
Membrane air dryer	420	530	1,050	1,200	1,300

Materials

Sectional view



Membrane air dryer

[1] Housing	Die-cast aluminium
[2] Bowl	Wrought aluminium alloy
- Seals	NBR
Note on materials	RoHS-compliant


Membrane air dryers MS4/MS6-LDM1, MS series

Technical data


FESTO

Pressure dew point t_{pd} (output) as a function of the standard flow rate at output q_n ¹⁾


MS4-LDM1...-P05




MS4-LDM1...-P10




MS6-LDM1...-P20



MS6-LDM1...-P30



MS6-LDM1...-P40




- 1) Measured at pressure dew point t_{pd} (supply) = 25 °C.
- Example MS6-LDM1...-P40 with 10 bar operating pressure:
the pressure dew point reduction at a nominal flow rate
of $q_n = 550$ l/min is 25 K.

Membrane air dryers MS4/MS6-LDM1, MS series


Technical data

Differential pressure Δp as a function of the standard flow rate at output q_n


MS4-LDM1-...-P05




MS4-LDM1-...-P10




MS6-LDM1-...-P20



MS6-LDM1-...-P30



MS6-LDM1-...-P40



**New
Variant UL1**


Membrane air dryers MS4/MS6-LDM1, MS series

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



Type	B1	B2	B3	D1	D2	L1	L2	L3	L4	L5
MS4-LDM1-1/8-P05	40	21	54	G1/8	64	245	29	60	18	40
MS4-LDM1-1/8-P10						345				
MS4-LDM1-1/4-P05	40	21	54	G1/4	64	245	29	60	18	40
MS4-LDM1-1/4-P10						345				
MS6-LDM1-1/4-P20	62	31	76	G1/4	80	345	42	87	34	40
MS6-LDM1-1/4-P30						415				
MS6-LDM1-1/4-P40						475				
MS6-LDM1-3/8-P20	62	31	76	G3/8	80	345	42	87	34	40
MS6-LDM1-3/8-P30						415				
MS6-LDM1-3/8-P40						475				
MS6-LDM1-1/2-P20	62	31	76	G1/2	80	345	42	87	34	40
MS6-LDM1-1/2-P30						415				
MS6-LDM1-1/2-P40						475				

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data				
Size	Flow cartridge	Connection	Part No.	Type
MS4	P10	G1/8	543630	MS4-LDM1-1/8-P10
		G1/4	543632	MS4-LDM1-1/4-P10
MS6	P20	G1/4	543640	MS6-LDM1-1/4-P20
		G3/8	543642	MS6-LDM1-3/8-P20
		G1/2	543644	MS6-LDM1-1/2-P20
	P40	G1/4	543646	MS6-LDM1-1/4-P40
		G3/8	543648	MS6-LDM1-3/8-P40
		G1/2	543650	MS6-LDM1-1/2-P40

Membrane air dryers MS4/MS6-LDM1, MS series

Ordering data – Modular products

M Mandatory data						O Options			
Module No.	Series	Size	Function	Pneumatic connection	Flow cartridge	Purging air	Type of mounting	UL certification	Flow direction
543628	MS	4	LDM1	1/8, 1/4, 3/8, 1/2 AGA, AGB, AGC, AGD, AGE	P05 P10 P20 P30 P40	PAC	WP WPM WB WBM	UL1	Z
543638		6							
Ordering example									
543628	MS	4	- LDM1 - AGC - P10 -				WP		

Ordering table		Grid dimension [mm]	40	62	Conditions	Code	Enter code
M	Module No.	543628	543638				
	Series	Standard				MS	MS
	Size	4	6			...	
	Function	Membrane dryer				-LDM1	-LDM1
M	Pneumatic connection	Female thread G1/8	-			-1/8	
		Female thread G1/4	Female thread G1/4			-1/4	
		-	Female thread G3/8			-3/8	
		-	Female thread G1/2			-1/2	
		Connecting plate G1/8	-			-AGA	
		Connecting plate G1/4	Connecting plate G1/4			-AGB	
		Connecting plate G3/8	Connecting plate G3/8			-AGC	
		-	Connecting plate G1/2			-AGD	
		-	Connecting plate G3/4			-AGE	
	Flow cartridge	50 l/min	-			-P05	
		100 l/min	-			-P10	
		-	200 l/min			-P20	
		-	300 l/min			-P30	
		-	400 l/min			-P40	
O	Purging air	Ducted purging air				-PAC	
	Type of mounting	Wall mounting plate	[1]			-WP	
		Wall mounting plate	[1]			-WPM	
		Wall mounting bracket				-WB	
		Wall mounting bracket	-			-WBM	
	UL certification	cULus, ordinary location for Canada and USA				-UL1	
	Flow direction	Flow direction from right to left				-Z	

WP, WPM Only with connecting plate AGA, AGB, AGC, AGD or AGE.

Transfer order code

MS - LDM1 - - - - - - -