

Flow control valves

FESTO



Flow control valves

Key features


FESTO

Function

Flow control or one-way flow control valves regulate the piston speed of pneumatic drives during advance and return strokes. This is done through suitable restriction of the flow rate of compressed air in exhaust air or supply air direction. With the one-way

flow control valve GRLA or GRLZ, the flow control function works in one direction only (exhaust air or supply air); the non-return function works in the opposite direction. With the flow control valve GRLO, the flow control function is active in both directions.

The flow control function creates an adjustable annular gap inside the valve. This gap can be increased or decreased by turning the knurled screw or slotted head screw. The required restriction can be set with the help of this adjustment component.

 **Note**
The documentation for the one-way flow control valves can be found at
www.festo.com/catalogue

General information


Standard nominal flow rate q_{nN}

The standard nominal flow rate q_{nN} is the flow rate based on standard conditions at an operating pressure of $p_1 = 6$ bar and an output pressure of $p_2 = 5$ bar, measured at room temperature $t = 20$ °C.


Standard flow rate q_n

The standard flow rate is measured at an operating pressure of $p_1 = 6$ bar and an output pressure with respect to atmospheric pressure ($p_2 = 0$ bar).

Exhaust air one-way flow control function




Supply air one-way flow control function



Flow control function in both directions







Flow measurement circuit



Flow control valves

Key features

FESTO


| Flow control functions and range of applications | | | |
|---|---|--|---|
| Application | Description | Application | Description |
| Double-acting cylinder with one-way flow control valve | | | |
| Exhaust air one-way flow control function | | Supply air one-way flow control function | |
|  | Speed adjustment through exhaust air flow control. Uncontrolled supply air and controlled exhaust air move the piston between air cushions (improves motion, even with load changes). |  | Adjustable speed during advance and return strokes. The flow rate is identical in both directions. |
| Single-acting cylinder with one-way flow control valve | | Single-acting cylinder with flow control valve | |
| Exhaust air and supply air one-way flow control function | | Flow control function in both directions | |
|  | Adjustable speed during advance and return strokes. The flow rate can be adjusted differently for both directions. |  | Speed adjustment through flow control on both sides is often applied in the case of single-acting or small cylinders. The benefit of this application lies in its simplicity. |

Application examples

Mini slide SLT

Flat cylinder DZF







Multimount cylinder DMM



Flow control valves

Product range overview

FESTO

| Version | Valve function | Version | Type | Connection direction | Pneumatic connection 1 | Pneumatic connection 2 | q _N ¹⁾ [l/min] | Adjustment component | → Page/ Internet |
|-----------------------------|---|---|------|----------------------|------------------------|------------------------|---|----------------------|---------------------|
| Standard | Metal Flow control function |  | GRLO | Elbow outlet | M5 | M5 | 95 | Slotted head screw | 6 |
| | |  | | | M5 | PK-3 | 83 | Slotted head screw | 6 |
| | | | | | | | | | |
| Mini | Metal Flow control function |  | GRLO | Elbow outlet | M3, M5 | QS-3, QS-4 | 40 ... 41 | Slotted head screw | 8 |
| | |  | | | M3 | M3 | 18 | Slotted head screw | 10 |
| | |  | GRGO | Parallel outlet | M3 | QS-3 | 41 | Slotted head screw | 8 |
| In-line installation | Polymer Flow control function |  | GRO | Inline | QS-3, QS-4, QS-6 | QS-3, QS-4, QS-6 | 25 ... 160 | Knurled screw | gro |
| | | | | | | | | | |

1) Standard nominal flow rate in direction of flow control.

Flow control valves

Type codes

FESTO

GRLO/GRGO

GRLO - M5 - PK-3 - - B

Type

| | |
|------|-------------------------------------|
| GRLO | Flow control valve, elbow outlet |
| GRGO | Flow control valve, parallel outlet |

Pneumatic connection 1

| | |
|----|----------------|
| M3 | Male thread M3 |
| M5 | Male thread M5 |

Pneumatic connection 2

| | |
|------|---|
| - | Female thread (connection size as for connection 2) |
| QS-3 | Push-in connector for tubing O.D. 3 mm |
| QS-4 | Push-in connector for O.D. tubing 4 mm |
| PK-3 | Push-in connector for tubing I.D. 3 mm |

Flow rate characteristic

| | |
|----|-------------|
| LF | Low flow |
| MF | Medium flow |

Generation


| | |
|---|----------|
| B | B series |
| C | C series |




Flow control valves GRLO, standard

Technical data – Female thread/barbed connector, metal

FESTO

Function



-  - Flow rate
83 ... 95 l/min
-  - Temperature range
-10 ... +60 °C
-  - Operating pressure
0 ... 10 bar



GRLO-M5


GRLO-M5-PK

| General technical data | | |
|-----------------------------|-----------------------|------|
| Valve function | Flow control function | |
| Pneumatic connection 1 | M5 | M5 |
| Pneumatic connection 2 | M5 ¹⁾ | PK-3 |
| Adjustment component | Slotted head screw | |
| Type of mounting | Screw-in | |
| Mounting position | Any | |
| Max. tightening torque [Nm] | 1.5 | 1.5 |


1)  - Note: This product conforms to ISO 1179-1 and ISO 228-1.

| Operating and environmental conditions | | |
|--|--|--|
| Operating pressure [bar] | 0 ... 10 | |
| Operating medium | Compressed air in accordance with ISO 8573-1:2010 [7:4:4] | |
| Note on operating/pilot medium | Operation with lubricated medium possible (in which case lubricated operation will always be required) | |
| Ambient temperature [°C] | -10 ... +60 | |
| Temperature of medium [°C] | -10 ... +60 | |
| Storage temperature [°C] | -10 ... +40 | |

Standard nominal flow rate q_{nN} at 6 \rightarrow 5 bar
as a function of turns of the adjusting screw n



Standard flow rate q_n at 6 \rightarrow 0 bar
as a function of turns of the adjusting screw n




Flow control valves GRLO, standard

Technical data – Female thread/barbed connector, metal

FESTO

Materials

Sectional view



Flow control valve



| | | |
|-------------------|-------------------|---------------------|
| 1 | Adjusting screw | Brass |
| 2 | Swivel connection | Die-cast zinc |
| 3 | Threaded plug | Nickel-plated brass |
| – | Seals | NBR |
| Note on materials | | RoHS-compliant |

Dimensions

Download CAD data → www.festo.com

Female thread

Push-in connector



3 Barbed connector

Note: This product conforms to ISO 1179-1 and to ISO 228-1

| Type | Connection D | Nominal size [mm] | B | H | H1 | L max. | L1 | L2 | ⌀ |
|-------------------|-----------------|----------------------|----------|------|------|-----------|--------|-----|---|
| Female thread | | | | | | | | | |
| GRLO-M5 | M5 | 2 | 10 –0.15 | 17.5 | 12.5 | 17.6 | 4 ±0.3 | 7.1 | 9 |
| Push-in connector | | | | | | | | | |
| GRLO-M5-PK-3 | M5 | 2 | 10 –0.15 | 19.7 | 14.7 | 17.6 | 4 ±0.3 | 8.5 | 9 |

Ordering data

| | Pneumatic connection | | Standard nominal flow rate q _N at 6 → 5 bar in direction of flow control [l/min] | Standard flow rate q _n at 6 → 0 bar in direction of flow control [l/min] | Weight [g] | Part No. | Type |
|--------------------|-------------------------|------|--|--|---------------|----------|----------------|
| | 1 | 2 | | | | | |
| Slotted head screw | | | | | | | |
| | M5 | M5 | 95 | 169 | 11 | 151181 | GRLO-M5-B |
| | M5 | PK-3 | 83 | 140 | 10 | 151182 | GRLO-M5-PK-3-B |


- 7 - Type GRGO discontinued Available up until 2018

Flow control valves GRLO/GRGO, mini

Technical data – Push-in connector QS, metal

FESTO

Function



- Low flow: precision adjustment for low speed


- - Flow rate
40 ... 41 l/min
- - Temperature range
-10 ... +60 °C
- - Operating pressure
0 ... 10 bar




| General technical data | | |
|-----------------------------|-----------------------|------------|
| Valve function | Flow control function | |
| Pneumatic connection 1 | M3 | M5 |
| Pneumatic connection 2 | QS-3 | QS-3, QS-4 |
| Adjustment component | Slotted head screw | |
| Type of mounting | Screw-in | |
| Mounting position | Any | |
| Max. tightening torque [Nm] | 0.3 | 1.5 |

| Operating and environmental conditions | | |
|--|--|--|
| Operating pressure [bar] | 0 ... 10 | |
| Operating medium | Compressed air in accordance with ISO 8573-1:2010 [7:4:4] | |
| Note on operating/pilot medium | Operation with lubricated medium possible (in which case lubricated operation will always be required) | |
| Ambient temperature [°C] | -10 ... +60 | |
| Temperature of medium [°C] | -10 ... +60 | |
| Storage temperature [°C] | -10 ... +40 | |


Standard nominal flow rate q_{nN} at 6 \rightarrow 5 bar
as a function of turns of the adjusting screw n
GRLO/GRGO-M3




Standard flow rate q_n at 6 \rightarrow 0 bar
as a function of turns of the adjusting screw n
GRLO/GRGO-M3



GRLO-M5



GRLO-M5



- 2 - Type GRGO discontinued
Available up until 2018


Flow control valves GRLO/GRGO, mini

Technical data – Push-in connector QS, metal

FESTO

Materials

Sectional view



Flow control valve



| | | |
|-------------------|-------------------|----------------|
| 1 | Adjusting screw | Brass |
| 2 | Swivel connection | Die-cast zinc |
| 3 | Releasing ring | POM |
| 4 | Threaded plug | Brass |
| - | Seals | NBR |
| Note on materials | | RoHS-compliant |

Dimensions

GRLO, elbow outlet

GRGO, parallel outlet

Download CAD data → www.festo.com



| Type | Connection | Nominal size | Tubing O.D. | B | H | H1 | H2 | L max. | L1 | L2 | L3 | ☞ |
|------|------------|--------------|-------------|-----------|------|------|------|--------|-----------------|-----|----|---|
| | D | [mm] | D1 | | | | | | | | | |
| GRLO | M3 | 1.4 | 3 | 8 -0.15 | 20 | 15.8 | - | 16.6 | 2.3 +0.15/-0.3 | 7 | - | 7 |
| | M5 | 1.4 | 3 | 9.8 -0.15 | 22.4 | 18.4 | | 17.7 | 3.1 +0.15/-0.35 | 7.3 | | |
| | | 1.4 | 4 | 9.8 -0.15 | 22.2 | 18.2 | | 17.7 | 3.1 +0.15/-0.35 | 7.3 | | |
| GRGO | M3 | 1.4 | 3 | 8 -0.15 | 18 | 14 | 9.25 | 16.6 | 2.3 +0.15/-0.3 | 7.5 | 22 | 7 |

Ordering data


| | Pneumatic connection | | Standard nominal flow rate qnN at 6 → 5 bar in direction of flow control [l/min] | Standard flow rate qn at 6 → 0 bar in direction of flow control [l/min] | Weight [g] | Part No. | Type |
|--------------------|----------------------|------|--|---|------------|----------|-------------------|
| | 1 | 2 | | | | | |
| Slotted head screw | | | | | | | |
| | M3 | QS-3 | 41 | 95 | 7 | 175042 | GRLO-M3-QS-3 |
| | M5 | QS-3 | 40 | 80 | 9 | 175054 | GRLO-M5-QS-3-LF-C |
| | | QS-4 | 40 | 80 | 9 | 175057 | GRLO-M5-QS-4-LF-C |
| | M3 | QS-3 | 41 | 95 | 14 | 175045 | GRGO-M3-QS-3 ☞ |




Flow control valves GRLO, mini

Technical data – Female thread, metal

FESTO

Function




-  - Flow rate
0 ... 18 l/min
-  - Temperature range
-10 ... +60 °C
-  - Operating pressure
0 ... 10 bar




| General technical data | |
|-----------------------------|-----------------------|
| Valve function | Flow control function |
| Pneumatic connection 1 | M3 |
| Pneumatic connection 2 | M3 |
| Adjustment component | Slotted head screw |
| Type of mounting | Screw-in |
| Mounting position | Any |
| Max. tightening torque [Nm] | 0.3 |

| Operating and environmental conditions | |
|--|--|
| Operating pressure [bar] | 0 ... 10 |
| Operating medium | Compressed air in accordance with ISO 8573-1:2010 [7:4:4] |
| Note on operating/pilot medium | Operation with lubricated medium possible (in which case lubricated operation will always be required) |
| Ambient temperature [°C] | -10 ... +60 |
| Temperature of medium [°C] | -10 ... +60 |
| Storage temperature [°C] | -10 ... +40 |

Standard nominal flow rate q_{nN} at 6 → 5 bar
as a function of turns of the adjusting screw n




Standard flow rate q_n at 6 → 0 bar
as a function of turns of the adjusting screw n



Materials

Sectional view



| Flow control valve | |
|-------------------------------------|--------------------------------------|
| 1 | Adjusting screw Brass |
| 2 | Swivel connection Die-cast zinc |
| 3 | Threaded plug Nickel-plated brass |
| - | Seals NBR |
| Note on materials RoHS-compliant | |

Flow control valves GRLO, mini


Technical data – Female thread, metal

FESTO

Dimensions


Download CAD data → www.festo.com

Slotted head screw



| Type | Connection | Nominal size | B | H | H1 | L max. | L1 | L2 | ⌀ |
|------|------------|--------------|--------|---|-----|-----------|----------------|-----|-----|
| | D | [mm] | | | | | | | |
| GRLO | M3 | 0.8 | 5 -0.1 | 9 | 6.5 | 13.3 | 2.5 +0.15/-0.3 | 6.4 | 4.5 |

Ordering data

| | Pneumatic connection | | Standard nominal flow rate q _N at 6 → 5 bar in direction of flow control | Standard flow rate q _n at 6 → 0 bar in direction of flow control | Weight | Part No. | Type |
|---|----------------------|----|---|---|--------|----------|---------|
| | 1 | 2 | [l/min] | [l/min] | [g] | | |
| Slotted head screw | | | | | | | |
|  | M3 | M3 | 18 | 33 | 2 | 175039 | GRLO-M3 |