
FESTO



Overview




Servo-pneumatic drive technology

Positioning and Soft Stop applications as an integral component of the valve terminal CPX – the modular peripheral system for decentralised automation tasks.

The modular design means that valves, digital inputs and outputs, positioning modules and end-position controllers, as appropriate to the application, can be combined in almost any way on the CPX terminal.

- Pneumatics and electrics control and positioning on one platform
- Innovative positioning technology piston rod drives, rodless drives, rotary drives
- Actuation via fieldbus
- Remote maintenance, remote diagnostics, web server, SMS and e-mail alert are all possible via TCP/IP
- Modules can be quickly exchanged and expanded without altering the wiring



Key features



Axis controllers CPX-CMAX



Free choice:

Position and force control, directly actuated or selected from one of 128 configurable position sets. If you are looking for something

the configurable function for switching to the next set enables simple functional sequences to be realised in the axis controller CPX-CMAX. Everything is recognisable: the auto-identification function identifies each station with its device data on the controller CPX-CMAX.

Also included:

The functional scope of the controller CPX-CMAX includes actuation of a brake or clamping unit via the proportional directional control valve VPWP.

Up to 7 modules (max. 7 axes) can be operated in parallel and independently of each other.

Commissioning via FCT (Festo configuration software) or via fieldbus: no programming, only configuration.

Technical data → Internet: cpx-cmax

Advantages:

- · Greater flexibility
- OEM friendly commissioning also via fieldbus
- Clear installation and fast commissioning
- Cost-effective
- You program the system in your PLC environment

End-position controllers CPX-CMPX



Fast travel between the mechanical end stops of the cylinder, stopping gently and without impact in the end position.

Fast commissioning via control panel, fieldbus or handheld unit. Improved control of downtime. Actuation of a brake or clamping unit via the proportional directional control valve VPWP is an integral component of the controller CMPX.

Depending on the fieldbus chosen, up to 9 end-position controllers can be actuated on the CPX terminal. All system data can be read and written via the fieldbus, including, for example the mid positions.

Technical data → 7

Advantages:

- · Greater flexibility
- OEM friendly commissioning also via fieldbus
- Clear installation and fast commissioning
- Cost-effective
 - Up to 30% faster cycle rates
 - Significantly reduced system vibration
- Improved work ergonomics thanks to significantly reduced noise level
- The extended diagnostics help to reduce the service time of the machine

Proportional directional control valve VPWP



The 5/3-way proportional directional control valve for applications with Soft Stop and pneumatic positioning.
Fully digitalised – with integrated pressure sensors, with new diagnostic functions.
In sizes 4, 6 and 8.
Flow rate of 350, 700 and 1400 l/min.

With switching output for actuating a brake.
Coloured supply ports.

Pre-assembled cables guarantee faultless and fast connection with the controllers CPX-CMPX and CPX-CMAX.

Technical data → Internet: vpwp

- Clear installation and fast commissioning
- Reduction of system downtimes thanks to the new diagnostic options
- With switching output for actuating a brake/clamping unit

Drive options



System with linear drive DDLI, DGCI



- 1 Controller module CPX-CMPX or CPX-CMAX
- 2 Proportional directional control valve VPWP
- 3 Linear drive DDLI, DGCI with displacement encoder
- 6 Connecting cable KVI-CP-3-...


- Pneumatic rodless linear drive with displacement encoder, with or without recirculating ball bearing guide
- Displacement encoder with absolute and contactless measurement
- Diameters:
- DGCI: 18 ... 63 mm
- DDLI: 25 ... 63 mm
- Stroke: 100 ... 2000 mm in fixed lengths
- Range of applications: Soft Stop and pneumatic positioning
- Loads from 1 ... 180 kg
- No sensor interface required

Technical data → Internet: ddli or dgci

Advantages:

- Complete drive unit
- DDLI for easy connection to customer's guide system
- Excellent running characteristics
- For fast and accurate positioning down to ±0.2 mm (only with axis controller CPX-CMAX)

System with standard cylinder DNCI, DDPC



- 1 Controller module CPX-CMPX or CPX-CMAX
- 2 Proportional directional control valve VPWP
- 3 Standard cylinder DNCI, DDPC with displacement encoder
- 5 Sensor interface CASM-S-D3-R7
- 6 Connecting cable KVI-CP-3-...

Standard cylinder with integrated displacement encoder, conforms to DIN ISO 6432, VDMA 24 562, NF E 49 003.1 and Uni 10 290

- Displacement encoder with contactless and incremental measuring
- Diameter: 32 ... 100 mm
- Stroke: 100 ... 750 mm
- Range of applications: Soft Stop and pneumatic positioning
- Loads from 3 ... 450 kg and a matching sensor interface CASM-S-D3-R7
- Pre-assembled cables guarantee faultless and fast electrical connection


Technical data → Internet: dnci

- · Compact drive unit
- Can be used universally
- · Also with guide unit
- For fast and accurate positioning up to ±0.5 mm (only with axis controller CPX-CMAX)

Drive options

FESTO

System with swivel module DSMI



- 1 Controller module CPX-CMPX or CPX-CMAX
- 2 Proportional directional control valve VPWP
- 3 Swivel module DSMI with displacement encoder
- 4 Sensor interface CASM-S-D2-R3
- 6 Connecting cable KVI-CP-3-...
- 7 Connecting cable NEBC-P1W4-K-0,3-N-M12G5


- Swivel module DSMI with integrated displacement encoder
- Identical construction as pneumatic swivel module DSM
- Absolute displacement encoder on basis of potentiometer
- Swivel range from 0 ... 270°
- Size: 25, 40, 63
- Max. torque: 5 ... 40 Nm
- Range of application of Soft Stop and pneumatic positioning: mass moments of inertia from 15 ... 6000 kgcm² and the matching sensor interface CASM-S-D2-R3
- Pre-assembled cables guarantee faultless and fast connection with the proportional directional control valve VPWP

Technical data → Internet: dsmi

Advantages:

- Complete drive unit, compact, can be used immediately
- High angular acceleration
- With adjustable fixed stops
- For fast and accurate positioning down to ±0.2° (only with axis controller CPX-CMAX)

System with potentiometer



- 1 Controller module CPX-CMPX or CPX-CMAX
- 2 Proportional directional control valve VPWP
- 4 Sensor interface CASM-S-D2-R3
- 6 Connecting cable KVI-CP-3-...
- 7 Connecting cable NEBC-P1W4-K-0,3-N-M12G5
- 8 Connecting cable NEBC-A1W3-K-0,4-N-M12G5

Attachable potentiometers with absolute measurement, with high degree of protection

- With connecting rod or moment compensator
- Measuring range:
 Connecting rod: 100 ... 750 mm
 Moment compensator:
 225 ... 2000 mm
- Pre-assembled cables guarantee faultless and fast connection with the sensor interface CASM
- Range of applications: Soft Stop and pneumatic positioning with cylinder Ø 25 ... 80 mm, e.g. DNC or DSBC
- Loads from 1 ... 300 kg

Technical data → Internet: casm

- Easy installation and fast commissioning
- Cost-effective
- Can also be used in harsh ambient conditions
- Variety of drives: CPX-CMPX and CPX-CMAX also support cylinders with external displacement encoder


End-position controllers CPX-CMPXDrive options




Syste	System components for Soft Stop systems with end-position controller CPX-CMPX						
3		Linear drive	Standard cylinder	Swivel module	Displacement encode	Displacement encoder	
		DDLI/DGCI	DNCI/DDPC	DSMI	MLO-LWG/-TLF	MME-MTS	Internet
1	End-position controller	_	_	_		_	7
	CPX-CMPX	•	-	-	-	-	/
2	Proportional directional						
	control valve		•	•	•	•	vpwp
	VPWP						
4	Sensor interface			_	_		
	CASM-S-D2-R3	_	_	-	-	_	casm
5	Sensor interface						caem
	CASM-S-D3-R7	_	-	_	_	_	casm
6	Connecting cable		_	_	_	_	10
	KVI-CP-3	-	-	-	-	-	10
7	Connecting cable				■/-		nebc
	NEBC-P1W4	_	_	-	- / -	_	перс
8	Connecting cable				- / ■		nebc
	NEBC-A1W3	_	_	_	- / -	_	Hebc
1	Connecting cable					_	L/DIA/D
	NEBP-M16W6	_	_	_	_	-	vpwp

End-position controllers CPX-CMPX Type codes and peripherals overview





Peripherals overview



Accessories					
	Туре	Brief description	→ Page/Internet		
1	End-position controller	Integrated in the CPX terminal.	8		
	CPX-CMPX	Screws for mounting on the plastic interlinking block are included in the scope of delivery.			
6	Connecting cable	For connecting end-position controller CPX-CMPX and proportional directional control valve VPWP.	10		
	KVI-CP-3				
11	Inscription label	For labelling the modules.	10		
	IBS				
12	Interlinking block	Connects the individual modules.	11		
	CPX-GE	Two versions are available: plastic or metal interlinking block.			
-	Screws	For mounting on the metal interlinking block.	10		
	CPX-M-M3				

End-position controllers CPX-CMPXTechnical data

FESTO

The end-position controller CPX-CMPX is intended exclusively for use in valve terminals CPX.




General technical data			
Operating voltage			
		[V DC]	18 30
Nominal operating voltage		[V DC]	24
Current consumption at nominal op	perating voltage	[mA]	80
Load voltage			
Load voltage range		[V DC]	20 30
Nominal load voltage		[V DC]	24
Perm. load current		[A]	2.5
Number of axes per module			1
Length of connecting cable to axis		[m]	≤ 30
Max. no. of modules			9
Display			7-segment display
Control elements			3 keys
Assigned addresses	Outputs	[bit]	6x8
	Inputs	[bit]	6x8
Diagnostics			Module-orientated
			Via local 7-segment display
Status display			Module status
			Power Load
Control interface			
Data			CAN bus with Festo protocol
			Digital
Electrical connection			5-pin
			M9
			Socket
Materials: Housing			Reinforced PA
		[g]	240
Dimensions	Length	[mm]	107
DIIIICII3IUII3	Width	[mm]	50
	Height	[mm]	55
	пеідін	liiiiii	ננ

End-position controllers CPX-CMPXTechnical data



Operating and environmental conditions				
Ambient temperature [°C]	-5 +50			
Relative air humidity [%]	5 95, non-condensing			
Protection class to IEC 60529	IP65			
CE mark (see declaration of conformity)	To EU EMC Directive			

Connection and display components



- 1 3-digit display
- 2 Control interface
- 3 Status LEDs
- 4 Operating buttons
- 5 Inscription labels

	Pin a	llocation	Control	interface
--	-------	-----------	---------------------------	-----------

	Pin	Signal	Designation
/3	1	+24 V	Nominal operating voltage
2 4	2	+24 V	Load voltage
(0)0	3	0 V	Ground
1-0-5	4	CAN_H	CAN high
	5	CAN_L	CAN low
	Housing	Screened	Cable screening

Permitted bus nodes/CEC			
Bus node/CEC	Protocol	Max. no. of CMPX modules	
CPX-CEC	-	9	
CPX-FB6	INTERBUS	2	
CPX-FB11	DeviceNet ¹⁾	9	
CPX-FB13	PROFIBUS ²⁾	9	
CPX-FB14	CANopen	5	
CPX-M-FB21	INTERBUS	2	
CPX-FB23-24	CC-Link	5 (function module F23)	
		9 (function module F24)	
CPX-FB33	PROFINET RT, M12	9	
CPX-M-FB34	PROFINET RT, RJ45	9	
CPX-M-FB35	PROFINET RT, SCRJ	9	
CPX-FB36	EtherNet/IP	9	
CPX-FB37	EtherCAT	9	
CPX-FB39	Sercos III	9	
CPX-FB40	POWERLINK	9	
CPX-M-FB41	PROFINET RT	9	

¹⁾ With Revision 20 (R20) 2) With Revision 23 (R23)

 $PROFIBUS^{\circledR}, DeviceNet^{\circledR}, CANopen^{\circledR}, INTERBUS^{\circledR}, CC-LINK^{\circledR}, EtherCAT^{\circledR}, PROFINET^{\circledR}, Sercos^{\circledR}, EtherNet/IP^{\circledR} \ is \ a \ registered \ trademark \ of its \ respective \ trademark$ holder in certain countries.

End-position controllers CPX-CMPXAccessories



Brief description		Part No.	Туре
Order code in the CPX configurator: T20		548931	CPX-CMPX-C-1-H1
Connecting cable with angled plug and angled socket	0.25 m	540327	KVI-CP-3-WS-WD-0,25
commonly caste min angles plag and angles soulier			KVI-CP-3-WS-WD-0,5
			KVI-CP-3-WS-WD-2
			KVI-CP-3-WS-WD-5
			KVI-CP-3-WS-WD-8
Connecting cable with straight plug and straight socket	-		
connecting capic with straight plug and straight socket			KVI-CP-3-GS-GD-5
	-		
Connector for control cabinet through-feed	1	543252	KVI-CP-3-SSD
			CDV M MAYOR VV
For mounting on the metal interlinking block		550219	CPX-M-M3X22-4X
Inscription labels 6x10, in frames	64 pieces	18576	IBS-6X10
End-position controller description CPX-CMPX ¹⁾	German	555479	P.BE-CPX-CMPX-SYS-DE
		555480	P.BE-CPX-CMPX-SYS-EN
	English		
	Spanish French	555481 555482	P.BE-CPX-CMPX-SYS-ES P.BE-CPX-CMPX-SYS-FR
	Connecting cable with angled plug and angled socket Connecting cable with straight plug and straight socket Connector for control cabinet through-feed For mounting on the metal interlinking block	Connecting cable with angled plug and angled socket Connecting cable with angled plug and angled socket O.25 m 0.5 m 2 m 5 m 8 m Connecting cable with straight plug and straight socket 2 m 5 m 8 m Connector for control cabinet through-feed For mounting on the metal interlinking block Inscription labels 6x10, in frames 64 pieces	Connecting cable with angled plug and angled socket Connecting cable with angled plug and angled socket Connecting cable with angled plug and angled socket Connecting cable with straight plug and straight socket Connecting cable with straight plug and straight socket Connector for control cable through-feed Connector for control cabinet through-feed For mounting on the metal interlinking block Society For mounting on the metal interlinking block Society German Society German Society Soci

¹⁾ User manual in paper form is not included in the scope of delivery.

End-position controllers CPX-CMPXAccessories



Ordering data				
	Brief description		Part No.	Туре
Interlinking block, plas	stic, as expansion block			
<i>→</i>	Without power supply	-	195742	CPX-GE-EV
	With additional power supply for outputs	M18 – 4-pin	195744	CPX-GE-EV-Z
		7/8" – 5-pin	541248	CPX-GE-EV-Z-7/8-5POL
		7/8" - 4-pin	541250	CPX-GE-EV-Z-7/8-4POL
	With additional power supply for valves	M18 – 4-pin	533577	CPX-GE-EV-V
		7/8" - 4-pin	541252	CPX-GE-EV-V-7/8-4POL
		<u>'</u>	'	
Tie rods				
	For expansion using an interlinking block	1-fold	525418	CPX-ZA-1-E