

Service units FRC/FRCS, D series







FESTO



Service units FRC/FRCS, D series, metal design

FESTO

Product range overview D series service units, metal design

Type	Size	Pneumatic connection										Pressure regulation range [bar]			Grade of filtration [µm]				
		M5	M7	G1/8	G1/4	G3/8	G1/2	G3/4	G1	QS4	QS6	0.5 ...	0.5 ...	2.5 ...	0.01	1	5	40	
Service units																			
FRC/FRCS		Micro	■	■	■	–	–	–	–	–	■	■	■	–	–	–	–	■	–
		Mini	–	–	■	■	■	–	–	–	–	■	■	–	–	–	–	■	■
		Midi	–	–	–	■	■	■	■	–	–	■	■	–	–	–	–	■	■
		Maxi	–	–	–	–	–	■	■	■	–	–	■	■	–	–	–	■	■
Service unit combinations																			
FRC-K		Micro	–																
		Mini	–	–	■	■	–	–	–	–	–	–	–	■	■	–	–	–	■
		Midi	–	–	–	■	■	■	–	–	–	–	–	■	■	–	–	–	■
		Maxi	–	–	–	–	–	■	■	–	–	–	–	■	■	–	–	–	■
LFR-K LFRS-K		Micro	–																
		Mini	–	–	■	■	–	–	–	–	–	–	–	■	■	–	–	–	■
		Midi	–	–	–	■	■	■	–	–	–	–	–	■	■	–	–	–	■
		Maxi	–	–	–	–	–	■	■	–	–	–	–	■	■	–	–	–	■
Individual devices																			
Filter regulators LFR/LFRS		Micro	■	■	■	–	–	–	–	–	■	■	■	–	–	–	–	■	–
		Mini	–	–	■	■	■	–	–	–	–	■	■	–	–	–	–	■	■
		Midi	–	–	–	■	■	■	■	–	–	–	■	■	–	–	–	■	■
		Maxi	–	–	–	–	–	■	■	■	–	–	■	■	–	–	–	■	■
Filters LF		Micro	■	■	■	–	–	–	–	–	■	■	–	–	–	–	–	■	–
		Mini	–	–	■	■	■	–	–	–	–	–	–	–	–	–	–	■	■
		Midi	–	–	–	■	■	■	■	–	–	–	–	–	–	–	–	■	■
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–	–	–	–	■	■
Fine and micro filters LFMA/LFMB		Micro	–																
		Mini	–	–	■	■	■	–	–	–	–	–	–	–	■	■	–	–	
		Midi	–	–	–	■	■	■	■	–	–	–	–	–	■	■	–	–	
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–	■	■	–	–	
Active carbon filters LFX		Micro	–																
		Mini	–	–	■	■	■	–	–	–	–	–	–	–	–	–	–	–	
		Midi	–	–	–	■	■	■	■	–	–	–	–	–	–	–	–	–	
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–	–	–	–	–	
Filter combinations LFMBA		Micro	–																
		Mini	–	–	■	■	■	–	–	–	–	–	–	–	■	■	–	–	
		Midi	–	–	–	■	■	■	■	–	–	–	–	–	■	■	–	–	
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–	■	■	–	–	
Pressure regulators LR/LRS		Micro	■	■	■	–	–	–	–	–	■	■	■	–	–	–	–	–	–
		Mini	–	–	■	■	■	–	–	–	–	■	■	–	–	–	–	–	
		Midi	–	–	–	■	■	■	■	–	–	–	■	■	–	–	–	–	
		Maxi	–	–	–	–	–	■	■	■	–	–	■	■	–	–	–	–	

Service units FRC/FRCS, D series, metal design

FESTO










Product range overview D series service units, metal design

Type	Size	Bowl guard		Condensate drain			Pressure indication		Actuator lock		Supply voltage			Options			→ Page/ Internet
		Metal bowl guard	Plastic bowl	Manual rotary	Semi-automatic	Fully automatic	With pressure gauge	Without pressure gauge	Rotary knob with detent	Rotary knob with integrated lock	24 V DC	110 V AC	230 V AC	Directly actuated pressure regulator with integrated return flow function	Pilot actuated pressure regulator with integrated return flow function	Differential pressure indicator	
Service units																	
FRC/FRCS	Micro	–	■	■	■	–	■	■	■	–	–	–	–	–	–	–	6
	Mini	■	–	■	–	■	■	■	■	■	–	–	–	–	–	–	
	Midi	■	–	■	–	■	■	■	■	■	–	–	–	–	–	–	
	Maxi	■	–	■	–	■	■	■	■	■	–	–	–	■	■	–	
Service unit combinations																	
FRC-K	Micro	–															frc
	Mini	■	–	■	–	■	■	–	■	–	–	–	–	–	–	–	
	Midi	■	–	■	–	■	■	–	■	–	–	–	–	–	–	–	
	Maxi	■	–	■	–	■	■	–	■	–	–	–	–	■	■	–	
LFR-K LFRS-K	Micro	–															lfr
	Mini	■	–	■	–	■	■	–	■	■	■	–	–	–	–	–	
	Midi	■	–	■	–	■	■	–	■	■	■	–	–	–	–	–	
	Maxi	■	–	■	–	■	■	–	■	■	■	–	–	■	■	–	
Individual devices																	
Filter regulators LFR/LFRS	Micro	–	■	■	■	–	■	■	■	–	–	–	–	–	–	–	lfr
	Mini	■	–	■	–	■	■	■	■	■	–	–	–	–	–	–	
	Midi	■	–	■	–	■	■	■	■	■	–	–	–	–	–	–	
	Maxi	■	–	■	–	■	■	■	■	■	–	–	–	■	■	–	
Filters LF	Micro	–	■	■	■	–	–	–	–	–	–	–	–	–	–	–	lf
	Mini	■	–	■	–	■	–	–	–	–	–	–	–	–	–	–	
	Midi	■	–	■	–	■	–	–	–	–	–	–	–	–	–	–	
	Maxi	■	–	■	–	■	–	–	–	–	–	–	–	–	–	–	
Fine and micro filters LFMA/LFMB	Micro	–															lfma, lfmb
	Mini	■	–	■	–	■	–	–	–	–	–	–	–	–	–	■	
	Midi	■	–	■	–	■	–	–	–	–	–	–	–	–	–	■	
	Maxi	■	–	■	–	■	–	–	–	–	–	–	–	–	–	■	
Active carbon filters LFX	Micro	–															lfx
	Mini	■	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
	Midi	■	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
	Maxi	■	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
Filter combinations LFMBA	Micro	–															lfmba
	Mini	■	–	■	–	■	–	–	–	–	–	–	–	–	–	■	
	Midi	■	–	■	–	■	–	–	–	–	–	–	–	–	–	■	
	Maxi	■	–	■	–	■	–	–	–	–	–	–	–	–	–	■	
Pressure regulators LR/LRS	Micro	–	–	–	–	–	■	■	■	–	–	–	–	–	–	–	lr
	Mini	–	–	–	–	–	■	■	■	■	–	–	–	■	–	–	
	Midi	–	–	–	–	–	■	■	■	■	–	–	–	■	–	–	
	Maxi	–	–	–	–	–	■	■	■	■	–	–	–	■	■	–	

Service units FRC/FRCS, D series, metal design

FESTO

Product range overview D series service units, metal design

Type	Size	Pneumatic connection										Pressure regulation range [bar]		
		M5	M7	G1/8	G1/4	G3/8	G1/2	G3/4	G1	QS4	QS6	0.5 ... 7	0.5 ... 12	
Individual devices														
Pressure regulators LRB/LRBS		Micro	–											
		Mini	–	–	–	■	–	–	–	–	–	–	■	■
		Midi	–	–	–	–	■	–	–	–	–	–	■	■
		Maxi	–											
Pressure regulator combinations LRB-K		Micro	–											
		Mini	–	–	–	■	■	–	–	–	–	–	■	■
		Midi	–	–	–	–	■	■	–	–	–	–	■	■
		Maxi	–											
Lubricators LOE		Micro	■	■	■	–	–	–	–	–	■	■	–	–
		Mini	–	–	■	■	■	–	–	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–
On-off valves HE		Micro	–											
		Mini	–	–	■	■	■	–	–	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–
On-off valves, electrical HEE		Micro	–											
		Mini	–	–	■	■	■	–	–	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–
On-off valves, pneumatic HEP		Micro	–											
		Mini	–	–	■	■	■	–	–	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–
Soft-start valves HEL		Micro	–											
		Mini	–	–	■	■	■	–	–	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–
Membrane air dryers LDM1		Micro	–											
		Mini	–											
		Midi	–											
		Maxi	–	–	–	–	–	–	■	■	■	–	–	–
Branching modules FRM		Micro	–											
		Mini	–	–	■	■	■	–	–	–	–	–	–	–
		Midi	–	–	–	■	■	■	■	–	–	–	–	–
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–
Distributor block FRZ		Micro	–	–	–	–	–	–	–	–	–	–	–	
		Mini	–	–	–	–	–	–	–	–	–	–	–	–
		Midi	–	–	–	–	–	–	–	–	–	–	–	–
		Maxi	–	–	–	–	–	–	–	–	–	–	–	–

Service units FRC/FRCS, D series, metal design

FESTO

Product range overview D series service units, metal design

Type	Size	Bowl guard		Pressure indication		Actuator lock		Supply voltage			Options		➔ Page/ Internet	
		Metal bowl guard	Plastic bowl	With pressure gauge	Without pressure gauge	Rotary knob with detent	Rotary knob with integrated lock	24 V DC	110 V AC	230 V AC	Non-return function	Pressure switch		
Individual devices														
Pressure regulators LRB/LRBS	Micro	-											lrb	
	Mini	-	-	-	■	■	■	-	-	-	-	-		
	Midi	-	-	-	■	■	■	-	-	-	-	-		
	Maxi	-												
Pressure regulator combinations LRB-K	Micro	-											lrb	
	Mini	-	-	-	■	■	-	-	-	-	-	-		
	Midi	-	-	-	■	■	-	-	-	-	-	-		
	Maxi	-												
Lubricators LOE	Micro	-	■	-	■	-	-	-	-	-	-	-	loe	
	Mini	■	-	-	■	-	-	-	-	-	-	-		
	Midi	■	-	-	■	-	-	-	-	-	-	-		
	Maxi	■	-	-	■	-	-	-	-	-	-	-		
On-off valves HE	Micro	-											he	
	Mini	-	-	-	■	■	-	-	-	-	-	-		
	Midi	-	-	-	■	■	-	-	-	-	-	-		
	Maxi	-	-	-	■	■	-	-	-	-	-	-		
On-off valves, electrical HEE	Micro	-											hee	
	Mini	-	-	-	■	-	-	■	■	■	-	-		
	Midi	-	-	-	■	-	-	■	■	■	-	-		
	Maxi	-	-	-	■	-	-	■	■	■	-	-		
On-off valves, pneumatic HEP	Micro	-											hep	
	Mini	-	-	-	■	-	-	-	-	-	-	-		
	Midi	-	-	-	■	-	-	-	-	-	-	-		
	Maxi	-	-	-	■	-	-	-	-	-	-	-		
Soft-start valves HEL	Micro	-											hel	
	Mini	-	-	-	■	-	-	-	-	-	-	-		
	Midi	-	-	-	■	-	-	-	-	-	-	-		
	Maxi	-	-	-	■	-	-	-	-	-	-	-		
Membrane air dryers LDM1	Micro	-											ldm1	
	Mini	-												
	Midi	-												
	Maxi	■	-	-	■	-	-	-	-	-	-	-		
Branching modules FRM	Micro	-											frm	
	Mini	-	-	-	■	-	-	-	-	-	■	■		
	Midi	-	-	-	■	-	-	-	-	-	■	■		
	Maxi	-	-	-	■	-	-	-	-	-	■	■		
Distributor block FRZ	Micro	-	-	-	■	-	-	-	-	-	-	-	frz	
	Mini	-	-	-	■	-	-	-	-	-	-	-		
	Midi	-	-	-	■	-	-	-	-	-	-	-		
	Maxi	-	-	-	■	-	-	-	-	-	-	-		

Service units FRC/FRCS, D series, metal design



Peripherals overview

FESTO

Micro

Service unit FRC with connection plates,
connection size G $\frac{1}{8}$, QS4 or QS6

Service unit FRC without connection plates,
connection size M5 or M7 in housing



Mounting attachments and accessories

	with connection plates	without connection plates	→ Page/ Internet
1 Mounting bracket HFOE	■	■	hfoe-d
2 Connecting plate kit PBL	—	■	pbl
3 Mounting bracket with hexagon nut HRS	■	■	hrs-d
4 Pressure gauge MA-27	■	■	31

Service units FRC/FRCS, D series, metal design



Peripherals overview

FESTO

Mini/Midi/Maxi

Service unit FRC

Service unit FRCS, lockable



Mounting attachments and accessories			
	Rotary knob with detent	Rotary knob, lockable	→ Page/ Internet
1 Mounting bracket HFOE	■	■	hfoe-d
2 Regulator lock LRVS	■	—	lrvs-d
3 Padlock LRVS-D	■	—	lrvs-d
4 Pressure gauge MA	■	■	31

Service units FRC/FRCS, D series, metal design

FESTO

Type codes


FRC		3/4	D		5M	O	DI	MAXI	A
Basic function									
FRC	Service unit								
FRCS	Service unit, lockable								
Pneumatic connection									
M5	Thread M5								
M7	Thread M7								
QS4	Push-in fitting QS4								
QS6	Push-in fitting QS6								
1/8	Thread G1/8								
1/4	Thread G1/4								
3/8	Thread G3/8								
1/2	Thread G1/2								
3/4	Thread G3/4								
1	Thread G1								
Series									
D	Series								
Pressure regulation range									
	0.5 ... 12 bar								
7	0.5 ... 7 bar								
Grade of filtration									
	40 µm								
5M	5 µm								
Pressure gauge									
	With pressure gauge								
O	Without pressure gauge								
Function (FRC and MAXI size only)									
DI	Directly actuated pressure regulator with integrated return flow function								
Size									
MICRO	Grid dimension 25 mm (without connecting plates)								
MINI	Grid dimension 40 mm (without connecting plates)								
MIDI	Grid dimension 55 mm (without connecting plates)								
MAXI	Grid dimension 66 mm (without connecting plates)								
Condensate drain									
	Turned manually								
H	Semi-automatic								
A	Fully automatic								

Service units FRC/FRCS, D series, metal design


FESTO

Technical data


FRC/FRCS-...-MICRO/MINI/MIDI
Manual rotary condensate drain,
with pressure gauge




Semi or fully automatic condensate
drain, with pressure gauge



FRC/FRCS-...-MAXI
Manual rotary condensate drain,
with pressure gauge



Fully automatic condensate drain,
with pressure gauge



Flow rate
90 ... 8700 l/min

Temperature range
-10 ... +60 °C

Pressure
1 ... 16 bar



- Filter, regulator and lubricator functions in a single unit
- High flow rate and highly efficient removal of contaminants
- Good regulating characteristics with minimal pressure hysteresis
- Setting values are secured by locking the rotary knob
- Lockable rotary knob
- Two pressure regulation ranges: 0.5 ... 7 bar and 0.5 ... 12 bar
- Two pressure gauge connections for different fitting options
- With manual, semi-automatic or fully automatic condensate drain
- Choice of filter cartridges: 5 µm or 40 µm
- New filter cartridges → 30

The following oils are recommended for Festo components:

Viscosity range to
ISO 3448 class VG 32
32 mm²/s (cSt) at 40 °C

- Festo special oil → 31
- ARAL Vitam GF 32
- BP Energol HLP 32
- Esso Nuto H 32
- Mobil DTE 24
- Shell Tellus Oil DO 32

General technical data															
Size	Micro					Mini			Midi				Maxi		
Pneumatic connection	M5	M7	G1/8	QS4	QS6	G1/8	G1/4	G3/8	G1/4	G3/8	G1/2	G3/4	G1/2	G3/4	G1
Operating medium	Compressed air														
Design	Filter regulator with/without pressure gauge														
	Proportional standard mist lubricator														
Type of mounting	Via accessories														
	In-line installation														
Assembly position	Vertical ±5°														
Regulator lock	Rotary knob with detent														
	–					Rotary knob with integrated lock									
Grade of filtration [µm]	5					5 or 40									
Max. hysteresis [bar]	0.3					0.2								0.4	
Pressure regulation range [bar]	0.5 ... 7					0.5 ... 7									
						0.5 ... 12									
Pressure indication	Via pressure gauge														
	M5 prepared					G1/8 prepared			G1/4 prepared				G1/4 prepared		
Max. condensate volume [cm³]	3					22			43				80 ¹⁾		
Input pressure [bar]															
Condensate drain	turned manually	1 ... 10				1 ... 16									
	semi-automatic	1 ... 10				–									
	fully automatic	–				2 ... 12									

1) The max. condensate volume for the FRC-...-DI-MAXI is 43 cm³.

Note: This product conforms to ISO 1179-1 and ISO 228-1

Service units FRC/FRCS, D series, metal design

FESTO

Technical data

Standard nominal flow rate ¹⁾ qnN [l/min]					
Connection	Female thread		Connecting plate		
	M5	M7	G1/8	QS4	QS6
Micro					
FRC/FRCS	90	170	140	100	140

- 1) Measured at p₁ = 10 bar, p₂ = 6 bar and Δp = 1 bar.
A minimum flow rate of 125 l/min is required for flawless functioning.

Standard nominal flow rate ¹⁾ qnN [l/min]						
Connection	G1/8	G1/4	G3/8	G1/2	G3/4	G1
Mini						
FRC/FRCS-...-D-...(-A)	700	1000	1200	–	–	–
FRC/FRCS-...-D-7-...(-A)	800	1300	1500	–	–	–
FRC/FRCS-...-D-5M-...(-A)	600	850	1050	–	–	–
Midi						
FRC/FRCS-...-D-...(-A)	–	1500	2000	2600	2600	–
FRC/FRCS-...-D-7-...(-A)	–	1700	2000	2800	2800	–
FRC/FRCS-...-D-5M-...(-A)	–	1300	1700	1800	2100	–
Maxi						
FRC/FRCS-...-D-...(-A)	–	–	–	7600	8300	8500
FRC/FRCS-...-D-7-...(-A)	–	–	–	7700	8500	8700
FRC/FRCS-...-D-5M-...(-A)	–	–	–	6800	7000	7200
Maxi – Directly actuated pressure regulator with integrated return flow function						
FRC-...-D-...(-A)	–	–	–	3300	3800	4000
FRC-...-D-7-...(-A)	–	–	–	4500	5000	5200
FRC-...-D-5M-...(-A)	–	–	–	3000	3600	3800

- 1) Measured at p₁ = 10 bar, p₂ = 6 bar and Δp = 1 bar.
A minimum flow rate of 125 l/min is required for flawless functioning.

Screw-in depth of connecting thread [mm]					
Connection	M5	M7	G1/8	QS4	QS6
Micro					
In housing	5	6	–	–	–
In connecting plates	–	–	8	–	–

Ambient conditions		Micro	Mini	Midi	Maxi
Size					
Ambient temperature	[°C]	–10 ... +60			
Temperature of medium	[°C]	–10 ... +60			
Corrosion resistance class	CRC ¹⁾	2			

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Service units FRC/FRCS, D series, metal design


FESTO

Technical data

Weight [g]						
Size	Micro		Mini	Midi	Maxi	
	Female thread	Connecting plate			Connection G½, G¾	Connection G1
With pressure gauge						
FRC-...	113	133	660	1440	2390	2520
FRC-...-DI	–	–	–	–	2670	2670
FRCS-...	–	–	760	1680	2490	2620
Without pressure gauge						
FRC-...	103	123	600	1350	2280	2460
FRC-...-DI	–	–	–	–	2600	2600
FRCS-...	–	–	700	1590	2380	2560

Materials

Sectional view



Service units	Micro	Mini/Midi/Maxi
1 Housing	Wrought aluminium alloy	Die-cast zinc
2 Connecting plates	Wrought aluminium alloy	Die-cast zinc/aluminium
3 Bowl	Polycarbonate	Polycarbonate
4 Metal bowl guard	–	Aluminium
5 Regulating knob	Polyacetal	Polyacetal
6 Support	Polycarbonate	–
– Seals	Nitrile rubber	Nitrile rubber


Service units FRC/FRCS, D series, metal design

Technical data


FESTO

Standard flow rate q_n as a function of the output pressure p_2


FRC-M5-...-MICRO




FRC-M7-...-MICRO B




FRC-QS4-...-MICRO




FRC-QS6-...-MICRO and FRC-1/8-...-MICRO



FRC/FRCS-1/4-D-MINI



FRC/FRCS-1/2-D-MIDI



Primary pressure $p_1 = 10$ bar


Service units FRC/FRCS, D series, metal design

FESTO


Technical data

Standard flow rate q_n as a function of the output pressure p_2

FRC/FRCS-1-D-MAXI



FRC-1-D-DI-MAXI



Primary pressure $p_1 = 10$ bar

Note


In order to improve control behaviour, primary-pressure

dependent internal air consumption is provided on the FRC/FRCS-...-MAXI.

Dimensions

Download CAD Data → www.festo.com/us/cad

Micro



Type	B1	B2	D1	H1
FRC-M5-D-7-5M-MICRO (H)	50	-	M5	-
FRC-M7-D-7-5M-MICRO (H) B			M7	
FRC-1/8-D-7-5M-MICRO (H)			G1/8	
FRC-QS4-D-7-5M-MICRO (H)	70	~2.5	QS4	~8
FRC-QS6-D-7-5M-MICRO (H)			QS6	~10

Note: This product conforms to ISO 1179-1 and ISO 228-1

Service units FRC/FRCS, D series, metal design


Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad

Mini/Midi/Maxi



Type	B1	B2	B3	B4	D1	D2 Ø	D3	D4	D5 Ø	D6 Ø
Mini										
FRC/FRCS-1⁄8-D-MINI	104	92	40	76	G1⁄8	31	M4	M36x1.5	41	38
FRC/FRCS-1⁄4-D-MINI					G1⁄4					
FRC/FRCS-3⁄8-D-MINI					G3⁄8					
Midi										
FRC/FRCS-1⁄4-D-MIDI	140	125	55	95	G1⁄4	50	M5	M52x1.5	50	52
FRC/FRCS-3⁄8-D-MIDI					G3⁄8					
FRC/FRCS-1⁄2-D-MIDI					G1⁄2					
FRC/FRCS-3⁄4-D-MIDI					G3⁄4					
Maxi										
FRC/FRCS-1⁄2-D-MAXI	162	146	66	107	G1⁄2	31	M5	M36x1.5	50	65
FRC-1⁄2-D-DI-MAXI						49		M52x1.5		
FRC/FRCS-3⁄4-D-MAXI					G3⁄4	31		M36x1.5		
FRC-3⁄4-D-DI-MAXI						49		M52x1.5		
FRC/FRCS-1-D-MAXI	182	157			G1	31		M36x1.5		
FRC-1-D-DI-MAXI						49		M52x1.5		

Note: This product conforms to ISO 1179-1 and ISO 228-1

Service units FRC/FRCS, D series, metal design

FESTO

Technical data

Type	H1	H2	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	T1	≈C 1	≈C 2
Mini															
FRC/FRCS-1⁄8-D-MINI	20	11	193	169	60	69	100	98	60	15	19	3	7	14	22
FRC/FRCS-1⁄4-D-MINI															
FRC/FRCS-3⁄8-D-MINI															
Midi															
FRC/FRCS-1⁄4-D-MIDI	32	22	250	204	80	99	120	130	60	15	19	3	8	14	24
FRC/FRCS-3⁄8-D-MIDI															
FRC/FRCS-1⁄2-D-MIDI															
FRC/FRCS-3⁄4-D-MIDI															
Maxi															
FRC/FRCS-1⁄2-D-MAXI	32	22	252	228	90	82	150	111	60	15	19	3	8	14	24
FRC-1⁄2-D-DI-MAXI			275			105		135							
FRC/FRCS-3⁄4-D-MAXI			252			82		111							
FRC-3⁄4-D-DI-MAXI			275			105		135							
FRC/FRCS-1-D-MAXI	40		252			82		111							
FRC-1-D-DI-MAXI			275			105		135							

Service units FRC/FRCS, D series, metal design

Technical data

FESTO

Ordering data				
Pressure regulation range 0.5 ... 7 bar				
Condensate drain	Size	Connection	Grade of filtration 5 µm	
			Part No.	Type
With pressure gauge				
Turned manually	Micro	Without threaded connecting plates, connecting thread in housing		
		M5	527860	FRC-M5-D-7-5M-MICRO
		M7	534189	FRC-M7-D-7-5M-MICRO-B
		With threaded connecting plates		
		G1/8	527864	FRC-1/8-D-7-5M-MICRO
		With connecting plate and push-in fitting		
		QS4	527876	FRC-QS4-D-7-5M-MICRO
		QS6	527880	FRC-QS6-D-7-5M-MICRO
Semi-automatic	Micro	Without threaded connecting plates, connecting thread in housing		
		M5	527861	FRC-M5-D-7-5M-MICRO-H
		M7	534190	FRC-M7-D-7-5M-MICRO-H-B
		With threaded connecting plates		
		G1/8	527865	FRC-1/8-D-7-5M-MICRO-H
		With connecting plate and push-in fitting		
		QS4	527877	FRC-QS4-D-7-5M-MICRO-H
		QS6	527881	FRC-QS6-D-7-5M-MICRO-H
Without pressure gauge				
Turned manually	Micro	Without threaded connecting plates, connecting thread in housing		
		M5	527862	FRC-M5-D-7-O-5M-MICRO
		M7	534191	FRC-M7-D-7-O-5M-MICRO-B
		With threaded connecting plates		
		G1/8	527866	FRC-1/8-D-7-O-5M-MICRO
		With connecting plate and push-in fitting		
		QS4	527878	FRC-QS4-D-7-O-5M-MICRO
		QS6	527882	FRC-QS6-D-7-O-5M-MICRO
Semi-automatic	Micro	Without threaded connecting plates, connecting thread in housing		
		M5	527863	FRC-M5-D-7-O-5M-MICRO-H
		M7	534192	FRC-M7-D-7-O-5M-MICRO-H-B
		With threaded connecting plates		
		G1/8	527867	FRC-1/8-D-7-O-5M-MICRO-H
		With connecting plate and push-in fitting		
		QS4	527879	FRC-QS4-D-7-O-5M-MICRO-H
		QS6	527883	FRC-QS6-D-7-O-5M-MICRO-H

Service units FRC/FRCS, D series, metal design

FESTO

Technical data

Ordering data						
Pressure regulation range 0.5 ... 12 bar, metal bowl guard						
Condensate drain	Size	Connection	Grade of filtration 5 µm		Grade of filtration 40 µm	
			Part No.	Type	Part No.	Type
With pressure gauge						
Turned manually	Mini	G1/8	162770	FRC-1/8-D-5M-MINI	159604	FRC-1/8-D-MINI
		G1/4	162771	FRC-1/4-D-5M-MINI	159605	FRC-1/4-D-MINI
		G3/8	162772	FRC-3/8-D-5M-MINI	162734	FRC-3/8-D-MINI
	Midi	G1/4	186499	FRC-1/4-D-5M-MIDI	186497	FRC-1/4-D-MIDI
		G3/8	162773	FRC-3/8-D-5M-MIDI	159588	FRC-3/8-D-MIDI
		G1/2	162774	FRC-1/2-D-5M-MIDI	159590	FRC-1/2-D-MIDI
		G3/4	162775	FRC-3/4-D-5M-MIDI	162735	FRC-3/4-D-MIDI
	Maxi	G1/2	186507	FRC-1/2-D-5M-MAXI	186505	FRC-1/2-D-MAXI
		G3/4	162776	FRC-3/4-D-5M-MAXI	159606	FRC-3/4-D-MAXI
		G1	162777	FRC-1-D-5M-MAXI	159607	FRC-1-D-MAXI
Fully automatic	Mini	G1/8	162778	FRC-1/8-D-5M-MINI-A	159608	FRC-1/8-D-MINI-A
		G1/4	162779	FRC-1/4-D-5M-MINI-A	159609	FRC-1/4-D-MINI-A
		G3/8	162780	FRC-3/8-D-5M-MINI-A	162736	FRC-3/8-D-MINI-A
	Midi	G1/4	186502	FRC-1/4-D-5M-MIDI-A	186500	FRC-1/4-D-MIDI-A
		G3/8	162781	FRC-3/8-D-5M-MIDI-A	159589	FRC-3/8-D-MIDI-A
		G1/2	162782	FRC-1/2-D-5M-MIDI-A	159591	FRC-1/2-D-MIDI-A
		G3/4	162783	FRC-3/4-D-5M-MIDI-A	162737	FRC-3/4-D-MIDI-A
	Maxi	G1/2	186510	FRC-1/2-D-5M-MAXI-A	186508	FRC-1/2-D-MAXI-A
		G3/4	162784	FRC-3/4-D-5M-MAXI-A	159610	FRC-3/4-D-MAXI-A
		G1	162785	FRC-1-D-5M-MAXI-A	159611	FRC-1-D-MAXI-A
Without pressure gauge						
Turned manually	Mini	G1/8	192650	FRC-1/8-D-5M-O-MINI	162738	FRC-1/8-D-O-MINI
		G1/4	192651	FRC-1/4-D-5M-O-MINI	162739	FRC-1/4-D-O-MINI
		G3/8	192652	FRC-3/8-D-5M-O-MINI	162740	FRC-3/8-D-O-MINI
	Midi	G1/4	192653	FRC-1/4-D-5M-O-MIDI	186498	FRC-1/4-D-O-MIDI
		G3/8	192654	FRC-3/8-D-5M-O-MIDI	162741	FRC-3/8-D-O-MIDI
		G1/2	192655	FRC-1/2-D-5M-O-MIDI	162742	FRC-1/2-D-O-MIDI
		G3/4	192656	FRC-3/4-D-5M-O-MIDI	162743	FRC-3/4-D-O-MIDI
	Maxi	G1/2	192657	FRC-1/2-D-5M-O-MAXI	186506	FRC-1/2-D-O-MAXI
		G3/4	192658	FRC-3/4-D-5M-O-MAXI	162744	FRC-3/4-D-O-MAXI
		G1	192659	FRC-1-D-5M-O-MAXI	162745	FRC-1-D-O-MAXI
Fully automatic	Mini	G1/8	192660	FRC-1/8-D-5M-O-MINI-A	162746	FRC-1/8-D-O-MINI-A
		G1/4	192661	FRC-1/4-D-5M-O-MINI-A	162747	FRC-1/4-D-O-MINI-A
		G3/8	192662	FRC-3/8-D-5M-O-MINI-A	162748	FRC-3/8-D-O-MINI-A
	Midi	G1/4	192663	FRC-1/4-D-5M-O-MIDI-A	186501	FRC-1/4-D-O-MIDI-A
		G3/8	192664	FRC-3/8-D-5M-O-MIDI-A	162749	FRC-3/8-D-O-MIDI-A
		G1/2	192665	FRC-1/2-D-5M-O-MIDI-A	162750	FRC-1/2-D-O-MIDI-A
		G3/4	192666	FRC-3/4-D-5M-O-MIDI-A	162751	FRC-3/4-D-O-MIDI-A
	Maxi	G1/2	192667	FRC-1/2-D-5M-O-MAXI-A	186509	FRC-1/2-D-O-MAXI-A
		G3/4	192668	FRC-3/4-D-5M-O-MAXI-A	162752	FRC-3/4-D-O-MAXI-A
		G1	192669	FRC-1-D-5M-O-MAXI-A	162753	FRC-1-D-O-MAXI-A

Service units FRC/FRCS, D series, metal design

FESTO

Technical data

Ordering data				
Pressure regulation range 0.5 ... 7 bar, metal bowl guard				
Condensate drain	Size	Connection	Grade of filtration 40 µm	
			Part No.	Type
With pressure gauge				
Turned manually	Mini	G1/8	162754	FRC-1/8-D-7-MINI
		G1/4	162755	FRC-1/4-D-7-MINI
		G3/8	162756	FRC-3/8-D-7-MINI
	Midi	G1/4	186503	FRC-1/4-D-7-MIDI
		G3/8	162757	FRC-3/8-D-7-MIDI
		G1/2	162758	FRC-1/2-D-7-MIDI
		G3/4	162759	FRC-3/4-D-7-MIDI
	Maxi	G1/2	186511	FRC-1/2-D-7-MAXI
		G3/4	162760	FRC-3/4-D-7-MAXI
		G1	162761	FRC-1-D-7-MAXI
Fully automatic	Mini	G1/8	162762	FRC-1/8-D-7-MINI-A
		G1/4	162763	FRC-1/4-D-7-MINI-A
		G3/8	162764	FRC-3/8-D-7-MINI-A
	Midi	G1/4	186504	FRC-1/4-D-7-MIDI-A
		G3/8	162765	FRC-3/8-D-7-MIDI-A
		G1/2	162766	FRC-1/2-D-7-MIDI-A
		G3/4	162767	FRC-3/4-D-7-MIDI-A
	Maxi	G1/2	186512	FRC-1/2-D-7-MAXI-A
		G3/4	162768	FRC-3/4-D-7-MAXI-A
		G1	162769	FRC-1-D-7-MAXI-A
Without pressure gauge				
Turned manually	Mini	G1/8	192630	FRC-1/8-D-7-O-MINI
		G1/4	192631	FRC-1/4-D-7-O-MINI
		G3/8	192632	FRC-3/8-D-7-O-MINI
	Midi	G1/4	192633	FRC-1/4-D-7-O-MIDI
		G3/8	192634	FRC-3/8-D-7-O-MIDI
		G1/2	192635	FRC-1/2-D-7-O-MIDI
		G3/4	192636	FRC-3/4-D-7-O-MIDI
	Maxi	G1/2	192637	FRC-1/2-D-7-O-MAXI
		G3/4	192638	FRC-3/4-D-7-O-MAXI
		G1	192639	FRC-1-D-7-O-MAXI
Fully automatic	Mini	G1/8	192640	FRC-1/8-D-7-O-MINI-A
		G1/4	192641	FRC-1/4-D-7-O-MINI-A
		G3/8	192642	FRC-3/8-D-7-O-MINI-A
	Midi	G1/4	192643	FRC-1/4-D-7-O-MIDI-A
		G3/8	192644	FRC-3/8-D-7-O-MIDI-A
		G1/2	192645	FRC-1/2-D-7-O-MIDI-A
		G3/4	192646	FRC-3/4-D-7-O-MIDI-A
	Maxi	G1/2	192647	FRC-1/2-D-7-O-MAXI-A
		G3/4	192648	FRC-3/4-D-7-O-MAXI-A
		G1	192649	FRC-1-D-7-O-MAXI-A

Service units FRC/FRCS, D series, metal design

FESTO

Technical data

Ordering data						
Pressure regulation range 0.5 ... 12 bar, directly actuated pressure regulator with integrated return flow function, metal bowl guard						
Condensate drain	Size	Connection	Grade of filtration 5 µm		Grade of filtration 40 µm	
			Part No.	Type	Part No.	Type
With pressure gauge						
Turned manually	Maxi	G½	192406	FRC-½-D-5M-DI-MAXI	192404	FRC-½-D-DI-MAXI
		G¾	192412	FRC-¾-D-5M-DI-MAXI	192410	FRC-¾-D-DI-MAXI
		G1	192418	FRC-1-D-5M-DI-MAXI	192416	FRC-1-D-DI-MAXI
Fully automatic	Maxi	G½	192424	FRC-½-D-5M-DI-MAXI-A	192422	FRC-½-D-DI-MAXI-A
		G¾	192430	FRC-¾-D-5M-DI-MAXI-A	192428	FRC-¾-D-DI-MAXI-A
		G1	192436	FRC-1-D-5M-DI-MAXI-A	192434	FRC-1-D-DI-MAXI-A
Without pressure gauge						
Turned manually	Maxi	G½	192407	FRC-½-D-5M-O-DI-MAXI	192405	FRC-½-D-O-DI-MAXI
		G¾	192413	FRC-¾-D-5M-O-DI-MAXI	192411	FRC-¾-D-O-DI-MAXI
		G1	192419	FRC-1-D-5M-O-DI-MAXI	192417	FRC-1-D-O-DI-MAXI
Fully automatic	Maxi	G½	192425	FRC-½-D-5M-O-DI-MAXI-A	192423	FRC-½-D-O-DI-MAXI-A
		G¾	192431	FRC-¾-D-5M-O-DI-MAXI-A	192429	FRC-¾-D-O-DI-MAXI-A
		G1	192437	FRC-1-D-5M-O-DI-MAXI-A	192435	FRC-1-D-O-DI-MAXI-A

Ordering data						
Pressure regulation range 0.5 ... 7 bar, directly actuated pressure regulator with integrated return flow function, metal bowl guard						
Condensate drain	Size	Connection	Grade of filtration 5 µm		Grade of filtration 40 µm	
			Part No.	Type	Part No.	Type
With pressure gauge						
Turned manually	Maxi	G½	–		192408	FRC-½-D-7-DI-MAXI
		G¾	–		192414	FRC-¾-D-7-DI-MAXI
		G1	–		192420	FRC-1-D-7-DI-MAXI
Fully automatic	Maxi	G½	–		192426	FRC-½-D-7-DI-MAXI-A
		G¾	–		192432	FRC-¾-D-7-DI-MAXI-A
		G1	–		192438	FRC-1-D-7-DI-MAXI-A
Without pressure gauge						
Turned manually	Maxi	G½	–		192409	FRC-½-D-7-O-DI-MAXI
		G¾	–		192415	FRC-¾-D-7-O-DI-MAXI
		G1	–		192421	FRC-1-D-7-O-DI-MAXI
Fully automatic	Maxi	G½	–		192427	FRC-½-D-7-O-DI-MAXI-A
		G¾	–		192433	FRC-¾-D-7-O-DI-MAXI-A
		G1	–		192439	FRC-1-D-7-O-DI-MAXI-A

Service units FRC/FRCS, D series, metal design

FESTO

Technical data

Ordering data						
Pressure regulation range 0.5 ... 12 bar, metal bowl guard, lockable						
Condensate drain	Size	Connection	Grade of filtration 5 µm		Grade of filtration 40 µm	
			Part No.	Type	Part No.	Type
With pressure gauge						
Turned manually	Mini	G $\frac{1}{8}$	194860	FRCS- $\frac{1}{8}$ -D-5M-MINI	194852	FRCS- $\frac{1}{8}$ -D-MINI
		G $\frac{1}{4}$	194872	FRCS- $\frac{1}{4}$ -D-5M-MINI	194864	FRCS- $\frac{1}{4}$ -D-MINI
		G $\frac{3}{8}$	194884	FRCS- $\frac{3}{8}$ -D-5M-MINI	194876	FRCS- $\frac{3}{8}$ -D-MINI
	Midi	G $\frac{1}{4}$	194896	FRCS- $\frac{1}{4}$ -D-5M-MIDI	194888	FRCS- $\frac{1}{4}$ -D-MIDI
		G $\frac{3}{8}$	194908	FRCS- $\frac{3}{8}$ -D-5M-MIDI	194900	FRCS- $\frac{3}{8}$ -D-MIDI
		G $\frac{1}{2}$	194920	FRCS- $\frac{1}{2}$ -D-5M-MIDI	194912	FRCS- $\frac{1}{2}$ -D-MIDI
		G $\frac{3}{4}$	194932	FRCS- $\frac{3}{4}$ -D-5M-MIDI	194924	FRCS- $\frac{3}{4}$ -D-MIDI
	Maxi	G $\frac{1}{2}$	194944	FRCS- $\frac{1}{2}$ -D-5M-MAXI	194936	FRCS- $\frac{1}{2}$ -D-MAXI
		G $\frac{3}{4}$	194956	FRCS- $\frac{3}{4}$ -D-5M-MAXI	194948	FRCS- $\frac{3}{4}$ -D-MAXI
		G1	194968	FRCS-1-D-5M-MAXI	194960	FRCS-1-D-MAXI
Fully automatic	Mini	G $\frac{1}{8}$	194862	FRCS- $\frac{1}{8}$ -D-5M-MINI-A	194853	FRCS- $\frac{1}{8}$ -D-MINI-A
		G $\frac{1}{4}$	194874	FRCS- $\frac{1}{4}$ -D-5M-MINI-A	194865	FRCS- $\frac{1}{4}$ -D-MINI-A
		G $\frac{3}{8}$	194886	FRCS- $\frac{3}{8}$ -D-5M-MINI-A	194877	FRCS- $\frac{3}{8}$ -D-MINI-A
	Midi	G $\frac{1}{4}$	194898	FRCS- $\frac{1}{4}$ -D-5M-MIDI-A	194889	FRCS- $\frac{1}{4}$ -D-MIDI-A
		G $\frac{3}{8}$	194910	FRCS- $\frac{3}{8}$ -D-5M-MIDI-A	194901	FRCS- $\frac{3}{8}$ -D-MIDI-A
		G $\frac{1}{2}$	194922	FRCS- $\frac{1}{2}$ -D-5M-MIDI-A	194913	FRCS- $\frac{1}{2}$ -D-MIDI-A
		G $\frac{3}{4}$	194934	FRCS- $\frac{3}{4}$ -D-5M-MIDI-A	194925	FRCS- $\frac{3}{4}$ -D-MIDI-A
	Maxi	G $\frac{1}{2}$	194946	FRCS- $\frac{1}{2}$ -D-5M-MAXI-A	194937	FRCS- $\frac{1}{2}$ -D-MAXI-A
		G $\frac{3}{4}$	194958	FRCS- $\frac{3}{4}$ -D-5M-MAXI-A	194949	FRCS- $\frac{3}{4}$ -D-MAXI-A
		G1	194970	FRCS-1-D-5M-MAXI-A	194961	FRCS-1-D-MAXI-A
Without pressure gauge						
Turned manually	Mini	G $\frac{1}{8}$	194861	FRCS- $\frac{1}{8}$ -D-5M-O-MINI	194854	FRCS- $\frac{1}{8}$ -D-O-MINI
		G $\frac{1}{4}$	194873	FRCS- $\frac{1}{4}$ -D-5M-O-MINI	194866	FRCS- $\frac{1}{4}$ -D-O-MINI
		G $\frac{3}{8}$	194885	FRCS- $\frac{3}{8}$ -D-5M-O-MINI	194878	FRCS- $\frac{3}{8}$ -D-O-MINI
	Midi	G $\frac{1}{4}$	194897	FRCS- $\frac{1}{4}$ -D-5M-O-MIDI	194890	FRCS- $\frac{1}{4}$ -D-O-MIDI
		G $\frac{3}{8}$	194909	FRCS- $\frac{3}{8}$ -D-5M-O-MIDI	194902	FRCS- $\frac{3}{8}$ -D-O-MIDI
		G $\frac{1}{2}$	194921	FRCS- $\frac{1}{2}$ -D-5M-O-MIDI	194914	FRCS- $\frac{1}{2}$ -D-O-MIDI
		G $\frac{3}{4}$	194933	FRCS- $\frac{3}{4}$ -D-5M-O-MIDI	194926	FRCS- $\frac{3}{4}$ -D-O-MIDI
	Maxi	G $\frac{1}{2}$	194945	FRCS- $\frac{1}{2}$ -D-5M-O-MAXI	194938	FRCS- $\frac{1}{2}$ -D-O-MAXI
		G $\frac{3}{4}$	194957	FRCS- $\frac{3}{4}$ -D-5M-O-MAXI	194950	FRCS- $\frac{3}{4}$ -D-O-MAXI
		G1	194969	FRCS-1-D-5M-O-MAXI	194962	FRCS-1-D-O-MAXI
Fully automatic	Mini	G $\frac{1}{8}$	194863	FRCS- $\frac{1}{8}$ -D-5M-O-MINI-A	194855	FRCS- $\frac{1}{8}$ -D-O-MINI-A
		G $\frac{1}{4}$	194875	FRCS- $\frac{1}{4}$ -D-5M-O-MINI-A	194867	FRCS- $\frac{1}{4}$ -D-O-MINI-A
		G $\frac{3}{8}$	194887	FRCS- $\frac{3}{8}$ -D-5M-O-MINI-A	194879	FRCS- $\frac{3}{8}$ -D-O-MINI-A
	Midi	G $\frac{1}{4}$	194899	FRCS- $\frac{1}{4}$ -D-5M-O-MIDI-A	194891	FRCS- $\frac{1}{4}$ -D-O-MIDI-A
		G $\frac{3}{8}$	194911	FRCS- $\frac{3}{8}$ -D-5M-O-MIDI-A	194903	FRCS- $\frac{3}{8}$ -D-O-MIDI-A
		G $\frac{1}{2}$	194923	FRCS- $\frac{1}{2}$ -D-5M-O-MIDI-A	194915	FRCS- $\frac{1}{2}$ -D-O-MIDI-A
	G $\frac{3}{4}$	194935	FRCS- $\frac{3}{4}$ -D-5M-O-MIDI-A	194927	FRCS- $\frac{3}{4}$ -D-O-MIDI-A	
	Maxi	G $\frac{1}{2}$	194947	FRCS- $\frac{1}{2}$ -D-5M-O-MAXI-A	194939	FRCS- $\frac{1}{2}$ -D-O-MAXI-A
		G $\frac{3}{4}$	194959	FRCS- $\frac{3}{4}$ -D-5M-O-MAXI-A	194951	FRCS- $\frac{3}{4}$ -D-O-MAXI-A
G1		194971	FRCS-1-D-5M-O-MAXI-A	194963	FRCS-1-D-O-MAXI-A	

Service units FRC/FRCS, D series, metal design

FESTO

Technical data

Ordering data				
Pressure regulation range 0.5 ... 7 bar, metal bowl guard, lockable				
Condensate drain	Size	Connection	Grade of filtration 40 µm	
			Part No.	Type
With pressure gauge				
Turned manually	Mini	G1⁄8	194856	FRCS-1⁄8-D-7-MINI
		G1⁄4	194868	FRCS-1⁄4-D-7-MINI
		G3⁄8	194880	FRCS-3⁄8-D-7-MINI
	Midi	G1⁄4	194892	FRCS-1⁄4-D-7-MIDI
		G3⁄8	194904	FRCS-3⁄8-D-7-MIDI
		G1⁄2	194916	FRCS-1⁄2-D-7-MIDI
		G3⁄4	194928	FRCS-3⁄4-D-7-MIDI
	Maxi	G1⁄2	194940	FRCS-1⁄2-D-7-MAXI
		G3⁄4	194952	FRCS-3⁄4-D-7-MAXI
		G1	194964	FRCS-1-D-7-MAXI
Fully automatic	Mini	G1⁄8	194858	FRCS-1⁄8-D-7-MINI-A
		G1⁄4	194870	FRCS-1⁄4-D-7-MINI-A
		G3⁄8	194882	FRCS-3⁄8-D-7-MINI-A
	Midi	G1⁄4	194894	FRCS-1⁄4-D-7-MIDI-A
		G3⁄8	194906	FRCS-3⁄8-D-7-MIDI-A
		G1⁄2	194918	FRCS-1⁄2-D-7-MIDI-A
		G3⁄4	194930	FRCS-3⁄4-D-7-MIDI-A
	Maxi	G1⁄2	194942	FRCS-1⁄2-D-7-MAXI-A
		G3⁄4	194954	FRCS-3⁄4-D-7-MAXI-A
		G1	194966	FRCS-1-D-7-MAXI-A
Without pressure gauge				
Turned manually	Mini	G1⁄8	194857	FRCS-1⁄8-D-7-O-MINI
		G1⁄4	194869	FRCS-1⁄4-D-7-O-MINI
		G3⁄8	194881	FRCS-3⁄8-D-7-O-MINI
	Midi	G1⁄4	194893	FRCS-1⁄4-D-7-O-MIDI
		G3⁄8	194905	FRCS-3⁄8-D-7-O-MIDI
		G1⁄2	194917	FRCS-1⁄2-D-7-O-MIDI
		G3⁄4	194929	FRCS-3⁄4-D-7-O-MIDI
	Maxi	G1⁄2	194941	FRCS-1⁄2-D-7-O-MAXI
		G3⁄4	194953	FRCS-3⁄4-D-7-O-MAXI
		G1	194965	FRCS-1-D-7-O-MAXI
Fully automatic	Mini	G1⁄8	194859	FRCS-1⁄8-D-7-O-MINI-A
		G1⁄4	194871	FRCS-1⁄4-D-7-O-MINI-A
		G3⁄8	194883	FRCS-3⁄8-D-7-O-MINI-A
	Midi	G1⁄4	194895	FRCS-1⁄4-D-7-O-MIDI-A
		G3⁄8	194907	FRCS-3⁄8-D-7-O-MIDI-A
		G1⁄2	194919	FRCS-1⁄2-D-7-O-MIDI-A
		G3⁄4	194931	FRCS-3⁄4-D-7-O-MIDI-A
	Maxi	G1⁄2	194943	FRCS-1⁄2-D-7-O-MAXI-A
		G3⁄4	194955	FRCS-3⁄4-D-7-O-MAXI-A
		G1	194967	FRCS-1-D-7-O-MAXI-A

Service units FRC, D series, polymer

Product range overview D series service units, polymer

FESTO

Type	Size	Pneumatic connection			Pressure regulation range [bar]	Grade of filtration	
		G1/8	G1/4	G1/2		[µm]	

Service units FRC, D series, polymer

Product range overview D series service units, polymer


FESTO

Type	Size	Condensate drain		Pressure display		Actuator lock	Regulating functions		→ Page/ Internet
		Manual rotary	Semi-automatic	With pressure gauge	Without pressure gauge	Rotary knob with detent	With secondary venting	With return flow function	
Service units									
FRC	Mini	■	■	■	–	■	■	■	24
Individual devices									
Filter regulators LFR	Mini	■	■	■	■	■	■	■	lfr
Pressure regulators LR	Mini	–	–	■	■	■	■	■	lr
Pressure regulator combinations LRB-K	Mini	–	–	–	■	■	■	■	lrb

Service units FRC, D series, polymer

Peripherals overview

FESTO



Mounting attachments and accessories		→ Page/ Internet
1	Connecting plate kit PBL	pbl
2	Mounting bracket HFOE	hfoe-d
3	Mounting bracket HR-D	hr-d
4	Hex nut HMR	hmr-d
5	Threaded pin FRB	frb-db

Service units FRC, D series, polymer

FESTO

Type codes


		FRC	–	1/8	–	DB	–	7	–	5M	–	MINI	–	H
Basic function														
FRC	Service unit													
Pneumatic connection														
1/8	Thread G1/8													
1/4	Thread G1/4													
Series														
DB	Series													
Pressure regulation range														
7	0.5 ... 7 bar													
Grade of filtration														
	40 µm													
5M	5 µm													
Size														
	MINI													
Condensate drain														
	Manual rotary													
H	Semi-automatic													

Service units FRC, D series, polymer


Technical data

FESTO

Manual rotary condensate drain



Semi-automatic condensate drain



Flow rate
400 ... 650 l/min

Temperature range
-5 ... +50 °C

Pressure
1.5 ... 10 bar



- Filter, regulator and lubricator functions in a single unit
- High flow rate and highly efficient removal of contaminants
- Good regulating characteristics with minimal pressure hysteresis
- Setting values are secured by means of the rotary knob with detent
- With manual or semi-automatic condensate drain
- New filter cartridges → 30

The following oils are recommended for Festo components:

Viscosity range to
ISO 3448 class VG 32
32 mm²/s (cSt) at 40 °C

- Festo special oil → 31
- ARAL Vitam GF 32
- BP Energol HLP 32
- Esso Nuto H 32
- Mobil DTE 24
- Shell Tellus Oil DO 32

General technical data		
Size	Mini	
Pneumatic connection	G1/8	G1/4
Operating medium	Compressed air	
Design	Filter/regulator/lubricator	
Regulating function	With return flow function With secondary venting	
Type of mounting	Inline installation Via through-holes Via mounting bracket	
Assembly position	Vertical ±5°	
Regulator lock	Rotary knob with detent	
Grade of filtration [µm]	5 or 40	
Max. hysteresis [bar]	0.5	
Input pressure [bar]	1.5 ... 10	
Pressure regulation range [bar]	0.5 ... 7	
Pressure indication	Via pressure gauge	
Pressure gauge connection	G1/8	

Standard nominal flow rate ¹⁾ qnN [l/min]			
Pneumatic connection		G1/8	G1/4
Mini			
Grade of filtration	5 µm	≥ 400	≥ 550
	40 µm	≥ 550	≥ 650

1) Measured at p1 = 10 bar, p2 = 6 bar and Δp = 1 bar.

Service units FRC, D series, polymer

Technical data

Ambient conditions		
Size	Mini	
Ambient temperature	[°C]	−5 ... +50
Temperature of medium	[°C]	−5 ... +50
Corrosion resistance class	CRC ¹⁾	1


1) Corrosion resistance class 1 according to Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Weight [g]	
Size	Mini
Service unit	300

Materials

Sectional view



Service unit	Mini
1 Housing	Polyamide, reinforced
2 Bowl	Polycarbonate
3 Filter	Polyethylene
4 Rotary knob	Polyacetate
– Seals	Nitrile rubber

Service units FRC, D series, polymer

Technical data



FESTO

Standard flow rate q_n as a function of output pressure p_2

Pneumatic connection $G\frac{1}{8}$

Grade of filtration $5\ \mu\text{m}$



Grade of filtration $40\ \mu\text{m}$



Pneumatic connection $G\frac{1}{4}$

Grade of filtration $5\ \mu\text{m}$

Grade of filtration $40\ \mu\text{m}$



Primary pressure $p_1 = 10\ \text{bar}$

Note

Slight leakage at the output has been taken into account in the design. It improves the control behaviour of the non pre-pressure compensated controller.

In a few cases leakage may amount to 500 l/min.

Service units FRC, D series, polymer


Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad

Mini



Type	D1
FRC-1/8-DB	G1/8
FRC-1/4-DB	G1/4

Ordering data

Pressure regulation range 0.5 ... 7 bar

Condensate drain	Size	Connection	Grade of filtration 5 µm		Grade of filtration 40 µm	
			Part No.	Type	Part No.	Type
Manual rotary	Mini	G1/8	537659	FRC-1/8-DB-7-5M-MINI	537655	FRC-1/8-DB-7-MINI
		G1/4	537658	FRC-1/4-DB-7-5M-MINI	537654	FRC-1/4-DB-7-MINI
Semi-automatic	Mini	G1/8	537661	FRC-1/8-DB-7-5M-MINI-H	537657	FRC-1/8-DB-7-MINI-H
		G1/4	537660	FRC-1/4-DB-7-5M-MINI-H	537656	FRC-1/4-DB-7-MINI-H

Service units FRC/FRCS, D series

Accessories

FESTO

Filter cartridges, D series, metal design



Ordering data			
Size	Grade of filtration [µm]	Part No.	Type
Micro	5	526818	LFP-D-MICRO-5M
Mini	5 (colour: blue)	159640	LFP-D-MINI-5M
	40 (colour: white)	363665	LFP-D-MINI-40M
Midi	5 (colour: blue)	159594	LFP-D-MIDI-5M
	40 (colour: white)	363667	LFP-D-MIDI-40M
Maxi	5 (colour: blue)	159641	LFP-D-MAXI-5M
	40 (colour: white)	363664	LFP-D-MAXI-40M

Filter cartridges, D series, polymer



Ordering data			
Size	Grade of filtration [µm]	Part No.	Type
Mini	5	547957	LFP-DB-MINI-5M
	40	534502	MS4-LFP-E

Service units FRC/FRCS, D series

Accessories

FESTO

Special oil



Ordering data		
Scope of delivery	Part No.	Type
1 litre	152811	OFSW-32

Ordering data – Pressure gauge MA						
	Nominal size	Pneumatic connection	Indicating range		Part No.	Type
			[bar]	[psi]		
	Pressure gauge MA					Technical data → Internet: ma
	27	M5	0 ... 10	–	526323	MA-27-10-M5
	40	G1/8	0 ... 10	0 ... 145	359874	MA-40-10-1/4
			0 ... 16	0 ... 232	345395	MA-40-16-1/4
	50	G1/4	0 ... 10	0 ... 145	359873	MA-50-10-1/4
			0 ... 16	0 ... 232	356759	MA-50-16-1/4

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788
Phone: 1.631.435.0800; Fax: 1.631.435.8026;
Email: info@festo-usa.com www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4
Phone: 1.905.624.9000; Fax: 1.905.624.9001;
Email: festo.canada@ca.festo.com www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México
Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;
Email: festo.mexico@mx.festo.com www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com