

Flow sensors SFAB

FESTO



Flow sensors SFAB

Key features

FESTO

At a glance

Quick and secure installation thanks to QS fitting

Manifold assembly of the sensor via H-rail or individual assembly via adapter plate for wall mounting

Plate assembly of the sensor using mounting screws, 5 measuring ranges from 0.1 ... 10 l/min up to 10 ... 100 l/min



Display can be rotated 270°

- High-contrast LCD display with blue background and white 9-segment display
- Bar graph visualises the current measured value
- Switching point-dependent colour change

Central electrical connection via M12 plug

Impressive, simple, reliable

Designed according to the attractive display and operation concept, the flow sensors have produced outstanding results in the areas of:

- Leakage detection in production
- Leakage tightness testing of end products
- Flow monitoring in parts feeding

The sensor supplies:

- Absolute flow rate information
 - with threshold values and
 - convenient switching point adjustment via a display
- Cumulative air consumption measurement
- Patented – adjustable consumption-based switching impulse for the cumulative air consumption measurement via the switching output

Easier to operate

- A large, illuminated LCD display increases the operational safety and makes the currently displayed flow rate or consumption values easy to read
- Measured values outside the measuring range are visualised: flow rate values are shown flashing
- Values falling below or above the threshold can also be detected remotely or, if the sensor is in an inaccessible location, by means of the display changing colour
- Simple checking of the current sensor settings in SHOW mode
- Simple switching between consumption and flow rate display

Flexible installation

This is enabled by the extremely compact design that does away with the need for an upstream and downstream smoothing section; the SFAB has an integrated stabilising flow channel.

Systematically more reliable

The sensor supplies precise information thanks to its very large measuring range, even in the case of fluctuating or unreliable flow rate conditions.

User-friendly

- Quick and easy menu navigation
- Integrated QS fittings
- Ultra-fast teach-in function
- Rotatable display
- Secure connections with extremely short assembly times
- Manual consumption measurement with start/stop and reset functionality

Advantages

For the designer

- During design, minimal information is required regarding the applied flow rate
- Festo plug and work solution
- The same device can be used for different applications
- The sensor covers a large measuring range with a specified accuracy thanks to its high dynamic response of 1:100
- NPN/PNP switching via the software
- Minimal assembly times
- Alternatively with 4 ... 20 mA or 0 ... 10 V analogue output
- Flexible installation without restrictions imposed by smoothing sections, any installation position
- High pneumatic connection variance possible via the modular product system
- Design of more efficient machines


For the machine operator

- Precise information is available even in the event of fluctuating pressure conditions
- Flow rates can be read easily and reliably
- Visualisation (colour change, flashing measured value) of deviations
- Easy operation without the need for training
- Greater system reliability
- Displayed values:
 - Can be displayed for flow rate and consumption for different standard conditions
 - Can be filtered/averaged with highly dynamic measuring independently of the analogue output
- Fast commissioning thanks to easy-to-use, intuitive teach-in function

Flow sensors SFAB

Peripherals overview

FESTO



Accessories	Description	→ Page/Internet
1 Adapter plate SDE1-...-W-...	Included in the scope of delivery with SFAB-...-W...	11
2 Mounting rail	To DIN EN 60715	nrh
3 Connecting cable NEBU-M12G5	Straight socket	11
4 Connecting cable NEBU-M12W5	Angled socket	11

Flow sensors SFAB

FESTO

Type codes

		SFAB	-	600	U	-	H	Q8	-	P2	-	M12
Type												
SFAB	Flow sensor											
Flow measuring range [l/min]												
10	Max. 10											
50	Max. 50											
200	Max. 200											
600	Max. 600											
1000	Max. 1000											
Flow input												
U	Unidirectional											
Type of mounting												
H	Via H-rail											
W	Via wall bracket											
Pneumatic connection												
Q6	Push-in connector 6 mm											
Q8	Push-in connector 8 mm											
Q10	Push-in connector 10 mm											
Electrical output												
2SA	2x PNP or NPN, 1 analogue output 4 ... 20 mA											
2SV	2x PNP or NPN, 1 analogue output 0 ... 10 V											
Electrical connection												
M12	Straight plug, M12x1, 5-pin											

Additional variants can be ordered using the modular system → 10

- Pneumatic connection
- Electrical accessories
- EU certification (ATEX)


Flow sensors SFAB

Technical data


FESTO

Function

Current output 2SA



Voltage output 2SV



- Analogue output 0 ... 10 V, adjustable switching outputs 2x PNP or 2x NPN
- Analogue output 4 ... 20 mA, adjustable switching outputs 2x PNP or 2x NPN
- Freely selectable pulse output for consumption measurement
- Analogue filter for setting the rise time
- Digital filter for smoothing the display values



General technical data						
		-10U	-50U	-200U	-600U	-1000U
General						
Certification	RCM trademark					
	c UL us - Recognized (OL)					
Certificate issuing authority	UL E322346					
CE mark (see declaration of conformity)	To EU EMC Directive					
	In accordance with EU Explosion Protection Directive (ATEX)					
	To EU RoHS Directive					
Note on materials	RoHS-compliant					
Input signal/measuring element						
Measured variable	Flow rate, consumption					
Direction of flow	Unidirectional P1 → P2					
Measuring principle	Thermal					
Flow measuring range	[l/min]	0.1 ... 10	0.5 ... 50	2 ... 200	6 ... 600	10 ... 1000
Operating pressure	[bar]	0 ... 10				
Nominal pressure	[bar]	6				
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [6:4:4]			Compressed air in accordance with ISO 8573-1:2010 [7:4:4]		
	Nitrogen			Nitrogen		
Temperature of medium	[°C]	0 ... 50				
Ambient temperature	[°C]	0 ... 50				
Nominal temperature	[°C]	23				

Flow sensors SFAB


Technical data

FESTO

Electrical data						
		-10U	-50U	-200U	-600U	-1000U
Output, general ^{1), 2)}						
Accuracy of flow rate values		+/- (3% o.m.v. + 0.3% FS)				
Repetition accuracy of zero point ±FS	[%]	0.2				
Repetition accuracy of margin ±FS	[%]	0.8				
Temperature coefficient of margin ±FS/K	[%]	≤0.1				
Pressure dependence of margin ±FS/bar	[%]	0.5				
Switching output						
Switching output		2x PNP or 2x NPN, adjustable				
Switching function		Window comparator or threshold value comparator, adjustable				
Switching element function		N/C or N/O contact, adjustable				
Switch-on time		Adjustable (factory setting: approx. 80 ms)				
Switch-off time		Adjustable (factory setting: approx. 80 ms)				
Max. output current	[mA]	≤100				
Voltage drop	[V]	Max. 1.5				
Inductive protective circuit		Adapted to MZ, MY, ME coils				
Analogue output						
Characteristic flow rate curve	[l/min]	0 ... 10	0 ... 50	0 ... 200	0 ... 600	0 ... 1000
Output characteristic curve for current	[mA]	4 ... 20				
Output characteristic curve for voltage	[V]	0 ... 10				
Rise time	[ms]	Possible settings: 15, 30, 60 (factory setting), 125, 250, 500, 999				
Max. load resistance at current output	[ohms]	500				
Min. load resistance at voltage output	[kohms]	10				
Output, additional data						
Protection against short circuit		Yes				
Protection against overloading		Yes				
Electronic components						
Operating voltage range DC	[V]	15 ... 30				
Protection against polarity reversal		For all electrical connections				
Electromechanical components						
Electrical connection		Straight plug, M12x1, 5-pin				
Max. length of connecting cable	[m]	<10				

1) Accuracy with nominal conditions (6 bar, 23 °C and horizontal installation position).

2) % FS = % of the measuring range final value (full scale).

Pin allocation		
Plug M12x1, 5-pin	Pin	Meaning
	1	Operating voltage +24 V DC
	2	Binary output B
	3	0 V
	4	Binary output A
	5	Analogue output C

Flow sensors SFAB

Technical data

FESTO

Mechanical components					
	-10U	-50U	-200U	-600U	-1000U
Mounting position	Any				
Pneumatic connection	QS6	QS6	–	–	–
	QS8	QS8	QS8		
	QS10	QS10	QS10	QS10	QS10
	QS12	QS12	QS12	QS12	QS12
	QS1/4	QS1/4	–	–	–
	QS5/16	QS5/16	QS5/16	–	–
	QS3/8	QS3/8	QS3/8	QS3/8	QS3/8
Product weight [g]	160				
Material: Housing	PA reinforced				

Display/operation						
		-10U	-50U	-200U	-600U	-1000U
Indicator type		Illuminated LCD, blue				
Displayable units		l/min, l/h, scfm, l, m³, scf			l/min, scfm, l, m³, scf	
Setting range for flow rate threshold value		1% FS ... 100% FS				
Setting range for consumption	[l]	0.1 ... 1999.9	0.2 ... 1999.9	1 ... 1999.9	2 ... 1999.9	3 ... 1999.9
impulse threshold value	[m³]	0.01 ... 199.99			0.1 ... 1999.9	1 ... 19999
	[scf]	0.01 ... 199.99		0.03 ... 199.99	0.1 ... 1999.9	
Hysteresis setting range		0% FS ... 90% FS				

Immissions/emissions					
	-10U	-50U	-200U	-600U	-1000U
Storage temperature [°C]	–20 ... +80 (characteristic -D: –10 ... +60)				
Degree of protection	IP65				
Pressure drop [mbar]	<100				
Electrical protection class	III				

Flow sensors SFAB


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

SFAB-...-H/-W



- 1 Plug M12x1 to EN 60947-5-2
- 2 LCD display
- 3 Pneumatic connection
- 4 Hole for mounting screw M4
- 5 Adapter plate for wall mounting
- 6 Connecting cable, straight socket
- 7 Connecting cable, angled socket

Type	B1	D1	D2	H1	H2	H3	H4	H5	H6	H7	H8	L1	L2	L3	L4	L6	L7
SFAB-...-HQ6	32.3	17.7	M12x1	–	51.6	11	48.5	44.3	24.4	1.1	12	95.6	69.8	78.9	54	56	35
SFAB-...-HQ8												99.8					
SFAB-...-HQ10												119.8					
SFAB-...-HQ12												124.4					
SFAB-...-WQ6	32.3	17.7	M12x1	79	51.6	11	48.5	44.3	24.4	1.1	12	95.6	69.8	78.9	54	56	35
SFAB-...-WQ8												99.8					
SFAB-...-WQ10												119.8					

Flow sensors SFAB

Technical data

FESTO

Ordering data				
Version	Electrical output	Flow measuring range [l/min]	Part No.	Type
H-rail mounting				
	2x PNP or NPN, 1 analogue output 4 ... 20 mA	0.1 ... 10	565385	SFAB-10U-HQ6-2SA-M12
		0.5 ... 50	565389	SFAB-50U-HQ6-2SA-M12
		2 ... 200	565393	SFAB-200U-HQ8-2SA-M12
		2 ... 200	565397	SFAB-200U-HQ10-2SA-M12
		6 ... 600	565401	SFAB-600U-HQ10-2SA-M12
		10 ... 1000	565405	SFAB-1000U-HQ10-2SA-M12
	2x PNP or NPN, 1 analogue output 0 ... 10 V	0.1 ... 10	565386	SFAB-10U-HQ6-2SV-M12
		0.5 ... 50	565390	SFAB-50U-HQ6-2SV-M12
		2 ... 200	565394	SFAB-200U-HQ8-2SV-M12
		2 ... 200	565398	SFAB-200U-HQ10-2SV-M12
		6 ... 600	565402	SFAB-600U-HQ10-2SV-M12
		10 ... 1000	565406	SFAB-1000U-HQ10-2SV-M12
Wall or surface mounting				
	2x PNP or NPN, 1 analogue output 4 ... 20 mA	0.1 ... 10	565387	SFAB-10U-WQ6-2SA-M12
		0.5 ... 50	565391	SFAB-50U-WQ6-2SA-M12
		2 ... 200	565395	SFAB-200U-WQ8-2SA-M12
		2 ... 200	565399	SFAB-200U-WQ10-2SA-M12
		6 ... 600	565403	SFAB-600U-WQ10-2SA-M12
		10 ... 1000	565407	SFAB-1000U-WQ10-2SA-M12
	2x PNP or NPN, 1 analogue output 0 ... 10 V	0.1 ... 10	565388	SFAB-10U-WQ6-2SV-M12
		0.5 ... 50	565392	SFAB-50U-WQ6-2SV-M12
		2 ... 200	565396	SFAB-200U-WQ8-2SV-M12
		2 ... 200	565400	SFAB-200U-WQ10-2SV-M12
		6 ... 600	565404	SFAB-600U-WQ10-2SV-M12
		10 ... 1000	565408	SFAB-1000U-WQ10-2SV-M12

Flow sensors SFAB

Ordering data – Modular products

FESTO

Ordering table				Condi- tions	Code	Enter code
M	Module No.	563795				
	Function	Flow sensor			SFAB	-SFAB
					-	
O	Medium	Compressed air			-	
M	Flow measuring range	l/min	Max. 10		10	
			Max. 50		50	
			Max. 200		200	
			Max. 600		600	
			Max. 1000		1000	
	Flow input	Unidirectional			U	U
	Type of mounting	H-rail mounting			-H	
		Wall mounting			-W	
	Pneumatic connection	Push-in connector 6 mm		1	Q6	
		Push-in connector 8 mm		2	Q8	
		Push-in connector 10 mm			Q10	
		Push-in connector 12 mm			Q12	
		Push-in connector for 1/4		1	T14	
		Push-in connector for 5/16		2	T516	
		Push-in connector for 3/8			T38	
	Electrical output	2x PNP or NPN, 1 analogue output 4 ... 20 mA			-2SA	
		2x PNP or NPN, 1 analogue output 0 ... 10 V			-2SV	
	Electrical connection	Plug M12, A-coded			-M12	M12
O	Electrical accessories	Not specified				
		Angled plug socket, cable 2.5 m			-2.5A	
		Straight socket, cable 2.5 m			-2.5S	
		Angled plug socket, cable 5 m			-5A	
		Straight socket, cable 5 m			-5S	
	EU certification	Not specified				
		II 3GD			-EX2	

1 Q6, T14 Not with flow measuring range 200; 600; 1000

2 Q8, T516 Not with flow measuring range 600; 1000

Transfer order code

563795 SFAB - - -U - - - M12 - - -



Flow sensors SFAB

FESTO

Accessories

Adapter plate SDE1-...-W...
for wall or surface mounting

Material:
Steel



Ordering data – Adapterplate ¹⁾															
Type	B1	B2	D1	H1	H2	H3	H4	H5	H6	L1	L2	L3	Part No.	Type	
	–0.4		∅	±0.1											
SDE1-...-W...	7.5	0.9	3.4	65.8	40	13.5	59	3.4	1.5	30.3	22.3	1.5	194297	SDE1-...-W...	

1) Included in the scope of delivery with SFAB-...-W...

Ordering data – One-way flow control valve				Technical data → Internet: grx-vfoi	
	Pneumatic connection	Suitable for SFAB ¹⁾	Part No.	Type	
	QS-4	SFAB-10U	193967	GR-QS-4	
	QS-6	SFAB-50U	193969	GR-QS-6	
	QS-8	SFAB-200U	193970	GR-QS-8	

1) Additional accessories may be required for adaptation to the pneumatic connection.

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Number of wires	Cable length [m]	Part No.	Type	
M12x1, straight socket					
	5	2.5	541330	NEBU-M12G5-K-2.5-LE5	
		5	541331	NEBU-M12G5-K-5-LE5	
M12x1, angled socket					
	5	2.5	567843	NEBU-M12W5-K-2.5-LE5	
		5	567844	NEBU-M12W5-K-5-LE5	

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center

Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalneapantla,
Estado de México

Multinational Contact Center

01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center

1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us



www.festo.com/socialmedia



www.festo.com

Subject to change