

Self-closing/rotary push-in fittings QS, Quick Star


FESTO






Self-closing/rotary push-in fittings QS, Quick Star

FESTO

Key features

Application	Simply "plug and work"	Reliably connected	Captive seal
 Effortless selection of the right fitting. Quick Star offers a secure solution for every connection. The convenient push-in fitting system includes well over 1000 types of standard and function fittings.	 The stainless steel retaining ring within the fitting holds the tubing securely without damaging its surface. Vibration and pressure surges are safely absorbed. The tubing can be detached easily by pressing down the blue release ring. For your convenience, the appropriate outside tubing diameter is marked on the release ring.	 A nitrile rubber sealing ring guarantees a perfect seal between standard OD tubing and the body of the fitting. Standard tubing is suitable for use with compressed air and vacuum.	 All of the brass components included in Festo's push-in fittings are nickel plated and are thus highly resistant to corrosion. The tapered ISO R threads have a self-sealing PTFE coating, which allows the fitting to be re-used up to five times without the need for additional sealing components.

360° rotatable	360° rotatable, with ball bearing
 Alignment is performed during assembly. Tube movement is compensated during use.	 Permits rotating motion of up to 500 rpm during use.

Which fitting fits which thread?		
Metric thread - Cylindrical metric thread is comparable with G-thread - Sealing is guaranteed by a clip-on O-ring	G thread to DIN ISO 228-1 - Shorter thread - Constant installation depth - Replaceable sealing ring - Sealing at front - Can be re-used a number of times thanks to replaceable sealing ring	R thread to DIN 2999-1 und ISO 7/1 - Self-sealing thread - Sealing on the threads - No additional sealing surface required - Smaller installation dimensions since there is no need for a rebate for the sealing surface - Can be re-used up to five times
 Metric male thread Metric female thread	 G male thread G female thread	 R male thread G female thread R female thread


Self-closing/rotary push-in fittings QS, Quick Star

FESTO

Technical data

Materials

Sectional view



	Standard QS
1 Release ring	Polyacetate
2 Seal	Nitrile rubber
3 Housing	Polybuteneterephthalate Nickel plated brass
4 Tube clamping segment	High alloy stainless steel
5 Threaded coupling	Nickel plated brass PTFE sealing compound
6 Plastic tubing, standard O.D.	PAN PUN PUN-H PUN-E
Note on materials	RoHS-conform

Tubing insertion depth



Tubing O.D. [mm]	4	6	8	10	12
Standard QSK	12.5 (QSSK: 15)	13.5 (QSSK: 17)	19 (QSK-1/8: 22)	21 (QSK-1/4: 25)	23 (QSK-3/8: 29)
Standard QSR	16	17	19	21	23


Operating and environmental conditions

	Standard QSK	Standard QSR
Temperature dependent operating pressure [bar]	-0.95 ... +14	
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:-:-]	
Operating temperature [°C]	-10 ... +80	0 ... +60
Corrosion resistance CRC ¹⁾	1	
Certification	Germanischer Lloyd	

1) Corrosion resistance class 1 according to Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Operating pressure p as a function of temperature t



Self-closing/rotary push-in fittings QS, Quick Star

FESTO

Technical data

Possible push-in fitting/tubing combinations					
Thread	Tubing O.D. [mm]				
	4	6	8	10	12
M5	++	+	–	–	–
R1/8	+	++	+	+	–
R1/4	+	+	++	+	+
R3/8	–	+	+	++	+
R1/2	–	–	–	+	++
G1/8	+	++	+	–	–
G1/4	–	+	++	+	+
G3/8	–	–	+	++	+

+ Possible thread/tubing O.D. combinations

++ Optimum thread/tubing O.D. combinations (with regard to flow)

Self-closing/rotary push-in fittings QS, Quick Star

Product range overview

FESTO

Shape	Design	Type	Connection D1			Connection D2	→ Page/ Internet	
			M thread	R thread	G thread	Tubing O.D.		Tubing O.D.
Straight	Self-closing push-in fitting – Male thread with external hex							
		QSK	M5	–	–	–	4, 6	6
			–	R1/8	G1/8		4, 6, 8	
				R1/4	G1/4		6, 8, 10	
				R3/8	G3/8		8, 10, 12	
				R1/2	G1/2		12	
	Self-closing push-in connector							
		QSK	–	–	–	4	–	7
						6		
						8		
						10		
						12		
	Push-in bulkhead connector							
		QSSK	–	–	–	4	–	8
						6		
						8		
						10		
						12		
	Rotary push-in fitting, rotatable 360° via ball bearing – Male thread with external hex							
		QSR	M5	–	–	–	4, 6	11
			–	R1/8	G1/8		4, 6, 8	
				R1/4	G1/4		6, 8	
				R3/8	G3/8		8, 10, 12	
				R1/2	G1/2		12	
L-shape	Self-closing push-in L-fitting – can be turned 360° – Male thread with external hex							
		QSKL	M5	–	–	–	4, 6	9
			–	R1/8	G1/8		4, 6, 8	
				R1/4	G1/4		6, 8, 10	
				R3/8	G3/8		8, 10, 12	
				R1/2	G1/2		12	
	Rotary push-in L-fitting, rotatable 360° via ball bearing – Male thread with external hex							
		QSRL	M5	–	–	–	4, 6	10
			–	R1/8	G1/8		4, 6, 8	
				R1/4	G1/4		6, 8	
				R3/8	G3/8		8, 10, 12	
				R1/2	G1/2		12	



Self-closing push-in fittings QSK, Quick Star

FESTO

Technical data

Self-closing push-in fitting QSK

Male thread
with external hex



Dimensions and ordering data											
Connection	Nominal size	Tubing O.D.	D5 Ø	L1	L2	L3	≅	Weight/ piece [g]	Part No.	Type	PU*
D1	[mm]	D2									
Metric thread with sealing ring											
M5	1.4	4	8	29.5	3.5	–	8	7.1	153 291	QSK-M5-4	1
	1.7	6	10	32.5	3.5	–	10	12	153 292	QSK-M5-6	1
R thread											
R1/8	1.6	4	9	25	8	20	10	9.5	153 419	QSK-1/8-4	1
	3	6	10	27.5	8	23	10	9.5	153 420	QSK-1/8-6	1
	3.4	8	14	36	8	32	14	22.5	153 422	QSK-1/8-8	1
R1/4	3	6	12	27.5	11	21	14	21	153 421	QSK-1/4-6	1
	4.3	8	14	36	11	30	14	22.5	153 423	QSK-1/4-8	1
	4.8	10	17	38.5	11	32.5	17	32	153 425	QSK-1/4-10	1
R3/8	4.5	8	15	36	12	29.5	17	39	153 424	QSK-3/8-8	1
	5.6	10	17	40	12	33.5	17	35	153 426	QSK-3/8-10	1
	6.1	12	21	46	12	39.5	21	63.5	153 427	QSK-3/8-12	1
R1/2	6.4	12	21	46	15	38	21	65.5	153 428	QSK-1/2-12	1

* Packaging unit quantity


Self-closing push-in fittings QSK, Quick Star

FESTO

Technical data

Self-closing push-in fitting QSK

Male thread with
external hex



Dimensions and ordering data										
Connection	Nominal size	Tubing O.D.	D5 Ø	L1	L2	≡	Weight/piece	Part No.	Type	PU*
D1	[mm]	D2					[g]			
G thread with sealing ring										
G1/8	1.6	4	8.8	23.5	5.1	13	14	186 294	QSK-G1/8-4	1
	3	6	10	26.2	5.1	13	14	186 295	QSK-G1/8-6	1
	3.4	8	14	34.7	5.1	14	23	186 297	QSK-G1/8-8	1
G1/4	3	6	12	25.6	5.6	17	26	186 296	QSK-G1/4-6	1
	4.3	8	14	34.5	5.6	17	30	186 298	QSK-G1/4-8	1
	4.8	10	17	36.8	5.6	17	33	186 300	QSK-G1/4-10	1
G3/8	4.5	8	15	34.5	6.6	19	43	186 299	QSK-G3/8-8	1
	5.6	10	17	38.3	6.6	19	41	186 301	QSK-G3/8-10	1
	6.1	12	20.8	43.3	6.6	21	63	186 302	QSK-G3/8-12	1
G1/2	6.4	12	20.8	44.9	7.6	24	78	186 303	QSK-G1/2-12	1


* Packaging unit quantity

Self-closing push-in fittings QSK/QSSK, Quick Star

Technical data

FESTO


Self-closing push-in connector QSK



Dimensions and ordering data							
Tubing O.D. D1	Nominal size [mm]	D5 Ø	L1	Weight/piece [g]	Part No.	Type	PU*
4	1.6	8.5	36	3.5	153 439	QSK-4	1
6	3	11	39.5	6	153 440	QSK-6	1
8	4.4	14.5	54.5	16	153 441	QSK-8	1
10	5.3	17.5	60.5	26	153 442	QSK-10	1
12	6.2	21	70.5	40.5	153 443	QSK-12	1

* Packaging unit quantity

Push-in bulkhead connector QSSK



Dimensions and ordering data											
Tubing O.D. D1	Nominal size [mm]	D5 Ø	D6 Ø	L1	L2	L3	⌀	Weight/ piece [g]	Part No.	Type	PU*
4	1.5	M10x1	10	43.1	29.6	10	12	14	130 637	QSSK-4	10
6	3	M12x1	12.5	47.6	34.2	9.9	14	20	130 638	QSSK-6	10
8	4.3	M16x1	14.5	58.1	37.1	14.7	19	38	130 639	QSSK-8	10
10	5.4	M20x1	17.5	66.5	43.4	16.2	24	68	130 640	QSSK-10	1
12	6.3	M22x1	21	75.5	48.6	20.7	27	98	130 641	QSSK-12	1

* Packaging unit quantity

Self-closing push-in fittings QSKL, Quick Star



FESTO

Technical data

Self-closing push-in L-fitting QSKL

360° rotatable

Male thread
with external hex



Dimensions and ordering data												
Connection	Nominal size	Tubing O.D.	D5	H1	H2	H3	L1	≈	Weight/ piece	Part No.	Type	PU*
D1	[mm]	D2	Ø						[g]			
Metric thread with sealing ring												
M5	1.4	4	10	20.8	3.5	–	30.3	10	13	153 294	QSKL-M5-4	1
	1.7	6	12.5	22.5	3.5	–	30.4	12	20	153 295	QSKL-M5-6	1
R thread												
R1/8	1.5	4	10	23.5	8	19.5	30.5	10	17	153 429	QSKL-1/8-4	1
	3	6	12.5	25	8	21	30.5	12	22	153 430	QSKL-1/8-6	1
	4.2	8	14.5	28	8	24	43	14	34	153 432	QSKL-1/8-8	1
R1/4	3.2	6	12.5	28	11	22	30.5	14	29.5	153 431	QSKL-1/4-6	1
	4.1	8	14.5	31	11	25	43	14	40	153 433	QSKL-1/4-8	1
	5.2	10	17.5	36	11	30	49.5	17	58.5	153 435	QSKL-1/4-10	1
R3/8	4.3	8	14.5	33	12	26.5	43	17	53	153 434	QSKL-3/8-8	1
	5.3	10	17.5	37	12	30.5	49.5	17	67	153 436	QSKL-3/8-10	1
	6.2	12	21	39	12	32.5	57.5	21	92.5	153 437	QSKL-3/8-12	1
R1/2	6.2	12	21	42	15	34	57.5	21	107	153 438	QSKL-1/2-12	1

* Packaging unit quantity

Self-closing push-in fittings QSKL, Quick Star

FESTO


Technical data

Self-closing push-in L-fitting QSKL-...

360° rotatable

Male thread

with external hex



Dimensions and ordering data											
Connection	Nominal size	Tubing O.D.	D5 Ø	H1	H2	L1	≅	Weight/ piece [g]	Part No.	Type	PU*
D1	[mm]	D2									
G thread with sealing ring											
G $\frac{1}{8}$	1.5	4	10	23.3	5.1	30.3	13	19	186 304	QSKL-G$\frac{1}{8}$-4	1
	2.9	6	12.5	24	5.1	30.4	13	22	186 305	QSKL-G$\frac{1}{8}$-6	1
	4.2	8	14.5	27	5.1	43	14	34	186 307	QSKL-G$\frac{1}{8}$-8	1
G $\frac{1}{4}$	3.2	6	12.5	25.5	5.6	30.4	17	31	186 306	QSKL-G$\frac{1}{4}$-6	1
	4.1	8	14.5	28.5	5.6	43	17	43	186 308	QSKL-G$\frac{1}{4}$-8	1
	5.2	10	17.5	32.5	5.6	49.3	17	57	186 310	QSKL-G$\frac{1}{4}$-10	1
G $\frac{3}{8}$	4.3	8	14.5	30	6.6	43	19	56	186 309	QSKL-G$\frac{3}{8}$-8	1
	5.3	10	17.5	34	6.6	49.3	19	66	186 311	QSKL-G$\frac{3}{8}$-10	1
	6.2	12	21	36	6.6	57.1	21	86	186 312	QSKL-G$\frac{3}{8}$-12	1
G $\frac{1}{2}$	6.2	12	21	39	7.6	57.1	24	112	186 313	QSKL-G$\frac{1}{2}$-12	1

* Packaging unit quantity

Rotary push-in fittings QSR, Quick Star

Technical data



FESTO

Rotary push-in fitting QSR

Rotatable 360°

via ball bearing

Male thread with
external hex



Dimensions and ordering data												
Connection	Nominal size	Tubing O.D.	Rotational speed	D5	L1	L2	L3	≈	Weight/ piece	Part No.	Type	PU*
D1	[mm]	D2	[rpm]	Ø					[g]			
Metric thread with sealing ring												
M5	1.6	4	500	10	33.1	3.5	–	12	13	153 526	QSR-M5-4	1
	1.6	6	500	12.5	36.7	3.5	–	14	19	153 527	QSR-M5-6	1
R thread												
R1/8	2.1	4	500	10	34.1	8	30.1	12	14	153 401	QSR-1/8-4	1
	3.4	6	500	12.5	36.9	8	32.9	14	18	153 402	QSR-1/8-6	1
	5	8	400	14.5	45.3	8	41.3	17	34	153 404	QSR-1/8-8	1
R1/4	3.4	6	500	12.5	38.9	11	32.8	14	23	153 403	QSR-1/4-6	1
	5	8	400	14.5	44.3	11	38.3	17	32	153 405	QSR-1/4-8	1
R3/8	5	8	400	14.5	44.3	12	38	17	39	153 406	QSR-3/8-8	1
	6.7	10	300	18	55.8	12	49.5	22	61	153 407	QSR-3/8-10	1
	8	12	250	21	63.2	12	56.9	24	82	153 408	QSR-3/8-12	1
R1/2	8	12	250	21	63.2	15	55	24	89	153 409	QSR-1/2-12	1

* Packaging unit quantity

Rotary push-in fittings QSR, Quick Star

Technical data

FESTO


Rotary push-in fitting QSR

Rotatable 360°

via ball bearing

for plastic tubing

with standard O.D.



Dimensions and ordering data											
Connection	Nominal size	Tubing O.D.	Rotational speed	D5	L1	L2	≅	Weight/ piece	Part No.	Type	PU*
D1	[mm]	D2	[rpm]	Ø				[g]			
G thread with sealing ring											
G1/8	2.1	4	500	10	33.1	5.1	13	15	186 276	QSR-G1/8-4	1
	3.4	6	500	12.5	35.9	5.1	14	17	186 277	QSR-G1/8-6	1
	5	8	400	14.5	44.3	5.1	17	34	186 279	QSR-G1/8-8	1
G1/4	3.4	6	500	12.5	35.4	5.6	17	24	186 278	QSR-G1/4-6	1
	5	8	400	14.5	40.8	5.6	17	30	186 280	QSR-G1/4-8	1
G3/8	5	8	400	14.5	41.3	6.6	19	40	186 281	QSR-G3/8-8	1
	6.7	10	300	18	53.8	6.6	22	59	186 282	QSR-G3/8-10	1
	8	12	200	21	60.2	6.6	23.8	78	186 283	QSR-G3/8-12	1
G1/2	8	12	200	21	58.2	7.6	23.8	79	186 284	QSR-G1/2-12	1

* Packaging unit quantity

Rotary push-in fittings QSRL, Quick Star

FESTO

Technical data



Rotary push-in L-fitting QSRL

Rotatable 360°

via ball bearing

Male thread

with external hex



Dimensions and ordering data													
Connection	Nominal size	Tubing O.D.	Rotational speed	D5	H1	H2	H3	L1	≡	Weight/ piece	Part No.	Type	PU*
D1	[mm]	D2	[rpm]	Ø						[g]			
Metric thread with sealing ring													
M5	1.4	4	500	10	21	3.5	–	19.7	12	13	153 529	QSRL-M5-4	1
	1.6	6	500	12.5	23.8	3.5	–	22.8	14	20	153 530	QSRL-M5-6	1
R thread													
R1/8	1.8	4	500	10	23	8	18	20	12	15	153 410	QSRL-1/8-4	1
	3.1	6	500	12.5	24	8	20	23	14	19	153 411	QSRL-1/8-6	1
	4.6	8	400	14.5	31.5	8	27.5	26	17	33	153 413	QSRL-1/8-8	1
R1/4	3.1	6	500	12.5	26	11	20	23	14	23	153 412	QSRL-1/4-6	1
	4.6	8	400	14.5	30.5	11	24.5	26	17	32	153 414	QSRL-1/4-8	1
R3/8	4.6	8	400	14.5	30.5	12	24	26	17	39	153 415	QSRL-3/8-8	1
	6.2	10	300	17.5	36	12	29.5	30	22	56	153 416	QSRL-3/8-10	1
	7.4	12	250	21	41.5	12	35	33	24	84	153 417	QSRL-3/8-12	1
R1/2	7.4	12	250	21	41.5	15	33.5	33	24	90	153 418	QSRL-1/2-12	1

* Packaging unit quantity

Rotary push-in fittings QSRL, Quick Star

Technical data

FESTO


Rotary push-in L-fitting QSRL

Rotatable 360°

via ball bearing

Male thread

with external hex



Dimensions and ordering data												
Connection	Nominal size	Tubing O.D.	Rotational speed	D5	H1	H2	L1	⌀	Weight/ piece	Part No.	Type	PU*
D1	[mm]	D2	[rpm]	Ø					[g]			
G thread with sealing ring												
G $\frac{1}{8}$	1.9	4	500	10	21	5.1	19.7	13	15	186 285	QSRL-G $\frac{1}{8}$ -4	1
	3.1	6	500	12.5	23	5.1	22.8	14	18	186 286	QSRL-G $\frac{1}{8}$ -6	1
	4.6	8	400	14.5	30.5	5.1	25.7	17	35	186 288	QSRL-G $\frac{1}{8}$ -8	1
G $\frac{1}{4}$	3.1	6	500	12.5	22.5	5.6	22.8	17	25	186 287	QSRL-G $\frac{1}{4}$ -6	1
	4.6	8	400	14.5	27	5.6	25.7	17	31	186 289	QSRL-G $\frac{1}{4}$ -8	1
G $\frac{3}{8}$	4.6	8	400	14.5	27.5	6.6	25.7	19	41	186 290	QSRL-G $\frac{3}{8}$ -8	1
	6.2	10	300	17.5	33.3	6.6	29.5	22	59	186 291	QSRL-G $\frac{3}{8}$ -10	1
	7.4	12	200	21	38.5	6.6	32.7	24	81	186 292	QSRL-G $\frac{3}{8}$ -12	1
G $\frac{1}{2}$	7.4	12	200	21	36.5	7.6	32.7	24	81	186 293	QSRL-G $\frac{1}{2}$ -12	1

* Packaging unit quantity

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788
Phone: 1.631.435.0800; Fax: 1.631.435.8026;
Email: info@festo-usa.com www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4
Phone: 1.905.624.9000; Fax: 1.905.624.9001;
Email: festo.canada@ca.festo.com www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México
Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;
Email: festo.mexico@mx.festo.com www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com