


Connecting cables

FESTO



Key features

Cable characteristic

The cable characteristic indicates the resistance of the connecting cable to the mechanical load.

There are four qualities:

- For static applications
- Standard
- Suitable for energy chains
- Suitable for robot applications

The connecting cables NEBB are simple lines with a PVC cable sheath.


Connecting cables NEBB match the cable properties for static applications.

Cable properties for static applications

Static applications are characterised by fixed cable installation with no mechanical loads.

The connecting cable is not constantly moving (kinked or twisted).

The cable sheath for the connecting cables is usually made of PVC.



Connection technology version

The type of plug for the connecting cable can be selected (e.g. angled or straight).

Product range overview

Function	Design	Type	Connection technology (Electrical connection 2)	Cable characteristic	Length	→ Page/Internet
Electrical connecting cable	Electrical connection 1: socket M8					
	3-pin	NEBB-M8G3 NEBB-M8W3	Open cable end	For static applications	2.5 m 5 m 10 m	5
	4-pin	NEBB-M8G4 NEBB-M8W4	Open cable end	For static applications	2.5 m 5 m 10 m	8
	Electrical connection 1: socket M12					
	5-pin	NEBB-M12G5 NEBB-M12W5	Open cable end	For static applications	2.5 m 5 m 10 m	11

Type codes

001	Series	
NEBB	Connecting cable	

002	Connection technology left, field device side	
M8	Socket M8x1 A-coded, EN 61076-2-104	
M12	Socket M12x1 A-coded, EN 61076-2-101	

003	Cable outlet left	
G	Straight	
W	Angled	

004	Number of pins/wires on the left	
3	3	
4	4	
5	5	

005	Cable characteristic	
P	Basic	

006	Cable length [m]	
2.5	2.5	
5	5	
10	10	

007	Connection technology right, controller side	
LE	Open end	

008	Number of pins/wires on the right	
3	3	
4	4	
5	5	

Data sheet

**Connecting cable
NEBB-M8**

- Connecting cable for connecting sensors and actuators
- Pre-assembled
- Cable lengths 2.5 m, 5 m and 10 m
- 3 wires
- M8

**General technical data**

Conforms to standard	Wire colours and connection numbers to EN 60947-5-2 EN 61076-2-104
Cable designation	With inscription label holder
Degree of protection	IP65, IP68, IP69K
Note on degree of protection	In assembled state

Technical data – Electrical connection 1

Function	Field device side
Design type	Round
Connection type	Socket
Cable outlet	Straight, angled
Connection technology	M8x1, A-coded to EN 61076-2-104
Number of pins/wires	3
Assigned pins/wires	3
Type of mounting	Screw-type lock with A/F9

Technical data – Electrics

Operating voltage range	[V DC]	0 ... 60
	[V AC]	0 ... 60
Surge resistance	[kV]	1.5
Acceptable current load at 40°C	[A]	4

Technical data – Cable

Cable characteristic	For static applications
Cable test conditions	Test conditions on request
Bending radius, fixed cable installation	[mm] ≥12
Cable diameter	[mm] 3.8
Cable composition	[mm²] 3 x 0.25
Conductor nominal cross section	[mm²] 0.25

Technical data – Electrical connection 2

Function	Controller side
Connection type	Cable
Connection technology	Open end
Number of pins/wires	3
Assigned pins/wires	3
Wire ends	Sheath removed, cut off bluntly

Data sheet


Materials	
Housing	TPE-U(PU)
Housing colour	Black
Cable sheath	PVC
Cable sheath colour	Grey
Insulating sheath	PVC
Screw-type lock	Nickel-plated brass
Seals	NBR
Pin contacts	Gold-plated copper alloy
Note on materials	RoHS-compliant
	Free of copper and PTFE

Operating and environmental conditions	
Ambient temperature [°C]	-25 ... +70
Corrosion resistance class CRC ¹⁾	2
CE marking (see declaration of conformity) ²⁾	To EU Low Voltage Directive
Pollution degree	3

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

2) Additional information: www.festo.com/catalogue/nebb → Support/Downloads.


Circuitry (socket view)				
Electrical connection 1	Pin	Wire colour ¹⁾	Pin	Electrical connection 2
	1	BN	-	
	3	BU	-	
	4	BK	-	

1) To IEC 757

Dimensions

Download CAD data → www.festo.com

Cable outlet straight



[1] Socket M8x1

[2] Inscription label holder

[3] Cable, length 2.5 m, 5 m or 10 m depending on the order

[4] Wire ends cut off bluntly


Type	D1 Ø	D2	D3 Ø	L1	L2	L3	≙ 1
NEBB-M8G3	3.8	M8x1	10	34.6	23	50	9

Data sheet

Dimensions

Download CAD data → www.festo.com

Cable outlet angled



[1] Socket M8x1



[3] Cable, length 2.5 m, 5 m or
10 m depending on the order

[4] Wire ends cut off bluntly



[2] Inscription label holder

Type	D1 Ø	D2	D3 Ø	H1	L1	L2	L3	±1
NEBB-M8W3	3.8	M8x1	10	17	26.9	23	50	9

Ordering data

		Cable length [m]	Part no.	Type
Open cable end, 3-wire				
	Cable outlet straight	2.5	8066658	NEBB-M8G3-P-2.5-LE3
		5	8066659	NEBB-M8G3-P-5-LE3
		10	8066660	NEBB-M8G3-P-10-LE3
	Cable outlet angled	2.5	8066664	NEBB-M8W3-P-2.5-LE3
		5	8066665	NEBB-M8W3-P-5-LE3
		10	8066666	NEBB-M8W3-P-10-LE3

Ordering data – Accessories

Designation		Part no.	Type
Plug			
	Pre-assembled plugs	–	→ Internet: necu
		–	→ Internet: sea
Inscription labels			
	Inscription labels 23 mm for inscription label holder, 34 pieces, in frame	541598	ASLR-L-423

Data sheet

**Connecting cable
NEBB-M8**

- Connecting cable for connecting sensors and actuators
- Pre-assembled
- Cable lengths 2.5 m, 5 m and 10 m
- 4 wires
- M8

**General technical data**

Conforms to standard	Wire colours and connection numbers to EN 60947-5-2 EN 61076-2-104
Cable designation	With inscription label holder
Degree of protection	IP65, IP68, IP69K
Note on degree of protection	In assembled state

Technical data – Electrical connection 1

Function	Field device side
Design type	Round
Connection type	Socket
Cable outlet	Straight, angled
Connection technology	M8x1, A-coded to EN 61076-2-104
Number of pins/wires	4
Assigned pins/wires	4
Type of mounting	Screw-type lock with A/F9

Technical data – Electrics

Operating voltage range	[V DC]	0 ... 30
	[V AC]	0 ... 30
Surge resistance	[kV]	0.8
Acceptable current load at 40°C	[A]	4

Technical data – Cable

Cable characteristic	For static applications
Cable test conditions	Test conditions on request
Bending radius, fixed cable installation	[mm] ≥14
Cable diameter	[mm] 4.5
Cable composition	[mm ²] 4 x 0.25
Conductor nominal cross section	[mm ²] 0.25

Technical data – Electrical connection 2

Function	Controller side
Connection type	Cable
Connection technology	Open end
Number of pins/wires	4
Assigned pins/wires	4
Wire ends	Sheath removed, cut off bluntly


Data sheet

Materials	
Housing	TPE-U(PU)
Housing colour	Black
Cable sheath	PVC
Cable sheath colour	Grey
Insulating sheath	PVC
Screw-type lock	Nickel-plated brass
Seals	NBR
Pin contacts	Gold-plated copper alloy
Note on materials	RoHS-compliant
	Free of copper and PTFE

Operating and environmental conditions	
Ambient temperature [°C]	-25 ... +70
Corrosion resistance class CRC ¹⁾	2
Pollution degree	3

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.


Circuitry (socket view)				
Socket	Pin	Wire colour ¹⁾	Pin	Plug
Electrical connection, socket, 4-pin, M8 – open cable end				
	1	BN	–	–
	2	WH	–	–
	3	BU	–	–
	4	BK	–	–

1) To IEC 757

Dimensions

Download CAD data → www.festo.com

Cable outlet straight



[1] Socket M8x1

[2] Inscription label holder

[3] Cable, length 2.5 m, 5 m or 10 m depending on the order

[4] Wire ends cut off bluntly


Type	D1 ø	D2	D3 ø	L1	L2	L3	1
NEBB-M8G4	4.5	M8x1	10	34.6	23	50	9

Data sheet

Dimensions

Download CAD data → www.festo.com

Cable outlet angled



[1] Socket M8x1



[3] Cable, length 2.5 m, 5 m or
10 m depending on the order

[4] Wire ends cut off bluntly



[2] Inscription label holder

Type	D1 Ø	D2	D3 Ø	H1	L1	L2	L3	≈ 1
NEBB-M8W4	4.5	M8x1	10	17	26.9	23	50	9

Ordering data

		Cable length [m]	Part no.	Type
Open cable end, 4-wire				
	Cable outlet straight	2.5	8066661	NEBB-M8G4-P-2.5-LE4
		5	8066662	NEBB-M8G4-P-5-LE4
		10	8066663	NEBB-M8G4-P-10-LE4
	Cable outlet angled	2.5	8066667	NEBB-M8W4-P-2.5-LE4
		5	8066668	NEBB-M8W4-P-5-LE4
		10	8066669	NEBB-M8W4-P-10-LE4


Ordering data – Accessories

Designation	Part no.	Type
Plug		
	Pre-assembled plugs	
	–	→ Internet: necu
	–	→ Internet: sea
Inscription labels		
	Inscription labels 23 mm for inscription label holder, 34 pieces, in frame	541598 ASLR-L-423

Data sheet

**Connecting cable
NEBB-M12**

- Connecting cable for connecting sensors and actuators
- Pre-assembled
- Cable lengths 2.5 m, 5 m and 10 m
- 3, 4 or 5 wires
- M12x1, 5-pin

**General technical data**

Conforms to standard	Wire colours and connection numbers to EN 60947-5-2 EN 61076-2-101
Cable designation	With inscription label holder
Degree of protection	IP65, IP68, IP69K
Note on degree of protection	In assembled state

Technical data – Electrical connection 1

Function	Field device side		
Design type	Round		
Connection type	Socket		
Cable outlet	Straight, angled		
Connection technology	M12x1, A-coded to EN 61076-2-101		
Number of pins/wires	5		
Assigned pins/wires	3	4	5
Type of mounting	Screw-type lock with A/F13		

Technical data – Electrics

Assigned pins/wires	3	4	5
Operating voltage range	[V DC] 0 ... 250	0 ... 250	0 ... 60
	[V AC] 0 ... 250	0 ... 250	0 ... 60
Surge resistance	[kV] 2.5	2.5	1.5
Acceptable current load at 40°C	[A] 4	4	4

Technical data – Cable

Assigned pins/wires	3	4	5
Cable characteristic	For static applications		
Cable test conditions	Test conditions on request		
Bending radius, fixed cable installation	[mm] ≥12	≥14	≥14
Cable diameter	[mm] 3.8	4.5	4.5
Cable composition	[mm ²] 3 x 0.25	4 x 0.25	5 x 0.25
Conductor nominal cross section	[mm ²] 0.25	0.25	0.25

Technical data – Electrical connection 2

Assigned pins/wires	3	4	5
Function	Controller side		
Connection type	Cable		
Connection technology	Open end		
Number of pins/wires	3	4	5
Assigned pins/wires	3	4	5
Wire ends	Sheath removed, cut off bluntly		

Data sheet




Materials	
Housing	TPE-U(PU)
Housing colour	Black
Cable sheath	PVC
Cable sheath colour	Grey
Insulating sheath	PVC
Screw-type lock	Nickel-plated brass
Seals	NBR
Pin contacts	Gold-plated copper alloy
Note on materials	RoHS-compliant
	Free of copper and PTFE

Operating and environmental conditions	
Ambient temperature [°C]	−25 ... +70
Corrosion resistance class CRC ¹⁾	2
CE marking (see declaration of conformity) ²⁾	To EU Low Voltage Directive
Pollution degree	3

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

2) Additional information: www.festo.com/catalogue/nebb → Support/Downloads.

Circuitry (socket view)				
Electrical connection 1	Pin	Wire colour ¹⁾	Pin	Electrical connection 2
Electrical connection 2: open cable end, 3-wire				
	1	BN	–	–
	3	BU	–	
	4	BK	–	
Electrical connection 2: open cable end, 4-wire				
	1	BN	–	–
	2	WH	–	
	3	BU	–	
	4	BK	–	
Electrical connection 2: open cable end, 5-wire				
	1	BN	–	–
	2	WH	–	
	3	BU	–	
	4	BK	–	
	5	GY	–	


1) To IEC 757

Data sheet

Dimensions

Download CAD data → www.festo.com

Cable outlet straight



[1] Socket M12x1


[3] Cable, length 2.5 m, 5 m or
10 m depending on the order

[4] Wire ends cut off bluntly

[2] Inscription label holder

Type	D1 ø	D2	D3 ø	L1	L2	L3	⚡ 1
NEBB-M12G5-...-LE3	3.8	M12x1	15	47.5	23	50	13
NEBB-M12G5-...-LE4	4.5	M12x1	15	47.5	23	50	13
NEBB-M12G5-...-LE5	4.5	M12x1	15	47.5	23	50	13

Cable outlet angled



[1] Socket M12x1









[3] Cable, length 2.5 m, 5 m or
10 m depending on the order

[4] Wire ends cut off bluntly

[2] Inscription label holder

Type	D1 ø	D2	D3 ø	H1	L1	L2	L3	⚡ 1
NEBB-M12W5-...-LE3	3.8	M12x1	15	26	37.5	23	50	13
NEBB-M12W5-...-LE4	4.5	M12x1	15	26	37.5	23	50	13
NEBB-M12W5-...-LE5	4.5	M12x1	15	26	37.5	23	50	13

Data sheet

Ordering data		Cable length [m]	Part no.	Type
Open cable end, 3-wire				
	Cable outlet straight	2.5	8066670	NEBB-M12G5-P-2.5-LE3
		5	8066671	NEBB-M12G5-P-5-LE3
		10	8066672	NEBB-M12G5-P-10-LE3
	Cable outlet angled	2.5	8066679	NEBB-M12W5-P-2.5-LE3
		5	8066680	NEBB-M12W5-P-5-LE3
		10	8066681	NEBB-M12W5-P-10-LE3
Open cable end, 4-wire				
	Cable outlet straight	2.5	8066673	NEBB-M12G5-P-2.5-LE4
		5	8066674	NEBB-M12G5-P-5-LE4
		10	8066675	NEBB-M12G5-P-10-LE4
	Cable outlet angled	2.5	8066682	NEBB-M12W5-P-2.5-LE4
		5	8066683	NEBB-M12W5-P-5-LE4
		10	8066684	NEBB-M12W5-P-10-LE4
Open cable end, 5-wire				
	Cable outlet straight	2.5	8066676	NEBB-M12G5-P-2.5-LE5
		5	8066677	NEBB-M12G5-P-5-LE5
		10	8066678	NEBB-M12G5-P-10-LE5
	Cable outlet angled	2.5	8066685	NEBB-M12W5-P-2.5-LE5
		5	8066686	NEBB-M12W5-P-5-LE5
		10	8066687	NEBB-M12W5-P-10-LE5
Ordering data – Accessories				
Designation		Part no.	Type	
Plug				
	Pre-assembled plugs	–	→ Internet: necu	
		–	→ Internet: sea	
Inscription labels				
	Inscription labels 23 mm for inscription label holder, 34 pieces, in frame	541598	ASLR-L-423	