


Vacuum generators OVTL

FESTO



Key features

At a glance

Rapid reduction of vacuum for safe placement of the workpiece by a solenoid valve to control the ejector pulse, optional


Flow control screw for regulating the ejector pulse

Electrical connection via H3 plug

Fast vacuum build-up using a solenoid valve to control the compressed air supply

Supply port, secured with clamp strap

Additional supply port for the separate supply of the ejector pulse, optional, secured with clamp strap



Pressure transmitter SPTE/pressure sensor SPAE to monitor the vacuum, optional, secured with clamp strap

Maintenance-free operation and reduced noise level by an open silencer, optional

Vacuum generator cartridge, secured with clamp strap

Vacuum port, secured with clamp strap

Housing with mounting holes

The compact vacuum generator

OVTL → Page 3

The vacuum generator OVTL is a configurable module comprising vacuum generators OVEL, the common supply manifold OABM-P and connection accessories.

All products are available from the factory fully assembled.



OVEL → ovel

- Low-cost, compact vacuum generator
- Lightweight
- Various performance levels and vacuum types
- Short switching times with integrated solenoid valves
 - Vacuum on/off
 - Ejector pulse
- Simple installation with H3 plugs and push-in fittings
- Straightforward mounting with retaining screws
- Low-noise operation due to integrated silencer
- Integrated filter
- Reduced contamination of the vacuum generator with open silencer
- Solenoid valves are switched by mechanical manual override
- Vacuum monitored by vacuum sensor
- Link up to 8 vacuum generators on a single common supply manifold.

Functional principle OVEL

Vacuum ON/OFF

The compressed air supply is controlled by a solenoid valve. The solenoid valve can be supplied with the N/C (normally closed) switching


function, i.e. the vacuum is not generated until the vacuum generator is pressurised with compressed air and the solenoid valve has been switched.

Ejector pulse, optional

After the vacuum is switched off, an ejector pulse is activated and generated by a second solenoid valve to release the workpiece safely from the suction cup with connection and to purge the vacuum quickly.

The compressed air for the ejector pulse can be supplied either via the supply port or a separate port.

Peripherals overview



Mounting attachments and accessories

		→ Page/Internet
[5]	Plug NECU-S-M8G3/M12G3	13
[6]	Plug NECU-S-ECG4	13
[7]	Signal converter SCDN	13
[8]	Plug socket with cable NEBV	13
[12]	Suction gripper ESG	esg
-	Suction cup complete holder ESH	esh
-	Suction cup with connection ESS	ess
-	Vacuum filter OAFF	12

Type codes

001	Series	
OVTL	Vacuum generator	

002	Size	
10	10 mm	
15	15 mm	

003	Compressed air supply connection	
Q6	Push-in connector 6 mm	
Q8	Push-in connector 8 mm	
G18	G1/8	

004	Compressed air supply connection position	
	Both sides	
L	Left	
R	Right	

005	Exhaust connection	
RQ	QS connections, metric	
UA	Open silencer UO	

006	Number of vacuum generators	
2	2 pieces	
4	4 pieces	
8	8 pieces	

007	Position function	
SL	Vacant position	
SA	Laval nozzle 0.45 mm, for high vacuum, push-in connector 4 mm	
SB	Laval nozzle 0.7 mm, for high suction rate, push-in connector 6 mm	
SC	Laval nozzle 0.7 mm, for high vacuum, push-in connector 4 mm	
SD	Laval nozzle 0.95 mm, for high suction rate, push-in connector 6 mm	
SE	Laval nozzle 0.95 mm, for high vacuum, push-in connector 6 mm	

008	Sensor signal	
	None	
V	0 ... 10 V	
PNLK	PNP or NPN or IO-Link®	

Datasheet

Vacuum generator OVTL:

- Vacuum generators OVEL
- Common supply manifold OABM-P with 2, 4 or 8 positions
- Mounting kits OABM-MK
- Push-in fittings QS
- Blanking plug B

-  - Temperature range
0 ... +50°C
-  - Operating pressure
2 ... 7 bar




The vacuum generator OVTL is a module comprising vacuum generators OVEL, the common supply manifold OABM-P and connection accessories. All products are available from the factory fully assembled.

The vacuum generator OVTL can be ordered using the modular product system, which is a simpler and quicker alternative to ordering and assembling the various individual products.


Every vacuum generator OVEL has

- a solenoid valve for controlling the ejector pulse
- a flow control screw for regulating the ejector pulse
- an additional supply port for the separate supply of the ejector pulse


Without vacuum sensor
OVEL-...-RQ




With vacuum sensor
OVEL-...-RQ



OVEL-...-UA



OVEL-...-UA



General technical data			OVTL-10	OVTL-15
Type				
Number of device positions			2 ... 8	
Grid dimension	[mm]		10	15
Nominal width of	OVTL-...-SA	[mm]	0.45	
Laval nozzle	OVTL-...-SB/SC	[mm]	-	0.7
	OVTL-...-SD/SE	[mm]	-	0.95
Grade of filtration	[µm]		40	
Mounting position			Any	
Type of mounting			With through-hole	
Pneumatic connection 1 (common supply manifold)	OVTL-...-Q6		For tubing O.D. 6 mm	
	OVTL-...-Q8		For tubing O.D. 8 mm	
	OVTL-...-G18		Female thread G1/8	
Vacuum connection	OVTL-...-SA		For tubing O.D. 4 mm	
	OVTL-...-SC		-	For tubing O.D. 4 mm
	OVTL-...-SB/SD/SE		-	For tubing O.D. 6 mm
Pneumatic connection 3	OVTL-...-UA		Open silencer	
	OVTL-...-RQ-...-SA		For tubing O.D. 4 mm	
	OVTL-...-RQ-...-SB/SC/SD/SE		-	For tubing O.D. 6 mm
Product weight ¹⁾	[g]		118 ... 890	

1) Total weight calculated by adding the weights of the separate components.

Datasheet

Technical data – design			
Type	OVTL-...-UA	OVTL-...-RQ	
Design		Connection position on both sides	
	OVTL-...-L/R	Connection position on the side	
Ejector characteristic	OVTL-...-SA/SC/SE	High vacuum/standard	
	OVTL-...-SB/SD	High suction rate/standard	
Silencer design	Open	-	
Integrated function		Electric on/off valve	
		Filters	
		Open silencer	-
		Ejector pulse, electrical	
		Flow control valve	
	OVTL-...-V	Pressure transmitter	
	OVTL-...-PNLK	Pressure sensor	
Valve function		Closed	
Manual override		Non-detenting	

Operating and environmental conditions		
Operating pressure	[bar]	2 ... 7
Nominal operating pressure	[bar]	4
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium		Lubricated operation not possible
Ambient temperature	[°C]	0 ... +50
Temperature of medium	[°C]	0 ... +50
Corrosion resistance class CRC ¹⁾		2
CE marking (see declaration of conformity) ²⁾		To EU EMC Directive
Degree of protection		IP40

- 1) Corrosion resistance class CRC 2 to Festo standard FN 940070
Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.
- 2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/sp → Certificates.
If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Performance data		
Max. vacuum	[%]	89 ... 92
Operating pressure for max. vacuum	[bar]	3.8 ... 4.5
Operating pressure for max. suction rate	[bar]	3 ... 6
Max. suction rate with respect to atmosphere	[l/min]	4 ... 45
Pressurisation time at nominal operating pressure 4 bar (for 1 l volume) ¹⁾	[s]	0.4 ... 2
Sound pressure level at p1 = 4 bar	[db(A)]	52 ... 68

- 1) Time required to reduce the vacuum to a residual vacuum of -0.05 bar


Datasheet

Technical data – electrical connection		
Solenoid valve		
Electrical connection input,	Function	Ejector pulse Vacuum generation
	Connection type	2x plug
	Connection technology	Plug pattern H
	Number of pins/wires	2
	Plug pattern	
Type of mounting	Snap-locking	
Operating voltage range	[V DC]	21.6 ... 26.4
Duty cycle	[%]	100
Characteristic coil data, 24 V DC	[W]	1.0
Vacuum sensor		
Electrical connection output,	Function	Sensor
	Connection type	Cable
	Connection technology	Open end
	Number of pins/wires	3
Cable diameter	[mm]	2.9 ±0.1
Cable length	[m]	2.5
Nominal conductor cross section	[mm ²]	0.14
Cable characteristic		Suitable for energy chains
Technical data – vacuum sensor		
Type	OVTL-...V	OVTL-...PNLK
Mechanical system		
Measurement method	Piezoresistive pressure sensor	Piezoresistive pressure sensor with display
Pressure measuring range	[bar]	-1 ... 0
Setting options	-	Teach-in
	-	IO-Link®
	-	Via display and buttons
Display type	-	LED display, 2-digit
Electrical		
Operating voltage range, sensor	[V DC]	18 ... 30
Switching output	-	PNP/NPN, switchable
Switching element function	-	N/C or N/O, switchable
Switching function	-	Freely programmable
Analogue output	[V]	0 ... 10
Materials		
Sub-base		Wrought aluminium alloy
Hollow bolt		Wrought aluminium alloy
Fitting		Brass, nickel-plated
Housing		PA-reinforced
Silencer		PE
Jet nozzle		Wrought aluminium alloy
Female nozzle		POM
Filters		POM
Adjusting screw		Steel
Connecting thread		POM
Screws		Steel
Cable sheath		PVC (colour: grey)
Seals		NBR
Note on materials		RoHS-compliant

Datasheet

Dimensions

Download CAD data → www.festo.com



- [1] Common supply manifold
- [2] Push-in fitting
- [3] Blanking plug
- [4] Vacuum generator OVEL-5
- [5] Vacuum generator OVEL-7/10

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	D2 ∅	H1	H2	H3	H4
OVTL	74	31	62	25	57	52	30	16	16	10	14	125	21	19.5	8

Type	L1	L2	L3	L4
OVTL-10-...-2	40.5	10.5	10.5	30.5
OVTL-10-...-4	61.5		31.5	51.5
OVTL-10-...-8	103.5		73.5	93.5
OVTL-15-...-2	51.5	15.5	15.5	41.5
OVTL-15-...-4	82.5		46.5	72.5
OVTL-15-...-8	144.5		108.5	134.5

Type	D1	L5	L6	L7					
				OVTL-10-...-2	OVTL-10-...-4	OVTL-10-...-8	OVTL-15-...-2	OVTL-15-...-4	OVTL-15-...-8
OVTL-...-G18	-	-	-	40.5	61.5	103.5	51.5	82.5	144.5
OVTL-...-G18-L	-	-	5	45.5	66.5	108.5	56.5	87.5	149.5
OVTL-...-G18-R	-	5	-	45.5	66.5	108.5	56.5	87.5	149.5
OVTL-...-Q6	12	17	17	74.5	95.5	137.5	85.5	116.5	178.5
OVTL-...-Q6-L	12	17	5	62.5	83.5	125.5	73.5	104.5	166.5
OVTL-...-Q6-R	12	5	17	62.5	83.5	125.5	73.5	104.5	166.5
OVTL-...-Q8	14	22	22	84.5	105.5	147.5	95.5	126.5	188.5
OVTL-...-Q8-L	14	22	5	67.5	88.5	130.5	78.5	109.5	171.5
OVTL-...-Q8-R	14	5	22	67.5	88.5	130.5	78.5	109.5	171.5

Ordering data – Modular product system

Ordering table		Conditions	Code	Enter code
Type	OVTL			
Module no.	8103599			
Vacuum generator	Vacuum generators module, series L		OVTL	OVTL
Size	10 mm		-10	
	15 mm		-15	
Compressed air supply connection	Push-in connector 6 mm		-Q6	
	Push-in connector 8 mm		-Q8	
	G1/8		-G18	
Compressed air supply port position	Both sides			
	Left		-L	
	Right		-R	
Exhaust port	QS ports, metric		-RQ	
	Silencer open UO		-UA	
Number of vacuum generators	2 pieces		-2	
	4 pieces		-4	
	8 pieces		-8	
Position function	Vacant position		-SL	
	Laval nozzle 0.45 mm, for high vacuum, push-in connector 4 mm		-SA	
	Laval nozzle 0.7 mm, for high suction rate, push-in connector 6 mm	[1]	-SB	
	Laval nozzle 0.7 mm, for high vacuum, push-in connector 4 mm	[1]	-SC	
	Laval nozzle 0.95 mm, for high suction rate, push-in connector 6 mm	[1]	-SD	
	Laval nozzle 0.95 mm, for high vacuum, push-in connector 6 mm	[1]	-SE	
Sensor signal	Without vacuum sensor			
	0 ... 10 V	[2]	V	
	PNP or NPN or IO-Link®	[2]	PNLK	

- [1] SB, SC, SD, SE Not with size 10.
 [2] V, PNLK Not with position function SL.

 **Note**

The position function and sensor signal must be selected for every vacuum generator in accordance with the number of vacuum generators configured.

Example with 4:

- OVTL-10-Q8R-UA-4-SAVSESEPNLK-SL


Accessories

Common supply manifold OABM-P

For vacuum generator
OVEL-...-P

- Up to 8 vacuum generators OVEL on a common supply manifold
- Common compressed air supply via common supply manifold


 **Note**
On the common supply manifold vacuum generators with an additional port for the ejector pulse (OVEL-...-Z-C-A) cannot be combined with vacuum generators without an additional port (OVEL-...-C-A).



General technical data	
Pneumatic connection 1	G1/8
Type of mounting	With through-hole

Materials	
Sub-base	Wrought aluminium alloy
Note on materials	RoHS-compliant

Dimensions Download CAD data → www.festo.com




Type	B1	B2	B3	B4	D1	D2 ø	D3 ø	D4	H1	H2
OABM-P-G3-10-2	30	13	23	7	G1/8	8	4.5	M7	19.5	11.5
OABM-P-G3-10-4										
OABM-P-G3-10-8										
OABM-P-G3-15-2	30	13	23	7	G1/8	8	4.5	M7	19.5	11.5
OABM-P-G3-15-4										
OABM-P-G3-15-8										

Type	L1	L2	L3	L4	L5	L6	T1	T2	T3
OABM-P-G3-10-2	40.5	30.5	10.5	10.5	10	5	8	4.6	6.6
OABM-P-G3-10-4	61.5	51.5	31.5						
OABM-P-G3-10-8	103.5	93.5	73.5						
OABM-P-G3-15-2	51.5	41.5	15.5	15.5	13	5	8	4.6	6.6
OABM-P-G3-15-4	82.5	72.5	46.5						
OABM-P-G3-15-8	144.5	134.5	108.5						

Accessories

Dimensions

Download CAD data → www.festo.com



Note

Combined allocation with OVEL-5 and OVEL-7/-10 is possible only with common supply manifolds OABM-...-15.

Use mounting kit OABM-MK for mounting the OVEL on the common supply manifold.

Min. tightening torque: 0.3 Nm

Max. tightening torque: 3.3 Nm

[1] Vacuum generator OVEL-5/7/10

Type		B1	B2	B3	B4	B5	B6	B7	D1	H1	H2	L1	L2	L3
OABM-P-G3-10-2	with OVEL-5	30	62	25	52	10	23	7	G1/8	19.5	110	40.5	10.5	10.5
OABM-P-G3-10-4												61.5	31.5	
OABM-P-G3-10-8												103.5	73.5	
OABM-P-G3-15-2	with OVEL-7/10	30	74	31	57	16	23	7	G1/8	19.5	125	51.5	15.5	15.5
OABM-P-G3-15-4												82.5	46.5	
OABM-P-G3-15-8												144.5	108.5	

Ordering data


Common supply manifold	Number of device positions	CRC ¹⁾	Weight [g]	Part no.	Type
For OVEL-5	2	2	45.2	8049141	OABM-P-G3-10-2
	4	2	69.6	8049142	OABM-P-G3-10-4
	8	2	118.6	8049143	OABM-P-G3-10-8
For OVEL-5/7/10	2	2	59.6	8049144	OABM-P-G3-15-2
	4	2	97.1	8049145	OABM-P-G3-15-4
	8	2	172	8049146	OABM-P-G3-15-8

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Accessories

Vacuum filter OAFF



General technical data		
Type of mounting		Push-on
		Latching
Grade of filtration	[µm]	40
Ejector pulse suitability	[bar]	≤7


Operating and environmental conditions		
Operating pressure	[bar]	-0.95
Operating medium		Atmospheric air based on ISO 8573-1:2010 [7:-:-]

Materials		
Type	OAFF-G3-5	OAFF-G3-7
Housing	POM	
Filters	Fabric, PA	
Seals	-	NBR
Note on materials	RoHS-compliant	

Ordering data				
	Weight [g]	Part no.	Type	PU ¹⁾
For vacuum generator OVEL-5	1	8068944	OAFF-G3-5	10
For vacuum generator OVEL-7/10	1.5	8068945	OAFF-G3-7	10



1) Packaging unit

Accessories

Ordering data – Plug NECU-S-M8G3/M12G3			Datasheets Internet: necu	
	Electrical connection	Part no.	Type	
	Plug M8x1, 3-pin, straight, insulation displacement connector	562024	NECU-S-M8G3-HX	
	Plug M12x1, A-coded, 3-pin, straight, insulation displacement connector	562027	NECU-S-M12G3-HX	

Ordering data – Plug NECU-S-ECG4			Datasheets Internet: necu	
	Electrical connection	Part no.	Type	
	Plug, square design, 4-pin, straight, insulation displacement connector	570922	NECU-S-ECG4-HX-Q3	

Ordering data – Signal converter SCDN			Datasheets Internet: scdn	
	Measured variable	Part no.	Type	
	Voltage	8035555	SCDN-2V-EC4-PNLK-L1	

Ordering data – Plug socket with cable NEBV					Datasheets Internet: nebv	
	Electrical connection		Cable length [m]	Part no.	Type	
	Socket, 2-pin Plug pattern H	Flying leads Open end	0.5	566654	NEBV-H1G2-KN-0.5-N-LE2	
			1	566655	NEBV-H1G2-KN-1-N-LE2	
			2.5	566656	NEBV-H1G2-KN-2.5-N-LE2	
			5	566657	NEBV-H1G2-KN-5-N-LE2	
	Socket, 2-pin Plug pattern H	Cable Open end	0.5	566658	NEBV-H1G2-P-0.5-N-LE2	
			1	566659	NEBV-H1G2-P-1-N-LE2	
			2.5	566660	NEBV-H1G2-P-2.5-N-LE2	
			5	566661	NEBV-H1G2-P-5-N-LE2	

Ordering data – Blanking plug B					
	Pneumatic connection	Part no.	Type	PU ¹⁾	
	M7	174309	B-M7	10	
	G1/8	3568	B-1/8	10	

1) Packaging unit.

Ordering data – Push-in fitting QS					
	Pneumatic connection		Part no.	Type	PU ¹⁾
	G1/8	Tubing O.D. 8 mm	186098	QS-G1/8-8	10
	G1/8	Tubing O.D. 8 mm	186109	QS-G1/8-8-I	10

1) Packaging unit.