


Quick connectors

FESTO



Quick connectors

Product range overview

FESTO

Design	Design	Type	Connection D1		Tubing I.D.	→ Page/ Internet
			M thread	G thread		
Straight	Quick connector – Female thread with sealing ring					
		ACK Aluminium design	–	G1/8	3, 4, 6	5
				G1/4	4, 6	
				G3/8	6, 9	
				G1/2	13	
	Quick connector – Male thread with sealing ring					
		CK Metal design	M5	–	3, 4	6
			–	G1/8	3, 4, 6	
				G1/4	4, 6, 9	
				G3/8	6, 9, 13	
				G1/2	13	
		CK-...-KU Polymer design	–	G1/8	3, 4, 6	7
			–	G1/4	4, 6, 9	
				G3/8	6, 9	
	Bulkhead quick connector – Female thread with sealing ring					
		QCK	M5	–	PK-3	8
			–	G1/8	PK-4	
				G1/4	PK-6	
				G3/8	PK-9	
	Bulkhead quick connector					
		SCK Aluminium design	–	–	PK-3, PK-4, PK-6, PK-9	9
		SCK-...-KU Polymer design	–	–	PK-3, PK-4, PK-6, PK-9	9
	End cap for plastic tube connectors and barbed connectors					
		CV-PK	–	–	3, 4, 6, 9	10

Quick connectors

Product range overview

FESTO

Design	Design	Type	Connection D1			Tubing I.D.	→ Page/ Internet
			M thread	R thread	G thread		
L-shape	Elbow quick connector						
		GCK-...-KU Polymer design	–	R1/8	–	4, 6	11
				R1/4		4, 6	
				R3/8		6, 9	
	Elbow quick connector with 2 sealing rings, orientable						
		LCK Metal design	M5	–	–	3, 4	12
			–		G1/8	3, 4, 6	
					G1/4	4, 6, 9	
					G3/8	6, 9, 13	
					G1/2	13	
		LCK-...-KU Polymer design	–	–	G1/8	4, 6	12
			G1/4	4, 6			
T-shape	T quick connector with 2 sealing rings, orientable						
		TCK Metal design	M5	–	–	3, 4	13
			–		G1/8	3, 4, 6	
					G1/4	4, 6	
					G3/8	6, 9	
					G1/2	13	
		TCK-...-KU Polymer design	–	–	G1/8	4, 6	13
			G1/4	4, 6			
	T-distributor						
		FCK-...-KU	–	–	–	3	14
						4	
						6	
						9	
	Union nut for CK tube connector						
		MCK Metal design	–	–	–	3, 4, 6, 9, 13	15
MCK-...-KU Polymer design		–	–	–	3, 4, 6, 9	15	

Quick connectors

Product range overview

FESTO

Design	Design	Type	Connection D1		Tubing I.D.	→ Page/ Internet
			M thread	G thread		
Multiple distributor	Combination hollow bolt VT with ring piece LK					
		VT-...-2 for 2 ring pieces	M5	G1/8, G1/4, G3/8	–	16
		VT-...-3 for 3 ring pieces	M5	G1/8, G1/4, G3/8	–	16
		LK Metal design	–	–	3, 4, 6	16
		LK-...-KU Polymer design	–	–	4, 6	16
	Combination hollow bolt VT with ring piece TK					
		VT-...-2 for 2 ring pieces	M5	G1/8, G1/4, G3/8	–	17
		VT-...-3 for 3 ring pieces	M5	G1/8, G1/4, G3/8	–	17
		TK Metal design	–	–	3, 4, 6	17
		TK-...-KU Polymer design	–	–	4, 6	17

Quick connectors ACK

Technical data

FESTO

Quick connector ACK

Female thread with sealing ring

Materials:

Threaded plug: Aluminium

Union nut: Aluminium

Note on materials:

RoHS-compliant



General technical data	
Mounting position	Any
Type of seal on threaded plug	Sealing ring

Operating and environmental conditions	
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration ²⁾
Note on operating/pilot medium	Operation with lubricated medium possible
Ambient temperature [°C]	-10 ... +60
Corrosion resistance class CRC ¹⁾	2
Maritime classification	See certificate ²⁾


1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

2) Additional information www.festo.com/sp → Certificates.

Dimensions

Download CAD data → www.festo.com



Ordering data										
Pneumatic connection			Nominal size [mm]	L1	L2			Part No.	Type	PU ¹⁾
Female thread D1	For tubing O.D. [mm]	For tubing I.D. [mm]								
G1/8	4	–	2.4	23.9	9	13	8	5664	ACK-1/8-PK-3	10
	6	–	3.4	27	9	13	12	3714	ACK-1/8-PK-4	10
	8	–	5.3	27	9	13	14	7842	ACK-1/8-PK-6	10
G1/4	6	–	3.4	30	12	17	12	3713	ACK-1/4-PK-4	10
	8	–	5.3	30	12	17	14	3712	ACK-1/4-PK-6	10
G3/8	8	–	5.3	31	12	19	14	3711	ACK-3/8-PK-6	10
	–	9	8	37.4	15	19	19	3710	ACK-3/8-PK-9	10
G1/2	–	13	12	40.2	15	27	24	4099	ACK-1/2-PK-13	1

1) Packaging unit quantity

Quick connectors CK

Technical data

FESTO

Quick connector CK

Metal design

Male thread with sealing ring

Materials:

Threaded plug

M thread: Galvanised steel

G thread: Aluminium

Union nut: Aluminium

Note on materials:

RoHS-compliant



General technical data	
Mounting position	Any
Type of seal on threaded plug	Sealing ring


Operating and environmental conditions	
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration ²⁾
Note on operating/pilot medium	Operation with lubricated medium possible
Ambient temperature [°C]	-10 ... +60
Corrosion resistance class CRC ¹⁾	2
Maritime classification	See certificate ²⁾

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

2) Additional information www.festo.com/sp → Certificates.

Dimensions Download CAD data → www.festo.com



Ordering data										
Pneumatic connection			Nominal size [mm]	L1	L2	≡	≡1	Part No.	Type	PU ¹⁾
Male thread D1	For tubing O.D. [mm]	For tubing I.D. [mm]								
M5	4	–	2.0	19.3	3.8	7	8	3561	CK-M5-PK-3	10
	6	–	2.9	21.5	3.8	10	–	3562	CK-M5-PK-4	10
G ¹ / ₈	4	–	2.0	21.6	4.9	13	8	3563	CK- ¹ / ₈ -PK-3	10
	6	–	2.9	24.7	4.9	13	12	2027	CK- ¹ / ₈ -PK-4	10
	8	–	4.9	24.8	4.9	13	14	2028	CK- ¹ / ₈ -PK-6	10
G ¹ / ₄	6	–	2.9	27.2	5.8	17	12	2029	CK- ¹ / ₄ -PK-4	10
	8	–	4.9	27.3	5.8	17	14	2030	CK- ¹ / ₄ -PK-6	10
	–	9	8	30.6	5.8	17	19	2031	CK- ¹ / ₄ -PK-9	10
G ³ / ₈	8	–	4.9	28.3	6.8	19	14	2032	CK- ³ / ₈ -PK-6	10
	–	9	8	31.6	6.8	19	19	2033	CK- ³ / ₈ -PK-9	10
	–	13	11.7	33.2	6.8	24	24	4097	CK- ³ / ₈ -PK-13	10
G ¹ / ₂	–	13	11.7	34.7	8.5	24	24	4098	CK- ¹ / ₂ -PK-13	1

1) Packaging unit quantity

Quick connectors CK

Technical data

FESTO

Quick connector CK-...-KU

Polymer design

Male thread with moulded-on sealing edge

Materials:

Threaded plug: POM

Union nut: POM

Note on materials:

RoHS-compliant



General technical data

Mounting position	Any
Type of seal on threaded plug	Sealing edge

Operating and environmental conditions

Operating pressure [bar]	0 ... 10
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration ²⁾
Note on operating/pilot medium	Operation with lubricated medium possible
Ambient temperature [°C]	-10 ... +60
Corrosion resistance class CRC ¹⁾	2
Maritime classification	See certificate ²⁾


1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

2) Additional information www.festo.com/sp → Certificates.

Dimensions

Download CAD data → www.festo.com



Ordering data

Pneumatic connection			Nominal size [mm]	L1	L2	C	C1	Part No.	Type	PU ¹⁾
Male thread D1	For tubing O.D. [mm]	For tubing I.D. [mm]								
G1/8	4	—	2.4	22.2	6.5	13	8	6253	CK-1/8-PK-3-KU	10
	6	—	3.4	25.3	6.5	13	12	6254	CK-1/8-PK-4-KU	10
	8	—	4.4	25.4	6.5	13	14	6255	CK-1/8-PK-6-KU	10
G1/4	6	—	3.4	28.5	8.5	17	12	6256	CK-1/4-PK-4-KU	10
	8	—	5.3	28.6	8.5	17	14	6257	CK-1/4-PK-6-KU	10
	—	9	7.3	31.9	8.5	17	19	6258	CK-1/4-PK-9-KU	10
G3/8	8	—	5.3	31	10.5	19	14	6460	CK-3/8-PK-6-KU	10
	—	9	8	34.5	10.5	19	19	6468	CK-3/8-PK-9-KU	10

1) Packaging unit quantity

Bulkhead quick connectors QCK

Technical data

FESTO

Bulkhead quick connector QCK
Female thread with sealing ring

Materials:
Housing: Aluminium


Note on materials:
RoHS-compliant
Free of copper and PTFE



General technical data	
Mounting position	Any
Type of seal on threaded plug	Sealing ring

Operating and environmental conditions	
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:-:-]
Note on operating/pilot medium	Operation with lubricated medium possible

Dimensions Download CAD data → www.festo.com



Ordering data														
Pneumatic connection		Nominal size	B1	D5	L1	L2	L3	L4	⌀C1	⌀C2	⌀C3	Part No.	Type	PU ¹⁾
D1		[mm]						max.						
M5	PK-3 ²⁾	2.4	3.2	M6x0.75	31	6	10	8	7	8	10	9424	QCK-M5-PK-3-B	10
G1/8	PK-4 ²⁾	3.4	3.5	M10x1	40	8	13.5	10	13	12	13	9425	QCK-1/8-PK-4-B	10
G1/4	PK-6 ²⁾	5.3	4	M12x1	45	12	18	10	17	14	17	9426	QCK-1/4-PK-6-B	10
G3/8	PK-9 ²⁾	8	5	M16x1	50	12	18.6	10	19	19	22	9427	QCK-3/8-PK-9-B	1

1) Packaging unit quantity
2) With union nut

Bulkhead quick connectors SCK

Technical data

FESTO

Bulkhead quick connector SCK

Materials:

Bulkhead quick connector SCK-...-KU

with moulded-on sealing ring

Housing
SCK: Aluminium
SCK-...-KU: POM

Note on materials:
RoHS-compliant
Free of copper and PTFE



General technical data


Mounting position	Any
-------------------	-----

Operating and environmental conditions

Operating pressure	[bar]	0 ... +10
Ambient temperature	[°C]	-10 ... +60

Dimensions

Download CAD data → www.festo.com



Ordering data

Pneumatic connection	Nominal size [mm]	B1	D5	L1	L2 max.	≡C1	Part No.	Type	PU ¹⁾
Aluminium design									
PK-3 ²⁾	2.4	3.2	M6x0.75	34	8	10	9420	SCK-PK-3	10
PK-4 ²⁾	3.4	3.5	M10x1	43	10	13	9421	SCK-PK-4	10
PK-6 ²⁾	5.3	4	M12x1	44	10	17	9422	SCK-PK-6	10
PK-9 ²⁾	8	5	M16x1	53	10	22	9423	SCK-PK-9	1
Polymer design									
PK-3 ²⁾	2.4	5	M10x1 ³⁾	41	10	13	9387	SCK-PK-3-KU	10
PK-4 ²⁾	3.4	5	M10x1	46	10	13	9388	SCK-PK-4-KU	10
PK-6 ²⁾	5.3	6	M12x1	48	10	17	9389	SCK-PK-6-KU	10
PK-9 ²⁾	8	7	M16x1	57	10	22	9390	SCK-PK-9-KU	1

1) Packaging unit quantity

2) With union nut

3) Installation diameter varies from aluminium version

End caps CV

Technical data

FESTO

End cap CV


for sealing barbed fittings and
connectors for polymer tubing

Material:

Polyurethane

Free of copper and PTFE

Conforms to RoHS



Dimensions and ordering data				
Tubing I.D.	Weight/piece [g]	Part No.	Type	PU*
3	0.001	6213	CV-PK-3-B	10
4	0.001	6214	CV-PK-4-B	10
6	0.001	6215	CV-PK-6-B	10
9	0.002	6216	CV-PK-9-B	10

Operating conditions (permissible static pressure)								
Type	CV-PK-3-B ... CV-PK-6-B						CV-PK-9-B	
Operating pressure [bar]	10	10	8	7	6	6	6	4
Ambient temperature [°C]	-35	+20	+40	+60	+80	+60	+60	+80

* Packaging unit quantity

Elbow quick connectors GCK


Technical data

FESTO

Elbow quick connector GCK-...-KU

Material:
Polyacetate
Free of copper and PTFE
Conforms to RoHS

Pressure range: 0 ... 10 bar
Temperature range: -10 ... +60 °C



Dimensions and ordering data												
Connection D1	Nominal size [mm]	Tubing I.D.	B1	H1	H2	H3	L1	L2	$\varnothing C1$	Part No.	Type	PU*
R $\frac{1}{8}$	2.9	4	13	22.5	8	16.5	26.5	20.5	20.5	6267	GCK-$\frac{1}{8}$-PK-4-KU	10
	4.9	6	17	24.5	8	17.5	28.5	21.5	21.5	6268	GCK-$\frac{1}{8}$-PK-6-KU	10
R $\frac{1}{4}$	2.9	4	17	25.5	11	19.5	30	22.5	22.5	6269	GCK-$\frac{1}{4}$-PK-4-KU	10
	4.9	6	17	27.5	11	20.5	30	22.5	22.5	6270	GCK-$\frac{1}{4}$-PK-6-KU	10
R $\frac{3}{8}$	4.9	6	19	28.5	10.5	21	34	24.5	24.5	6271	GCK-$\frac{3}{8}$-PK-6-KU	10
	8	9	19	33.5	10.5	23.5	37.2	27.7	27.7	6272	GCK-$\frac{3}{8}$-PK-9-KU	10

* Packaging unit quantity

L quick connectors LCK

Technical data

FESTO

L quick connector LCK

with 2 sealing rings

Orientable

Materials:

Housing

LCK: Die-cast zinc

LCK-...-KU: POM

L quick connector LCK-...-KU

with moulded-on sealing edge

Orientable

Note on materials:

RoHS-compliant


Free of copper and PTFE



General technical data		
Type	LCK	LCK-...-KU
Mounting position	Any	
Type of seal on threaded plug	Sealing ring	Sealing edge

Operating and environmental conditions		
Operating pressure [bar]	0 ... +16	
Ambient temperature [°C]	-10 ... +60	

Dimensions Download CAD data → www.festo.com



Ordering data													
Pneumatic connection	Nominal size	B1	H1	H2	L1	L2	L3	⌀C1	⌀C2	Part No.	Type	PU ²⁾	
D1	[mm]												
Die-cast zinc design													
M5	PK-3 ¹⁾	2.4	10	21.1	16.1	17.2	3.8	5.2	7	8	4468	LCK-M5-PK-3	10
	PK-4 ¹⁾	2.4	11	21.1	16.1	18	3.8	5.6	7	8	4562	LCK-M5-PK-4	10
G1/8	PK-3 ¹⁾	2	16	27.1	19.1	21.1	4.9	6.1	13	8	4136	LCK-1/8-PK-3	10
	PK-4 ¹⁾	2.9	16	30.2	22.2	27.1	4.9	9.1	13	12	4469	LCK-1/8-PK-4	10
	PK-6 ¹⁾	4.9	16	30.3	22.3	27.1	4.9	9.1	13	14	4470	LCK-1/8-PK-6	10
G1/4	PK-4 ¹⁾	2.9	20	34.2	24.2	28.1	5.7	9.2	17	12	4471	LCK-1/4-PK-4	10
	PK-6 ¹⁾	4.9	20	34.3	24.3	28.1	5.5	9.3	17	14	4472	LCK-1/4-PK-6	10
	PK-9 ¹⁾	8	20	37.6	27.6	33.3	5.7	11.8	17	19	11452	LCK-1/4-PK-9	10
G3/8	PK-6 ¹⁾	4.9	25	39.3	26.8	30.3	6.7	9.3	22	14	4473	LCK-3/8-PK-6	1
	PK-9 ¹⁾	8	25	42.6	30.1	35.3	6.7	11.8	22	19	4474	LCK-3/8-PK-9	1
G1/2	PK-13 ¹⁾	11.7	30	49.2	34.2	46.6	7.9	16.85	27	24	4100	LCK-1/2-PK-13	1
Polymer design													
G1/8	PK-4 ¹⁾	3.4	16	30.5	22.5	27.5	7.1	8.25	13	12	6259	LCK-1/8-PK-4-KU	10
	PK-6 ¹⁾	5.3	16	30.5	22.5	27.5	7.1	8.25	13	14	6260	LCK-1/8-PK-6-KU	10
G1/4	PK-4 ¹⁾	3.4	20	34.5	24.5	28.5	8.1	8.25	17	12	6261	LCK-1/4-PK-4-KU	10
	PK-6 ¹⁾	5.3	20	34.5	24.5	28.5	8.1	8.25	17	14	6262	LCK-1/4-PK-6-KU	10

1) With union nut

2) Packaging unit quantity

T quick connectors TCK

Technical data

FESTO

T quick connector TCK

with 2 sealing rings

Orientable

T quick connector

TCK-...-KU

with moulded-on sealing ring

Orientable

Materials:

Housing

TCK: Die-cast zinc

TCK-...-KU: POM

Union nut

TCK: Aluminium

TCK-...-KU: POM

Note on materials:

RoHS-compliant



General technical data


Type	TCK	TCK-...-KU
Mounting position	Any	
Type of seal on threaded plug	Sealing ring	Sealing edge

Operating and environmental conditions

Operating pressure	[bar]	0 ... +10
Ambient temperature	[°C]	-10 ... +60

Dimensions

Download CAD data → www.festo.com



Ordering data

Pneumatic connection		Nominal size	H1	H2	H3	L1	L2	≡C1	≡C2	Part No.	Type	PU ²⁾
D1		[mm]										
Die-cast zinc design												
M5	PK-3 ¹⁾	2	17.2	3.8	5.2	32.2	10	7	8	4484	TCK-M5-PK-3	10
	PK-4 ¹⁾	2	18	3.8	5.6	39.4	11	7	8	4563	TCK-M5-PK-4	10
G1/8	PK-3 ¹⁾	2	21.1	4.9	6.1	38.2	16	13	8	4137	TCK-1/8-PK-3	10
	PK-4 ¹⁾	2.9	27.1	4.9	9.1	44.4	16	13	12	4485	TCK-1/8-PK-4	10
	PK-6 ¹⁾	4.9	27.1	4.9	9.1	44.6	16	13	14	4486	TCK-1/8-PK-6	10
G1/4	PK-4 ¹⁾	2.9	28.1	5.7	9.2	48.4	20	17	12	4487	TCK-1/4-PK-4	10
	PK-6 ¹⁾	4.9	28.1	5.5	9.3	48.6	20	17	14	4488	TCK-1/4-PK-6	10
G3/8	PK-6 ¹⁾	4.9	30.3	6.7	9.3	53.6	25	22	14	4489	TCK-3/8-PK-6	1
	PK-9 ¹⁾	8	35.3	6.7	11.8	60.2	25	22	14	4490	TCK-3/8-PK-9	1
G1/2	PK-13 ¹⁾	11.7	46.6	7.9	16.9	68.4	30	27	24	4101	TCK-1/2-PK-13	1
Polymer design												
G1/8	PK-4 ¹⁾	3.4	27.5	7.1	8.25	45	16	13	12	6263	TCK-1/8-PK-4-KU	10
	PK-6 ¹⁾	5.3	27.5	7.1	8.25	45	16	13	14	6264	TCK-1/8-PK-6-KU	10
G1/4	PK-4 ¹⁾	3.4	28.5	8.1	8.25	49	20	17	12	6265	TCK-1/4-PK-4-KU	10
	PK-6 ¹⁾	5.3	28.5	8.1	8.25	49	20	17	14	6266	TCK-1/4-PK-6-KU	10

1) With union nut

2) Packaging unit quantity

T quick connectors FCK

Technical data

FESTO

T-distributor FCK-...-KU

Material:


Polymer

Free of copper and PTFE

Conforms to RoHS

Pressure range: 0 ... 10 bar

Temperature range: -10 ... +60 °C



Dimensions and ordering data												
Tubing I.D.	Nominal size [mm]	B1	D5	H1	H2	H3	L1	L2	≈C1	Part No.	Type	PU*
3	2.4	11	4.3	23.8	19.8	5	39.6	10	8	6273	FCK-3-PK-3-KU	10
4	3.4	15	4.3	30.2	24.2	6	48.4	12	12	6274	FCK-3-PK-4-KU	10
6	5.3	18	4.3	31.2	24.2	6	48.4	12	14	6275	FCK-3-PK-6-KU	10
9	8	22	4.3	38.3	28.8	7.1	56.4	13	19	6276	FCK-3-PK-9-KU	10

* Packaging unit quantity


Union nuts MCK

Technical data

FESTO

Union nut MCK for tube connectors

Material:
Blue anodised aluminium
Free of copper and PTFE
Conforms to RoHS



Union nut MCK-...-KU for tube connectors

Material:
Polymer design
Free of copper and PTFE
Conforms to RoHS

Dimensions and ordering data						
Tubing I.D.	D1	L1	≈C1	Part No.	Type	PU*
Aluminium design						
3	M6x0.75	8.5	8	205254	MCK-PK-3	1
4	M10x1	11	12	2965	MCK-PK-4 ¹⁾	1
4	M8x1	9.5	–	205257	MCK-PK-4-R ²⁾	1
6	M12x1	11	14	2966	MCK-PK-6	1
9	M16x1	14.4	19	2967	MCK-PK-9	1
13	M22x1	18	24	206504	MCK-PK-13	1
Polymer design						
3	M6x0.75	9.5	8	211289	MCK-PK-3-KU	1
4	M10x1	12.5	12	211291	MCK-PK-4-KU ¹⁾	1
6	M12x1	12.5	14	211292	MCK-PK-6-KU	1
9	M16x1	16	19	211293	MCK-PK-9-KU	1

* Packaging unit quantity

1) except for connectors CK-M5-PK-4, LCK-M5-PK-4, TCK-M5-PK-4

2) for connectors CK-M5-PK-4, LCK-M5-PK-4, TCK-M5-PK-4

Multiple distributors

Technical data

FESTO

Hollow bolt VT with ring piece LK
(one outlet connection)

Certification:
Ring piece LK: Germanischer Lloyd

Materials:
Hollow bolt: Galvanised steel
Ring piece LK: Die-cast zinc
Ring piece LK-...-KU: Polymer

Note on materials:
Conforms to RoHS



VT



LK

Ordering data				Dimensions → 18			
Hollow bolt				Ring piece			
Pneumatic connection	No. of ring pieces	Part No.	Type	Pneumatic connection	Part No.	Type	PU*
Die-cast zinc design							
M5	2	206145	VT-M5-2 ³⁾	PK-3 with union nut	4475	LK-M5-PK-3 ¹⁾	10
	3	4594	VT-M5-3 ³⁾				
G1/8	2	4593	VT-1/8-2-PK-3 ³⁾	PK-3 with union nut	4597	LK-1/8-PK-3 ¹⁾	10
	3	4595	VT-1/8-3-PK-3 ³⁾				
G1/8	2	206146	VT-1/8-2 ³⁾	PK-4 with union nut	4476	LK-1/8-PK-4 ¹⁾	10
	3	4596	VT-1/8-3 ³⁾				
G1/8	2	206146	VT-1/8-2 ³⁾	PK-6 with union nut	4477	LK-1/8-PK-6 ¹⁾	10
	3	4596	VT-1/8-3 ³⁾				
G1/4	2	206147	VT-1/4-2 ³⁾	PK-4 with union nut	4478	LK-1/4-PK-4 ¹⁾	10
	3	2335	VT-1/4-3 ³⁾				
G1/4	2	206147	VT-1/4-2 ³⁾	PK-6 with union nut	4479	LK-1/4-PK-6 ¹⁾	10
	3	2335	VT-1/4-3 ³⁾				
G3/8	2	206148	VT-3/8-2 ³⁾	PK-6 with union nut	4480	LK-3/8-PK-6 ¹⁾	1
	3	2336	VT-3/8-3 ³⁾				
Polymer design							
G1/8	2	206146	VT-1/8-2 ³⁾	PK-4 with union nut	6280	LK-1/8-PK-4-KU ^{2) 3)}	10
	3	4596	VT-1/8-3 ³⁾				
G1/8	2	206146	VT-1/8-2 ³⁾	PK-6 with union nut	6281	LK-1/8-PK-6-KU ^{2) 3)}	10
	3	4596	VT-1/8-3 ³⁾				
G1/4	2	206147	VT-1/4-2 ³⁾	PK-4 with union nut	6282	LK-1/4-PK-4-KU ^{2) 3)}	10
	3	2335	VT-1/4-3 ³⁾				
G1/4	2	206147	VT-1/4-2 ³⁾	PK-6 with union nut	6283	LK-1/4-PK-6-KU ^{2) 3)}	10
	3	2335	VT-1/4-3 ³⁾				

* Packaging unit quantity

1) With union nut MCK and 2 sealing rings OK

2) With union nut MCK, with moulded-on sealing ring, pressure range 0 ... 10 bar, temperature range -10 ... +60 °C

3) Free of copper and PTFE

Multiple distributors

Technical data

FESTO

Hollow bolt VT with ring piece TK (2 outlet connections)

Materials:
Hollow bolt: Galvanised steel
Ring piece TK: Die-cast zinc
Ring piece TK-...-KU: Polymer

Note on materials:
Conforms to RoHS



VT



TK

Operating and environmental conditions		
Operating pressure	[bar]	0 ... +10
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:-:-]	
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)	
Certification	Ring piece TK: Germanischer Lloyd	

Ordering data				Dimensions → 18			
Hollow bolt				Ring piece			
Pneumatic connection	No. of ring pieces	Part No.	Type	Pneumatic connection	Part No.	Type	PU*
Die-cast zinc design							
M5	2	206145	VT-M5-2 ³⁾	PK-3 with union nut	4491	TK-M5-PK-3 ¹⁾	1
	3	4594	VT-M5-3 ³⁾				
G1/8	2	4593	VT-1/8-2-PK-3 ³⁾	PK-3 with union nut	4598	TK-1/8-PK-3 ¹⁾	1
	3	4595	VT-1/8-3-PK-3 ³⁾				
	2	206146	VT-1/8-2 ³⁾	PK-4 with union nut	4492	TK-1/8-PK-4 ¹⁾	1
	3	4596	VT-1/8-3 ³⁾				
	2	206146	VT-1/8-2 ³⁾	PK-6 with union nut	4493	TK-1/8-PK-6 ¹⁾	1
	3	4596	VT-1/8-3 ³⁾				
G1/4	2	206147	VT-1/4-2 ³⁾	PK-4 with union nut	4494	TK-1/4-PK-4 ¹⁾	1
	3	2335	VT-1/4-3 ³⁾				
	2	206147	VT-1/4-2 ³⁾	PK-6 with union nut	4495	TK-1/4-PK-6 ¹⁾	1
	3	2335	VT-1/4-3 ³⁾				
G3/8	2	206148	VT-3/8-2 ³⁾	PK-6 with union nut	4496	TK-3/8-PK-6 ¹⁾	1
	3	2336	VT-3/8-3 ³⁾				
Polymer design							
G1/8	2	206146	VT-1/8-2 ³⁾	PK-4 with union nut	6284	TK-1/8-PK-4-KU ^{2) 3)}	1
	3	4596	VT-1/8-3 ³⁾				
	2	206146	VT-1/8-2 ³⁾	PK-6 with union nut	6285	TK-1/8-PK-6-KU ^{2) 3)}	1
	3	4596	VT-1/8-3 ³⁾				
G1/4	2	206147	VT-1/4-2 ³⁾	PK-4 with union nut	6286	TK-1/4-PK-4-KU ^{2) 3)}	1
	3	2335	VT-1/4-3 ³⁾				
	2	206147	VT-1/4-2 ³⁾	PK-6 with union nut	6287	TK-1/4-PK-6-KU ^{2) 3)}	1
	3	2335	VT-1/4-3 ³⁾				

* Packaging unit quantity

1) With 2 union nuts MCK and 2 sealing rings OK

2) With 2 union nuts MCK, with moulded-on sealing ring, pressure range 0 ... 10 bar, temperature range -10 ... +60 °C

3) Free of copper and PTFE

Multiple distributors

Technical data

FESTO

Multiple distributor

consisting of:


- Hollow bolt VT and ring piece LK

→ 16

or

- Hollow bolt VT and ring piece TK

→ 17



- 1 Hollow bolt VT
- 2 Ring piece LK
- 3 Ring piece TK

Dimensions													
Connection D1	Hollow bolt Type	Ring piece Type	H1	H2	H3	H4	H5	L1	L2	L3	≡C1	≡C2	
M5	VT-M5-2	LK-M5-PK-3	27.3	4	5.2	15.1	–	–	5	16.1	7	8	
		TK-M5-PK-3						32.2	–				
	VT-M5-3	LK-M5-PK-3	37.1	3.9	5.2	15.1	25	–	5	16.1	7	8	
		TK-M5-PK-3						32.2	–				
G1/8	VT-1/8-2-PK-3	LK-1/8-PK-3	32.7	5.9	6.1	16.7	–	–	8	19.1	13	8	
		TK-1/8-PK-3						38.2	–				
	VT-1/8-3-PK-3	LK-1/8-PK-3	43.3	5.9	6.1	16.7	27.3	–	8	19.1	13	8	
		TK-1/8-PK-3						38.2	–				
	VT-1/8-2	LK-1/8-PK-4	44.8	6	9.1	25.7	–	–	8	22.2	13	12	
		TK-1/8-PK-4						44.4	–				
		LK-1/8-PK-6						–	8	22.3		14	
		TK-1/8-PK-6						44.6	–				
	VT-1/8-3	LK-1/8-PK-4	61.2	5.8	9.1	25.7	42.3	–	8	22.2	13	12	
		TK-1/8-PK-4						44.4	–				
		LK-1/8-PK-6						–	8	22.3		14	
		TK-1/8-PK-6						44.6	–				
G1/4	VT-1/4-2	LK-1/4-PK-4	45.2	6.6	9.2	25.4	–	–	10	24.2	17	12	
		TK-1/4-PK-4						48.4	–				
		LK-1/4-PK-6		6.2	9.3	25.7		–	10	24.3		14	
		TK-1/4-PK-6						48.6	–				
	VT-1/4-3	LK-1/4-PK-4	62.5	6.7	9.2	25.4	41.6	–	10	24.2	17	12	
		TK-1/4-PK-4						48.4	–				
		LK-1/4-PK-6		6.1	9.3	25.7		42.1	–	10		24.3	14
		TK-1/4-PK-6							48.6	–			
G3/8	VT-3/8-2	LK-3/8-PK-6	47.5	7.5	9.3	25.7	–		–	12.5	26.8	22	14
		TK-3/8-PK-6						53.6	–				
	VT-3/8-3	LK-3/8-PK-6	63.9	7.5	9.3	25.7		42.1	–	12.5	26.8	22	14
		TK-3/8-PK-6							53.6	–			