

Fitting NLFA

FESTO



Key features

At a glance

- Fittings for liquid media, especially suitable for laboratory applications
- Five different fittings for a range of tubing and dosing nozzles
- Intended use:

The fittings NLFA are intended for installation in laboratory devices. The fittings are used for mounting tubing or needles within the scope of their technical data. The chemical resistance of the fittings coming into contact with the media must be checked for each application. The application must be validated.

- Misuse:

Use with incompatible media (compatibility must be checked by the customer in advance). Please contact Festo for advice if you are unsure about the product's suitability for the planned application.

Type codes

001	Series	
NLFA	Fitting	
002	Design	
D	Straight	
003	Fluid connection 1	
U14	1/4-28 UNF	

004	Fluid connection 2	
B1.2	Barbed connector, 1.2 mm	
B2.1	Barbed connector, 2.1 mm	
K1.6	Clamped connection 1.6 mm	
K3	Clamped connection 3 mm	
K3.2	Clamped connection 3.2 mm	
005	Material, in contact with media	
PP	Polypropylene	
006	Packaging unit	
P10	10	

Data sheet

General technical data – Barbed connector	
Type ID code	NLFA
Design	Tubing mount via barbed connector
Fluid connection	UNF1/4-28
Fluid connection 2	For tubing I.D. 1.2 mm, for tubing I.D. 2.1 mm
Design	Straight design
Sealing principle	Hard
Mounting position	Any
Product weight	0.5 ... 1.06 g
Pack size	10

General technical data – Clamped connection	
Type ID code	NLFA
Design	Tubing mount via clamped connection
Fluid connection	UNF1/4-28
Fluid connection 2	For tubing O.D. 1.6 mm, for tubing O.D. 3 mm, for tubing O.D. 3.2 mm
Design	Straight design
Sealing principle	Hard
Mounting position	Any
Product weight	0.44 ... 0.53 g
Pack size	10

Operating and environmental conditions – Barbed connector	
Type ID code	NLFA
Medium	Liquid media, gaseous media
Note on the medium	Note resistance of materials in contact with the medium
Operating pressure for entire temperature range	-0.75 ... 4 bar
Temperature of medium	0 ... 35°C
Ambient temperature	0 ... 35°C
Storage temperature ¹⁾	-20 ... 70°C
Food-safe	See supplementary material information

1) Only valid for uninstalled state.


Operating and environmental conditions – Clamped connection	
Type ID code	NLFA
Medium	Liquid media, gaseous media
Note on the medium	Note resistance of materials in contact with the medium
Operating pressure for entire temperature range	-0.75 ... 6 bar
Temperature of medium	0 ... 50°C
Ambient temperature	0 ... 50°C
Storage temperature ¹⁾	-20 ... 70°C
Food-safe	See supplementary material information

1) Only valid for uninstalled state.

Materials	
Type ID code	NLFA
Screwed trunnion material	PA-reinforced
Note on materials	RoHS-compliant

Dimensions

Dimensions – With barbed connector

[Download CAD data → www.festo.com](http://www.festo.com)



[1] Mounting surface

	D1	D2 ø	D3 ø	D4 ø	D5 ø	D6 ø	D7	D8 ø max.
NLFA-D-U14-B1.2-PP-P10	UNF1/4-28	7,5	4,7	0,6	1,6	1,5	UNF1/4-28	1,2
NLFA-D-U14-B2.1-PP-P10	UNF1/4-28	7,5	4,7	1,3	2,6	2,2	UNF1/4-28	2,4

	H1	H2	H3	L1	T1	T2	W1
NLFA-D-U14-B1.2-PP-P10	16,8	14,9	9,4	0,8	8,9	7,1	90°
NLFA-D-U14-B2.1-PP-P10	16,8	14,9	9,4	0,8	8,9	7,1	90°

Dimensions

Dimensions – With clamped connection

Download CAD data → www.festo.com

[1] Mounting surface

	D1	D2 ø	D3 ø	D4 ø	D7	D8 ø max.	H1
NLFA-D-U14-K1.6-PP-P10	UNF1/4-28	7,5	4,7	1,7	UNF1/4-28	1,2	15,5
NLFA-D-U14-K3-PP-P10	UNF1/4-28	7,5	4,7	3,1	UNF1/4-28	2,4	15,5
NLFA-D-U14-K3.2-PP-P10	UNF1/4-28	7,5	4,7	3,3	UNF1/4-28	2,4	15,5

	H2	H3	L1	T1	T2	W1
NLFA-D-U14-K1.6-PP-P10	14	8,5	0,8	8,9	7,1	90°
NLFA-D-U14-K3-PP-P10	14	8,5	0,8	8,9	7,1	90°
NLFA-D-U14-K3.2-PP-P10	14	8,5	0,8	8,9	7,1	90°

Ordering data

Ordering data			
Design	Fluid connection 2	Part no.	Type
Straight	Barbed connector, 1.2 mm	8104288	NLFA-D-U14-B1.2-PP-P10
	Barbed connector, 2.1 mm	8104289	NLFA-D-U14-B2.1-PP-P10
	Clamped connection 1.6 mm	8104285	NLFA-D-U14-K1.6-PP-P10
	Clamped connection 3 mm	8104286	NLFA-D-U14-K3-PP-P10
	Clamped connection 3.2 mm	8104287	NLFA-D-U14-K3.2-PP-P10

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change