

Round cylinders EG

FESTO



Characteristics and type codes

Characteristics

Pneumatic cylinders in miniature design

- The slim design makes these cylinders especially suitable for compact assemblies, e.g. in testing systems for keyboards or mobile phones
- Single-acting
- Low mass: 2 to 24 g
- Ready for installation
- Corrosion-resistant
- Barbed fitting for standard I.D. plastic tubing

Type codes


001	Series
EG	Round cylinder, single-acting

002	Piston diameter
2.5	2.5
4	4
6	6

003	Stroke
5	5
10	10
15	15
20	20
25	25

004	Pneumatic connection
PK-2	
PK-3	

Data sheet



- $\varnothing$ - Diameter
2.5 ... 6 mm
- l - Stroke length
5 ... 25 mm



Technical data												
Piston diameter	2.5			4				6				
Stroke	[mm]	5	10	5	10	15	20	5	10	15	20	25
Design	Piston											
	Cylinder barrel											
	Piston rod at one end											
Mode of operation	Single-acting, pushing											
Pneumatic connection	PK-2							PK-3				
Type of mounting	With lock nut											
Piston rod thread	ø 1			M2				M3				
Cushioning	No cushioning							At one end, non-adjustable				
Position sensing	Without											
Mounting position	Any											
Product weight	[g]	2	2	4	5	5	6	19	20	20	23	24

Operating and environmental conditions			
Piston diameter	2.5	4	6
Operating pressure [bar]	3.5 ... 7		3 ... 7
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]		
Ambient temperature [°C]	+5 ... +60		
Corrosion resistance CRC ¹⁾	2		


1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Forces [N]												
Piston diameter	2.5				4				6			
Stroke [mm]	5	10	15	20	5	10	15	20	5	10	15	20
Theoretical force at 6 bar, advancing	1.9				4.8	4.7	4.9	4.9	11.8			
Theoretical spring return force												
Min.	0.5				1.5	1.7	1.8	1.5	4.1	3.1	2.0	3.1
Max.	1.0				2.7	2.8	2.6		5.2			

Materials

Sectional view




Piston diameter	2.5	4	6
[1] Piston rod	High-alloy steel		
[2] Cover	High-alloy steel		
[3] Cylinder barrel	Nickel-plated brass		High-alloy steel
- Seals	Nitrile rubber	Thermoplastic polyurethane elastomer	Nitrile rubber
Note on materials	RoHS-compliant		

Data sheet

Dimensions


EG-2.5/-4

Download CAD data → www.festo.com


- [1] Barbed fitting for standard I.D. plastic tubing NW
- [2] Tightening torque
EG-2.5: 0.25 Nm
EG-4: 0.85 Nm

Type	AM	B1	B2	D1	D2 ø	D3 ø	KK	L1	L2	L3	L4	L5	≈G1	≈G2
EG-2.5-5-PK-2	–	1.6	–	M2.5	2.65	3.5	ø1	29	3.5	3	1.5	5	–	4
EG-2.5-10-PK-2								38						
EG-4-5-PK-2	6	3	1.6	M4	2.65	5	M2	41	6	5	7	5	4	5
EG-4-10-PK-2								50						
EG-4-15-PK-2								59						
EG-4-20-PK-2								64						

EG-6



- [1] Barbed fitting for standard I.D. plastic tubing NW 3
- [2] Tightening torque
EG-6: 8.5 Nm

Type	AM	B1	B2	D1	D2 ø	D3 ø	D4 ø	D5 ø	KK	L1	L2	L3	L4	L5	L6	≈G1	≈G2	≈G3
EG-6-5-PK-3	15	4	2.4	M8x1	3.4	7	10	8	M3	75	8	6.5	20	6	4.5	5.5	12	9
EG-6-10-PK-3										80								
EG-6-15-PK-3										85								
EG-6-20-PK-3										102								
EG-6-25-PK-3										107								

Ordering data

	Piston diameter	Stroke [mm]	Part no.	Type
	2.5	5	15883	EG-2.5-5-PK-2
		10	15884	EG-2.5-10-PK-2
	4	5	15885	EG-4-5-PK-2
		10	15886	EG-4-10-PK-2
		15	15887	EG-4-15-PK-2
		20	15888	EG-4-20-PK-2
	6	5	15891	EG-6-5-PK-3
		10	15892	EG-6-10-PK-3
		15	15893	EG-6-15-PK-3
		20	15894	EG-6-20-PK-3
		25	15895	EG-6-25-PK-3

Accessories

Ordering data – Plastic tubing						
	For type	Description	Colour	Part no.	Type	PE ¹⁾ [m]
	EG-2.5 and EG-4	Highly flexible plastic tubing Suitable for energy chains Material: TPE-U (PU)	Blue	159660	PUN-3x0.5-BL	50
			Blue	525745	PUN-3x0.5-BL-500	500
			Yellow	178416	PUN-3x0.5-GE	50
			Green	178423	PUN-3x0.5-GN	50
			Red	178409	PUN-3x0.5-RT	50
			Silver	152583	PUN-3x0.5-SI	50
			Silver	525738	PUN-3x0.5-SI-500	500
			Black	159661	PUN-3x0.5-SW	50
			Black	553936	PUN-3x0.5-SW-500	500
	EG-6	Highly flexible plastic tubing Suitable for energy chains Material: TPE-U (PU)	Blue	159662	PUN-4x0.75-BL	50
			Blue	525746	PUN-4x0.75-BL-500	500
			Yellow	178417	PUN-4x0.75-GE	50
			Green	178424	PUN-4x0.75-GN	50
			Red	178410	PUN-4x0.75-RT	50
			Silver	152584	PUN-4x0.75-SI	50
			Silver	525739	PUN-4x0.75-SI-500	500
			Black	159663	PUN-4x0.75-SW	50
			Black	553937	PUN-4x0.75-SW-500	500

1) Packaging unit