

Air reservoirs

FESTO




Air reservoirs CRVZS

FESTO

Technical data


Function

CRVZS-Q1/0.4/0.75/2



CRVZS-5/10/20

with condensate drain



•  Temperature range
-10 ... +100 °C

•  Operating pressure
-0.95 ... 16 bar



- The reservoirs can be used to compensate pressure fluctuations, and act as accumulators in the event of sudden air consumption
- They can also be used to provide large quantities of compressed air for supplying fast pulsing drives
- Time delays for pressure build-up can be achieved in combination with flow control valves

Technical data							
Type	CRVZS-Q1	CRVZS-Q4	CRVZS-Q75	CRVZS-2	CRVZS-5	CRVZS-10	CRVZS-20
Pneumatic connection	G $\frac{1}{8}$	G $\frac{1}{4}$		G $\frac{1}{2}$	G1		
Condensate drain connection	-				G $\frac{3}{8}$		
Type of mounting	Retaining clips			Via through-holes			
Installation position	Any				Condensate drain downwards		
Volume [l]	0.1 ±20%	0.4 ±20%	0.75 ±20%	2 ±10%	5 ±10%	10 ±10%	20 ±10%
Weight [g]	226	543	736	1,681	3,581	6,459	10,208

•  Note: This product conforms to ISO 1179-1 and to ISO 228-1

Operating and environmental conditions							
Type	CRVZS-Q1	CRVZS-Q4	CRVZS-Q75	CRVZS-2	CRVZS-5	CRVZS-10	CRVZS-20
Operating pressure [bar]	−0.95 ... +16						
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [−:−:−]						
	Nitrogen						
Ambient temperature [°C]	−10 ... +100 (observe operating range of tubing and pipe)						
Temperature of medium [°C]	−10 ... +100 (observe operating range of tubing and pipe)						
Corrosion resistance class CRC ¹⁾	3						
Conforms to standard	AD 2000						
CE symbol (see declaration of conformity) ²⁾	–				In accordance with EU Pressure Equipment Directive		
Food-safe ²⁾	See supplementary material information						
Approval ²⁾	German Technical Control Board (TÜV)						
	CRN						
Certificate issuing department	TSSACRN0H17477.5C				CRN0H15669.5C		

1) Corrosion resistance class CRC 3 to Festo standard FN 940070
High corrosion stress. Outdoor exposure under moderate corrosive conditions. External visible parts with primarily functional requirements for the surface and which are in direct contact with a normal industrial environment.

2) Additional information www.festo.com/sp → Certificates.

Air reservoirs CRVZS

Technical data


FESTO

Materials							
Type	CRVZS-Q1	CRVZS-Q4	CRVZS-Q75	CRVZS-2	CRVZS-5	CRVZS-10	CRVZS-20
Air reservoir	High-alloy stainless steel						
Retaining clips	High-alloy stainless steel			–			
Note on materials	Free of copper and PTFE						
	Conforms to RoHS						

Dimensions

Download CAD data → www.festo.com

CRVZS-Q1/CRVZS-Q4/CRVZS-Q75



Type	B ±2	B1	B2 ±2	D Ø	D1	D2 Ø	D3 Ø	H ±1	H1 ±1
CRVZS-Q1	51	14	–	40	G1/8	15	42	43	28
CRVZS-Q4	54	14	–	52	G1/4	19	54	50	34
CRVZS-Q75	60	20	79	70	G1/4	19	72	61	34


Type	L ±1	L1		L2	L3	≙	Max. tightening torque for connecting thread [Nm]
		min.	max.				
CRVZS-Q1	132	13	50	10	6	19	15
CRVZS-Q4	240	13	150	14	9	27	23
CRVZS-Q75	248	13	140	14	9	27	23

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Dimensions

Download CAD data → www.festo.com

CRVZS-2



• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Air reservoirs CRVZS


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

CRVZS-5




Note: This product conforms to ISO 1179-1 and to ISO 228-1

Dimensions

Download CAD data → www.festo.com

CRVZS-10/CRVZS-20



Type	D1 ± 2	H1 ± 1.5	L1 ± 3	Max. tightening torque	
				Connecting thread [Nm]	Condensate drain [Nm]
CRVZS-10	160	115	558	130	27
CRVZS-20	194	136	740	130	27

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data


Volume [l]	Part No.	Type	Volume [l]	Part No.	Type
0.1 $\pm 20\%$	160233	CRVZS-01	5 $\pm 10\%$	192159	CRVZS-5
0.4 $\pm 20\%$	160234	CRVZS-04	10 $\pm 10\%$	160237	CRVZS-10
0.75 $\pm 20\%$	160235	CRVZS-075	20 $\pm 10\%$	534845	CRVZS-20
2 $\pm 10\%$	160236	CRVZS-2			

Air reservoirs VZS

Technical data

FESTO

Function
with condensate drain



-  - Temperature range
-10 ... +100 °C

-  - Operating pressure
-0.95 ... 16 bar



- The reservoirs can be used to compensate pressure fluctuations, and act as accumulators in the event of sudden air consumption
- They can also be used to provide large quantities of compressed air for supplying fast pulsing drives
- Time delays for pressure build-up can be achieved in combination with flow control valves

Technical data	
Type	VZS-20-B
Pneumatic connection	G1
Condensate drain connection	G3/8
Type of mounting	Via through-holes
Installation position	Condensate drain downwards
Volume [l]	20 ±10%
Weight [g]	8,600

-  - Note: This product conforms to ISO 1179-1 and to ISO 228-1

Operating and environmental conditions	
Type	VZS-20-B
Operating pressure [bar]	-0.95 ... +16
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [-:-:-] Nitrogen
Ambient temperature [°C]	-10 ... +100 (observe operating range of tubing and pipe)
Temperature of medium [°C]	-10 ... +100 (observe operating range of tubing and pipe)
Corrosion resistance class CRC ¹⁾	4
Conforms to	EN 286-1
CE symbol (see declaration of conformity)	In accordance with EU Simple Pressure Vessel Directive

1) CRC4: Corrosion resistance class to Festo standard 940 070
Components with very heavy corrosion exposure. Components in contact with aggressive media, e.g. in food or chemical industries. These applications must, if necessary, be verified by special tests with the media concerned.

Materials	
Air reservoir	Painted steel
Note on materials	Free of copper and PTFE


Air reservoirs VZS

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



Type	B ±2	B1 ±1	D ±4 Ø	D1	D2 Ø	D3	D4 Ø	D5 ±0.5 Ø	H ±1.5	H1
VZS-20-B	150	100	206	G1	44.5	G $\frac{3}{8}$	28	9	146.5	4

Type	H2 min.	H3	L ±6	L1 ±1.5	L2	L3	Max. tightening torque	
							Connecting thread [Nm]	Condensate drain [Nm]
VZS-20-B	2	12	696	300	18	25	130	27

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data

Volume [l]	Part No.	Type
20 ±10%	192161	VZS-20-B

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalneptla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change