

Rodless Cylinders DGO - Inch Series

FESTO



- Piston Ø 1/2" to 1-5/8"
- Strokes up to 157"
- Double-acting
- Patented magnetic-coupling design
- Leakproof operation

Product range overview						
Function	Type	Piston Ø [in]	Stroke [in]	Force [lbf]	Variants	
					P	PPV
Double-acting	DGO	1/2, 5/8, 3/4, 1, 1-1/4, 1-5/8	0.4 ... 157	13 ... 145	■	■

Variants

- P Flexible cushioning rings
at both ends
- PPV Adjustable air cushioning
at both ends

Double-acting rodless cylinders equipped with magnetic coupling between the internal piston and external yoke. Movement of the external yoke results when the internal piston is driven with air pressure in

either direction. The magnetic force of the piston pulls the external yoke along the cylinder tube. As the piston moves, the working force is transferred to the yoke.

Because no piston rod extends, these cylinders require less space than traditional pneumatic cylinders. Operating devices and loads can be mounted directly to a flat mounting surface on the outer yoke.


Intermediate and end positions of the piston can be detected by proximity sensors, using the magnetic field of the yoke. The cylinder area is hermetically sealed from the outer yoke to prevent leakage.

Rodless cylinders DGO - Inch Series

Technical data

FESTO

Function




- Double-acting
- Magnetically coupled

Diameter

1/2 ... 1-5/8 inch

Stroke length

0.4 ... 157 inch



General technical data						
Piston Ø	1/2	5/8	3/4	1	1-1/4	1-5/8
Stroke [in]	0.4 ... 47	0.4 ... 98	0.4 ... 118	0.4 ... 137		0.4 ... 157
Pneumatic connection	10-32 UNF		1/8" NPT		1/4" NPT	
Operating medium	Filtered compressed air, lubricated or unlubricated, other media upon request.					
Design	Rodless (magnetically coupled)					
Cushioning	Flexible cushioning rings at both ends (P)	Adjustable air cushioning at both ends (PPV)				
Cushioning length [in]	–	0.55	0.67	0.75	0.79	0.91
Magnet for position sensing ¹⁾	Standard					

1) Position sensing via magnetic proximity sensor (ordered separately, see accessories).


Operating and environmental conditions						
Piston Ø	1/2	5/8	3/4	1	1-1/4	1-5/8
Operating pressure [psi]	29.4 ... 102.9	25.0 ... 102.9	23.5 ... 102.9	22.0 ... 102.9	20.6 ... 102.9	19.1 ... 102.9
Temperature range ¹⁾ [°F]	–4 ... +140					

1) Note operating range of proximity sensors

Forces [lbf]						
Piston Ø	1/2	5/8	3/4	1	1-1/4	1-5/8
Theoretical force at 90 psi	15.3	27.2	42.3	66.3	108.6	169.5
Breakaway force of the magnetic coupling	22.5	36.0	60.7	89.9	152.9	236.0

Materials

Sectional view



1	End cap	Anodized aluminum
2	Outer slide	Anodized aluminum
3	Cylinder barrel	High-alloy steel
–	Seals	Nitrile rubber, polyurethane



Rodless cylinders DGO - Inch Series

Technical data



FESTO

Weights [oz]						
Piston Ø	1/2	5/8	3/4	1	1-1/4	1-5/8
Product weight with 0 inch stroke	11.3	21.9	35.3	47.3	84.7	138.3
Additional weight per 1 inch stroke	0.18	0.27	0.36	0.43	0.54	0.72

Permissible axial force F dependent on lever arm A



Permissible lateral force F_q dependent on stroke length L



Rodless cylinders DGO - Inch Series



Technical data

Max. piston speed v dependent on the moving mass m

If the operating conditions are outside the permissible range, the moving mass must be externally cushioned using suitable equipment (shock absorbers or stops). This is done to avoid de-coupling the carriage from the piston.

Lubrication

The DGO has been lubricated during assembly. Additional lubrication is required every 120 miles of linear travel. The required lubricant is Festo GEL, available in a 14.5 ounce cartridge for grease guns. Part No. 13000257.




— Horizontal mounting position
 - - - Vertical mounting position

Contactless position sensing

Mounting the proximity sensors SMEO-/SMTO-/SMPO-1

Installation of proximity sensors, Types SMEO, SMTO and SMPO for sensing end and intermediate positions. Proximity sensors are mounted by the user near the rodless cylinder (1/4 in / 6 mm diameter rod may be used). Sensing is possible only in the indicated area of the outer yoke [2]. If sensing distance A is too small, multiple sensing may result.



- 1 Switching magnet for proximity sensor
- 2 Switching range
- 3 Outer slide 360° rotatable
- 4 Proximity sensor with mounting kit SMB-1


Switching distances, switching travel and hysteresis [in]

Proximity sensors	A	X						Switching travel	Hysteresis
		DGO-1/2-...	DGO-5/8-...	DGO-3/4-...	DGO-1-...	DGO-1-1/4-...	DGO-1-5/8-...		
SMEO-1, SMTO-1	0.24 ... 0.31	0.40 ... 0.43	0.51 ... 0.55	0.63 ... 0.67	0.79 ... 0.83	0.98 ... 1.02	1.26 ... 1.30	0.30 ... 0.51	0.04 ... 0.18
SMPO-1-H-B	0.20 ... 0.24							0.28 ... 0.59	0.02 ... 0.10


Technical data

Dimensions


Piston Ø1/2 inch



Piston Ø5/8... 1 inch



Piston Ø1-1/4... 1-5/8 inch



Dimensions are in inches, unless otherwise noted.

Rodless cylinders DGO - Inch Series

Technical data

FESTO

Dimensions									
Ø	B1	B2	D2 Ø	D3	D4 Ø	D5	D6 Ø	D7 Ø	D8 Ø
[in]									
5/8	0.31	1.4	0.6	M16x1.5	0.8	10-24 UNC	0.69	0.3	–
3/4	0.43	1.7	0.9	M22x1.5	1.1	10-24 UNC	0.84	0.3	–
1	0.43	2.0	0.9	M22x1.5	1.1	1/4-20 UNC	1.04	0.4	–
1-1/4	0.31	2.4	1.2	M30x1.5	1.5	1/4-20 UNC	1.32	0.4	1.7
1-5/8	0.39	2.9	1.5	M38x1.5	1.8	5/16-18 UNC	1.68	0.5	2.0

Ø	E1	J1	L1	L2	L3	L4	L5	L6	L7
[in]									
5/8	10-32 UNF	0.53	8.1	0.5	5.9	0.5	1.1	7.1	2.5
3/4	1/8" NPT	0.65	8.5	0.6	6.7	0.6	1.0	7.3	2.7
1	1/8" NPT ¹⁾	0.81	9.4	0.8	7.5	0.6	1.1	8.1	3.0
1-1/4	1/8" NPT	1.00	10.6	0.9	8.6	0.6	1.3	9.4	3.3
1-5/8	1/4" NPT	1.26	12.9	1.4	10.7	0.6	1.9	11.6	3.9

Ø	L8	L9	L10	L11	L12	L13	T1	T2	≈S1
[in]									[mm]
5/8	1.0	1.9	1.0	0.6	1.6	4.9	0.3	0.2	24
3/4	1.3	2.0	1.3	0.3	1.6	5.3	0.4	0.1	32
1	1.4	2.2	1.4	0.3	1.7	5.9	0.4	0.2	32
1-1/4	1.9	2.4	1.9	0.4	1.9	6.7	0.5	0.2	–
1-5/8	2.2	3.0	2.0	0.5	2.5	7.9	0.6	0.2	–

1) Max. screw-in depth 0.28 inch.

Dimensions are in inches, unless otherwise noted.

Rodless cylinders DGO - Inch Series

Ordering Data

FESTO

Mandatory data				
Function	Piston Ø	Stroke	Cushioning	Magnet for position sensing
DGO	1/2 5/8 3/4 1 1 1/4 1 5/8	0.4 ... 157	P PPV	A
DGO	- 1	- 100	- PPV	- A

Ordering table									
Size		1/2	5/8	3/4	1	1 1/4	1 5/8	Code	Enter code
[M]	Function	Standard cylinder, single-acting pushing						DGO	DGO
	Piston Ø [in]	1/2	5/8	3/4	1	1 1/4	1 5/8	-...	
	Stroke [in]	0.4 ... 47	0.4 ... 98	0.4 ... 118	0.4 ...137		0.4 ...157	-...	
	Cushioning [in]	Flexible cushioning rings at both ends	—	—	—	—	—	-P	
		—	Adjustable air cushioning at both ends						-PPV
	Magnet for position sensing	For use with magnetic proximity sensors						-A	-A


Transfer order code

DGO	-		-		-		-	A
------------	---	--	---	--	---	--	---	----------

Rodless cylinders DGO - Inch Series

Accessories overview

FESTO



Mounting attachments and accessories	
	Description
[1] Moment compensator FKG	To compensate misalignments and eliminate tilting moments
[2] Foot mounting HBN	On end caps for piston $\varnothing$ 1/2 ... 1 inch
[3] Flange mounting FBN	On end caps for piston $\varnothing$ 1/2 ... 1 inch
[4] Flange mounting FBN	On end caps for piston $\varnothing$ 1-1/4 ... 1-5/8 inch
[5] Proximity sensors SMEO-/SMT0-/SMPO-1	For contactless position sensing, mountable externally via a mounting kit
[6] One-way flow control valve GRLA	To regulate speed
[7] Push-in fitting QS	For connecting compressed air tubing with standard external diameters

Rodless cylinders DGO - Inch Series

Accessories

FESTO

Moment compensator FKG


for piston $\varnothing$ 5/8 ... 1-5/8 inch

The yoke mounting bracket prevents moment arm torque on the yoke by transferring the torque force to the centerline of the yoke. This greatly reduces the force lost to bearing friction and compensates for non-parallel alignment.

Maximum permissible misalignment of parallel guide in longitudinal axis of cylinder = 0.04 inch.

Includes: 1 moment compensator and 8 mounting screws

Material: Galvanized steel



Dimensions and ordering data																					
For $\varnothing$ [in]	B1	B2	B3	B4	B5	D1 $\varnothing$	D2 $\varnothing$	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	CRC ¹⁾	Weight [oz]	Part No.	Type
5/8	0.7	0.6	1.0	1.6	0.3	0.4	0.22	1.9	1.6	1.1	0.2	0.3	2.9	2.1	1.0	1.9	2.7	2	9.07	15233	FKG-16-B
3/4	0.7	0.6	1.3	1.7	0.3	0.4	0.22	2.1	1.7	1.3	0.2	0.3	3.2	2.4	1.3	2.2	3.0	2	10.65	33339	FKG-20-B
1	0.9	0.6	1.4	2.0	0.5	0.5	0.26	2.5	2.0	1.5	0.2	0.3	3.9	2.8	1.4	2.5	3.5	2	18.02	15234	FKG-25-B
1-1/4	0.9	0.6	1.9	2.4	0.5	0.5	0.26	2.9	2.2	1.7	0.2	0.3	4.3	3.1	1.9	2.9	3.9	2	23.88	33340	FKG-32-B
1-5/8	1.2	0.9	2.0	2.8	0.6	0.6	0.35	3.5	2.8	2.1	0.2	0.4	5.3	3.9	2.2	3.6	4.8	2	45.04	15235	FKG-40-B

1) Corrosion resistance class 2 according to Festo standard 940 070

Components with moderate corrosion resistance for use in normal industrial environments subjected to contact with coolants or lubricating agents.


Foot mounting HBN

for piston $\varnothing$ 1/2 ... 1 inch

Material:

Galvanized steel

Free of copper, PTFE and silicone



Dimensions and ordering data														
For Ø [in]	AB Ø	AH	AO	AT	AU	R1	SA	SS	TR	US	CRC ¹⁾	Weight [oz]	Part No.	Type
1/2	0.22	0.8	0.2	0.2	0.6	0.5	6.0	4.1	1.3	1.7	2	1.41	5125	HBN-12/16x1
5/8	0.22	1.1	0.2	0.2	0.6	0.5	8.2	6.3	1.3	1.7	2	1.76	6062	HBN-12/16x1-A
3/4	0.26	1.2	0.3	0.2	0.7	0.8	8.6	6.3	1.6	2.1	2	3.53	6064	HBN-20/25x1-A
1	0.26	0.9	0.3	0.2	0.7	0.8	9.4	7.2	1.6	2.1	2	3.53	6064	HBN-20/25x1-A

1) Corrosion resistance class 2 according to Festo standard 940 070

Components with moderate corrosion resistance for use in normal industrial environments subjected to contact with coolants or lubricating agents.

Dimensions are in inches, unless otherwise noted.

Rodless cylinders DGO - Inch Series

Accessories

FESTO


Flange mounting FBN

for piston $\varnothing$ 1/2 ... 1 inch

Material:

Galvanized steel

Free of copper, PTFE and silicone



Dimensions and ordering data											
For $\varnothing$ [in]	AB $\varnothing$	AT	L10	TF	UF	UR	US	CRC ¹⁾	Weight [oz]	Part No.	Type
1/2	0.22	0.2	5.2	1.6	2.1	1.2	1.7	2	0.88	5130	FBN-12/16
5/8	0.22	0.2	7.4	1.6	2.1	1.2	1.7	2	0.88	5130	FBN-12/16
3/4	0.26	0.2	7.4	2.0	2.6	1.6	2.1	2	1.59	5131	FBN-20/25
1	0.26	0.2	8.5	2.0	2.6	1.6	2.1	2	1.59	5131	FBN-20/25

1) Corrosion resistance class 2 according to Festo standard 940 070

Components with moderate corrosion resistance for use in normal industrial environments subjected to contact with coolants or lubricating agents.


Flange mounting FBN

for piston $\varnothing$ 1-1/4 ... 1-5/8 inch

Material:

Galvanized steel

Free of copper, PTFE and silicone



Dimensions and ordering data															
For Ø [in]	AB Ø	AH	AO	AT	AU	H1	SA	SS	TF	TR	US	CRC ¹⁾	Weight [oz]	Part No.	Type
1-1/4	0.3	1.1	0.3	0.2	0.6	0.6	10.5	8.6	1.1	2.0	2.6	2	3.6	195855	FBN-32
1-5/8	0.4	1.3	0.4	0.2	0.7	0.7	13.2	10.4	1.2	2.4	3.1	2	6.7	195856	FBN-40

1) Corrosion resistance class 2 according to Festo standard 940 070

Components with moderate corrosion resistance for use in normal industrial environments subjected to contact with coolants or lubricating agents.

Dimensions are in inches, unless otherwise noted.

Rodless cylinders DGO - Inch Series

Accessories

FESTO

Ordering data – Block-shape proximity sensor, magneto-resistive, NO contact							
	Mounting	Switch output	Electrical connection		Cable length [ft]	Part No.	Type
			Cable	M8 plug			
	Via mounting kit	PNP	3-wire	–	8.2	151683	SMT0-1-PS-K-LED-24-C
			–	3-pin	–	151685	SMT0-1-PS-S-LED-24-C
		NPN	3-wire	–	8.2	151684	SMT0-1-NS-K-LED-24-C
			–	3-pin	–	151686	SMT0-1-NS-S-LED-24-C

Ordering data – Block-shape proximity sensor, magnetic reed, NO contact						
	Mounting	Electrical connection		Cable length [ft]	Part No.	Type
		Cable	M8 plug			
	Via mounting kit	3-wire	–	8.2	30459	SME0-1-LED-24-B
		3-wire	–	16.4	151672	SME0-1-LED-24-K5-B
		–	3-pin	–	150848	SME0-1-S-LED-24-B

Ordering data – Block-shape proximity sensor, pneumatic				
	Mounting	Pneumatic connection	Part No.	Type
3/2-way valve, normally closed				
	Via mounting kit	Barbed fitting for 1/8 inch tubing ID	31008	SMPO-1-H-B

Ordering data – Mounting kit			
	Mounting	Part No.	Type
	For cylinder with tie rod Ø 1/4 inch or DUO rail mounting profile	11886	SMB-1

Ordering data – Plug sockets							
	Mounting	Switch output		Connection	Cable length [ft]	Part No.	Type
		PNP	NPN				
Straight socket							
	M8 union nut			3-pin	8.2	159420	SIM-M8-3GD-2.5-PU
					16.4	159421	SIM-M8-3GD-5-PU
Angled socket							
	M8 union nut			3-pin	8.2	159422	SIM-M8-3WD-2.5-PU
					16.4	159423	SIM-M8-3WD-5-PU

Ordering data – One-way flow control valves				
	Connection		Part No.	Type
	Thread	For tubing OD		
	10-32 UNF	3/16"	151573	GRLA-10-UNF-3/16-B
		1/4"	151574	GRLA-10-UNF-1/4-B
	1/8" NPT	5/32"	165009	GRLA-1/8-NPT-QS-5/32-U
		3/16"	190941	GRLA-1/8-NPT-QS-3/16-U
		1/4"	165010	GRLA-1/8-NPT-QS-1/4-U
		5/16"	165013	GRLA-1/8-NPT-QS-5/16-U
	1/4" NPT	3/16"	190944	GRLA-1/4-NPT-QS-3/16-U
		1/4"	165011	GRLA-1/4-NPT-QS-1/4-U
		5/16"	165014	GRLA-1/4-NPT-QS-5/16-U
		3/8"	190947	GRLA-1/4-NPT-QS-3/8-U

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

[f](#) [t](#) [in](#) [You Tube](#)

www.festo.com/socialmedia



www.festo.com

Subject to change