



Key features

Components for positioning and measuring using the standards-based cylinder DDPC



Measuring With measured-value transducer DADE











Positioning With end-position controller SPC11 or controller module CPX-CMAX/-CMPX

Proportional directional control valve MPYE



End-position controller SPC11-INC



Proportional directional control valve VPWP







Controller module CPX-CMAX, CPX-CMPX



Type codes

001	Series
DDPC	Standards-based cylinder, integrated displacement encoder
002	Protection against rotation
D	With guide unit
Q	With protection against rotation
003	Piston diameter
80	80
100	100
004	Stroke
	10 2000
005	Clamping unit
	None
	None

Piston rod type		
At one end		
Through piston rod		
Cushioning		
Elastic cushioning rings/plates on both sides		
Position sensing		
For proximity sensor		
Piston rod extension		
None		
1 500 mm		
	At one end Through piston rod Cushioning Elastic cushioning rings/plates on both sides Position sensing For proximity sensor Piston rod extension None	At one end Through piston rod Cushioning Elastic cushioning rings/plates on both sides Position sensing For proximity sensor Piston rod extension None

Peripherals overview



- 📲 - Note

If the drive DDPC is used without an end-position controller CPX-CMPX, SPC11 or axis controller CPX-CMAX, e.g. as a measuring cylinder, then the standard accessories for the drive DNC can be used.

Peripherals overview

Acces	Accessories						
	Туре	Description	→ Page/Internet				
[1]	Rod eye SGS	With spherical bearing	ddpc				
[2]	Foot mounting HNC	For mounting the drive on the bearing and end caps	ddpc				
[3]	Flange mounting FNC	For mounting the drive on the bearing and end caps	ddpc				
[4]	Guide unit ¹⁾ FENG-KF	For protecting against rotation at high torque loads	12				
[5]	Trunnion support LNZG	For mounting the trunnion flange kit DAMT	ddpc				
[6]	Trunnion flange kit DAMT	For swivelling movements of the drive	ddpc				
[7]	Slot cover ABP-5-S	For protection against contamination	ddpc				
[8]	Proximity switch SME/SMT-8	For additional sensing of the piston position, can be ordered optionally, only in conjunction with the order code A in the drive's modular product system	ddpc				
[9]	Measured-value transducer DADE	Converts the sensor signal of the cylinder to a voltage signal of 0 10 V and/or a current signal of 4 20 mA	14				
[10]	Push-in fitting QS	For connecting tubing with standard O.D.	qs				

1) Guide unit FENG-KF must be attached to the piston rod so that backlash is eliminated

Data sheet



www.festo.com

- **O** - Diameter 80 and 100 mm

- Stroke length 10 ... 1250 mm



General technical data

Piston Ø		80	100		
Based on standard		ISO 15552			
Design		Piston			
		Piston rod			
		Profile barrel			
Mode of operation		Double-acting			
Guide ¹⁾		Guide rod with yoke, with ball bearing guide			
Protection against rotation		Square piston rod			
Mounting position	Mounting position		Any		
Type of mounting		Via accessories			
Cushioning		Elastic cushioning rings/pads at both ends			
Position sensing		Integrated displacement encoder			
		Via proximity switch ²⁾			
Measuring principle (displacement encoder)		Encoder, contactless and relative measurement			
Pneumatic connection		G3/8	G1/2		
Stroke					
DDPC	[mm]	10 1250			
DDPCD	[mm]	100 500			
Extended piston rod	[mm]	1 500			

1) Guide unit FENG-KF can be ordered via the modular product system (feature D) and is supplied attached. The maximum stroke is restricted.

2) Not included in the scope of delivery, can be ordered as an option

Operating and environmental conditions

-1		
Operating pressure	[bar]	412
Operating pressure ¹⁾	[bar]	48
Operating medium ²⁾		Compressed air to ISO 8573-1:2010 [6:4:4]
Note on the operating/pilot medium		Lubricated operation not possible
		Pressure dew point 10°C below ambient/medium temperature
Ambient temperature ³⁾	[°C]	-20+80
Vibration resistance to DIN/IEC 68, Part 2-6		Severity level 2
Continuous shock resistance to DIN/IEC 68, Part 2	2 - 82	Severity level 2
CE marking (see declaration of conformity) ⁴⁾		To EU EMC Directive
Corrosion resistance class CRC ⁵⁾		1

1) Only applies to applications with end-position controller CPX-CMPX, SPC11 and axis controller CPX-CMAX

2) The proportional directional control valve VPWP, MPYE used requires these characteristic values

3) Note operating range of proximity switches

4) For information about the area of use, see the EC declaration of conformity: www.festo.com/sp \rightarrow Certificates.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

5) Corrosion resistance class CRC 1 to Festo standard FN 940070 Low corrosion stress. Dry indoor application or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions). 1

Data sheet

Forces [N] and impact energy [Nm]						
Piston Ø	i	80		100		
Theoretical force at 6 bar, advancing		3016		4712	2	
Theoretical force at 6 bar, retracting		2721		4418	3	
Impact energy at the end positions		1.8		2.5		
Permissible impact velocity:	$v = \sqrt{\frac{2 \cdot E}{m_1 + r}}$	n ₂	v E m ₁	Permissible impact velo Max. impact energy Moving mass (drive)	- 📕 The	 Note se specifications represent the kimum values that can be
Maximum permissible mass:	$m_2 = \frac{2 \cdot E}{v^2} - $	m_1	m ₂	Moving payload	ach	ieved. The maximum permissible act energy must be observed.

Electrical data – Displacement encoder

Output signal		Analogue
Linearity error		
Strokes up to 500 mm	[mm]	< ±0.08
Strokes up to 1000 mm	[mm]	< ±0.09
Strokes over 1000 mm	[mm]	<±0.11
Resolution ¹⁾	[%]	≤ 0.025
Repetition accuracy		
≤ 400	[mm]	±0.1
≤ 500	[mm]	±0.13
≤ 750	[mm]	±0.19
≤ 1200	[mm]	±0.3
≤ 1250	[mm]	±0.4
Max. speed of travel	[m/s]	1.5
Degree of protection		IP65
CE marking (see declaration of conformity) ²⁾		To EU EMC Directive
Max. permitted magnetic interference field ³⁾	[kA/m]	10
Electrical connection		Cable with 8-pin plug, round design, M12
Cable length	[m]	1.5

1) Always refers to max. stroke

2) For information about the area of use, see the EC declaration of conformity: www.festo.com/sp \rightarrow Certificates.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

3) At a distance of 100 mm

Pin allocation for the plug



Pin	Function	Colour
1	5 V	Black
2	GND	Brown
3	sin+	Red
4	sin-	Orange
5	COS-	Green
6	COS+	Yellow
7	Shielding	Shielding
8	n.c.	-

Weight [g]		
Piston Ø	80	100
DDPC		
Basic weight with 0 mm stroke	3053	4330
Additional weight per 10 mm stroke	87	95
Moving mass with 0 mm stroke	804	994
Additional weight per 10 mm stroke	31	31
DDPCT – Through piston rod		
Basic weight with 0 mm stroke	3537	5019
Additional weight per 10 mm stroke	127	134
Moving mass with 0 mm stroke	1247	1467
Additional weight per 10 mm stroke	70	70
DDPCE – Additional weight with piston rod ext	ension	
Additional weight per 10 mm extension	31	31
DDPCC – Additional weight with clamping unit		
Additional weight	2046	2829
DDPCD – Additional weight with guide unit		
Basic weight with 0 mm stroke	10430	12990
Additional weight per 10 mm stroke	80	80

Materials



Stan	andards-based cylinder				
[1]	Cover	Wrought aluminium alloy			
[2]	Piston rod	High-alloy steel			
[3]	Cylinder barrel	Wrought aluminium alloy			
-	Seals	NBR, polyurethane			
	Note on materials	Free of copper and PTFE			
		RoHS-compliant			

Torques and lateral forces

Max. torque for protection against rotation: Dynamic ≤ 3 Nm Static ≤ 5 Nm An external guide unit FENG-KF is recommended with higher torque loads. The guide unit is supplied attached. The permissible static and dynamic characteristic load values with and without attached guide

 \rightarrow Internet: feng



DDPC

А

Mounting conditions

When mounting a drive A with magnet (for position sensing) next to a standards-based cylinder DDPC, the following conditions must be observed:

- X Minimum distance between the drives
- Y Offset between the drives on the bearing cap

Parallel assembly

The drives can be mounted directly next to one another if the offset Y = 0 mm.



If the offset Y > 0 mm and the cable outlet is between the drives, a distance of X > 70 mm must be observed.



Offset mounting, cable outlet upwards or downwards

If the offset is Y > 0 mm and the cable outlet is up or down, a distance of X > 60 mm must be observed.



Data sheet





[mm]	max.	Ø f9				
80	500	48	G1/8	165.5	95	31.5
100	500	48	G1/8	174	98	31
ø	VD	WH	Zj		ZM	
[mm]			DDPCT	DDPCCT	DDPCT	DDPCCT
80	16.7	46	174	269	222	317
100	20.5	51	189	287	240	338



Compensating coupling [2]

[3] Customers can drill additional mounting holes here as required

+ = plus stroke length

ø	B1	B2	B3	B4	D1	D2	D3	D4	D6
					ø		ø	ø	ø
[mm]	-0.3		±0.2	±0.6					h6
80	105	100	148	106	78	M10	18	11	25
100	130	120	172	131	78	M10	18	11	25
		1			1				
Ø	H1	H2	H3	H4	КК	L1	L2	L3	L4
[mm]	-0.5		±0.2	±0.2			+10		
80	189	180	130	130	M20x1.5	258	111	194	215
100	213	200	150	150	M20x1.5	263	116	138	220
ø	L5	L6	L9	L10	L11	L12	L13	L14	=© 1
[mm]						±0.2			
80	40	128	32	20	21	72	11	20	27
100	40	128	32	20	24.5	89	11	20	27

Ordering data – Modular product system

Order	ing	tab	le

Ordering table						
Piston Ø		80	100	Conditions	Code	Enter cod
Module no.		1677705	1691433			
Function		Standards-based cylinder with in	Standards-based cylinder with integrated displacement encoder		DDPC	DDPC
Protection against rotation		With protection against rotation			-Q	-Q
Piston Ø	[mm]	80	100			
Stroke	[mm]	10 1250				
Guide unit		None				
		Attached			-D	
Clamping unit		None				
		Attached		[1]	-C	
Piston rod		At one end				
		Through piston rod			T	
Cushioning		Elastic cushioning rings/pads at both ends			-Р	-P
Position sensing		Via proximity switch			Α	А
Piston rod extension		None				
	[mm]	1 500			E	

[1] C Only available with T

Data sheet

Measured-value transducer DADE-MVC-010 DADE-MVC-420 The measured-value transducer converts sensor signals of the standards-based cylinder DDPC into a voltage signal of 0 ... 10 V and/or a current signal of 4 ... 20 mA. These signals can be evaluated by a PLC with an appropriate signal input.



General technical data

Type of mounting	With through-hole
Mounting position	Any
Short circuit current rating	Yes
Reverse polarity protection	Yes
Diagnostic function	Display via LED

General electrical data

Analogue output	[V]	0 10 (as per EN 61131-2)
	[mA]	4 20 (as per EN 61131-2)
Nominal operating voltage	[V DC]	24 ±25%
Residual ripple	[%]	4 (at 50 Hz)
Current consumption at nominal operating	[mA]	20 30
voltage		
Switching logic at outputs		PNP
Switching logic at inputs		PNP
Debounce time at inputs	[ms]	3
Linearity error FS		0.2%

Operating and environmental conditions

[°C]	055		
	IP65		
	95% non-condensing		
	To EU EMC Directive		
	To EU RoHS Directive		
	KC EMC		
	1		
[g]	128		
	Polybutylene terephthalate		

1) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. Dry indoor application or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

Data sheet





Pin	Function	Cable colour
1	24 V	White
2	Analogue measurement signal	Brown
3	Reference output	Green
4	0 V measurement signal	Yellow
5	Reference input	Grey
6	Calibration input	Pink
7	Ready output	Blue
8	0 V power supply and inputs/outputs	Red

Magguring	custom	interface
Measuring	System	interface



Pin	Function
1	Ub
2	0 V
3	Signal sine +
4	Signal sine -
5	Signal cosine -
6	Signal cosine +
7	Screening / earth
8	-

Ordering data				
		Description	Part no.	Туре
Measured-value transd	ucer			
	With voltage signal	0 10 V	542117	DADE-MVC-010
	With current signal	4 20 mA	542118	DADE-MVC-420
Accessories				Data sheets → Internet: sim
O THE S	Connecting cable	PLC connecting cable (length 2 m)	525616	SIM-M12-8GD-2-PU
		PLC connecting cable (length 5 m)	525618	SIM-M12-8GD-5-PU
			·	