


Clamping modules EV

FESTO




Product range overview


Function	Version	Type	Clamping area [mm]	Stroke [mm]
Single-acting	Clamping module, rectangular			
		EV	10x30	3
			15x40	4
			15x63	4
			20x75	5
			20x120	5
			20x180	5
	Clamping module, round			
		EV	Ø 12	3
			Ø 16	4
			Ø 20	4
			Ø 25	4
			Ø 32	5
			Ø 40	5
			Ø 50	5
			Ø 63	5

Examples of applications and installations


Clamping module, rectangular



Clamping module, round



Peripherals overview and type codes




Mounting components and accessories		Description	Clamping module, rectangular	Clamping module, round	→ Page/Internet
[1]	Foot mounting HBEV	For horizontal clamping direction	■	—	8
[2]	Pressure plate, rectangular EV-...-DP	Protects the diaphragm against external damage	■	—	8
[3]	Pressure plate, round EV-...-DP	Protects the diaphragm against external damage	—	■	9
[4]	Push-in fitting QS	For connecting compressed air tubing with standard O.D.	■	■	qs

Type codes

001	Series		003	Stroke	
EV	Clamping module, single-acting		3	3	
			4	4	
			5	5	

002	Clamping area	
12	Ø12	
16	Ø16	
20	Ø20	
25	Ø25	
32	Ø32	
40	Ø40	
50	Ø50	
63	Ø63	
1030	10x30 mm	
1540	15x40 mm	
1563	15x63 mm	
2075	20x75 mm	
20120	20x120 mm	
20180	20x180 mm	


Data sheet



- Ø - Diameter
Clamping module,
rectangular:
approx. Ø 20 ... 68 mm
Clamping module, round:
12 ... 63 mm

- | - Stroke length
3 ... 5 mm

 www.festo.com



General technical data – Clamping module, rectangular

Clamping area	10x30	15x40	15x63	20x75	20x120	20x180
Pneumatic connection	M3	M5				
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]					
Design	Diaphragm					
Cushioning	None					
Position sensing	None					
Type of mounting	With through-hole					
	With accessories					
Mounting position	Any					

General technical data – Clamping module, round

Clamping area Ø	12	16	20	25	32	40	50	63
Pneumatic connection	M3							
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]							
Design	Diaphragm							
Cushioning	None							
Position sensing	None							
Type of mounting	With through-hole							
Mounting position	Any							

Operating conditions – Clamping module, rectangular

Clamping area	10x30	15x40	15x63	20x75	20x120	20x180
Operating pressure [bar]	≤ 6	2 ... 6				
Ambient temperature [°C]	-20 ... +40					

Operating conditions – Clamping module, round

Clamping area Ø	12	16	20	25	32	40	50	63
Operating pressure [bar]	≤ 6							
Ambient temperature [°C]	-10 ... +40							

Data sheet

Forces [N] – Clamping module, rectangular						
Clamping area	10x30	15x40	15x63	20x75	20x120	20x180
Clamping force at 6 bar, stroke 1 mm	95	195	350	660	1100	1690
Clamping force at 6 bar, maximum stroke	80	165	290	600	1000	1480

Forces [N] – Clamping module, round								
Clamping area $\varnothing$	12	16	20	25	32	40	50	63
Clamping force at 6 bar, stroke 1 mm	55	102	162	226	376	680	1090	1660
Clamping force at 6 bar, maximum stroke	56	125	187	271	456	675	1075	1640

**Note**


Only operate the clamping module with a counter-stop.

Weights [g] – Clamping module, rectangular						
Clamping area	10x30	15x40	15x63	20x75	20x120	20x180
Product weight	20	45	65	130	190	270

Weights [g] – Clamping module, round								
Clamping area $\varnothing$	12	16	20	25	32	40	50	63
Product weight	11	15	19	24	34	52	68	100

Materials

Sectional view




Clamping module	
[1] Housing	Aluminium
[2] Diaphragm	Polyurethane
– Note on materials	Free of copper and PTFE
	RoHS-compliant

Data sheet

Dimensions

Download CAD data → www.festo.com

Clamping module, rectangular



- [1] Maximum permissible stroke against a stop
- [2] Choice of supply port connection by repositioning sealing plug
- [3] Clamping area


Clamping area	B1	B2	B3	D1 Ø	E1	H1	H2	H3	H7	L1	L2	L3	L4	T1
[mm]														
10x30	17	9	3	3.3	M3	14.5 ^{+0.3}	12.5	3	3	45	13.5	37	16	4.6
15x40	23	15.5	4.9	4.3	M5	18 ^{±0.54}	16	4	4.8	55	13	47	25	3
15x63										80	13	72	50	3
20x75	33	23	9.5	5.3	M5	21.5 ^{±0.57}	19.5	5	4.8	98	18.9	88	55	5.2
20x120										144	18.9	134	103	5.2
20x180										204	18.9	194	161	5.2

Data sheet

Dimensions

Download CAD data → www.festo.com

Clamping module, round



- [1] Maximum permissible stroke
against a stop
- [2] Clamping area

Clamping area Ø [mm]	B1	B2	B3	D1 Ø	D2 Ø	D3	D4 Ø	D5 Ø	H1	H2	H3	H4	L1	L2
12	29	16.5	13	3.5	2	M3	6.5	3	10.5	3	4	3.5	25	18
16	33	18.5	15	3.5	2	M3	6.5	7	10.5	4	4	3.5	29	22
20	37	20.5	16.5	4.5	2	M3	6.5	11	10.5	4	4	3.5	33	25
25	42	23	18.5	5.5	2	M3	6.5	16	10.5	4	4	3.5	38	28
32	49	26.5	21	5.5	2	M3	6.5	23	10.5	5	4	3.5	45	34
40	57	30.5	25	5.5	2	M3	6.5	31	10.5	5	4	2.5	53	42
50	67	35.5	29	5.5	2	M3	6.5	41	10.5	5	4	2.5	63	49
63	80	42	34	5.5	2	M3	6.5	54	10.5	5	4	2.5	76	60

Ordering data – Clamping module, rectangular

Clamping area [mm]	Stroke [mm]	Part no.	Type
10x30	3	151993	EV-1 0/30-3
15x40	4	13289	EV-1 5/40-4
15x63	4	13290	EV-1 5/63-4
20x75	5	13291	EV-2 0/75-5
20x120	5	13292	EV-2 0/120-5
20x180	5	13293	EV-2 0/180-5


Ordering data – Clamping module, round

Clamping area Ø [mm]	Stroke [mm]	Part no.	Type
12	3	150681	EV-12-3
16	4	150682	EV-16-4
20	4	150683	EV-20-4
25	4	150684	EV-25-4
32	5	150685	EV-32-5
40	5	184857	EV-40-5
50	5	184858	EV-50-5
63	5	184859	EV-63-5

Accessories

Foot mounting HBEV
for clamping module, rectangular

Material:
Wrought aluminium alloy




[1] Clamping module EV
[2] Clamping direction

Dimensions and ordering data

For clamping area	B1	B2	D1 Ø	D2 Ø	D3	H1	L1	L2	L3	L4	L5	T1	Part no.	Type
10x30	20	9	4.5	8	M3	10	45	23	37	–	22.5	4.6	152512	HBEV-1 0/30
15x40	25	15.5	5.4	11	M 4	15	55	29	47	–	27.5	7	34562	HBEV-1 5/40
15x63							80	50	72	–	40	7	34563	HBEV-1 5/63
20x75	36	23	6.4	13	M5	16	98	64	88	–	49	9	34564	HBEV-2 0/75
20x120							144	110	134	–	72	9	34565	HBEV-2 0/120
20x180							204	170	194	60	102	9	34566	HBEV-2 0/180

Pressure plate EV- ...-DP
for clamping module, rectangular

Material:
Steel



[4] The pressure plate can be snap-fitted onto the diaphragm of the clamping module.

Dimensions and ordering data

For clamping area	H4	H5	H6	L5	KBK ¹⁾	Part no.	Type
10x30	17	5	2.5	19	2	151994	EV-1 0/30-DP
15x40	20.5	5.6	2.5	29	2	13783	EV-1 5/40-DP
15x63				54	2	13784	EV-1 5/63-DP
20x75	24.5	6.6	3	63	2	13785	EV-2 0/75-DP
20x120				109	2	13786	EV-2 0/120-DP
20x180				169	2	13787	EV-2 0/180-DP


1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Accessories

Pressure plate EV- ...-DP for clamping module, round

Material:
Steel



[3] The pressure plate can be snap-fitted into the diaphragm of the clamping module by using gentle pressure together with a twisting movement.

Dimensions and ordering data					
For clamping area Ø	D6 Ø	H5	KBK ¹⁾	Part no.	Type
12	11	1.5	2	150690	EV-12-DP
16	15	1.5	2	150691	EV-16-DP
20	19	1.5	2	150692	EV-20-DP
25	24	1.5	2	150693	EV-25-DP
32	31	1.5	2	150694	EV-32-DP
40	39	1.6	2	184860	EV-40-DP
50	49	1.6	2	184861	EV-50-DP
63	62	1.6	2	184862	EV-63-DP

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia

