



Characteristics

At a glance

- The clamping cartridges/units use spring force to hold round material in any required position.
- They can stop and hold material for long periods, even in applications with varying loads, fluctuating operating pressure and system leaks.
- The clamping force is released by pressurising the clamping cartridge.
- The clamping cartridges/units can be mounted in any position.
- Clamping cartridges/units are not suitable for positioning.
- The clamping cartridge KP and the clamping units KPE, KEC, KEC-S are standalone components.
- Cylinders with integrated clamping unit
- ADNKP
- DSNU-...-KP
- DSBC-...-C
- DNCKE/DNCKE-S

- Zero backlash in clamped condition with varying loads on the piston rod:
 - Clamping cartridge/unit KP/KPE: no
 - Clamping unit
 - KEC/KECS: yes

Selection aid

Clamping cartridge KP

- KP
- -

- For in-house assembly of clamping units
- Not certified for use in safety-related control systems

→ Page 6



application):

operations

- Ready-to-install combination of clamping cartridge KP and housing
- Wide range of mounting options
 → 9
- Not certified for use in safety-related control systems

• Mounting hole pattern to ISO 15552

• Not certified for use in safety-related

(DIN ISO 6431)

control systems

Clamping unit KEC



Clamping unit KEC-...-S, for safety-related applications



- Pneumatic braking/holding device for use in safety-related parts of control systems.
 The clamping unit is not a complete safety solution, but it can be used as part of a solution.
- Certified by the Institute for Occupational Safety and Health of the German Social Accident Insurance (DGUV). Testing and certification body in DGUV Test (IFA). Pneumatic braking/holding device with safety function.
- For use as a holding device (static application):

• For use as a holding device (static

 Holding and clamping in the event of power failure

 Protection against pressure failure and pressure drop
 Securing the piston rod during intermediate stops for process

- Holding and clamping in the event of power failure
- Protection against pressure failure and pressure drop
- Securing the piston rod during intermediate stops for process operations
- For use as a braking device (dynamic application):
 - Braking or stopping a movement
 - Suspension of a movement if a danger zone is entered
- Mounting hole pattern to ISO 15552 (DIN ISO 6431)
- When used as a braking device, the overtravel must be checked regularly

→ Page 12

→ Page 8

→ Page 10

- Suitable for use in safety-related parts of control systems belonging to category 1 to EN ISO 13849-1 (tried-and-tested component). Additional control measures are required for use in higher categories.
- Products intended for use in safety-related applications must be selected, sized and arranged in accordance with valid standards and regulations.

exceed the static holding force.

Characteristics

Requirements for the round material t In combination with clamping cartridge			
 Material: Hard-chrome-plated steel Hardened steel Rolled steel:	 Diameter tolerance: h8 Surface roughness: R_{max.} = 4 μm 	• The specified holding forces refer to a static load. If these values are exceeded, slippage may occur.	 Clamping cartridge KP and clamping unit KPE are not suitable for dynamic operation.
In combination with clamping unit KEC			
 Material: Hard-chrome-plated steel: layer thickness min. 20 µm Hardened steel: min. HRC 60 	 Diameter tolerance: h7 f7 Surface roughness: R_{max.} = 4 μm 	• The specified holding forces refer to a static load. If these values are exceeded, slippage may occur.	 Clamping unit KEC is not suitable for dynamic operation. For clamping unit KEC-S, the following applies: dynamic forces occurring during operation must not

Type codes

001	Series	
КР	Clamping cartridge	
002	Piston rod diameter [mm]	_
4	4	
6	6	
8	8	
10	10	
12	12	
16	16	
20	20	
25	25	
32	32	

003	Static holding force	
80	80	
180	180	
350	350	
600	600	
1000	1000	
1400	1400	
2000	2000	
5000	5000	
7500	7500	

Type codes

001	Series						
KPE	Clamping unit						
KEC	Clamping unit						
002	Piston rod diameter [mm]						
4	4						
6	6						
8	8						
10	10						
12	12						
16	16						
20	20						
25	25						
32	32						

003	Certification	
	None	
S	Safety device to Machinery Directive 2006/42/EC	

Clamping cartridges KP

Data sheet





- 🖡 - Note

Additional measures are required for use in safety-related applications; in Europe, for example, the standards listed under the EC Machinery Directive must be observed. Without additional measures in accordance with statutory minimum requirements, the product is not suitable as a safety-related part of control systems.

General technical data

For round material diameter		4	6	8	10	12	16	20		25	32
Pneumatic connection		M5					G1/8				
Design		Tilting plates									
Type of mounting		Via self-configured housing									
Type of clamping with active direction	rpe of clamping with active direction At both ends										
		Clamping via	spring force,	compressed ai	r to release						
Static holding force	[N]	80	180	350	350	600	1000	1400	2000	5000	7500
Axial play under load	[mm]	0.2	0.3		0.5			0.8			1.8
Min. release pressure	[MPa]	0.3									
	[bar]	3									
Mounting position		Any									
Product weight	[g]	10	15	50	50	50	90	170	170	700	1600

Operating and environmental conditions

Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[bar]	≤ 10
Ambient temperature	[°C]	-10 +80
Corrosion resistance CRC ¹⁾		2

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Materials

Sectional view



Clam	Clamping cartridge					
[1]	Housing	Anodised aluminium				
[2]	Clamping jaws	Brass				
[3]	Spring	Spring steel				
[4]	Piston	РОМ				
-	Seals	NBR, TPE-U(PU)				

Clamping cartridges KP

Data sheet

Dimensions and ordering data





Download CAD data \rightarrow <u>www.festo.com</u>

- 🌡 - Note

When installing the clamping cartridge in a housing, plain bearings must be installed on both sides of this housing.

For diam.	D1	D2	D3	D4	D5	E1	н	1	H2
	ø	ø	Ø	ø	ø				
[mm]		h12	f9	D9					
4	4	10	12	12	11	M5	2	8	7
6	6	14	16	16	15	M5	3	5	10
8	8	18	20	20	19	M5	6	2	17.5
10	10	18	20	20	19	M5	6	2	17.5
12	12	18	20	20	19	M5	6	2	17.5
16	16	22	24	24	23	G1/8	8	3	22
20	20	28	30	30	29	G1/8	10	00	25
	20	36	38	38	37	G1/8	11	5.5	30
25	25	46	48	48	47	G1/8	1	55	36
32	32	63	65	65	64	G1/8	19	95	55
For diam.	H3	H4	H5		H6	Weight	Part no.	Туре	
[mm]		min.	min.			[g]			
4	2	9				101			
6			7.5		6	10	178452	KP-4-80)
	3	10	7.5		6 8		178452 178453	KP-4-80 KP-6-18	
8	3	-				10			0
		10	11	; ;	8	10 15	178453	KP-6-18	0 0
10	3	10 18	11		8 15.5	10 15 50	178453 178454	KP-6-18 KP-8-35	0 0 50
10 12	3	10 18 18	11 18.5 18.5		8 15.5 15.5	10 15 50 50	178453 178454 178455	KP-6-18 KP-8-35 KP-10-3	0 0 50 00
8 10 12 16 20	3 3 3	10 18 18 18 18	11 18.5 18.5 18.5		8 15.5 15.5 15.5	10 15 50 50 50	178453 178454 178455 178456	KP-6-18 KP-8-35 KP-10-3 KP-12-6	0 0 50 00 000
10 12 16	3 3 3 3	10 18 18 18 18 22	11 18.5 18.5 18.5 23		8 15.5 15.5 15.5 20	10 15 50 50 50 90	178453 178454 178455 178456 178457	KP-6-18 KP-8-35 KP-10-3 KP-12-6 KP-16-1	0 0 50 00 000 400
10 12 16	3 3 3 3 3 3	10 18 18 18 22 25	11 18.5 18.5 18.5 23 26		8 15.5 15.5 15.5 20 23	10 15 50 50 50 90 170	178453 178454 178455 178456 178456 178457 178458	KP-6-18 KP-8-35 KP-10-3 KP-12-6 KP-16-1 KP-20-1	0 0 50 00 000 400 000

Clamping units KPE

Data sheet





- Note

-

Additional measures are required for use in safety-related applications; in Europe, for example, the standards listed under the EC Machinery Directive must be observed. Without additional measures in accordance with statutory minimum requirements, the product is not suitable as a safety-related part of control systems.

General technical data

For round material diameter		4	6	8	10	12	16	20	25	32
Pneumatic connection		M5 G1/8								
Design		Tilting plates								
Type of mounting		With mountin	g thread							
		With through-	hole							
Type of clamping with active direc	of clamping with active direction At both ends									
		Clamping via	spring force, con	npressed air to r	elease					
Static holding force	[N]	80	180	350	350	600	1000	2000	5000	7500
Axial play under load	[mm]	0.2	0.3		0.5	•		0.8		1.8
Min. release pressure	[MPa]	0.3								
[bar]		3	3							
Mounting position		Any								
Product weight	[g]	100	150	240	260	270	410	930	2000	4600

Operating and environmental conditions

- F		
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[bar]	≤10
Ambient temperature	[°C]	-10+80
Corrosion resistance CRC ¹⁾		2

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Materials



Clamping unit

[1]	Retaining bracket	Anodised aluminium
[2]	Clamping jaws	Brass
[3]	Spring	Spring steel
[4]	Piston	POM
-	Seals	NBR, TPE-U(PU)

I

Data sheet

Mounting options

With mounting thread





With through-hole



For round material diameter 8 ... 32 mm



Download CAD data → <u>www.festo.com</u>

Dimensions and ordering data For round material diameter 4 ... 6 mm





.



For diam.	B1	B2	B3	D1	D2	D3	D4	D5	D6	D7	D8	E1	H1	H2
				Ø	ø	Ø			ø	Ø	ø			
[mm]										d11				
4	27	19.5	12	4	-	12	-	M5	4.2	12	4.5	M5	34.5	13.5
6	32	24	16	6	-	16	-	M5	4.2	16	4.5	M5	41	16
8	36	27	20	8	4.2	20	M5	M5	4.2	22	-	M5	62.5	18
10	36	27	20	10	4.2	20	M5	M5	4.2	22	-	M5	62.5	18
12	40	28	20	12	5.2	20	M6	M6	5.2	28	-	M5	64.5	20
16	45	32.5	25	16	5.2	24	M6	M6	5.2	32	-	G1/8	83.5	22.5
20	65	50	38	20	6.5	38	M8	M8	6.5	45	-	G1/8	118	32.5
25	88	65	50	25	8.5	48	M10	M10	8.5	55	-	G1/8	163	44
32	118	90	70	32	10.3	65	M12	M12	10.3	60	-	G1/8	199	59
For diam.	H3	L1		L2	L3	L4	1	[1	T2	Weight	Part no.	Ty	ype	
[mm]										[g]				
4	19.5	33	3	7.5	18	-		9	11	100	1784	62 K	PE-4	
6	24	4	5	10	25	-		9	11	150	1784	63 K	PE-6	
0	0.7			4.0	2.2					2/2	4 - 0 /		DF 0	

6	24	45	10	25	-	9	11	150	178463	KPE-6
8	27	58	10	38	20	10	11	240	178464	KPE-8
10	27	62	12	38	20	10	11	260	178465	KPE-10
12	28	65	11	43	22	12	12	270	178466	KPE-12
16	32.5	69	12.5	44	22	12	12	410	178467	KPE-16
20	50	83	12.5	58	30	16	16	930	178468	KPE-20
25	65	100	15	70	34	20	20	2000	178469	KPE-25
32	90	154	25	104	60	24	24	4600	178470	KPE-32

Clamping units KEC

Data sheet





Note

_

Additional measures are required for use in safety-related applications; in Europe, for example, the standards listed under the EC Machinery Directive must be observed. Without additional measures in accordance with statutory minimum requirements, the product is not suitable as a safety-related part of control systems.

1

General technical data

ocherat technicat auta										
For round material diameter		16	25							
Pneumatic connection		G1/8	G1/8 G1/4 G3/8							
Type of mounting		With female thread								
		With accessory → page 14								
Type of clamping with active dir	rection	At both ends								
		Clamping via spring force, compressed	air to release							
Static holding force		1300	3200	8000						
Min. release pressure	[MPa]	0.38								
	[bar]	3.8								
Mounting position		Any								
Product weight	[g]	1860	4515	16760						

Operating and environmental conditions

	Compressed air to ISO 8573-1:2010 [7:4:4]
	Lubricated operation possible (in which case lubricated operation will always be required)
[bar]	3.8 10
[°C]	-20+80
	Selected types → www.festo.com
	h7 f7
	Hardened (min. HRC 60) or hard-chrome-plated (layer thickness min. 20 µm)
	Surface roughness Rmax. = 4 µm
	3 mm wide 15° chamfer on the end of the round material
	[bar]

- 📲 - Note

The specified holding force refers to a static load. If this value is exceeded, slippage may occur. Dynamic forces occurring during operation must not exceed the static holding force if slippage is to be avoided. The clamping unit is backlash-free in the clamped condition when varying loads are applied to the piston rod. Lateral loads and bending moments on the round material can impair the function. (Make sure that the load on the round material is only in the direction of movement.)

Actuation:

The clamping unit may only be released when the forces on the round material are balanced out. Otherwise there is a risk of accidents due to the sudden movement of the round material. Blocking off the compressed air supply at both ends (e.g. with a 5/3-way valve) does not provide any safety.

Data sheet





Dimensions and ordering data





Clamping unit [1]

[2]

[3]

[4]

Housing

Spring

Piston

Seals

Clamping jaws

Download CAD data → <u>www.festo.com</u>

-Note -

Wrought aluminium alloy

Wrought aluminium alloy NBR, TPE-U(PU)

Tool steel

High-alloy steel

The clamping unit can only be exhausted when it contains round material.

- [2] Round material to be clamped
- [3] Locking screw

For diam. [mm]	B Ø f8	BG	BG1	E	E1	EE	G	G1	L1	L2	MM Ø f7-h7
16	35	15	15	54	53	G1/8	27	22	178	160	16
20	45	14	17	80	79	G1/4	30	29.5	208.5	187	20
25	55	17	17	126	126	G3/8	32.5	32.5	287	258	25
For diam. [mm]	PL	RT	TG	VA	VD	- ©1	= ©2	Weight [g]	Part no.	Туре	
16	13	M6	38	5.5	18	30	6	1860	527492	KEC-16	
20	15.5	M8	56.5	6	21.5	36	8	4515	527493	KEC-20	
25	17	M10	89	7	29	41	10	15600	527494	KEC-25	

Clamping units KEC-...-S

Data sheet



bar]	10
°C]	-10+60
	h7f7
	Hardened (min. HRC 60) or hard-chrome-plated (layer thickness min. 20 µm)
	Surface roughness Rmax. = 4 µm
	3 mm wide 15° chamfer on the end of the round material
_	C]

- 🕴 - Note

The specified holding force refers to a static load. If this value is exceeded, slippage may occur. Dynamic forces occurring during operation must not exceed the static holding force if slippage is to be avoided. The clamping unit is backlash-free in the clamped condition when varying loads are applied to the piston rod. Lateral loads and bending moments on the round material can impair the function. (Make sure that the load on the round material is only in the direction of movement.)

Actuation:

The clamping unit may only be released when the forces on the round material are balanced out. Otherwise there is a risk of accidents due to the sudden movement of the round material. Blocking off the compressed air supply at both ends (e.g. with a 5/3-way valve) does not provide any safety.

Safety data

Safety function	Stopping a linear movement
Performance Level (PL)	Cat. 1, PLc
Certificate issuing authority	IFA 1504155
CE marking (see declaration of conformity)	To EU Machinery Directive

Data sheet



Dimensions and ordering data

KEC-S – for safety-related control systems



Clamping unit

	*	
[1]	Housing	Wrought aluminium alloy
[2]	Clamping jaws	Tool steel
[3]	Spring	High-alloy steel
[4]	Piston	Wrought aluminium alloy
-	Seals	NBR, TPE-U(PU)

Download CAD data → <u>www.festo.com</u>

- 🚪 - Note

The clamping unit can only be exhausted when it contains round material.

KEC-25-S

538244

- [2] Round material
 - to be clamped
- [3] Locking screw

For diam. [mm]	B Ø f8	BG	BG1	E	E1	EE	G	G1	L1	L2	MM Ø f7-h7
16	35	15	15	54	53	G1/8	27	22	178	160	16
20	45	14	17	80	79	G1/4	30	29.5	208.5	187	20
25	55	17	17	126	126	G3/8	32.5	32.5	287	258	25
For diam. [mm]	PL	RT	TG	VA	VD	=©1	≕ ©2	Weight [g]	Part no.	Туре	
16	13	M6	38	5.5	18	30	6	1860	538242	KEC-16-S	
20	15.5	M8	56.5	6	21.5	36	8	4515	538243	KFC-20-S	

29

- 🖡 - Note

17

25

The overtravel is the distance that the piston rod covers between exhausting of the clamping unit and coming to a standstill. It must be determined by the customer when the machine is being set up. When the clamping unit is used as a braking device, an increase in the overtravel as a function of the load and the frequency of braking (wear) must be expected. The clamping unit KEC-S can be used in safety-related parts of control systems belonging to category 1 (tried-and-tested component) as defined by EN ISO 13849-1. For use in higher categories than category 1 to EN ISO 13849-1, the overtravel must be achieved even in the event of faults.

89

M10

The overtravel is dependent on the ambient conditions and

15600

stress, e.g.:

41

- Operating pressure
- Nominal size of the switching valveCable length

10

- Cable length
- Diameter of the connecting cable to the clamping unit
- Load and speed

The overtravel can be reduced by attaching a quick exhaust valve to the compressed air supply port of the clamping unit.

Clamping units

Accessories

Foot mounting HNC

Material: Galvanised steel Free of copper and PTFE







Dimensions and ordering data

For diam.	AB	AH	AO	AT	AU	SA	TR	US	XA	XS	CRC ¹⁾	Weight	Part no.	Туре
	Ø													
[mm]												[g]		
16	10	36	9	5	28	216	36	54	206	42	2	193	174370	HNC-40
20	10	50	12.5	6	32	251	50	75	240.5	48.5	2	436	174372	HNC-63
25	14.5	71	17.5	6	41	340	75	110	328	64	2	1009	174374	HNC-100

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Flange mounting FNC

Material: Galvanised steel Free of copper and PTFE





Dimensions and ordering data

For diam.	E	FB	MF	R	TF	UF	W	ZF	CRC ¹⁾	Weight	Part no.	Туре
		ø										
[mm]		H13								[g]		
16	54	9	10	36	72	90	8	188	1	291	174377	FNC-40
20	75	9	12	50	100	120	9.5	220.5	1	679	174379	FNC-63
25	110	14	16	75	150	175	13	303	1	2041	174381	FNC-100

1) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. Dry internal application or transport and storage protection. Also applies to parts behind coverings, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).