Spiral plastic tubing PUN-SG





Spiral plastic tubing PUN-SG

Characteristics

At a glance

Pre-assembled plastic tubing with rotatable threaded outlets for supplying compressed air tools.

- Polyurethane, nickel-plated brass, polyacetal
- Pre-assembled with non-detachable rotatable fittings
- Operating medium: compressed air, vacuum
- Highly resistant to microbes and hydrolysis

Diagrams

<u>سرا</u>

The diagrams shown in this document are also available online. These can be used to display precise values.

Pipe/tubing O.D. x wall thickness

For this spiral tubing, the outside diameter of the tubing and the wall thickness are specified as the tubing size.

Design

Extremely flexible and largely hydrolysis-resistant pneumatic tubing with fabric insert.

Working length [m]

The working length is 80% of the maximum permissible extension.

Further information \rightarrow pun-sg

Type code

001	Series	
PUN	Plastic tubing, polyurethane	
002	Pipe/tubing outside diameter [mm]	
10	10	
12	12	
003	Design	
SG	Spiral with fabric	

004	Working length [m]	
2,4	2.4	
4,8	4.8	
6	6	
005	Colour	
BL	Blue	
006	Pneumatic connection	
1/4	Male thread G1/4	
3/8	Male thread G3/8	

Spiral plastic tubing PUN-SG

Datasheet

General technical data			
Outside diameter	9.5	11.7	
Pneumatic connection, port 1	Male thread G1/4	Male thread G3/8	
Pneumatic connection, port 2	Male thread G1/4	Male thread G3/8	
Nominal torque	11 Nm	12.5 Nm	
Tolerance for nominal tighten-	± 20%		
ing torque			

Tube geometry						
Outside diameter	9.5			11.7		
Working length	2.4	4.8	6	4.8	6	
	6.4			7.9		
Inside diameter	6.4			7.9		
Inside diameter Winding diameter	6.4 42 mm			7.9 51 mm		

Operating and environmental conditions

Temperature-dependent oper- ating pressure	-0.95 15 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:]
Ambient temperature	-40 60°C
Corrosion resistance class CRC ¹⁾	1 - Low corrosion stress

1) More information: www.festo.com/x/topic/crc

Operating pressure p as a function of temperature t



Materials		
Shore hardness	A 87 +/-3	
Material tubing	TPE-U(PU)	
Material connecting thread	Brass, Nickel-plated	
Material buckling protection	РОМ	
Colour	Blue	
LABS (PWIS) conformity ¹⁾	VDMA24364-B1/B2-L	

1) Applies to PUN-H with O.D. 3 ... 16 mm and PUN-H-DUO

Ordering data

	Outside diameter	Working length	Block length	Product weight	Part no.	Туре
Company Company	9.5 mm	2.4 m	0.889 m	180 g	533463	PUN-10X1,5-SG-2,4-BL-1/4
		4.8 m	1.165 m	340 g	533464	PUN-10X1,5-SG-4,8-BL-1/4
		6 m	1.317 m	430 g	533465	PUN-10X1,5-SG-6-BL-1/4
	11.7 mm	4.8 m	1.172 m	480 g	533466	PUN-12X2-SG-4,8-BL-3/8
		6 m	1.312 m	560 g	533467	PUN-12X2-SG-6-BL-3/8
of any other states of the second						