

Standard Filters MS12N-LF – Inch Series

FESTO



Standard filters, with filtration grades of 5 microns or 40 microns, are equipped with a water separator that cleans the compressed air of impurities, rust, and condensate. For pre-filtering in pneumatic systems or for special applications.

- Pneumatic connection: 1 NPT, 1¼ NPT, 1½ NPT, 2 NPT
- Supply pressure
 - For manual drain: 12 ... 294 psi
 - For fully automatic drain: 29 ... 176 psi
 - For fully automatic drain, electrically actuated: 12 ... 235 psi
- Flow rate: 406.0 ... 564.8 scfm

Product Range Overview														
Type	Pneumatic connections	Filtration grade [µm]				Bowl guard	Bowl drain						Contamination control	Reverse flow
	Port plate	0.01	1	5	40	Metal bowl	Manual	Fully automatic	Electrical 24 V DC M12	Electrical 110 V AC with terminals	Electrical 230 V AC with terminals	Electrical 24 V DC with terminals	Differential pressure indicator	Flow direction from right to left
MS12N	AG...	A	B	C	E	U	M	V	E1	E2	E3	E4	DA	Z
LF	1 NPT, 1¼ NPT, 1½ NPT, 2 NPT	–	–	■	■	■	■	■	■	■	■	■	–	■

Features

- Sintered filter with centrifugal separation removes contamination, rust and condensate from the compressed air.
- High flow rate with minimal pressure drop
- Replaceable filter cartridges

Contents

Technical Data	➔ 1112
Dimensional Drawings	➔ 1115
Ordering Data	➔ 1116
Accessories	➔ 1118


➔ www.festo.com/catalog/ms12n-lf

Standard Filters MS12N-LF – Inch Series

Technical Data

FESTO

ISO Symbol



Manual bowl drain



Fully automatic bowl drain



General Technical Data					
Pneumatic connection 1, 2 ¹⁾		1 NPT	1¼ NPT	1½ NPT	2 NPT
Filtration grade	[µm]	5 (air purity class at the output 3.7.– to DIN ISO 8573-1)			
		40 (air purity class at the output 5.7.– to DIN ISO 8573-1)			
Supply pressure	M [psi]	12 ... 294 (manual drain)			
	V [psi]	29 ... 176 (fully automatic drain)			
	E... [psi]	12 ... 235 (fully automatic drain, electrically actuated)			

1) Dependent on port plate selected, must be ordered separately as an accessory → 1119

Standard Nominal Flow Rate qnN ²⁾ [scfm]					
Pneumatic connection 1, 2		1 NPT	1¼ NPT	1½ NPT	2 NPT
Filtration grade	5 µm	406.0	441.3	476.6	494.2
	40 µm	441.3	458.9	494.2	564.8

2) Dependent on port plate selected, must be ordered separately as an accessory → 1119
Measured at p₁ = 88 psi and Δp = 7.4 psi

Standard Filters MS12N-LF – Inch Series

Technical Data

FESTO

Operating and Environmental Conditions			
Bowl drain	Manual M	Fully automatic V	Fully automatic, electrically actuated E...
Operating medium	Compressed air, air quality class 5.7.– to DIN ISO 8573-1		
Max. condensate volume [in ³]	24.40		
Bowl guard	Metal bowl		
Ambient temperature [°F]	14 ... 140	41 ... 140	34 ... 140
Temperature of medium [°F]	14 ... 140	41 ... 140	34 ... 140
Storage temperature [°F]	14 ... 140	14 ... 140	34 ... 140
Assembly position	Vertical ±5°		
Corrosion resistance CRC ¹⁾	2		

1) Corrosion resistance class 2 according to Festo standard 940 070


Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [lb]	
With metal bowl	13.00
With metal bowl and fully automatic, electrically actuated bowl drain	14.40

- Filter cartridges → 1121
- For spare parts go to: www.festo.com/en/spare_parts_service

Materials

Sectional view





Filter		
1	Body	Die-cast aluminum
4	Metal bowl	Wrought aluminum alloy
5	Filter element	Sintered bronze
7	Spin disk	Polyacetate
8	Filter holder	Polyacetate
9	Separating plate	Polyacetate
10	Stabilizing disk	Polyacetate
–	Seals	Nitrile rubber

Standard Filters MS12N-LF – Inch Series



Technical Data

FESTO

Standard Flow Rate q_n as a Function of the Differential Pressure Δp_{1-2}		
Filtration grade 5 μm	With port plate MS12-AGF Pneumatic connection 1 NPT	With port plate MS12-AGI Pneumatic connection 2 NPT




Filtration grade 40 μm	With port plate MS12-AGF Pneumatic connection 1 NPT	With port plate MS12-AGI Pneumatic connection 2 NPT
-----------------------------------	--	--



Standard Filters MS12N-LF – Inch Series

Dimensional Drawings





B1	B2	B3	B4	D5 Ø	L1	L2	L4	L5	L6	≈C
4.88	4.80	2.40	5.83	1.57	18.03	3.39	6.54	9.84	0.63	1.97

1) Dimensions are in inches, unless otherwise noted.

Standard Filters MS12N-LF – Inch Series


Dimensional Drawings, Ordering Data – Pre-configured Products

FESTO

Dimensions ¹⁾ – Bowl Drain		Download CAD Data → www.festo.com/us/cad
Manual M		Fully automatic V
 Barbed fitting for plastic tubing PCN-4		 Barbed fitting for plastic tubing PCN-4

Type	L6
MS12-LF-...-M	0.43

Type	L6
MS12-LF-...-V	0.51

Fully automatic, electrically actuated E1 ... E4		Technical data PWEA → www.festo.com/catalog/pwea
		1 Variant E1 PWEA-AP-... with M12x1 plug, 5-pin for SIM-M12-5GD-... 2 Variant E2/E3/E4 PWEA-AC-... with cable conduit fitting Pg9 3 Connection 360° rotatable for plastic tubing PUN-H-12x2-...

1) Dimensions are in inches, unless otherwise noted.

Ordering Data					
Metal bowl					
Bowl drain	Connection	Filtration grade 5 µm			Filtration grade 40 µm
		Part No.	Type	LT	Part No. Type LT
Fully automatic	1 NPT ... 2 NPT ²⁾	537152	MS12-LF-G-CUV	1D	537151 MS12-LF-G-EUV 1D

LT = Lead time 1D typically ships same day/next day 1W typically ships within 1 week Q request a quote for lead time

2) Port plate must be ordered separately as an accessory → 1119

Standard Filters MS12N-LF – Inch Series

Ordering Data – Configurable Products



M Mandatory Data									O Options	
Part No.	Series	Size	Thread	Function	Connection size	Filtration grade	Bowl	Bowl drain	Type of mounting	Reverse flow direction
535026	MS	12	N	LF	AQT AQU AQV AQW G	E C	U	M V E1 E2 E3 E4	WP	Z
Order example										
535026	MS	12	N	- LF	- G	- E	- U	- V	-	-

Ordering Table						
Grid dimension		[mm]	124	Conditions	Code	Enter code
M	Part No.	535026				
	Series	Standard			MS	MS
	Size	12			12	12
	Thread	NPT thread			N	N
	Function	Filter			-LF	-LF
	Connection size	Port plate 1 NPT (dimensions ➔ 1119)			-AQT	
		Port plate 1¼ NPT (dimensions ➔ 1119)			-AQU	
		Port plate 1½ NPT (dimensions ➔ 1119)			-AQV	
		Port plate 2 NPT (dimensions ➔ 1119)			-AQW	
		Module without connecting thread, without port plate			-G	
	Filtration grade	40 µm			-E	
		5 µm			-C	
	Bowl	Metal bowl			-U	-U
	Bowl drain	Manual			-M	
		Fully automatic (P1 max. 176 psi)			-V	
		External fully automatic bowl drain, electrical, 24 V DC, M12			-E1	
		External fully automatic bowl drain, electrical, 110 V AC, terminals			-E2	
External fully automatic bowl drain, electrical, 230 V AC, terminals			-E3			
External fully automatic bowl drain, electrical, 24 V DC, terminals			-E4			
O	Type of mounting	Mounting bracket (dimensions ➔ 1120)		1	-WP	
	Reverse flow direction	Flow direction from right to left			-Z	

1 WP Only with port plate AQT, AQU, AQV or AQW

Transfer order code


535026	MS	12	N	-	LF	-		-		-	U	-		-		-	
--------	----	----	---	---	----	---	--	---	--	---	---	---	--	---	--	---	--

Standard Filters MS12N-LF – Inch Series

Accessories Overview



Mounting Attachments and Accessories



Mounting Attachments and Accessories		→ Page
1	Port plate MS12-AQ...	1119
2	Mounting bracket MS12-WP	1120
3	Body connector MS12-MV	1119

Standard Filters MS12N-LF – Inch Series

Accessories


1 Port plate MS12-AQ...

- Adapter for pneumatic connection

Material:

Die-cast aluminum

Free of copper and PTFE



Dimensions and Ordering Data												
B1	B2	B3	B4	B5	D1	L1	L2	L3	L4	Weight [lb]	Part No.	Type
6.38	4.88	0.47	3.90	7.24	1 NPT	9.06	3.94	0.43	3.94	2.60	537139	MS12-AQT
				7.24	1¼ NPT						537140	MS12-AQU
				7.24	1½ NPT						537141	MS12-AQV
				7.72	2 NPT						537142	MS12-AQW

3 Body connector MS12-MV

- For connecting modules

Material:

Die-cast aluminum,

Free of copper and PTFE



Ordering Data			
Size	Weight [lb]	Part No.	Type
MS12	1.00	537134	MS12-MV

Standard Filters MS12N-LF – Inch Series




Accessories

2 Mounting bracket MS12-WP

- To connect the modules for wall mounting
- In combination with a port plate for mounting an individual unit on a wall

Material:
Die-cast aluminum
Free of copper and PTFE



Dimensions and Ordering Data											
Size	B1	B2	B3	B4	L1	L2	L3	L4	Weight [[b]	Part No.	Type
MS12	6.38	4.88	0.47	3.90	9.06	3.94	0.43	3.94	1.40	537133	MS12-WP

Standard Filters MS12N-LF – Inch Series

Replacement Parts



Ordering Data – Filter Cartridges			
Size	Filtration grade [µm]	Part No.	Type
MS12	5	537143	MS12-LFP-C
	40	537144	MS12-LFP-E

- For spare parts go to: www.festo.com/en/spare_parts_service

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change