

Plastic tubing PUN-H, PUN-H-DUO

FESTO



Characteristics

At a glance

Flexible and hydrolysis-resistant tubing with standard O.D. in various colours in single or double tubing design

- Polyurethane
- Highly resistant to microbes and hydrolysis
- Food grade see www.festo.com/certificates/PUN_H
- Suitable for energy chains
- Also available as DUO plastic tubing
- Operating medium: compressed air, vacuum, water
- Very easy installation thanks to “one-click” principle

Recommended tubing/fitting combinations (further information at www.festo.com/catalogue/pun-h → Support/Downloads):

- PUN-H/PUN-H-DUO with QS fitting (for tube size 2 to 12; 16 and 22)
- PUN-H/PUN-H-DUO with NPQH fitting (for tube size 4 to 14)
- PUN-H with NPKA fitting (for tube size 6) → cleanroom-compatible combination

Product segmentation




Festo Core Range

Solves the majority of your automation tasks

With the Festo Core Range, we have selected the most important products and functions from our broad product catalogue, and added the quickest delivery. the Core Range offers you the best value with the expected high Festo quality.

- Quickest delivery, worldwide – wherever, whenever
- Expected high Festo quality
- Easy and fast to select

Ordering data - modular system



Configurable product

This product and all its product options can be ordered online via the configurator.

Diagrams Further information → [pun-h](#)



The diagrams shown in this document are also available online. These can be used to display precise values.

Alternative material characteristic

[H]	Hydrolysis-resistant
-----	----------------------

Hydrolysis-resistant and suitable for water applications.

Pipe/tubing O.D. x wall thickness

For standard O.D. tubing, the outside diameter of the tube and the wall thickness are given as the tube size.

Tubing type

[]	Standard	[DUO]	DUO pneumatic tubing
-----	----------	-------	----------------------

Consists of a single tube

Two pieces of tubing are welded together to form a pair. During installation, the tubing pair is cut to the required length at both ends.

Characteristics

Packaging unit [m]

- Standard: 50 m
- In some cases, available in longer lengths on a reel.

Type code

001	Series	
PUN	Plastic tubing, polyurethane	

002	Alternative material characteristic	
H	Hydrolysis-resistant	

003	Pipe/tubing O.D. x wall thickness	
2x0,4	2x0.4 mm	
3x0,5	3x0.5 mm	
4x0,75	4x0.75 mm	
6x1	6x1 mm	
8x1,25	8x1.25 mm	
10x1,5	10x1.5 mm	
12x2	12x2 mm	
14x2	14x2 mm	
16x2,5	16x2.5 mm	

004	Tubing type	
	Standard	
DUO	DUO pneumatic tubing	

005	Colour	
BL	Blue	
BS	Blue/black	
GE	Yellow	
GN	Green	
NT	Natural	
RT	Red	
SI	Silver	
SW	Black	
TBL	Translucent blue	
TGE	Translucent yellow	
TGN	Translucent green	
TRT	Translucent red	
TSW	Translucent black	

006	Packaging unit [m]	
	Standard	
25	25 m	
100	100 m	
200	200 m	
300	300 m	
400	400 m	
500	500 m	

Datasheet

Operating and environmental conditions PUN-H with O.D. 2 mm

Outside diameter	2 mm
Inside diameter	1.2 mm
Pneumatic connection	For push-in connector O.D. 2 mm
Flow-relevant bending radius	8 mm
Min. bending radius	5 mm
Temperature-dependent operating pressure	-0.095 ... 1 MPa
Temperature-dependent operating pressure	-0.95 ... 10 bar
Temperature-dependent operating pressure	-13.775 ... 145 psi
Operating pressure complete temperature range	-0.095 ... 0.6 MPa
Operating pressure complete temperature range	-0.95 ... 6 bar
Operating pressure complete temperature range	-13.775 ... 87 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-]
Ambient temperature	-35 ... 60°C
Tubing characteristics	Suitable for energy chains

Operating and environmental conditions PUN-H with O.D. 3 ... 16 mm

Outside diameter	3 mm	4 mm	6 mm	8 mm	10 mm	12 mm	14 mm	16 mm
Inside diameter	2.1 mm	2.6 mm	4 mm	5.7 mm	7 mm	8 mm	9.8 mm	11 mm
Pneumatic connection	For push-in connector outside diameter of 3 mm	For push-in connector O.D. 4 mm For barbed fitting I.D. 3 mm with union nut	For push-in connector O.D. 6 mm For barbed fitting I.D. 4 mm with union nut	For push-in connector O.D. 8 mm For barbed fitting inside diameter of 6 mm with union nut	For push-in connector O.D. 10 mm	For push-in connector outside diameter of 12 mm	For push-in connector outer diameter of 14 mm	For push-in connector O.D. 16 mm
Flow-relevant bending radius	12 mm	16 mm	26 mm	37 mm	52 mm	62 mm	78 mm	88 mm
Min. bending radius	6 mm	8 mm	10 mm	21 mm	28 mm	33 mm	38 mm	
Temperature-dependent operating pressure	-0.095 ... 1 MPa							
Temperature-dependent operating pressure	-0.95 ... 10 bar							
Temperature-dependent operating pressure	-13.775 ... 145 psi							
Operating pressure complete temperature range	-0.095 ... 0.6 MPa							
Operating pressure complete temperature range	-0.95 ... 6 bar							
Operating pressure complete temperature range	-13.775 ... 87 psi							
Note on operating pressure	Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C							
Operating medium	Compressed air to ISO 8573-1:2010 [7:-] Water (liquid, ice-free)			Compressed air to ISO 8573-1:2010 [7:-] Water as per manufacturer's declaration at www.festo.com Water (liquid, ice-free)				Compressed air to ISO 8573-1:2010 [7:-] Water (liquid, ice-free)
Suitable for use with food ¹⁾	See supplementary material information							
Ambient temperature	-35 ... 60°C							
Fire test material	UL94 HB							
Approval	German Technical Control Board (TÜV)							
Certificate issuing authority	B 013277 0506 00							
Tubing characteristics	Suitable for energy chains							


1) More information www.festo.com/catalogue/pun-h → Support/Downloads.

Datasheet


Operating and environmental conditions – PUN-H-DUO				
Outside diameter	4 mm	6 mm	8 mm	10 mm
Inside diameter	2.6 mm	4 mm	5.7 mm	7 mm
Pneumatic connection	For push-in connector O.D. 4 mm For barbed fitting I.D. 3 mm with union nut	For push-in connector O.D. 6 mm For barbed fitting I.D. 4 mm with union nut	For push-in connector O.D. 8 mm For barbed fitting inside diameter of 6 mm with union nut	For push-in connector O.D. 10 mm
Flow-relevant bending radius	16 mm	26 mm	37 mm	52 mm
Min. bending radius	8 mm	10 mm	21 mm	28 mm
Temperature-dependent operating pressure	-0.095 ... 1 MPa			
Temperature-dependent operating pressure	-0.95 ... 10 bar			
Temperature-dependent operating pressure	-13.775 ... 145 psi			
Operating pressure complete temperature range	-0.095 ... 0.6 MPa			
Operating pressure complete temperature range	-0.95 ... 6 bar			
Operating pressure complete temperature range	-13.775 ... 87 psi			
Note on operating pressure	Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C			
Operating medium	Compressed air to ISO 8573-1:2010 [7:::] Water (liquid, ice-free)			
Suitable for use with food ¹⁾	See supplementary material information			
Ambient temperature	-35 ... 60°C			
Fire test material	UL94 HB			
Approval	German Technical Control Board (TÜV)			
Certificate issuing authority	B 013277 0506 00			
Tubing characteristics	Suitable for energy chains			

1) More information www.festo.com/catalogue/pun-h → Support/Downloads.

Operating pressure p as a function of temperature t



Operating pressure p as a function of temperature t (medium: water)



Deviating maximum operating pressures apply to the medium water, with a safety factor of s=4.


Datasheet

Materials	
Shore hardness	D 52 +/-3
Material tubing	TPE-U(PU)
Note on materials	RoHS-compliant
LABS (PWIS) conformity ¹⁾	VDMA24364-B2-L
Suitability for the production of Li-ion batteries ²⁾	Metals with more than 1% by mass of copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Instructions on use	TPE-U Ether based

1) Applies to PUN-H with O.D. 3 ... 16 mm and PUN-H-DUO

2) Applies to PUN-H with O.D. 3 ... 16 mm and PUN-H-DUO

Dimensions



	D1 Ø	D2 Ø	D3 Ø	D4 Ø	D5 Ø	D6 Ø	D7 Ø	D8 Ø	H1	H2	L1	L2	W1
PUN-H-3x0,5-...-500	545	246	21	20	216	75	20	20	152,5	80,5	128	8	45°
PUN-H-4x0,75-...-500	545	246	21	20	216	75	20	20	152,5	80,5	128	8	45°
PUN-H-6x1-...-500	545	246	21	20	216	75	20	20	152,5	80,5	128	8	45°
PUN-H-8x1,25-...-400	545	310	21	20	280	75	20	20	152,5	80,5	254	8	45°
PUN-H-10x1,5-...-300	600	310	21	20	280	75	20	20	152,5	80,5	254	8	45°
PUN-H-12x2-...-200	600	310	21	20	280	75	20	20	152,5	80,5	254	8	45°
PUN-H-16x2,5-...-100	545	310	21	20	280	75	20	20	152,5	80,5	254	8	45°

Ordering data

Ordering data PUN-H

	Outside diameter	Packaging unit [m] ¹⁾	Product weight according to length	Colour	Part no.	Type	
	2 mm	Standard	0.002 kg/m	Natural	133038	PUN-H-2X0,4-NT	
	3 mm			Red	133040	PUN-H-2X0,4-RT	
				Black	133039	PUN-H-2X0,4-SW	
			0.004 kg/m	Blue	197382	PUN-H-3X0,5-BL	
				Yellow	558298	PUN-H-3X0,5-GE	
				Green	558291	PUN-H-3X0,5-GN	
				Natural	197375	PUN-H-3X0,5-NT	
				Red	558284	PUN-H-3X0,5-RT	
				Black	197389	PUN-H-3X0,5-SW	
				Silver	558277	PUN-H-3X0,5-SI	
		Blue		558256	PUN-H-3X0,5-BL-500		
	Natural	558263		PUN-H-3X0,5-NT-500			
	Black	558249		PUN-H-3X0,5-SW-500			
	Silver	558270		PUN-H-3X0,5-SI-500			
	4 mm	Standard	0.009 kg/m	Blue	★ 197383	PUN-H-4X0,75-BL	
				Yellow	558299	PUN-H-4X0,75-GE	
				Green	558292	PUN-H-4X0,75-GN	
				Natural	★ 197376	PUN-H-4X0,75-NT	
				Red	★ 558285	PUN-H-4X0,75-RT	
				Black	★ 197390	PUN-H-4X0,75-SW	
				Silver	★ 558278	PUN-H-4X0,75-SI	
				Translucent blue	★ 8048671	PUN-H-4X0,75-TBL	
				Translucent yellow	8048679	PUN-H-4X0,75-TGE	
				Translucent green	8048677	PUN-H-4X0,75-TGN	
		Translucent red		8048675	PUN-H-4X0,75-TRT		
		Translucent black		8048673	PUN-H-4X0,75-TSW		
		25 m			8205512	PUN-H-4X0,75-BL-25	
				Red	8204445	PUN-H-4X0,75-RT-25	
				Black	8205515	PUN-H-4X0,75-SW-25	
				Translucent blue	8205518	PUN-H-4X0,75-TBL-25	
				500 m	Blue	★ 558257	PUN-H-4X0,75-BL-500
					Natural	★ 558264	PUN-H-4X0,75-NT-500
		Black			★ 558250	PUN-H-4X0,75-SW-500	
		Silver			★ 558271	PUN-H-4X0,75-SI-500	
		Translucent blue			★ 8048672	PUN-H-4X0,75-TBL-500	
		Translucent yellow			8048680	PUN-H-4X0,75-TGE-500	
		Translucent green			8048678	PUN-H-4X0,75-TGN-500	
		Translucent red			8048676	PUN-H-4X0,75-TRT-500	
		Translucent black			8048674	PUN-H-4X0,75-TSW-500	
	6 mm	Standard	0.018 kg/m	Blue	★ 197384	PUN-H-6X1-BL	
				Yellow	558300	PUN-H-6X1-GE	
				Green	558293	PUN-H-6X1-GN	
				Natural	★ 197377	PUN-H-6X1-NT	
				Red	★ 558286	PUN-H-6X1-RT	
				Black	★ 197391	PUN-H-6X1-SW	
				Silver	★ 558279	PUN-H-6X1-SI	
				Translucent blue	★ 8048681	PUN-H-6X1-TBL	
				Translucent yellow	8048689	PUN-H-6X1-TGE	

Ordering data

Ordering data PUN-H								
	Outside diameter	Packaging unit [m] ¹⁾	Product weight according to length	Colour	Part no.	Type		
	6 mm	Standard	0.018 kg/m	Translucent green	8048687	PUN-H-6X1-TGN		
				Translucent red	8048685	PUN-H-6X1-TRT		
				Translucent black	8048683	PUN-H-6X1-TSW		
		25 m		Blue	8205513	PUN-H-6X1-BL-25		
				Red	8204446	PUN-H-6X1-RT-25		
				Black	8205516	PUN-H-6X1-SW-25		
				Translucent blue	8205519	PUN-H-6X1-TBL-25		
				500 m	Blue	★ 558258	PUN-H-6X1-BL-500	
					Natural	★ 558265	PUN-H-6X1-NT-500	
		Black			★ 558251	PUN-H-6X1-SW-500		
		Silver			★ 558272	PUN-H-6X1-SI-500		
		Translucent blue			★ 8048682	PUN-H-6X1-TBL-500		
		Translucent yel- low			8048690	PUN-H-6X1-TGE-500		
		Translucent green			8048688	PUN-H-6X1-TGN-500		
		Translucent red			8048686	PUN-H-6X1-TRT-500		
		Translucent black			8048684	PUN-H-6X1-TSW-500		
		8 mm			Standard	0.029 kg/m	Blue	★ 197385
				Yellow			558301	PUN-H-8X1,25-GE
				Green			558294	PUN-H-8X1,25-GN
	Natural		★ 197378	PUN-H-8X1,25-NT				
	Red		★ 558287	PUN-H-8X1,25-RT				
	Black		★ 197392	PUN-H-8X1,25-SW				
	Silver		★ 558280	PUN-H-8X1,25-SI				
	Translucent blue		★ 8048691	PUN-H-8X1,25-TBL				
	Translucent yel- low		8048699	PUN-H-8X1,25-TGE				
	Translucent green		8048697	PUN-H-8X1,25-TGN				
	Translucent red		8048695	PUN-H-8X1,25-TRT				
	Translucent black		8048693	PUN-H-8X1,25-TSW				
	25 m		Blue	8205514	PUN-H-8X1,25-BL-25			
			Red	8204447	PUN-H-8X1,25-RT-25			
			Black	8205517	PUN-H-8X1,25-SW-25			
			Translucent blue	8205520	PUN-H-8X1,25-TBL-25			
			400 m	Blue	★ 558259		PUN-H-8X1,25-BL-400	
				Natural	★ 558266		PUN-H-8X1,25-NT-400	
	Black			★ 558252	PUN-H-8X1,25-SW-400			
	Silver			★ 558273	PUN-H-8X1,25-SI-400			
	Translucent blue			★ 8048692	PUN-H-8X1,25-TBL-400			
	Translucent yel- low			8048700	PUN-H-8X1,25-TGE-400			
	Translucent green			8048698	PUN-H-8X1,25-TGN-400			
	Translucent red		8048696	PUN-H-8X1,25-TRT-400				
	Translucent black		8048694	PUN-H-8X1,25-TSW-400				
	10 mm	Standard	0.046 kg/m	Blue	★ 197386	PUN-H-10X1,5-BL		
				Yellow	558302	PUN-H-10X1,5-GE		
				Green	558295	PUN-H-10X1,5-GN		
				Natural	★ 197379	PUN-H-10X1,5-NT		
				Red	★ 558288	PUN-H-10X1,5-RT		


Ordering data

Ordering data PUN-H						
	Outside diameter	Packaging unit [m] ¹⁾	Product weight according to length	Colour	Part no.	Type
	10 mm	Standard	0.046 kg/m	Black	★ 197393	PUN-H-10X1,5-SW
				Silver	★ 558281	PUN-H-10X1,5-SI
				Translucent blue	★ 8048701	PUN-H-10X1,5-TBL
				Translucent yellow	8048709	PUN-H-10X1,5-TGE
				Translucent green	8048707	PUN-H-10X1,5-TGN
				Translucent red	8048705	PUN-H-10X1,5-TRT
				Translucent black	8048703	PUN-H-10X1,5-TSW
		25 m		Blue	8204441	PUN-H-10X1,5-BL-25
				Red	8204448	PUN-H-10X1,5-RT-25
				Black	8204443	PUN-H-10X1,5-SW-25
				Translucent blue	8205521	PUN-H-10X1,5-TBL-25
		300 m		Blue	★ 558260	PUN-H-10X1,5-BL-300
				Natural	★ 558267	PUN-H-10X1,5-NT-300
				Black	★ 558253	PUN-H-10X1,5-SW-300
				Silver	★ 558274	PUN-H-10X1,5-SI-300
				Translucent blue	★ 8048702	PUN-H-10X1,5-TBL-300
				Translucent yellow	8048710	PUN-H-10X1,5-TGE-300
				Translucent green	8048708	PUN-H-10X1,5-TGN-300
				Translucent red	8048706	PUN-H-10X1,5-TRT-300
				Translucent black	8048704	PUN-H-10X1,5-TSW-300
	12 mm	Standard	0.073 kg/m	Blue	★ 197387	PUN-H-12X2-BL
				Yellow	558303	PUN-H-12X2-GE
				Green	558296	PUN-H-12X2-GN
				Natural	★ 197380	PUN-H-12X2-NT
				Red	★ 558289	PUN-H-12X2-RT
				Black	★ 197394	PUN-H-12X2-SW
				Silver	★ 558282	PUN-H-12X2-SI
				Translucent blue	★ 8048711	PUN-H-12X2-TBL
				Translucent yellow	8048719	PUN-H-12X2-TGE
				Translucent green	8048717	PUN-H-12X2-TGN
				Translucent red	8048715	PUN-H-12X2-TRT
				Translucent black	8048713	PUN-H-12X2-TSW
25 m		Blue		8204442	PUN-H-12X2-BL-25	
		Red		8204449	PUN-H-12X2-RT-25	
		Black		8204444	PUN-H-12X2-SW-25	
		Translucent blue		8205522	PUN-H-12X2-TBL-25	
200 m		Blue		★ 558261	PUN-H-12X2-BL-200	
		Natural		★ 558268	PUN-H-12X2-NT-200	
		Black		★ 558254	PUN-H-12X2-SW-200	
		Silver		★ 558275	PUN-H-12X2-SI-200	
	Translucent blue	★ 8048712	PUN-H-12X2-TBL-200			
	Translucent yellow	8048720	PUN-H-12X2-TGE-200			
	Translucent green	8048718	PUN-H-12X2-TGN-200			
	Translucent red	8048716	PUN-H-12X2-TRT-200			
Translucent black	8048714	PUN-H-12X2-TSW-200				


Ordering data

Ordering data PUN-H						
	Outside diameter	Packaging unit [m] ¹⁾	Product weight according to length	Colour	Part no.	Type
	14 mm	Standard	0.091 kg/m	Blue	★ 570386	PUN-H-14X2-BL
				Natural	570388	PUN-H-14X2-NT
				Black	570387	PUN-H-14X2-SW
	16 mm		0.123 kg/m	Blue	★ 197388	PUN-H-16X2,5-BL
				Yellow	558304	PUN-H-16X2,5-GE
				Green	558297	PUN-H-16X2,5-GN
				Natural	★ 197381	PUN-H-16X2,5-NT
				Red	★ 558290	PUN-H-16X2,5-RT
				Black	★ 197395	PUN-H-16X2,5-SW
				Silver	★ 558283	PUN-H-16X2,5-SI
		100 m		Blue	★ 558262	PUN-H-16X2,5-BL-100
				Natural	558269	PUN-H-16X2,5-NT-100
				Black	558255	PUN-H-16X2,5-SW-100
				Silver	558276	PUN-H-16X2,5-SI-100

1) Standard: 50 m

Ordering data PUN-H-DUO						
	Outside diameter	Packaging unit [m] ¹⁾	Product weight according to length	Colour	Part no.	Type
	4 mm	Standard	0.017 kg/m	Blue/black	197396	PUN-H-4X0,75-DUO
	6 mm		0.037 kg/m		197397	PUN-H-6X1-DUO
	8 mm		0.057 kg/m		197398	PUN-H-8X1,25-DUO
	10 mm		0.093 kg/m		197399	PUN-H-10X1,5-DUO

1) Standard: 50 m

Ordering data – Modular product system			
	Short type code	Part no.	Type
	PUN, PUN-CM, PUN-H, PUN-V0, PUN-V0-C	553573	PUN