

## Heavy-duty tubing PAN-R

**FESTO**




## Characteristics

### At a glance

Powerful performance at pressure ranges up to 20 bar, e.g. in applications using the pressure booster DPA

- Polyamide
- For applications with high pressure ranges
- Highly resistant to microbes
- Operating medium: compressed air, vacuum

### Ordering data - modular system



Configurable product

This product and all its product options can be ordered online via the configurator.

### Diagrams

[Further information → pan-r](#)



The diagrams shown in this document are also available online. These can be used to display precise values.

### Alternative material characteristic

[R] Sturdy

For applications with high pressure ranges

### Pipe/tubing O.D. x wall thickness

For standard O.D. tubing, the outside diameter of the tube and the wall thickness are given as the tube size.

### Packaging unit [m]

Standard: 50 m

## Type code

001	Series
PAN	Standard O.D. tubing

002	Alternative material characteristic
R	Sturdy

003	Pipe/tubing O.D. x wall thickness
4x0,75	4x0.75 mm
6x1,1	6x1.1 mm
8x1,5	8x1.5 mm
10x1,9	10x1.9 mm
12x2,2	12x2.2 mm
16x3	16x3 mm
22x2	22x2 mm
28x2,5	28x2.5 mm


004	Colour
SW	Black
SI	Silver

Datasheet

**Operating and ambient conditions – O.D. 4 ... 16 mm**

Outside diameter	4 mm	6 mm	8 mm	10 mm	12 mm	16 mm
Inside diameter	2.5 mm	3.8 mm	5 mm	6.2 mm	7.6 mm	10 mm
Pneumatic connection	For push-in connector O.D. 4 mm	For push-in connector O.D. 6 mm	For push-in connector O.D. 8 mm	For push-in connector O.D. 10 mm	For push-in connector outside diameter of 12 mm	For push-in connector O.D. 16 mm
Flow-relevant bending radius	16 mm	21 mm	29 mm	44 mm	46 mm	73 mm
Min. bending radius	10 mm	16 mm	20 mm	25 mm	30 mm	42 mm
Temperature-dependent operating pressure	-0.095 ... 3.5 MPa					
Temperature-dependent operating pressure	-0.95 ... 35 bar					
Temperature-dependent operating pressure	-13.775 ... 507.5 psi					
Operating medium	Compressed air to ISO 8573-1:2010 [7:-]					
Ambient temperature	-30 ... 80°C					
Approval	German Technical Control Board (TÜV)					
Certificate issuing authority	B 013277 0506 00					
Tubing characteristics	Suitable for energy chains					

**Operating pressure p as a function of temperature t**




**Operating and environmental conditions – O.D. 22 ... 28 mm**

Outside diameter	22	28
Inside diameter	18 mm	23 mm
Pneumatic connection	For push-in connector O.D. 22 mm	For push-in connector O.D. 28 mm
Flow-relevant bending radius	350 mm	
Temperature-dependent operating pressure	-0.095 ... 1.4 MPa	
Temperature-dependent operating pressure	-0.95 ... 14 bar	
Temperature-dependent operating pressure	-13.775 ... 203 psi	
Operating pressure complete temperature range	-0.95 ... 8 bar	
Operating pressure complete temperature range	-13.775 ... 116 psi	
Operating pressure complete temperature range	-0.095 ... 0.8 MPa	
Operating medium	Compressed air to ISO 8573-1:2010 [7:-]	
Ambient temperature	-30 ... 80°C	

## Datasheet

### Operating pressure $p$ as a function of temperature $t$




### Materials

Shore hardness	D 62 +/-3
Material tubing	TPE-A
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B2-L


Ordering data

Ordering data – Outer-Ø 4 ... 16 mm

	Outside diameter	Packaging unit [m] <sup>1)</sup>	Product weight according to length	Colour	Part no.	Type
	4 mm	50 m	0.008 kg/m	Silver	<b>541674</b>	<b>PAN-R-4X0,75-SI</b>
	6 mm	Standard	0.017 kg/m		<b>541675</b>	<b>PAN-R-6X1,1-SI</b>
	8 mm		0.032 kg/m		<b>541676</b>	<b>PAN-R-8X1,5-SI</b>
	10 mm		0.05 kg/m		<b>541677</b>	<b>PAN-R-10X1,9-SI</b>
	12 mm		0.07 kg/m		<b>541678</b>	<b>PAN-R-12X2,2-SI</b>
	16 mm		0.126 kg/m		<b>541679</b>	<b>PAN-R-16X3-SI</b>

1) Standard: 50 m

Ordering data – O.D. 22 ... 28 mm

	Outside diameter	Packaging unit [m] <sup>1)</sup>	Product weight according to length	Colour	Part no.	Type
	22 mm	50 m	0.131 kg/m	Black	<b>8036207</b>	<b>PAN-R-22X2-SW</b>
	28 mm		0.207 kg/m		<b>8036208</b>	<b>PAN-R-28X2,5-SW</b>

1) Standard: 50 m

Ordering information – Modular product system

	Short type code	Part no.	Type
	PAN, PAN-ME, PAN-R	<b>553610</b>	<b>PAN</b>