

Electrical connection technology, for multi-pin plug connection


FESTO


Technical data – VMPA-KMS-H

- Plug socket for multi-pin connection (to valve terminal type 32 MPA)
- Can be fabricated with any cable lengths
- 25-pin
- Sub-D



General technical data	
Type	VMPA-KMS-H
Type of mounting	3 M3x22 screws
Mounting position	Any
Cable gland connection	M20x1.5
Operating voltage range [V DC]	24
Current-carrying capacity [A]	3
Protection class to EN 60 529	IP65 (assembled)
Material of housing	Fibreglass reinforced polyamide
Material of contacts	Gold-plated copper base alloy
Material of seal	Polyurethane
Ambient temperature [°C]	–30 ... +80

Ordering data				
	Electrical connection	Perm. cable diameter [mm]	Type	Part No.
	25-pin Sub-D socket	6 ... 12	VMPA-KMS-H	533 198

Dimensions		Download CAD Data → www.festo.com/us/cad
VMPA-KMS-H		
		
1 Cable gland fitting M20x1.5		

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change