


Solenoid valve, inch MN1H

FESTO




Characteristics

At a glance

- Pilot-operated diaphragm valve
- Brass version
- Can only be used for gaseous media
- Adjustable closing cushioning, in-line mounting or through-hole
- Operating voltage 24 V DC, 110/230 V AC (50 ... 60 Hz)
- When switching on the voltage, the solenoid is energised and the valve is reversed

Function



Type code

001	Series	
MN1H	Valve with armature tube for solenoid coil MSN, single solenoid MN1H	

002	Valve function	
2	2/2-way valve	

003	Process valve connection	
N14	1/4 NPT	
N38	3/8 NPT	
N12	1/2 NPT	
N34	3/4 NPT	
N1	1 NPT	
N112	1 1/2 NPT	

004	Housing material	
MS	Brass	

Datasheet

General technical data

General technical data						
Connection Process valve	1/4 NPT	3/8 NPT	1/2 NPT	3/4 NPT	1 NPT	1 1/2 NPT
Valve function	2/2-way, closed, monostable					
Design	Diaphragm valve					
Sealing principle	Soft					
Type of actuation	Electric	–				
Type of reset	Pneumatic spring					
Type of piloting	Pilot actuated					
Flow direction	Non-reversible					
Exhaust-air function	Without flow control option					
Manual override	Detenting via accessory, Non-detenting					
Type of mounting	In-line installation					
Mounting position	optional					
Nominal size	13 mm			20 mm	25 mm	40 mm
Degree of protection	IP65					
Product weight	450 g		400 g	1,100 g		2,600 g

Operating and environmental conditions


Medium	Filtered compressed air, grade of filtration 200 µm
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Medium pressure	0.5 ... 10 bar
Ambient temperature	-10 ... 60°C
Media temperature	-10 ... 60°C

Materials

Material screws	High-alloy stainless steel
Material number screw	1.4301

Dimensions

Dimensions – 2/2-way valve


[Download CAD data](#) www.festo.com


- [1] Connection for plug socket according to DIN 43650, type A
- [2] Manual override attachment can be rotated and latched
- [3] Manual override without attachment, non-detenting
- [4] Location for inscription label type IBS-9x20
- [5] Retaining bracket HRM-...

	D	B	D1	H	H1	H2
MN1H-2-1/4-MS-NPT	1/4 NPT	48	M4	67	46	15
MN1H-2-3/8-MS-NPT	3/8 NPT	48	M4	67	46	15
MN1H-2-1/2-MS-NPT	1/2 NPT	48	M4	67	46	15
MN1H-2-3/4-MS-NPT	3/4 NPT	70	M6	78	57	23
MN1H-2-1-MS-NPT	1 NPT	70	M6	78	57	23
MN1H-2-1 1/2-MS-NPT	1 1/2 NPT	96	M6	91,5	70,5	31,5

	L	L1	L2	L3	L4	≅
MN1H-2-1/4-MS-NPT	67	25	21	26,5	20	27
MN1H-2-3/8-MS-NPT	67	25	21	26,5	20	27
MN1H-2-1/2-MS-NPT	67	25	21	26,5	20	27
MN1H-2-3/4-MS-NPT	95	40	27,5	26,5	21,5	41
MN1H-2-1-MS-NPT	95	40	27,5	26,5	21,5	41
MN1H-2-1 1/2-MS-NPT	140	59,5	38,3	26,5	30	58

Dimensions





	B1	B2	B3	D1 Ø	D2 Ø	H1	H2	L1	L2 ±0,1
HRM-1	25	12,5	2	6	5	37	10	40	25
HRM-2	35	17,5	3	7	7	66	16	55	40
HRM-3	47	23,5	3	9	7	87	23	75	59,5


Ordering data

Ordering data			
	Connection Process valve	Part no.	Type
	1/4 NPT	161724	MN1H-2-1/4-MS-NPT
	3/8 NPT	161726	MN1H-2-3/8-MS-NPT
	1/2 NPT	161729	MN1H-2-1/2-MS-NPT
	3/4 NPT	161730	MN1H-2-3/4-MS-NPT
	1 NPT	161733	MN1H-2-1-MS-NPT
	1 1/2 NPT	161735	MN1H-2-1 1/2-MS-NPT


Accessories

Mounting bracket HRM				
	Size	Product weight	Part no.	Type
	Size 1	39 g	9769	HRM-1
	Size 2	130 g	9770	HRM-2
	Size 3	246 g	9771	HRM-3


Solenoid coils			
	Characteristic coil data	Part no.	Type
	110 V AC: 50 Hz, pick-up power 7.5 VA, holding power 5.0 VA, 110 V AC: 60 Hz, pick-up power 5.0 VA, holding power 3.7 VA, 120 V AC: 60 Hz, pick-up power 5.0 VA, holding power 3.7 VA	123061	MSN1W-110AC-OD
	230 V AC: 50 Hz, pick-up power 7.5 VA, holding power 5.0 VA, 230 V AC: 60 Hz, pick-up power 5.0 VA, holding power 3.7 VA	123062	MSN1W-230AC-OD
	24 V DC: 2.5 W	123060	MSN1G-24DC-OD


Plug socket without cable			
	Electrical connection	Part no.	Type
	3-pin, Angled socket, Type A, To DIN EN 175301-803, Square design MSC, Square design MSN1	34583	MSSD-C


Plug socket without cable with insulation displacement technology			
	Electrical connection	Part no.	Type
	4-pin, Socket, Type A	192748	MSSD-C-S-M16

Connecting cables					
	Nominal operating voltage DC	Cable length	Switching status indication	Part no.	Type
		2.5 m		30932	KMC-1-230AC-2,5
		5 m		30934	KMC-1-230AC-5
	24 V	2.5 m	LED	30931	KMC-1-24DC-2,5-LED
		5 m		30933	KMC-1-24DC-5-LED
		10 m		193459	KMC-1-24-10-LED

Accessories

Illuminating seal			
	Operational voltage range DC	Part no.	Type
	12 ... 24 V	19145	MC-LD-12-24DC

Manual override			
	Description	Part no.	Type
	for N1 coils	157651	AHB-MD/MF/MV

Inscription labels			
	Description	Part no.	Type
	Scope of delivery: 20 pieces in frames	18182	IBS-9X20