Plastic tubing PTFEN





Plastic tubing PTFEN

Characteristics

At a glance

Particularly resistant to chemicals, cleaning processes, extreme temperatures and pressure. Perfect for use in the food industry, e.g. in meat processing. • Polytetrafluoroethylene

- For food-safe grade, see www.festo.com/certificates/PTFEN
- High resistance to chemicals
- High temperature resistance
- Operating medium: compressed air, vacuum

Diagrams

Link S ptfen



The diagrams shown in this document are also available online. These can be used to display precise values.

Pipe/tubing O.D. x wall thickness

For standard O.D. tubing, the outside diameter of the tube and the wall thickness are given as the tube size.

Packaging unit [m]

Standard: 50 m

Type code

001	Series	
PTFEN	Plastic tubing, polytetrafluorethylene, standard O.D.	
002	Pipe/tubing O.D. x wall thickness	
4x0,5	4x0.5 mm	
6x1	6x1 mm	
8x1	8x1 mm	
10x1,5	10x1.5 mm	
12x2	12x2 mm	
14x2	14x2 mm	
16x2,5	16x2.5 mm	

003	Colour					
NT	Natural					
004	Packaging unit [m]					
	Standard					
25	25 m					
100	100 m					
300	300 m					
400	400 m					
500	500 m					

Datasheet

Operating and environmental conditions

Outside diameter	4 mm	6 mm	8 mm	10 mm	12 mm	14 mm	16 mm
Inside diameter	2.9 mm	4 mm	5.9 mm	7 mm	8.4 mm	10 mm	11 mm
Pneumatic connection	For push-in connec- tor O.D. 4 mm For barbed fitting I.D. 4 mm with un- ion nut For barbed fitting I.D. 3 mm with un- ion nut For barbed fitting I.D. 3 mm	For push-in connec- tor O.D. 6 mm For barbed fitting outside diameter of 6 mm with union nut For barbed fitting I.D. 4 mm with un- ion nut For barbed fitting I.D. 4 mm	For push-in connec- tor O.D. 8 mm For barbed fitting outside diameter of 8 mm with union nut For barbed fitting inside diameter of 6 mm with union nut For barbed fitting inside diameter of 6 mm	For push-in connec- tor O.D. 10 mm For barbed fitting outside diameter of 10 mm with union nut	For push-in connec- tor outside diameter of 12 mm	For push-in connec- tor outer diameter of 14 mm	For push-in connec tor O.D. 16 mm
Flow-relevant bending radius	32 mm	40 mm	90 mm	100 mm	120 mm		160 mm
Min. bending radius	32 mm	38 mm	64 mm	70 mm	84 mm	106 mm	109 mm
Temperature-dependent oper- ating pressure	-0.095 1.2 MPa -0.095 1.5 MPa -0.095 1.2 MPa						
Temperature-dependent oper- ating pressure	-0.95 12 bar -0.95 15 bar -0.95 12 bar						
Temperature-dependent oper- ating pressure	-13.775 174 psi	174 psi -13.775 217.5 -13.775 174 psi psi					
Operating pressure complete temperature range	-0.095 0.5 MPa						
Operating pressure complete temperature range	-0.95 5 bar						
Operating pressure complete temperature range	-13.775 72.5 psi						
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]						
Suitable for use with food $^{\mbox{\tiny 1)}}$	See supplementary material information						
Ambient temperature	-20 150°C						
Fire test material	UL94 V-0						

1) More information www.festo.com/catalogue/ptfen \rightarrow Support/Downloads.

Operating pressure p as a function of temperature t



D 55 +/-5
PTFE
RoHS-compliant
VDMA24364-B2-L
Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Tubing without printing

Ordering data

Ordering data

Ordering data						
	Outside diameter	Packaging unit [m] ¹⁾	Product weight according to length	Colour	Part no.	Туре
	4 mm	100 m	0.013 kg/m	Natural	8061171	PTFEN-4X0,5-NT-100
	6 mm		0.034 kg/m]	8061172	PTFEN-6X1-NT-100
		500 m			8061178	PTFEN-6X1-NT-500
	8 mm	Standard	0.047 kg/m		8061173	PTFEN-8X1-NT
		400 m]		8061179	PTFEN-8X1-NT-400
	10 mm	Standard	0.086 kg/m]	8061174	PTFEN-10X1,5-NT
		300 m			8061180	PTFEN-10X1,5-NT-300
	12 mm	Standard	0.124 kg/m		8061175	PTFEN-12X2-NT
	14 mm		0.162 kg/m		8061176	PTFEN-14X2-NT
	16 mm	25 m	0.228 kg/m		8061177	PTFEN-16X2,5-NT-25

1) Standard: 50 m