





Distributors, universal

FESTO



Product range overview

Function	Version	Version	Type	Connection technology	Degree of protection	→ Page/ Internet
T-distributor		Round plug M12				
		3-pin	NEDU-L2R1-V8-M12G5-M12G5	1x socket M12, 5-pin 1x plug M12, 2-pin	IP65, IP67	3
		4-pin	NEDU-M12D4-M12T4-IS	2x socket M12, 4-pin	IP65, IP67	5
		5-pin	FB-TA-M12	2x socket M12, 5-pin	IP67	7
			NEDU-L2R1-V10-M12G5-M12G5	2x socket M12, 5-pin	IP65, IP67	7
Y-distributor with cable		Socket M12				
		5-pin	NEDU-L1R2-M12G5-M12LE-1R	1x plug M12, 3-pin 1x open end, 2-wire	IP40, IP65, IP68, IP69K	9
		8-pin	NEBV-M12G8-KD-3-M12G4	2x plug M12, 4-pin	IP67	12
		8-pin	NEDU-L1R2-V9-M12G8-...	2x open cable end	IP65, IP67	12
Multiple distributor/multi-pin plug distributor		Round plug M12				
		8-pin	NEDU-L4R1-M8G3L-M12G8	4x socket M8, 3-pin	IP68	16
			NEDU-L6R1-M8G3L-M12G8	6x socket M8, 3-pin	IP68	16
		Sub-D plug				
		15-pin	MPV-E/A08-M8	8x socket M8, 3-pin	IP65	19
			MPV-E/A12-M8	12x socket M8, 3-pin	IP65	19

Datasheet

Push-in T-connector NEDU-L2R1-V8

- T-adapter
- For IO-Link



General technical data

Electrical connection 1	Straight socket, M12, 5-pin, A-coded
Electrical connection 2	Straight plug, M12, 2-pin, A-coded
Electrical connection 3	Straight plug, M12, 3-pin, A-coded
Type of mounting	Screw-in
Max. tightening torque [Nm]	0.6
Operating voltage range [V DC]	0 ... 30
Surge resistance [kV]	1.5
Current rating [A]	4
Degree of protection to EN 60529	IP65, IP67, in assembled state
Product weight [g]	28

Materials

Housing	TPE-U(PUR)
Housing colour	Black
Union nut	Die-cast zinc, nickel-plated
Seals	FPM
Pin contacts	Gold-plated copper alloy
Note on materials	RoHS-compliant





Operating and environmental conditions

Ambient temperature [°C]	-25 ... +85
Corrosion resistance class CRC ¹⁾	2
Pollution degree	3

1) Corrosion resistance class CRC 2 to Festo standard FN 940070


Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Datasheet

Circuitry (socket/plug view)	Circuitry	
		
		

Dimensions

Download CAD data → www.festo.com



Type	B1	B2	D1	D2	D3	D4	D5	H1	H2	H3	L1	L2	⌀ 1
NEDU-L2R1-V8	15	8.3	15	M12	15	M12	4.2	33.3	21	36	48.5	13.2	13

Ordering data		Product weight [g]	Part no.	Type
Electrical connection				
Plug M12, A-coded, 3-pin	1x socket M12, A-coded, 5-pin 1x plug M12, A-coded, 2-pin	28	2839846	NEDU-L2R1-V8-M12G5-M12G5

Datasheet

Push-in T-connector NEDU-M

- T-adapter




General technical data		
Type of mounting	Screw-in	
Contact durability	100	
Operating voltage range	[V DC]	0 ... 30
Degree of protection to EN 60529	IP65, IP67	
Based on standard	EN 61076-2-101	
Max. tightening torque	[Nm]	0.5
Product weight	[g]	25.5

Materials	
Housing	Reinforced TPE-U(PU)
	Die-cast zinc
Pin contacts	Gold-plated copper alloy
Union nut	Reinforced PA
Seals	FPM
Note on materials	RoHS-compliant


Operating and environmental conditions		
Ambient temperature	[°C]	−25 ... +85
Corrosion resistance class CRC	3 ¹⁾	

1) Corrosion resistance class CRC 3 to Festo standard FN 940070
High corrosion stress. Outdoor exposure under moderate corrosive conditions. Externally visible parts with primarily functional surface requirements which are in direct contact with a normal industrial environment.



Datasheet

Dimensions Download CAD data → www.festo.com



Type	B1	D1 ø	D2	D3 ø	H1	H2	L1	L2
NEDU-M12D4-M12T4-IS	13.5	14	M12	14.4	33	20	40.3	10

Ordering data			
Electrical connection			Part no. Type
Plug M12, A-coded, 4-pin		2x socket M12, A-coded, 4-pin	562248 NEDU-M12D4-M12T4-IS

Datasheet

T-adapter

FB-TA

NEDU-L2R1-V10

- T-adapter
- Branch line for connecting and disconnecting fieldbus components
- Connected fieldbus components can be disconnected without interrupting signal transmission (to other components)



General technical data		
Type	FB-TA	NEDU-L2R1-V10
Electrical connection 3	Plug, M12, 5-pin	Straight plug, M12, 5-pin, A-coded
Electrical connection 1	M12 socket, 5-pin	Straight socket, M12, 5-pin, A-coded
Electrical connection 2	M12 socket, 5-pin	Straight socket, M12, 5-pin, A-coded
Type of mounting	Via through-hole	Screw-in
Max. tightening torque [Nm]	–	0.6
Operating voltage range [V DC]	10 ... 30	0 ... 30
Surge resistance [kV]	–	1.5
Current rating [A]	4	4
Degree of protection to EN 60529	IP67, in assembled state	IP65, IP67, in assembled state





Materials		
Type	FB-TA	NEDU-L2R1-V10
Housing	–	TPE-U(PUR)
Housing colour	–	Black
Union nut	–	Die-cast zinc, nickel-plated
Seals	–	FPM
Pin contacts	–	Gold-plated copper alloy
Note on materials	–	RoHS-compliant





Operating and environmental conditions		
Type	FB-TA	NEDU-L2R1-V10
Ambient temperature [°C]	–25 ... +90	–25 ... +85
Corrosion resistance class CRC ¹⁾	–	2
Pollution degree	–	3

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.


Datasheet

Circuitry (socket/plug view)	Circuitry	
FB-TA		
		
		

NEDU-L2R1-V10		
		
		


Dimensions

FB-TA



[1] M12 socket, 5-pin [2] Plug M12, 5-pin

NEDU-L2R1-V10



Download CAD data → www.festo.com


Type	B1	B2	D1	D2	D3	D4	D5	H1	H2	H3	L1	L2	L3	≈G 1
FB-TA	17	12	8	4.5	–	–	–	45.2	16	6.5	57	23.5	10.4	–
NEDU-L2R1-V10	15	8.3	15	M12	15	M12	4.2	33.3	21	36	45	13.2	–	13

Ordering data				
Electrical connection		Product weight [g]	Part no.	Type
Plug M12, 5 pin	2x socket M12, 5-pin	–	171175	FB-TA-M12-5POL
		25	2839867	NEDU-L2R1-V10-M12G5-M12G5

Datasheet

Distributor NEDU-L1R2-V9

- Y-distributor
- For IO-Link
- Enables separate supply of load voltage



General technical data

Design	Y distributor with cable on controller side
Distributor type	1 to 2
Cable designation	Without inscription label holder
Based on standard	EN 61076-2-101
Additional functions	Additional supply for port B
Contact durability	100

Technical data – Electrical connection 1

Function	Field device side
Connection type	Socket
Cable outlet	Straight
Design	Round
Connection technology	M12x1, A-coded to EN 61076-2-101
Number of pins/wires	5
Assigned pins/wires	5
Type of mounting	Screw lock with 18 mm hexagon and longitudinal knurl

Technical data – Electrical connection 2

Function	IO-Link Communication
Connection type	Plug
Cable outlet	Straight
Design	Round
Connection technology	M12x1, A-coded to EN 61076-2-101
Number of pins/wires	3
Assigned pins/wires	3
Type of mounting	Screw lock with 13 mm hexagon and longitudinal knurl

Technical data – Electrical connection 3

Function	Additional supply
Connection type	2x single wires
Connection technology	Open end
Number of pins/wires	2
Assigned pins/wires	2

Datasheet

Technical data – Electrics

Nominal operating voltage	[V DC]	24
Operating voltage range	[V DC]	0 ... 30
Surge resistance	[kV]	0.8
Acceptable current load at 40°C	[A]	4
Protective earth connection		Not provided
Screening		No

Technical data – Cable 1

Cable diameter	[mm]	3.8
Cable diameter tolerance	[mm]	±0.1
Cable composition	[mm ²]	3x0.25
Nominal conductor cross section	[mm ²]	0.25
Cable characteristic		For static applications
Bending radius, fixed cable installation	[mm]	≥11.7
Cable length	[m]	1

Technical data – Cable 2

Cable diameter	[mm]	1.75
Cable diameter tolerance	[mm]	±0.05
Cable composition	[mm ²]	2x0.5
Nominal conductor cross section	[mm ²]	0.5
Bending radius, fixed cable installation	[mm]	≥6
Cable length	[m]	1

Materials

Housing	PA
	TPE-U(PUR)
Housing colour	Black
Screw lock	Nickel-plated brass
	Die-cast zinc, nickel-plated
Seals	NBR
Pin contacts	Nickel-plated and gold-plated bronze
	Gold-plated brass
Cable sheath	TPE-U(PUR)
Cable sheath colour	Grey
Insulating sheath	PVC
Note on materials	RoHS-compliant
PWIS conformity	VDMA24364-B2-L




Datasheet

Operating and environmental conditions		
Ambient temperature	[°C]	-30 ... +80
Storage temperature	[°C]	-30 ... +80
Degree of protection		IP65
		IP68
		IP69K
Note on degree of protection		In assembled state
		IP40 for M12 socket
CE marking (see declaration of conformity) ²⁾		To EU RoHS Directive
UKCA marking (see declaration of conformity) ²⁾		To UK RoHS instructions
Corrosion resistance class CRC ¹⁾		1
Pollution degree		3


1) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. Dry internal application or transport and storage protection. Also applies to parts behind coverings, in the non-visible interior area, or parts that are covered in the application (e.g. drive trunnions).

2) Additional information: www.festo.com/catalogue/... → Support/Downloads.

Circuitry (socket/plug view)		
Electrical connection 2	Circuitry	Electrical connection 3
		Wire colour ¹⁾
		RD
		BK
		

1) To IEC 757

Dimensions		Download CAD data → www.festo.com
		

Type	D1	D2	D3	D4	D5	D6	L1	L2	L3	⌀G1	⌀G2
NEDU-L1R2	20.2	M12x1	3.8	15	M12x1	1.75	1000	54	54.5	18	13


Ordering data		Product weight	Part no.	Type
Electrical connection		[g]		
M12 socket, 5-pin	- Plug M12, 3-pin - Open cable end, 2-wire	72.5	8091516	NEDU-L1R2-M12G5-M12LE-1R

Datasheet

Connecting cable NEBV-M12G8

DUO cable NEDU-L1R2-V9

- Y-distributor
- For proportional pressure regulators



General technical data		
Type	NEBV-M12G8	NEDU-L1R2-V9
Design	Y-distributor with cables on both sides	Y-distributor with cable on field device and controller sides
Distributor type	1 to 2	1 to 2
Type of mounting	Via through-hole for M3 screw	–
Cable designation	Without inscription label holder	Without inscription label holder
Based on standard	–	EN 61076-2-101
Conforms to standard	DIN 47100, EN 61076-2-101	–
Additional functions	Distribution of the analogue inputs and outputs of a proportional pressure regulator	Connection of sensor and controller to proportional pressure regulator

Technical data – Electrical connection 1		
Type	NEBV-M12G8	NEDU-L1R2-V9
Function	Field device side	
Connection type	Socket	
Cable outlet	Straight	
Design	Round	
Connection technology	M12x1, A-coded to EN 61076-2-101	
Number of pins/wires	8	
Assigned pins/wires	5	6
Type of mounting	Screw lock	

Technical data – Electrical connection 2		
Type	NEBV-M12G8	NEDU-L1R2-V9
Function	Controller side	
Connection type	Plug	Cable
Cable outlet	Straight	–
Design	Round	–
Connection technology	M12x1, A-coded to EN 61076-2-101	Open end
Number of pins/wires	4	5
Assigned pins/wires	4	5
Type of mounting	Screw lock	–

Technical data – Electrical connection 3		
Type	NEBV-M12G8	NEDU-L1R2-V9
Function	Controller side	Field device side
Connection type	Plug	Cable
Cable outlet	Straight	–
Design	Round	–
Connection technology	M12x1, A-coded to EN 61076-2-101	Open end
Number of pins/wires	4	3
Assigned pins/wires	3	3
Type of mounting	Screw lock	–

Datasheet

Technical data – Electrics		
Operating voltage range	[V DC]	0 ... 30
	[V AC]	0 ... 30
Surge resistance	[kV]	0.8
Acceptable current load at 40°C	[A]	2

Technical data – Cable		
Type	NEBV-M12G8	NEDU-L1R2-V9
Cable diameter 1	[mm]	6.3
Cable diameter 2	[mm]	6.3
Cable diameter tolerance	[mm]	±0.2
Cable composition	[mm ²]	8x0.25
		–
Nominal conductor cross section	[mm ²]	0.25
Cable characteristic		Standard
Bending radius, fixed cable installation	[mm]	≥33
Bending radius, flexible cable installation	[mm]	≥66

Materials		
Type	NEBV-M12G8	NEDU-L1R2-V9
Housing	TPE-U(PUR)	TPE-U(PUR)
Housing colour	Black	Black
Screw lock	Nickel-plated brass	Nickel-plated brass
Seals	NBR	NBR
Pin contacts	Nickel-plated and gold-plated brass	Gold-plated brass
Cable sheath	TPE-U(PUR)	TPE-U(PUR)
Cable sheath colour	Grey	Grey
Insulating sheath	PP	PVC
Note on materials	RoHS-compliant	RoHS-compliant
	Halogen-free	–
PWIS conformity	VDMA24364-B2-L	VDMA24364-B2-L





Operating and environmental conditions		
Type	NEBV-M12G8	NEDU-L1R2-V9
Ambient temperature	[°C]	–25 ... +80
Ambient temperature with flexible cable installation	[°C]	–5 ... +80
Degree of protection	IP67	IP65, IP67
Note on degree of protection	In assembled state	In assembled state
Corrosion resistance class CRC ¹⁾	2	
Pollution degree	3	
CE marking (see declaration of conformity) ²⁾	To EU RoHS Directive	
UKCA marking (see declaration of conformity) ²⁾	To UK RoHS instructions	



1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

2) Additional information: www.festo.com/catalogue/... → Support/Downloads.

Datasheet

Circuitry (socket/plug view) – NEBV-M12G8		Circuitry		Electrical connection 3
Electrical connection 3				
		A (AI Modul) 1 2 3 4 shielding  B (AO Modul) 1 2 3 4 shielding C 1 2 3 4 5 6 7 8 shielding 		

Circuitry (socket/plug view) – NEDU-L1R2-V9		Circuitry		Electrical connection 2	
Electrical connection 3				No.	Wire colour ¹⁾
Wire colour ¹⁾	No.			1	BN
BN	1			2	BK
WH	2			3	BU
BU	3				
BK	4				
GY	5				
					


1) To IEC 757

Datasheet

Dimensions

Download CAD data → www.festo.com


NEBV-M12G8



[1] M12 socket, 8-pin

[2] Plug M12, 4-pin

NEDU-L1R2-V9




Type	B1	B2	B3	D1	D2	D6	D7	D8	H1	H2	H2	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
NEBV-M12G8	38.8	20.5	13.8	6.3	3.2	–	–	–	18.8	16.3	9.4	2500	500	44.9	41.7	17.5	15	15	13.3	7.1	3.6
NEDU-L1R2-V9	–	–	–	14.5	M12	20	4.5	5.3	–	–	–	5000	51.6	–	–	–	–	–	–	–	–

Ordering data

Electrical connection		Product weight [g]	Part no.	Type
M12 socket, 8-pin	• Plug M12, 4-pin • Plug M12, 4-pin	–	547888	NEBV-M12G8-KD-3-M12G4
M12 socket, 8-pin	• Open cable end, 3-wire • Open cable end, 5-wire	377	2903567	NEDU-L1R2-V9-M12G8-E-LE5-5R1-LE3-5R2

Datasheet

- Multi-pin plug distributor NEDU-L
- Multi-pin plug distributor
 - Particularly compact




General technical data		
Electrical connection		Straight plug, M12, 8-pin
		Straight socket, M8, 3-pin
Mounting position		Any
Operating voltage range	[V DC]	10 ... 30
	[A]	3
Current rating	[A]	3
	[A]	2
Acceptable current load per slot		
Ready status indication		Green LED
Status indication		Yellow LED
Degree of protection to EN 60529		IP68
Materials		
Housing		PBT-reinforced
Housing colour		Grey
Seals		FPM
Pin contacts		Nickel-plated and gold-plated
Socket		Nickel-plated brass
Note on materials		RoHS-compliant
Operating and environmental conditions		
Ambient temperature		[°C] −20 ... +80
Corrosion resistance class CRC ¹⁾		3

1) Corrosion resistance class CRC 3 to Festo standard FN 940070
High corrosion stress. Outdoor exposure under moderate corrosive conditions. Externally visible parts with primarily functional surface requirements which are in direct contact with a normal industrial environment.

Datasheet


Connection and display components

NEDU-L4R1-M8G3L-M12G8



- [1] Sensor connection, position 1
 [2] Sensor connection, position 2
 [3] Sensor connection, position 3
 [4] Sensor connection, position 4
 [5] Mounting holes
 [6] Multi-pin plug connection
 [7] Holder for inscription label (ASLR-L-55)
 [8] LED for status indication

NEDU-L6R1-M8G3L-M12G8



- [1] Sensor connection, position 1
 [2] Sensor connection, position 2
 [3] Sensor connection, position 3
 [4] Sensor connection, position 4
 [5] Sensor connection, position 5
 [6] Sensor connection, position 6
 [7] Mounting holes
 [8] Multi-pin plug connection
 [9] Holder for inscription label (ASLR-L-55)
 [10] LED for status indication

Circuitry (socket/plug view)

Individual connection			Allocation	Multi-pin plug connection	
	Position	Pin		Pin	
	1	1	+UB	5	
		3	-UB	7	
		4	Input ₁	1	
	2	1	+UB	5	
		3	-UB	7	
		4	Input ₂	2	
	3	1	+UB	5	
		3	-UB	7	
		4	Input ₃	3	
	4	1	+UB	5	
		3	-UB	7	
		4	Input ₄	4	
	5	1	+UB	5	
		3	-UB	7	
		4	Input ₅	6	
	6	1	+UB	5	
		3	-UB	7	
		4	Input ₆	8	

Datasheet



Dimensions

Download CAD data → www.festo.com

[1] Plug M12, 8-pin
[2] M8 socket, 3-pin


Type	B1	B2	B3	B4	D1 Ø	D2 Ø	H1	H2	H3	L1	L2	L3	L4	L5	L6
NEDU-L4R1-M8G3L-M12G8	24	17	12	8.4	4.2	4.2	23	18.2	9	87	80	14.5	21	13	3.5
NEDU-L6R1-M8G3L-M12G8	24	17	12	8.4	4.2	4.2	23	18.2	9	113	106	14.5	21	13	3.5

Ordering data			Weight [g]	Part no.	Type
Electrical connection					
Plug M12, 8-pin	4x socket M8, 3-pin		58	574586	NEDU-L4R1-M8G3L-M12G8
	6x socket, M8, 3-pin		74	574587	NEDU-L6R1-M8G3L-M12G8

Ordering data – Accessories					
Designation				Part no.	Type
Connecting cable					
	Socket M12, 8-pin, straight	Open cable end, 8-wire	Length: 2 m	525616	SIM-M12-8GD-2-PU
			Length: 5 m	525618	SIM-M12-8GD-5-PU
			Length: 10 m	570008	SIM-M12-8GD-10-PU
	Modular system for a choice of connecting cables			–	NEBU-... → Internet: nebu
Cover cap					
	Cover cap for closing off unused connections (10 pieces)		For M8 connections	177672	ISK-M8
Inscription label					
	Inscription labels in frames, pack of 1000		5x5 mm	574590	ASLR-L-55

Datasheet

Multi-pin plug distributors MPV



General technical data

Electrical connection technology for I/O	M8, 3-pin
Type of mounting	Either via H-rail or through-hole
Operating voltage range [V DC]	10 ... 30
Current rating [A]	4
Acceptable current load per slot [A]	1
Degree of protection to EN 60529	IP65, in assembled state

Materials

Housing	Reinforced PA6
Socket	Brass


Operating and environmental conditions

Ambient temperature [°C]	-20 ... +80
--------------------------	-------------

Datasheet


Connection and display components

MPV-E/A08-M8






- [1] Sensor connection, position 1
- [2] Sensor connection, position 2
- [3] Sensor connection, position 3
- [4] Sensor connection, position 4
- [5] Sensor connection, position 5
- [6] Sensor connection, position 6
- [7] Sensor connection, position 7
- [8] Sensor connection, position 8
- [9] Mounting holes
- [10] Holder for inscription label (IBS-6x10)
- [11] LED for status indication
- [12] Multi-pin plug connection

MPV-E/A12-M8




- [1] Sensor connection, position 1
- [2] Sensor connection, position 2
- [3] Sensor connection, position 3
- [4] Sensor connection, position 4
- [5] Sensor connection, position 5
- [6] Sensor connection, position 6
- [7] Sensor connection, position 7
- [8] Sensor connection, position 8
- [9] Sensor connection, position 9
- [10] Sensor connection, position 10
- [11] Sensor connection, position 11
- [12] Sensor connection, position 12
- [13] Mounting holes
- [14] Holder for inscription label (IBS-6x10)
- [15] LED for status indication
- [16] Multi-pin plug connection

Circuitry (socket/plug view)

Individual connection			Allocation	Pin	Multi-pin plug connection		Pin	Allocation	Individual connection	
	Position	Pin								Pin
	1	1	24 V DC	13		13	24 V DC	1	2	
		3	0 V	14/15		14/15	0 V	3		
		4	Input ₁	1		2	Input ₂	4		
	3	1	24 V DC	13		13	24 V DC	1	4	
		3	0 V	14/15		14/15	0 V	3		
		4	Input ₃	3		4	Input ₄	4		
	5	1	24 V DC	13		13	24 V DC	1	6	
		3	0 V	14/15		14/15	0 V	3		
		4	Input ₅	5		6	Input ₆	4		
	7	1	24 V DC	13		13	24 V DC	1	8	
		3	0 V	14/15		14/15	0 V	3		
		4	Input ₇	7		8	Input ₈	4		
	9	1	24 V DC	13		13	24 V DC	1	10	
		3	0 V	14/15		14/15	0 V	3		
		4	Input ₉	9		10	Input ₁₀	4		
	11	1	24 V DC	13		13	24 V DC	1	12	
		3	0 V	14/15		14/15	0 V	3		
		4	Input ₁₁	11		12	Input ₁₂	4		

Datasheet

Dimensions



Download CAD data → www.festo.com

- [1] Connecting cable
- [2] M8 socket, 3-pin
- [3] Switching status indication
- [4] Inscription label


Type	B1	B2	B3	D1	D2	D3 ø	H1	H2	H3	L1	L2	L3	L4	L5	L6	L7
MPV-E/A08-M8	45	39	29	M8	M3	4.2	126	19.5	15	98	90	18	14	12	9	4
MPV-E/A12-M8	45	39	29	M8	M3	4.2	126	19.5	15	126	118	18	14	12	9	4

Accessories

Ordering data		Weight [g]	Part no.	Type
Electrical connection				
Plug Sub-D, 15-pin	8x socket M8	100	177669	MPV-E/A08-M8
	12x socket M8	120	177670	MPV-E/A12-M8

Ordering data – Accessories				
Designation			Part no.	Type
Multi-pin plug connection				
	Plug socket with cable • Socket Sub-D, 15-pin • Open cable end, 15-wire	5 m	177673	KMPV-SUB-D-15-5
		10 m	177674	KMPV-SUB-D-15-10
	Socket Sub-D, 15-pin		177675	SD-SUB-D-BU15

Cover cap				
	Cover cap for sealing unused sockets (10 pieces)	For M8 connections	177672	ISK-M8

Inscription label				
	Inscription labels in frames, pack of 64	6x10 mm	18576	IBS-6x10

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change