


Service unit combinations MSB, MS series

FESTO



Festo Kernprogramm
Löst 80% Ihrer Automatisierungsaufgaben

Weltweit: Schnell verfügbar, auch langfristig
Gewohnt gut: Immer in Festo Qualität
Schnell zum Ziel: Einfache Auswahl

Das Festo Kernprogramm ist eine Vorauswahl der wichtigsten Funktionen und Produkte – Teil unseres gesamten Produktportfolios. Im Kernprogramm finden Sie das beste Preis-Leistungs-Verhältnis für Ihre Automatisierung.

Schauen Sie
nach dem
Stern!

Key features

Service unit components of the MS series

Solutions for every application

With its large product range, highly effective components and a wide choice of functions, the Festo MS series offers a complete concept for compressed air preparation. It is suitable for simple standard applications as well as for application-specific solutions with very high quality requirements. Available as individual components, pre-assembled

combinations ex-stock, application-specific combinations or complete turnkey solutions. The five sizes of the MS series achieve maximum flow rates with minimum space requirements.

CAD models and configurator

Convenient tools for planning and selecting application-specific individual devices and combinations. The product configurator can be used to configure customised solutions quickly and to transfer the order data without any hassle.

Engineering tools

Selection tool for choosing the right service unit combination without oversizing, and with the right air purity class:

→ www.festo.com/engineering/service-unit

Freely combinable functional modules

Pressure regulators, on/off and soft-start valves with safety function, filters, pressure and flow sensors, dryers, sensors and lubricators can be assembled into a suitable solution for every task. Thanks to the modular structure the components can be combined as required. The simple connection system saves time because there is no

need to disassemble the entire combination when replacing individual modules.

Many of the components are also UL and ATEX certified.

Air quality

This program supports configuring an appropriate service unit. Please insert the required air cleanliness either by your application or an ISO code or by direct selection of air filters.

Selection criteria: Application

Filter combination is proposed based upon your selected application

☐ standard pneumatics operation of valves and cylinders, e.g. in automotive industry, secondary packaging

☐ mining and building industry applications without special air cleanliness requirements

☐ application of pressure operated tools and machines pneumatic hammer, air engine, positioning with proportional valve

☐ electronic, flatpanel and solar industry, textile and paper production application with residual oil content <0.5 mg/m³

☐ painting, powder coating, air bearing application with residual oil content <0.01 mg/m³

☐ food and beverage industry, optics application with residual oil content <0.003 mg/m³ reduction of oil vapours and aromas

Selection criteria: ISO-class

Filter combination is proposed based upon the air cleanliness class according to ISO 8573-1:2010

particle : 4 * : oil

ISO

* Downstream from the compressor the water content is assumed to be ISO class 4, better classes can be achieved by applying an adsorption dryer PDAD or a membrane dryer LDM

Direct filter selection

Independent selection of filter combination

☐ 40 µm Filter

☐ 5 µm Filter

☐ 1 µm Fine Filter

☐ 0.01 µm Micro Filter *

☐ Active Carbon Filter



* To enhance the filter lifetime and in consequence the maintenance interval arrange a 1 µm Fine Filter in front of the 0.01 µm Micro Filter as a preliminary filter.

Integrated sensors

Pressure and flow sensors



- Maximum machine availability thanks to controlled processes
- Reliable compressed air preparation and system supply
- Integrated or stand-alone
- Easy to connect with M8/M12 plug

Safety functions

Soft-start/quick exhaust valves MS6-SV/MS9-SV



- Fast and reliable exhausting of systems up to Performance Level e, certified to EN ISO 13849-1
- Integrated soft-start function

Saving energy

Service unit combinations MSE6



- Fully automatic monitoring and regulation of compressed air supply
- Compressed air automatically shut off in stand-by mode
- Detection and notification of leakages
- Condition monitoring of relevant process data

Intelligent mix of sizes



- Optimum flow rate with a size that is up to 18% smaller
- Excellent energy efficiency
- Cost-optimised combinations – save up to 30%!

Size differences

Size	MS2	MS4	MS6	MS9	MS12
Grid dimension [mm]	25	40	62	90	124
Connection sizes	M5, QS-6	G1/8, G1/4, G3/8	G1/4, G3/8, G1/2, G3/4	G1/2, G3/4, G1, G1 1/4, G1 1/2	G1, G1 1/4, G1 1/2, G2
Standard nominal flow rate qn ¹⁾ [l/min]	350	1800	6500	20000	22000

1) Using pressure regulator MS-LR as an example

Key features

Note

Information

The next few pages provide a brief overview of the product range for the components of the MS series service units.

You can find detailed information and all the technical data in the documentation for the relevant service unit component.

Accessories such as connecting plates or mounting brackets can be ordered either via the configurator or separately.

Designing a service unit combination

The order of the individual service unit components within a combination is relevant for safety and functionality. The service unit components cannot be combined in any order in the flow direction. They are subject to restrictions and rules.

The configurator for the service unit combination MSB is a reliable and convenient way of combining the individual service unit components and ensures compliance with the applicable rules. As a result, you get a fully assembled unit, including UL or ATEX certification, if necessary.

When combining a unit from individually configured and ordered service unit components, the points on the right must be adhered to under all circumstances.

- Regulators MS-LFR/LR/LRP are only permissible in the flow direction with the same or decreasing pressure regulation range
- Filters MS-LFR/LF/LFM/LFX are only permissible in the flow direction with an increasing grade of filtration
- Lubricators MS-LOE are not permitted in the flow direction upstream of a filter MS-LFR/LFM/LF/LFX, water separator MS-LWS or membrane air dryer MS-LDM1
- A micro filter MS-LFM must be installed in the flow direction upstream of an activated carbon filter MS-LFX or membrane air dryer MS-LDM1
- A flow sensor SFAM cannot be installed directly downstream of a regulator MS-LFR/LR; a branching module MS-FRM must be positioned between them
- A soft-start/quick exhaust valve MS-SV must be the last service unit component in the flow direction

Product range for service unit components MS series

Type	Description	Size	Pneumatic connection					
			Push-in connector	Female thread			Connecting plate with thread	
				M	G	NPT	G	NPT
Combinations								
Service unit combinations MSB-FRC Datasheets → Internet: msb								
	Combinations of filter regulator and lubricator	4	–	–	1/8, 1/4	–	–	–
		6	–	–	1/4, 3/8, 1/2	–	–	–
Service unit combinations MSB Datasheets → Internet: msb								
	Certain predefined combinations	4	–	–	1/4	–	–	–
		6	–	–	1/2	–	–	–
	Freely configurable combinations	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
Service unit combinations MSE6 Datasheets → Internet: mse6								
	Combinations with fieldbus connection for measuring pressure, flow rate and consumption	6	–	–	–	–	1/2	–

Key features

Product range for service unit components MS series								
Type	Description	Size	Pneumatic connection					
			Push-in connector	Female thread			Connecting plate with thread	
				M	G	NPT	G	NPT
Individual devices								
Filter regulators MS-LFR			Datasheets → Internet: ms2-lfr; ms4-lfr; ms6-lfr; ms9-lfr; ms12-lfr					
	Filter and pressure regulator in a single device, grade of filtration 5 or 40 µm	2	QS-6	M5	–	–	–	–
		4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Filter regulators MS-LFR-B			Datasheets → Internet: ms4-lfr-b; ms6-lfr-b					
	Filter and pressure regulator in a single device in polymer housing, grade of filtration 5 or 40 µm	4	–	–	1/4	–	–	–
		6	–	–	1/2	–	–	–
Filter MS-LF			Datasheets → Internet: ms4-lf; ms6-lf; ms9-lf; ms12-lf					
	Grade of filtration 5 or 40 µm	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Fine and micro filters MS-LFM			Datasheets → Internet: ms4-lfm; ms6-lfm; ms9-lfm; ms12-lfm					
	Grade of filtration 0.01 or 1 µm	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Activated carbon filter MS-LFX			Datasheets → Internet: ms4-lfx; ms6-lfx; ms9-lfx; ms12-lfx					
	For removing liquid and gaseous oil particles	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Water separator MS-LWS			Datasheets → Internet: ms6-lws; ms9-lws; ms12-lws					
	Remove condensate from compressed air, maintenance-free	6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–

Key features

Product range for service unit components MS series								
Type	Description	Size	Pneumatic connection					
			Push-in connector	Female thread			Connecting plate with thread	
				M	G	NPT	G	NPT
Individual devices								
Pressure regulators MS-LR			Datasheets → Internet: ms2-lr; ms4-lr; ms6-lr; ms9-lr; ms12-lr					
	For setting the required operating pressure, 4 pressure regulation ranges	2	QS-6	M5	–	–	–	–
		4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Pressure regulators MS-LR-B			Datasheets → Internet: ms4-lr-b; ms6-lr-b					
	For setting the required operating pressure, in polymer housing	4	–	–	1/4	–	–	–
		6	–	–	1/2	–	–	–
Pressure regulators MS-LRB			Datasheets → Internet: ms4-lrb; ms6-lrb					
	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is at the front or rear.	4	–	–	1/4	–	1/8, 1/4, 3/8	–
		6	–	–	1/2	–	1/4, 3/8, 1/2, 3/4	–
Precision pressure regulators MS-LRP			Datasheets → Internet: ms6-lrp					
	For precisely setting the required operating pressure, 4 pressure regulation ranges, pressure hysteresis 0.02 bar	6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
Precision pressure regulators MS-LRPB			Datasheets → Internet: ms6-lrpb					
	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is at the front or rear.	6	–	–	1/2	–	1/4, 3/8, 1/2, 3/4	–
Lubricator MS-LOE			Datasheets → Internet: ms4-loe; ms6-loe; ms9-loe; ms12-loe					
	Add a precisely dosed amount of oil to the compressed air. The amount of oil mist is proportional to the compressed air flow rate.	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–

Key features

Product range for service unit components MS series								
Type	Description	Size	Pneumatic connection					
			Push-in connector	Female thread			Connecting plate with thread	
				M	G	NPT	G	NPT
Individual devices								
On/off valves MS-EM			Datasheets → Internet: ms4-em; ms6-em; ms9-em; ms12-em					
	Manually actuated on/off valve for pressurising and exhausting pneumatic systems.	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
On/off valves MS-EE								
	Electrically actuated on/off valve for pressurising and exhausting pneumatic systems.	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
On/off valves MS-EE-B			Datasheets → Internet: ms4-ee-b; ms6-ee-b					
	Electrically actuated on/off valve in polymer housing for pressurising and exhausting pneumatic systems.	4	–	–	1/4	–	–	–
		6	–	–	1/2	–	–	–
Soft-start valves MS-DL			Datasheets → Internet: ms4-dl; ms6-dl; ms12-dl					
	Pneumatically actuated soft-start valve for slowly pressurising and exhausting pneumatic systems.	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Soft-start valves MS-DE			Datasheets → Internet: ms4-de; ms6-de; ms12-de					
	Electrically actuated soft-start valve for slowly pressurising and exhausting pneumatic systems.	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
On/off valves MS-EDE-B			Datasheets → Internet: ms4-ed-e-b; ms6-ed-e-b					
	Electrically actuated soft-start valve in polymer housing for slowly pressurising and exhausting pneumatic systems.	4	–	–	1/4	–	–	–
		6	–	–	1/2	–	–	–
Soft-start/quick exhaust valves MS-SV			Datasheets → Internet: ms6-sv; ms9-sv					
	For building up pressure gradually and reducing pressure quickly and safely in pneumatic piping systems. Up to category 1, PL c.	6	–	–	1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
	Up to category 3, PL d. Up to category 4, PL e in the case of optional extension.	6	–	–	1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	Up to category 4, PL e.	6	–	–	1/2	–	1/4, 3/8, 1/2, 3/4	–

Key features


Product range for service unit components MS series								
Type	Description	Size	Pneumatic connection					
			Push-in connector	Female thread			Connecting plate with thread	
				M	G	NPT	G	NPT
Individual devices								
Membrane air dryer MS-LDM1 Datasheets → Internet: ms4-ldm; ms6-ldm								
	Wear-free membrane dryer with internal air consumption	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
Branching modules MS-FRM Datasheets → Internet: ms4-frm; ms6-frm; ms9-frm; ms12-frm								
	Compressed air distributors with 4 connections	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	–
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	–
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Distributor blocks MS-FRM-FRZ Datasheets → Internet: ms4-frm-frz; ms6-frm-frz								
	Compressed air distributors with 4 connections and half the grid width	4	–	–	–	–	–	–
		6	–	–	–	–	–	–
Flow sensors SFAM Datasheets → Internet: sfam								
	For absolute flow rate information and cumulative air consumption measurement	6	–	–	–	–	1/2	1/2
		9	–	–	–	–	1, 1 1/2	1, 1 1/2

Key features

Configurable service unit combinations MSB
Overview



- 3 sizes:
MSB4 – grid dimension 40 mm,
MSB6 – grid dimension 62 mm,
MSB9 – grid dimension 90 mm
- Threaded connections in the product housing or with connecting plates
- Type of mounting and flow direction can be optionally selected
- Can be configured in accordance with the ATEX directive for explosive atmospheres
- Food-safe (MSB4/MSB6)



Configurator

The configurator enables complex service unit combinations to be configured step by step. It is divided into a basic configuration and the individual service unit configurations. The technical parameters for the entire service unit combination are defined using the key features of the basic configuration. The service unit components are defined by both the configuration and the general technical conditions. You can navigate through your configuration using the menu [1]. All the key features available for selection can be found in drop-down lists [2]. Missing or incomplete information is indicated by an exclamation mark. Features shown against a grey background cannot be selected in the chosen configuration → "Conditions and excluded features" table. If you select a feature shown against a grey background, a red font will indicate that the configuration is incorrect. A dynamic graphic [3] and the order code [4] (→ type codes) are created in accordance with your current configuration.

Service unit combination MSB6

Close

Select features

Product list

My favourites

MSB6-AGD:D4:A1:J1:F1:I5-WP

4

1

Basic configuration

Basic function

Size

Connection size

Mounting type

EU certification

>>> Alternative flow direction

Service unit 1

Service unit equipment position 1

>>> Supply voltage 1

>>> Silencer 1

Service unit 2

Service unit 3

Service unit 4

Service unit 5

Service unit 6

Service unit 7

Basic configuration

Basic function

MSB Standard manifold

Size

6

2

Connection size

AGD Connecting plate G1/2

Mounting type

WP Mounting bracket

EU certification

None

>>> Alternative flow direction

Flow direction from left to right

Value Z: with LRB(O1-O6), LRPB(R1-R4) pressure output to the front

Service unit 1

Service unit equipment position 1

EE On-off valve, electrical

>>> Supply voltage 1

V24 24 V DC

>>> Silencer 1

S Silencer

Add to basket

2D/3D view

Accessories

Documentation

Data Sheet

Display Overview

Save as

Reset

Valid selection

request your price

531030

W - One week delivery time

3

EE DL LFR FRM LFM

V24 AS D7 40 004

S R M

D4 A1 J1 F1 I5

Key features


Information

General

The adjacent columns and the complete product range of service unit components MS series → page 3 provide a brief overview of the service unit components that are available in a specific size.

The clarification of the short code for a service unit component that is transferred to the order can be found from page 13 for size MSB4/MSB6 and from page 43 for MSB9.

You can find detailed information and all the technical data in the documentation for the relevant service unit component. Enter the short code of the service unit component (e.g. MS6-EE) in the search window of the product catalogue and select the documentation.



Note

Individual devices with selected key features are available for the configurable service unit combinations

→ Overview lists.

Additional key feature options can be selected via the configurable individual device.

1) Not available in all markets.

2) Polymer service unit components series MS basic

★ 531029 MSB4 (ISO) 532306 MSB4N (NPT)¹⁾

- Filter regulator MS4-LFR
- Filter regulator MS4-LFR-...-B²⁾
- Pressure regulator MS4-LR
- Pressure regulator MS4-LR-...-B²⁾
- Pressure regulator for manifold assembly MS4-LRB
- Filter MS4-LF
- Fine and micro filter MS4-LFM
- Activated carbon filter MS4-LFX
- Lubricator MS4-LOE
- On/off valve, manual MS4-EM1
- On/off valve, electric MS4-EE
- On/off valve, electric MS4-EE-...-B²⁾
- Soft-start valve, pneumatic MS4-DL
- Soft-start valve, electric MS4-DE
- Soft-start valve, electric MS4-EDE-...-B²⁾
- Membrane air dryer MS4-LDM1
- Branching module MS4-FRM

★ 531030 MSB6 (ISO) 532307 MSB6N (NPT)¹⁾

- Filter regulator MS6-LFR
- Filter regulator MS6-LFR-...-B²⁾
- Pressure regulator MS6-LR
- Pressure regulator MS6-LR-...-B²⁾
- Pressure regulator for manifold assembly MS6-LRB
- Precision pressure regulator MS6-LRP
- Precision pressure regulator for manifold assembly MS6-LRPB
- Filter MS6-LF
- Fine and micro filter MS6-LFM
- Activated carbon filter MS6-LFX
- Water separator MS6-LWS
- Lubricator MS6-LOE
- On/off valve, manual MS6-EM1
- On/off valve, electric MS6-EE
- On/off valve, electric MS6-EE-...-B²⁾
- Soft-start valve, pneumatic MS6-DL
- Soft-start valve, electric MS6-DE
- Soft-start valve, electric MS6-EDE-...-B²⁾
- Soft-start/quick exhaust valve MS6-SV
- Membrane air dryer MS6-LDM1
- Branching module MS6-FRM
- Flow sensor SFAM-62

552938 MSB9 (ISO + NPT)

- Filter regulator MS9-LFR
- Pressure regulator MS9-LR
- Filter MS9-LF
- Fine and micro filter MS9-LFM
- Activated carbon filter MS9-LFX
- Water separator MS9-LWS
- Lubricator MS9-LOE
- On/off valve, manual MS9-EM
- On/off valve, electric MS9-EE
- Soft-start/quick exhaust valve MS9-SV
- Branching module MS9-FRM
- Flow sensor SFAM-90

Notes on individual service unit components and their key features

MS-LFR and MS-LF:

- Grade of filtration with key feature E (40 µm) or C (5 µm)

MS-LRB/LRPB:

- Pressure output is at the rear, the pressure output is at the front if key feature Z (alternative flow direction) is selected

MS-LFM:

- Grade of filtration with key feature B (1 µm) or A (0.01 µm)
- Filter contamination sensor with key feature DA is a visual differential pressure display with red/green range
- Filter contamination sensor with key feature DP is an electric filter contamination indicator with switching output

MS-EE and MS-DE:

- The supply voltage with key feature 10V24 is permissible only to a max. operating pressure of 10 bar.
- With the supply voltages with key feature V24/V110/V230 the solenoid actuator has a non-detenting/detenting manual override, with feature 10V24 just a non-detenting manual override

MS-LDM1:

- Flow cartridge with key feature P05, P10 only for MSB4; with key feature P20, P30, P40 only for MSB6

Key features

Conditions and exclusions of key features

Note

If a service unit combination is configured with ISO thread, the individual devices also have ISO thread (e.g. the outlets of the branching module MS-FRM), individual devices with integrated MS pressure gauge (e.g. the pressure regulator MS-LR) have a display scale in [bar].

If you configure a service unit combination with NPT thread, the other pneumatic connections have NPT threads and integrated MS pressure gauges with the display unit [psi].

In addition to the conditions and exclusions mentioned here, you can also obtain information by selecting the information button next to some of the selection lists in the configurator.

General rules

- Selection of minimum 2 to maximum 10 service unit components
- Lubricators MS-LOE are not permitted in the flow direction upstream of a filter MS-LFR/LFM/LF/LFX, water separator MS-LWS or membrane air dryer MS-LDM1
- A micro filter MS-LFM must be installed in the flow direction upstream of an activated carbon filter MS-LFX or membrane air dryer MS-LDM1
- Mounting bracket for large wall clearance WPB must be selected if the combination includes the soft-start/quick exhaust valve MS-SV-E or the block-mountable regulator MS-LRB without angled outlet block
- Regulators MS-LFR/LR/LRP are only permissible in the flow direction with the same or decreasing pressure regulation range
- Filters MS-LFR/LF/LFM/LFX are only permissible in the flow direction with an increasing grade of filtration

Rules specific to the service unit component

MS-LFM:

- Only a manual condensate drain can be used with MS4-LFM with plastic bowl

MS-DL:

- No filter MS-LFR/LF/LFM with fully automatic condensate drain downstream of MS4-DL

SFAM:

- Connection size of the service unit combination with SFAM-62 must be at least G1/2, with SFAM-90 at least G3/4
- A SFAM cannot be installed immediately downstream of a regulator MS-LFR/LR; a branching module MS-FRM must be positioned between them
- SFAM-90 only in flow direction from left to right

MS-SV-D/E:

- Must be the last service unit component in the flow direction

UL certification

Certified by UL as a component for the market in USA and Canada for a standard environment. Can be selected with code UL1 in the order section "UL certification".

- Operating pressure/pressure regulation range max. 10 bar
- Supply voltage with on/off valve MS-EE or soft-start valve MS-DE max. 24 V DC

Key features

ATEX certification

A configured service unit consisting of mechanical service unit components can be used in zones 1 and 2 of explosive gas atmospheres and in zones 21 and 22 of explosive dust atmospheres. The following service unit components are approved and can be selected using the code EX4 in the order section "EU certification":

- Filter regulator MS4/6/9-LFR
- Pressure regulator MS4/6/9-LR
- Pressure regulator for manifold assembly MS4/6-LRB

- Precision pressure regulator MS6-LRP
- Precision pressure regulator for manifold assembly MS6-LRPB
- Filter MS4/6/9-LF
- Fine and micro filter MS4/6/9-LFM
- Activated carbon filter MS4/6/9-LFX
- Water separator MS6/9-LWS
- Lubricator MS4/6-LOE
- On/off valve, manual MS4/6-EM1, MS9-EM
- Soft-start valve, pneumatic MS4/6-DL
- Membrane air dryer MS4/6-LDM1
- Branching module MS4/6/9-FRM

A configured service unit combination consisting of mechanical and electric service unit components can be used in zone 2 of explosive gas atmospheres and in zone 22 of explosive dust atmospheres. In this case, code EX2 must be selected in the order section "EU certification". The following electric service unit components are approved in addition to the mechanical service unit components:

- On/off valve, electric MS4/6/9-EE

- Soft-start valve, electric MS4/6-DE
- Flow sensor SFAM
- Supplied with special accessories, e.g. mounting brackets, module connectors, connecting plates with earthing screws
- Only connecting plates with G thread can be used
- Lubricated operation not permissible
- On/off valve MS-EE or soft-start valve MS-DE only with 24 V supply voltage

EU certification	EX2	EX4
MSB4/6		
ATEX category for gas	II 3G	II 2G
Type of ignition protection for gas	Ex nA IIC T4 X Gc	Ex h IIC T6 Gb X
ATEX category for dust	II 3D	II 2D
Type of ignition protection for dust	Ex tc IIIC T105°C X Dc IP65	Ex h IIIC T60°C Db X
Explosion-proof ambient temperature	-10 °C ≤ Ta ≤ +60 °C	
	+5 °C ≤ Ta ≤ +60 °C ¹⁾	
	+2 °C ≤ Ta ≤ +50 °C ²⁾	
Explosion protection certification outside the EU	EPL Dc (GB) EPL Gc (GB)	EPL Db (GB) EPL Gb (GB)
CE marking (see declaration of conformity) ³⁾	To EU Explosion Protection Directive (ATEX)	
	To EU EMC Directive	–
	To EU Low Voltage Directive	–
	To EU RoHS Directive	–
	To EU Machinery Directive	–
UKCA marking (see declaration of conformity) ³⁾	According to UK explosion regulations	
	According to UK EMC regulations	–
	In accordance with UK electrical equipment	–
	According to UK RoHS regulations	–
	According to UK regulations for machines	–
Certificate issuing authority ³⁾	Intertek UK-MCR-0086	

1) When using a service unit component with manual, semi-automatic or fully automatic condensate drain.

2) When using a membrane air dryer MS4/6-LDM1.

3) More information: www.festo.com/catalogue/MSB → Support/Downloads.

Key features

EU certification	EX2	EX4
MSB9		
ATEX category for gas	II 3G	II 2G
Type of ignition protection for gas	Ex nA IIC T5 X Gc	Ex h IIC T6 Gb X
ATEX category for dust	II 3D	II 2D
Type of ignition protection for dust	Ex tc IIIB T95°C X Dc IP54	Ex h IIIC T60°C Db X
Explosion-proof ambient temperature	$-10\text{ °C} \leq T_a \leq +50\text{ °C}$	$-10\text{ °C} \leq T_a \leq +60\text{ °C}$
	$+5\text{ °C} \leq T_a \leq +50\text{ °C}^{1)}$	$+5\text{ °C} \leq T_a \leq +60\text{ °C}^{1)}$
Explosion protection certification outside the EU	EPL Dc (GB) EPL Gc (GB)	EPL Db (GB) EPL Gb (GB)
CE marking (see declaration of conformity) ²⁾	To EU Explosion Protection Directive (ATEX)	
	To EU EMC Directive	–
	To EU Machinery Directive	–
	To EU RoHS Directive	–
	To EU Low Voltage Directive	–
UKCA marking (see declaration of conformity) ²⁾	According to UK explosion regulations	
	According to UK EMC regulations	–
	According to UK regulations for machines	–
	According to UK RoHS regulations	–
	In accordance with UK electrical equipment	–

1) When using a service unit component with manual, semi-automatic or fully automatic condensate drain.

2) More information: www.festo.com/catalogue/MSB → Support/Downloads.

Type codes

001	Series	
MSB	Service unit component MS series	

002	Size	
4	Grid dimension 40 mm	

003	Pneumatic connection	
1/8	Female thread G1/8	
1/4	Female thread G1/4	
AGA	Sub-base G1/8	
AGB	Sub-base G1/4	
AGC	Sub-base G3/8	
AQK	Sub-base NPT1/8	
AQN	Sub-base NPT1/4	
AQP	Sub-base NPT3/8	

004	Service unit component equipment	
...	For selection, see overview list	

005	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
WPB	Mounting bracket for large wall gap	
WPM	Mounting bracket for hooking in service unit components	

006	EU certification	
	None	
EX2	II 3GD to EU Explosion Protection Directive (ATEX)	
EX4	II 2GD	

007	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	

008	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Type codes

001	Series	
MSB	Service unit component MS series	

002	Size	
6	Grid dimension 62 mm	

003	Pneumatic connection	
1/4	Female thread G1/4	
3/8	Female thread G3/8	
1/2	Female thread G1/2	
AGB	Sub-base G1/4	
AGC	Sub-base G3/8	
AGD	Sub-base G1/2	
AGE	Sub-base G3/4	
AQN	Sub-base NPT1/4	
AQP	Sub-base NPT3/8	
AQR	Sub-base NPT1/2	
AQS	Sub-base NPT3/4	

004	Service unit component equipment	
...	For selection, see overview list	

005	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
WPB	Mounting bracket for large wall gap	
WPM	Mounting bracket for hooking in service unit components	

006	EU certification	
	None	
EX2	II 3GD to EU Explosion Protection Directive (ATEX)	
EX4	II 2GD	

007	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	

008	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Type codes

001	Series		005	Service unit component equipment	
MSB	Service unit component MS series		...	For selection, see overview list	
002	Size		006	Type of mounting	
4	Grid dimension 40 mm			Without mounting bracket	
003	Thread type		WP	Mounting bracket basic design	
N	NPT thread		WPB	Mounting bracket for large wall gap	
			WPM	Mounting bracket for hooking in service unit components	
004	Pneumatic connection, inch		007	Flow direction	
1/8	Female thread NPT 1/8			Flow direction from left to right	
1/4	Female thread NPT 1/4		Z	Flow direction from right to left	
AQK	Sub-base NPT1/8				
AQN	Sub-base NPT1/4				
AQP	Sub-base NPT3/8				

Type codes

001	Series	
MSB	Service unit component MS series	

002	Size	
6	Grid dimension 62 mm	

003	Thread type	
N	NPT thread	

004	Pneumatic connection, inch	
1/4	Female thread NPT 1/4	
3/8	Female thread NPT 3/8	
1/2	Female thread NPT 1/2	
AQN	Sub-base NPT1/4	
AQP	Sub-base NPT3/8	
AQR	Sub-base NPT1/2	
AQS	Sub-base NPT3/4	

005	Service unit component equipment	
...	For selection, see overview list	

006	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
WPB	Mounting bracket for large wall gap	
WPM	Mounting bracket for hooking in service unit components	

007	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	
		Size: 4	Size: 6
Soft-start valve MS-DL, pneumatically actuated			
A1	MS-DL	Soft-start valve, pneumatic	
A2	MS-DL-AD7 ¹⁾	Pneumatic soft-start valve, with pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa)	
Soft-start valve MS-DE, electrically actuated			
B1	MS-DE-V24	Soft-start valve, electric, (plug pattern to EN 175301), MO (manual override) non-detenting/detenting, 24 V DC, 0.4 ... 1.4 MPa	0.4 ... 1.8 MPa
B2	MS-DE-V110	Soft-start valve, electric, (plug pattern to EN 175301), MO (manual override) non-detenting/detenting, 110 V AC, 0.4 ... 1.4 MPa	0.4 ... 1.8 MPa
B3	MS-DE-V230	Soft-start valve, electric, (plug pattern to EN 175301), MO (manual override) non-detenting/detenting, 230 V AC, 0.4 ... 1.4 MPa	0.4 ... 1.8 MPa
B4	MS-DE-10V24	Soft-start valve, electric, (plug pattern to EN 175301), MO (manual override) non-detenting, 24 V DC, 0.4 ... 1.0 MPa	
B5	MS-DE-V24-EX2 ¹⁾	Soft-start valve, electric, (plug pattern to EN 175301), MO (manual override) non-detenting/detenting, 24 V DC, ATEX certification, II 3GD, 0.4 ... 1.4 MPa	0.4 ... 1.8 MPa
Soft-start valve MS-EDE, electrically actuated			
B20B	MS-EDE-V24-B ²⁾	Soft-start valve (polymer) 3/2-way valve, electric, 24 V DC, MO non-detenting/detenting, 0.3 ... 0.7 MPa	
B21B	MS-EDE-V24-F1A-B ²⁾	Soft-start valve (polymer) 3/2-way valve, electric, 24 V DC, MO non-detenting/detenting. Recommended for production plants for the manufacture of lithium-ion batteries (Cu<=1%, Zn<=1%, Ni<=1%), 0.3 ... 0.7 MPa	
On/off valve MS-EM1, manually actuated			
C3)	MS-EM1	On/off valve 0 ... 1.4 MPa	0 ... 1.8 MPa
C4)	MS-EM1-S	On/off valve with silencer 0 ... 1.4 MPa	0 ... 1.8 MPa
C6)	MS-EM1-R	On/off valve, red rotary knob 0 ... 1.4 MPa	0 ... 1.8 MPa
C7)	MS-EM1-R-S	On/off valve, red rotary knob, with silencer 0 ... 1.4 MPa	0 ... 1.8 MPa
C8)	MS-EM1-F1A ¹⁾	Recommended for production plants for the manufacture of lithium-ion batteries (Cu<=1%, ,Zn<=1%, Ni<=1%) 0 ... 1.4 MPa	
On/off valve MS-EE, electrically actuated			
D1	MS-EE-V24	On/off valve, electric, (plug pattern to EN 175301), MO (manual override) non-detenting/detenting, 24 V DC, 0.4 ... 1.4 MPa	0.4 ... 1.8 MPa
D1B	MS-EE-V24-B ²⁾	Soft-start valve (polymer) 3/2-way valve, electric, 24 V DC, MO non-detenting/detenting2, 0.3 ... 0.7 MPa	
D2	MS-EE-V110	On/off valve, electric, (plug pattern to EN 175301), MO (manual override) non-detenting/detenting, 110 V AC, 0.4 ... 1.4 MPa	0.4 ... 1.8 MPa
D3	MS-EE-V230	On/off valve, electric, (plug pattern to EN 175301), MO (manual override) non-detenting/detenting, 230 V AC, 0.4 ... 1.4 MPa	0.4 ... 1.8 MPa
D4	MS-EE-V24-S	On/off valve, with silencer, electric, (plug pattern to EN 175301), MO (manual override) non-detenting/detenting, 24 V DC, 0.4 ... 1.4 MPa	0.4 ... 1.8 MPa
D5	MS-EE-V110-S	On/off valve, with silencer, electric, (plug pattern to EN 175301), MO (manual override) non-detenting/detenting, 110 V AC, 0.4 ... 1.4 MPa	0.4 ... 1.8 MPa
D6	MS-EE-V230-S	On/off valve, with silencer, electric, (plug pattern to EN 175301), MO (manual override) non-detenting/detenting, 230 V AC, 0.4 ... 1.4 MPa	0.4 ... 1.8 MPa
D7	MS-EE-10V24	On/off valve, electric, (plug pattern to EN 175301), MO (manual override) non-detenting, 24 V DC, 0.4 ... 1.0 MPa	

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

2) Polymer service unit components series MS Basic, female thread only with G1/4 (MS4) or G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
On/off valve MS-EE, electrically actuated			
D9	MS-EE-V24-EX2 ¹⁾	On/off valve, electric, (plug pattern to EN 175301), MO (manual override) non-detenting/detenting, 24 V DC, ATEX certification, II 3GD, 0.4 ... 1.4 MPa	0.4 ... 1.8 MPa
D10	MS-EE-V24-S-EX2 ¹⁾	On/off valve, with silencer, electric, (plug pattern to EN 175301), MO (manual override) non-detenting/detenting, 24 V DC, ATEX certification, II 3GD, 0.4 ... 1.4 MPa	0.4 ... 1.8 MPa
D12	MS-EE-10V24-AD7 ¹⁾	Electric on/off valve, electric, (plug pattern to EN 175301), MO (manual override) non-detenting, 24 V DC, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact, 0.4 ... 1.0 MPa	
D13	MS-EE-10V24-S-AD7 ¹⁾	On/off valve, with silencer, electric, (plug pattern to EN 175301), MO (manual override) non-detenting, 24 V DC, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O, 0.4 ... 1.0 MPa	
D14	MS-EE-10V24P-AD7 ¹⁾	On/off valve, electric, M12 to IEC 61076-2-101, 24 V DC, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact 0.4 ... 1.0 MPa	MO (manual override) non-detenting/detenting MO (manual override) non-detenting
D15	MS-EE-10V24P-S-AD7 ¹⁾	On/off valve, with silencer, electric, M12 to IEC 61076-2-101, MO (manual override) non-detenting/detenting, 24 V DC, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact, 0.4 ... 1.0 MPa	
D19	MS-EE-10V24P ¹⁾	On/off valve, electric, M12 to IEC 61076-2-101, MO (manual override) non-detenting/detenting, 24 V DC, 0.4 ... 1.0 MPa	
D20	MS-EE-10V24P-S ¹⁾	On/off valve, with silencer, electric, M12 to IEC 61076-2-101, MO (manual override) non-detenting/detenting, 24 V DC, 0.4 ... 1.0 MPa	
D21B	MS-EE-V24-F1A-B ¹⁾²⁾	Soft-start valve (polymer) 3/2-way valve, electric, 24 V DC, MO non-detenting/detenting, recommended for production plants for manufacturing Li-ion batteries (Cu≤1%, Zn≤1%, Ni≤1%), 0.3 ... 0.7 MPa	
Branching module MS-FRM/distributor block MS-FRM-FRZ			
F1	MS-FRM	Branching module	
F2	MS-FRM-I	Branching module with integrated non-return function	
F3	MS-FRM-Y	Branching module with pressure switch PEV without display, plug socket, EN 175301, type A, square, max. input pressure 1.2 MPa	
F6	MS-FRM-AD1	Branching module with pressure sensor with LCD display, M8 plug, PNP, 3-pin Max. input pressure 1.0 MPa	
F7	MS-FRM-I-AD1	Polymer service unit component Branching module with non-return function, with pressure sensor with LCD display, M8 plug, PNP, 3-pin, Max. input pressure 1.0 MPa	
F8	MS-FRM-M12	Branching module pressure switch PEV without display, plug socket, round, M12, 4-pin, max. input pressure 1.2 MPa	
F9	MS-FRM-I-M12	Branching module with non-return function, pressure switch PEV without display, plug socket, round, M12, 4-pin, max. input pressure 1.2 MPa	
F10	MS-FRM-AD3	Branching module with pressure sensor with LCD display, M12 plug, PNP, 4-pin, analogue output 4 ... 20 mA, Max. input pressure 1.0 MPa	
F11	MS-FRM-I-AD3	Branching module with non-return function, with pressure sensor with LCD display, M12 plug, PNP, 4-pin, analogue output 4 ... 20 mA, Max. input pressure 1.0 MPa	
F12	MS-FRM-AD7	Branching module with pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/O contact, Max. input pressure 1.0 MPa	
F13	MS-FRM-I-AD7	Branching module with non-return function, with pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact, Max. input pressure 1.0 MPa	
F14	MS-FRM-FRZ	Branching module, half grid dimension (20 mm)	Branching module, half grid dimension (31 mm)
F15	MS-FRM-AD12	Branching module with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20mA, Max. input pressure 1.0 MPa	
F16	MS-FRM-I-AD12	Branching module with non-return function, with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20mA, Max. input pressure 1.0 MPa	

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

2) Polymer service unit components series MS Basic, female thread only with G1/4 (MS4) or G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
Size: 4			
Branching module MS-FRM/distributor block MS-FRM-FRZ			
F17	MS-FRM-AD11	Branching module with pressure sensor, with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4 ... 20 mA Max. input pressure 1.0 MPa	
F18	MS-FRM-I-AD11	Branching module with non-return function, with pressure sensor, with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4 ... 20 mA Max. input pressure 1.0 MPa	
F19	MS-FRM-F1A	Branching module, recommended for production facilities for the manufacture of lithium-ion batteries (Cu≤1%, Zn≤1%, Ni≤1%)	
Soft-start valve MS-EDE, electrically actuated			
G3	MS-LDM1-P05	Membrane air dryer, flow cartridge 50 l/min, 0.3 ... 1.25 MPa	–
G4	MS-LDM1-P10	Membrane air dryer, flow cartridge 100 l/min, 0.3 ... 1.25 MPa	–
G5	MS-LDM1-P20	–	Membrane air dryer, flow cartridge 200 l/min, 0.3 ... 1.25 MPa
G6	MS-LDM1-P30	–	Membrane air dryer, flow cartridge 300 l/min, 0.3 ... 1.25 MPa
G7	MS-LDM1-P40	–	Membrane air dryer, flow cartridge 400 l/min, 0.3 ... 1.25 MPa
Filter MS-LF			
H1	MS-LF-ERV	Filter, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), 0.2 ... 1.2 MPa	
H2	MS-LF-ERM	Filter, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain	
H3	MS-LF-CRM	Filter, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain	
H4	MS-LF-CRV	Filter, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), 0.2 ... 1.2 MPa	
H5	MS-LF-CUM	Filter, 5 µm grade of filtration, metal bowl, manual condensate drain	
H6	MS-LF-CUV	Filter, 5 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), 0.2 ... 1.2 MPa	
H7	MS-LF-EUV	Filter, 40 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), 0.2 ... 1.2 MPa	
H8	MS-LF-EUM	Filter, 40 µm grade of filtration, metal bowl, manual condensate drain	
Fine and micro filter MS-LFM			
I1	MS-LFM-BRM	Fine and micro filter, 1 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain	
I2	MS-LFM-BRV	–	Fine and micro filter, 1 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), 0.2 ... 1.2 MPa
I3	MS-LFM-ARM	Fine and micro filter, 0.01 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain	
I4	MS-LFM-ARV	–	Fine and micro filter, 0.01 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), 0.2 ... 1.2 MPa
I5	MS-LFM-ARM-DA	Fine and micro filter, 0.01 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, optical differential pressure display	
I6	MS-LFM-ARV-DA	–	Fine and micro filter, 0.01 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), optical differential pressure display
I7	MS-LFM-BUV	Fine and micro filter, 1 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), 0.2 ... 1.2 MPa	
I8	MS-LFM-AUV	Fine and micro filter, 0.01 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), 0.2 ... 1.2 MPa	
I9	MS-LFM-BUV-DA	Fine and micro filter, 1 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), differential pressure display, 0.2 ... 1.2 MPa	
I10	MS-LFM-BRM-DA	Fine and micro filter, 1 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, optical differential pressure display	

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description Size: 4	Size: 6
Fine and micro filter MS-LFM			
I11	MS-LFM-BRV-DA	–	Fine and micro filter, 1 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), optical differential pressure display, 0.2 ... 1.2 MPa
I12	MS-LFM-AUV-DA	Fine and micro filter, 0.01 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain	
I13	MS-LFM-BRM-DP	Fine and micro filter, 1 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, filter contamination indicator, M8 plug, positive switching output signal PNP, 3-pin, 0 ... 1.0 MPa	
I14	MS-LFM-BRV-DP	–	Fine and micro filter, 1 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), differential pressure display, filter contamination indicator, M8 plug, positive switching output signal PNP, 3-pin, 0.2 ... 1.2 MPa
I15	MS-LFM-ARM-DP	Fine and micro filter, 0.01 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, filter contamination indicator, M8 plug, positive switching output signal PNP, 3-pin, 0 ... 1.0 MPa	
I16	MS-LFM-ARV-DP	–	Fine and micro filter, 0.01 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), differential pressure display, filter contamination indicator, M8 plug, positive switching output signal PNP, 3-pin, 0.2 ... 1.2 MPa
I17	MS-LFM-BUV-DP	Fine and micro filter, 1 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), differential pressure display, filter contamination indicator, M8 plug, positive switching output signal PNP, 3-pin, 0.2 ... 1.2 MPa	
I18	MS-LFM-AUV-DP	Fine and micro filter, 0.01 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), differential pressure display, filter contamination indicator, M8 plug, positive switching output signal PNP, 3-pin, 0.2 ... 1.2 MPa	
I23	MS-LFM-BUV-HF	–	Fine and micro filter, 1 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), high flow rate, 0.2 ... 1.2 MPa
I24	MS-LFM-AUV-HF	–	Fine and micro filter, 0.01 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), high flow rate, 0.2 ... 1.2 MPa
I25	MS-LFM-BUV-HF-DA	–	Fine and micro filter, 1 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), high flow rate, optical differential pressure display 0.2 ... 1.2 MPa
I26	MS-LFM-AUV-HF-DA	–	Fine and micro filter, 0.01 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), high flow rate, optical differential pressure display, 0.2 ... 1.2 MPa
I27	MS-LFM-BUV-HF-DP	–	Fine and micro filter, 1 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), high flow rate, differential pressure display, filter contamination indicator, M8 plug, positive switching output signal PNP, 3-pin, 0.2 ... 1.2 MPa
I28	MS-LFM-AUV-HF-DP	–	Fine and micro filter, 0.01 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), high flow rate, differential pressure display, filter contamination indicator, M8 plug, positive switching output signal PNP, 3-pin, 0.2 ... 1.2 MPa

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description Size: 4	Size: 6
Fine and micro filter MS-LFM			
I29	MS-LFM-ARV-HP ¹⁾	–	Fine and micro filter, 0.01 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), sealing and purge air application, 0.2 ... 1.2 MPa
I30	MS-LFM-BRV-HP ¹⁾	–	Fine and micro filter, 1 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), sealing and purge air application, 0.2 ... 1.2 MPa
I31	MS-LFM-ARV-HP-DP ¹⁾	–	Fine and micro filter, 0.01 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), sealing and purge air application, differential pressure display, filter contamination indicator, M8 plug, positive switching output signal PNP, 3-pin, 0.2 ... 1.2 MPa
I32	MS-LFM-BRV-HP-DP ¹⁾	–	Fine and micro filter, 1 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), sealing and purge air application, differential pressure display, filter contamination indicator, M8 plug, positive switching output signal PNP, 3-pin, 0.2 ... 1.2 MPa
Filter regulator MS-LFR			
J1	MS-LFR-D7-ERM-AS	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J2	MS-LFR-D7-ERV-AS	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), input pressure 0.2 ... 1.2 MPa, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J3	MS-LFR-D7-CRM-AS	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J4	MS-LFR-D7-CRV-AS	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), input pressure 0.2 ... 1.2 MPa, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J5	MS-LFR-D6-ERM-AS	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J5B	MS-LFR-D6-EPM-AG-BAR-B ²⁾	Filter regulator, (polymer), 40 µm grade of filtration, plastic bowl, manual condensate drain, input pressure: 1.0 MPa, integrated MS pressure gauge with outer scale in bar and inner scale in psi, pressure regulation range 0.05 ... 0.7 MPa	
J6	MS-LFR-D6-ERV-AS	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), input pressure 0.2 ... 1.2 MPa, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J6B	MS-LFR-D6-EPVC-AG-BAR-B ²⁾	Filter regulator, (polymer), 40 µm grade of filtration, plastic bowl, fully automatic condensate drain (normally closed), input pressure: 1.0 MPa, integrated MS pressure gauge with outer scale in bar and inner scale in psi, pressure regulation range 0.05 ... 0.7 MPa	
J7	MS-LFR-D6-CRM-AS	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J7B	MS-LFR-D6-CPM-AG-BAR-B ²⁾	Filter regulator, (polymer), 5 µm grade of filtration, plastic bowl, manual condensate drain, input pressure: 1.0 MPa, integrated MS pressure gauge with outer scale in bar and inner scale in psi, pressure regulation range 0.05 ... 0.7 MPa	

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

2) Polymer service unit components series MS basic

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
Filter regulator MS-LFR			
J8	MS-LFR-D6-CRV-AS	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), input pressure 0.2 ... 1.2 MPa, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J8B	MS-LFR-D6-CPVC-AG-BAR-B ¹⁾	Filter regulator, (polymer), 5 µm grade of filtration, plastic bowl, fully automatic condensate drain (normally closed), input pressure: 1.0 MPa, integrated MS pressure gauge with outer scale in bar and inner scale in psi, pressure regulation range 0.05 ... 0.7 MPa	
J9	MS-LFR-D7-CUM-AS	Filter regulator, 5 µm grade of filtration, metal bowl, manual condensate drain, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J10	MS-LFR-D7-CUV-AS	Filter regulator, 5 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), input pressure 0.2 ... 1.2 MPa, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J11	MS-LFR-D7-EUM-AS	Filter regulator, 40 µm grade of filtration, metal bowl, manual condensate drain, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J12	MS-LFR-D7-EUV-AS	Filter regulator, 40 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), input pressure 0.2 ... 1.2 MPa, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J13	MS-LFR-D7-ERM-AD1-AS	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J14	MS-LFR-D7-ERV-AD1-AS	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), with pressure sensor with LCD display, M8 plug, PNP, 3-pin (input pressure 0.2 ... 1 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J15	MS-LFR-D7-CRM-AD1-AS	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, with pressure sensor with LCD display, M8 plug, PNP, 3-pin, (max. input pressure 1 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J16	MS-LFR-D7-CRV-AD1-AS	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), with pressure sensor with LCD display, M8 plug, PNP, 3-pin (input pressure 0.2 ... 1 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J17	MS-LFR-D6-ERM-AD1-AS	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, with pressure sensor with LCD display, M8 plug, PNP, 3-pin, (max. input pressure 1 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J18	MS-LFR-D6-ERV-AD1-AS	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), with pressure sensor with LCD display, M8 plug, PNP, 3-pin (input pressure 0.2 ... 1 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J19	MS-LFR-D6-CRM-AD1-AS	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, with pressure sensor with LCD display, M8 plug, PNP, 3-pin, (max. input pressure 1 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J20	MS-LFR-D6-CRV-AD1-AS	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), with pressure sensor with LCD display, M8 plug, PNP, 3-pin (input pressure 0.2 ... 1 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J21	MS-LFR-D7-EUM-AD1-AS	Filter regulator, 5 µm grade of filtration, metal bowl, manual condensate drain, with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J22	MS-LFR-D7-EUV-AD1-AS	Filter regulator, 40 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), with pressure sensor with LCD display, M8 plug, PNP, 3-pin (input pressure 0.2 ... 1 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J23	MS-LFR-D7-CUM-AD1-AS	Filter regulator, 5 µm grade of filtration, metal bowl, manual condensate drain, with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	

1) Polymer service unit components series MS basic

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
Filter regulator MS-LFR			
J23	MS-LFR-D7-CUV-AD1-AS	Filter regulator, 5 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), with pressure sensor with LCD display, M8 plug, PNP, 3-pin (input pressure 0.2 ... 1 MPa), lockable rotary knob pressure regulation range 0.05 ... 1.2 MPa	
J24	MS-LFR-D7-CUV-AD1-AS	Filter regulator, 5 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), with pressure sensor with LCD display, M8 plug, PNP, 3-pin (input pressure 0.2 ... 1 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J35	MS-LFR-D7-ERM-AD7-AS	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, lockable rotary knob, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), pressure regulation range 0.05 ... 1.0 MPa	
J36	MS-LFR-D7-ERV-AD7-AS	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), lockable rotary knob, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), pressure regulation range 0.05 ... 1.0 MPa	
J37	MS-LFR-D7-CRM-AD7-AS	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, lockable rotary knob, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), pressure regulation range 0.05 ... 1.0 MPa	
J38	MS-LFR-D7-CRV-AD7-AS	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), lockable rotary knob, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), pressure regulation range 0.05 ... 1.0 MPa	
J39	MS-LFR-D6-ERM-AD7-AS	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, lockable rotary knob, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), pressure regulation range 0.05 ... 0.7 MPa	
J40	MS-LFR-D6-ERV-AD7-AS	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), lockable rotary knob, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), pressure regulation range 0.05 ... 0.7 MPa	
J41	MS-LFR-D6-CRM-AD7-AS	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, lockable rotary knob, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), pressure regulation range 0.05 ... 0.7 MPa	
J42	MS-LFR-D6-CRV-AD7-AS	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), lockable rotary knob, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), pressure regulation range 0.05 ... 0.7 MPa	
J43	MS-LFR-D7-EUM-AD7-AS	Filter regulator, 40 µm grade of filtration, metal bowl, manual condensate drain, lockable rotary knob, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), pressure regulation range 0.05 ... 1.0 MPa	
J44	MS-LFR-D7-EUV-AD7-AS	Filter regulator, 40 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), lockable rotary knob, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), pressure regulation range 0.05 ... 1.0 MPa	
J45	MS-LFR-D7-CUM-AD7-AS	Filter regulator, 5 µm grade of filtration, metal bowl, manual condensate drain, lockable rotary knob, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), pressure regulation range 0.05 ... 1.0 MPa	
J46	MS-LFR-D7-CUV-AD7-AS	Filter regulator, 5 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), lockable rotary knob, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), pressure regulation range 0.05 ... 1.0 MPa	
J79	MS-LFR-D7-ERM-RG-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, integrated MS pressure gauge, red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J80	MS-LFR-D7-ERV-RG-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), input pressure 0.2 ... 1.2 MPa, integrated MS pressure gauge, red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
Filter regulator MS-LFR			
J81	MS-LFR-D7-CRM-RG-AS ¹⁾	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, integrated MS pressure gauge, red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J82	MS-LFR-D7-CRM-RG-AS ¹⁾	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), input pressure 0.2 ... 1.2 MPa, integrated MS pressure gauge, red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J83	MS-LFR-D7-CRM-RG-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, integrated MS pressure gauge, red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 0.7 MPa	
J84	MS-LFR-D6-ERV-RG-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), input pressure 0.2 ... 1.2 MPa, integrated MS pressure gauge, red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 0.7 MPa	
J85	MS-LFR-D6-CRM-RG-AS ¹⁾	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, integrated MS pressure gauge, red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 0.7 MPa	
J86	MS-LFR-D6-CRV-RG-AS ¹⁾	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), input pressure 0.2 ... 1.2 MPa, integrated MS pressure gauge, red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 0.7 MPa	
J87	MS-LFR-D7-EUM-RG-AS ¹⁾	Filter regulator, 40 µm grade of filtration, metal bowl, manual condensate drain, integrated MS pressure gauge, red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J88	MS-LFR-D7-EUV-RG-AS ¹⁾	Filter regulator, 40 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), input pressure 0.2 ... 1.2 MPa, integrated MS pressure gauge, red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J89	MS-LFR-D7-CUM-RG-AS ¹⁾	Filter regulator, 5 µm grade of filtration, metal bowl, manual condensate drain, integrated MS pressure gauge, red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J90	MS-LFR-D7-CUV-RG-AS ¹⁾	Filter regulator, 5 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), input pressure 0.2 ... 1.2 MPa, integrated MS pressure gauge, red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J91	MS-LFR-D7-ERM-A8-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	–
	MS-LFR-D7-ERM-A4-AS ¹⁾	–	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa
J92	MS-LFR-D7-ERV-A8-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	–
	MS-LFR-D7-ERV-A4-AS ¹⁾	–	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description Size: 4	Size: 6
Filter regulator MS-LFR			
J93	MS-LFR-D7-CRM-A8-AS	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	–
	MS-LFR-D7-CRM-A4-AS	–	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa
J94	MS-LFR-D7-CRV-A8-AS ¹⁾	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	–
	MS-LFR-D7-CRV-A4-AS ¹⁾	–	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa
J95	MS-LFR-D6-ERM-A8-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 0.7 MPa	–
	MS-LFR-D6-ERM-A4-AS ¹⁾	–	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 0.7 MPa
J95B	MS-LFR-D6-EPM-A8-B ¹⁾²⁾	Filter regulator, (polymer), input pressure 1.0 MPa, 40 µm grade of filtration, plastic bowl, manual condensate drain, adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.05 ... 0.7 MPa	
J96	MS-LFR-D6-ERV-A8-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 0.7 MPa	–
	MS-LFR-D6-ERV-A84-AS ¹⁾	–	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 0.7 MPa
J96B	MS-LFR-D6-EPVC-A8-B ¹⁾²⁾	Filter regulator, (polymer), input pressure 1.0 MPa, 40 µm grade of filtration, plastic bowl, fully automatic condensate drain (normally closed), adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.05 ... 0.7 MPa	
J97	MS-LFR-D6-CRM-A8-AS ¹⁾	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 0.7 MPa	–
	MS-LFR-D6-CRM-A4-AS ¹⁾	–	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 0.7 MPa
J97B	MS-LFR-D6-CPM-A8-B ¹⁾²⁾	Filter regulator, (polymer), input pressure 1.0 MPa, 5 µm, plastic bowl, manual condensate drain, adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.05 ... 0.7 MPa	

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

2) Polymer service unit components series MS basic

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description Size: 4	Size: 6
Filter regulator MS-LFR			
J98	MS-LFR-D6-CRV-A8-AS ¹⁾	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 0.7 MPa	–
	MS-LFR-D6-CRV-A4-AS ¹⁾	–	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 0.7 MPa
J98B	MS-LFR-D6-CPVC-A8-B ¹⁾²⁾	Filter regulator, (polymer), input pressure 1.0 MPa, 5 µm, plastic bowl, fully automatic condensate drain (normally closed), adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.05 ... 0.7 MPa	
J99	MS-LFR-D7-EUM-A8-AS ¹⁾	Filter regulator, 40 µm grade of filtration, metal bowl, manual condensate drain, adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	–
	MS-LFR-D7-EUM-A4-AS ¹⁾	–	Filter regulator, 40 µm grade of filtration, metal bowl, manual condensate drain, adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa
J100	MS-LFR-D7-EUV-A8-AS ¹⁾	Filter regulator, 40 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	–
	MS-LFR-D7-EUV-A4-AS ¹⁾	–	Filter regulator, 40 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa
J101	MS-LFR-D7-CUM-A8-AS ¹⁾	Filter regulator, 5 µm grade of filtration, metal bowl, manual condensate drain, adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	–
	MS-LFR-D7-CUM-A4-AS ¹⁾	–	Filter regulator, 5 µm grade of filtration, metal bowl, manual condensate drain, adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa
J102	MS-LFR-D7-CUV-A8-AS ¹⁾	Filter regulator, 5 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	–
	MS-LFR-D7-CUV-A4-AS ¹⁾	–	Filter regulator, 5 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa
J119	MS-LFR-D6-CRV-MPA-AS ¹⁾	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), input pressure 0.2 - 1.2 MPa, integrated MS pressure gauge with outer scale in MPa, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J119B	MS-LFR-D6-CPVC-AG-MPA-B ¹⁾²⁾	Filter regulator, (polymer), 5 µm grade of filtration, plastic bowl, fully automatic condensate drain (normally closed), input pressure: 1.0 MPa, integrated MS pressure gauge with outer scale in MPa, pressure regulation range 0.05 ... 0.7 MPa	

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

2) Polymer service unit components series MS basic

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
Filter regulator MS-LFR			
J120	MS-LFR-D6-ERM-MPA-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, integrated MS pressure gauge with outer scale in MPa, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J120B	MS-LFR-D6-EPM-AG-MPA-B ¹⁾²⁾	Filter regulator, (polymer), 40 µm grade of filtration, plastic bowl, fully automatic condensate drain (normally closed), manual condensate drain, input pressure: 1.0 MPa, integrated MS pressure gauge with outer scale in MPa, pressure regulation range 0.05 ... 0.7 MPa	
J121	MS-LFR-D6-ERV-MPA-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), input pressure 0.2 ... 1.2 MPa, integrated MS pressure gauge with outer scale in MPa, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J121B	MS-LFR-D6-EPVC-AG-MPA-B ¹⁾²⁾	Filter regulator, (polymer), 40 µm grade of filtration, plastic bowl, fully automatic condensate drain (normally closed), input pressure: 1.0 MPa, integrated MS pressure gauge with outer scale in MPa, pressure regulation range 0.05 ... 0.7 MPa	
J124	MS-LFR-D6-CRM-MPA-AS ¹⁾	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, integrated MS pressure gauge with outer scale in MPa, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J124B	MS-LFR-D6-CPM-AG-MPA-B ¹⁾²⁾	Filter regulator, (polymer), 5 µm grade of filtration, plastic bowl, manual condensate drain, input pressure: 1.0 MPa, integrated MS pressure gauge with outer scale in MPa, pressure regulation range 0.05 ... 0.7 MPa	
J125	MS-LFR-D7-ERM-AD12-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, with pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V. 4...20 mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J126	MS-LFR-D7-ERV-AD12-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V. 4...20 mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J127	MS-LFR-D7-CRM-AD12-AS ¹⁾	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, with pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V. 4...20 mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J128	MS-LFR-D7-CRV-AD12-AS ¹⁾	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V. 4...20 mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J129	MS-LFR-D6-ERM-AD12-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, with pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V. 4...20 mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J130	MS-LFR-D6-ERV-AD12-AS ¹⁾	Filter regulator, 40 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V. 4...20 mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J131	MS-LFR-D6-CRM-AD12-AS ¹⁾	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, manual condensate drain, with pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V. 4...20 mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J132	MS-LFR-D6-CRV-AD12-AS ¹⁾	Filter regulator, 5 µm grade of filtration, plastic bowl with plastic bowl guard, fully automatic condensate drain (normally open), with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V. 4...20 mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
J133	MS-LFR-D7-EUM-AD12-AS ¹⁾	Filter regulator, 40 µm grade of filtration, metal bowl, manual condensate drain, with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V. 4...20 mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J134	MS-LFR-D7-EUV-AD12-AS ¹⁾	Filter regulator, 40 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V. 4...20 mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

2) Polymer service unit components series MS basic

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
Filter regulator MS-LFR			
J135	MS-LFR-D7-CUM-AD12-AS ¹⁾	Filter regulator, 5 µm grade of filtration, metal bowl, manual condensate drain, with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
J136	MS-LFR-D7-CUV-AD12-AS ¹⁾	Filter regulator, 5 µm grade of filtration, metal bowl, fully automatic condensate drain (normally open), with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
Activated carbon filter MS-LFX			
L1	MS-LFX-R	Activated carbon filter, plastic bowl with plastic bowl guard	
L2	MS-LFX-U	Activated carbon filter with metal bowl	
L3	MS-LFX-U-HF	–	Activated carbon filter with metal bowl, high flow rate
L4	MS-LFX-R-HP ¹⁾	–	Activated carbon filter, plastic bowl with plastic bowl guard, suitable for sealing air and purge air
Lubricator MS-LOE			
M1	MS-LOE-R	Compressed air lubricator, plastic bowl with plastic bowl guard, 0.1 ... 1.2 MPa	0.1 ... 1.6 MPa
M2	MS-LOE-U	Compressed air lubricator, metal bowl, 0.1 ... 1.2 MPa	0.1 ... 1.6 MPa
Pressure regulator MS-LR			
N1	MS-LR-D5-AS	Pressure regulator, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
N2	MS-LR-D6-AS	Pressure regulator, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
N2B	MS-LR-D6-AG-BAR-B ²⁾	Pressure regulator, (polymer), input pressure: 1.0 MPa, integrated MS pressure gauge with outer scale in bar and inner scale in psi, pressure regulation range 0.05 ... 0.7 MPa	
N3	MS-LR-D7-AS	Pressure regulator, integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
N4	MS-LR-D5-AD1-AS	Pressure regulator, with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
N5	MS-LR-D6-AD1-AS	Pressure regulator, with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
N6	MS-LR-D7-AD1-AS	Pressure regulator, with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
N7	MS-LR-D5-KD-AS	Pressure regulator, integrated MS pressure gauge with outer scale in bar and inner scale in psi, rotary knob underneath, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
N8	MS-LR-D6-KD-AS	Pressure regulator, integrated MS pressure gauge with outer scale in bar and inner scale in psi, rotary knob underneath, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
N9	MS-LR-D7-KD-AS	Pressure regulator, integrated MS pressure gauge with outer scale in bar and inner scale in psi, rotary knob underneath, lockable rotary knob, pressure regulation range 0.03 ... 1.2 MPa	
N10	MS-LR-D5-AD1-KD-AS	Pressure regulator, with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1.0 MPa), rotary knob underneath, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
N11	MS-LR-D6-AD1-KD-AS	Pressure regulator, with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1.0 MPa), rotary knob underneath, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
N12	MS-LR-D7-AD1-KD-AS	Pressure regulator, with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1.0 MPa), rotary knob underneath, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

2) Polymer service unit components series MS basic

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
Pressure regulator MS-LR			
N19	MS-LR-D5-AD7-AS	Pressure regulator, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
N20	MS-LR-D6-AD7-AS	Pressure regulator, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
N21	MS-LR-D7-AD7-AS	Pressure regulator, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
N22	MS-LR-D5-AD7-KD-AS	Pressure regulator, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
N23	MS-LR-D6-AD7-KD-AS	Pressure regulator, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
N24	MS-LR-D7-AD7-KD-AS	Pressure regulator, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
N28	MS-LR-D5-VS-DM2	–	Pressure regulator, pressure regulation range 0.03 ... 0.4 MPa, cover plate, MS pressure gauge integrated in the rotary knob (large), with outer scale in bar and inner scale in psi, pressure regulation range 0.03 ... 0.4 MPa
N29	MS-LR-D6-VS-DM2	–	Pressure regulator, pressure regulation range 0.03 ... 0.7 MPa, cover plate, MS pressure gauge integrated in the rotary knob (large), with outer scale in bar and inner scale in psi, pressure regulation range 0.03 ... 0.7 MPa
N30	MS-LR-D7-VS-DM2	–	Pressure regulator, pressure regulation range 0.05 ... 1.2 MPa, cover plate, MS pressure gauge integrated in the rotary knob (large), with outer scale in bar and inner scale in psi, pressure regulation range 0.05 ... 1.2 MPa
N31	MS-LR-D5-VS-DM1	Pressure regulator, pressure regulation range 0.03 ... 0.4 MPa, cover plate, MS pressure gauge integrated in the rotary knob, with outer scale in bar and inner scale in psi, pressure regulation range 0.03 ... 0.4 MPa	–
N32	MS-LR-D6-VS-DM1	Pressure regulator, pressure regulation range 0.03 ... 0.7 MPa, cover plate, MS pressure gauge integrated in the rotary knob, with outer scale in bar and inner scale in psi, pressure regulation range 0.03 ... 0.7 MPa	–
N33	MS-LR-D7-VS-DM1	Pressure regulator, pressure regulation range 0.05 ... 1.2 MPa, cover plate, MS pressure gauge integrated in the rotary knob, with outer scale in bar and inner scale in psi, pressure regulation range 0.05 ... 1.2 MPa	–
N47	MS-LR-D5-RG-AS ¹⁾	Pressure regulator, pressure regulation range 0.03 ... 0.4 MPa, integrated MS pressure gauge red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
N48	MS-LR-D6-RG-AS ¹⁾	Pressure regulator, pressure regulation range 0.03 ... 0.7 MPa, integrated MS pressure gauge red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
N49	MS-LR-D7-RG-AS ¹⁾	Pressure regulator, pressure regulation range 0.05 ... 1.2 MPa, integrated MS pressure gauge red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
N50	MS-LR-D5-A8-AS ¹⁾	Pressure regulator, adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	–
	MS-LR-D5-A4-AS ¹⁾	–	Pressure regulator, adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description Size: 4	Size: 6
Pressure regulator MS-LR			
N51	MS-LR-D6-A8-AS ¹⁾	Pressure regulator, adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	–
	MS-LR-D6-A4-AS ¹⁾	–	Pressure regulator, adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa
N51B	MS-LR-D6-A8-B ¹⁾²⁾	Pressure regulator, (polymer), input pressure: 1.0 MPa, adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.05 ... 0.7 MPa	
N52	MS-LR-D7-A8-AS ¹⁾	Pressure regulator, adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	–
	MS-LR-D7-A4-AS ¹⁾	–	Pressure regulator, adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa
N59	MS-LR-D5-MPA-AS ¹⁾	Pressure regulator, integrated MS pressure gauge with outer scale in MPa, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
N60	MS-LR-D6-MPA-AS ¹⁾	Pressure regulator, integrated MS pressure gauge with outer scale in MPa, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
N60B	MS-LR-D6-AG-MPA-B ¹⁾²⁾	Pressure regulator, (polymer), input pressure: 1.0 MPa, integrated MS pressure gauge with outer scale in MPa, pressure regulation range 0.05 ... 0.7 MPa	
N61	MS-LR-D5-AD12-AS ¹⁾	Pressure regulator, with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
N62	MS-LR-D6-AD12-AS ¹⁾	Pressure regulator, with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
N63	MS-LR-D7-AD12-AS ¹⁾	Pressure regulator, with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20mA (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
N64	MS-LR-D5-AD12-KD-AS ¹⁾	Pressure regulator, with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA (max. input pressure 1.0 MPa), rotary knob underneath, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
N65	MS-LR-D6-AD12-KD-AS ¹⁾	Pressure regulator, with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA (max. input pressure 1.0 MPa), rotary knob underneath, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
N66	MS-LR-D7-AD12-KD-AS ¹⁾	Pressure regulator, with pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA (max. input pressure 1.0 MPa), rotary knob underneath, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
N67B	MS-LR-D6-AG-BAR-F1A-B ¹⁾²⁾	Pressure regulator, (polymer), input pressure: 1.0 MPa, integrated MS pressure gauge with outer scale in bar and inner scale in psi, recommended for production plants for manufacturing lithium-ion batteries (Cu<=1%, Zn<=1%, Ni<=1%) pressure regulation range 0.05 ... 0.7 MPa	
N68B	MS-LR-D6-A8-F1A-B ¹⁾²⁾	Pressure regulator, (polymer), input pressure: 1.0 MPa, adapter for 1/8" EN pressure gauge (does not include pressure gauge), recommended for production plants for manufacturing lithium-ion batteries (Cu<=1%, Zn<=1%, Ni<=1%), pressure regulation range 0.05 ... 0.7 MPa	
N69B	MS-LR-D6-AG-MPA-F1A-B ¹⁾²⁾	Pressure regulator, (polymer), input pressure: 1.0 MPa, integrated MS pressure gauge with outer scale in MPa, recommended for production plants for manufacturing lithium-ion batteries (Cu<=1%, Zn<=1%, Ni<=1%), pressure regulation range 0.05 ... 0.7 MPa	

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

2) Polymer service unit components series MS basic

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	
		Size: 4	Size: 6
Pressure regulator MS-LRB			
O1	MS-LRB-D5-AS ¹⁾	Pressure regulator for manifold assembly (pressure output port at rear, pressure supply port on the left and right), integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
O2	MS-LRB-D6-AS ¹⁾	Pressure regulator for manifold assembly (pressure output port at rear, pressure supply port on the left and right), integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
O3	MS-LRB-D7-AS ¹⁾	Pressure regulator for manifold assembly (pressure output port at rear, pressure supply port on the left and right), integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
O4	MS-LRB-D5-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 2xQS8 at rear, pressure supply port on the left and right), integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
O5	MS-LRB-D6-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1xQS8 at rear, pressure supply port on the left and right), integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
O6	MS-LRB-D7-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1xQS8 at rear, pressure supply port on the left and right), integrated MS pressure gauge with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
O7	MS-LRB-D5-A8-AS ¹⁾	Pressure regulator for manifold assembly (pressure output port at rear, pressure supply port on the left and right), adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	–
O8	MS-LRB-D6-A8-AS ¹⁾	Pressure regulator for manifold assembly (pressure output port at rear, pressure supply port on the left and right), adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	–
	MS-LRB-D6-A4-AS ¹⁾	–	Pressure regulator for manifold assembly (pressure output port at rear, pressure supply port on the left and right), adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa
O9	MS-LRB-D7-A8-AS ¹⁾	Pressure regulator for manifold assembly (pressure output port at rear, pressure supply port on the left and right), adapter for 1/8" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	–
	MS-LRB-D7-A4-AS ¹⁾	–	Pressure regulator for manifold assembly (pressure output port at rear, pressure supply port on the left and right), adapter for 1/4" EN pressure gauge (does not include pressure gauge), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa
O10	MS-LRB-D5-AD1-AS ¹⁾	Pressure regulator for manifold assembly, with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
O11	MS-LRB-D6-AD1-AS ¹⁾	Pressure regulator for manifold assembly, with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
O12	MS-LRB-D7-AD1-AS ¹⁾	Pressure regulator for manifold assembly, with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
Pressure regulator MS-LRB			
013	MS-LRB-D5-AD1-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1xQS8 at rear (MS4) 2x QS8 at rear (MS6), pressure supply port on the left and right), with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
014	MS-LRB-D6-AD1-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1xQS8 at rear (MS4) 2x QS8 at rear (MS6), pressure supply port on the left and right), with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
015	MS-LRB-D7-AD1-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1xQS8 at rear (MS4) 2x QS8 at rear (MS6), pressure supply port on the left and right), with pressure sensor with LCD display, M8 plug, PNP, 3-pin (max. input pressure 1 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
016	MS-LRB-D5-VS-KD-AS ¹⁾	Pressure regulator for manifold assembly, cover plate, rotary knob underneath, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
017	MS-LRB-D6-VS-KD-AS ¹⁾	Pressure regulator for manifold assembly, cover plate, rotary knob underneath, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
018	MS-LRB-D7-VS-KD-AS ¹⁾	Pressure regulator for manifold assembly, cover plate, rotary knob underneath, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
019	MS-LRB-D5-KD-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1xQS8 at rear (MS4) 2x QS8 at rear (MS6), pressure supply port on the left and right), rotary knob underneath, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
020	MS-LRB-D6-KD-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1xQS8 at rear (MS4) 2x QS8 at rear (MS6), pressure supply port on the left and right), rotary knob underneath, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
021	MS-LRB-D7-KD-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1xQS8 at rear (MS4) 2x QS8 at rear (MS6), pressure supply port on the left and right), rotary knob underneath, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
022	MS-LRB-D5-AD7-AS ¹⁾	Pressure regulator for manifold assembly, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
023	MS-LRB-D6-AD7-AS ¹⁾	Pressure regulator for manifold assembly, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
024	MS-LRB-D7-AD7-AS ¹⁾	Pressure regulator for manifold assembly, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
025	MS-LRB-D5-AD7-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1xQS8 at rear (MS4) 2x QS8 at rear (MS6), pressure supply port on the left and right), pressure sensor with operational status display, M8 plug, threshold value comparator PNP, N/O contact (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
026	MS-LRB-D6-AD7-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1xQS8 at rear (MS4) 2x QS8 at rear (MS6), pressure supply port on the left and right), pressure sensor with operational status display, M8 plug, threshold value comparator PNP, N/O contact (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
027	MS-LRB-D7-AD7-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1xQS8 at rear (MS4) 2x QS8 at rear (MS6), pressure supply port on the left and right), pressure sensor with operational status display, M8 plug, threshold value comparator PNP, N/O contact (max. input pressure 1.0 MPa), lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
028	MS-LRB-D5-VS-DM2 ¹⁾	–	Pressure regulator for manifold assembly, cover plate, MS pressure gauge integrated in the rotary knob (large), with outer scale in bar and inner scale in psi, pressure regulation range 0.03 ... 0.4 MPa
029	MS-LRB-D6-VS-DM2 ¹⁾	–	Pressure regulator for manifold assembly, cover plate, MS pressure gauge integrated in the rotary knob (large), with outer scale in bar and inner scale in psi, pressure regulation range 0.03 ... 0.7 MPa

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
Pressure regulator MS-LRB			
O30	MS-LRB-D7-VS-DM2 ¹⁾	–	Pressure regulator for manifold assembly, cover plate, MS pressure gauge integrated in the rotary knob (large), with outer scale in bar and inner scale in psi, pressure regulation range 0.05 ... 1.2 MPa
O31	MS-LRB-D5-VS-DM1 ¹⁾	Pressure regulator for manifold assembly, cover plate, MS pressure gauge integrated in the rotary knob, with outer scale in bar and inner scale in psi, pressure regulation range 0.03 ... 0.4 MPa	–
O32	MS-LRB-D6-VS-DM1 ¹⁾	Pressure regulator for manifold assembly, cover plate, MS pressure gauge integrated in the rotary knob, with outer scale in bar and inner scale in psi, pressure regulation range 0.03 ... 0.7 MPa	–
O33	MS-LRB-D7-VS-DM1 ¹⁾	Pressure regulator for manifold assembly, cover plate, MS pressure gauge integrated in the rotary knob, with outer scale in bar and inner scale in psi, pressure regulation range 0.05 ... 1.2 MPa	–
O34	MS-LRB-D5-RG-AS ¹⁾	Pressure regulator for manifold assembly, integrated MS pressure gauge red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
O35	MS-LRB-D6-RG-AS ¹⁾	Pressure regulator for manifold assembly, integrated MS pressure gauge red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
O36	MS-LRB-D7-RG-AS ¹⁾	Pressure regulator for manifold assembly, integrated MS pressure gauge red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
O37	MS-LRB-D5-RG-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1x QS8 at rear (MS4), 2x QS8 at rear (MS6), pressure supply port on the left and right), integrated MS pressure gauge red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
O38	MS-LRB-D6-RG-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1x QS8 at rear (MS4), 2x QS8 at rear (MS6), pressure supply port on the left and right), integrated MS pressure gauge red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
O39	MS-LRB-D7-RG-AS-BD ¹⁾	Pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 1x QS8 at rear (MS4), 2x QS8 at rear (MS6), pressure supply port on the left and right), integrated MS pressure gauge red/green scale with outer scale in bar and inner scale in psi, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
O40	MS-LRB-D5-MPA-AS ¹⁾	Pressure regulator for manifold assembly, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
O41	MS-LRB-D6-MPA-AS ¹⁾	Pressure regulator for manifold assembly, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
O42	MS-LRB-D5-AD12-ASS ¹⁾	Pressure regulator for manifold assembly, pressure sensor with LCD display, M8 plug, IO-Link®, PNP, NPN, 4-pin, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	
O43	MS-LRB-D6-AD12-AS ¹⁾	Pressure regulator for manifold assembly, pressure sensor with LCD display, M8 plug, IO-Link®, PNP, NPN, 4-pin, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
O44	MS-LRB-D7-AD12-AS ¹⁾	Pressure regulator for manifold assembly, pressure sensor with LCD display, M8 plug, IO-Link®, PNP, NPN, 4-pin, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
O46	MS-LRB-D5-AD12-AS-BD ¹⁾	Pressure regulator for manifold assembly with angled outlet block at rear (pressure output port 1x QS8 at rear (MS4) 2x QS8 at rear (MS6), pressure supply port on the left and right), pressure sensor with LCD display, M8 plug, IO-Link®, PNP, NPN, 4-pin, lockable rotary knob, pressure regulation range 0.03 ... 0.4 MPa	

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
Size: 4			
Pressure regulator MS-LRB			
O47	MS-LRB-D6-AD12-AS-BD ¹⁾	Pressure regulator for manifold assembly with angled outlet block at rear (pressure output port 1x QS8 at rear (MS4) 2x QS8 at rear (MS6), pressure supply port on the left and right), pressure sensor with LCD display, M8 plug, IO-Link®, PNP, NPN, 4-pin, lockable rotary knob, pressure regulation range 0.03 ... 0.7 MPa	
O48	MS-LRB-D7-AD12-AS-BD ¹⁾	Pressure regulator for manifold assembly with angled outlet block at rear (pressure output port 1x QS8 at rear (MS4) 2x QS8 at rear (MS6), pressure supply port on the left and right), pressure sensor with LCD display, M8 plug, IO-Link®, PNP, NPN, 4-pin, lockable rotary knob, pressure regulation range 0.05 ... 1.2 MPa	
Precision pressure regulator MS-LRP			
P1	MS-LRP-D2-A8	–	Precision pressure regulator, 0.005 to 0.07 MPa, adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.005 ... 0.07 MPa
P2	MS-LRP-D4-A8	–	Precision pressure regulator, 0.005 to 0.25 MPa, adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.005 ... 0.25 MPa
P3	MS-LRP-D5-A8	–	Precision pressure regulator, 0.03 to 0.4 MPa, adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.03 ... 0.4 MPa
P4	MS-LRP-D7-A8	–	Precision pressure regulator, 0.05 to 1.2 MPa, adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.05 ... 1.2 MPa
Precision pressure regulator MS-LRPB			
R1	MS-LRPB-D2-A8 ¹⁾	–	Precision pressure regulator for manifold assembly, adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.005 ... 0.07 MPa
R2	MS-LRPB-D4-A8 ¹⁾	–	Precision pressure regulator for manifold assembly, adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.005 ... 0.25 MPa
R3	MS-LRPB-D5-A8 ¹⁾	–	Precision pressure regulator for manifold assembly, adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.03 ... 0.4 MPa
R4	MS-LRPB-D7-A8 ¹⁾	–	Precision pressure regulator for manifold assembly, adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.05 ... 1.2 MPa
R5	MS-LRPB-D2-A8-BD ¹⁾	–	Precision pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 2x QS8 at rear, pressure supply port on the left and right), adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.005 ... 0.07 MPa
R6	MS-LRPB-D4-A8-BD ¹⁾	–	Precision pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 2x QS8 at rear, pressure supply port on the left and right), adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.005 ... 0.25 MPa
R7	MS-LRPB-D5-A8-BD ¹⁾	–	Precision pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 2x QS8 at rear, pressure supply port on the left and right), adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.03 ... 0.4 MPa

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
		Size: 4	
Precision pressure regulator MS-LRPB			
R8	MS-LRPB-D7-A8-BD ¹⁾	–	Precision pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 2x QS8 at rear, pressure supply port on the left and right), adapter for 1/8" EN pressure gauge (does not include pressure gauge) pressure regulation range 0.05 ... 1.2 MPa
R9	MS-LRPB-D2-A8-BE ¹⁾	–	Precision pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 2x QS10 at rear, pressure supply port on the left and right), adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.005 ... 0.07 MPa
R10	MS-LRPB-D4-A8-BE ¹⁾	–	Precision pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 2x QS10 at rear, pressure supply port on the left and right), adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.005 ... 0.25 MPa
R11	MS-LRPB-D5-A8-BE ¹⁾	–	Precision pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 2x QS10 at rear, pressure supply port on the left and right), adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.01 ... 0.4 MPa
R12	MS-LRPB-D7-A8-BE ¹⁾	–	Precision pressure regulator for manifold assembly, with angled outlet block at rear (pressure output port 2x QS10 at rear, pressure supply port on the left and right), adapter for 1/8" EN pressure gauge (does not include pressure gauge), pressure regulation range 0.01 ... 1.2 MPa
Flow sensor SFAM			
U5	SFAM-1000-M-2SA-M12	–	Flow sensor, max. 1000 l/min, manifold assembly, 2x PNP or NPN, 1 analogue output 4 ... 20 mA, M12 plug, A-coded
U6	SFAM-1000-M-2SV-M12	–	Flow sensor, max. 1000 l/min, manifold assembly, 2x PNP or NPN, 1 analogue output 0 ... 10 V, M12 plug, A-coded
U7	SFAM-3000-M-2SA-M12	–	Flow sensor, max. 3000 l/min, manifold assembly, 2x PNP or NPN, 1 analogue output 4 ... 20 mA, M12 plug, A-coded
U8	SFAM-3000-M-2SV-M12	–	Flow sensor, max. 3000 l/min, manifold assembly, 2x PNP or NPN, 1 analogue output 0 ... 10 V, M12 plug, A-coded
U9	SFAM-5000-M-2SA-M12	–	Flow sensor, max. 5000 l/min, manifold assembly, 2x PNP or NPN, 1 analogue output 4 ... 20 mA, M12 plug, A-coded
U10	SFAM-5000-M-2SV-M12	–	Flow sensor, max. 5000 l/min, manifold assembly, 2x PNP or NPN, 1 analogue output 0 ... 10 V, M12 plug, A-coded

1) Female thread only with G1/4 (MS4) or G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description Size: 4	Size: 6
Soft-start/quick exhaust valve MS-SV (not with EX2/EX4 EU certification)			
V1	MS-SV-E-10V24-SO-AG ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, open silencer, MS pressure gauge with outer scale in bar and inner scale in psi, 0.35 ... 1.0 MPa
V2	MS-SV-E-10V24-AG ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, MS pressure gauge with outer scale in bar and inner scale in psi, 0.35 ... 1.0 MPa
V3	MS-SV-E-10V24-AD1 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, pressure sensor with LCD display, M8 plug, PNP, 3-pin, 0.35 ... 1.0 MPa
V4	MS-SV-E-10V24-SO-AD1 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, open silencer, pressure sensor with LCD display, M8 plug, PNP, 3-pin, 0.35 ... 1.0 MPa
V5	MS-SV-E-10V24-SO-AG-MP1 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, open silencer, MS pressure gauge with outer scale in bar and inner scale in psi, with multi-pin plug socket MP1, 0.35 ... 1.0 MPa
V6	MS-SV-E-10V24-AG-MP1 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, MS pressure gauge with outer scale in bar and inner scale in psi, with multi-pin plug socket MP1, 0.35 ... 1.0 MPa
V7	MS-SV-E-10V24-AD1-MP1 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, pressure sensor with LCD display, M8 plug, PNP, 3-pin, with multi-pin plug socket MP1, 0.35 ... 1.0 MPa
V8	MS-SV-E-10V24-SO-AD1-MP1 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, open silencer, pressure sensor with LCD display, M8 plug, PNP, 3-pin, with multi-pin plug socket MP1, 0.35 ... 1.0 MPa
V12	MS-SV-C-10V24-S ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, type C (plug pattern to EN 175301-803), 24 V DC, non-detenting manual override on pilot actuator and detenting on soft-start/quick exhaust valve, with silencer, 0.3 ... 1.0 MPa
V22	MS-SV-C-10V24-S-AD7 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, type C (plug pattern to EN 175301-803), 24 V DC, 0.3-1 MPa, non-detenting manual override on pilot actuator and detenting on soft-start/quick exhaust valve, with silencer, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, 3-pin, 0.3 ... 1.0 MPa
			0.35 ... 1.0 MPa

1) Female thread only with G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description Size: 4	Size: 6
Soft-start/quick exhaust valve MS-SV (not with EX2/EX4 EU certification)			
V31	MS-SV-E-10V24-SO-AG-MP3 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, open silencer, MS pressure gauge with outer scale in bar and inner scale in psi, with multi-pin plug socket MP3, 0.35 ... 1.0 MPa
V32	MS-SV-E-10V24-AG-MP3 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, MS pressure gauge with outer scale in bar and inner scale in psi, with multi-pin plug socket MP3, 0.35 ... 1.0 MPa
V34	MS-SV-E-10V24-SO-AD1-MP3 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, open silencer, pressure sensor with LCD display, M8 plug, PNP, 3-pin, with multi-pin plug socket MP3, 0.35 ... 1.0 MPa
V35	MS-SV-C-10V24P-S ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, non-detenting/detenting manual override on pilot actuator and detenting on soft-start/quick exhaust valve, with silencer, pressure sensor with no display, M12 plug, 0.3 ... 1.0 MPa
V36	MS-SV-C-10V24P-S-AD7 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, non-detenting/detenting manual override on pilot actuator and detenting on soft-start/quick exhaust valve, with silencer, pressure sensor with operational status display, M8 plug, threshold value comparator, PNP, 3-pin, 0.3 ... 1.0 MPa
V37	MS-SV-D-10V24-2M8 ¹⁾	–	Soft-start/quick exhaust valve, category 3 with Performance Level d to EN ISO 13849-1, 2-channel, type C (port pattern to EN 175301-803), 24 V DC, non-detenting manual override on the pilot actuator, 2 proximity switches SMT, 0.3 m, M8, 0.35 ... 1.0 MPa
V38	MS-SV-D-10V24-2M8-SO-AG ¹⁾	–	Soft-start/quick exhaust valve, category 3 with Performance Level d to EN ISO 13849-1, 2-channel, type C (plug pattern to EN 175301-803), 24 V DC, non-detenting manual override on pilot actuator, open silencer, 2 proximity switches SMT, 0.3 m, M8, MS pressure gauge with outer scale in bar and inner scale in psi, 0.35 ... 1.0 MPa
V39	MS-SV-D-10V24P-2M12-SO-AG ¹⁾	–	Soft-start/quick exhaust valve, category 3 with Performance Level d to EN ISO 13849-1, 2-channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, non-detenting/detenting manual override on pilot actuator, open silencer, 2 proximity switches SMT, 0.3 m, M12, MS pressure gauge with outer scale in bar and inner scale in psi, 0.35 ... 1.0 MPa
V40	MS-SV-D-10V24P-2OE-SO-AG ¹⁾	–	Soft-start/quick exhaust valve, category 3 with Performance Level d to EN ISO 13849-1, 2-channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, non-detenting/detenting manual override on pilot actuator, open silencer, 2 proximity switches SMT, 5 m, OE, MS pressure gauge with outer scale in bar and inner scale in psi, 0.35 ... 1.0 MPa

1) Female thread only with G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description Size: 4	Size: 6
Soft-start/quick exhaust valve MS-SV (not with EX2/EX4 EU certification)			
V41	MS-SV-E-10V24-SO-AG-MP5 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, open silencer, MS pressure gauge with outer scale in bar and inner scale in psi, with multi-pin plug socket MP5, 0.35 ... 1.0 MPa
V42	MS-SV-E-10V24-AG-MP5 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, MS pressure gauge with outer scale in bar and inner scale in psi, with multi-pin plug socket MP5, 0.35 ... 1.0 MPa
V43	MS-SV-E-10V24-AD1-MP5 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, pressure sensor with LCD display, M8 plug, PNP, 3-pin, with multi-pin plug socket MP5, 0.35 ... 1.0 MPa
V44	MS-SV-E-10V24-SO-AD1-MP5 ¹⁾	—	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, open silencer, pressure sensor with LCD display, M8 plug, PNP, 3-pin, with multi-pin plug socket MP5, 0.35 ... 1.0 MPa
V45	MS-SV-E-10V24-RG ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, integrated pressure gauge with red/green scale with outer scale in bar and inner scale in psi, 0.35 ... 1.0 MPa
V46	MS-SV-E-10V24-SO-RG ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, open silencer, integrated pressure gauge with red/green scale with outer scale in bar and inner scale in psi, 0.35 ... 1.0 MPa
V47	MS-SV-D-10V24-2M8-SO-RG ¹⁾	–	Soft-start/quick exhaust valve, category 3 with Performance Level d to EN ISO 13849-1, 2-channel, type C (plug pattern to EN 175301-803), 24 V DC, non-detenting manual override on pilot actuator, open silencer, 2 proximity switches SMT, 0.3 m, M8, integrated pressure gauge with red/green scale with outer scale in bar and inner scale in psi, 0.35 ... 1.0 MPa
V48	MS-SV-D-10V24P-2M12-SO-RG ¹⁾	–	Soft-start/quick exhaust valve, category 3 with Performance Level d to EN ISO 13849-1, 2-channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, non-detenting/detenting manual override on pilot actuator, open silencer, 2 proximity switches SMT, 0.3 m, M12, integrated pressure gauge with red/green scale with outer scale in bar and inner scale in psi, 0.35 ... 1.0 MPa
V49	MS-SV-D-10V24-2OE-SO-RG ¹⁾	–	Soft-start/quick exhaust valve, category 3 with Performance Level d to EN ISO 13849-1, 2-channel, type C (plug pattern to EN 175301-803), 24 V DC, non-detenting manual override on pilot actuator, open silencer, 2 proximity switches SMT, 5 m, OE, integrated pressure gauge with red/green scale with outer scale in bar and inner scale in psi, 0.35 ... 1.0 MPa

1) Female thread only with G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
Soft-start/quick exhaust valve MS-SV (not with EX2/EX4 EU certification)			
V50	MS-SV-C-10V24-S-AD11 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, type C (plug pattern to EN 175301-803), 24 V DC, non-detenting manual override on pilot actuator and detenting on soft-start/quick exhaust valve, silencer, pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.3 ... 1.0 MPa
V51	MS-SV-C-10V24C-S-AD11 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, type C (plug pattern to EN 175301-803), 24 V DC, no manual override on pilot actuator and none on soft-start/quick exhaust valve, silencer, pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.3 ... 1.0 MPa
V52	MS-SV-C-10V24D-S-AD11 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, plug pattern to IEC 61076-2-101, 24 V DC, no manual override on pilot actuator and none on soft-start/quick exhaust valve, silencer, pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.3 ... 1.0 MPa
V53	MS-SV-C-10V24E-S-AD11 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, no manual override on pilot actuator and detenting on soft-start/quick exhaust valve, silencer, pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.3 ... 1.0 MPa
V54	MS-SV-C-10V24F-S-AD11 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, non-detenting manual override on pilot actuator and detenting on soft-start/quick exhaust valve, silencer, pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.3 ... 1.0 MPa
V55	MS-SV-C-10V24P-S-AD11 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, non-detenting/detenting manual override on pilot actuator and detenting on soft-start/quick exhaust valve, silencer, pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.3 ... 1.0 MPa
V56	MS-SV-C-10V24-S-AD12 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, type C (plug pattern to EN 175301-803), 24 V DC, non-detenting manual override on pilot actuator and detenting on soft-start/quick exhaust valve, 24 V DC, silencer, pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.3 ... 1.0 MPa

1) Female thread only with G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description Size: 4	Size: 6
Soft-start/quick exhaust valve MS-SV (not with EX2/EX4 EU certification)			
V57	MS-SV-C-10V24C-S-AD12 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, type C (plug pattern to EN 175301-803), 24 V DC, no manual override on pilot actuator and none on soft-start/quick exhaust valve, silencer, pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.3 ... 1.0 MPa
V58	MS-SV-C-10V24D-S-AD12 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, no manual override on pilot actuator and none on soft-start/quick exhaust valve, silencer, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.3 ... 1.0 MPa
V59	MS-SV-C-10V24E-S-AD12 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, no manual override on pilot actuator and detenting on soft-start/quick exhaust valve, silencer, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.3 ... 1.0 MPa
V60	MS-SV-C-10V24F-S-AD12 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, non-detenting manual override on pilot actuator and detenting on soft-start/quick exhaust valve, silencer, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.3 ... 1.0 MPa
V61	MS-SV-C-10V24P-S-AD12 ¹⁾	–	Soft-start/quick exhaust valve, category 1 with Performance Level c to EN ISO 13849-1, single channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, non-detenting/detenting manual override on pilot actuator and detenting on soft-start/quick exhaust valve, silencer, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.3 ... 1.0 MPa
V62	MS-SV-E-10V24-AD12 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.35 ... 1.0 MPa
V63	MS-SV-E-10V24-SO-AD12 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, open silencer, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 0.35 ... 1.0 MPa
V64	MS-SV-E-10V24-AD12-MP1 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, with multi-pin plug socket MP1, 0.35 ... 1.0 MPa

1) Female thread only with G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
Soft-start/quick exhaust valve MS-SV (not with EX2/EX4 EU certification)			
V65	MS-SV-E-10V24-SO-AD12-MP1 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, open silencer, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, with multi-pin plug socket MP1, 0.35 ... 1.0 MPa
V66	MS-SV-E-10V24-AD12-MP3 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, with multi-pin plug socket MP3, 0.35 ... 1.0 MPa
V67	MS-SV-E-10V24-SO-AD12-MP3 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, open silencer, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, with multi-pin plug socket MP3, 0.35 ... 1.0 MPa
V68	MS-SV-E-10V24-AD12-MP5 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, with multi-pin plug socket MP5, 0.35 ... 1.0 MPa
V69	MS-SV-E-10V24-SO-AD12-MP5 ¹⁾	–	Soft-start/quick exhaust valve, category 4 with Performance Level e to EN ISO 13849-1, 2-channel with self-monitoring, 24 V DC, open silencer, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, with multi-pin plug socket MP5, 0.35 ... 1.0 MPa
V70	MS-SV-D-10V24-2M8-SO-AD12 ¹⁾	–	Soft-start/quick exhaust valve, category 3 with Performance Level d to EN ISO 13849-1, 2-channel, type C (plug pattern to EN 175301-803), 24 V DC, non-detenting manual override on pilot actuator, open silencer, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 2 proximity switches SMT, 0.3m, M8, 0.35 ... 1.0 MPa
V71	MS-SV-D-10V24-2M8-AD12 ¹⁾	–	Soft-start/quick exhaust valve, category 3 with Performance Level d to EN ISO 13849-1, 2-channel, type C (plug pattern to EN 175301-803), 24 V DC, non-detenting manual override on pilot actuator, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 2 proximity switches SMT, 0.3m, M8, 0.35 ... 1.0 MPa
V72	MS-SV-D-10V24P-2M8-SO-AD11 ¹⁾	–	Soft-start/quick exhaust valve, category 3 with Performance Level d to EN ISO 13849-1, 2-channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, non-detenting/detenting manual override on pilot actuator, open silencer, pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 2 proximity switches SMT, 0.3 m, M8, 0.35 ... 1.0 MPa

1) Female thread only with G1/2 (MS6)

Type codes

Overview list – Service unit components MS4/6			
Code	Type	Description	Size: 6
		Size: 4	
Soft-start/quick exhaust valve MS-SV (not with EX2/EX4 EU certification)			
V73	MS-SV-D-10V24P-2M8-AD11 ¹⁾	–	Soft-start/quick exhaust valve, category 3 with Performance Level d to EN ISO 13849-1, 2-channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, non-detenting/detenting manual override on pilot actuator, pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 2 SMT proximity switches, 0.3 m, M8, 0.35 ... 1.0 MPa
V74	MS-SV-D-10V24P-2M8-SO-AD12 ¹⁾	–	Soft-start/quick exhaust valve, category 3 with Performance Level d to EN ISO 13849-1, 2-channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, non-detenting/detenting manual override on pilot actuator, open silencer, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 2 proximity switches SMT, 0.3 m, M8, 0.35 ... 1.0 MPa
V75	MS-SV-D-10V24P-2M8-AD12 ¹⁾	–	Soft-start/quick exhaust valve, category 3 with Performance Level d to EN ISO 13849-1, 2-channel, M12 (plug pattern to IEC 61076-2-101), 24 V DC, non-detenting/detenting manual override on pilot actuator, pressure sensor, with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA, 2 proximity switches SMT, 0.3 m, M8, 0.35 ... 1.0 MPa
Water separator MS-LWS			
W1	MS-LWS-U-V	–	Water separator, metal bowl, fully automatic condensate drain

1) Female thread only with G1/2 (MS6)

Type codes

001	Series	
MSB	Service unit component MS series	
002	Size	
9	Grid dimension 90 mm	
003	Pneumatic connection	
3/4	Female thread G3/4	
1	Female thread G1	
AGD	Sub-base G1/2	
AGE	Sub-base G3/4	
AGF	Sub-base G1	
AGG	Sub-base G11/4	
AGH	Sub-base G11/2	
N3/4	Female thread N3/4	
N1	Female thread N1	
AQR	Sub-base NPT1/2	
AQS	Sub-base NPT3/4	
AQT	Sub-base NPT1	
AQU	Sub-base NPT11/4	
AQV	Sub-base NPT11/2	
G	Module without connecting thread, without sub-base	
NG	Module without connecting thread, without sub-base (inch)	

004	Service unit component equipment	
...	For selection, see overview list	
005	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
WPB	Mounting bracket for large wall gap	
WPM	Mounting bracket for hooking in service unit components	
006	EU certification	
	None	
EX2	II 3GD to EU Explosion Protection Directive (ATEX)	
EX4	II 2GD	
007	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	
008	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Type codes

Overview list – Service unit components MS9		
Code	Type	Description
On/off valve MS-EM, manually actuated		
C2)	MS-EM-S	On/off valve with silencer
C7)	MS-EM-RS	On/off valve, red rotary knob, silencer
On/off valve MS-EE, electrically actuated		
D4	MS-EE-V24-S	Electric on/off valve, 24 V, with silencer, 18 bar
D16	MS-EE-V24-S-AD7	Electric on/off valve, 24 V, silencer, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact
D17	MS-EE-V24P-S	Electric on/off valve, 24 V DC plug (plug pattern M12 to DESINA), silencer
D18	MS-EE-V24P-S-AD7	Electric on/off valve, 24 V DC plug (plug pattern M12 to DESINA), silencer, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact
Branching module MS-FRM		
F1	MS-FRM	Branching module
F3	MS-FRM-Y	Branching module with pressure switch, no display
F8	MS-FRM-M12	Branching module with pressure switch, no display, M12 plug, 4-pin
Filter MS-LF		
H5	MS-LF-C-U-M	Filter, 5 µm, metal bowl, manual condensate drain
H6	MS-LF-C-U-V	Filter, 5 µm, metal bowl, fully automatic condensate drain
H7	MS-LF-E-U-V	Filter, 40 µm, metal bowl, fully automatic condensate drain
H8	MS-LF-E-U-M	Filter, 40 µm, metal bowl, manual condensate drain
Fine and micro filter MS-LFM		
I7	MS-LFM-B-U-V	Fine and micro filter, 1 µm, metal bowl, fully automatic condensate drain
I8	MS-LFM-A-U-V	Fine and micro filter, 0.01 µm, metal bowl, fully automatic condensate drain
I9	MS-LFM-B-U-V-DA	Fine and micro filter, 1 µm, metal bowl, fully automatic condensate drain, differential pressure display
I12	MS-LFM-A-U-V-DA	Fine and micro filter, 0.01 µm, metal bowl, fully automatic condensate drain, differential pressure display
I23	MS-LFM-B-U-V-HF	Fine and micro filter, 1 µm grade of filtration, metal bowl, fully automatic condensate drain high flow rate
I24	MS-LFM-A-U-V-HF	Fine and micro filter, 0.01 µm grade of filtration, metal bowl, fully automatic condensate drain high flow rate
I25	MS-LFM-B-U-V-HF-DA	Fine and micro filter, 1 µm grade of filtration, metal bowl, fully automatic condensate drain, differential pressure display, high flow rate
I26	MS-LFM-A-U-V-HF-DA	Fine and micro filter, 0.01 µm grade of filtration, metal bowl, fully automatic condensate drain, differential pressure display, high flow rate
Filter regulator MS-LFR		
J47	MS-LFR-D6-E-U-M-DI-AS	Filter regulator, lockable, directly controlled, 40 µm, metal bowl, manual condensate drain, (MS pressure gauge with pressure gauge scale in bar or PSI), 0.5 ... 7 bar
J50	MS-LFR-D6-E-U-V-DI-AS	Filter regulator, lockable, directly controlled, 40 µm, metal bowl, fully automatic condensate drain, (MS pressure gauge with pressure gauge scale in bar or PSI), 0.5 ... 7 bar
J53	MS-LFR-D6-C-U-M-DI-AS	Filter regulator, lockable, directly controlled, 5 µm, metal bowl, manual condensate drain, (MS pressure gauge with pressure gauge scale in bar or PSI), 0.5 ... 7 bar
J56	MS-LFR-D6-C-U-V-DI-AS	Filter regulator, lockable, directly controlled, 5 µm, metal bowl, fully automatic condensate drain, (MS pressure gauge with pressure gauge scale in bar or PSI), 0.5 ... 7 bar
J59	MS-LFR-D6-E-U-M-AS	Filter regulator, lockable, piloted, 40 µm, metal bowl, manual condensate drain, (MS pressure gauge with pressure gauge scale in bar or PSI), 0.5 ... 7 bar
J62	MS-LFR-D6-E-U-V-AS	Filter regulator, lockable, piloted, 40 µm, metal bowl, fully automatic condensate drain, (MS pressure gauge with pressure gauge scale in bar or PSI), 0.5 ... 7 bar
J65	MS-LFR-D6-C-U-M-AS	Filter regulator, lockable, piloted, 5 µm, metal bowl, manual condensate drain, (MS pressure gauge with pressure gauge scale in bar or PSI), 0.5 ... 7 bar
J68	MS-LFR-D6-C-U-V-AS	Filter regulator, lockable, piloted, 5 µm, metal bowl, fully automatic condensate drain, (MS pressure gauge with pressure gauge scale in bar or PSI), 0.5 ... 7 bar

Type codes

Overview list – Service unit components MS9		
Code	Type	Description
Filter regulator MS-LFR		
J71	MS-LFR-D7-C-U-M-AS	Filter regulator, lockable, piloted, 5 µm, metal bowl, manual condensate drain, (MS pressure gauge with pressure gauge scale in bar or PSI), 0.5 ... 12 bar
J72	MS-LFR-D7-C-U-V-AS	Filter regulator, lockable, piloted, 5 µm, metal bowl, fully automatic condensate drain, (MS pressure gauge with pressure gauge scale in bar or PSI), 0.5 ... 12 bar
J73	MS-LFR-D7-E-U-M-AS	Filter regulator, lockable, piloted, 40 µm, metal bowl, manual condensate drain, (MS pressure gauge with pressure gauge scale in bar or PSI), 0.5 ... 12 bar
J74	MS-LFR-D7-E-U-V-AS	Filter regulator, lockable, piloted, 40 µm, metal bowl, fully automatic condensate drain, (MS pressure gauge with pressure gauge scale in bar or PSI) 0.5 ... 12 bar
J103	MS-LFR-D7-E-U-M-RG-AS	Filter regulator, piloted, 40 µm, metal bowl, manual condensate drain, integrated pressure gauge with red/green scale, can be locked using accessories, 0.5 ... 12 bar
J104	MS-LFR-D7-E-U-V-RG-AS	Filter regulator, piloted, 40 µm, metal bowl, fully automatic condensate drain, integrated pressure gauge with red/green scale, can be locked using accessories, 0.5 ... 12 bar
J105	MS-LFR-D7-C-U-M-RG-AS	Filter regulator, piloted, 5 µm, metal bowl, manual condensate drain, integrated pressure gauge with red/green scale, can be locked using accessories, 0.5 ... 12 bar
J106	MS-LFR-D7-C-U-V-RG-AS	Filter regulator, piloted, 5 µm, metal bowl, fully automatic condensate drain, integrated pressure gauge with red/green scale, can be locked using accessories, 0.5 ... 12 bar
J107	MS-LFR-D6-E-U-M-RG-AS	Filter regulator, piloted, 40 µm, metal bowl, manual condensate drain, integrated pressure gauge with red/green scale, can be locked using accessories, 0.3 ... 7 bar
J108	MS-LFR-D6-E-U-V-RG-AS	Filter regulator, piloted, 40 µm, metal bowl, fully automatic condensate drain, integrated pressure gauge with red/green scale, can be locked using accessories, 0.3 ... 7 bar
J109	MS-LFR-D6-C-U-M-RG-AS	Filter regulator, piloted, 5 µm, metal bowl, manual condensate drain, integrated pressure gauge with red/green scale, can be locked using accessories, 0.3 ... 7 bar
J110	MS-LFR-D6-C-U-V-RG-AS	Filter regulator, piloted, 5 µm, metal bowl, fully automatic condensate drain, integrated pressure gauge with red/green scale, can be locked using accessories, 0.3 ... 7 bar
J111	MS-LFR-D7-E-U-M-A4-AS	Filter regulator, piloted, 40 µm, metal bowl, manual condensate drain, adapter for EN pressure gauge 1/4, can be locked using accessories, 0.5 ... 12 bar
J112	MS-LFR-D7-E-U-V-A4-AS	Filter regulator, piloted, 40 µm, metal bowl, fully automatic condensate drain, adapter for EN pressure gauge 1/4, can be locked using accessories, 0.5 ... 12 bar
J113	MS-LFR-D7-C-U-M-A4-AS	Filter regulator, piloted, 5 µm, metal bowl, manual condensate drain, adapter for EN pressure gauge 1/4, can be locked using accessories, 0.5 ... 12 bar
J114	MS-LFR-D7-C-U-V-A4-AS	Filter regulator, piloted, 5 µm, metal bowl, fully automatic condensate drain, adapter for EN pressure gauge 1/4, can be locked using accessories, 0.5 ... 12 bar
J115	MS-LFR-D6-E-U-M-A4-AS	Filter regulator, piloted, 40 µm, metal bowl, manual condensate drain, adapter for EN pressure gauge 1/4, can be locked using accessories, 0.3 ... 7 bar
J116	MS-LFR-D6-E-U-V-A4-AS	Filter regulator, piloted, 40 µm, metal bowl, fully automatic condensate drain, adapter for EN pressure gauge 1/4, can be locked using accessories, 0.3 ... 7 bar
J117	MS-LFR-D6-C-U-M-A4-AS	Filter regulator, piloted, 5 µm, metal bowl, manual condensate drain, adapter for EN pressure gauge 1/4, can be locked using accessories, 0.3 ... 7 bar
J118	MS-LFR-D6-C-U-V-A4-AS	Filter regulator, piloted, 5 µm, metal bowl, fully automatic condensate drain, adapter for EN pressure gauge 1/4, can be locked using accessories, 0.3 ... 7 bar

Type codes

Overview list – Service unit components MS9		
Code	Type	Description
Filter regulator MS-LFR		
J122	MS-LFR-D6-E-U-M-AG-MPA-AS	Filter regulator, piloted, 40 µm, metal bowl, manual condensate drain, integrated pressure gauge with MPa scale, can be locked using accessories, 0.03 ... 0.7 MPa
J123	MS-LFR-D6-E-U-V-AG-MPA-AS	Filter regulator, piloted, 40 µm, metal bowl, fully automatic condensate drain, integrated pressure gauge with MPa scale, can be locked using accessories 0.03 ... 0.7 MPa
Activated carbon filter MS-LFX		
L2	MS-LFX-U	Activated carbon filter with metal bowl
Lubricator MS-LOE (not with EU EX2/EX4 certification)		
M2	MS-LOE-U	Lubricator with metal bowl
Pressure regulator MS-LR		
N1	MS-LR-D5-DI-AS	Pressure regulator, lockable, directly controlled, (MS pressure gauge with pressure gauge scale in bar or PSI) 0.3 ... 4 bar
N2	MS-LR-D6-DI-AS	Pressure regulator, lockable, directly controlled, (MS pressure gauge with pressure gauge scale in bar or PSI) 0.3 ... 7 bar
N7	MS-LR-D5-DI-KD-AS	Pressure regulator, lockable, directly controlled, rotary knob underneath (MS pressure gauge with pressure gauge scale in bar or PSI) 0.3 ... 4 bar
N8	MS-LR-D6-DI-KD-AS	Pressure regulator, lockable, directly controlled, rotary knob underneath (MS pressure gauge with pressure gauge scale in bar or PSI) 0.3 ... 7 bar
N35	MS-LR-D5-AS	Pressure regulator, lockable, piloted, (MS pressure gauge with pressure gauge scale in bar or PSI) 0.3 ... 4 bar
N36	MS-LR-D6-AS	Pressure regulator, lockable, piloted, (MS pressure gauge with pressure gauge scale in bar or PSI) 0.3 ... 7 bar
N37	MS-LR-D7-AS	Pressure regulator, lockable, piloted, (MS pressure gauge with pressure gauge scale in bar or PSI) 0.5 ... 12 bar
N53	MS-LR-D5-RG-AS	Pressure regulator, integrated pressure gauge with red/green scale, can be unlocked with accessories 0.3 ... 4 bar
N54	MS-LR-D6-RG-AS	Pressure regulator, integrated pressure gauge with red/green scale, can be locked using accessories 0.3 ... 7 bar
N55	MS-LR-D7-RG-AS	Pressure regulator, integrated pressure gauge with red/green scale, can be locked using accessories 0.5 ... 12 bar
N56	MS-LR-D5-A4-AS	Pressure regulator, adapter for EN pressure gauge 1/4, can be locked using accessories 0.3 ... 4 bar
N57	MS-LR-D6-A4-AS	Pressure regulator, adapter for EN pressure gauge 1/4, can be locked using accessories 0.3 ... 7 bar
N58	MS-LR-D7-A4-AS	Pressure regulator, adapter for EN pressure gauge 1/4, can be locked using accessories 0.5 ... 12 bar
N61	MS-LR-D6-AG-MPA-AS	Pressure regulator, integrated pressure gauge with MPa scale, can be locked using accessories 0.03 ... 0.7 MPa

Type codes

Overview list – Service unit components MS9		
Code	Type	Description
Flow sensor SFAM (only in flow direction from left to right)		
U9	SFAM-5000-M-2SA-M12	Flow sensor, max. 5000 l/min, manifold assembly, 2x PNP or NPN, 1 analogue output 4 ... 20 mA, M12 plug, A-coded
U10	SFAM-5000-M-2SV-M12	Flow sensor, max. 5000 l/min, manifold assembly, 2x PNP or NPN, 1 analogue output 0 ... 10 V, M12 plug, A-coded
U11	SFAM-10000-M-2SA-M12	Flow sensor, max. 10000 l/min, manifold assembly, 2x PNP or NPN, 1 analogue output 4 ... 20 mA, M12 plug, A-coded
U12	SFAM-10000-M-2SV-M12	Flow sensor, max. 10000 l/min, manifold assembly, 2x PNP or NPN, 1 analogue output 0 ... 10 V, M12 plug, A-coded
U13	SFAM-15000-M-2SA-M12	Flow sensor, max. 15000 l/min, manifold assembly, 2x PNP or NPN, 1 analogue output 4 ... 20 mA, M12 plug, A-coded
U14	SFAM-15000-M-2SV-M12	Flow sensor, max. 15000 l/min, manifold assembly, 2x PNP or NPN, 1 analogue output 0 ... 10 V, M12 plug, A-coded
Soft-start/quick exhaust valve MS-SV (not with EX2/EX4 EU certification)		
V12	MS-SV-C-V24-S	Soft-start/quick exhaust valve, Performance Level c, category 1, single channel, maximum attainable to EN ISO 13849-1, 24 V DC, with silencer
V22	MS-SV-C-V24-S-AD7	Soft-start/quick exhaust valve, Performance Level c, category 1, single channel, maximum attainable to EN ISO 13849-1, 24 V DC, with silencer, pressure sensor without display, M8 plug, PNP, 3-pin
V35	MS-SV-C-10V24P-S	Soft-start/quick exhaust valve, Performance Level c, category 2, single channel with sensing, maximum attainable to ISO 13849-1, electrical 24V DC, M12 to IEC 61076-2-101, 10 bar, with silencer
V36	MS-SV-C-10V24P-S-AD7	Soft-start/quick exhaust valve, Performance Level c, category 2, single channel with sensing, maximum attainable to ISO 13849-1, electrical 24 V DC, M12 to IEC 61076-2-101, 10 bar, silencer, pressure sensor with operational status indicator, M8 plug, threshold value comparator, PNP, N/O contact
Water separator MS-LWS		
W1	MS-LWS-U-V	Water separator, metal bowl, fully automatic condensate drain