

Control blocks for two-hand start ZSB

FESTO



Key features

Function


The pneumatic control block for two-hand start ZSB is used where the operator is exposed to a risk of accident during manual operation, e.g. when triggering compressed air cylinders or equipment where both hands must be out of the danger zone during start-up.

The ZSB only switches when both inputs 1_1 and 1_2 of the ZSB are supplied simultaneously, i.e. within max. 0.5 seconds, by two external 3/2-way pushbutton valves. There is an output signal at connection 2. If both pushbutton valves are activated, outlet 2 is pressurised.

If one or both pushbutton valves are released, the flow is immediately interrupted and outlet 2 is no longer pressurised. The system exhausts from 2 to 3.

The pneumatic control block for two-hand start is a safety device as defined in the EU Machinery Directive. It conforms to category 1, PL "c" in accordance with EN ISO 13849-1 and to Type III A in accordance with EN 574.

Sample circuit




Note

When installing the two manual pushbuttons for actuating the control block for two-hand start, make sure that the protective effect cannot easily be overridden, e.g. through actuation with a hand and elbow etc. If necessary, attach an additional guard plate to the manual pushbuttons!


- [1] Front panel valve with pushbutton actuator, e.g. SV-3, T-30
- [2] Control chain
- [3] Pressure sequence valve, e.g. VD-3-PK-3
- [4] Service unit components, e.g. MS or D series

Peripherals overview



Accessories		Brief description	→ Page/Internet
[1]	Front panel valve SV	Poppet valve with quick snap-in coupling for actuator attachments	6
[2]	Pushbutton actuator T	Actuator attachment for front panel valve SV	6
[3]	Mushroom pushbutton P	Actuator attachment for front panel valve SV	6
[4]	Silencer U	For noise reduction at the exhaust port	6
[5]	Pressure sequence valve VD	For securing the minimum pressure of 4 bar required for operation	6
[6]	Service unit combination • D series • MS series	For compressed air preparation	lfr*k* msb

Datasheet



-  - Flow rate
up to 50 l/min
-  - Temperature range
0 ... +60°C
-  - Operating pressure
0.4 ... 0.8 MPa

**Safety data**

Safety function	Two-hand control in accordance with EN ISO 12100
Performance Level (PL)	Two-hand control: category 1, PL c in accordance with EN ISO 13849-1
Tried-and-tested component	Yes
Standard approval	Type III A according to EN 574
Certificate-issuing authority	IFA 1201046
CE marking (see declaration of conformity)	To EU Machinery Directive
Shock resistance	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27

General technical data

Pneumatic connection	G1/8
Nominal width [mm]	4
Actuation type	Pneumatic
Design	Poppet valve with spring return
Type of mounting	Via through-hole Via female thread
Mounting position	Any
Standard nominal flow rate [l/min]	50
Product weight [g]	420

Operating and environmental conditions

Operating pressure	[MPa]	0.4 ... 0.8
	[bar]	4 ... 8
	[psi]	58 ... 116
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Ambient temperature [°C]	0 ... +60	
Corrosion resistance class CRC ¹⁾	1	
CE marking (see declaration of conformity) ²⁾	To EU Machinery Directive	
UKCA marking (see declaration of conformity) ²⁾	To UK regulations for machines	
Certificate-issuing authority	IFA 1201046 Intertek UK-MCR-0080	

1) More information www.festo.com/x/topic/crc2) More information: www.festo.com/catalogue/zsb → Support/Downloads.**Materials**

Housing	Anodised wrought aluminium alloy
Cover	Die-cast aluminium
Seals	NBR
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L


Datasheet

Dimensions

Download CAD data → www.festo.com

[1] Filter

- 1₁, 1₂ = Inputs
- 2 = Output
- 3 = Exhaust





Type	B1	B2	B3	B4	D1	D2	D3 Ø	H1	H2	H3	H4	H5	H6	L1	L2	L3
ZSB	50	38	30.1	7	G1/8	M5	5.3	88	38	22	48.5	32.5	11	50	40	8

Ordering data


	Part no.	Type
Control block for two-hand start	576656	ZSB-1/8-B

Accessories

Ordering data – Front panel valve SV					Datasheets → Internet: sv
	Pneumatic connection	Valve function	Operating pressure [bar]	Part no.	Type
	M5	3/2-way valve, closed, monostable	–0.95 ... 8	6817	SV-3-M5

Ordering data – Pushbutton actuator T					Datasheets → Internet: t
	Colour	Installation diameter [mm]	Part no.	Type	
	Black	22.5	9289	T-22-SW	
		30.5	9291	T-30-SW	

Ordering data – Mushroom pushbutton P					Datasheets → Internet: p
	Colour	Installation diameter [mm]	Part no.	Type	
	Black	22.5	9293	P-22-SW	
		30.5	9295	P-30-SW	

Ordering data – Pressure sequence valve VD					Datasheets → Internet: vd
	Pneumatic connection	Valve function	Operating pressure [bar]	Part no.	Type
	PK-3	3/2-way valve, normally closed, adjustable switching pressure	1.8 ... 8	9270	VD-3-PK-3

Ordering data – Silencer U					Datasheets → Internet: u
	Pneumatic connection	Material	Part no.	Type	
	G1/8	PE	2307	U-1/8	
		Die-cast aluminium	6841	U-1/8-B	

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change