


Linear drives ELGL-LAS, with air bearing and linear motor

FESTO



Linear drives ELGL-LAS, with air bearing and linear motor

Key features

FESTO

At a glance

The electric linear drive ELGL is a handling axis with air-bearing guide and integrated linear motor. The drive elements and the air bearing form a single unit. The slide moves on the stator rail. An integrated displacement encoder sends signals to the controller.


The displacement encoder, controller and motor operate in a closed-loop control circuit.

This enables the motor to regulate to specified set values for speed and position within the permitted stroke range with a high degree of accuracy.

Advantages

- Highly accurate positioning and very good linearity thanks to the air bearing
- Integrated locking brake function through magnetic pretensioning of the air bearing
- Multiple carriages possible on one axis
- Opposing and synchronous movements possible
- No friction on the guide parts
- Maintenance and wear-free
- Insensitive to dirt thanks to air bearing

The technology in detail



- 1 Mounting thread with centring recesses
- 2 Slide
- 3 Supply port for air bearing
- 4 Stator
- 5 End stop with rubber buffer, shock absorbers can alternatively be screwed in
- 6 Integrated displacement encoder
- 7 Sensor
- 8 Electrical interface, rotatable in steps of 90°
- 9 Mounting thread for foot mountings

Complete system consisting of linear drive and motor controller

Linear axis ELGL

→ 3

Servo motor controller CMMP-AS

→ Internet: motor controller




Type codes

		ELGL	-	L	AS	-	30	-	500	-	M	-	M	-		-		-	R	-	E	-	B	-	F
Function																									
ELGL	Linear drives																								
Drive function																									
L	Linear motor																								
Motor technology																									
AS	AC synchronous																								
Size																									
Stroke [mm]																									
Slide 1																									
S	Double coil system																								
M	Triple coil system																								
L	Quadruple coil system																								
Slide 2																									
S	Double coil system																								
M	Triple coil system																								
L	Quadruple coil system																								
Slide 3																									
S	Double coil system																								
M	Triple coil system																								
L	Quadruple coil system																								
Slide 4																									
S	Double coil system																								
M	Triple coil system																								
L	Quadruple coil system																								
Electrical connection																									
R	Angled plug, rotatable																								
Measuring unit																									
E	Encoder																								
Electrical interface																									
B	Serial bi-directional (BISS)																								
Mounting attachments																									
	None																								
F	Foot mounting																								

Linear drives ELGL-LAS, with air bearing and linear motor

Peripherals overview

FESTO



Linear drives ELGL-LAS, with air bearing and linear motor

Peripherals overview

FESTO

Accessories			
Type	Brief description		→ Page/Internet
1 Shock absorber YSRW	For avoiding damage at the end stop in the event of malfunction		19
2 Centring sleeve ZBH	<ul style="list-style-type: none"> For centring loads and attachments on the slide Centring sleeves are not included in the scope of delivery of the drive 		19
3 Mounting kit EAHT	For mounting an energy chain (type: E6.29 or E6.40) on the linear drive ELGL		17
4 Foot mounting EAHF	<ul style="list-style-type: none"> For mounting the axis on the end cap 2 included in the scope of delivery 		14
5 Mounting kit EAHC	<ul style="list-style-type: none"> For mounting a pneumatic linear drive DGC on the linear drive ELGL The slides are connected to each other via a self-aligning rod coupler 		18
6 Linear drive DGC-18-...	For relieving the load on the linear motor when used vertically (→ below)		dgc
7 Adjustable foot mounting EAHF-...-PJ	<ul style="list-style-type: none"> For mounting the axis on the stator Height-adjustable foot mounting, compensates for unevenness of the mounting surface 1 included in the scope of delivery 		15
8 Foot mounting EAHF-...-P	<ul style="list-style-type: none"> For mounting the axis on the stator 2 included in the scope of delivery 		14
9 Sensor bracket EAPR	For attaching the inductive proximity sensors to the foot mountings EAHF-...-P or EAHF-...-PJ		16
10 Proximity sensor SIES	Inductive proximity sensor, square design		19
11 Proximity sensor SIEN	Inductive proximity sensor, round design		20
12 Connecting cable NEBU	For connecting the proximity sensor with plug connection to the controller		20
13 Motor cable NEBM	<ul style="list-style-type: none"> For connecting the motor and controller Connection can be rotated in steps of 90° 		19
13 Encoder cable NEBM	<ul style="list-style-type: none"> For connecting the displacement encoder and controller Connection can be rotated in steps of 90° 		19


Compressed air backup for vertical operation

A pneumatic linear drive DGC-18 can be attached to the linear drive ELGL to protect the linear motor from overheating. The effective load is additionally held by the DGC when approaching the position by means of an appropriate backpressure in the DGC.

Ordering aid:

Part number: 532446

Type: DGC-18-...-G-...




- 1 Linear drive ELGL
- 2 Linear drive DGC
- 3 Self-aligning rod coupler FK
- 4 Mounting kit EAHC

Linear drives ELGL-LAS, with air bearing and linear motor

FESTO

Technical data

Function



Size
30 ... 120

Stroke length
1 ... 5,750 mm

 Note

All values are based on a normal temperature of 23 °C.
Dynamic response and accuracy depend on the mounting (rigidity) and temperature stresses (heat concentration).



General technical data							
Size	30	64	120				
Coil system	S	S	M	S	M	L	
Mechanical							
Constructional design	Electric linear direct drive						
	Guide with integrated displacement encoder						
Guide	Air bearing						
Type of mounting	Via accessories						
Mounting position	Horizontal	Any					
Effective stroke	[mm]	1 ... 740	1 ... 1,750 ¹⁾	1 ... 1,650 ¹⁾	1 ... 1,750 ¹⁾	1 ... 1,650 ¹⁾	1 ... 1,550 ¹⁾
Max. feed force Fx	[N]	44	119	164	240	310	450
Continuous feed force Fx	[N]	44	110	160	217	282	330
Max. speed	[m/s]	4			3.4	3.2	2
Max. acceleration	[m/s²]	15.4	29.4	29.1	47.6	40.4	50.2
Repetition accuracy	[mm]	±0.01					
Locking brake	Integrated by means of air bearing						
Pneumatic							
Operating pressure	[bar]	5					6
Air consumption	[l/min]	15	15	20	15	20	40
Electric							
Type of motor	Linear AC servo motor						
Displacement encoder	Magnetic						
Intermediate circuit voltage	[V]	600					
Peak current	[A]	4.0	4.0	4.0	4.5	4.5	4.5
Nominal current	[A]	3.5	3.5	3.0	3.5	3.0	2.75
Magnetic radiation	None						

1) Work strokes up to 5,750 mm on request

Operating and environmental conditions		
Ambient temperature ¹⁾ [°C]	0 ... +40	
Max. motor temperature [°C]	70	
Normal temperature ²⁾ [°C]	23	
Temperature monitoring	Automatic switch-off in event of over-temperature (PTC resistor)	
Degree of protection	IP65	
Relative air humidity (non-condensing) [%]	20 ... 80	
CE mark (see declaration of conformity)	To EU EMC Directive	
	To EU Low Voltage Directive	
Certification	C-Tick	

1) Note operating range of proximity sensors


2) Unless otherwise stated, all values are based on normal temperature

Linear drives ELGL-LAS, with air bearing and linear motor

Technical data


FESTO

Weight							
Size		30	64	120			
Coil system		S	S	M	S	M	L
Slide	[kg]	2.8	3.8	5.0	4.7	6.8	8.7
Stator	[kg/m]	4.9	13.3		27.0		

Materials	
Sectional view	
	
Linear drive	
1 Stator	Steel
2 Housing	Wrought aluminium alloy, anodised
– Note on materials	Contains PWIS (paint-wetting impairment substances)
	RoHS-compliant

Static characteristic load values


The indicated forces and torques refer to the slide surface. The point of application of force is the point where the centre of the guide and the longitudinal centre of the slide intersect. These values must not be exceeded during dynamic operation. Attention must be paid to the acceleration and braking.



If the axis is simultaneously subjected to more than two of the indicated forces and torques, the following equation must be satisfied in addition to the indicated maximum loads:

$$\frac{|F_y|}{F_{y_{\max.}}} + \frac{|F_z|}{F_{z_{\max.}}} + \frac{|M_x|}{M_{x_{\max.}}} + \frac{|M_y|}{M_{y_{\max.}}} + \frac{|M_z|}{M_{z_{\max.}}} \leq 1$$

Permissible forces and torques							
Size		30	64	120			
Coil system							
F _y _{max.}	[N]	600	600	600	600	600	600
Limit load F _z _{max.}	[N]	160	700	1,000	1,300	1,700	2,500
Tensile load F _z _{max.}	[N]	35	140	220	260	300	400
M _x _{max.}	[Nm]	1.2	8	10	14	21	28
M _y _{max.}	[Nm]	7	20	28	45	60	80
M _z _{max.}	[Nm]	20	20	30	20	30	50

 Note
 Positioning Drives
 sizing software
www.festo.com


Linear drives ELGL-LAS, with air bearing and linear motor

FESTO


Technical data

Speed v and current I as a function of feed force F


ELGL-LAS-30-...-S




ELGL-LAS-64-...-S




ELGL-LAS-64-...-M




ELGL-LAS-120-...-S



ELGL-LAS-120-...-M



ELGL-LAS-120-...-L



— Speed m/s
- - - Current A

 Note

Characteristics for intermediate circuit voltage of 600 V.

Linear drives ELGL-LAS, with air bearing and linear motor

Technical data

FESTO

Mounting options

The stator has an evenness value of $7 \mu\text{m}/300 \text{ mm}$. To ensure the quality of the air bearing, the mounting surface must be correspondingly precise.

For points of support with smooth surfaces, the linear drive can be mounted directly at the stator **1** or with the help of the foot mountings **2**.


If the surface is not sufficiently even, the foot mounting **3** is used together with the adjustable foot mounting **4**.

A 3 or 4-point mounting is recommended to secure the load.

1 Direct mounting

Range of application:

- Only with smooth surface (e.g. granite table)




- 1** Linear drive
- 2** Mounting surface
- 3** Socket head screw

2 Angled foot mounting

Range of application:

- Only with smooth surface (e.g. granite table)
- Up to a stator length of max. 500 mm




- 1** Linear drive
- 2** Mounting surface
- 3** Socket head screw
- 4** Foot mounting EAHF...

3 Foot mounting

Range of application:

- With milled surface (good evenness)
- Recommended support spacing: every 360 mm




- 1** Linear drive
- 2** Mounting surface
- 3** Socket head screw
- 4** Foot mounting EAHF-...-P

4 Adjustable foot mounting

Range of application:

- With surface with low evenness
- Recommended support spacing: every 360 mm



- 1** Linear drive
- 2** Mounting surface
- 3** Socket head screw
- 4** Foot mounting EAHF-...-PJ

Linear drives ELGL-LAS, with air bearing and linear motor


Technical data

FESTO



Dimensions

Download CAD data → www.festo.com


ELGL-64/120




ELGL-30



ELGL- ... -S



View A



1 → table on page 12

2 Hole for centring sleeve ZBH-9, thread depth 12 mm

3 Hole for centring sleeve ZBH-9, thread depth 9 mm

 Note

Use max. 4 screws to mount the effective load.



Linear drives ELGL-LAS, with air bearing and linear motor

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



Size	B1	B3	B4	B5	B6	B7	B8	B9	D1	D2	D4	D5	D6	D7	D8	H1
						±0.01								H7		
30	105.8	–	42	84	30	20	–	3	M10x1	–	M4	M5	18	9	M6	62
64	139.8	83.5	59	118	64	40	24	8	M14x1	M8x1	M6	M5	18	9	M6	62
120	195.8	111.5	87	174	120	80	72	12	M14x1	M8x1	M6	M5	18	9	M6	62

Size	H2	H3	H4	H5	H6	H7	L4	L5	L6	L7	L8	L9	L10	T1	T2	T3	T4
													±0.01		+0.1		
30	–	46.5	47	58	12	1	20	17	5	10	120	20	40	10	2.1	12	9
64	50	47	47	60	12	1	16	14	5	30	120	–	40	12	2.1	12	9
120	50	47	52	60	12	1	16	14	5	30	120	–	40	12	2.1	12	9


Size	Rotor variant	B2	D3	L1	L2	L3
						±0.01
30	S	68	M5	248.6	210	25
64	S	102	M5	248.6	210	25
	M	102	M5	348.6	310	35
120	S	158	M5	248.6	210	25
	M	158	M5	348.6	310	35
	L	154	G1/8	453.1	410	25

Linear drives ELGL-LAS, with air bearing and linear motor

FESTO

Technical data

Total length of the drive with one slide						
Size	30	64	120			
Slide variant	S	S	M	S	M	L
Work stroke [mm]						
100	360	350	450	350	450	550
200	460	450	550	450	550	650
300	560	550	650	550	650	765
400	660	650	765	650	765	850
500	765	765	850	765	850	950
600	860	850	950	850	950	1,050
700	960	950	1,050	950	1,050	1,150
800	–	1,050	1,150	1,050	1,150	1,250
900	–	1,150	1,250	1,150	1,250	1,365
1,000	–	1,250	1,365	1,250	1,365	1,450
1,100	–	1,365	1,450	1,365	1,450	1,550
1,200	–	1,450	1,550	1,450	1,550	1,650
1,300	–	1,550	1,650	1,550	1,650	1,750
1,400	–	1,650	1,750	1,650	1,750	1,850
1,500	–	1,750	1,850	1,750	1,850	1,965
1,600	–	1,850	1,965	1,850	1,965	–
1,700	–	1,965	–	1,965	–	–



Note

Total length for other variants
on request.

Linear drives ELGL-LAS, with air bearing and linear motor

Ordering data – Modular products

FESTO

Ordering table								
Size		30	64	120	Condi- tions	Code	Enter code	
[M]	Module No.	560753	560754	560755				
	Function	Electrical linear drive				ELGL		ELGL
	Drive type	Linear motor				-L		-L
	Motor technology	AC synchronous				AS		AS
	Size [mm]	30				-30		
			64			-64		
				120		-120		
	Stroke [mm]	1 ... 740	1 ... 1,750		[1]	-...		
	Slide 1	Double coil system, 3 strings				-S		
			Triple coil system, 3 strings			-M		
			Quadruple coil system, 3 strings		-L			
[O]	Slide 2	None						
		Double coil system, 3 strings				-S		
			Triple coil system, 3 strings			-M		
				Quadruple coil system, 3 strings		-L		
	Slide 3	None					ELGL	
		Double coil system, 3 strings				-S		
			Triple coil system, 3 strings			-M		
				Quadruple coil system, 3 strings		-L		
	Slide 4	None						
		Double coil system, 3 strings				-S		
			Triple coil system, 3 strings			-M		
				Quadruple coil system, 3 strings		-L		
	[M]	Electrical connection	Angled plug, rotatable				-R	-R
		Measuring unit	Encoder				E	E
		Electrical interface	Serial bi-directional (BiSS)				-B	-B
	[O]	Mounting attachments	None					
Foot mounting			[2]	-F				

[1] Stroke For sizes 64 and 120: 1,750 ... 5,750 mm on request

[2] F Can be selected with stator length <500 mm

Transfer order code

ELGL - **LAS** - - - - - - - - **RE** - **B** -

Linear drives ELGL-LAS, with air bearing and linear motor

Accessories

FESTO

Foot mounting EAHF


2 included in the scope of delivery

Material:

Aluminium

Contains PWIS (paint-wetting
impairment substances)

RoHS-compliant



Dimensions and ordering data												
For size	AB	AH -0.1	AO	AT	AU	D1	T1	TR	US	CRC ¹⁾	Weight [g]	Part No. Type
30	5.5	2	10	10	18	10	3	18	29	1	180	564252 EAHF-L1-30
64	6.5	2	12	10	26	11	3	44	60	1	400	564253 EAHF-L1-64
120	6.5	2	12	10	26	11	3	78	94	1	600	564254 EAHF-L1-120

1) Corrosion resistance class 1 as per Festo standard 940 070

Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Foot mounting EAHF-...-P


2 included in the scope of delivery

Material:

Aluminium

Contains PWIS (paint-wetting
impairment substances)

RoHS-compliant



Dimensions and ordering data												
For size	B1	B2	B3	B8	D1	D2	H1 -0.01	H2	L1	CRC ¹⁾	Weight [g]	Part No. Type
30	107	50	10	20	11	6.5	28	30	30	1	250	564246 EAHF-L1-30-P
64	141	84	10	24	15	8.5	28	30	30	1	310	564247 EAHF-L1-64-P
120	197	140	10	72	15	8.5	28	30	30	1	450	564248 EAHF-L1-120-P

1) Corrosion resistance class 1 as per Festo standard 940 070

Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Linear drives ELGL-LAS, with air bearing and linear motor

Accessories

Adjustable foot mounting

EAHF-...-PJ


1 included in the scope of delivery

Material:

Aluminium

Contains PWIS (paint-wetting
impairment substances)

RoHS-compliant



Dimensions and ordering data													
For size	B1	B2	B3	B8	D1	D2	D3	H1	H2	L1	CRC ¹⁾	Weight [g]	Part No. Type
30	106	50	10	20	11	6.5	22	28	29	30	1	210	564249 EAHF-L1-30-PJ
64	140	84	10	24	15	8.5	22	28	29	20	1	230	564250 EAHF-L1-64-PJ
120	196	140	10	72	15	8.5	22	28	29	20	1	260	564251 EAHF-L1-120-PJ

1) Corrosion resistance class 1 as per Festo standard 940 070
Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.


Linear drives ELGL-LAS, with air bearing and linear motor

FESTO

Accessories

Sensor bracket EAPR

Material:
Aluminium
Contains PWIS (paint-wetting
impairment substances)
RoHS-compliant



Dimensions and ordering data

For size	B1	B2	B3	D1	H1	H2	H3	H4
30, 64, 120	17.5	10.5	9	M8	11.2	17	17.7	8.5

For size	L1	L2	L3	L4	L5	CRC ¹⁾	Weight [g]	Part No.	Type
30, 64, 120	195	140	60	20	7	1	75	564259	EAPR-L1-S

1) Corrosion resistance class 1 as per Festo standard 940 070
Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Linear drives ELGL-LAS, with air bearing and linear motor

FESTO

Accessories


Mounting kit EAHT

Material:

Aluminium

Contains PWIS (paint-wetting
impairment substances)

RoHS-compliant



Dimensions and ordering data									
For size	B1	H1	H2	L1	L2	CRC ¹⁾	Weight [g]	Part No.	Type
For energy chain type: E6.29									
30, 64, 120	60	62	12	170	50	1	300	564255	EAHT-L1-E6-29-L
	60	62	12	105	50	1	300	564256	EAHT-L1-E6-29-R
For energy chain type: E6.40									
30, 64, 120	76	78	12	210	80	1	400	564257	EAHT-L1-E6-40-L
	76	78	12	146	80	1	400	564258	EAHT-L1-E6-40-R

1) Corrosion resistance class 1 as per Festo standard 940 070

Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Linear drives ELGL-LAS, with air bearing and linear motor

FESTO

Accessories


Mounting kit EAHC

Material:

Aluminium

Contains PWIS (paint-wetting
impairment substances)

RoHS-compliant



Dimensions and ordering data													
For size	B1	B2	B3	B4	B5	B6	B7	B8	B9	D1 Ø	D2 Ø	D3	D4
30	173	95.5	50	10	10	111	56	–	3	11	6.5	M3	M4
64	207	129.5	84	10	10	145	56	24	8	15	8.5	M3	M6
120	263	185.5	140	10	10	201	56	72	12	15	8.5	M3	M6

For size	H1	H2 –0.01	L1	L2	L3	T1	T2	CRC ¹⁾	Weight [g]	Part No.	Type
30	89.6	28	nx120	30	20	8	6	1	960	564260	EAHC-L1-30
64	89.6	28	nx120	30	–	11	6	1	1,100	564261	EAHC-L1-64
120	89.6	28	nx120	30	–	11	6	1	1,350	564262	EAHC-L1-120



1) Corrosion resistance class 1 as per Festo standard 940 070

Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.



Linear drives ELGL-LAS, with air bearing and linear motor

Accessories



FESTO

Ordering data					
	For size	Comment	Part No.	Type	PU ¹⁾
Shock absorber YSRW			Technical data ➔ Internet: ysrw		
	30	For avoiding damage at the end stop in the event of malfunction	191193	YSRW-7-10	1
	64, 120		191195	YSRW-10-17	
Centring sleeve ZBH					
	30, 64, 120	For slide	150927	ZBH-9	10

1) Packaging unit quantity

Ordering data – Cables					
	Brief description	Cable length [m]	Part No.	Type	
	Motor cable, for connecting motor and controller	5	550306	NEBM-T1G7-E-5-N-LE7	
		10	550307	NEBM-T1G7-E-10-N-LE7	
		15	550308	NEBM-T1G7-E-15-N-LE7	
		X length ¹⁾	550309	NEBM-T1G7-E- -N-LE7	
	Encoder cable, for connecting motor and controller	5	550314	NEBM-T1G8-E-5-N-S1G15	
		10	550315	NEBM-T1G8-E-10-N-S1G15	
		15	550316	NEBM-T1G8-E-15-N-S1G15	
		X length ¹⁾	550317	NEBM-T1G8-E- -N-S1G15	





1) Max. 25 m



Ordering data – Proximity sensors, inductive					Technical data → Internet: sies	
	Type of mounting	Switching output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Is screwed on via mounting attachment	PNP	Cable, 3-wire	2.5	178294	SIES-Q8B-PS-K-L
			Plug M8x1, 3-pin	0.3	178295	SIES-Q8B-PS-S-L
N/C contact						
	Is screwed on via mounting attachment	PNP	Cable, 3-wire	2.5	174552	SIES-Q8B-PO-K-L
			Plug M8x1, 3-pin	0.3	174553	SIES-Q8B-PO-S-L

Linear drives ELGL-LAS, with air bearing and linear motor

Accessories

FESTO

Ordering data – Inductive proximity sensors M8						Technical data → Internet: sien	
	Electrical connection		Switching output	LED	Cable length [m]	Part No.	Type
	Cable	Plug M8					
N/O contact							
	3-wire	–	PNP	■	2.5	150386	SIEN-M8B-PS-K-L
	–	3-pin	PNP	■		150387	SIEN-M8B-PS-S-L
N/C contact							
	3-wire	–	PNP	■	2.5	150390	SIEN-M8B-PO-K-L
	–	3-pin	PNP	■		150391	SIEN-M8B-PO-S-L

Ordering data – Connecting cables					Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type	
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541333	NEBU-M8G3-K-2.5-LE3	
			5	541334	NEBU-M8G3-K-5-LE3	
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541338	NEBU-M8W3-K-2.5-LE3	
			5	541341	NEBU-M8W3-K-5-LE3	