



Key features - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm





Innovative

- High-performance valves in sturdy metal housing
- Four valve sizes on one valve terminal
- Standardised from the multi-pin plug to the fieldbus connection and control block
- Dream team: fieldbus valve terminal suitable for CPX electrical peripherals. This means:
 - Forward-looking internal communication system for actuating the valves and CPX modules
- Four valve sizes on one valve terminal without adapters
- Valve functions for integration in control architectures of higher categories to EN ISO 13849-1

Versatile

- Modular system offering a range of configuration options
- Expandable with up to 32 solenoid coils
- Conversions and extensions are possible at any time
- Manifold sub-bases can be extended using four screws, sturdy duct separation on metal substrate
- Integration of innovative function modules possible
- Supply plates enable a flexible air supply and variable pressure zones
- Reverse operation
 High pressure range -0.9 ... 10 bar
- Flow range from 400 l/min up to 4,000 l/min
- Wide range of valve functions
- Valve supply: 24 V DC or 110 V AC

Reliable

- Sturdy and durable metal components
 - Valves
 Manifold sub-bases
 - Manifold s
 - Seals
- Fast troubleshooting thanks to LEDs on the valves and diagnostics via fieldbus
- Reliability of service thanks to valves that can be replaced quickly and easily
- Manual override either non-detenting, non-detenting/detenting or covered
- Durable thanks to tried-and-tested piston spool valves
- Large and durable labelling system
- 100% duty cycle

Easy to mount

- Ready-to-install and tested unit
- Lower selection, ordering, installation and commissioning costs
- Secure mounting on wall or H-rail

Key features - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm



Reduced downtimes:

On-the-spot diagnostics via LEDs

Width 18 mm, 26 mm, 42 mm and 52 mm can be combined on a single valve terminal without adapter

Pneumatic interface to CPX

Simple electrical connections

- Fieldbus connection via CPX
- Multi-pin plug connection with pre-assembled cable or terminal strip (Cage Clamp®)
- Control block via CPX
- AS-interface
- Individual connection

CPX diagnostic interface for handheld devices (channel-oriented diagnostics down to the individual valve)

Quick mounting: Direct mounting using screws or H-rail

Safe: Valves, outputs and logic voltage can be switched off separately

Equipment options

Valve functions

- 2x 2/2-way valve, single solenoid, pneumatic spring, normally closed
- 2x 3/2-way valve, single solenoid - Normally open
 - Normally open, reversible
 - Normally closed
- Normally closed, reversible
- 2x 3/2-way valve, single solenoid
 - 1x normally open, 1x normally closed
 - 1x normally open,
 - 1x normally closed, reversible

- Reliable operation: Manual override. non-detenting/detenting or covered

Flexible:

- 32 valve positions/32 solenoid coils - One valve series for a wide range of flow rates

Functional:

Large ports, flow-optimised ducts, sturdy metal thread or pre-assembled QS connectors

Modular:

Supply plates facilitate the creation of multiple pressure zones as well as numerous additional exhaust and supply ports

Comprehensive range of valve functions

· Soft-start valve for slow and safe

- Safe pressurisation by means of

pressure build-up

- High degree of safety

sensor function

Practical: Large inscription labels

- 5/2-way valve
- Single solenoid, pneumatic
- spring/mechanical spring
- Double solenoid
- Double solenoid with dominant signal
- 5/2-way valve for special functions,
 - single solenoid
 - Mechanical spring
 - Switching position sensing via inductive sensors with PNP or NPN output
- Protection against unexpected start-up to EN 1037
- Reversing

- 5/3-way valve
 - Mid-position pressurised
 - Mid-position closed
 - Mid-position exhausted
- 5/3-way valve for special functions
 - Switching position 14 with memory function (switching position 14 is retained in the event of an emergency-stop application/power failure) since there is no spring return on switching position 12
 - Only for valve terminal (plug-in)
 - Mid-position exhausted or
 - Switching position 14 with memory function
 - Pneumatic spring return

Key features - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Special features

Individual valve on individual sub-base up to width 52 mm

Plug-in

- Electrical connection via standardised 4-pin M12 plug or via 4-pin spring-loaded terminal for configuration by the user
- Available with internal/external pilot air supply

Valve terminal with individual connection

- Max. 20 valve positions/ max. 20 solenoid coils
- Any compressed air supply
- Any number of pressure zones

Square plug or plug-in, with integrated piston position sensing

• Electrical connection to DIN EN 175301-803 type C (square design) or for configuration by the user via 4-pin spring-loaded terminal or cable with open end

Valve terminal with multi-pin plug

• Max. 32 valve positions/

max. 32 solenoid coils

• Any compressed air supply

Parallel modular valve linking

• Any number of pressure zones

connection

Valve terminal with fieldbus connection and electrical peripherals

Type CPX

- Max. 32 valve positions/ max. 32 solenoid coils
- Any compressed air supply
- Any number of pressure zones

AS-interface

- 1 to 8 valve positions/ max. 8 solenoid coils
- Soft-start valve for slow and safe pressure build-up
 - High degree of safety
 - Safe pressurisation by means of sensor function

Combinable

- Width 18 mm: valve flow rate up to 550 (700) l/min
- Width 26 mm: valve flow rate up to 1,100 (1,400) l/min
- Width 42 mm: valve flow rate up to 1,400 l/min
- Width 52 mm: valve flow rate up to 2,900 l/min
- Width 18 mm, 26 mm, 42 mm and 52 mm can be combined on a single valve terminal

- Note

- Valve terminal VTSA complies with ISO 15407-2 in width 18 and 26 mm and
- with ISO 5599-2in width 42 and 52 mm

Values in brackets apply to type 45, VTSA-F

Valve terminal configurator

A valve terminal configurator is available to help you select a suitable VTSA/VTSA-F valve terminal. This makes it much easier to order the right product.

The valve terminals are fully assembled according to your order specification and are individually tested. This reduces assembly and installation time to a minimum.

		→ Internet: www.festo.com
r	You order a valve terminal VTSA using the order code:	You order a valve terminal VTSA-F using the order code:
ł	Ordering system for VTSA	Ordering system for VTSA-F

➔ Internet: vtsa

Ordering system for CPX → Internet: cpx Ordering system for CPX → Internet: cpx

➔ Internet: vtsa-f

Key features - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Valves on individual sub-bases can be

used for actuators further away from

the valve terminal.

Individual pneumatic connection

FESTO

spring-loaded terminal or a cable with

open end 24 V DC or 110 V AC, which

are configured by the user.

(EN 61076-2-101), 4-pin Valve terminal with individual electrical connection Control signals from the controller to The valve terminal can be equipped The electrical connection is the valve terminal are transmitted via with max. 20 valves and established via a 5-pin M12 plug an individual connecting cable. max. 20 solenoid coils. 24 V DC. Valve terminal with multi-pin plug connection Versions Control signals from the controller to The valve terminal can be equipped the valve terminal are transmitted via with max. 32 valves and • Multi-pin plug connection with a pre-assembled multi-wire cable or max. 32 solenoid coils. terminal strip (spring-loaded a self-assembled multi-pin plug terminal) 24 V DC or 110 V AC connection (spring-loaded terminal), • Pre-assembled connecting cable which substantially reduces 24 V DC installation time. • Sub-D plug connector for assembly by the user, 37-pin • Round plug connector M23, 19-pin, 24 V DC **AS-interface connection** CPX: M8, M12, quick connection, A special feature of the AS-interface is With one to eight modular valve the simultaneous transmission of positions (max. 8 solenoid coils). Sub-D, spring-loaded terminal data and supply power via a two-wire This corresponds to one to eight (terminals to IP20). cable. The encoded cable profile valves VTSA/VTSA-F. prevents connection with incorrect • With all available valve functions. More information The connection technology used for → Internet: as-interface polarity. The valve terminal with AS-interface is the inputs can be selected as with available in the following versions: Note The valve terminal VTSA/VTSA-F with (→ page 97). AS-interface connection is based on The technical specifications of the the same electrical manifold module AS-interface system must be as the valve terminal with multi-pin observed in this case. plug connection. This means it is possible to convert a valve terminal → Page 52 with multi-pin plug connection using → Internet: as-interface an AS-interface module

The electrical connection is

4-pin M12 plug 24 V DC

established either via a standardised

Key features - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Valve terminal with fieldbus connection from the CPX system



An integrated fieldbus node manages the communication connection with a higher-order PLC. This enables a space-saving pneumatic and electronic solution. Valve terminals with fieldbus interfaces from the CPX system can be configured with up to 16 manifold sub-bases. With 2 solenoid coils per connection, up to 32 solenoid coils can thus be actuated.

Versions

• Profibus DP

FESTO

- InterbusDeviceNet
- CANopen
- CC-Link
- CPX terminal
- Ethernet/IP
- EtherCAT
- CoDeSys controller
- Modbus/TCP
- PROFINET
- → Internet: cpx

Valve terminal with control block connection from the CPX system



units with protection to IP65 without a control cabinet thanks to two different operating modes.

valve terminal enables the

A controller integrated in the Festo

construction of stand-alone control

In the slave operating mode, these valve terminals can be used for intelligent preprocessing and are therefore ideal modules for designs using decentralised intelligence. In the master operating mode, terminal groups can be designed with many options and functions that can autonomously control a medium-sized machine/system.

- CPX terminal
- → Internet: cpx

CP string extension from the CPX system



The optional CP string extension enables additional valve terminals and I/O modules to be connected to the fieldbus node of the CPX terminal on up to 4 CP strings. Different input and output modules as well as CPV-SC, CPV and CPA valve terminals can be connected. The maximum length of the CP string extension is 10 metres, which means that the extension modules can be mounted directly on-site. All of the required electrical signals are transmitted via the CP cable, which in turn means that no further installation is needed on the extension module. One CP string offers:

- 32 input signals
- 32 output signals for output modules 24 V DC or solenoid coils
- Logic and sensor supply for the input modules
- Load voltage supply for the valve terminals
- Logic supply for the output module
- → Internet: ctec

Key features – Valves

Solenoid valve with switching position sensing, width 26 mm

The single solenoid 5/2-way valve with spring return in width 26 mm features switching position sensing. The normal position of the piston spool valve is monitored.

Designed as plug-in or individual connection valve with pilot valves to ISO 15218 and square plug type C. This valve is not a safety component in accordance with the Machinery Directive 2006/42/EC. It is suitable for use in safety-related parts of control systems to EN ISO 13849-1.

➔ Page 99

Control block with safety function, with	idth 26 mm		
	 These valves are used for special applications, for example for: Protecting against unexpected start-up Reversing Drives in manually loaded devices 	This control block is suitable for use as a press safety valve to EN 962.	This valve is a safety component in accordance with the Machinery Directive 2006/42/EC. → Page 105
For holding, blocking a movement (me	chanically)	For pressureless switching, self-holding	g, pneumatic operation
5/3-way valve for special functions; port 2 is pressurised, port 4 exhausted. Switching position 14 features a memory function.	Possible applications:Using lifting cylindersUsing rotary cylinders	5/3-way valve for special functions (3 phases). Mid-position is exhausted. Switching position 14 features a memory function.	 Possible applications: Pneumatic manual clamps for devices (insert stations)
Pilot air switching valve, width 26 m	m		
	The pilot air switching valve is designed to switch pilot air from duct 1 to 14. The piston position sensing feature of the inductive PNP proximity sensor is realised using a cable and a push-in connector in the size M12x1 to EN 61076-2-104.	This valve is not a safety component in accordance with the Machinery Directive 2006/42/EC. It is suitable for use in safety-related parts of control systems to EN ISO 13849-1. → Page 112 - 🌒 - Note The pilot air switching valve may only by VTSA/VTSA-F in combination with a right type VABE-S6-1RZ Port 14 on the right this.	nt-hand end plate for external pilot air
Soft-start valve, module width 43 m	n		



The soft-start valve is separately electrically actuated, independently of the multi-pin plug, AS-interface or fieldbus connection, via a 4-pin plug to ISO 15407-1 or optionally via an M12 adapter. The valve can optionally be ordered with a sensor that monitors switching of the soft-start valve and in this way supplies the valve terminal or one or more pressure zones with supply air. The optimum pressure build-up required by the application for each pressure zone is configured directly on the valve terminal by setting the switchover pressure and filling time. A maximum of 5 soft-start valves can be integrated on one valve terminal in this way.

➔ Page 118

Peripherals – ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Modular pneumatic peripherals

The modular design of the valve terminal VTSA/VTSA-F enables maximum flexibility right from the planning stage and offers maximum ease of service in operation. The system consists of manifold sub-bases and valves. The manifold sub-bases are screwed together and thus form the support system for the valves. Inside the manifold sub-bases are the connection ducts for supplying compressed air to and venting from the valves on the terminal as well as the working lines for the pneumatic cylinders for each valve. Each manifold sub-base is connected to the next using four screws. Individual valve terminal sections can be isolated and further blocks easily inserted by loosening these screws. This ensures that the valve terminal can be rapidly and reliably extended.

Basic system modularity

Valve modularity





Vertical stacking modularity



Modular electrical peripherals

The manner in which the valves are actuated differs according to whether you are using a multi-pin terminal or fieldbus terminal.

The VTSA/VTSA-F with CPX interface is based on the internal bus system of the CPX and uses this communication system for all solenoid coils and a range of electrical input and output functions.

Parallel linking enables the following: • Transmission of switching

- information
- High valve density
- Compact design
- Position-based diagnostics
- Separate voltage supply for valves

FESTO

- Flexible conversion without address shifting
- Option of CP interface
- CPX-FEC as stand-alone controller with access via Ethernet and web server
- Transmission of status, parameter and diagnostic data
- → Internet: cpx

VTSA/VTSA-F with electrical peripherals CPX

Modularity with electrical peripherals CPX



CPX terminal in metal design



The mechanical connection between the CPX modules in metal design is created using special angle fittings. The CPX terminal can thus be expanded at any time.

Note

The CPX manifold blocks are also available in a metal design. This means a complete solution in a sturdy metal design can be selected for applications of the valve terminal VTSA/VTSA-F in welding environments.

Individual sub-base, width 18 mm, ISO 15407-2

Order code:

Individual sub-bases can be equipped with any valve.

• Using individual part numbers



	Brief description	→ Page/Internet
1 Fitting	1/8" NPT for working air/exhaust ports (1, 3, 5) and working lines (2, 4)	134
2 Silencer	U-1/8-B-NPT for exhaust ports (3, 5)	134
3 Electrical connection	Spring-loaded terminal, cable (open end)	-
4 Valve VSVA	Width 18 mm	81
5 Manual override	Non-detenting/detenting, per solenoid coil	-
6 Cover cap	For non-detenting manual override	95
7 Cover cap	For covered manual override	95
8 Inscription label holder	For valves	98
9 Individual sub-base	For valve VSVA	133
10 Inscription label holder	For manifold blocks	98



	Brief description	→ Page/Internet
1 Fitting	1/4" NPT for working air/exhaust ports (1, 3, 5) and working lines (2, 4)	134
2 Silencer	U-1/4-B-NPT for exhaust ports (3, 5)	134
3 Electrical connection	Spring-loaded terminal, cable (open end)	-
4 Valve VSVA	Width 26 mm	82
5 Manual override	Non-detenting/detenting, per solenoid coil	-
6 Cover cap	For non-detenting manual override	95
7 Cover cap	For covered manual override	95
8 Inscription label holder	For valves	98
9 Individual sub-base	For valve VSVA	133
10 Inscription label holder	For manifold blocks	98

2011/02 - Subject to change



	Brief description	→ Page/Internet
1 Fitting	3/8" NPT for working air/exhaust ports (1, 3, 5) and working lines (2, 4)	134
2 Silencer	U-3/8-B-NPT for exhaust ports (3, 5)	134
3 Electrical connection	Spring-loaded terminal, cable (open end)	-
4 Valve VSVA	Width 42 mm	83
5 Manual override	Non-detenting/detenting, per solenoid coil	-
6 Cover cap	For non-detenting manual override	95
7 Cover cap	For covered manual override	95
8 Inscription label holder	For valves	98
9 Individual sub-base	For valve VSVA	133
10 Inscription label holder	For manifold blocks	98



	Brief description	→ Page/Internet
1 Fitting	$\frac{1}{2}$ " NPT for working air/exhaust ports (1, 3, 5) and working lines (2, 4)	134
2 Silencer	U-1/2-B-NPT for exhaust ports (3, 5)	134
3 Electrical connection	Spring-loaded terminal, cable (open end)	-
4 Valve VSVA	Width 52 mm	84
5 Manual override	Non-detenting/detenting, per solenoid coil	-
6 Cover cap	For non-detenting manual override	95
7 Cover cap	For covered manual override	95
8 Inscription label holder	For valves	98
9 Individual sub-base	For valve VSVA	133
10 Inscription label holder	For manifold blocks	98

Valve terminal pneumatics

- The manifold sub-bases for valves with a width of 18 or 26 mm are either prepared for
- 2 single solenoid valves or
- 2 double solenoid valves.

The manifold sub-bases for valves with a width of 42 or 52 mm are suitable for

- 1 single solenoid valve or
- 1 double solenoid valve.
- Double solenoid valve positions can be equipped with any valve or a blanking plate.
- Single solenoid valve positions can only be equipped with single solenoid valves or a blanking plate.



Valve terminal pneumatics			
	Brief description	→ Page/Internet	
1 Exhaust port cover	For ducted exhaust air (ports 3 and 5 combined)	90	
2 Duct separation/seal	-	90	
3 Manifold sub-base	For soft-start valve	118	
4 Soft-start valve	For slow and safe pressure build-up	118	
5 Plug socket	-	123	
6 Flow control plate	-	95	
7 Pressure regulator plate	-	91	
8 Valve	Width 18 mm or 26 mm	89	
9 Cover cap	For manual override, non-detenting, covered	95	
10 Inscription label holder	For valve	98	
11 Blanking plate	For unused valve position (vacant position)	95	
12 Valve	Width 42 mm or 52 mm	89	
13 End plate with pilot air selector	-	89	
14 Blanking plug	-	134	
15 Manifold sub-base VTSA	For valves with a width of 42 mm or 52 mm	89	
15 Manifold sub-base VTSA-F	For valves with a width of 42 mm or 52 mm	89	
16 Manifold sub-base VTSA	For valves with a width of 18 mm or 26 mm	89	
16 Manifold sub-base VTSA-F	For valves with a width of 18 mm or 26 mm	89	
17 Fittings	-	134	
18 Silencer	-	134	
19 Inscription label holder	For manifold sub-base, sub-base, 90° connection plate	98	
20 Supply plate	-	90	
21 Control element	Regulator knobs in different versions	34	



Valve terminal widths

Order code for VTSA:

- 44E-... for the electrical components
- 44P-... for the pneumatic components
- Order code for VTSA-F:
- 45E-... for the electrical components
- 45P-... for the pneumatic components

Regardless of the type of actuation (e.g. multi-pin plug, fieldbus, etc.), valve terminals VTSA/VTSA-F

- in the widths • 18 mm
- 26 mm
- 42 mm
- 52 mm

can be combined without adapters. This enables a flow range of 400 l/min to 2,900 l/min in the case of VTSA and 700 l/min to 2,900 l/min in the case of VTSA-F to be covered on one valve terminal. A wide range of valve functions and vertical stacking components are available for all widths.



		Brief description	→ Page/Internet
1	Valve	Width 18 mm	89
2	Valve	Width 26 mm	89
3	Valve	Width 42 mm	89
4	Valve	Width 52 mm	89
5	Multi-pin plug connection	Via multi-pin cable 24 V DC	96
6	Inscription labels	For manifold sub-base, sub-base, 90° connection plate	98

Valve terminal with individual electrical connection

Order code for VTSA:

- 44E-... for the electrical components
- 44P-... for the pneumatic components
- Order code for VTSA-F:
- 45E-... for the electrical components
- 45P-... for the pneumatic components

1

Valve terminals VTSA/VTSA-F with individual electrical connection can be expanded with up to 20 valves with max. 20 solenoid coils. The manifold sub-bases for valves with a width of 18 or 26 mm are either prepared for

- 2 single solenoid valves or
- 2 double solenoid valves

and the manifold sub-bases for valves with a width of 42 or 52 mm are prepared for

- 1 single solenoid valve or
- 1 double solenoid valve.
- Double solenoid valve positions can be equipped with any valve or a blanking plate.
- Single solenoid valve positions can only be equipped with single solenoid valves or a blanking plate.
- The electrical connection is established via a 5-pin M12 plug (24 V DC).



	Brief description	→ Page/Internet
1 Cover	For individual connection	96
2 Multi-pin plug connection	Individual connection with M12, 10-way or 6-way (including cover)	96

Peripherals - Electrical components - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Valve terminal with electrical multi-pin plug connection

Order code for VTSA:

- 44E-... for the electrical components
- 44P-... for the pneumatic components

Order code for VTSA-F:

- 45E-... for the electrical components
- 45P-... for the pneumatic components

1

2

Valve terminals VTSA/VTSA-F with multi-pin plug connection can be expanded with up to 32 valves with max. 32 solenoid coils. The manifold sub-bases for valves with a width of 18 or 26 mm are prepared for

- 2 single solenoid valves or

2 double solenoid valves
 and the manifold sub-bases for valves
 with a width of 42 or 52 mm are

- prepared for - 1 single solenoid valve or
- 1 double solenoid valve.

- Double solenoid valve positions can be equipped with any valve or a blanking plate.
- Single solenoid valve positions can only be equipped with single solenoid valves or a blanking plate.
- The following multi-pin plug connections to IP65 are available:
- 37-pin Sub-D connection (24 V DC): the connecting cable can be ordered in lengths of 2.5 m, 5 m and 10 m for max. 8, 22 or 32 solenoid coils respectively.
- Terminal strip (24 V DC or 110 V AC) 19-pin round plug connector (24 V DC).



	Brief description	→ Page/Internet
1 Inscription labels	Large, for multi-pin plug connection	-
2 Multi-pin plug cable	-	97
3 Multi-pin plug connection	Via M23 round plug connection 24 V DC	96
4 Multi-pin plug connection	Via terminal strip (Cage Clamp®) 24 V DC or 110 V AC	96
5 Multi-pin plug connection	Via multi-pin cable 24 V DC	96

Valve terminal with AS-interface connection

2

Order code for VTSA:

- 52E-... for the electrical components
- 44P-... for the pneumatic components
- Order code for VTSA-F:
- 52E-... for the electrical components
- 45P-... for the pneumatic components

Valve terminals VTSA/VTSA-F with AS-interface connection can be expanded with up to 8 valves with max. 8 solenoid coils. The manifold sub-bases for valves with a width of 18 or 26 mm are either prepared for

• 2 single solenoid valves or

P

3

- 2 double solenoid valves

and the manifold sub-bases for valves with a width of 42 or 52 mm are prepared for

- 1 single solenoid valve or
- 1 double solenoid valve.
- Double solenoid valve positions can be equipped with any valve or a blanking plate.
- Single solenoid valve positions can only be equipped with single solenoid valves or a blanking plate.

	Brief description	→ Page/Internet
1 Multi-pin plug connection	Can be ordered together with the AS-interface module as an electrical connection	97
	for AS-interface	
2 Manifold block for AS-interface	-	97
3 AS-interface module	-	97

1



Valve terminal with fieldbus connection, control block (electrical peripherals CPX)

Order code:

- 50E-... for the electrical peripherals
- 51E-... for the electrical peripherals,
- metal manifold module For VTSA: • 44P-... for the pneumatic
- components For VTSA-F:

• 45P-... for the pneumatic components

Valve terminals VTSA/VTSA-F with fieldbus interface can be expanded

with up to 32 valves with max. 32 solenoid coils.

Each valve position can be equipped with any valve or a blanking plate. The rules for CPX apply to the equipment that can be used in combination with the electrical peripherals CPX.

In general:

- Max. 10 electrical modules
- Digital inputs/outputs
- Analogue inputs/outputs
- Parameterisation of inputs and outputs
- Integrated convenient diagnostic system
- Preventive maintenance concepts



	Brief description	→ Page/Internet
1 Inscription labels	Large, for pneumatic interface CPX	-
2 Pneumatic interface	-	96
3 Fieldbus interface	-	срх

FESTO

Valve terminal with fieldbus/multi-pin plug connection and individually electrically actuated valve

In applications with specific emergency stop conditions, it may be necessary to switch one or more valves separately from the valve terminal controller. Standard valves (VSVA) with individual electrical connection (round or square plug) are mounted on the

valve terminal to this end. In order for the protection class IP65 to be achieved, the functionless opening in the sub-base for the electrical connection must be sealed. A sealing cap is available for the 18 mm and 26 mm widths.

With manifold or individual sub-bases, valves with width 42 mm and 52 mm must be used with a seal to comply with the IP protection class (see → page 95). For central control of the valve terminal via a multi-pin plug or

fieldbus connection, the valve position occupied in this way acts like a vacant position, i.e. the assigned address in the fieldbus node or the corresponding connection in the multi-pin plug connection is occupied.



	Brief description	→ Page/Internet
1 Sealing cap	For sealing the electrical connection on the sub-base	95
2 Valve	Width 18 mm or width 26 mm	valves vsva
3 Connecting cable	-	valves vsva
4 Seal	For ensuring the IP protection class (with width 42 mm and 52 mm)	95
5 Valve	Width 42 mm or width 52 mm	valves vsva

Key features - Pneumatic components - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Manifold sub-base



VTSA/VTSA-F is based on a modular system which consists of manifold sub-bases and valves. Manifold sub-bases are available for valve widths 18 mm and 26 mm in a double grid, i.e. two valves per manifold sub-base. For valves with a width of 42 mm or 52 mm, there are manifold sub-bases with one valve per sub-base. The manifold sub-base contains a duct seal and an electrical interlinking module. They can be freely mixed within a valve terminal. The manifold sub-bases are screwed together and thus form the support system for the valves. Inside the manifold sub-bases are the connection ducts for supplying compressed air to and venting from the valves on the terminal as well as the working lines for the pneumatic cylinders for each valve. Each manifold sub-base is connected to the next using four screws. Individual valve terminal sections can be isolated and further manifold sub-bases inserted by loosening these screws. This ensures that the valve terminal can be rapidly and reliably extended.

FESTO



- 📲 - Note

The illustrations shown depict a schematic representation of the pneumatic ISO port patterns.

The port patterns on the valve terminal VTSA-F do not correspond to the ISO standard.

Manifol	d sub-base variants with NPT th	nread, valve terminal VTSA						
Code		Туре	Width				No. of valve positions/	Working lines (2, 4) on the manifold sub-base
			18 mm	26 mm	42 mm	52 mm	solenoid coils	
Manifol	d sub-base for multi-pin plug/fie	eldbus connection for double sol	enoid valv	es				
A AK		VABV-S4-2S-N18-2T2	•	-	-	-	2/4	1⁄8" NPT QS-1⁄8-5⁄16-U, QS-1⁄8-1⁄4-U
B BK		VABV-S4-1S-N14-2T2	_	•	-	_	2/4	1⁄4 " NPT: QS-1⁄4-3⁄8-U, QS-1⁄4-5⁄16-U
C CK		VABV-S2-1S-N38-T2	_	-		_	1/2	3⁄8" NPT QS-3⁄8-3⁄8-U, QS-3⁄8-1⁄2-U
D DK		VABV-S2-2S-N12-T2	-	_	-	•	1/2	1⁄2" NPT QS-1⁄2-1⁄2-U
Manifol	d sub-base for multi-pin plug/fie	eldbus connection for single sole	noid valve	S	1	I	1	
E EK		VABV-S4-2S-N18-2T1	•	-	_	-	2/2	1⁄8" NPT QS-1⁄8-5⁄16-U, QS-1⁄8-1⁄4-U
F FK		VABV-S4-1S-N14-2T1	_	•	_	_	2/2	1/4 " NPT QS-1/4-3/8-U, QS-1/4-5/16-U
G GK		VABV-S2-1S-N38-T1	-	-	•	_	1/1	3⁄8" NPT QS-3⁄8-3⁄8-U, QS-3⁄8-1⁄2-U
H HK		VABV-S2-2S-N12-T1	-	_	_	•	1/1	1⁄2" NPT QS-1⁄2-1⁄2-U



Code		Туре	Width				No. of valve positions/	Working lines (2, 4) on the manifold sub-base
			18 mm	26 mm	42 mm	52 mm	solenoid coils	
Nanifol	d sub-base for multi-pin plug/f	ieldbus connection for double s	solenoid valv	es				
A AK		VABV-S4-2HS-N18-2T2	•	-	-	-	2/4	¹ /8" NPT QS-1/8-5/16-U, QS-1/8-1/4-U
3 3K	000	VABV-S4-1HS-N14-2T2	-	•	_	_	2/4	1/4 " NPT QS-1/4-3/8-U, QS-1/4-5/16-U
CK		VABV-S2-1HS-N38-T2	_	_		_	1/2	³ /8" NPT QS-3/8-3/8-U, QS-3/8-1/2-U
) DK		VABV-S2-2HS-N12-T2	-	_	_	•	1/2	1⁄2" NPT QS-1⁄2-1⁄2-U
Manifol	d sub-base for multi-pin plug/f	ieldbus connection for single so	olenoid valve	S		I		
e EK		VABV-S4-2HS-N18-2T1	-	_	-	_	2/2	¹ /8" NPT QS-1/8-5/16-U, QS-1/8-1/4-U
f FK		VABV-S4-1HS-N14-2T1	-	•	_	_	2/2	1/4" NPT QS-1/4-3/8-U, QS-1/4-5/16-U
G GK		VABV-S2-1HS-N38-T1	-	_	•	_	1/1	3%" NPT QS-3%-3%-U, QS-3%-1/2-U
H HK		VABV-S2-2HS-N12-T1		_	-		1/1	1/2 " NPT QS-1/2-1/2-U

90° conn	90° connection plate for working lines 2 and 4 with NPT thread										
Code		Туре	Width				Ports	Working lines (2, 4) on the 90°			
			18 mm	26 mm	42 mm	52 mm		connection plate			
Р		VABF-S4A2G2-N					2 and 4	1⁄8" NPT			
				•]	1⁄4" NPT			
	Q 0							3⁄8" NPT			
								1⁄2" NPT			

Key features - Pneumatic components - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Sub-base valve



VTSA/VTSA-F offers a comprehensive range of valve functions. All valves are fitted with piston spool and patented sealing system, which ensures efficient sealing, a broad operating pressure range and long service life. Sub-base valves can be quickly replaced since the tubing connections remain on the sub-base. Irrespective of the valve function there are sub-base valves with one solenoid coil (single solenoid) or with two solenoid coils for double solenoid or double valve functions.

Reverse/vacuum operation

Select reverse operation (code Z) if you wish to operate an actuator (cylinder) with different pressures for the forward and return stroke. Please note that the valves must then be operated via a separate pressure zone.

The reversible 3/2-way valves are also suitable for vacuum operation.

Blanking plate



Plate without valve function for reserving valve positions on a valve terminal.

Valves and blanking plates are attached to the manifold sub-base using screws.

Design

Valve replacement

The valves are attached to the metal manifold sub-base using two screws, which means that they can be easily

replaced. The mechanical robustness of the manifold sub-base guarantees efficient long-term sealing.

Expansion

Vacant positions can be fitted with valves at a later date. The dimensions, mounting points and existing pneumatic installations remain unchanged during this process. The order code VSVA-... is located on the front of the valve beneath the manual override.

Valve fu	nctions					
Code	Circuit symbol	Width				Description
		18 mm	26 mm	42 mm	52 mm	
VC	4 2					2x 2/2-way valve, single solenoid
		_	_	_	_	Normally closed
		-	-	-	-	Pneumatic spring return
	12/16 1 (14)					
VV	4 2					2x 2/2-way valve, single solenoid
			_	_		Normally closed
		-	-	-	_	Pneumatic spring return
	112/114 11 1 (14) (5) (3)					• Vacuum operation possible at 3 and 5
Ν	4 2					2x 3/2-way valve, single solenoid
				_	_	Normally open
		-	-	-		Pneumatic spring return
	12/14 1 5 3 (14)					 Operating pressure > 3 bar
К	4 2					2x 3/2-way valve, single solenoid
						Normally closed
			-			Pneumatic spring return
	12/14 1 5 3 (14)					• Operating pressure > 3 bar
Н	4 2					2x 3/2-way valve, single solenoid
						Normal position
		_	_	_	_	– 1x closed
	12/14 1 5 3 (14)	-	-	-	-	 1x open
	(14)					Pneumatic spring return
						• Operating pressure > 3 bar
Р	4 2					2x 3/2-way valve, single solenoid
		_	_	_	_	Reverse operation
		-	-	-		Normally open
	112/114 11 33/55 11 12 (14) (5) (1) (9)					Pneumatic spring return
Q	ái 2i					2x 3/2-way valve, single solenoid
						Reverse operation
				-		Normally closed
	112/114 11 33/55 11 12 (14) (3) (1) (3)					Pneumatic spring return
R						2x 3/2-way valve, single solenoid
ix iii						Reverse operation
						Normal position
	10/114 11 33/55 11 12					- 1x closed
	110/114 11 33/55 11 12 (14) (5) (1) (3)					– 1x open
						Pneumatic spring return
		I	1	1	I	r u

-- Note

A filter must be installed upstream of valves operated in vacuum mode. This prevents any foreign matter in the intake air getting into the valve (e.g. when operating a suction cup).

Valve fu	nction					
Code	Circuit symbol	Width				Description
		18 mm	26 mm	42 mm	52 mm	
M		-	•	•	•	5/2-way valve, single solenoidPneumatic spring return
0		-	•	•	•	5/2-way valve, single solenoidMechanical spring return
J		-	•	•	•	5/2-way valve, double solenoid
D		•	•	•	•	5/2-way valve, double solenoidDominant signal at port 14 on the control side
SO SQ		-	•	-	-	5/2-way valve2), single solenoid, in plug-in or via pilot valve with pneumatic interface to ISO 15218 See also special valve function in the section "Control block with safety function" → page 105
В		•	•	•	•	 5/3-way valve Mid-position pressurised¹⁾ Mechanical spring return
G		•	•	•	•	 5/3-way valve Mid-position closed¹⁾ Mechanical spring return
E		-	•	•	-	 5/3-way valve Mid-position exhausted¹⁾ Mechanical spring return
SA		_	•	-	-	 5/3-way valve, with enhanced function through signal storage in switching position 14 Pressureless switching, self-holding, pneumatic operation Mid-position exhausted, switching position 14 with memory function Mechanical spring return
SB		-	•	-	-	 5/3-way valve, with enhanced function through signal storage in switching position 14 Holding, blocking a movement (mechanically) Mid-position: port 2 pressurised, port 4 exhausted, switching position 14 with memory function Mechanical spring return
L		•	•	•	•	For valve terminal only: Blanking plate for vacant valve position

1) If neither solenoid coil is energised, the valve moves to its mid-position by means of a mechanical spring. If the two coils are permanently energised one after the other, the valve remains in the switching position of

the coil that was activated first.
The symbol represents a valve with a proximity sensor with a switching output signal, in the illustration an N/O contact. In accordance with ISO 1219-1, this symbol applies to both N/O contacts as well as N/C contacts. The switching element function of all sensors used here is an N/C contact.

Vertical stacking



Additional functions can be added to each valve position between the sub-base and the valve. These functions are known as vertical stacking modules and enable special

functioning or control of an individual valve position. Combinations of several valve sizes on one valve terminal are possible.

-Note

Certain combinations are not recommended due to the design of the individual vertical stacking components.

FESTO

Vertical stacking components



The following component sequence is recommended for valve positions with vertical stacking: 1 ISO valve

2 Pressure regulator plate

3 Flow control plate

- 4 Vertical pressure shut-off plate
- 5 Vertical supply plate
- 6 Manifold sub-base

Key features - Pneumatic components - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Vertical stacking



An adjustable pressure regulator can be installed between the sub-base and the valve in order to control the force of the triggered actuator. This pressure regulator maintains an essentially constant output pressure (secondary side) independent of pressure fluctuations (primary side) and air consumption. Also suitable for symmetrical valves.

Standard version:

- Standard port pattern to ISO 15407-2 or ISO 5599-2
- For supply pressure up to 6 bar or up to 10 bar

FESTO

- Without pressure gauge (optional)
- Regulator knob with 3 positions (locked, reference position, free running)

- 📲 - Note

With the A, B and AB pressure regulators VABF-S-1..., the control pressure should not be under 2 bar. Use the reversible A, B or AB pressure regulators for control pressures under 2 bar.

- Note

Please note for repeat orders:

Certain equipment versions of pressure regulator plates can only be ordered via type codes. The part number imprinted on the regulator plate installed on the VTSA/VTSA-F valve terminal will not match the equipment version in these cases. For that reason, always use the VABF configurator for repeat orders.

Mode of operation of the pressure regulator plate (P regulator) for port 1; code: ZA, ZAY, ZF, ZFY



Advantages

- The pressure regulator is not affected by venting, since the pressure is regulated upstream of the valve.
- The pressure regulator can always be adjusted, since the pressure from the valve terminal is always present.

This pressure regulator regulates the pressure upstream of the valve in duct 1. Ducts 2 and 4 thus have the same regulated pressure.

During venting, the exhaust flow in the valve is from duct 2 to duct 3 and from duct 4 to duct 5.

Application examples

- An equal working pressure is required at working lines 2 and 4.
- A lower working pressure

 (e.g. 3 bar) than the operating
 pressure present on the valve
 terminal (e.g. 8 bar) is required.

Key features - Pneumatic components - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Vertical stacking

Mode of operation of the pressure regulator plate (AB regulator) for ports 2 and 4; code: ZD, ZDY, ZI, ZIY



Restrictions

 The pressure regulator cannot be adjusted in the exhaust position.
 For example, the pressure regulator for duct 4 cannot be adjusted when the valve is pressurised in the switching position from duct 1 to duct 2 and exhausted from duct 4 to duct 5.

This pressure regulator regulates the pressure in ducts 2 and 4 after the pressure medium flows through the valve. During venting, the exhaust flow in the valve is from duct 2 to duct 3 and from duct 4 to duct 5 via the pressure regulator.

Example with the following switching position:

The supply air flows from duct 1 of the manifold sub-base via the valve to duct 2, it is then regulated and made available at port 2 of the manifold sub-base. At the same time, venting takes place via duct 4 of the manifold sub-base, via the regulator and via the valve into duct 5 of the manifold sub-base.

Application examples

 When two different working pressures are required at ports 2 and 4 instead of the valve terminal operating pressure.

Key features - Pneumatic components - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

FESTO

Vertical stacking



Application examples

- When two different pressures are required in ducts 2 and 4 instead of the operating pressure.
- When fast venting is required.
- When the pressure regulator must
 - always be adjustable.

With this pressure regulator, the supply air (duct 1) is split and routed directly to both pressure regulators. In each case the regulated supply air is present in ducts 3 and 5 on the valve. The valve is thus operated in reversible mode. This means:

- Duct 3 routes the working pressure to port 2
- Duct 5 routes the working pressure to port 4

Example with the following switching position:

The supply air in duct 1 is split between ducts 3 and 5 in the regulator and flows from here to the valve. In the valve, the supply air is routed to port 2 of the manifold sub-base. The exhaust air is simultaneously routed via duct 4 of the manifold sub-base and via the valve to regulator duct 1, where it is split between ducts 3 and 5 and then expelled via the manifold sub-base.

Note

- Reversible pressure regulator plates may only be combined with valves that can be operated in reversible mode.
- Valves in valve positions with vertical pressure shut-off plates are operated with internal pilot air supply, even when the valve terminal is operated with external pilot air supply.
- The following combination of reversible valve terminals with vertical stacking components is not permitted:
 - Reversible pressure regulator plates
 - Flow control plates
 - Vertical pressure shut-off plates
 - Vertical supply plates

Advantages

- Fast cycle times.
- 50% higher exhaust flow rate, as air is not vented via the pressure regulator. The load on the pressure regulator is also reduced.
- No quick exhaust valves are required.
- Operating pressure is always present at the pressure regulator, as the pressure is regulated upstream of the valve, i.e. the regulator can always be adjusted.

Disadvantages

- 2x 3/2-way valves (code N, K, H) cannot be used, as pressure is present at ports 3 and 5.
- No practical combination with a flow control plate possible.

FESTO

	stacking – Pressure regulator plat	- 1	Width				Supply p		Description
Code		Туре				1			Description
			18 mm	26 mm	42 mm	52 mm	6 bar	10 bar	
	e regulator plate for port 1 (P regula								
ZA		VABF-SR1C2-C-10	-	•			-		Regulates the operating pressure
ZAY ²⁾		VABF-SR1C2-C-10-E	-	•	•	•	-	•	in duct 1 upstrea
ZF		VABF-SR1C2-C-6	-	-	-	•	•	-	of the directional control valve
ZFY ²⁾		VABF-SR1C2-C-6-E						-	control valve
Droccur	e regulator plate for port 2 (B regula	ator)							
<u>ZC</u>		VABF-SR2C2-C-10							Regulates the
							-		operating pressur
ZCY ²⁾		VABF-SR2C2-C-10-E	-	-			-	•	in duct 2 down-
ZH		VABF-SR2C2-C-6	-	-	•			-	stream of the directional contro
ZHY ²⁾		VABF-SR2C2-C-6-E	•	•		•		-	valve
		•	•	•	•	•		•	
Pressur	e regulator plate for port 4 (A regula	ator)							
2B ²⁾		VABF-SR3C2-C-10	•	•	•	•	-	•	Regulates the operating pressur in duct 4 down-
(G ²⁾		VABF-SR3C2-C-6	•	•	•	•	•	-	stream of the directional contro valve
		•		•	•	•			
ressur	e regulator plate for ports 2 and 4 (AB regulator)							
ZD		VABF-SR4C2-C-10	•	•	•	•	-	-	 Regulates the working pressure in ducts 2 and 4
ZDY ²⁾		VABF-SR4C2-C-10-E	•	•	•	•	-	-	downstream of th directional contro valve
1	14 5 1 9 12	VABF-SR4C2-C-6							- 着 - Note
			•	-	-	•	•	-	₹ These pressure regu
<u>ηγ2)</u>	4	VABF-SR4C2-C-6-E							lator plates cannot
.11-/		VADI-3N4U2-U-0-E			_				be combined with
			-					-	reversible 2x 3/2-wa valves (code P, Q, R)

1) These functions are also available via the pressure regulator configurator VABF-S2 for width 42 mm and 52 mm (ISO 5599-2, ISO 1 and ISO 2) 2) Also suitable for symmetrical valves

Vertical	stacking – Pressure regulator plate	– Variants ¹⁾							
Code		Туре	Width				Supply p	ressure	Description
			18 mm	26 mm	42 mm	52 mm	6 bar	10 bar	
Pressure	e regulator plate for port 2, reversible	(B regulator)	<u>.</u>	<u>.</u>	<u>.</u>	<u>.</u>	<u>.</u>	<u>.</u>	
ZL		VABF-SR6C2-C-10					-		Reversible
ZLY ²⁾		VABF-SR6C2-C-10-E					_		pressure regulator
ZN		VABF-SR6C2-C-6						-	for port 2
ZNY ²⁾		VABF-SR6C2-C-6-E				-	•	-	-
	34 9 3 5 122			1				1	
	e regulator plate for port 4, reversible	e (A regulator)							
ZK ²⁾		VABF-SR7C2-C-10	•	•	•	•	-	-	Reversible pressure regulator for port 4
ZM ²⁾		VABF-SR7C2-C-6	•					-	
Proceure	e regulator plate for ports 2 and 4, re	versible (AB regulator)							
ZE	Pregulator plate for ports 2 and 4, re	VABF-SR5C2-C-10	•	-	•	-	-		 Reversible pressure regulator for ports 2 and 4 Pressure regula- tion upstream of the directional control valve
ZEY ²⁾		VABF-SR5C2-C-10-E	•	•	•	-	_	•	 Routes the operating pressure from duct 1 to ducts 3 and 5 Routes the exhaust air from duct 1 to ducts 3 and 5
ZJ		VABF-SR5C2-C-6		•	•	•	•	-	- Difference of the second sec
ZJY ²⁾		VABF-SR5C2-C-6-E	•	•	•	•	•	-	(code N, K, H). Reversible 2x 3/2-way valves (code P, Q, R) must not be operated in a separate pressure zone in combination with these pressure regulators.

1) These functions are also available via the pressure regulator configurator VABF-S2 for width 42 mm and 52 mm (ISO 5599-2, ISO 1 and ISO 2) 2) Also suitable for symmetrical valves



Vertical stacking – Pressure regulator plate – Type codes

		VABF	- S2	-	1	R1	C2	- L	С	- L	6	-	L1	- L	E
Valve s	arias														
VABF	Regulator plate														
Allocat	ion														
S2	ISO 5599-2 ¹⁾														
S4	ISO 15407-2														
L		I													
Valve s	ize														
1	26 mm (ISO 15407-2, ISO 01)					-									
2	18 mm (ISO 15407-2, ISO 02)														
1	42 mm (ISO 5599-2, ISO 1)														
2	52 mm (ISO 5599-2, ISO 2)														
Functio	on plate														
	•														
R1	Pressure regulator, port 1														
R2 R3	Pressure regulator, port 2														
R4	Pressure regulator, port 4 Pressure regulator, ports 2 and 4														
R5	Pressure regulator, ports 2 and 4,														
N J	reversible														
R6	Pressure regulator, port 2, reversible	<u> </u>													
R7	Pressure regulator, port 4, reversible														
κ7		c													
Pressu	re display														
C2	Sealed							J							
С3	Pressure gauge [bar] ¹⁾														
C4	Pressure gauge [MPa] ¹⁾														
C6	Pressure gauge [psi] ¹⁾														
	atic connection														
С	Sealed														
Process	re range														
6	6 bar														
10	10 bar														
Contro	l element ²⁾														
-	Short (standard button)														
L1	Long														
L2	Long, lockable														
К2	Short, lockable														
K3	With integrated lock														
Option	al														
E	Extended design ¹⁾														
L															

1) These functions are available via the pressure regulator configurator VABF-S2. for width 42 mm and 52 mm (ISO 5599-2, ISO 1 and ISO 2) only. Alternatively they can be selected for all four sizes in the valve terminal configurator or via their own order numbers in the chapter Accessories on page 91.

2) All variants are only possible for VABF-S2.

Key features - Pneumatic components - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

FESTO

Vertical stacking



The flow control plate is equipped with two flow control valves on which the exhaust air flow rate at exhaust ports 3 or 5 can be adjusted. This enables the movement of the drive to be initiated and the desired speed to be set on the valve terminal using the manual override. Ducts 3 and 5 can be adjusted independently of each other.

- Note

On reversible valve terminals, supply air flow control takes place in ducts 3 and 5 upstream of the valve.

Code	Туре	Width			Description		
		18 mm	26 mm	42 mm	52 mm		
Х	VABF-S4F1B1-C	•	•	•		 Restricts the exhaust air down- stream of the valve in ducts 3 and 5 	

Vertical pressure shut-off plate



The vertical pressure shut-off plate is equipped with a switch via which the compressed air supply can be shut off. This enables a directional control valve or subsequent vertical stacking plate to be replaced without switching off the overall air supply. If the control chain has a redundant connection, the cycle can continue in the case of a cyclical control system. Following activation of the shut-off, the exhaust air/return air from the cylinder is expelled via the M5 threaded connection.

- Note

It must be ensured that the operating pressure of the valve terminal lies within the range of the required pilot pressure (i.e. min. 3 bar). When using an end plate with pilot air selector, only end plates with the code W and U can be used.

Code		Туре	Width				Description	
			18 mm	26 mm	42 mm	52 mm		
ZT	4 2 +	VABF-S4L1D1-C	•	•	•	•	 3/2-way valve for shutting off the operating pressure at the valve position Blocks ducts 1 and 14 for the valve position Supplies the valve position with internal pilot air 	

Vertical supply plate



This plate enables a valve to be supplied with individual operating pressure independently of the operating pressure of the valve terminal.

As additional pressure supply for a valve. To supply an additional pressure zone.

Code		Туре	Width				Description
			26 mm	18 mm	42 mm	52 mm	
ZU	4 2 11 14 5 1 3 12	VABF-S4P1A3	-	•	•	•	 Plate with port 11 for supplying individual operating pressure to a valve position
Key features - Pneumatic components - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Compressed air supply and venting

Right-hand end plate

- Code V
- Internal pilot air supply



Right-hand end plate

- Code V1
- Internal pilot air supply



Port configuration for supply plates Exhaust port 3/5 separated

• Code K



Pilot air supply

The port for the pneumatic supply is located on the supply plates or the right-hand end plate.

Internal pilot air supply

Internal pilot air supply can be selected if the working pressure is between 3 and 10 bar.

Right-hand end plate Code X

• External pilot air supply







- Code X1External pilot air supply

Port configuration for supply plates Exhaust port 3/5 common • Code L



The ports differ for the following types of pilot air supply:

- Internal
- External

The pilot air supply is then branched from the compressed air supply 1 using an internal connection. Port 14 on the right-hand end plate is sealed with a blanking plug.

- Note

If a gradual pressure build-up is required in the system by means of a soft-start valve, then external pilot air should be selected whereby the pilot pressure is already applied at the point of switch-on.

External pilot air supply

End plate with pilot air selector

• Code Z, Y, W, U

If the supply pressure is less than 3 bar, you must operate your valve terminal VTSA/VTSA-F using external pilot air supply. The pilot air supply is then supplied via port 14 on the right-hand end plate. This is the case even if the valve terminal is operated with different pressure zones.

supplied with compressed air at one or more points. This is a reliable way of ensuring that all functional components will always offer good performance, even with large-scale extensions. The valve terminal is supplied via supply plates (max. 16 per valve terminal) or via an end

plate.

The valve terminal VTSA/VTSA-F can be

Venting is via silencers or ports for ducted exhaust air on the supply plates and/or on the right-hand end plate. There are two types of supply plates:

- Exhaust port 3/5 common
- Exhaust port 3/5 separated

Key features - Pneumatic components - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Additional compressed air supply/duct separation

Additional supply plates can be used for larger valve terminals or to create additional pressure zones. These can be selected at any point upstream or downstream of the manifold sub-bases.

Supply plates contain the ports:

- Compressed air supply (1)
- Exhaust port (3/5) common or separated

Depending on your order, the exhaust air ducts are either ducted or vented via silencers.

VTSA/VTSA-F with ducted exhaust air:

With ducted exhaust air, venting can be via a supply plate or a right-hand end plate (code V or X).

If duct separation is required, there are three different options:

- Duct separation 1, 3, 5: code S
- Duct separation 1: code T
- Duct separation 3, 5: code R

If a combination of duct separation (S, T or R) and one or two supply plates is required, the following variants can be selected:

- Supply plate with duct separation on the left-hand side: code SU, TU, RU
- Supply plate with duct separation on the right-hand side: code US, UT, UR
- 2 supply plates with intermediate duct separation: code USU, UTU, URU

Supply	plates						
Code		Туре	Width				Description
			18 mm	26 mm	42 mm	52 mm	
U		 Exhaust port 3/5 common VABF-S6-10-P1A7-G12 Exhaust port 3/5 separated VABF-S6-10-P1A6-G12 	•	•	•	•	Supply plate without duct separation (no R, S or T selected)
SU TU RU			•	•			Supply plate with duct separation on left, if R, S or T selected
US UT UR			•	•	•	•	Supply plate with duct separation on right, if R, S or T selected
USU UTU URU			•	•	•	•	2 supply plates with duct separation in centre, if R, S or T selected

Key features - Pneumatic components - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Right-hand end plate

Different right-hand end plates are available.

With the following two end plates, the outgoing direction of the ports is aligned with the horizontal stacking direction.

Right-hand end plates with pilot air supply/pilot exhaust air

- Internal pilot air supply: code V, V1 and V2
- External pilot air supply: code X, X1 and X2

For end plates with pilot air selector, the outgoing direction of the ports is to the front of the valve terminal. This means that all the ports on the valve terminal can be combined in one outgoing direction.

The special feature of the end plates with pilot air selector is the selector switch itself, which has four settings for different pilot air supply/pilot exhaust air. End plates with pilot air selector switch set at the factory for:

- External pilot air supply: code Z
- Internal pilot air supply: code YExternal pilot air supply,
- ducted pilot exhaust air: code WInternal pilot air supply,
- ducted pilot exhaust air: code U

≜ - Note

The end plate with pilot air selector must be used in combination with a supply plate. The reversible 3/2-way valves (code P, Q, R) must only be operated in selector position 1 or 2. Ducted pilot exhaust air via port 12 is only possible with turned seals on the valve.

Right-hand end plate					
Code	Pilot supply air	Seal turned, pilot exhaust air	Connecting thread		
		ducted at port 12	1, 3, 5	12,14	
V, V1, V2	Internal		1⁄2" NPT	1⁄4 " NPT	
X, X1, X2	External		1⁄2 " NPT	1⁄4 " NPT	

Right-hand end plate with pilot air selector									
Code	Pilot supply air	Selector position	Seal turned, pilot exhaust air ducted at port 12	Connecting thread 12, 14					
Z	External	1		1⁄4 " NPT					
Y	Internal	2		1⁄4 " NPT					
W	External	3		1⁄4 " NPT					
U	Internal	4		1⁄4 " NPT					



2011/02 - Subject to change

Right-h	and end plate							
Code	Type of compressed air supply and	l pilot air supply	Width				Description	
			18 mm	26 mm	42 mm	52 mm		
	Right-hand end plate							
V V1 V2	000		•	•	-	•	 Internal pilot air supply Pilot air supply is branched internally from port 1 Port 14 is sealed with a blanking plug Exhaust air via ports 3 and 5 For operating pressure in the range 3 10 bar Pilot exhaust air via port 12¹⁾ 	
X X1 X2	0000		•	•	•	•	 External pilot air supply Pilot air supply between 2 and 10 bar is connected at port 14 Exhaust air via ports 3 and 5 For operating pressure in the range 0.9 10 bar (suitable for vacuum) Pilot exhaust air via port 12¹) 	
XP1			•	•	•	•	External pilot air supply, pressure supply via soft-start valve ²⁾ • Port 1 is sealed with a blanking plug • Exhaust air via ports 3 and 5 • Pilot exhaust air via port 12 ¹⁾	
XP2			•	•	•	•	 External pilot air supply, pressure supply via soft-start valve²⁾ Internal pilot air supply 14 via soft-start valve Ports 1 and 14 are sealed with a blanking plug Exhaust air via ports 3 and 5 Pilot exhaust air via port 12¹⁾ 	
XP3			•	•	•	•	 External pilot air supply, pressure supply via soft-start valve²⁾ Internal pilot air supply 14 via soft-start valve Ports 1, 3, 5 and 14 are sealed with a blanking plug Pilot exhaust air via port 12¹⁾ 	

Ducted pilot exhaust air is only possible with turned seals on the valve
 Application with XP1, XP2, XP3 and soft-start valve in combination with valves of width 52 mm: please note the maximum flow rate of the soft-start valve in this pressure zone

Right-ha	and end plate						
Code	Type of compressed air supply and	l pilot air supply	Width				Description
			18 mm	26 mm	42 mm	52 mm	
Code ²⁾	End plate with pilot air selector ³⁾			-			
Z (1)			•	•	•	•	 External pilot air supply Pilot air supply is connected at port 14 Port 12 is sealed with a blanking plug Ports 12 and 14 are internally connected Pilot exhaust air unducted via valve housing
Y (2)			•	•	•	•	 Internal pilot air supply Pilot air supply is branched internally from port 1 Ports 1, 12 and 14 are internally connected Ports 12 and 14 are sealed with blanking plugs Pilot exhaust air unducted via valve housing
W (3)			•				External pilot air supply, ducted pilot exhaust air • Pilot air supply is connected at port 14 • Pilot exhaust air via port 12 ¹⁾
U (4)			•	•	•	•	 Internal pilot air supply, ducted pilot exhaust air Pilot air supply is branched internally from port 1 Ports 1 and 14 are internally connected Port 14 is sealed with a blanking plug Pilot exhaust air via port 12¹⁾

Ducted pilot exhaust air is only possible with turned seals on the valve
 Selector setting in brackets
 Ducted pilot exhaust air is only possible in pilot air selector position 3 or 4



FESTO

Code	ration of all pneumatic connections		Port	Designation	Code M Push-in connector, large	Code N Push-in connector small
	Right-hand end plate		-	- I	1	1
V		3	1	Push-in fitting	QS-1/2-5/8-U	QS-1/2-1/2-U
		5	3 and 5	Silencer or push-in fitting	U-1/2-B-NPT	U-1/2-B-NPT
		12			or	or
	6000				QS-1/2-5/8-U	QS-1/2-1/2-U
			12	Silencer or push-in fitting	U-1⁄4-B-NPT	U-1⁄4-B-NPT
					or	or
		Ļ			QS-1/4-3/8-U	QS-1/4-5/16-U
		5	14	Blanking plug	B-1/4-NPT	B-1/4-NPT
		3	1	Push-in fitting	QS-1/2-5/8-U	QS-1/2-1/2-U
		5	3 and 5	Silencer or push-in fitting	U-1/2-B-NPT	U-1/2-B-NPT
		12			or	or
	6000	14			QS-1/2-5/8-U	QS-1/2-1/2-U
			12	Silencer or push-in fitting	U-1/4-B-NPT	U-1/4-B-NPT
					or	or
					QS-1/4-3/8-U	QS-1/4-5/16-U
	*		14	Push-in fitting	QS-1/4-3/8-U	QS-1/4-5/16-U
/1		3	1	Female hose connector	N-3/4-P-19-NPT ¹⁾	-
		5	3 and 5	Silencer or female hose	U-3/4-B-NPT ¹⁾	-
				connector	or	
			1.0		N-3/4-P-19-NPT ¹⁾	
			12	Silencer or push-in fitting	U-1⁄4-B-NPT	U-1/4-B-NPT
					or	or
		L A	4.4	Diaultina ulua	QS-1/4-1/2-U	QS-1/4-3/8-U
1		<u> </u>	14	Blanking plug Female hose connector	B-1/4-NPT N-3/4-P-19-NPT ¹⁾	B-1/4-NPT
.1		3	1 3 and 5	Silencer or female hose	U-3/4-P-19-NPT	_
			5 anu 5	connector	Or Or	_
					N-3/4-P-19-NPT ¹⁾	
			12	Silencer or push-in fitting	U-1/4-B-NPT	U-1/4-B-NPT
			12		or	or
					QS-1/4-1/2-U	QS-1/4-3/8-U
			14	Push-in fitting	QS-1/4-1/2-U	QS-1/4-3/8-U

1) For tubing with I.D. 19 mm. Use tubing clips to DIN 3017

FESTO

Code		Port	Designation	Code M Push-in connector,	Code N Push-in connector,
				large	small
Code ¹⁾	End plate with pilot air selector		·		
Z (1)		12	Blanking plug	B-1/4-NPT	B-1⁄4-NPT
		14	Push-in fitting	QS-1/4-3/8-U	QS-1/4-5/16-U
Y (2)		12	Blanking plug	B-1/4-NPT	B-1/4-NPT
		14	Blanking plug	B-1/4-NPT	B-1/4-NPT
W (3)		12	Silencer or push-in fitting	U-1/4-B-NPT or QS-1/4-3/8-U	U-1⁄4-B-NPT or QS-1⁄4-5⁄16-U
		14	Push-in fitting	QS-1/4-3/8-U	QS-1/4-5/16-U
U (4)		12	Silencer or push-in fitting	U-1/4-B-NPT or QS-1/4-3/8-U	U-1⁄4-B-NPT or QS-1⁄4-5⁄16-U
	OF LOO	14	Blanking plug	B-1/4-NPT	B-1/4-NPT

1) Selector setting in brackets

Key features - Pneumatic components - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Creating pressure zones and separating exhaust air

The valve terminal VTSA/VTSA-F offers a number of options for creating pressure zones if different working pressures are required. Pressure zones are created by isolating the internal supply ducts between the manifold sub-bases by means of appropriate duct separation. Compressed air is supplied and vented via a supply plate. The position of the supply plates and duct separations can be freely selected for VTSA/VTSA-F. Duct separations are integrated ex-works as per your order. Duct separations can be distinguished by their coding, even when the valve terminal is assembled.



Creating	Creating pressure zones									
Code	Separating seal		Width				Description			
	Pictorial examples	Coding	18 mm	26 mm	42 mm 52 mm					
Т			•	•	•	•	Duct 1 separated			
S			•	•	•	•	Ducts 1, 3 and 5 separated			
R				•	•	•	Ducts 3 and 5 separated			

Examples: Compressed air supply and pilot air supply, right-hand end plate Internal pilot air supply, silencer/ducted exhaust air

Pight hand and plate: code V and V1

Right-hand end plate: code V and V1 The diagram opposite shows an example of the configuration and connection of the compressed air supply with internal pilot air supply. Port 14 on the right-hand end plate is tightly sealed. At exhaust port 3/5 the air is expelled via the silencer. Duct separations can optionally be used to create pressure zones.





Key features - Pneumatic components - Compressed air supply and pressure zones, examples - ISO 15407-2, width 18 / 26 mm; ISO 5599-2, width 42 / 52 mm

Examples: Compressed air supply and pilot air supply, right-hand end plate

External pilot air supply, silencer/ducted exhaust air

Right-hand end plate: code X and X1 The diagram opposite shows an example of the configuration and connection of the compressed air supply with external pilot air supply. Port 14 on the right-hand end plate is equipped with a fitting for this. At exhaust port 3/5 the air is expelled via the silencer.

Duct separations can optionally be used to create pressure zones.



Examples: Compressed air supply and pilot air supply via end plate with pilot air selector Internal pilot air supply, ducted exhaust air/silencer

Right-hand end plate: code U The diagram opposite shows an example of the configuration and connection of the compressed air supply with internal pilot air supply. Port 14 on the right-hand end plate is tightly sealed. At exhaust port 3/5 the air is ducted or expelled via the silencer.

The selector switch in the pilot air selector is in position 4. Duct separations can optionally be used to create pressure zones.



FESTO

Key features - Pneumatic components - Compressed air supply and pressure zones, examples - ISO 15407-2, width 18 / 26 mm; ISO 5599-2, width 42 / 52 mm

Examples: Compressed air supply and pilot air supply via end plate with pilot air selector

External pilot air supply, ducted exhaust air/silencer Right-hand end plate: code Z The diagram opposite shows an example of the configuration and connection of the compressed air supply with external pilot air supply. Port 14 on the right-hand end plate is equipped with a fitting for this. Port 12 is sealed with a blanking plug since it is internally connected with port 14. At exhaust port 3/5 the air is ducted or expelled via the silencer. The selector switch on the pilot air selector is in position 1.

Duct separations can optionally be used to create pressure zones.



Examples: Creating pressure zones

VTSA/VTSA-F with CPX terminal connection

VTSA/VTSA-F facilitates the creation of up to 16 pressure zones (up to 32 pressure zones if only size 1, ISO 5599-2, is fitted). The diagram shows an example of the configuration and connection of three pressure zones using duct separations – with internal pilot air supply.



Key features - Mounting - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Valve terminal mounting

Sturdy valve terminal mounting thanks to:

Four through-holes for wall
 Additional mounting brackets
mounting

Wall mounting





• H-rail mounting

The valve terminal VTSA/VTSA-F is screwed onto the mounting surface using M6 screws. The mounting holes are located at the following points:

- Multi-pin plug (4 pieces):
 2 each on the multi-pin connection block and the right-hand end plate
- Fieldbus, CPX (4 pieces):
 2 each on the left-hand (CPX) and right-hand (VTSA/VTSA-F) end plate.
 The pneumatic interface additionally provides further mounting holes as well as optional mounting brackets.

1 Hole for M6 screw

- 2 Hole for M5 screw
- 3 Hole for H-rail mounting



When wall mounting valve terminals with more than five manifold sub-bases, use additional mounting brackets of the type VAME-S...-10-W to prevent damage to the valve terminal. The mounting brackets are mounted on the pneumatic supply plates.

H-rail mounting



The valve terminal VTSA/VTSA-F is hooked onto the H-rail (see arrow A). It is then swivelled onto the H-rail and secured in place with the clamping component (see arrow B). For H-rail mounting of the valve terminal you will need the following VTSA/VTSA-F mounting kit:

• CPX-CPA-BG-NRH This permits mounting of the valve terminal on an H-rail to EN 60715.

Individual valve mounting 1 Vertical mounting holes The individual sub-base for wall Ï mounting is designed for integration into a system or machine. It is mounted vertically. 1

Key features - Display and operation - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Display and operation

Each solenoid coil is allocated an LED which indicates its switching status.

- Indicator 12 shows the switching status of the pilot control for output 2
- Indicator 14 shows the switching status of the pilot control for output 4

Pneumatic connection and control elements

Manual override

The manual override enables the valve to be switched when not electrically actuated or energised. The valve is switched by pushing the manual override. The set switching

status can also be locked by turning

Alternatives:

the manual override.

- A cover cap (accessory code N) can be fitted over the manual override to prevent it from being turned. The valve can then only be actuated by pressing it.
- A cover (code V) can be fitted over the manual override to prevent it from being accidentally actuated.

Electrical connection and display components



- 1 Pressure gauge (optional)
- 2 Adjusting knob of optional pressure regulator plate
- Manual override (for each pilot solenoid coil, non-detenting or non-detenting/detenting)
- Optional cover cap for manual override (prevents usage of manual override)
- 5 Optional cover cap for manual override with non-detenting function
- 6 Inscription label holder for valve
- 7 Adjusting screw of optional flow control plate
- 8 Exhaust ports "valves" (3/5)

- 9 Pilot ports 12 and 14 for supplying the external pilot air
- 10 Inscription label holder for sub-base
- 11 Supply port 1 "operating pressure"
- 12 Working lines 2 and 4, for each valve position

- Note

A manually actuated valve (manual override) cannot be reset electrically. Conversely, an electrically actuated valve cannot be reset using the mechanical manual override.

- 1 Inscription area and cover for H-rail mounting
- 2 Yellow LEDs: signal status display for pilot solenoid coils
- 3 Power supply connection
- 4 Earth terminal
- 5 Fieldbus connection
- (bus-specific)
- 6 Service interface for handheld unit, etc.
- Red LED: common error display for valves

Key features - Display and operation - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

FESTO

Manual override (MO) MO with automatic return (non-detenting) MO set via turning (covered) 1 Press in the stem of the manual 1 Press in the stem of the manual 2 1 2 1 override using a pointed object override using a pointed object or screwdriver. or screwdriver until the valve Valve is then switched switches and then turn the stem 2 Remove the pointed object or clockwise by 90° until the stop is screwdriver. reached. Spring force pushes the stem of Valve remains switched the manual override back. 2 Turn the stem anti-clockwise by Valve returns to initial position 90° until the stop is reached and (not with double solenoid valve then remove the pointed object code J). or screwdriver. Spring force pushes the stem of the manual override back. Valve returns to initial position (not with double solenoid valve code J and D).

Identification system



ASCF-M-S2-2

Inscription label holders can be applied to the valves and manifold sub-bases to identify them. These inscription label holders can be ordered by entering the code B or T in the order code for accessories. Scope of delivery: inscription label holder including inscription label. The following inscription labels can be used as spares:

- Inscription label holder for valve type ASCF-T-S6: Part-No. 540888
- Inscription label holder for manifold sub-base type ASCF-M-S6: Part No. 540889
- Inscription label holder for manifold sub-base (for valve width 52 mm) type ASCF-M-S2-2: Part No. 562577

Large inscription labels can be attached to the pneumatic interface as an alternative or in addition to the smaller labels.

Protective circuit

- Each VSVA solenoid coil is protected with a spark arresting protective circuit as well as against polarity reversal.
- The 24 V DC version of width 52 mm additionally features integrated holding current reduction.

24 V DC version (width 18 to 42 mm)



110 V AC version (width 18 to 52 mm)



24 V DC version (width 52 mm)



Individual valve

Valves can also be used on individual sub-bases for actuators further away from the valve terminal.

- Electrical connection M12, 4 pin 24 V DC
- 4-pin clamped terminal connection for configuration by the user 24 V DC or 110 V AC
- Cable (open end) for configuration by the user 24 V DC or 110 V AC

Individual electrical connection

A maximum of 20 solenoid coils can be actuated. 2 solenoid coils per valve can be addressed.

- Individual electrical connection:
- M12
- 6-way or 10-way
- 5-pin • 24 V DC

Key features - Electrical components - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Electrical multi-pin plug connection

The following multi-pin plug connection variants are offered for the valve terminal VTSA/VTSA-F:

- Sub-D multi-pin plug connection (37-pin for 24 V DC): this valve terminal is available with 1 ... 16 valve positions equipped with double solenoid valves and 1 ... 32 valve positions equipped with single solenoid valves. A maximum of 32 solenoid coils can be actuated.
- Terminal box (terminal strip for 24 V DC or 110 V AC): this valve terminal is available with
- 1 ... 16 valve positions equipped

AS-interface connection

Valve terminals VTSA/VTSA-F with AS-interface connection can be expanded with up to 8 valves with max. 8 solenoid coils. The valve terminal with AS-interface connection is based on the same electrical manifold module as the

with double solenoid valves and 1 ... 32 valve positions equipped with single solenoid valves. A maximum of 32 solenoid coils can be actuated.

• Multi-pin node (round plug connector): electrical multi-pin plug connection with round plug connector, 19-pin to CNOMO E03.62.530.N, connecting thread M23 for 24 V DC. The valve terminal can be equipped with max. 16 solenoid coils.

The valves are switched by means of positive or negative logic

(PNP or NPN). Mixed operation is not permitted.

Each pin on the Sub-D multi-pin plug or terminal box (terminal strip) can actuate exactly one solenoid coil. If the maximum configurable number of valve positions is 32, this means that 32 valves, each with a single solenoid coil, can be addressed. With 16 or fewer valve positions, 2 solenoid coils per valve can be addressed.

Note

Use the following 37-pin connecting cables from Festo to connect the valve terminal VTSA/VTSA-F with Sub-D multi-pin plug connection:

- NEBV-S1W37-...-LE10 for max. 8 solenoid coils
- NEBV-S1W37-...-LE26
- for max. 22 solenoid coils NEBV-S1W37-...-LE37
- for max. 32 solenoid coils NECV-S1W37 pre-assembled plug
- connector

valve terminal with multi-pin plug connection.

This means it is possible to convert a valve terminal with multi-pin plug connection using an AS-interface module.

• The technical specifications of the AS-interface system must be observed in this case.

Note

AS-i module VAEM-S6-S-FAS-4-4E. Always operate solenoid valves with additional power supply if 4 solenoid coils (width 52 mm) are supplied with current simultaneously. More information can be found at: ➔ Internet: as-interface

Fieldbus connection/control block

All functions and features of the electrical peripherals CPX are permitted in connection with the CPX interface. This means:

- The valves and electrical outputs are supplied via the operating voltage connection CPX
- The valves are supplied and switched off independently via a separate port on the CPX

Note

More information can be found at: → Internet: cpx

FESTO

Pin allocation	Pin allocation – Sub-D plug socket, 24 V DC; electrical connection code MP1									
			Pin ²⁾	Address/coil	Wire colour ¹⁾		Pin ²⁾	Address/coil	Wire colour ¹⁾	
(1	0	WH		17	16	WH PK	
PIN 1 -	$+\circ$	- PIN 20	2	1	BN		18	17	PK BN	
			3	2	GN		19	18	WH BU	
	00		4	3	YE		20	19	BN BU	
	00		5	4	GY		21	20	WH RD	
	000		6	5	РК		22	21	BN RD	
	000		7	6	BU		23	22	GY GN	
			8	7	RD		24	23	YE GY	
	000		9	8	GY PK		25	24	PK GN	
	000		10	9	RD BU		26	25	YE PK	
	000		11	10	WH GN		27	26	GN BU	
	000		12	11	BN GN		28	27	YE BU	
			13	12	WH YE		29	28	GN RD	
PIN 19 -		- PIN 37	14	13	YE BN		30	29	YE RD	
	Ľ		15	14	WH GY		31	30	GN BK	
			16	15	GY BN		32	31	GY BU	
- Note			Conduc	tor						
·≣ - Note			33	0 V ³⁾	YE BK		35	0 V ³⁾	BN BK	
he drawing s			34	0 V ³⁾	WH BK	1	36	0 V ³⁾	BK	
Sub-D plug so	cket at the co	onnecting	Earthin	g	4	1		1	1	
able NEBV-S1	1W37		37	FE	VT		-	-	-	

1) To IEC 757

Pin 9 ... 35: not used with connecting cable NEBV-S1-W37-...-LE10

Pin 23 ... 33: not used with connecting cable NEBV-S1-W37-...-LE26

3) 0 V for positive switching control signals; connect 24 V for negative switching control signals; mixed operation is not permitted.

Dimensions



Download CAD data → www.festo.com

The wire colours refer to the following pre-assembled connecting cables from Festo:

- NEBV-S1W37-...-LE10 for valve terminal with max. 8 solenoid coils
- NEBV-S1W37-...-LE26 for valve terminal with max. 22 solenoid coils
- NEBV-S1W37-...-LE37 for valve terminal with max. 32 solenoid coils

	Sheath	Length	Wire x mm ²	Cable diameter	Part No.	Туре
		[m]	[mm ²]	[mm]		
	Polyurethane	2.5	10 x 0.34	7.7	539240	NEBV-S1W37-E2,5-LE10
		5			539241	NEBV-S1W37-E5-LE10
		10			539242	NEBV-S1W37-E10-LE10
- Carlo		2.5	26 x 0.34	11.5	539243	NEBV-S1W37-E2,5-LE26
		5			539244	NEBV-S1W37-E5-LE26
		10			539245	NEBV-S1W37-E10-LE26
		2.5	37 x 0.34	13	539246	NEBV-S1W37-K2,5-LE37
		5			539247	NEBV-S1W37-K5-LE37
		10			539248	NEBV-S1W37-K10-LE37
	Polyvinyl chloride,	2.5	10 x 0.34	7.7	543271	NEBV-S1W37-KM-2,5-LE10
	cable properties	5			543272	NEBV-S1W37-KM-5-LE10
	(standard)	10			543273	NEBV-S1W37-KM-10-LE10
		2.5	27 x 0.34	11.5	543274	NEBV-S1W37-KM-2,5-LE27
		5			543275	NEBV-S1W37-KM-5-LE27
		10			543276	NEBV-S1W37-KM-10-LE27
		2.5	37 x 0.34	13	543277	NEBV-S1W37-KM-2,5-LE37
		5			543278	NEBV-S1W37-KM-5-LE37
		10			543279	NEBV-S1W37-KM-10-LE37

FESTO

		Terminal	Coil/address	Terminal	Coil/address				
Each solenoid coil must b	e assigned to a specific terminal o	า 1	0	17	16				
the terminal strip in order	for the valves to be actuated.	2	1	18	17				
		3	2	19	18				
Coil 0	Coil 19	4	3	20	19				
		5	4	21	20				
		6	5	22	21				
		7	6	23	22				
		8	7	24	23				
		9	8	25	24				
		10	9	26	25				
		11	10	27	26				
		12	11	28	27				
		13	12	29	28				
		14	13	30	29				
		15	14	31	30				
0 V ¹⁾ Coil 20	Coil 31	16	15	32	31				
- Note		Conductor	Conductor						
The drawing shows the vie	ew onto the multi-pin terminal strip		0 V	35	0 V				
(Cage Clamp®).		34	0 V	36	0 V				

Pin allocation – Round plug connector, 24 V DC; electrical connection code MP4										
	Address	Pin ¹⁾		Address	Pin ¹⁾					
	0	15		8	17					
5 6 7	1	7		9	9					
$\left(\left(4 + \frac{1}{14} + \frac{1}{16} + 8 \right) \right) \right)$	2	5		10	2					
$\left(\left(\begin{array}{c} 3+ \frac{19}{13} + \frac{19}{17} + 9 \\ - + \frac{13}{12} + \frac{19}{12} + - 2 \end{array} \right) \right)$	3	4		11	13					
$\left(\left(\frac{2^{+} + \frac{1}{2} + \frac{1}{2} + \frac{1}{2} + \frac{1}{2} + \frac{1}{2} \right) \right)$	4	16		12	11					
	5	8		13	10					
	6	3		14	1					
	7	14		15	18					

Pin allocation – Round plug connector, 24 V DC; electr	ical connection – CNOI	AO assignment		
	Pin	Valve position/solenoid coil	Pin	Valve position/solenoid coil
	1	8/14	10	7/12
10 120 10	2	6/14	11	7/14
	3	4/14	12	FE
	4	2/12	13	6/12
\\\\₀° ¹⁵ ° ⁴ ////	5	2/14	14	4/12
07 06 05	6	0 V ¹⁾	15	1/14
	7	1/12	16	3/14
	8	3/12	17	5/14
	9	5/12	18	8/12
			19	Unused

1) Pin 6: 0 V for positive switching control signals; connect 24 V for negative switching control signals; mixed operation is not permitted. Pin 12: earth

Pin 19: unused

Rules for addressing

- Address allocation does not depend on whether single or double solenoid valves are fitted.
- Addresses are allocated in

ascending order without gaps, from left to right.

- A valve position for actuating one solenoid coil occupies one address (type VABV-...-...T1).
- A valve position for actuating two solenoid coils occupies two addresses (type VABV-...-...T2). The following allocation applies in this case:
- Coil 14: lower-value address
- Coil 12: higher-value address





Pin al	location for assembly by the	
user		
With p	oositive logic:	Wit
Pin1	– Unused (with 110 V AC	Pin
	connection for earthing)	Pin
Pin2	– U _B for coil 12	Pin
Pin3	– 0 V for coil 12 and 14	Pin
Pin4	– U _B for coil 14	

th negative logic: 1 – Unused 12 - 0 V for coil 12 - U_B for coil 12 and 14 4 - 0 V for coil 14

Individual electrical connection, 6-way or 10-way, 24 V DC, code MP2/MP3 for valve terminal up to width 52 mm





1 Connector plug M12x1, 5-pin

Pin al	location M12
With p	oositive logic:
Pin1	– Unused
Pin2	– U _B for coil 12
Pin3	– 0 V for coil 12 and 14
Pin4	– U _B for coil 14
Pin5	– Functional earth

Pin allocation M12 With negative logic: Pin1 – Unused Pin2 - 0 V for coil 12 Pin 3 - U_B for coil 12 and 14 Pin4 - 0 V for coil 14 Pin5 - Functional earth

Note

Mixed operation of positive switching (PNP) and negative switching (NPN) control signals is not permitted.

Instructions for use - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

System equipment

Operate system equipment with unlubricated compressed air if possible. Festo valves and cylinders are designed so that, if used as designated, they will not require additional lubrication and will still achieve a long service life. The quality of compressed air downstream of the compressor must correspond to that of unlubricated compressed air. If possible, do not operate all of your system equipment with lubricated compressed air. The lubricators should, where possible, always be installed directly upstream of the actuator used.

Incorrect additional oil and too high an oil content in the compressed air reduce the service life of the valve terminal.

Use Festo special oil OFSW-32 or the alternatives listed in the Festo catalogue (as specified in DIN 51524 HLP32; basic oil viscosity 32 CST at 40 °C).

Bio-oils

When using bio-oils (oils which are based on synthetic or native ester, e.g. rapeseed oil methyl ester), the maximum residual oil content of 0.1 mg/m^3 must not be exceeded (see ISO 8573-1 Class 2).

Mineral oils

When using mineral oils (e.g. HLP oils to DIN 51524, parts 1 to 3) or similar oils based on poly-alpha-olefins (PAO), the maximum residual oil content of 5 mg/m³ must not be exceeded (see ISO 8573-1 Class 4). A higher residual oil content irrespective of the compressor oil cannot be permitted, as the basic lubricant would be flushed out over time.



Values in brackets apply to VTSA-F

General technical data

General technical data	
Design	Piston spool valve
Sealing principle	Soft
Actuation type	Electrical
Type of control	Piloted
Exhaust function, with flow control	Via flow control plate
Lubrication	Lubricated for life
Type of mounting	Wall mounting
	On H-rail to EN 60715
Mounting position	Any
Manual override	Non-detenting, detenting, covered
Valve terminal design	Modular and expandable
Max. no of valve positions	32
	- ·
Pneumatic connections – NPT thread	

Pneumatic connections – NPT	thread				
Width		18 mm	26 mm	42 mm	52 mm
Pneumatic connection		Via manifold sub-base			·
Supply port	1	• ½" NPT	• 1/2" NPT	• 1/2" NPT	• 3⁄4" NPT
		• QS-1/2-5/8-U	• QS-1/2-5/8-U	• QS-1/2-5/8-U	• N-3/4-P-19-NPT
		• QS-1/2-1/2-U	• QS-1/2-1/2-U	• QS-1/2-1/2-U	
Exhaust port	3/5	• 1/2" NPT	• 1/2" NPT	• 1/2" NPT	• 3/4" NPT
		• QS-1/2-5/8-U	• QS-1/2-5/8-U	• QS-1/2-5/8-U	• N-3/4-P-19-NPT
		• QS-1/2-1/2-U	• QS-1/2-1/2-U	• QS-1/2-1/2-U	
Working lines	2/4	Dependent on the conr	nection type selected	I	
		• 1⁄8" NPT	• 1⁄4 " NPT	• 3⁄8" NPT	• 1/2 " NPT
		• QS-1/8-5/16-U	• QS-1/4-3/8-U	• QS-3/8-1/2-U	• QS-1/2-5/8-U
		• QS-1/8-1/4-U	● QS-1/4-5/16-U	• QS-3/8-3/8-U	• QS-1/2-1/2-U
External pilot air supply port	14	• 1⁄4 " NPT	• 1⁄4 " NPT	• 1⁄4 " NPT	• 1⁄4 " NPT
		• QS-1/4-3/8-U	• QS-1/4-3/8-U	• QS-1/4-3/8-U	• QS-1/4-1/2-U
		• QS-1/4-5/16-U	• QS-1/4-5/16-U	• QS-1/4-5/16-U	• QS-1/4-3/8-U
Pilot exhaust air port	12	• 1⁄4 " NPT	• 1⁄4 " NPT	• 1⁄4 " NPT	• 1/4 " NPT
		• QS-1/4-3/8-U	• QS-1/4-3/8-U	• QS-1/4-3/8-U	• QS-1/4-1/2-U
		• QS-1/4-5/16-U	• QS-1/4-5/16-U	• QS-1/4-5/16-U	• QS-1/4-3/8-U

Note: This product conforms to ISO 1179-1 and to ISO 228-1

→ Internet: www.festo.com/catalog/...

FESTO

Standard nominal flow rate -	· Valve term																	
Valve function order code		VC	VV	Ν	К	Н	Р	Q	R	М	0	J	D	В	G	E	SA	SB
Width 18 mm																		
Flow rate of valve	[l/min]	700		600)					750				7001	1), 3302)	-	-
Flow rate of valve on valve	[l/min]	500		400)					550				450 ¹	1), 3302)	-	-
terminal																		
Width 26 mm																		
Flow rate of valve	[l/min]	1,350		1,2	50					1,40	0			1,40	01)		1,400	700
Flow rate of valve on valve	[l/min]	1,000		900)					1,10	0			1,00	0 ^{1),} 70(02)	1,000	700
terminal																		
Width 42 mm																		
Flow rate of valve	[l/min]	1,600		1,6	00					2,00	0			1,90	0 ^{1),} 80(02)	-	-
Flow rate of valve on valve terminal	[l/min]	1,400		1,20	00					1,30	00			1,20	0 ^{1),} 80(0 ²⁾	-	-
				1														1
Width 52 mm																		
Flow rate of valve	[l/min]	4,000	-	3,0	00					4,00	00			3,60	0 ^{1),} 1,7	002)	-	-
Flow rate of valve on valve	[l/min]	2,800	-	2,40	00					2,90	0			2,80	0 ^{1),} 1,7	002)	-	-
terminal																		

Switching position
 Mid-position

Standard nominal flow rate -	- Valve termi	nal VTSA	-F															
Valve function order code		VC	VV	Ν	К	Н	Р	Q	R	М	0	J	D	В	G	E	SA	SB
Width 18 mm																		
Flow rate of valve	[l/min]	700		600						750				700 ¹⁾ 330 ²⁾			-	-
Flow rate of valve on valve terminal	[l/min]	650		550						700				480 ¹⁾ 330 ²⁾ 650 (0	(E)		-	-
Width 26 mm																	·	
Flow rate of valve	[l/min]	1,350		1,25	0					1,400)			1,400	1)		1,400	700
Flow rate of valve on valve terminal	[l/min]	1,300		1,15	0					1,350)			1,350 700 ²⁾			1,000	700

Switching position
 Mid-position

Operating and environmenta	l conditions	;																
Valve function order code		VC	Ν	К	Н	VV	Р	Q	R	М	0	J	D	В	G	E	SA	SB
Operating medium		Filtere	ed comp	ressed	air, lub	ricated	or unlu	bricate	ed, iner	t gases	→ 57							
Grade of filtration	[µm]	40 (av	verage p	oore siz	e)													
Operating pressure	[bar]	3 1	0			-0.9.	+10											
Operating pressure for valve	[bar]	3 1	0															
terminal with internal pilot																		
air supply																		
Pilot pressure	[bar]	3 1	0															
Ambient temperature	[°C]	-5 ·	+50															
Temperature of medium	[°C]	-5 ·	+50															
Storage temperature ¹⁾	[°C]	-20	. +40															
Relative air humidity	[%]	90																
PWIS criterion		Free o	f paint-	wetting	impair	ment sı	ıbstanc	es										

1) Long-term storage

FESTO

Pneumatic characteristic data																	
Valve function order code	VC	VV	Ν	К	Н	Р	Q	R	М	0	J	D	В	G	E	SA	SB
Direction of flow																	
Any	-		-	-	-	-	-	-								-	
Reversible only	-	-	-	-	-				-	-	-	-	-	-	-	-	-
Non-reversible		-				-	-	-	-	-	-	-	-	-	-		-
Reset method																	
Pneumatic				-						-	-	-	-	-	-		
Mechanical spring	-	-	-		-	-	-	-	-		-	-				-	-

Pilot pressure p12/14 as a function of operating pressure p1

for 3/2-way valves



Note

Reversible 3/2-way valves (flow direction reversible only)

- These values must only be operated on pressure zones with reversible supply (3 and 5 with supply pressure 1 as

exhaust air) or on a reversible pressure regulator. If necessary create pressure separation zones with duct separation.

- Reversible 3/2-way valves do not permit the special function "pilot exhaust air ducting"

- Ports 12 and 14 on the end plate variants must be supplied with the same pressure
- Right-hand end plate with pilot air selector: can be realised via

1 Operating range for valves with external pilot air supply

position 1 or 2

- Right-hand end plate with threaded connections: 12 and 14 must be supplied with the same pressure level

FESTO

Valve function order code ¹⁾		VC	VV	Ν	К	Н	Р	Q	R	М	0	J	D	В	G	E	SA	SB
Width 18 mm, nominal operating	g voltage 24 V D	C/110 \	V AC															
Switching times [ms]	On	12	12	12	12	12	25	25	25	22	12	-	-	15	15	15	-	-
	Off	30	30	30	30	30	12	12	12	28	38	-	-	44	44	44	-	-
	Change-	-	-	-	-	-	-	-	-	-	-	11	13	-	-	-	-	-
	over																	
Width 26 mm, nominal operating			V AC			-				-		-						
Switching times [ms]	On	20	20	20	20	20	32	32	32	25	20	-	-	22	22	22		9/1
	Off	38	38	38	38	38	30	30	30	45	65	-	-	65	65	65	49	36
	Change-	-	-	-	-	-	-	-	-	-	-	18	21	-	-	-	33	32
	over																	
	10 01117	-																
Width 42 mm, nominal operating			1.0.0	1.0.0	100	1.00		1.0.1		10-	0.0	<u> </u>	-	1.00	0.0	0.0	i	1
Switching times [ms]	On	20	20	20	20	20	34	34	34	27	22	-	-	22	22	22	-	-
	Off	38	38	38	38	38	28	28	28	45	60	-	-	65	65	65	-	-
	Change-	-	-	-	-	-	-	-	-	-	-	16	19	-	-	-	-	-
	over																	
Width 42 mm, nominal operating	g voltage 110 v <i>i</i>	AC .					-	1	1	20	20	r	1			22	1_	1
Switching times [ms]	On	22	22	22	22	22	24	24	24									
Switching times [ms]	On Off	22	22	22	22	22	34	34	34	20	20	-	-	22	22	22		-
Switching times [ms]	Off	46	46	46	46	46	38	38	38	55	55	-	-	68	68	68	-	-
Switching times [ms]	Off Change-																	
Switching times [ms]	Off	46	46	46	46	46	38	38	38	55	55	-	-	68	68	68	-	-
	Off Change- over	46 -	46 -	46 -	46 -	46 -	38	38	38	55	55	-	-	68	68	68	-	-
Width 52 mm, nominal operating	Off Change- over g voltage 24 V D	46 - C with I	46 -	46 –	46 –	46 - ction	38 -	38 -	38 -	55	55 -	- 16	- 19	68 -	68 -	68 -	-	-
	Off Change- over g voltage 24 V D On	46 - C with I 14	46 - holding	46 - g currer 20	46 - nt reduc 20	46 - ction 20	38 - 30	38 - 30	38 - 30	55 - 40	55 - 20	- 16 -	-	68 - 23	68 - 23	68 - 23	-	-
Width 52 mm, nominal operating	Off Change- over g voltage 24 V D On Off	46 - C with I 14 35	46 -	46 –	46 –	46 - ction	38 -	38 -	38 -	55 - 40 45	55 - 20 60	- 16 - -	- 19 - - -	68 -	68 -	68 -	-	-
Width 52 mm, nominal operating	Off Change- over g voltage 24 V D On Off Change-	46 - C with I 14	46 - holding - -	46 - g currer 20 35	46 - nt reduce 20 35	46 - ction 20 35	38 - 30 30	38 - 30 30	38 - 30 30	55 - 40	55 - 20	- 16 -	- 19 -	68 - 23 60	68 - 23 60	68 - 23 60	-	-
Width 52 mm, nominal operating	Off Change- over g voltage 24 V D On Off	46 - C with I 14 35	46 - holding - -	46 - g currer 20 35	46 - nt reduce 20 35	46 - ction 20 35	38 - 30 30	38 - 30 30	38 - 30 30	55 - 40 45	55 - 20 60	- 16 - -	- 19 - - -	68 - 23 60	68 - 23 60	68 - 23 60	-	-
Width 52 mm, nominal operating Switching times [ms]	Off Change- over g voltage 24 V D On Off Change- over	46 - C with I 14 35 -	46 - holding - -	46 - g currer 20 35	46 - nt reduce 20 35	46 - ction 20 35	38 - 30 30	38 - 30 30	38 - 30 30	55 - 40 45	55 - 20 60	- 16 - -	- 19 - - -	68 - 23 60	68 - 23 60	68 - 23 60	-	-
Width 52 mm, nominal operating	Off Change- over g voltage 24 V D On Off Change- over	46 - C with I 14 35 -	46 - holding - -	46 - g currer 20 35	46 - nt reduce 20 35	46 - ction 20 35	38 - 30 30	38 - 30 30	38 - 30 30	55 - 40 45	55 - 20 60	- 16 - -	- 19 - - -	68 - 23 60	68 - 23 60	68 - 23 60	-	-
Width 52 mm, nominal operating Switching times [ms] Width 52 mm, nominal operating	Off Change- over g voltage 24 V D On Off Change- over g voltage 110 V	46 - 14 35 - AC 35	46 	46 - 20 35 - 35	46 - 20 35 - 35	46 - 20 35 - 35	38 - 30 30 - - 50	38 - 30 30 - 50	38 - 30 30 - - 50	55 - 40 45 - 70	55 - 20 60 - 20	- 16 - - 18	- 19 - - 18	68 - 23 60 -	68 - 23 60 -	68 - 23 60 - 30	-	- - - -
Width 52 mm, nominal operating Switching times [ms] Width 52 mm, nominal operating	Off Change- over g voltage 24 V Dr On Off Change- over g voltage 110 V / On	46 - C with 1 14 35 -	46 	46 - 20 35 -	46 - 20 35 -	46 - 20 35 -	38 - 30 30 -	38 - 30 30 -	38 - 30 30 -	55 - 40 45 -	55 - 20 60 -	- 16 - - 18 -	- 19 - - 18 -	68 - 23 60 - 30	68 - 23 60 - 30	68 - 23 60 -	-	- - - -

1) Valve code SA, switching time 22 ms for control side 12, 9 ms for control side 14 Valve code SB, switching time 19 ms for control side 12, 9 ms for control side 14

Electrical data – Maximum current	consumptio	n per solenoid coil	
Width		52 mm	
At nominal voltage (valves with hold	ing current I	reduction)	
		2x 2/2-way and 2x 3/2-way valve	5/2-way, 5/3-way valve
Nominal pick-up current	[mA]	165	165
Nominal current following current	[mA]	35	35
reduction			
Time until current reduction	[ms]	30	30

Electrical data – Individual electric	al connectio	n			
Width		18 mm	26 mm	42 mm	52 mm
Load voltage supply for valves (Uval					
Operating voltage	[V DC]	24 ±10%			
Max. residual current at 24 V DC	[A]	10			
Duty cycle		100%			
Protection class to EN 60529		IP65 and NEMA 4 (for all	types of signal trans	mission in assembled state	2)
Coil characteristics at 24 V DC					
2/2-way and 3/2-way valve	[W]	1.3			4.6
5/2-way valve (code D)	[W]	1.3			4.6
5/2-way, 5/3-way valve	[W]	1.6			4.6

Electrical data – Multi-pin plug connection						
Width		18 mm	26 mm	42 mm	52 mm	
Load voltage supply for valves (U _{val})						
Operating voltage	[V DC]	24 ±10%				
	[V AC]	110 ±10% (50 60 Hz)				
Max. residual current	[A]	6	6			
Acceptable current load at 40 °C	[A]	1				
Surge capacity	[kV]	1.5				
Degree of contamination 3						
Duty cycle 100%						
Protection class to EN 60529 IP65 and NEMA 4 (for all types of signal transmission in assembled state)						
Coil characteristics at 24 V DC						
2/2-way and 3/2-way valve	[W]	1.3 4.6			4.6	
5/2-way valve (code D)	[W]	1.3 4.6				
5/2-way, 5/3-way valve	[W]	1.6 4.6				
Coil characteristics at 110 V AC						
2/2-way and 3/2-way valve	[VA]	1				
5/2-way, 5/3-way valve	[VA]	1.6				

Electrical data – With CPX terminal					
Width		18 mm	26 mm	42 mm	52 mm
Power supply for electronics (U _{EL/SEN}))				
Operating voltage	[V DC]	24 ±10%			
Max. intrinsic current consumption	[mA]	20			
at 24 V DC					
Duty cycle		100%			
Load voltage supply for valves (U_{val})					
Operating voltage	[V DC]	24 ±10%			
Diagnostic message undervoltage	[V]	21.6 21.5			
U _{OFF} , load voltage outside function					
range	range				
Protection class to EN 60529		IP65 and NEMA 4 (for all types of signal transmission in assembled state)			
Coil characteristics at 24 V DC					
2/2-way and 3/2-way valve	[W]	1.3 4.6			
5/2-way valve (code D)	[W]	1.3 4.6			4.6
5/2-way, 5/3-way valve	[W]	1.6 4.6			

FESTO

ATEX					
Connection variant ¹⁾	VTSA-MP	VTSA-FB	VTSA-ASI		
ATEX category for gas	II 3G				
Explosion ignition protection type for gas	Ex nA II T3 X				
ATEX category for dust	II 3D				
Explosion ignition protection type for dust	Ex tD A22 IP65 T125° C X				
ATEX temperature rating [°C]	-5 ≤ Ta ≤ +50				
CE marking (see declaration of conformity) ²⁾	To EU EMC Directive				

1) This product is certified for use in the ATEX zone in accordance with the EU ATEX Directive The certification is valid for: VTSA-MP, VTSA-FB and VTSA-ASI

Multi-pin plug variant 1 (24 V DC): no Multi-pin plug variant 2A (110 V): to EU Low Voltage Directive CPX variant: to EU EMC Directive

Materials				
Width	18 mm	26 mm	42 mm	52 mm
Manifold sub-base	Die-cast aluminium			
Valve	Die-cast aluminium, reinforced polyamide			
Seals	Nitrile rubber, elastomer (support made of steel)			
Supply plate	Die-cast aluminium			
Right-hand end plate	Die-cast aluminium			
Pneumatic interface for CPX	Die-cast aluminium			
Flow control plate	Die-cast aluminium			
Pressure regulator plate	Die-cast aluminium, reinforced polyamide			
Multi-pin connection block	Die-cast aluminium			
Cover for the pneumatic interface and multi-pin	Wellamid, reinforced polyamide			
plug connection				
RoHS status	RoHS-compliant			

Product weight				
Approx. weight [g]			
Width	18 mm	26 mm	42 mm	52 mm
Sub-D multi-pin interface module or terminal	550		I	
strip ¹⁾				
Multi-pin node with M12 individual connection	760			
Interface module CPX ¹⁾	1,470			
Electrical connection for AS-interface	300			
AS-interface module	850			
Supply plate ²⁾				
• Exhaust plate with 3 and 5 common	617			
• Exhaust port cover with 3 and 5 separated	597			
Right-hand end plate ³⁾				
– Axial	339			336
- Selector	281			-
Manifold sub-base ⁴⁾	447	634	340	815
90° connection plate ³⁾	170	230	176	359
Pressure regulator plate				
for port 1	350	402	640	1,190
for port 4 or 2	367	448	640	1,230
for ports 4 and 2	611	692	920	1,990
Flow control plate	228	320	220	565
Vertical supply plate ³⁾	140	191	340	605
Vertical pressure shut-off plate	209	273	600	1,030
Valves				
 5/3-way valve 	191	320	456	780
(code: B, G, E)				
 5/3-way valve 	-	301	-	-
(code: SA, SB)				
 5/2-way valve, single solenoid 	163	293	426	702
(code: M, O)				
 5/2-way valve, double solenoid 	172	276	439	732
(code: J, D)				
 2x 3/2-way valve 	190	335	442	740
(code: N, K, H, P, Q, R)				
 2x 2/2-way valve 	190	335	442	740
(code: VC, VV)				
Blanking plate	34	73	68	146

With sheet metal seal, printed circuit board
 With sheet metal seal and electrical interlinking module

With screws
With sheet metal seal, electrical interlinking module, inscription label holder, 4 screws



FESTO



Flow rate qn as a function of output pressure p2 with pressure regulator plates (P regulator plate) for port 1

Supply pressure 10 bar, set control pressure 6 bar





Width 42 mm (ISO 1)

Width 52 mm (ISO 2)













Flow rate qn as a function of output pressure p2 with pressure regulator plates (AB regulator plates, rev.) for ports 4/2, reversible 6 bar 10 bar 7 7 6 6 5 5 p2 [bar] p2 [bar] 4 4 3-3 2-2 1 1 0-0 600 800 1000 1200 1400 1600 600 800 1000 1200 1400 1600 0 200 400 0 200 400 qn [l/min] qn [l/min] Width 18 mm - Width 18 mm ----- Width 26 mm ----- Width 26 mm







Width 52 mm (ISO 2)

500 1000 1500 2000 2500 3000 3500 4000 4500

qn [l/min]





----- Width 26 mm

Flow rate qn as a function of flow control







FESTO



Width	L1		
18 mm	71.3 + n02 x 38 + n x 38 + 37.3		
26 mm	71.3 + n01 x 54 + n x 38 + 37.3		
42 mm	71.3 + n1 x 43 + n x 38 + 37.3		
52 mm	71.3 + n2 x 59 + n x 38 + 37.3		
Mixture of 18 mm, 26 mm, 42 mm and 52 mm	71.3 + n02 x 38 + n01 x 54 + n1 x 43 + n2x59 + n x 38 + 37.3		

 $\|\cdot\>$ Note: This product conforms to ISO 1179-1 and to ISO 228-1

FESTO



Width	L1		
18 mm	71.3 + n02 x 38 + n x 38 + 37.3		
26 mm	71.3 + n01 x 54 + n x 38 + 37.3		
42 mm	71.3 + n1 x 43 + n x 38 + 37.3		
52 mm	71.3 + n2 x 59 + n x 38 + 37.3		
Mixture of 18 mm, 26 mm, 42 mm and 52 mm	71.3 + n02 x 38 + n01 x 54 + n1 x 43 + n2 x 59 + n x 38+ 37.3		

Note: This product conforms to ISO 1179-1 and to ISO 228-1






Width	L1
18 mm	71.3 + n02 x 38 + n x 38 + 37.3
26 mm	71.3 + n01 x 54 + n x 38 + 37.3
42 mm	71.3 + n1 x 43 + n x 38 + 37.3
52 mm	71.3 + n2 x 59 + n x 38 + 37.3
Mixture of 18 mm, 26 mm , 42 mm and 52 mm	71.3 + n02 x 38 + n01 x 54 + n1 x 43 + n2 x 59 + n x 38 + 37.3

Valve terminals type 44/45, VTSA/VTSA-F, NPT

Technical data – Valve terminal – ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm



Width	L1
18 mm	30.4 + m x 50.1 + 50 + n02 x 38 + n x 38 + 37.3
26 mm	30.4 + m x 50.1 + 50 + n01 x 54 + n x 38 + 37.3
42 mm	30.4 + m x 50.1 + 50 + n1 x 43 + n x 38 + 37.3
52 mm	30.4 + m x 50.1 + 50 + n2 x 59 + n x 38 + 37.3
Mixture of 18 mm, 26 mm, 42 mm and 52 mm	30.4 + m x 50.1 + 50 + n02 x 38 + n01 x 54 + n1 x 43 + n2x59 + n x 38 + 37.3

Note: This product conforms to ISO 1179-1 and to ISO 228-1

FESTO



С. С

6

2011/02 - Subject to change

46

8 Pressure gauge,

freely positionable



Dimensions Download CAD data → www.festo.com Vertical stacking components, width 42 mm 137.8 ø 1 1 3 ₽ 105.3 28 173.8 45.3 0 4 0 9 117.6 45.3 5 1 Solenoid valve 6 65 3 Flow control plate 7 4 Vertical pressure shut-off plate 5 Vertical supply plate 5 6 Manifold sub-base 142 46 25.7 7 90° connection plate







Note

Pressure regulator plates for symmetrical valves with widths of 42 mm and 52 mm can only be ordered via the pressure regulator configurator VABF-S2.

→ Internet: vabf-s2

2011/02 - Subject to change

Dimensions Download CAD data **→** www.festo.com Vertical stacking components, width 52 mm 160.7 1 3-Υ, Γ 131 191.2 58.7 4 287 136 58.7 5 1 Solenoid valve 6 3 Flow control plate 63.5 65 6 21.2 4 Vertical pressure shut-off plate 5 Vertical supply plate 7-6 Manifold sub-base 142 46 7 90° connection plate Vertical stacking components, width 52 mm 10 160,7 9 1 8 Ē Ē ₩**∃**[@ 278 Ξ 品 2 1 Solenoid valve ഗ 2 Pressure regulator plate 3 131 22 3 Flow control plate

32.5

- 6 Manifold sub-base
- 7 90° connection plate
- 8 Pressure gauge, freely positionable
- 9 Standard rotary knob 10 Lockable rotary knob

Note

Pressure regulator plates for symmetrical valves with widths of 42 mm and 52 mm can only be ordered via the pressure regulator configurator VABF-S2.

➔ Internet: vabf-s2

6

7

63.5

21.2

TIT

46

142

FESTO



Right-hand end plate



Right-hand end plate with pilot air selector



Туре	D1	D2	With
VABE-S6-1R-N12	1⁄2" NPT	1⁄4 " NPT	1
VABE-S6-1RZ-N12	1⁄2" NPT	1⁄4 " NPT	-

Туре	D1
VABE-S6-1RZ-N-B1	1⁄4 " NPT

 $\|\cdot\|$ Note: This product conforms to ISO 1179-1 and to ISO 228-1

Right-hand end plate 65 10.8 6.6 49.9 121 θ 36.9 \oplus 2.2 3 10.5 6.3 26.7 2,3 40 1 Œ Fð 73.6 37.3 0.4 1 Blanking plug

Туре	D1	D2	With
VABE-S6-2R-N34	3⁄4 " NPT	1⁄4 " NPT	1
VABE-S6-2RZ-N34	3⁄4" NPT	1⁄4 " NPT	

 $\|\cdot\|$ Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data					
	Code	Valve function	Width	Part No.	Туре
Solenoid valves, 24	V DC				
	VC	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return	18 mm	561155	VSVA-B-T22C-AZD-A2-1T1L
A A A	VV	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return, vacuum operation possible at 3 and 5	18 mm	561159	VSVA-B-T22CV-AZD-A2-1T1L
	N	2x 3/2-way valve, single solenoid, normally open	18 mm	539178	VSVA-B-T32U-AZD-A2-1T1L
	К	2x 3/2-way valve, single solenoid, normally closed	18 mm	539176	VSVA-B-T32C-AZD-A2-1T1L
	Н	2x 3/2-way valve, single solenoid, 1x normally open, 1x normally closed	18 mm	539180	VSVA-B-T32H-AZD-A2-1T1L
	Ρ	2x 3/2-way valve, single solenoid, reverse operation, normally open	18 mm	539179	VSVA-B-T32F-AZD-A2-1T1L
	Q	2x 3/2-way valve, single solenoid, reverse operation, normally closed	18 mm	539177	VSVA-B-T32N-AZD-A2-1T1L
	R	2x 3/2-way valve, single solenoid, reverse operation, 1x normally open, 1x normally closed	18 mm	539181	VSVA-B-T32W-AZD-A2-1T1L
	М	5/2-way valve, single solenoid, pneumatic spring return	18 mm	539184	VSVA-B-M52-AZD-A2-1T1L
	0	5/2-way valve, single solenoid, mechanical spring return	18 mm	539185	VSVA-B-M52-MZD-A2-1T1L
	J	5/2-way valve, double solenoid	18 mm	539182	VSVA-B-B52-ZD-A2-1T1L
	D	5/2-way valve, double solenoid, with dominant signal	18 mm	539183	VSVA-B-D52-ZD-A2-1T1L
	В	5/3-way valve, mid-position pressurised	18 mm	539186	VSVA-B-P53U-ZD-A2-1T1L
	G	5/3-way valve, mid-position closed	18 mm	539188	VSVA-B-P53C-ZD-A2-1T1L
	E	5/3-way valve, mid-position exhausted	18 mm	539187	VSVA-B-P53E-ZD-A2-1T1L

Valve terminals type 44/45, VTSA/VTSA-F, NPT

Ordering data - Individual valve 24 V DC - ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Ordering data Valve function Width Part No. Code Туре Solenoid valves, 24 V DC VC 2x 2/2-way valve, single solenoid, 26 mm 561149 VSVA-B-T22C-AZD-A1-1T1L E normally closed, pneumatic spring return VV 2x 2/2-way valve, single solenoid, 26 mm 561153 VSVA-B-T22CV-AZD-A1-1T1L normally closed, pneumatic spring return, vacuum operation possible at 3 and 5 Ν 2x 3/2-way valve, single solenoid, 26 mm 539152 VSVA-B-T32U-AZD-A1-1T1L normally open К 2x 3/2-way valve, single solenoid, 26 mm 539150 VSVA-B-T32C-AZD-A1-1T1L normally closed 2x 3/2-way valve, single solenoid, 539154 VSVA-B-T32H-AZD-A1-1T1L Н 26 mm 1x normally open, 1x normally closed VSVA-B-T32F-AZD-A1-1T1L 2x 3/2-way valve, single solenoid, 26 mm 539153 Р reverse operation, normally open Q 2x 3/2-way valve, single solenoid, 26 mm 539151 VSVA-B-T32N-AZD-A1-1T1L reverse operation, normally closed 2x 3/2-way valve, single solenoid, R 26 mm 539155 VSVA-B-T32W-AZD-A1-1T1L reverse operation, 1x normally open, 1x normally closed Μ 5/2-way valve, single solenoid, 26 mm 539158 VSVA-B-M52-AZD-A1-1T1L pneumatic spring return 0 5/2-way valve, single solenoid, 26 mm 539159 VSVA-B-M52-MZD-A1-1T1L mechanical spring return 5/2-way valve, double solenoid 26 mm 539156 VSVA-B-B52-ZD-A1-1T1L I 5/2-way valve, double solenoid, 539157 VSVA-B-D52-ZD-A1-1T1L D 26 mm with dominant signal 539160 VSVA-B-P53U-ZD-A1-1T1L R 5/3-way valve, 26 mm mid-position pressurised 26 mm 539162 VSVA-B-P53C-ZD-A1-1T1L G 5/3-way valve, mid-position closed Ε 5/3-way valve, 26 mm 539161 VSVA-B-P53E-ZD-A1-1T1L mid-position exhausted SA 26 mm 560727 VSVA-B-P53ED-ZD-A1-1T1L 5/3-way valve, mid-position exhausted, switching position 14 detenting, mechanical spring return SB 26 mm VSVA-B-P53AD-ZD-A1-1T1L 5/3-way valve, 560728 mid-position 1x exhausted from 4 to 5, 1x pressurised from 1 to 2, switching position 14 detenting, same function in both switching positions: pressurised from 1 to 4 and exhausted from 2 to 3, mechanical spring return

Ordering data					
	Code	Valve function	Width	Part No.	Туре
Solenoid valves, 24	V DC				
	VC	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return	42 mm	561340	VSVA-B-T22C-AZD-D1-1T1L
	W	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return, vacuum operation possible at 3 and 5	42 mm	561344	VSVA-B-T22CV-AZD-D1-1T1L
	N	2x 3/2-way valve, single solenoid, normally open	42 mm	543692	VSVA-B-T32U-AZD-D1-1T1L
	К	2x 3/2-way valve, single solenoid, normally closed	42 mm	543690	VSVA-B-T32C-AZD-D1-1T1L
	Н	2x 3/2-way valve, single solenoid, 1x normally open, 1x normally closed	42 mm	543694	VSVA-B-T32H-AZD-D1-1T1L
	Ρ	2x 3/2-way valve, single solenoid, reverse operation, normally open	42 mm	543693	VSVA-B-T32F-AZD-D1-1T1L
	Q	2x 3/2-way valve, single solenoid, reverse operation, normally closed	42 mm	543691	VSVA-B-T32N-AZD-D1-1T1L
	R	2x 3/2-way valve, single solenoid, reverse operation, 1x normally open, 1x normally closed	42 mm	543695	VSVA-B-T32W-AZD-D1-1T1L
	М	5/2-way valve, single solenoid, pneumatic spring return	42 mm	543698	VSVA-B-M52-AZD-D1-1T1L
	0	5/2-way valve, single solenoid, mechanical spring return	42 mm	543699	VSVA-B-M52-MZD-D1-1T1L
	J	5/2-way valve, double solenoid	42 mm	543696	VSVA-B-B52-ZD-D1-1T1L
	D	5/2-way valve, double solenoid, with dominant signal	42 mm	543697	VSVA-B-D52-ZD-D1-1T1L
	В	5/3-way valve, mid-position pressurised	42 mm	543700	VSVA-B-P53U-ZD-D1-1T1L
	G	5/3-way valve, mid-position closed	42 mm	543702	VSVA-B-P53C-ZD-D1-1T1L
	E	5/3-way valve, mid-position exhausted	42 mm	543701	VSVA-B-P53E-ZD-D1-1T1L

Ordering data					
	Code	Valve function	Width	Part No.	Туре
olenoid valves,	24 V DC				
	VC	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return	52 mm	560831	VSVA-B-T22C-AZD-D2-1T1L
	N	2x 3/2-way valve, single solenoid, normally open	52 mm	560827	VSVA-B-T32U-AZD-D2-1T1L
	К	2x 3/2-way valve, single solenoid, normally closed	52 mm	560825	VSVA-B-T32C-AZD-D2-1T1L
	Н	2x 3/2-way valve, single solenoid, 1x normally open, 1x normally closed	52 mm	560829	VSVA-B-T32H-AZD-D2-1T1L
	Р	2x 3/2-way valve, single solenoid, reverse operation, normally open	52 mm	560828	VSVA-B-T32F-AZD-D2-1T1L
	Q	2x 3/2-way valve, single solenoid, reverse operation, normally closed	52 mm	560826	VSVA-B-T32N-AZD-D2-1T1L
	R	2x 3/2-way valve, single solenoid, reverse operation, 1x normally open, 1x normally closed	52 mm	560830	VSVA-B-T32W-AZD-D2-1T1L
	М	5/2-way valve, single solenoid, pneumatic spring return	52 mm	560820	VSVA-B-M52-AZD-D2-1T1L
	0	5/2-way valve, single solenoid, mechanical spring return	52 mm	560821	VSVA-B-M52-MZD-D2-1T1L
	J	5/2-way valve, double solenoid	52 mm	560818	VSVA-B-B52-ZD-D2-1T1L
	D	5/2-way valve, double solenoid, with dominant signal	52 mm	560819	VSVA-B-D52-ZD-D2-1T1L
	В	5/3-way valve, mid-position pressurised	52 mm	560822	VSVA-B-P53U-ZD-D2-1T1L
	G	5/3-way valve, mid-position closed	52 mm	560824	VSVA-B-P53C-ZD-D2-1T1L
	E	5/3-way valve, mid-position exhausted	52 mm	560823	VSVA-B-P53E-ZD-D2-1T1L

Ordering data					
	Code	Valve function	Width	Part No.	Туре
Solenoid valves, 110) V AC				
	VC	2x 2/2-way valve, single solenoid,	18 mm	561156	VSVA-B-T22C-AZD-A2-2AT1L
		normally closed,			
		pneumatic spring return			
R R	VV N	2x 2/2-way valve, single solenoid,	18 mm	561160	VSVA-B-T22CV-AZD-A2-2AT1L
	1	normally closed,			
		pneumatic spring return,			
		vacuum operation possible at 3 and 5			
	Ν	2x 3/2-way valve, single solenoid,	18 mm	539165	VSVA-B-T32U-AZD-A2-2AT1L
		normally open			
	К	2x 3/2-way valve, single solenoid,	18 mm	539163	VSVA-B-T32C-AZD-A2-2AT1L
		normally closed			
	Н	2x 3/2-way valve, single solenoid,	18 mm	539167	VSVA-B-T32H-AZD-A2-2AT1L
		1x normally open, 1x normally closed			
	Р	2x 3/2-way valve, single solenoid,	18 mm	539166	VSVA-B-T32F-AZD-A2-2AT1L
		reverse operation,			
		normally open			
	Q	2x 3/2-way valve, single solenoid,	18 mm	539164	VSVA-B-T32N-AZD-A2-2AT1L
		reverse operation,			
		normally closed			
	R	2x 3/2-way valve, single solenoid,	18 mm	539168	VSVA-B-T32W-AZD-A2-2AT1L
		reverse operation,			
		1x normally open, 1x normally closed			
	М	5/2-way valve, single solenoid,	18 mm	539171	VSVA-B-M52-AZD-A2-2AT1L
		pneumatic spring return			
	0	5/2-way valve, single solenoid,	18 mm	539172	VSVA-B-M52-MZD-A2-2AT1L
		mechanical spring return			
	J	5/2-way valve, double solenoid	18 mm	539169	VSVA-B-B52-ZD-A2-2AT1L
	-	-,,			
	D	5/2-way valve, double solenoid,	18 mm	539170	VSVA-B-D52-ZD-A2-2AT1L
		with dominant signal			
	В	5/3-way valve,	18 mm	539173	VSVA-B-P53U-ZD-A2-2AT1L
	-	mid-position pressurised			
	G	5/3-way valve,	18 mm	539175	VSVA-B-P53C-ZD-A2-2AT1L
	Ĩ	mid-position closed			
	E	5/3-way valve,	18 mm	539174	VSVA-B-P53E-ZD-A2-2AT1L
		mid-position exhausted	10 1111	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	
		Interposition condusted			

Ordering data	_			_	
	Code	Valve function	Width	Part No.	Туре
olenoid valves, 11	.0 V AC				
e.	VC	2x 2/2-way valve, single solenoid,	26 mm	561150	VSVA-B-T22C-AZD-A1-2AT1L
		normally closed,			
		pneumatic spring return			
	N N	2x 2/2-way valve, single solenoid,	26 mm	561154	VSVA-B-T22CV-AZD-A1-2AT1L
		normally closed,			
4		pneumatic spring return,			
		vacuum operation possible at 3 and 5			
	Ν	2x 3/2-way valve, single solenoid,	26 mm	539139	VSVA-B-T32U-AZD-A1-2AT1L
		normally open			
	К	2x 3/2-way valve, single solenoid,	26 mm	539137	VSVA-B-T32C-AZD-A1-2AT1L
		normally closed			
	Н	2x 3/2-way valve, single solenoid,	26 mm	539141	VSVA-B-T32H-AZD-A1-2AT1L
		1x normally open, 1x normally closed			
	Р	2x 3/2-way valve, single solenoid,	26 mm	539140	VSVA-B-T32F-AZD-A1-2AT1L
		reverse operation,			
		normally open			
	Q	2x 3/2-way valve, single solenoid,	26 mm	539138	VSVA-B-T32N-AZD-A1-2AT1L
		reverse operation,			
		normally closed			
	R	2x 3/2-way valve, single solenoid,	26 mm	539142	VSVA-B-T32W-AZD-A1-2AT1L
		reverse operation,			
		1x normally open, 1x normally closed			
	М	5/2-way valve, single solenoid,	26 mm	539145	VSVA-B-M52-AZD-A1-2AT1L
		pneumatic spring return			
	0	5/2-way valve, single solenoid,	26 mm	539146	VSVA-B-M52-MZD-A1-2AT1L
		mechanical spring return			
	J	5/2-way valve, double solenoid	26 mm	539143	VSVA-B-B52-ZD-A1-2AT1L
	D	5/2-way valve, double solenoid,	26 mm	539144	VSVA-B-D52-ZD-A1-2AT1L
		with dominant signal			
	В	5/3-way valve,	26 mm	539147	VSVA-B-P53U-ZD-A1-2AT1L
		mid-position pressurised			
	G	5/3-way valve,	26 mm	539149	VSVA-B-P53C-ZD-A1-2AT1L
		mid-position closed			
	E	5/3-way valve,	26 mm	539148	VSVA-B-P53E-ZD-A1-2AT1L
		mid-position exhausted		1	

Ordering data					
	Code	Valve function	Width	Part No.	Туре
Solenoid valves, 110					
	VC	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return	42 mm	561341	VSVA-B-T22C-AZD-D1-2AT1L
	vv	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return, vacuum operation possible at 3 and 5	42 mm	561345	VSVA-B-T22CV-AZD-D1-2AT1L
	N	2x 3/2-way valve, single solenoid, normally open	42 mm	543679	VSVA-B-T32U-AZD-D1-2AT1L
	К	2x 3/2-way valve, single solenoid, normally closed	42 mm	543677	VSVA-B-T32C-AZD-D1-2AT1L
	Н	2x 3/2-way valve, single solenoid, 1x normally open, 1x normally closed	42 mm	543681	VSVA-B-T32H-AZD-D1-2AT1L
	Р	2x 3/2-way valve, single solenoid, reverse operation, normally open	42 mm	543680	VSVA-B-T32F-AZD-D1-2AT1L
	Q	2x 3/2-way valve, single solenoid, reverse operation, normally closed	42 mm	543678	VSVA-B-T32N-AZD-D1-2AT1L
	R	2x 3/2-way valve, single solenoid, reverse operation, 1x normally open, 1x normally closed	42 mm	543682	VSVA-B-T32W-AZD-D1-2AT1L
	М	5/2-way valve, single solenoid, pneumatic spring return	42 mm	543685	VSVA-B-M52-AZD-D1-2AT1L
	0	5/2-way valve, single solenoid, mechanical spring return	42 mm	543686	VSVA-B-M52-MZD-D1-2AT1L
	J	5/2-way valve, double solenoid	42 mm	543683	VSVA-B-B52-ZD-D1-2AT1L
	D	5/2-way valve, double solenoid, with dominant signal	42 mm	543684	VSVA-B-D52-ZD-D1-2AT1L
	В	5/3-way valve, mid-position pressurised	42 mm	543687	VSVA-B-P53U-ZD-D1-2AT1L
	G	5/3-way valve, mid-position closed	42 mm	543689	VSVA-B-P53C-ZD-D1-2AT1L
	E	5/3-way valve, mid-position exhausted	42 mm	543688	VSVA-B-P53E-ZD-D1-2AT1L

Ordering data					
	Code	Valve function	Width	Part No.	Туре
olenoid valves,					
	VC	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return	52 mm	560812	VSVA-B-T22C-AZD-D2-2AT1L
	N	2x 3/2-way valve, single solenoid, normally open	52 mm	560808	VSVA-B-T32U-AZD-D2-2AT1L
	К	2x 3/2-way valve, single solenoid, normally closed	52 mm	560806	VSVA-B-T32C-AZD-D2-2AT1L
	Н	2x 3/2-way valve, single solenoid, 1x normally open, 1x normally closed	52 mm	560810	VSVA-B-T32H-AZD-D2-2AT1L
	Р	2x 3/2-way valve, single solenoid, reverse operation, normally open	52 mm	560809	VSVA-B-T32F-AZD-D2-2AT1L
	Q	2x 3/2-way valve, single solenoid, reverse operation, normally closed	52 mm	560807	VSVA-B-T32N-AZD-D2-2AT1L
	R	2x 3/2-way valve, single solenoid, reverse operation, 1x normally open, 1x normally closed	52 mm	560811	VSVA-B-T32W-AZD-D2-2AT1L
	М	5/2-way valve, single solenoid, pneumatic spring return	52 mm	560801	VSVA-B-M52-AZD-D2-2AT1L
	0	5/2-way valve, single solenoid, mechanical spring return	52 mm	560802	VSVA-B-M52-MZD-D2-2AT1L
	J	5/2-way valve, double solenoid	52 mm	560799	VSVA-B-B52-ZD-D2-2AT1L
	D	5/2-way valve, double solenoid, with dominant signal	52 mm	560800	VSVA-B-D52-ZD-D2-2AT1L
	В	5/3-way valve, mid-position pressurised	52 mm	560803	VSVA-B-P53U-ZD-D2-2AT1L
	G	5/3-way valve, mid-position closed	52 mm	560805	VSVA-B-P53C-ZD-D2-2AT1L
	E	5/3-way valve, mid-position exhausted	52 mm	560804	VSVA-B-P53E-ZD-D2-2AT1L

Ordering data					
Designation	Code	Description	Width	Part No.	Туре
Right-hand end pl	ate				
\sim	V	With supply air/exhaust air, internal pilot air supply, 1/2" NPT		539235	VABE-S6-1R-N12
0	V1	With supply air/exhaust air, internal pilot air supply, 3/4 " NPT		560838	VABE-S6-2R-N34
	Х	With supply air/exhaust air, external pilot air supply, ½" NPT		539237	VABE-S6-1RZ-N12
	X1	With supply air/exhaust air, external pilot air supply, 3/4 " NPT		560840	VABE-S6-2RZ-N34
	I				
End plate with pilo	ot air selecto	r			
~~	Y	Internal pilot air supply		539239	VABE-S6-1RZ-N-B1
	U	Internal pilot air supply, ducted pilot exhaust air			
	Z	External pilot air supply			
	W	External pilot air supply, ducted pilot exhaust air			
	1				
Manifold sub-base	e, port patter	n to ISO 15407-2 and ISO 5599-2			
	A	2 valve positions, 4 addresses, for double solenoid valves	18 mm	539219	VABV-S4-2S-N18-2T2
	В	2 valve positions, 4 addresses, for double solenoid valves	26 mm	539223	VABV-S4-1S-N14-2T2
	С	1 valve position, 2 addresses, for double solenoid valves	42 mm	542460	VABV-S2-1S-N38-T2
	D	1 valve position, 2 addresses, for double solenoid valves	52 mm	560843	VABV-S2-2S-N12-T2
*	E	2 valve positions, 2 addresses, for single solenoid valves	18 mm	539221	VABV-S4-2S-N18-2T1
	F	2 valve positions, 2 addresses, for single solenoid valves	26 mm	539225	VABV-S4-1S-N14-2T1
	G	1 valve position, 1 address, for single solenoid valves	42 mm	542461	VABV-S2-1S-N38-T1
	Н	1 valve position, 1 address, for single solenoid valves	52 mm	560844	VABV-S2-2S-N12-T1
Manifold sub-base	e VTSA-F, opti	mised for flow rate			
	A	2 valve positions, 4 addresses, for double solenoid valves	18 mm	546217	VABV-S4-2HS-N18-2T2
	В	2 valve positions, 4 addresses, for double solenoid valves	26 mm	546213	VABV-S4-1HS-N14-2T2
	E	2 valve positions, 2 addresses, for single solenoid valves	18 mm	546216	VABV-S4-2HS-N18-2T1
No. Contraction of the second	F	2 valve positions, 2 addresses, for single solenoid valves	26 mm	546212	VABV-S4-1HS-N14-2T1

Ordering data					
Designation	Code	Description	Width	Part No.	Туре
Separator plate					
	S	Duct separation 1, 3, 5		539228	VABD-S6-10-P3-C
	Т	Duct separation 1		539227	VABD-S6-10-P1-C
	R	Duct separation 3, 5		539229	VABD-S6-10-P2-C
90° connection pl	ate				
38	Р	Outlet at bottom, connecting thread 1/8" NPT	18 mm	539720	VABF-S4-2-A2G2-N18
		Outlet at bottom, connecting thread 1/4 " NPT	26 mm	539722	VABF-S4-1-A2G2-N14
	S	Outlet at bottom, connecting thread 3/8" NPT	42 mm	546098	VABF-S2-1-A1G2-N38
	3	Outlet at bottom, connecting thread 1/2" NPT	52 mm	555703	VABF-S2-2-A1G2-N12
Supply plate					
	L	With exhaust plate, 3/5 common, 1⁄2" NPT		539233	VABF-S6-10-P1A7-N12
	К	With exhaust port cover, 3/5 separated, 1/2" NPT		539232	VABF-S6-10-P1A6-N12
/ertical supply pla	ate				
< 1	ZU	Connecting thread 1/8" NPT	18 mm	540174	VABF-S4-2-P1A3-N18
		Connecting thread 1/4 " NPT	26 mm	540172	VABF-S4-1-P1A3-N14
		Connecting thread 3/s" NPT	42 mm	546094	VABF-S2-1-P1A3-N38
		Connecting thread 1/2" NPT	52 mm	555787	VABF-S2-2-P1A3-N12

Ordering data							
Designation	Code	Description	Width	Part No.	Туре		
Regulator plate, width	Regulator plate, width 18 mm						
.®	ZA	For port 1, 0.510 bar	18 mm	540153	VABF-S4-2-R1C2-C-10		
	ZF	For port 1, 0.56 bar	18 mm	540151	VABF-S4-2-R1C2-C-6		
	ZC	For port 2, 210 bar	18 mm	540161	VABF-S4-2-R2C2-C-10		
	ZH	For port 2, 26 bar	18 mm	540159	VABF-S4-2-R2C2-C-6		
	ZB	For port 4, 210 bar	18 mm	540157	VABF-S4-2-R3C2-C-10		
	ZG	For port 4, 26 bar	18 mm	540155	VABF-S4-2-R3C2-C-6		
	ZD	For ports 2 and 4, 210 bar	18 mm	540165	VABF-S4-2-R4C2-C-10		
	ZI	For ports 2 and 4, 26 bar	18 mm	540163	VABF-S4-2-R4C2-C-6		
	ZE	For ports 2 and 4, reversible, 0.510 bar	18 mm	540169	VABF-S4-2-R5C2-C-10		
	ZJ	For ports 2 and 4, reversible, 0.56 bar	18 mm	540167	VABF-S4-2-R5C2-C-6		
	ZL	For port 2, reversible, 0.510 bar	18 mm	546252	VABF-S4-2-R6C2-C-10		
	ZN	For port 2, reversible, 0.56 bar	18 mm	546248	VABF-S4-2-R6C2-C-6		
	ZK	For port 4, reversible, 0.510 bar	18 mm	546254	VABF-S4-2-R7C2-C-10		
	ZM	For port 4, reversible, 0.56 bar	18 mm	546250	VABF-S4-2-R7C2-C-6		

Ordering data					
Designation	Code	Description	Width	Part No.	Туре
Regulator plate, w	vidth 26 mm				
Q	ZA	For port 1, 0.510 bar	26 mm	540154	VABF-S4-1-R1C2-C-10
	ZF	For port 1, 0.56 bar	26 mm	540152	VABF-S4-1-R1C2-C-6
	ZC	For port 2, 210 bar	26 mm	540162	VABF-S4-1-R2C2-C-10
	ZH	For port 2, 26 bar	26 mm	540160	VABF-S4-1-R2C2-C-6
	ZB ZB	For port 4, 210 bar	26 mm	540158	VABF-S4-1-R3C2-C-10
	ZG	For port 4, 26 bar	26 mm	540156	VABF-S4-1-R3C2-C-6
	ZD	For ports 2 and 4, 210 bar	26 mm	540166	VABF-S4-1-R4C2-C-10
	ZI	For ports 2 and 4, 26 bar	26 mm	540164	VABF-S4-1-R4C2-C-6
	ZE	For ports 2 and 4, reversible, 0.510 bar	26 mm	540170	VABF-S4-1-R5C2-C-10
	ZJ	For ports 2 and 4, reversible, 0.56 bar	26 mm	540168	VABF-S4-1-R5C2-C-6
	ZL	For port 2, reversible, 0.510 bar	26 mm	546251	VABF-S4-1-R6C2-C-10
	ZN	For port 2, reversible, 0.56 bar	26 mm	546247	VABF-S4-1-R6C2-C-6
	ZK	For port 4, reversible, 0.510 bar	26 mm	546253	VABF-S4-1-R7C2-C-10
	ZM	For port 4, reversible, 0.56 bar	26 mm	546249	VABF-S4-1-R7C2-C-6

Ordering data					
Designation	Code	Description	Width	Part No.	Туре
Regulator plate, widt	h 42 mm				
Q	ZA	For port 1, 0.510 bar	42 mm	546084	VABF-S2-1-R1C2-C-10
	ZF	For port 1, 0.56 bar	42 mm	546083	VABF-S2-1-R1C2-C-6
	ZC	For port 2, 0.510 bar	42 mm	546088	VABF-S2-1-R2C2-C-10
	ZH	For port 2, 0.56 bar	42 mm	546087	VABF-S2-1-R2C2-C-6
	ZB	For port 4, 0.510 bar	42 mm	546086	VABF-S2-1-R3C2-C-10
	ZG	For port 4, 0.56 bar	42 mm	546085	VABF-S2-1-R3C2-C-6
	ZD	For ports 2 and 4, 0.510 bar	42 mm	546090	VABF-S2-1-R4C2-C-10
	ZI	For ports 2 and 4, 0.56 bar	42 mm	546089	VABF-S2-1-R4C2-C-6
	ZE	For ports 2 and 4, reversible, 0.510 bar	42 mm	546092	VABF-S2-1-R5C2-C-10
	ZJ	For ports 2 and 4, reversible, 0.56 bar	42 mm	546091	VABF-S2-1-R5C2-C-6
	ZL	For port 2, reversible, 0.510 bar	42 mm	546832	VABF-S2-1-R6C2-C-10
	ZN	For port 2, reversible, 0.56 bar	42 mm	546831	VABF-S2-1-R6C2-C-6
	ZK	For port 4, reversible, 0.510 bar	42 mm	546834	VABF-S2-1-R7C2-C-10
	ZM	For port 4, reversible, 0.56 bar	42 mm	546833	VABF-S2-1-R7C2-C-6

Ordering data					
Designation	Code	Description	Width	Part No.	Туре
Regulator plate, wi	dth 52 mm				
_0	ZA	For port 1, 0.510 bar	52 mm	555772	VABF-S2-2-R1C2-C-10
	ZF	For port 1, 0.56 bar	52 mm	555771	VABF-S2-2-R1C2-C-6
	ZC	For port 2, 0.510 bar	52 mm	555774	VABF-S2-2-R2C2-C-10
	ZH	For port 2, 0.56 bar	52 mm	555773	VABF-S2-2-R2C2-C-6
	ZB ZB	For port 4, 0.510 bar	52 mm	555776	VABF-S2-2-R3C2-C-10
	ZG	For port 4, 0.56 bar	52 mm	555775	VABF-S2-2-R3C2-C-6
	ZD	For ports 2 and 4, 0.510 bar	52 mm	555778	VABF-S2-2-R4C2-C-10
	ZI	For ports 2 and 4, 0.56 bar	52 mm	555777	VABF-S2-2-R4C2-C-6
	ZE	For ports 2 and 4, reversible, 0.510 bar	52 mm	555780	VABF-S2-2-R5C2-C-10
	ZJ	For ports 2 and 4, reversible, 0.56 bar	52 mm	555779	VABF-S2-2-R5C2-C-6
	ZL	For port 2, reversible, 0.510 bar	52 mm	555782	VABF-S2-2-R6C2-C-10
	ZN	For port 2, reversible, 0.56 bar	52 mm	555781	VABF-S2-2-R6C2-C-6
	ZK	For port 4, reversible, 0.510 bar	52 mm	555784	VABF-S2-2-R7C2-C-10
	ZM	For port 4, reversible, 0.56 bar	52 mm	555783	VABF-S2-2-R7C2-C-6

FESTO

Ordering data									
Designation	Code	Description	Width	Part No.	Туре				
Regulator plate for syr	Regulator plate for symmetrical valves, width 18 mm								
<u>\$</u>	ZAY	For port 1, 0.510 bar	18 mm	560756	VABF-S4-2-R1C2-C-10-E				
	ZFY	For port 1, 0.56 bar	18 mm	560758	VABF-S4-2-R1C2-C-6-E				
	ZCY	For port 2, 210 bar	18 mm	560763	VABF-S4-2-R2C2-C-10-E				
	ZHY	For port 2, 26 bar	18 mm	560765	VABF-S4-2-R2C2-C-6-E				
	ZDY	For ports 2 and 4, 210 bar	18 mm	560767	VABF-S4-2-R4C2-C-10-E				
	ZIY	For ports 2 and 4, 26 bar	18 mm	560769	VABF-S4-2-R4C2-C-6-E				
	ZEY	For ports 2 and 4, reversible, 0.510 bar	18 mm	560771	VABF-S4-2-R5C2-C-10-E				
	ZJY	For ports 2 and 4, reversible, 0.56 bar	18 mm	560773	VABF-S4-2-R5C2-C-6-E				
	ZLY	For port 2, reversible, 0.510 bar	18 mm	560775	VABF-S4-2-R6C2-C-10-E				
	ZNY	For port 2, reversible, 0.56 bar	18 mm	560777	VABF-S4-2-R6C2-C-6-E				

Ordering data	Ordering data								
Designation	Code	Description	Width	Part No.	Туре				
Regulator plate for syn	nmetrical	valves, width 26 mm							
<u>_</u>	ZAY	For port 1, 0.510 bar	26 mm	560757	VABF-S4-1-R1C2-C-10-E				
	ZFY	For port 1, 0.56 bar	26 mm	549876	VABF-S4-1-R1C2-C-6-E				
	ZCY	For port 2, 210 bar	26 mm	560764	VABF-S4-1-R2C2-C-10-E				
	ZHY	For port 2, 26 bar	26 mm	560766	VABF-S4-1-R2C2-C-6-E				
	ZDY	For ports 2 and 4, 210 bar	26 mm	560768	VABF-S4-1-R4C2-C-10-E				
	ZIY	For ports 2 and 4, 26 bar	26 mm	560770	VABF-S4-1-R4C2-C-6-E				
	ZEY	For ports 2 and 4, reversible, 0.510 bar	26 mm	560772	VABF-S4-1-R5C2-C-10-E				
	ZJY	For ports 2 and 4, reversible, 0.56 bar	26 mm	560774	VABF-S4-1-R5C2-C-6-E				
	ZLY	For port 2, reversible, 0.510 bar	26 mm	560776	VABF-S4-1-R6C2-C-10-E				
	ZNY	For port 2, reversible, 0.56 bar	26 mm	560778	VABF-S4-1-R6C2-C-6-E				

Ordering data					
Designation	Code	Description	Width	Part No.	Туре
Regulator plate for	r symmetrica	l valves, width 42 mm ¹⁾			
Q	ZAY	For port 1, 0.510 bar	42 mm		VABF-S2-1-R1C2-C-10-E
	ZFY	For port 1, 0.56 bar	42 mm		VABF-S2-1-R1C2-C-6-E
	ZCY	For port 2, 0.510 bar	42 mm		VABF-S2-1-R2C2-C-10-E
	ZHY	For port 2, 0.56 bar	42 mm		VABF-S2-1-R2C2-C-6-E
	ZBY	For port 4, 0.510 bar	42 mm		VABF-S2-1-R3C2-C-10-E
	ZGY	For port 4, 0.56 bar	42 mm		VABF-S2-1-R3C2-C-6-E
	ZDY	For ports 2 and 4, 0.510 bar	42 mm		VABF-S2-1-R4C2-C-10-E
	ZIY	For ports 2 and 4, 0.56 bar	42 mm		VABF-S2-1-R4C2-C-6-E
	ZEY	For ports 2 and 4, reversible, 0.510 bar	42 mm		VABF-S2-1-R5C2-C-10-E
	ZJY	For ports 2 and 4, reversible, 0.56 bar	42 mm		VABF-S2-1-R5C2-C-6-E
	ZLY	For port 2, reversible, 0.510 bar	42 mm		VABF-S2-1-R6C2-C-10-E
	ZNY	For port 2, reversible, 0.56 bar	42 mm		VABF-S2-1-R6C2-C-6-E
	ZKY	For port 4, reversible, 0.510 bar	42 mm		VABF-S2-1-R7C2-C-10-E
	ZMY	For port 4, reversible, 0.56 bar	42 mm		VABF-S2-1-R7C2-C-6-E

1) These functions are available via the pressure regulator configurator VABF-S2 for width 42 mm and 52 mm (ISO 5599-2, ISO 1 and ISO 2) only.

FESTO

Ordering data				
Designation	Code	Description	Width Pa	art No. Type
Regulator plate for	r symmetrica	l valves, width 52 mm ¹⁾		
- -	ZAY	For port 1, 0.510 bar	52 mm	VABF-S2-2-R1C2-C-10-E
	ZFY	For port 1, 0.56 bar	52 mm	VABF-S2-2-R1C2-C-6-E
C	ZCY	For port 2, 210 bar	52 mm	VABF-S2-2-R2C2-C-10-E
	ZHY	For port 2, 26 bar	52 mm	VABF-S2-2-R2C2-C-6-E
The state	SE ZBY	For port 4, 210 bar	52 mm	VABF-S2-2-R3C2-C-10-E
	ZGY	For port 4, 26 bar	52 mm	VABF-S2-2-R3C2-C-6-E
	ZDY	For ports 2 and 4, 210 bar	52 mm	VABF-S2-2-R4C2-C-10-E
	ZIY	For ports 2 and 4, 26 bar	52 mm	VABF-S2-2-R4C2-C-6-E
	ZEY	For ports 2 and 4, reversible, 0.510 bar	52 mm	VABF-S2-2-R5C2-C-10-E
	ZJY	For ports 2 and 4, reversible, 0.56 bar	52 mm	VABF-S2-2-R5C2-C-6-E
	ZLY	For port 2, reversible, 0.510 bar	52 mm	VABF-S2-2-R6C2-C-10-E
	ZNY	For port 2, reversible, 0.56 bar	52 mm	VABF-S2-2-R6C2-C-6-E
	ZKY	For port 4, reversible, 0.510 bar	52 mm	VABF-S2-2-R7C2-C-10-E
	ZMY	For port 4, reversible, 0.56 bar	52 mm	VABF-S2-2-R7C2-C-6-E

1) These functions are available via the pressure regulator configurator VABF-S2 for width 42 mm and 52 mm (ISO 5599-2, ISO 1 and ISO 2) only.

esignation	Code	Description	Width	Part No.	Туре
Pressure gauge					
	Т	With cartridge connection for regulator, 10 bar,	18 mm	543487	PAGN-26-16-P10
		scale bar/psi,	26 mm		
		display range 016 bar/0240 psi,	42 mm	548010	PAGN-40-16-P10
		for regulator plate code ZA, ZB, ZC, ZD, ZE, ZK, ZL	52 mm		
	U	With cartridge connection for regulator, 6 bar,	18 mm	543488	PAGN-26-10-P10
		scale bar/psi,	26 mm		
		display range 010 bar/0145 psi,	42 mm	548009	PAGN-40-10-P10
		for regulator plate code ZF, ZG, ZH, ZI, ZJ, ZM, ZN	52 mm		
	TM	With cartridge connection for regulator, 10 bar,	18 mm	563735	PAGN-26-1.6M-P10
		scale MPa,	26 mm		
		display range 016 bar/01.6 MPa,	42 mm	563737	PAGN-40-1.6M-P10
		for regulator plate code ZA, ZB, ZC, ZD, ZE, ZK, ZL	52 mm		
	UM	With cartridge connection for regulator, 6 bar,	18 mm	563736	PAGN-26-1M-P10
		scale MPa,	26 mm		
		display range 016 bar/01 MPa,	42 mm	563738	PAGN-40-1M-P10
		for regulator plate code ZF, ZG, ZH, ZI, ZJ, ZM, ZN	52 mm		
	TP	With cartridge connection for regulator, 10 bar,	18 mm	563731	PAGN-26-232P-P10
		scale psi/bar,	26 mm		
		display range 016 bar/0232 psi,	42 mm	563733	PAGN-40-232P-P10
		for regulator plate code ZA, ZB, ZC, ZD, ZE, ZK, ZL	52 mm		
	UP	With cartridge connection for regulator, 6 bar,	18 mm	563732	PAGN-26-145P-P10
		scale psi/bar,	26 mm		
		display range 010 bar/0145 psi,	42 mm	563734	PAGN-40-145P-P10
		for regulator plate code ZF, ZG, ZH, ZI, ZJ, ZM, ZN	52 mm		

Ordering data					
Designation	Code	Description	Width	Part No.	Туре
Cartridge for regulato	r plate	·		<u> </u>	
OD)	-	For tubing O.D. 4 mm		172972	QSP10-4
Adapter					
	-	Adapter for pressure gauge		565811	QSP10-G ¹ /8
Flow control plate	X	Controls the flow of exhaust air downstream of the valve to ducts	18 mm	540176	VABF-S4-2-F1B1-C
	^	3 and 5	10 11111	540170	
			26 mm	540175	VABF-S4-1-F1B1-C
			42 mm	546095	VABF-S2-1-F1B1-C
			52 mm	555789	VABF-S2-2-F1B1-C
Vertical pressure shut					
	ZT		18 mm	542884	VABF-S4-2-L1D1-C
		position	26 mm	542885	VABF-S4-1-L1D1-C
			42 mm	546096	VABF-S2-1-L1D1-C
			52 mm	555791	VABF-S2-2-L1D1-C
Cover					
	ΙL.	Blanking plate for vacant position	18 mm	539213	VABB-S4-2-WT
			26 mm	539212	VABB-S4-1-WT
			42 mm	543186	VABB-S2-1-WT
			52 mm	560845	VABB-S2-2-WT
P	N	Cover cap for manual override, non-detenting	10 pieces	541010	VAMC-S6-CH
P	V	Cover cap for manual override, covered	10 pieces	541011	VAMC-S6-CS
	-	End cap for electrical interlinking module	10 pieces	547713	VABD-S4-E-C
<u> </u>		(with individual connection), size 18 mm and 26 mm			
	-	Seal (with individual connection), size 42 mm and 52 mm	2 pieces	571343	VABD-S2-1-S-C

Ordering data				
Designation	Code	Description	Part No.	Туре
Multi-pin node				
	Т	Terminal strip, 36-pin	543412	VABE-S6-1LF-C-M1-C36M
	MP1	Sub-D plug, 37-pin	543414	VABE-S6-1LT-C-M1-S37
	MP4	Round plug, 19-pin	543415	VABE-S6-1LF-C-M1-R19
ndividual electrica	al connectior	1		
	-MP2	Multi-pin node with individual connection M12, 6-way	549046	VABE-S6-LT-C-S6-R5
0	-MP3	Multi-pin node with individual connection M12, 10-way	549047	VABE-S6-LT-C-S10-R5
	-	Cover for individual connection M12, 6-way	549048	VAEM-S6-C-S6-R5
	-	Cover for individual connection M12, 10-way	549049	VAEM-S6-C-S10-R5
Pneumatic interfac	ce			
	-	For electrical terminal CPX in plastic design	543416	VABA-S6-1-X1
	-	For electrical terminal CPX in metal design	550663	VABA-S6-1-X2

Ordering data					
Designation	Code	Description		Part No.	Туре
Electrical connection	for AS-int	erface			
. 🔊	-	4 inputs/4 outputs		549042	VABE-S6-1LF-C-A4-E
	-	8 inputs/8 outputs		549043	VABE-S6-1LF-C-A8-E
AS-interface module					
	1-	4 inputs/4 outputs		549044	VAEM-S6-S-FAS-4-4E
				545044	
	-	8 inputs/8 outputs		549045	VAEM-S6-S-FAS-8-8E
				545045	VALM-50-5-TAS-0-0L
Manifold block for AS	interface				
	X	4x M12, 5-pin, double, socket		195704	CPX-AB-4-M12x2-5POL
	GW	4x M12, 5-pin, socket, metal thread		541254	CPX-AB-4-M12x2-5POL-R
	R	8x M8, 3-pin, socket		195706	CPX-AB-8-M8-3POL
	1	8x spring-loaded terminal, Cage Clamp®, 4-pin		195708	CPX-AB-8-KL-4POL
₹.	H	4x Harax [®] , 4-pin, socket		525636	CPX-AB-4-HAR-4POL
	В	Sub-D, 25-pin, socket		525676	CPX-AB-1-SUB-BU-25POL
Connecting cable wit	h Sub-D p	lug socket			
	Polyure	thane, IP65			
	GA	Connecting cable for max. 8 solenoid coils, 10-pin	2.5 m	539240	NEBV-S1W37-E-2,5-LE10
	GB		5 m	539241	NEBV-S1W37-E-5-LE10
	GC		10 m	539242	NEBV-S1W37-E-10-LE10
	GD	Connecting cable for max. 22 solenoid coils, 26-pin	2.5 m	539243	NEBV-S1W37-E-2,5-LE26
	GE		5 m	539244	NEBV-S1W37-E-5-LE26
0	GF		10 m	539245	NEBV-S1W37-E-10-LE26
	GG	Connecting cable for max. 32 solenoid coils, 37-pin	2.5 m	539246	NEBV-S1W37-K-2,5-LE37
	GH		5 m	539247	NEBV-S1W37-K-5-LE37
	GI		10 m	539248	NEBV-S1W37-K-10-LE37
	Polyvin	yl chloride, IP65			
	GK	Connecting cable for max. 8 solenoid coils, 10-pin,	2.5 m	543271	NEBV-S1W37-KM-2,5-LE10
	GL	cable properties (standard)	5 m	543272	NEBV-S1W37-KM-5-LE10
	GM		10 m	543273	NEBV-S1W37-KM-10-LE10
	GN	Connecting cable for max. 22 solenoid coils, 27-pin,	2.5 m	543274	NEBV-S1W37-KM-2,5-LE27
	GO	cable properties (standard)	5 m	543275	NEBV-S1W37-KM-5-LE27
	GP		10 m	543276	NEBV-S1W37-KM-10-LE27
	GQ	Connecting cable for max. 32 solenoid coils, 37-pin,	2.5 m	543277	NEBV-S1W37-KM-2,5-LE37
	GR	cable properties (standard)	5 m	543278	NEBV-S1W37-KM-5-LE37
	GS		10 m	543279	NEBV-S1W37-KM-10-LE37
Cover for multi-pin pl	ug				
()	-	For user configuration		545974	NECV-S1W37

rdering data					
esignation	Code	Description		Part No.	Туре
scription label l	holder/inscrip				
\searrow	В	Clip-on inscription label holder for valve cap	5 pieces	540888	ASCF-T-S6
*	Т	Inscription label holder for manifold blocks	5 pieces	540889	ASCF-M-S6
\checkmark	TD	Inscription label holder for manifold blocks, size 52 mm	5 pieces	562577	ASCF-M-S2-2
	-	Inscription label (20 labels in frames)	20 pieces	18182	IBS-9x20
-rail mounting					
		VTSA/VTSA-F with fieldbus	3 pieces	526032	CPX-CPA-BG-NRH
<u> </u>	-	VTSA/VTSA-F with multi-pin plug	2 pieces	173498	CPA-BG-NRH
Vall mounting					
	U	Mounting bracket	5 pieces	539214	VAME-S6-10-W
<u> </u>	-	Mounting bracket		567038	VAME-S6-W-M46
Nanual					
	D	Manual for valve terminal VTSA/VTSA-F	German	538922	P.BE-VTSA-44-DE
	≥ E	-	English	538923	P.BE-VTSA-44-EN
	S		Spanish	538924	P.BE-VTSA-44-ES
\checkmark	F		French	538925	P.BE-VTSA-44-FR
	1		Italian	538926	P.BE-VTSA-44-IT
	V		Swedish	538927	P.BE-VTSA-44-SV
Pneumatic conne	ction accord	rioc			
		blanking plugs, silencers and			
		an be found in the chapter Accessories \rightarrow page 134			
		idual search terms:			
Internet 🗲 conne	ection techno	logy, silencer, blanking plug			

FESTO

Valve terminals type 44/45, VTSA/VTSA-F, NPT

Solenoid valve with switching position sensing



ISO valves with switching position sensing for safety-oriented pneumatic components

Function

The single solenoid 5/2-way valve with spring return in width 26 mm features valve diagnostics. Designed as plug-in or individual connection valve with pilot valves to ISO 15218 and square plug type C. The normal position of the piston spool valve is monitored by the inductive sensor.

This valve is not a safety component in accordance with the Machinery Directive 2006/42/EC. For use in higher categories, the sensor signal from the valve must be evaluated by the control system. This valve is suitable for use in safety-related parts of control systems to EN ISO 13849-1. This valve is designed for installation in machines or automated systems and must only be used in industrial applications (high-demand mode).

Decentralised individual connection variant



Valve on individual sub-base (square plug or plug-in), with integrated piston position sensing.

The electrical connection is established either via a standardised 4-pin M12 plug 24 V DC (ISO 15407-2), 4-pin spring-loaded terminal or a cable (open end) 24 V DC/110 V AC, which are configured by the user. The individual sub-base can be supplied with internal or external pilot air depending on the version.

Variant for valve terminal VTSA



The valves with integrated piston position sensing in plug-in design for valve terminal VTSA can be used regardless of the type of electrical actuation (individual, multi-pin plug or fieldbus/control block connection).

Pilot air supply:

The valve terminal can be supplied with internal or external pilot air via the various end plate variants.

- Note

Valves in plug-in design always get their pilot air from duct 14 in the manifold sub-base.

1) The circuit symbol represents a valve with a proximity sensor with switching output signal with an N/O contact. In accordance with ISO 1219-1, this symbol applies to both N/O contacts as well as N/C contacts. The switching element function of the sensors used here is designed as an N/C contact.

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Solenoid valve with switching position sensing

General technical data			
Valve		VSVA-B-M52-MZD-A1-1T1L on valve terminal	VSVA-B-M52-MZ-A1-1C1
Width		26 mm	
Design		Piston spool valve	
Sealing principle		Soft	
Actuation type		Electrical	
Type of control		Piloted	
Exhaust function, with flow	w control	Via individual sub-base, via flow control plate	
Lubrication		Lubricated for life	
Type of mounting		Via through-hole, on manifold sub-base	
Mounting position		Any	
Manual override		Covered	
Individual sub-base			
Pneumatic connection		NPT thread	Fitting
Supply port	1	1/4" NPT	QS-1/4-3/8
			QS-1/4-5/16-U
Exhaust port	3/5	1/4" NPT	QS-1/4-3/8
			QS-1/4-5/16-U
Working lines	2/4	1/4" NPT	QS-1/4-3/8
			QS-1/4-5/16-U
Pilot air supply port	14	1⁄8" NPT	QS-1/8-5/16-U
			QS-1/8-1/4-U
Pilot exhaust air port	12	1/8" NPT ¹⁾	QS-1/8-5/16-U
			QS-1/8-1/4-U
Valve terminal			→58
valve terminal			738

Pilot exhaust air port 12 vents directly at the valve, without a connection. Note: if the customer requests a "turned seal", exhaust air is vented at the end plates of the valve terminal, which does not conform to the ISO standard.

Standard nominal flow rate [l/min]				
Valve	VSVA-B-M52-MZD-A1-1T1L on valve terminal	VSVA-B-M52-MZ-A1-1C1		
Width	26 mm			
Flow rate of valve on individual sub-base	-	1,100		
Flow rate of valve on valve terminal	1,100	-		

Operating and environmental	Operating and environmental conditions			
Valves and manifold sub-base				
Width		26 mm		
Operating medium		Filtered compressed air, lubricated or unlubricated		
Grade of filtration	[µm]	40 (average pore size)		
Operating pressure	[bar]	-0.9 10		
Operating pressure for valve	[bar]	310		
terminal with internal pilot air				
supply				
Pilot pressure	[bar]	310		
Ambient temperature	[°C]	-5 +50		
Temperature of medium	[°C]	-5 +50		
Storage temperature ¹⁾	[°C]	-20 +40		
Relative air humidity	[%]	90		
Note on materials		Contains PWIS (paint-wetting impairment substances), RoHS-compliant		

·O· New

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Solenoid valve with switching position sensing

Valve switching times [ms]					
Valve		VSVA-B-M52-MZD-A1-1T1L on valve terminal	VSVA-B-M52-MZ-A1-1C1		
Width		26 mm			
Switching times	On	20	21		
Switching times	Off	54	41		

Electrical data – Valve			
Valve		VSVA-B-M52-MZD-A1-1T1L on valve terminal	VSVA-B-M52-MZ-A1-1C1
Width		26 mm	
Electrical connection		4-pin plug to ISO 15407-2	Plug to DIN EN 175301-803, type C, without protective
			earth conductor
Nominal operating voltage	[V DC]	24	
Permissible voltage	[%]	±10	-15/+10
fluctuations			
Surge capacity	[kV]	2.5	· ·
Degree of contamination		3	
Power consumption	[W]	1.6 W	1.8 W
Piston position sensing		Normal position via sensor	· ·
Duty cycle	[%]	100	
Protection class to DIN EN 605	29	IP65, NEMA 4	

Electrical data – Sensor		
Electrical connection		Cable, 3-wire
		Plug M8x1, 3-pin
Cable length	[m]	2.5
Switching output		PNP or NPN
Switching element function		N/C contact
Switching status display		Yellow LED
Operating voltage range	[V DC]	10 30
Residual ripple	[%]	±10
Sensor idle current	[mA]	<=10
Max. output current	[mA]	200
Voltage drop	[V]	<=2
Max. switching frequency	[Hz]	5,000
Protection against short circuit		Pulsed
Protection against polarity reve	rsal	For all electrical connections
for sensor		
Measuring principle		Inductive
Piston position sensing		Valve normal position via sensor

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Solenoid valve with switching position sensing

Materials			
Width	26 mm		
Sub-base/manifold sub-base	Die-cast aluminium		
Valve	Die-cast aluminium, reinforced polyamide		
Seals	Nitrile rubber, elastomer (support made of steel)		
Screws	Galvanised steel		
Sensor housing	High-alloy stainless steel		
Sensor cable sheath	Polyurethane		

Product weight	
Approx. weight [g]	
Width	26 mm
5/2-way valve type	
VSVA-B-M52-MZD-A1-1T1L-APC	307
VSVA-B-M52-MZD-A1-1T1L-APP	264
VSVA-B-M52-MZ-A1-1C1-APC	332
VSVA-B-M52-MZ-A1-1C1-APP	289
VSVA-B-M52-MZD-A1-1T1L-ANC	307
VSVA-B-M52-MZD-A1-1T1L-ANP	264
VSVA-B-M52-MZ-A1-1C1-ANC	332
VSVA-B-M52-MZ-A1-1C1-ANP	289
VSVA-B-M52-MZD-A1-1T1L-APX-0,5	281
Individual sub-base	302

Valve terminals type 44/45, VTSA/VTSA-F, NPT

Ordering data - Solenoid valve with switching position sensing

Ordering data Valve function Width Designation Code Part No. Туре Solenoid valves, 24 V DC, plug-in design for valve terminal VTSA 5/2-way valve, single solenoid, mechanical spring return, with 26 mm 560723 VSVA-B-M52-MZD-A1-1T1L-APC switching position sensing via inductive sensor with PNP output and cable, 3-wire, 2.5 m 5/2-way valve, single solenoid, mechanical spring return, with 26 mm 560742 VSVA-B-M52-MZD-A1-1T1L-ANC switching position sensing via inductive sensor with NPN output and cable, 3-wire, 2.5 m S0 5/2-way valve, single solenoid, mechanical spring return, with 26 mm 560724 VSVA-B-M52-MZD-A1-1T1L-APP switching position sensing via inductive sensor with PNP output and 3-pin sensor push-in connector M8x1 S0 5/2-way valve, single solenoid, mechanical spring return, with 26 mm 560743 VSVA-B-M52-MZD-A1-1T1L-ANP switching position sensing via inductive sensor with NPN output and 3-pin sensor push-in connector M8x1 VSVA-B-M52-MZD-A1-1T1L-APX-0.5 570850 5/2-way valve, single solenoid, mechanical spring return, with 26 mm switching position sensing via inductive sensor with PNP output and 0.5 m cable with 3-pin sensor push-in connector M12x1 Solenoid valves, 24 V DC, with pneumatic interface to ISO 15218 for individual sub-base 5/2-way valve, single solenoid, mechanical spring return, with 26 mm 560725 VSVA-B-M52-MZ-A1-1C1-APC switching position sensing via inductive sensor with PNP output and cable, 3-wire 5/2-way valve, single solenoid, mechanical spring return, with 26 mm 560744 VSVA-B-M52-MZ-A1-1C1-ANC switching position sensing via inductive sensor with NPN output and cable, 3-wire 5/2-way valve, single solenoid, mechanical spring return, with 26 mm 560726 VSVA-B-M52-MZ-A1-1C1-APP switching position sensing via inductive sensor with PNP output and 3-pin sensor push-in connector M8 5/2-way valve, single solenoid, mechanical spring return, with 26 mm 560745 VSVA-B-M52-MZ-A1-1C1-ANP switching position sensing via inductive sensor with NPN output and 3-pin sensor push-in connector M8

- Note

The sensors contained in the valves must not be replaced. Incorrect assembly can result in malfunctions or damage to the valve. Return the module to Festo for maintenance in the event of a fault.

Valves with switching position sensing from the VSVA-B-M52 -...series can only be ordered individually. If these are used on a valve terminal, appropriate vacant positions must be provided for them.

Exceptions are the two valves with ident. code SO and SQ.

2011/02 - Subject to change

Valve terminals type 44/45, VTSA/VTSA-F, NPT

Accessories - Solenoid valve with switching position sensing

Ordering data Width Designation Code Description Part No. Type Individual sub-base Individual sub-base, port pattern to ISO 15407-2, electrical connection via cable terminals Threaded connection, internal pilot air supply, 541066 VABS-S4-1S-N14-B-K2 26 mm lateral connections, 1/4 " NPT Threaded connection, external pilot air supply, 539726 VABS-S4-1S-N14-K2 26 mm lateral connections, 1/4 " NPT Plug socket for electrical connection of individual valves Angled socket, 3-pin, screw terminal, cable connector PG7 151687 MSSD-EB Angled socket, 3-pin, screw terminal, cable connector M12 539712 MSSD-EB-M12 Connecting cable for electrical connection of individual valves KMEB-1-24-2,5-LED Angled socket, 3-pin, cable length 2.5 m 151688 Angled socket, 3-pin, cable length 5 m KMEB-1-24-5-LED 151589 Angled socket, 3-pin, cable length 10 m 193457 KMEB-1-24-10-LED Angled socket, 4-pin, cable length 2.5 m 174844 KMEB-2-24-2,5-LED 174845 KMEB-2-24-5-LED Angled socket, 4-pin, cable length 5 m Connecting cable for electrical connection of sensors for switching position sensing Straight socket, 3-pin, M8 plug, cable length 2.5 m 541333 NEBU-M8G3-K-2,5-LE3 NEBU-M8G3-K-5-LE3 Straight socket, 3-pin, M8 plug, cable length 5 m 541334 Angled socket, 3-pin, M8 plug, cable length 2.55 m NEBU-M8-W3-K-2,5-LE3 541338 Angled socket, 3-pin, M8 plug, cable length 5 m 541341 NEBU-M8W3-K-5-LE3 554037 NEBU-M8G3-K-2,5-M8G4 Straight socket, straight plug, 3-pin, M8 plug, cable length 2.5 m NEBU-... Modular system for connecting cables → Internet: nebu Illuminating seal for plug pattern DIN EN 175301-803, type C Technical data → Internet: meb-ld 12 ... 24 V DC 151717 MEB-LD-12-24DC 230 V AC MEB-LD-230AC 151718 Pneumatic connection accessories A selection of possible fittings, blanking plugs, silencers and other pneumatic accessories can be found in the chapter Accessories → page 134 or on the Internet via the individual search terms: **Internet →** connection technology, silencer, blanking plug

FESTO

Valve terminals type 44/45, VTSA/VTSA-F, NPT

Control block with safety function - Width 26 mm



Description

The control block is designed for two-channel actuation of pneumatic drive components such as double-acting linear cylinders, for example, and can be used to realise the following protective measures:

- Protection against unexpected start-up (EN 1037)
- Reversing hazardous movements, provided the reversing motion will not result in further hazards

The control attributes of the control block enable a performance level e to be achieved for the safety measures. The control block has been developed and manufactured in accordance with the basic and proven safety principles of EN ISO 13849–2.

The requirements of EN ISO 13849 (e.g. CCF, DC) must be taken into consideration for use in higher categories (2 to 4). The basic safety principles of EN ISO 13849–2 relating to implementation and operation of the component must be satisfied. For category 2 to 4, the proven safety principles to EN ISO 13849–2 for implementation and operation of the component must be satisfied. When using this product in machines or systems subject to specific C standards, the requirements specified in these standards must be observed. The control block with safety function is designed for installation in machines and automation systems and must only be used in industrial applications (high-demand mode). The control block with safety function is suitable for use as a press safety valve to EN 962.

More information and technical data → Internet: manual

The valves with integrated piston position sensing on manifold sub-base for valve terminal VTSA must be supplied with electrical power regardless of the type of electrical actuation (individual, multi-pin plug or fieldbus/control block connection). The electrical connection for the solenoid valves is established separately via a standardised square plug to DIN EN 175301–803, type C. The piston position sensing feature of

the inductive PNP or NPN proximity sensor is realised using a push-in connector in the size M8x1 to EN 61076-2-104.

 The circuit symbol represents a valve with a proximity sensor with switching output signal with an N/O contact. In accordance with ISO 1219-1, this symbol applies to both N/O contacts as well as N/C contacts. The switching element function of the sensors used here is designed as an N/C contact.

Vertical stacking variant for valve terminal VTSA, width 26 mm

Valve terminals type 44/45, VTSA/VTSA-F, NPT

Technical data – Control block with safety function – Width 26 mm

Function – Pneumatic/electrical interlinking

Vertical stacking variant (on valve terminal)



The safety function is achieved through two-channel pneumatic interlinking of two single solenoid 5/2-way directional control valves within the control block: port (4) is only fed with compressed air if both solenoid valves are switched to switching position (14). Port (2) is always fed with compressed air if at least one of the two solenoid valves is in normal position. The valve is reset via a mechanical spring. The switching operation of the solenoid valves can be monitored by sensing the proximity sensors at the solenoid valves. This is done by linking the control signal and signal change of the proximity sensor so that it is possible to check whether the piston spools of the solenoid valves are reaching or leaving the normal position (expectations).

The piston spools of the solenoid valves are designed so that pneumatic short circuits between the ports (2) and (4) are ruled out (freedom from overlap).

FESTO

To achieve the required category, the two solenoid valves must be actuated via two separate channels.

General technical data				
Control block		VOFA-B26-T52-M-1C1 on valve terminal		
Width		53 mm		
Design		Piston spool valve		
Sealing principle		Soft		
Actuation type		Electrical		
Type of control		Piloted		
Pilot air supply		Internal/external via valve terminal		
Type of mounting		Via through-hole, on manifold sub-base		
Mounting position		Any		
Manual override		Covered		
Valve switching status d	lisplay	Via accessories		
Pneumatic connections		VOFA-B26-T52-M-1C1 on valve terminal		
-		Connection with NPT thread	Fitting	
Supply port	1	Via the manifold sub-base of the valve terminal		
Exhaust port	3/5	Via the manifold sub-base of the valve terminal		
Working lines	2/4	1/4" NPT	QS-1/4-3/8	
			QS-1/4-5/16-U	
Pilot air supply port	14	Via the manifold sub-base of the valve terminal		
Pressure gauge		G1⁄4		

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Control block with safety function – Width 26 mm

Standard nominal flow rate [l/min]	
Control block	VOFA-B26-T52-M-1C1 on valve terminal
Width	53 mm
Flow rate of valve on valve terminal	830

Operating and environmenta	l conditions	i de la constante de la constan
Control block		VOFA-B26-T52-M-1C1 on valve terminal
Width		53 mm
Operating medium		Filtered compressed air, lubricated or unlubricated ¹⁾
Grade of filtration	[µm]	40 (average pore size)
Operating pressure	[bar]	010
Operating pressure for valve	[bar]	3 10
terminal with internal pilot		
air supply		
Pilot pressure	[bar]	3 10
Noise level LpA	[dB (A)]	85
Ambient temperature	[°C]	-5 +50
Temperature of medium	[°C]	-5 +50
Fire protection classification t	o UL94	HB
Note on materials		Contains PWIS (paint-wetting impairment substances), RoHS-compliant
Common cause failure (CCF)		Observe operating pressure limits
		Observe pilot pressure limits
		Observe temperature range
		Observe vibration/shock limits
		Compressed air quality according to the technical data, in particular avoidance of flash rust dust (for example caused by
		servicing work) as well as adherence to the residual oil content of max. 0.1 mg/m3 when using ester-containing oils
		(which may, for example, be contained in the compressor oil)
Performance level	[PL]	Cat. 4, PL e safety component
Max. positive test pulse with	[µs]	1,000
0 signal		
Max. negative test pulse	[µs]	800
with 1 signal		

1) The pressure dew point must be at least 10 K lower than the temperature of the medium, since ice would otherwise form in the expanded compressed air.

- 🗍 - Note

With the test pulses, make sure that the maximum pulse length is not exceeded as otherwise the safety function can be impaired.

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Control block with safety function – Width 26 mm

Switching times [ms]		
Control block		VOFA-B26-T52-M-1C1 on valve terminal
Width		53 mm
Valve switching time	On	22
	Off	59
Valve sensor switching	On	60
time ¹⁾	Off	11

1) Valve sensor switching time off: period of time from coil being energised to sensor being switched off when using a PNP sensor. Valve sensor switching time on: period of time from coil being de-energised to 0-L edge at the sensor when using a PNP sensor.

Electrical data – Control block			
Control block		VOFA-B26-T52-M-1C1 on valve terminal	
Width		53 mm	
Electrical connection		Plug to DIN EN 175301-803, type C, without protective earth conductor	
Nominal operating voltage	[V DC]	24	
Permissible voltage	[%]	-15/+10	
fluctuations			
Surge capacity	[kV]	2.5	
Degree of contamination		3	
Power consumption	[W]	1.8 W	
Max. magnetic disruption	[mT]	60	
field			
Piston position sensing		Normal position via sensor	
Duty cycle	[%]	100	
Protection class to DIN EN 60	1529	IP65, NEMA 4 (for all types of signal transmission in assembled state)	
Protection against direct and indirect		PELV (Protective Extra-Low Voltage)	
contact		Protected to EN 60950/IEC 950	

Electrical data – Sensor		
Electrical connection		Cable, 3-wire
		Plug M8x1, 3-pin
Cable length	[m]	2.5
Switching output		PNP or NPN
Switching element function		N/C contact
Switching status display		Yellow LED
Operating voltage range	[V DC]	10 30
Residual ripple	[%]	±10
Sensor idle current	[mA]	<=10
Max. output current	[mA]	200
Voltage drop	[V]	<=2
Max. switching frequency	[Hz]	5,000
Protection against short circ	cuit	Pulsed
Protection against polarity r	eversal	For all electrical connections
for sensor		
Measuring principle		Inductive
Piston position sensing		Valve normal position via sensor

- 🗍 - Note

With a 100% duty cycle, the control block must be de-energised once per week.
Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Control block with safety function – Width 26 mm

Certifications		
Certification	BIA	
CE marking	To EU Machinery Directive	
(see declaration of conformity)		

Materials	
Control block	VOFA-B26-T52-M-1C1 on valve terminal
Width	53 mm
Sub-base/manifold sub-base	Die-cast aluminium
Valve	Die-cast aluminium, reinforced polyamide
Seals	Nitrile rubber, elastomer (support made of steel)
Screws	Galvanised steel
Sensor housing	High-alloy stainless steel
Sensor cable sheath	Polyurethane

Product weight	
Control block	VOFA-B26-T52-M-1C1 on valve terminal
Width	53 mm
Approx. weight [g]	1,112

Valve terminals type 44/45, VTSA/VTSA-F, NPT Ordering data – Control block with safety function – Width 26 mm

FESTO

Ordering data						
Designation	Code	Valve function	Width	Part No.	Туре	
Control block, 24 V DC	Control block, 24 V DC, vertical stacking variant for valve terminal VTSA					
	SP	5/2-way valve, single solenoid, mechanical spring return, with switching position sensing via inductive sensor with PNP output and 3-pin sensor push-in connector M8, mounted on intermediate plate for pneumatic interlinking	53 mm	_ 1)	VOFA-B26-T52-M-1C1-APP	
	SN	5/2-way valve, single solenoid, mechanical spring return, with switching position sensing via inductive sensor with NPN output and 3-pin sensor push-in connector M8, mounted on intermediate plate for pneumatic interlinking	53 mm	_ 1)	VOFA-B26-T52-M-1C1-ANP	

1) The control block with safety function can only be ordered via the valve terminal configurator and therefore does not have a separate part number.

--Note

The sensors contained in the valves must not be replaced. Incorrect assembly can result in malfunctions or damage to the valve. Please contact Festo in the event of a malfunction.

·O· New

Valve terminals type 44/45, VTSA/VTSA-F, NPT Accessories – Control block with safety function – Width 26 mm

Ordering data				
Designation	Code	Description	Part No.	Туре
Plug socket for ele	ctrical conne	ction of individual valves		
	-	Angled socket, 3-pin, screw terminal, cable connector PG7	151687	MSSD-EB
	-	Angled socket, 3-pin, screw terminal, cable connector M12	539712	MSSD-EB-M12
Connecting cable f	for electrical	connection of individual valves		
	-	Angled socket, 3-pin, cable length 2.5 m	151688	KMEB-1-24-2,5-LED
1 I I I	-	Angled socket, 3-pin, cable length 5 m	151589	KMEB-1-24-5-LED
	-	Angled socket, 3-pin, cable length 10 m	193457	KMEB-1-24-10-LED
	-	Angled socket, 4-pin, cable length 2.5 m	174844	KMEB-2-24-2,5-LED
A A A A A A A A A A A A A A A A A A A	-	Angled socket, 4-pin, cable length 5 m	174845	KMEB-2-24-5-LED
Connecting cable f	for electrical	connection of sensors for switching position sensing		
	-	Straight socket, 3-pin, M8 plug, cable length 2.5 m	541333	NEBU-M8G3-K-2,5-LE3
	-	Straight socket, 3-pin, M8 plug, cable length 5 m	541334	NEBU-M8G3-K-5-LE3
	-	Angled socket, 3-pin, M8 plug, cable length 2.55 m	541338	NEBU-M8-W3-K-2,5-LE3
	-	Angled socket, 3-pin, M8 plug, cable length 5 m	541341	NEBU-M8W3-K-5-LE3
a fair of	-	Straight socket, straight plug, 3-pin, M8 plug, cable length 2.5 m	554037	NEBU-M8G3-K-2,5-M8G4
C C C C C C C C C C C C C C C C C C C	-	Modular system for connecting cables	-	NEBU → Internet: nebu
Illuminating seal f	or plug patte	rn DIN EN 175301-803, type C		Technical data → Internet: meb-ld
	-	12 24 V DC	151717	MEB-LD-12-24DC
	-	230 V AC	151718	MEB-LD-230AC
Pneumatic connec			1	
		blanking plugs, silencers and		
		an be found in the chapter Accessories → page 134		
		dual search terms:		
internet → conne	ection technol	logy, silencer, blanking plug		

Valve terminals type 44/45, VTSA/VTSA-F, NPT

- 🔳

Pilot air switching valve – Width 26 mm



Flow rate 450 l/min

- Valve width
 26 mm
- Voltage 24 V DC
 Operating pressure

3 ... 10 bar



Description

The pilot air switching valve is designed to switch pilot air from duct 1 to 14. This valve is not a safety component in accordance with the Machinery Directive 2006/42/EC. For use in higher categories, the sensor signal from the valve must be evaluated by the control system.

This valve is suitable for use in safety-related parts of control systems to EN ISO 13849–1. This valve is designed for installation in machines and automation systems and must only be used in industrial applications (high-demand mode). More information and technical data → Internet: manual

Vertical stacking variant for valve terminal VTSA, width 26 mm

The circuit symbol represents a valve with a proximity sensor with switching output signal with an N/O

contact. In accordance with ISO 1219-1, this symbol applies to both N/O contacts as well as N/C

The switching element function of the sensors used here is designed as an N/C contact.



1)

contacts.

The pilot air switching valve with integrated piston position sensing on manifold sub-base for valve terminal VTSA is supplied with electrical power regardless of the type of electrical actuation of the valve terminal.

This module is supplied

pre-assembled together with the valve terminal VTSA. No other assembly steps are required before installation. The piston position sensing feature of the inductive PNP proximity sensor is realised using a cable and a push-in connector in the size M12x1 to EN 61076-2-104.

- 📲 - Note

The pilot air switching valve can only be operated on the valve terminal VTSA in combination with a right-hand end plate for external pilot air type VABE-S6-1RZ-.... Port 14 on the right-hand end plate must be sealed for this.

Valve terminals type 44/45, VTSA/VTSA-F, NPT

Technical data – Pilot air switching valve – Width 26 mm

Function - Pneumatic/electrical interlinking



The function for switching off the pilot air is achieved on this module by combining the vertical stacking plate type VABF-S4-1-S with the single solenoid 5/2-way valve type VSVA-B-M52-MZD-A1-1T1L-APX-0,5. The valve terminal is not supplied with any pilot air via the right-hand end plate type VABE-S6-1 (ident. code XS, external pilot air). Port 14 on the end plate is sealed. The pilot air for the valve is branched from duct (1) in the vertical stacking plate and redirected to the pilot air duct (14) of the valve terminal when the valve is in the switching position. Ports (2) and (4) of the manifold sub-base are sealed with blanking plugs. The switching operation of the solenoid valve can be monitored by sensing the proximity sensor in the solenoid valve. This is done by linking the control signal and signal change of the proximity sensor so that it is possible to check whether the piston spool of the solenoid valve is reaching or leaving the normal position (expectations). The piston spool of the solenoid valve is designed so that pneumatic short circuits between the ports (2) and (4) are ruled out (freedom from overlap).

- 🗍 - Note

A valve from the VTSA modular system can be planned or configured to the right of the valve with piston position sensing on the vertical stacking plate of the pilot air switching valve.

Genera	technical	data

Pilot air switching valve Width Design Sealing principle Actuation type Type of control	Vertical stacking plate type VABF-S4-1-S and solenoid valve type VSVA-B-M52-MZD-A1-1T1L-APX-0,5 mounted on valve terminal VTSA 26 mm Piston spool valve Soft Electrical Piloted
Design Sealing principle Actuation type	26 mm Piston spool valve Soft Electrical Piloted
Design Sealing principle Actuation type	Piston spool valve Soft Electrical Piloted
Sealing principle Actuation type	Soft Electrical Piloted
Actuation type	Electrical Piloted
,,	Piloted
Type of control	
Type of mounting	Via through-hole, on manifold sub-base
Mounting position	Any
Pneumatic connections	
Supply port 1	Via the manifold sub-base of the valve terminal
Exhaust port 3/5	Via the manifold sub-base of the valve terminal
Working lines 2/4	Sealed with blanking plug type U-1/4-B-NPT
Pilot air supply port 14	Via the manifold sub-base of the valve terminal
Pressure gauge	G1/4

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Pilot air switching valve – Width 26 mm

Standard nominal flow rate [l/min]	
Pilot air switching valve	Vertical stacking plate type VABF-S4-1-S and solenoid valve terminal VTSA
	solehold valve type vova b 1052 m2b TA TTTE ATA 0,5 mounted on valve terminat v 15A
Width	26 mm
Valve flow rate, port 1 to 4	950
Vertical stacking plate flow rate,	450
port 4 to 14	

Operating and environment	al conditions	5
Pilot air switching valve		Vertical stacking plate type VABF-S4-1-S and
		solenoid valve type VSVA-B-M52-MZD-A1-1T1L-APX-0,5 mounted on valve terminal VTSA
Operating medium		Filtered compressed air, lubricated or unlubricated
Grade of filtration	[µm]	40 (average pore size)
Operating pressure	[bar]	3 10
Noise level LpA	[dB (A)]	85
Ambient temperature	[°C]	-5 +50
Temperature of medium	[°C]	-5 +50
Fire protection classification	to UL94	HB
Note on materials		Contains PWIS (paint-wetting impairment substances), RoHS-compliant

Switching times [ms]		
Valve		VSVA-B-M52-MZD-A1-1T1L-APX-0,5
Width		26 mm
Valve switching time	On	20
	Off	54
Valve sensor switching	On	60
time ¹⁾	Off	11

1) Valve sensor switching time off: period of time from coil being energised to sensor being switched off when using a PNP sensor. Valve sensor switching time on: period of time from coil being de-energised to 0-L edge at the sensor when using a PNP sensor.

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Pilot air switching valve – Width 26 mm

Electrical data – Pilot air swi	tching valve	3
Pilot air switching valve		Vertical stacking plate type VABF-S4-1-S and solenoid valve type VSVA-B-M52-MZD-A1-1T1L-APX-0,5 mounted on valve terminal VTSA
Width		26 mm
Nominal operating voltage	[V DC]	24
Permissible voltage	[%]	±10
fluctuations		
Surge capacity	[kV]	2.5
Degree of contamination		3
Power consumption	[W]	1.6 W
Max. magnetic disruption	[mT]	60
field		
Piston position sensing		Normal position via sensor
Duty cycle	[%]	100
Protection class to DIN EN 60	529	IP65, NEMA 4 (for all types of signal transmission in assembled state)

Electrical data – Sensor		
Electrical connection		Plug M12x1, 4-pin
Cable length	[m]	0.5
Switching output		PNP
Switching element function		N/C contact
Switching status display		Yellow LED
Operating voltage range	[V DC]	10 30
Residual ripple	[%]	±10
Rated operating voltage	[V DC]	24
Sensor idle current	[mA]	<=10
Max. output current	[mA]	200
Voltage drop	[V]	<=2
Max. switching frequency	[Hz]	5,000
Protection against short circ	uit	Pulsed
Protection against polarity re	eversal	For all electrical connections
for sensor		
Measuring principle		Inductive
Piston position sensing		Valve normal position via sensor

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Pilot air switching valve – Width 26 mm

FESTO

Materials	
Pilot air switching valve	
Width	26 mm
Sub-base/manifold sub-base	Die-cast aluminium
Valve	Die-cast aluminium, reinforced polyamide
Seals	Nitrile rubber, elastomer (support made of steel)
Screws	Galvanised steel
Sensor housing	High-alloy stainless steel
Sensor cable sheath	Polyurethane

Product weight

Pilot air switching valve		Vertical stacking plate type VABF-S4-1-S without solenoid valve and adjacent configuration-dependent valve terminal
		components
Width		26 mm
Approx. weight	[g]	576

Valve terminals type 44/45, VTSA/VTSA-F, NPT Ordering data – Pilot air switching valve – Width 26 mm

FESTO

Ordering data					
Designation	Code	Valve function	Width	Part No.	Туре
Solenoid valve, 24 V I	DC, plug-ir	design for valve terminal VTSA			
	-	5/2-way valve, single solenoid, mechanical spring return, with switching position sensing via inductive sensor with PNP output and 0.5 m cable with 4-pin sensor push-in connector M12x1	26 mm	570850	VSVA-B-M52-MZD-A1-1T1L-APX-0 ,5
Vertical stacking plate	e for pilot a	ir switching valve for valve terminal VTSA			
0 · · · · · · · · · · · · · · · · · · ·	-	Vertical stacking plate, for switching pilot air from duct 1 to duct 14	26 mm	570851	VABF-S4-1-S
Cover					
P	-	Cover cap for manual override, non-detenting	10 pieces	541010	VAMC-S6-CH

- 🌡 - Note

The sensors contained in the valves must not be replaced themselves. Incorrect assembly can result in malfunctions or damage to the valve. Please contact Festo in the event of a malfunction.

Valve terminals type 44/45, VTSA/VTSA-F, NPT

Soft-start valve - Width 43 mm

Function



- Flow rate
 Pressurisation: 3,000 l/min
 Exhaust: 3,300 l/min
- **ГЈ** Module width 1: 43 mm
 - Temperature range -5 ... +50 °C
 - Operating pressure
 2 ... 10 bar



Description

Function

- The purpose of the soft-start valve is to slowly and safely build up the supply pressure in duct 1 of the valve terminal or to quickly vent it. Switch-on takes place in two stages:
- First the working pressure provided for duct 1 gradually increases (the speed can be adjusted using a flow control screw).

Diagnostics

Pilot air supply

The piston position of the soft-start valve can be monitored by a sensor with integrated LED display. This sensor registers whether the valve has • Once the working pressure in duct 1 reaches a previously set value, the soft-start valve switches the full operating pressure at duct 1 of the valve terminal.

The switching point for full operating pressure is set to 4 bar at the factory,

but can be changed using an adjusting screw.

The full operating pressure is applied to duct 14 (pilot air) at all times. This pressure causes the valves on the valve terminal to immediately move to the required switching position. When the valve is not switched, duct 1 of the valve terminal is exhausted via the soft-start valve's exhaust port. A self-resetting manual override is available for maintenance and service purposes.

FESTO

switched and thus whether the valve terminal is being supplied with air. Pressure sensing via a pressure gauge (optional) is also possible. The soft-start valve can alternatively be ordered with a sensor (retrofitting of a sensor is very complicated due to the necessary sensor calibration).

Connecting cables with integrated LED

display are provided for displaying the

signal status.

The valve terminal can either be supplied with internal pilot air via the soft-start valve or with internal or

external pilot air via the various end plate variants. The type of pilot air supply is determined by the seal of the

soft-start valve. The scope of delivery of the soft-start

valve includes both the seal for

internal pilot air supply and the seal for external pilot air supply.

Restrictions Compressed air supply Exhaust air Reverse operation Pilot air supply There must be no other elements Exhaust air cannot be expelled via the If internal pilot air supply (duct 14) The soft-start valve is not approved for supplying compressed air in the soft-start valve. If it is being operated via the soft-start valve is chosen, there reverse operation. pressure zone in which the soft-start in a pressure zone with duct 3/5 must be no other pilot air supply valve is being operated. separated, an exhaust plate is within the valve terminal. required.

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Soft-start valve – Width 43 mm

General technical data	
Design	Piston spool valve
Actuation type	Electrical
Sealing principle	Soft
Type of mounting	On sub-base
Mounting position	Any
Valve function	Soft-start function
Manual override	Non-detenting
Reset method	Mechanical spring
Type of control	Piloted
Pilot air supply	Internal, external
Direction of flow	Non-reversible
Piston position sensing	Switching position via sensor

Standard nominal flow rate [l/min]	
Pressurisation	3,000
Exhaust	3,300

Operating and environmental conditions			
Туре		VABF-S6-1-P5A42A	VABF-S6-1-P5A41
Operating pressure	[bar]	2 10	
Switchover pressure	[bar]	4	
presetting			
Operating medium		Filtered compressed air, lubricated or unlubricated, grade of	filtration 40 µm
Ambient temperature	[°C]	-5 +50	
CE mark		To EU EMC Directive	-
(see declaration of conformity)			

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Soft-start valve – Width 43 mm

Valve switching times [ms]		
Switching times	On	17
	Off	50
	Change-	-
	over	

Electrical data – Soft-start valve		
Туре	VABF-S6-1-P5A41	VABF-S6-1-P5A42A
Electrical connection	Plug type C to DIN EN 175301-803, square design	
Nominal operating voltage [V]	24 DC	110 AC
Operating voltage range [V]	24 DC ±10%	110 AC ±10%
Coil characteristics	24 V DC: 2.5 W	110 V AC: 50/60 Hz, 3 VA pull:
		110 V AC: 50/60 Hz, 2.4 VA hold
Protection class to EN 60529	IP65, NEMA 4	·

Electrical data – Sensor		
Electrical connection		Plug M12x1, 4-pin
Switching output		PNP
Switching element function		N/O contact
Switching status display		Yellow LED
Operating voltage range	[V DC]	10 30
Residual ripple	[%]	±10
Rated operating voltage	[V DC]	24
Sensor idle current	[mA]	<=10
Max. output current	[mA]	200
Voltage drop	[V]	<=2
Max. switching frequency	[Hz]	3,000
Protection against short circu	ıit	Pulsed
Protection against polarity		For all electrical connections
reversal for sensor		
Measuring principle		Inductive
Piston position sensing		Switching position via sensor

Materials	
Housing	Wrought aluminium alloy
Seals	Nitrile rubber
Screws	Galvanised steel

Product weight	
Approx. weight [g]	
Manifold sub-base	570
Soft-start valves without proximity	590
sensor	
Soft-start valves with proximity sensor	605

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Soft-start valve – Width 43 mm



FESTO

Download CAD data **→ www.festo.com**

Valve terminals type 44/45, VTSA/VTSA-F, NPT Ordering data – Soft-start valve – Width 43 mm

Ordering data				
Designation	Code	Description	Part No.	Туре
Soft-start valve, 24	i V DC			
	-	Without sensor output, pneumatic connection 1/2" NPT	558231	VABF-S6-1-P5A4-N12-4-1
	-	With sensor output PNP, pneumatic connection 1/2 " NPT	558232	VABF-S6-1-P5A4-N12-4-1-P
	-	With sensor output NPN, pneumatic connection 1/2" NPT	558234	VABF-S6-1-P5A4-N12-4-1-N
*	•			
Soft-start valve, 11	lo V AC			
	-	Without sensor output, pneumatic connection 1/2" NPT	558229	VABF-S6-1-P5A4-N12-4-2A
AA			· · · · · · · · · · · · · · · · · · ·	
Manifold sub-base				
	-	Pneumatic connection 1/2" NPT	556988	VABV-S6-1Q-N12

Valve terminals type 44/45, VTSA/VTSA-F, NPT Accessories – Soft-start valve – Width 43 mm

Ordering data					
Designation	Code	Description		Part No.	Туре
Proximity sensor					
	-	With integrated switching	PNP	150403	SIEN-M12B-PS-S-L
S S S S S S S S S S S S S S S S S S S		status display via LED (yellow)	NPN	150401	SIEN-M12B-NS-S-L
S					
Protective cap					
	-	M12, for sealing the sensor oper	ning (10 pieces)	165592	ISK-M12
(A)					
Plug socket for elect	rical conne	ection of the soft-start valve			
		Angled socket, 2-pin, for solenoi	d coil, straight plug, M12	188024	MSSD-EB-M12-MONO
Connecting cable fo	r electrical	connection of the proximity sensor		1//250	
	-	Straight socket, M12x1 plug, 4-v	vire, cable length 5 m	164259	SIM-M12-4GD-5-PU
St.					
-	-	Angled socket, 5-pin, M12 plug,	cable length 5 m	541370	NEBU-M12W5-K-5-LE3
2 mil					
		Straight socket, 5-pin, M12 plug	cable length 5 m	541364	NEBU-M12G5-K-5-LE3
		Straight Socket, 5 pm, M12 plug		541504	NEDO-M1209-R-9-LE9
ST. P.C.					
	-	Modular system for connecting c	ables	-	NEBU
38					→ Internet: nebu
OF THE					
Connecting cable fo	r electrical	connection of the soft-start valve			
<u> </u>	1-	Angled socket, type C, 24 V DC,	Cable length 2.5 m	151688	KMEB-1-24-2,5-LED
- B		with LED for switching status	Cable length 5 m	151689	KMEB-1-24-5-LED
() M		display	Cable length 10 m	193457	KMEB-1-24-10-LED
	-	Angled socket, type C,	Cable length 2.5 m	151690	KMEB-1-230AC-2,5
		for solenoid coil 230 V AC	Cable length 5 m	151691	KMEB-1-230-5
	-	Angled socket, type C, 24 V DC,	Cable length 2.5 m	174844	KMEB-1-250-5
		with LED for switching status			
		display	Cable length 5 m	174845	KMEB-2-24-5-LED
×	-	Angled socket, type C,	Cable length 2.5 m	174846	KMEB-2-230AC-2,5
		for solenoid coil 230 V AC	Cable length 5 m	174847	KMEB-2-230-5
Pressure gauge					
	-	0 10 bar, pneumatic connection	on M5	526323	MA-27-10-M5
		1			
Pneumatic connecti					
		blanking plugs, silencers and			
		an be found in the chapter Accesso	ries → page 134		
or on the Internet vi					
internet -> connect	ion techno	logy, silencer, blanking plug			

Valve terminals type 44/45, VTSA/VTSA-F, NPT Individual connection – ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Lubricated for life

Any

18 mm

1⁄8" NPT

1⁄8" NPT

10-32UNF-2B

10-32UNF-2B

1

3/5

2/4

14

12

Via sub-base 1⁄8" NPT

Through-hole to ISO 15407-2

Detenting, non-detenting, covered

FESTO

 - N - Flow rate Width 18 mm: up to 600 l/min Width 26 mm: up to 1,200 l/min Width 42 mm: up to 1,500 l/min Width 52 mm: up to 3,200 l/min - N - Valve width to ISO 15407-2 • 18 mm • 26 mm to ISO 5599-2 • 42 mm (ISO 1) • 52 mm (ISO 2) 	- G - Voltage 24 V DC 110 V AC	<image/>
General technical data	Distance and the last	
Design Sealing principle	Piston spool valve Soft	
Actuation type	Electrical	
Type of control	Piloted	
Exhaust function, with flow control	Via individual sub-base	

26 mm

1⁄4 " NPT

1⁄4 " NPT

1⁄4 " NPT

1⁄8" NPT

1⁄8" NPT

42 mm

3⁄8" NPT

3⁄8" NPT

3⁄8" NPT

1⁄8" NPT

1⁄8" NPT

52 mm

1⁄2" NPT

1⁄2" NPT

1⁄2" NPT

1⁄8" NPT

1⁄8" NPT

Subject to change - 2011/02

Lubrication

Width

Supply port

Exhaust port

Working lines

Type of mounting Mounting position

Manual override

Pneumatic connection

Pilot exhaust air port

External pilot air supply port

Pneumatic connections – NPT thread

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Individual connection – ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

FESTO

Standard nominal flow rate [l/min] Valve function order code ¹⁾	VC	VV	Ν	К	Н	Р	Q	R	М	0	- Ir	D	В	E	G	SA	SB
Width 18 mm							4			Ű	,	5	5	-	Ű	0/1	0.0
Flow rate of valve	700		600						750				700	(2)		1-	1_
	700		600						/ 50				330			-	-
ei (c i · !··i i	500		500						(00								
Flow rate of valve on individual	500		500						600				500		550	-	-
sub-base													330	(د			
Width 26 mm																	
Flow rate of valve	1,35	0	1,25	0					1,40	0			1,4	00 ²⁾		1,400	700
													700	3)			
Flow rate of valve on individual	1,10	0	1,10	0		1,0	00		1,20	0			1,20	00 ²⁾		1,200	700
sub-base													700	3)			
Width 42 mm																	
Flow rate of valve	1,60	0	1,60	0					2,00	0			1,90	<u>102)</u>		1-	1-
	1,00	0	1,00	0					2,00				950				
Flow rate of valve on individual	1,40	0	1,20	0					1,50	0			1,40	00 ¹⁾		-	-
sub-base													800				
Width 52 mm																	
Flow rate of valve	3,50	0	3,00	0					4,00	00			3,50	00 ²⁾		-	-
													1,70				
Flow rate of valve on individual	3,00	0	2,50	0					3,20	0			3,00	00 ²⁾		-	-
sub-base													1,70	003)			

Order code VV not for size 2
 Switching position
 Mid-position

Operating and environment	ntal condition	S
Operating medium		Filtered compressed air, lubricated or unlubricated, inert gases → 57
Grade of filtration	[µm]	40 (average pore size)
Operating pressure	[bar]	-0.9 +10
Ambient temperature	[°C]	-5 +50
PWIS criterion		Free of paint-wetting impairment substances

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Individual connection – ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

FESTO

Pneumatic characteristic da	ita																	
Valve function order code		VC	VV	N	К	Н	Р	Q	R	М	0	J	D	В	G	E	SA	SB
Direction of flow								~	1		-	,	-	-	-	-		
Any		1 -		1 -	1 -	1 -	1 -	1 -	1 -								1 -	
Reversible only		-	-	-	-	-				-	-	-	-	-	-	-	-	-
Non-reversible			-				-	-	-	-	-	-	-	-	-	-		-
				-														
Reset method																		
Pneumatic spring					1 -						-	T -	- 1	-	-	-		
Mechanical spring		-	-	-		-	-	-	-	-		-	-				-	-
·····			1															
Valve switching times																		
Valve function order code ¹⁾		VC	VV	N	К	Н	Р	Q	R	М	0	IJ	D	В	G	E	SA	SB
Width 18 mm, nominal oper	ating voltage					1		4			Ű	,	5	5	Ű	-	0,1	05
Switching times [ms]	On	12	12	V AC	12	12	25	25	25	22	12	1-	1-	15	15	15	1-	-
Switching times [IIIS]	Off	30	30	30	30	30	12	12	12	22	38	-	-	44	44	44	-	-
	Change-	-	-	-	-	- 50	-	-	-	- 20	-	- 11	13	- 44	- 44	-	-	-
	over				 		- 				- 	11	C1			- 		
	UVCI		1			1		1	1	1		1					1	1
Width 26 mm, nominal oper	ating voltage	24 V D	C/110	V AC														
Switching times [ms]	On	24 0 0	20	20	20	20	32	32	32	25	20	-	1-	22	22	22	9/22	9/19
Switching times [ins]	Off	38	38	38	38	38	30	30	30	45	65	-	-	65	65	65	49	36
	Change-	-	-	-	-	-	-	-	-	4 J -	-	18	21	-	-	-	33	32
	over		[-			_	-	_	10	21	_	_		,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	52
	0001																	
Width 42 mm, nominal oper	ating voltage	24 V D	ſ															
Switching times [ms]	On	24 0 0	20	20	20	20	34	34	34	27	22	-	-	22	22	22	1_	1_
Switching times [ins]	Off	38	38	38	38	38	28	28	28	45	60	-	-	65	65	65	-	-
	Change-	-	-	-	-	-	-		-	-	-	16	19	-	-	-	_	-
	over											10	17					
	0001																	
Width 42 mm, nominal oper	ating voltage	110 V	AC															
Switching times [ms]	On	22	22	22	22	22	34	34	34	20	20	-	-	22	22	22	-	-
errice finol	Off	46	46	46	46	46	38	38	38	55	55	-	-	68	68	68	-	-
	Change-	-	-	-	-	-	-	-	-	-	-	16	19	-	-	-	-	-
	over							1		1		10	1					
	0101																	
Width 52 mm, nominal oper	ating voltage	24 V D	C with	holding	curren	t reduct	tion											
Switching times [ms]	On	14	-	20	20	20	30	30	30	40	20	1-	1-	23	23	23	-	-
	Off	35	-	35	35	35	30	30	30	45	60	-	-	60	60	60	-	-
	Change-	-	-	-	-	-	-	-	-	-	-	18	18	-	-	-	-	-
	over							1		1		1	10					
		1	1	<u> </u>	1	1	1	1	1	1		1			1	1	1	1
Width 52 mm, nominal oper	ating voltage	110 V	AC															
Switching times [ms]	On	35	- -	35	35	35	50	50	50	70	25	-	-	30	30	30	-	-
	Off	70	-	70	70	70	65	65	65	90	110	-	-	100	100	100	-	-
	Change-	-	-	-	-	-	-	-	-	-	-	35	35	-	-	-	-	-
	over							1		1			,,,					
	0101	1	1	1	1	1	1	1	1	1						1	1	1

1) Not for individual sub-base with round plug type VABS ... B-R3

2) Order code SA, switching time 22 ms for control side 12, 9 ms for control side 14 Order code SB, switching time 19 ms for control side 12, 9 ms for control side 14

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Individual connection – ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

Electrical data					
Valve on individual sub-base	5	18 mm	26 mm	42 mm	52 mm
Acceptable current load at 40 °C	[A]	2 (1 A per coil)			
Variants with cable connecto					
Operating voltage range	[V AC]	110 ±10% (50 60 Hz) (with	variants with cable and spring	loaded terminal VABSK1/C	1)
Surge capacity	[kV]	4			
Degree of contamination		3			
Duty cycle	[%]	100			

-Note -

A cable connector is needed to ensure the IP protection class and to protect against tensile load, twisting and bending.

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Individual connection – ISO 15407-2, width 18 and 26 mm

Certifications	
This product is certified for use in the AT	EX zone in accordance with the EU ATEX Directive
ATEX category for gas	3G
Explosion ignition protection type	Ex nA II T3 X
for gas	
ATEX category for dust	II 3D
Explosion ignition protection type	Ex tD A22 IP65 T125° C X
for dust	
ATEX temperature rating [°C]	-5 ≤ Ta ≤ +50
Certification	cULus recognized (OL)
Protection class	IP65, NEMA 4 in assembled state
CE mark ¹⁾	To EU Low Voltage Directive
(see declaration of conformity)	

-Note

The sub-bases with the part numbers shown opposite	• 563066
are ATEX-certified	• 563067
	• 563068
	• 563069
	• 563070
	• 563071
	- (

- 563071 • 567703
 - 567704

Materials								
Width	18 mm	26 mm	42 mm	52 mm				
Sub-base	Die-cast aluminium			Chill-cast aluminium				
Valve	Die-cast aluminium, reinforce	e-cast aluminium, reinforced polyamide						
Seals	Nitrile rubber, elastomer (supp	rile rubber, elastomer (support made of steel)						

Product weight				
Approx. weight [g]				
Width	18 mm	26 mm	42 mm	52 mm
Valves				
 5/3-way valve 	191	320	456	780
(code: B, G, E)				
 5/3-way valve 	-	301	-	-
(code: SA, SB)				
 5/2-way valve, single 	163	293	426	702
solenoid				
(code: M, O)				
 5/2-way valve, double 	172	276	439	732
solenoid				
(code: J, D)				
 2x 3/2-way valve 	190	335	442	740
(code: N, K, H, P, Q, R)				
 2x 2/2-way valve 	190	335	442	740
(code: VC, VV)				
Individual sub-base	192	302	386	815

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Individual connection – ISO 15407-2, width 18 and 26 mm

FESTO



10-32UNF-2B

VABS-S4-2S-N18-B-K2	1⁄8" NPT

Note: This product conforms to ISO 1179-1 and to ISO 228-1

M20x1.5

Valve terminals type 44/45, VTSA/VTSA-F, NPT Technical data – Individual connection – ISO 15407-2, width 18 and 26 mm

FESTO



● Note: This product conforms to ISO 1179-1 and to ISO 228-1

Valve terminal VTSA

Technical data – Individual connection – ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

FESTO



Туре	D1	D2	D3	D4
External pilot air supply				
VABS-S2-1S-N38-K1	3⁄8" NPT	1⁄8" NPT	1⁄8" NPT	M20x1.5
VABS-S2-1S-N38-C1	3⁄8" NPT	1⁄8" NPT	1⁄8" NPT	M20x1.5
Internal pilot air supply				
VABS-S2-1S-N38-B-K1	3⁄8" NPT	1⁄8" NPT	-	M20x1.5
VABS-S2-1S-N38-B-C1	3⁄8" NPT	1⁄8" NPT	-	M20x1.5

 $\cdot \parallel \cdot ~$ Note: This product conforms to ISO 1179-1 and to ISO 228-1

- Note

Electrical connection

- VABS-...-K1: open end
- VABS-...-C1: spring-loaded terminal

Valve terminal VTSA

Technical data – Individual connection – ISO 15407-2, width 18 and 26 mm; ISO 5599-2, width 42 and 52 mm

FESTO



Туре	D1	D2	D3	D4
External pilot air supply				
VABS-S2-2S-N12-K1	1⁄2" NPT	1⁄8" NPT	1⁄8" NPT	M20x1.5
VABS-S2-2S-N12-C1	1⁄2" NPT	1⁄8" NPT	1⁄8" NPT	M20x1.5
Internal pilot air supply				
VABS-S2-2S-N12-B-K1	1⁄2" NPT	1⁄8" NPT	-	M20x1.5
VABS-S2-2S-N12-B-C1	1⁄2" NPT	1⁄8" NPT	-	M20x1.5

Note: This product conforms to ISO 1179-1 and to ISO 228-1

- Note

Electrical connection

• VABS-...-K1: open end

• VABS-...-C1: spring-loaded terminal

Valve terminals type 44/45, VTSA/VTSA-F, NPT Accessories – Individual connection – ISO 15407-2, width 18 and 26 mm

Ordering data							
Designation	Code	Description	Width	Part No.	Туре		
Individual sub-base	, port patte	ern to ISO 15407-2, electrical connection via cable termina	als	•			
	Thread	Threaded connection, internal pilot air supply					
	-	Lateral connections, ½" NPT	18 mm	541068	VABS-S4-2S-N18-B-K2		
	-	Lateral connections, 1⁄4 " NPT	26 mm	541066	VABS-S4-1S-N14-B-K2		
	Thread	ed connection, external pilot air supply					
	-	Lateral connections, ½" NPT	18 mm	539724	VABS-S4-2S-N18-K2		
	-	Lateral connections, 1/4 " NPT	26 mm	539726	VABS-S4-1S-N14-K2		
			۰. ۵	•			
ndividual sub-base		ern to ISO 5599-2, electrical connection via cable (open en	d)				
	Ihreade	ed connection, internal pilot air supply		1			
13 03 00 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	-	Lateral connections, 3/8" NPT	42 mm	546103	VABS-S2-1S-N38-B-K1		
	-	Lateral connections, 1/2" NPT	52 mm	555642	VABS-S2-2S-N12-B-K1		
		ed connection, external pilot air supply		1			
	-	Lateral connections, 3/8" NPT	42 mm	546100	VABS-S2-1S-N38-K1		
	-	Lateral connections, 1⁄2" NPT	52 mm	555637	VABS-S2-2S-N12-K1		
ndividual sub-base	nort natte	ern to ISO 5599-2, electrical connection via spring-loaded	terminal				
		ed connection, internal pilot air supply					
	-	Lateral connections, 3/8" NPT	42 mm	546763	VABS-S2-1S-N38-B-C1		
10000000000000000000000000000000000000	-	Lateral connections, 1/2" NPT	52 mm	555644	VABS-S2-2S-N12-B-C1		
		ed connection, external pilot air supply	52 1111	333044			
\checkmark	-	Lateral connections, 3/8" NPT	42 mm	546761	VABS-S2-1S-N38-C1		
	_	Lateral connections, ¹ / ₂ " NPT	52 mm	555639	VABS-S2-15-N30-C1		
			52.1111				
Plug socket for elect	rical conne	ection of individual valves					
	-	Angled socket, 4-pin, screw terminal, union nut M12		185498	SEA-M12-4WD-PG7		
				•			
Connecting cable for	r electrical	connection of individual valves at the individual electrical	connection				
	-	Modular system for connecting cables		-	NEBU		
2 Start					➔ Internet: nebu		
SCIE SC							
					Technical data Nutamat make		
illuminating seal for	r plug patte	ern DIN EN 175301-803, type C		454747	Technical data → Internet: meb-I		
	-	12 24 V DC		151717	MEB-LD-12-24DC		
	-	230 V AC		151718	MEB-LD-230AC		
	1			1			
Pneumatic connecti							
		blanking plugs, silencers and					
		an be found in the chapter Accessories $ ightarrow$ page 134					
or on the Internet vi							
nternet → connect	ion techno	logy, silencer, blanking plug					

Valve terminals type 44/45, VTSA/VTSA-F, NPT

Ordering data				
Designation	Code	Description	Part No.	Туре
Push-in fitting				
	-	Connecting thread 1/4" NPT for tubing O.D. 1/2"	190681	QS-1/4-1/2-U
		Connecting thread 1/4" NPT for tubing O.D. 3/8"	153611	QS-1/4-3/8-U
		Connecting thread 1/4" NPT for tubing O.D. 5/16"	153609	QS-1/4-5/16-U
OF P		Connecting thread 1/8" NPT for tubing O.D. 3/8"	190679	QS-1⁄8-3⁄8-U
		Connecting thread 1/8" NPT for tubing O.D. 1/4"	153605	QS-1/8-1/4-U
		Connecting thread 1/8" NPT for tubing O.D. 5/16"	153608	QS-1/8-5/16-U
		Connecting thread 3/8" NPT for tubing O.D. 1/2"	153614	QS-3/8-1/2-U
		Connecting thread 3/8" NPT for tubing O.D. 3/8"	153612	QS-3⁄8-3⁄8-U
		Connecting thread 1/2" NPT for tubing O.D. 5/8"	190682	QS-1/2-5/8-U
		Connecting thread 1/2" NPT for tubing O.D. 1/2"	153615	QS-1/2-1/2-U
Female hose connect	or			
	-	For right-hand end plate 3/4 " NPT	564848	N-¾-P-19-NPT
a Dub		For right-hand end plate R1	752414	N-1-P-19-R-NPT
		- ,		
		For adapter plate R1		
Silencer				
	-	Connecting thread 1/8" NPT	12638	U-1/8-B-NPT
See .		Connecting thread 1/4 " NPT	12639	U-1/4-B-NPT
0		Connecting thread 1/2" NPT	12741	U-1/2-B-NPT
		Connecting thread 3/4 " NPT	566823	U-¾-B-NPT
		Connecting thread 1 " NPT	571280	U-1-NPT-SA
	·	·	<u> </u>	
Blanking plug				
	-	Connecting thread 1/8" NPT	173985	B-1/8-NPT
		Connecting thread 1/4 " NPT	174165	B-¼-NPT
		Connecting thread 1/2" NPT	31785	B-1/2-NPT
		Connecting thread 3/4" NPT	31786	B-¾-NPT
		Connecting thread 1 " NPT	31787	B-1-NPT
Other pneumatic con				
A selection of possible fittings, blanking plugs and silencers can be found				
on the Internet via the individual search terms:				
Internet → connecti	on technology,	silencer, blanking plug		

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components Complete custom engineered solutions



Custom Control Cabinets Comprehensive engineering support and on-site services



Complete Systems Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical Electromechanical actuators, motors, controllers & drives



Pneumatics Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.





© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



FSC Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive Mississauga, Ontario L4W 5G4 Canada

USA Customers:

For ordering assistance, Call: 1.800.99.FESTO (1.800.993.3786) Fax: 1.800.96.FESTO (1.800.963.3786) Email: customer.service@us.festo.com For technical support, Call: 1.866.GO.FESTO (1.866.463.3786) Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com Canadian Customers:

 Call:
 1.877.GO.FESTO (1.877.463.3786)
 Fax:
 1.877.FX.FESTO (1.877.393.3786)

 Email:
 festo.canada@ca.festo.com
 Fax:
 festo.canada@ca.festo.com

USA Headquarters

Festo Corporation 395 Moreland Road P.O. Box 18023 Hauppauge, NY 11788, USA www.festo.com/us

USA Sales Offices

Appleton North 922 Tower View Drive, Suite N Greenville, WI 54942, USA

Boston 120 Presidential Way, Suite 330 Woburn, MA 01801, USA

Chicago 1441 East Business Center Drive Mt. Prospect, IL 60056, USA Dallas

1825 Lakeway Drive, Suite 600 Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center 2601 Cambridge Court, Suite 320 Auburn Hills, MI 48326, USA

New York 395 Moreland Road Hauppauge, NY 11788, USA Silicon Valley

4935 Southfront Road, Suite F Livermore, CA 94550, USA

Central USA

Festo Corporation 1441 East Business Center Drive Mt. Prospect, IL 60056, USA Phone: 1.847.759.2600 Fax: 1.847.768.9480



United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788 Phone: 1.631.435.0800; Fax: 1.631.435.8026; Email: info@festo-usa.com www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4 Phone: 1.905.624.9000; Fax: 1.905.624.9001; Email: festo.canada@ca.festo.com www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquinahuac, 54020 Tlalnepantla, Edo. de México Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65; Email: Festo.mexico@mx.festo.com www.festo.com/mx

 Western USA

 Festo Corporation

 4935 Southfront Road,

 Suite F

 Livermore, CA 94550, USA

 Phone: 1.925.371.1099

 Fax:
 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com